

Chemlok® 219 Primer and/or Adhesive

Technical Data Sheet

Chemlok® 219 adhesive can be used as either a one-coat adhesive or a primer in combination with Chemlok 213 adhesive for applications that require increased environmental resistance. It is composed of a mixture of organic resins and polymers in an organic solvent system.

Chemlok 219 adhesive is used for bonding a wide variety of both polyether and polyester castable urethanes to metal, as well as bonding certain thermoplastic polyurethanes (TPU).

Features and Benefits:

Versatile – bonds a wide variety of polyether and polyester castable urethanes of varying hardness, based on both TDI and MDI; can be used as a primer.

Economical – eliminates the need to inventory several adhesives due to the adhesive's versatility.

Convenient – requires only a single coat for most adhesive applications, minimizing application costs.

Time Saving – requires no agitation in preparation for use or during application, saving application time and reducing the potential for application errors. Non-settling Chemlok 219 adhesive is ready to dip or brush when opened.

Fast Drying – dries fast to allow rapid turnaround times, reducing the number of coated parts kept in inventory.

Elastomers:

- Millable Urethane
- Castable Urethane
- Thermoplastic Urethane (TPU)

Application:

Surface Preparation – Thoroughly clean metal surfaces prior to application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

Mixing – No agitation is required before or during use. Chemlok 219 adhesive is clear to amber in color with no suspended materials; Chemlok 219 adhesive can be used as received.

If dilution is needed, use MIBK or denatured ethanol. Note proper dilution for the various application methods is best achieved by experience. Give careful attention to agitation since dilution will accelerate settling.

Applying – Apply adhesive in a uniformly thin coat by brush, spray or dip methods. Thicker adhesive films caused by repeated brushing or improper dipping drainage can compromise performance.

Regardless of application method, the dry film thickness of Chemlok 219 adhesive should be 12.7 micron (0.5 mil).

Typical Properties*

Appearance	Clear to Amber Liquid
Viscosity, cps @ 25°C (77°F) Brookfield LVT Spindle 2, 30 rpm	50 - 110
Density kg/m ³ (lb/gal)	880 - 910 (7.3 - 7.6)
Solids Content by Weight, %	23.5 - 27.0
Flash Point (Seta), °C (°F)	14 (58)
Solvents	Ethanol, Methyl Isobutyl Ketone (MIBK)

*Data is typical and not to be used for specification purposes.



ENGINEERING YOUR SUCCESS.

Chemlok 219 adhesive doubles as an excellent primer for Chemlok 213 adhesive. For castable urethane, the properties of Chemlok 219 and Chemlok 213 adhesives are complimentary - Chemlok 219 adhesive provides excellent protection as a primer for the metal; Chemlok 213 adhesive bonds well to RIM, TPU and castable polyurethanes. Chemlok 213 adhesive is also tolerant of processing conditions such as long prebakes. Together, they increase resistance to a variety of environmental elements.

If prebake lasts longer than one hour at 100°C (212°F), use Chemlok 219 adhesive as a primer with Chemlok 213 adhesive. Chemlok 219 adhesive is a heat-reactive system, therefore, do not allow excessive time and temperature during the prebake stage. When used with Chemlok 213 adhesive, both systems will tolerate prebakes as long as 16 hours at 121°C (250°F) or as high as 163°C (325°F) for 2 hours.

Drying – Allow coated parts to air-dry for 30-45 minutes at room temperature.

Shelf Life/Storage:

Shelf life is one year from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container. Do not store or use near heat, sparks or open flame.

Cautionary Information:

Before using this or any Parker LORD product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker LORD has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker LORD does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING – USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

©2020 Parker Hannifin - All Rights Reserved

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

OD DS3110 12/20 Rev.11



Parker LORD
Engineered Materials Group

111 LORD Drive
Cary, NC 27511-7923
USA

phone +1 877 ASK LORD (275 5673)

www.lord.com