

CHEMLOK® 205 PRIMER AND/OR ADHESIVE

Technical Data Sheet

Chemlok® 205 primer/adhesive is a heat-activated material designed for use as either a substrate primer or as a one-coat adhesive for bonding unvulcanized nitrile elastomer compounds. It is composed of a mixture of polymers, organic compounds and mineral fillers dissolved or dispersed in an organic solvent system.

Features and Benefits

Versatile: can be used as a primer under a wide variety of Chemlok covercoat adhesives such as the Chemlok 230 series and Chemlok 6000 series adhesives.

Convenient: can be used as a one-coat adhesive to bond some nitrile rubber compounds to rigid substrates during vulcanization.

Easy to Apply: applies easily by brush, dip, spray or roll coat methods; suitable for existing production lines.

Durable: provides high tear and cohesive strength, as well as excellent environmental resistance when used in combination with Chemlok covercoat adhesives.

Elastomers

- Nitrile (NBR)
- Polyacrylate (ACM)

Application

Surface Preparation: Thoroughly clean metal surfaces prior to application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

Apply Chemlok 205 primer/adhesive to stainless steel, aluminum, brass or other nonferrous substrates within one-half hour after cleaning. For ferrous substrates such as steel, a longer layover can be tolerated if no rust is formed.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

Mixing: Thoroughly stir primer/adhesive before use, and agitate sufficiently during use to keep dispersed solids uniformly suspended. If dilution is needed, use ketone-type solvents such as MEK and MIBK. Note proper dilution for the various application methods is best achieved by experience. Give careful attention to agitation since dilution will accelerate settling.

Typical Properties*

Appearance	Gray Liquid
Viscosity, cps @ 25°C (77°F) Brookfield LVT Spindle 2, 30 rpm	85-165
Density kg/m ³ (lb/gal)	920.0-970.0 (7.7-8.1)
Solids Content by Weight, %	22-26
Flash Point (Seta), °C (°F)	14 (58)
Solvents	MIBK, MEK, Xylene

*Data is typical and not to be used for specification purposes.

Applying: Apply primer/adhesive by brush, dip, roll coat, spray or any method that gives a uniform coating and avoids excessive runs or tears.

Normally the dry film thickness of Chemlok 205 primer/adhesive should be 5.1-10.2 micron (0.2-0.4 mil). When using Chemlok 205 primer/adhesive over grit blasted substrates or when using Chemlok 205 primer/adhesive as a nitrile adhesive, apply a dry film thickness at the high end of the range. For all other applications (i.e., swaging or smooth substrates), apply Chemlok 205 primer/adhesive at the low end of the film thickness range.

Drying/Curing: Thoroughly dry coated parts before applying the covercoat adhesive. This will take approximately 30-45 minutes at room temperature. It is best to use temperatures of 65-93°C (150-200°F) and abundant circulating air; however, forced air drying is possible at temperatures up to 121°C (250°F) for short periods of time. Maximum air flow at minimum temperatures will give the best results. After parts have dried, apply Chemlok covercoats using similar application methods.

Cleanup: Clean areas with a rag as soon as possible using MEK.

Shelf Life/Storage

Shelf life is one year from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
www.parker.com/EPM

DS3172E OD 12/25 Rev.8

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

© 2025 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.