

CHEMLOK® 213 ADHESIVE

Technical Data Sheet

Chemlok® 213 adhesive is a one-coat adhesive used to bond castable and RIM urethane elastomers to metal. It is composed of a mixture of polymers, curatives and pigments dissolved in an organic solvent system.

Chemlok 213 adhesive can also be used to bond a wide variety of both polyether and polyester castable urethanes to metal, as well as bond certain thermoplastic polyurethanes (TPU).

Features and Benefits

Versatile: bonds metal to a wide variety of polyether and polyester castable urethanes of varying hardness, based on both TDI and MDI.

Economical: eliminates the need to inventory several adhesives due to the adhesive's versatility.

Convenient: requires only a single coat for most applications, minimizing application costs; bonds RIM urethane elastomers directly to aluminum or steel without the need for primers or prebaking.

Process Compatible: accommodates a wide range of processing conditions, including extended prebake.

Environmentally Resistant: adds durability for harsh environment exposure, including salt spray and water and temperature exposures, when used with Chemlok 219 primer.

Time Saving: requires no agitation in preparation for use or during application, saving application time and reducing the potential for application errors. Non-settling Chemlok 213 adhesive is ready to dip or brush when opened.

Fast Drying: dries fast to allow rapid turnaround times, reducing the number of coated parts kept in inventory.

Durable: provides bond strengths greater than the tear strength of the urethane substrate.

Elastomers

- Millable Urethane
- Castable Urethane
- Thermoplastic Urethane (TPU)

Application

Surface Preparation: Thoroughly clean metal surfaces prior to application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

Mixing: No agitation is required before or during use. If dilution is needed, use Chemlok 248 thinner. Slowly add Chemlok 248 thinner to Chemlok 213 adhesive while stirring to prevent shocking the adhesive system. For brush and dip application, use a ratio of four parts adhesive to one part thinner, by volume. For spray application, use a ratio of one part adhesive to one part thinner, by volume. Give careful attention to agitation since dilution will accelerate settling.

Typical Properties*

Appearance	Blue Liquid
Viscosity cps @ 25°C (77°F) Brookfield LVT Spindle 2, 30 rpm	100 - 300
seconds Zahn Cup #3	20 - 35
Density kg/m ³ (lb/gal)	870 - 910 (7.3 - 7.6)
Solids Content by Weight, %	20.5 - 23.5
Flash Point (Seta), °C (°F)	5 (41)
Solvents	MEK, Acetate Blend, Xylene

*Data is typical and not to be used for specification purposes.

Applying: Apply adhesive in a uniformly thin coat by brush, spray or dip methods. To avoid film bubbling, do not apply Chemlok 213 adhesive to substrates hotter than 82°C (180°F).

Regardless of application method, dry film thickness of Chemlok 213 adhesive should be 19.05-31.75 micron (0.75-1.25 mil). Thicker adhesive films caused by repeated brushing or improper dipping drainage can compromise bond strength.

Chemlok 219 adhesive is an excellent primer to use with Chemlok 213 adhesive. For castable urethane, the properties of Chemlok 219 and Chemlok 213 adhesives are complimentary - Chemlok 219 adhesive provides excellent protection as a primer for the metal; Chemlok 213 adhesive bonds well to RIM, TPU and castable polyurethanes. Chemlok 213 adhesive is also tolerant of processing conditions such as long prebakes. Together, they increase resistance to a variety of environmental elements.

When using Chemlok 219 adhesive as a primer, first apply Chemlok 219 adhesive and allow it to air-dry. Then apply Chemlok 213 adhesive and allow to air-dry. The combination is then prebaked at 121°C (250°F) for the desired time.

Drying/Curing: Allow coated parts to air-dry for 30-60 minutes at room temperature. Forced drying can speed the process at temperatures up to 93°C (200°F).

After application on a part, the adhesive is precured on the part to increase the overall environmental resistance. The large metal parts, which act as heat sinks, are preheated prior to casting.

Chemlok 213 adhesive allows a wide tolerance for prebake conditions. Without compromising the bond, the adhesive can prebake for as long as 16 hours in temperatures as high as 121°C (250°F).

When used with Chemlok 219 adhesive as a primer, both systems will tolerate prebakes as high as 163°C (325°F) for 2 hours.

When using the two-coat system of Chemlok 219 adhesive as a primer under Chemlok 213 adhesive, optimum performance requires prebaking. A minimum of two hours at 121°C (250°F) is recommended. For large parts such as roller cores, baking may extend from four to eight hours at 121°C (250°F), depending upon size.

Cleanup: Remove uncured adhesive with solvents such as MEK and xylene. Remove cured adhesive by grit blasting, grinding or belt sanding.

Shelf Life/Storage

Shelf life is one year from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container. Do not store or use near heat, sparks or open flame.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
www.parker.com/EPM

DS3179E OD 12/25 Rev.7

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

© 2025 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.