

CHEMLOK® 608 ADHESIVE

Technical Data Sheet

Chemlok® 608 adhesive is a one-coat adhesive designed for bonding unvulcanized silicone elastomers to various rigid substrates.

Chemlok 608 adhesive also provides excellent adhesion to a wide variety of commercially available silicone compounds which require a post cure.

Features and Benefits

Convenient: requires only a single coat, reducing labor, inventory and shipping costs.

Versatile: offers excellent adhesion to a variety of silicone compounds.

Environmentally Resistant: provides excellent resistance to many aggressive service environments.

Economical: used for most applications at dilutions of 500-1000% with dry alcohol solvents.

Elastomers

- Silicone (VMQ, PMQ, PVMQ) - peroxide cure

Application

Surface Preparation: Thoroughly clean metal surfaces prior to application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

Mixing: Chemlok 608 adhesive is best applied as a dilute solution. Specific dilution rates are dependent upon rubber type, substrate and bond performance requirements. Best results have been obtained using methanol in a range from 5-10 parts solvent to 1 part adhesive, by volume.

Applying: Apply adhesive in a uniformly thin coat.

Drying/Curing: Allow applied adhesive to air-dry for 10-30 minutes at room temperature. Drying time can be shortened by using heat sources to facilitate drying. Temperatures in the range of 65-93°C (150-200°F) for 5-15 minutes may be used for force drying. Maximum air flow at minimum temperature will give the best results.

Coated parts may be bonded immediately after air-drying. For best results, the parts should be coated and bonded in the same day.

A variety of commercially available silicone stocks have been successfully bonded with Chemlok 608 adhesive. Use press-cure times and temperatures recommended by the elastomer manufacturers for each compound.

Silicone-to-metal bonds formed with Chemlok 608 adhesive are resistant to most aggressive environments encountered in end-use service.

Shelf Life/Storage

Shelf life is two years from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container.

Tightly close the container when not in use to prevent solvent evaporation and possible moisture contamination. Do not return unused or diluted adhesive to original container. Take care to avoid moisture contamination indicated by a milky white appearance.

Typical Properties*

Appearance	Clear to Hazy Yellow Liquid
Density kg/m ³ (lb/gal)	830 - 860 (6.9 - 7.2)
Solids Content by Weight, %	18 - 20
Flash Point (Seta), °C (°F)	3 (38)
Solvents	Methanol

*Data is typical and not to be used for specification purposes.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
www.parker.com/EPM

DS3152E OD 05/26 Rev.6

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2026 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.