

CHEMLOK® 6258 ADHESIVE

Technical Data Sheet

Chemlok® 6258 adhesive is a high-performing adhesive that bonds rubber compounds to metal. It is proven in applications that require a combination of strong adhesion with high fatigue resistance and high tensile strength.

Chemlok 6258 adhesive provides excellent corrosion resistance when used with mechanically or chemically treated cold rolled steel or aluminum.

Features and Benefits

Versatile: bonds a variety of elastomers; can be used as a covercoat adhesive over Chemlok 205 or 207 primer for maximum protection or when environmental conditions are severe.

Convenient: requires only a single coat for most applications, reducing labor, solvent usage, inventory and shipping costs; contains high solvent content for roller coat applications.

Process Compatible: provides excellent resistance to sweeping, ideal for transfer or injection molding operations.

Environmentally Resistant: provides excellent resistance to water, humidity, salt spray and high temperatures.

Elastomers

- Natural Rubber (NR)
- Polychloroprene (CR)
- Polyisoprene (IR)
- Nitrile (NBR)
- Styrene-butadiene (SBR)
- EPDM Polymers
- Polybutadiene (BR)

Application

Surface Preparation: Thoroughly clean metal surfaces prior to application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

Mixing: Thoroughly stir adhesive before use, and agitate sufficiently during use to keep dispersed solids uniformly suspended. If dilution is needed, use xylene or toluene. Note proper dilution for the various application methods is best achieved by experience. Give careful attention to agitation since dilution will accelerate settling.

Applying: Apply adhesive by brush, spray, dip, roll coat or spin/dip methods.

When using Chemlok 6258 adhesive as a one-coat adhesive, the dry film thickness should be 17.8-25.4 micron (0.7-1.0 mil) for optimum adhesion. When used as a covercoat over a primer, the dry film thickness of Chemlok 6258 adhesive should be 12.7-25.4 micron (0.5-1.0 mil).

Curing: Chemlok 6258 adhesive cures during the rubber vulcanization process.

Cleanup: Use xylene, toluene or ketones for clean up.

Typical Properties*

Appearance	Black Liquid
Viscosity, seconds Zahn Cup #3	25 - 45
Density kg/m ³ (lb/gal)	970.6 - 1006.5 (8.1 - 8.4)
Solids Content by Weight, %	24.5 - 28
Flash Point (Seta), °C (°F)	5 (41)
Solvents	Xylene, Toluene

*Data is typical and not to be used for specification purposes.

Shelf Life/Storage

Shelf life is one year from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container. Do not store or use near heat, sparks or open flame.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275-5673
www.parker.com/EPM

DS4395 OD 08/26 Rev.3

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2026 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.