

FLOCKSIL® 1501 (SF) FLOCK ADHESIVE

Technical Data Sheet

Flocksil® 1501 (SF) adhesive is a polyurethane adhesive used to adhere polyester or polyamide flock fibers to a variety of uncured and semi-cured elastomers including EPDM, NR, CR and SBR. When used in combination with a surface treatment, Flocksil 1501 (SF) adhesive can be used for flocking of a variety of thermoplastic elastomers (TPE).

Flocksil 1501 (SF) flock adhesive will react and cure with moisture; however, an elevated temperature cure is required to optimize adhesion and performance properties.

Features and Benefits

Durable: provides a flexible, abrasion-resistant cured film.

Excellent Adhesion: provides excellent adhesion to a wide variety of substrates and types of flock.

Process Compatible: can be catalyzed to achieve faster cure time; provides extended working time at room temperature (>20 hours, 50% RH).

Application

Surface Preparation: Remove contaminants (e.g., dirt, rubber bloom, processing oils and mold release) from substrate surface. For some rubber compounds, adhesion is enhanced by using surface treatments such as corona, plasma or mechanical abrasion.

Mixing: Thoroughly stir adhesive before use, and agitate sufficiently during use to keep dispersed solids uniformly suspended.

The cure rate of Flocksil 1501 (SF) adhesive can be accelerated by using Cuvertin® K24 catalyst. Adding 1-3% catalyst is suggested. Keep the adhesive at low agitation when adding the catalyst.

Applying: Apply adhesive by brush or spray methods. Recommended dry film thickness of Flocksil 1501 (SF) adhesive is 40-50 micron (1.6-2.0 mil).

Curing: When uncatalyzed, Flocksil 1501 (SF) adhesive will typically cure in 4 minutes at 180°C (356°F). When catalyzed with Cuvertin K24 catalyst, Flocksil 1501 (SF) adhesive will cure faster at 180°C (356°F) depending on the amount of catalyst added.

Shelf Life/Storage

Shelf life is six months from date of manufacture when stored by the recipient in a well ventilated area below 25°C (77°F) in original, unopened container. During transportation to the customer, the temperature restriction does not apply.

After opening and while removing contents, protect adhesive from excessive exposure to moisture by using dry nitrogen as an inert cover. Do not leave container open.

Typical Properties*

Appearance	Brown Liquid
Viscosity**	
mPa·s / cps @ 25°C (77°F) Brookfield LVT Spindle 1, 30 rpm	20 - 100
seconds @ 20°C (68°F) 4 mm DIN cup	15 - 30
Density @ 20°C (68°F) g/cm ³ (lb/gal)	0.93 - 0.97 (7.76 - 8.01)
Solids Content by Weight, % 2.5 gram dried 30 minutes @ 130°C (266°F)	45 - 49
Gel Time, minutes @ 180°C (356°F)	4

*Data is typical and not to be used for specification purposes.

**Viscosity may increase by 25% after production.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
www.parker.com/EPM

Parker Hannifin GmbH
Itterpark 8
40724 Hilden
Germany
phone +49 (0) 2103 252 310

DS4363E OD 04/26 Rev.4

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2026 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.