

BRUSHLESS MOTOR  
**NX82HMSE**  
 ELECTRONIC DRIVE  
**Drive 154/517 Arms**



No UL certification

Preliminary DATA



P <sub>n</sub>	Rated power **	7.64	kW	Cooling type : Natural Air cooling Exchange surface: 60°C
M <sub>n</sub>	Rated torque **	12.6	Nm	
N <sub>n</sub>	Rated speed	5800	rpm	
I <sub>n</sub>	Rated current	98.9	A <sub>rms</sub>	Environment : Ambient temperature : 40°C MAX Altitude : < 1000 m Insulation class : H (180°C) Max Winding Temperature : 150°C (according to IEC 60034-1)
U <sub>n</sub>	Rated voltage *	47.3	V <sub>rms</sub>	
U <sub>R</sub>	Voltage of the mains	77	V <sub>rms</sub>	
U	DC voltage supply when motor is loaded	96	V	Number of poles : 10 Electrical frequency @N <sub>p</sub> 667 Hz
M <sub>o</sub>	Low speed torque **	19	N.m	
I <sub>o</sub>	Permanent current at low speed	146	A <sub>rms</sub>	
M <sub>p</sub>	Max. torque **	55	Nm	Efficiency : at rated torque : 94.7 % at 75% of rated torque : 93.9 %
I <sub>p</sub>	Max. current	516	A <sub>rms</sub>	
N <sub>p</sub>	Max. speed	8000	rpm	
J	Rotor inertia	0.0032	kg.m <sup>2</sup>	
K <sub>e</sub>	Back emf constant at 1000 rpm (25°C)*	8.17	V <sub>rms</sub>	
K <sub>t</sub>	Torque sensitivity (rotor 25°C)	0.13	Nm/A <sub>rms</sub>	
R <sub>b</sub>	Winding resistance(25°C) *	0.00614	Ω	
L	Winding inductance *	0.0481	mH	

All data are given in typical values under standard conditions.

\* Phase to Phase

Characteristics are given for an optimal drive of the motor.

\*\* General tolerances ±7.5 %, rotor at 25°C



BRUSHLESS MOTOR  
**NX82HMSE Parameters**  
ELECTRONIC DRIVE  
Drive 154/517 Arms



No UL certification

### Main characteristics

Rated power **	7.64	kW	Ps1
Peak power **	39.2	kW	Ps6
Low speed torque **	19	N.m	Mo
Low speed peak torque **	55	N.m	MoS6
Nominal speed (S1)	5800	rpm	Nb
Max speed ****	8000	rpm	Nmax
DC voltage supply when motor is loaded	96	Vdc	Ū
Permanent current at low speed	146	Arms	Io
S6 current at low speed	516	Arms	IoS6

### Mechanical parameters

Rotor inertia	0.0032	kg.m <sup>2</sup>	J
Motor mass	13	kg	M
Maximum speed with Drive	8000	rpm	Nmax
Maximum mechanical speed	8000	rpm	Nmec

### Electrical parameters

Number of poles	10		
Winding resistance (25°C) *	0.00614	Ω	Rb
Back EMF voltage/ 1000 rpm *	8.17	Vrms / 1000 rpm	ke
Back EMF voltage / (rad/s) *	0.078	Vrms / (rad/s)	ku
Torque constant	0.13	N.m / Arms	Kt
Short circuit current	364	Arms	Icc
Inductance Lq (Back EMF voltage axis) *	0.0481	mH	Lq
Inductance Ld *	0.0495	mH	Ld
Optimal phasing at permanent current	10	electrical degree	ψo
Optimal phasing at S6 current	20	electrical degree	ψm

### Thermal parameters

Motor thermal resistance	0.234	K/W	Rth
Motor thermal time constant	1390	s	Tth
Winding thermal time constant	80	s	Tthw
Natural Air cooling / Exchange surface: 60°C			

Thermal class according to IEC 60034-1 H

\* Phase to phase

\*\* Tolerances ± 7.5% and rotor at 25°C