


REV	ECR#	DESCRIPTION	DATE	BY	APP'D
A	E	DRAWN	03-10-2016	AH	—



- NOTES:
- 1. INPUT 5.0V±0.25V. OUTPUT SPECIFICATION BASED ON 5 VOLTS.
 - 2. OUTPUT FULLY OPEN IS 0.5V±0.1V
 - 3. OUTPUT FULLY CLOSED IS 4.5±0.1V
 - 4. LINEARITY ± 5% FULL SCALE
 - 5. REPEATABILITY ± 1% FULL SCALE

NOTE: "MADE IN USA" PRINTED ON WHITE WIRES.

TOLERANCES UNLESS OTHERWISE SPECIFIED		Parker Electronic Controls Division Sensor Business Unit			
0 ± .25" .0 ± .05" .00 ± .02" .000 ± .010" ANG ± 1°			DATE: 03-10-2016	BY: AH	CH: _____
N/A		N/A			
TOOLING REV:		MATERIAL:			
VA ADS50 LINEAR LEVER SENS (01710)					
TITLE:					
1138		B	143558-CL	A	1 OF 1
PROJ. NO:		SIZE	DWG NO:	REV:	SHEET