

**PVC PRESSURE HOSE
AIR / WATER / CHEMICAL**



CAC CHEM-AIR AIRLINE

Chem-Air combines the features and benefits of an extremely flexible air hose, kink resistance and a pesticide/weedicide chemical resistant tube. The combined features of Chem-Air will provide benefits to the stockist and user alike. With the potential for reduced inventory and multiple use, it is ideally suited to many industrial and agricultural applications.



FEATURES:

- ◆ High tensile synthetic reinforcing
- ◆ Soft black chemical resistant virgin PVC tube
- ◆ Soft blue virgin PVC cover
- ◆ Excellent flexibility even at cold temperatures
- ◆ Excellent kink resistance
- ◆ UV stabilised
- ◆ Meets AS/NZS 2554 Class B specifications
- ◆ Highly visible blue cover
- ◆ Suitable for air/water /chemical applications
- ◆ Australian Made

ID (mm)	OD (mm)	Working Pressure (psi)	Min Bend Radius (mm)	Weight (kg/mtr)	Coil Lengths (Mtrs)	Part No
6.0	12.0	250psi	60	0.11	20, 100, 300	CAC-006-***
8.0	14.0	250psi	70	0.13	20, 100, 300	CAC-008-***
10.0	17.0	290psi	85	0.18	20, 30, 100, 200	CAC-010-***
12.5	19.0	250psi	95	0.19	20, 100	CAC-012-***
20.0	27.5	250psi	190	0.35	20, 100	CAC-020-***

ID & OD dimensions are subject to the following tolerances:
6-20mm +/- 0.4mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Virgin PVC
Colour:	Blue cover and Black tube
Ink Branding:	M PARKER (SIZE)MM AIR/WATER/CHEMICAL HOSE WP (1.7) MPa AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.