

## PVC SUCTION HOSE



# PFX PUMPFLEX

The Parker Pumpflex PVC suction hose is manufactured from super elastic PVC, making it one of our most flexible. This product is suitable for the suction and discharge of liquids and granular materials in pumping applications and its abrasive resistant qualities also makes it suited for use on air seeder equipment



### FEATURES:

- ◆ Excellent flexibility
- ◆ UV stabilized
- ◆ Abrasion resistance
- ◆ High impact resistance
- ◆ Australian made

ID (mm)	OD (mm)	Working Pressure (psi)	Vacuum Rating (mmHg)	Min Bend Radius (mm)	Weight (kg/mtr)	Part No
25.5	31.9	130psi	600	75	0.39	PFX-025-***
32.2	39.0	120psi	600	115	0.52	PFX-032-***
38.5	46.1	105psi	600	160	0.61	PFX-038-***
45.2	53.2	105psi	600	190	0.79	PFX-045-***
51.2	59.6	95psi	600	220	0.87	PFX-050-***
64.4	74.0	95psi	600	320	1.28	PFX-063-***
76.1	87.2	85psi	600	360	1.65	PFX-075-***
102.1	114.2	80psi	675	570	2.56	PFX-100-***
127.8	141.4	60psi	675	800	3.8	PFX-125-***
153.4	169.8	45psi	675	1100	5.55	PFX-150-***

ID & OD dimensions are subject to the following tolerances:  
+/- 0.6mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Flexible / Rigid PVC
Colour:	Grey tube / cover
Ink Branding:	PARKER PFX PUMPFLEX (SIZE)MM MADE IN AUSTRALIA (DATE)

\*\*\* To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.