

BRUSHLESS MOTOR
NX82WMSC
 ELECTRONIC DRIVE
Drive 300/870 Arms



No UL certification

Preliminary DATA - Water Cooled



P _n	Rated power **	12.6	kW	Cooling type : Water cooling IC 97 W Minimum flow: 1.1 l/min Max. Inlet Temperature: 60+/-5 °C Max. absolute pressure: 5 bars
M _n	Rated torque **	19.4	Nm	
N _n	Rated speed	6200	rpm	
I _n	Rated current	263	A _{rms}	
U _n	Rated voltage *	29.3	V _{rms}	
U _R	Voltage of the mains	40	V _{rms}	Environment : Ambient temperature : 65°C MAX Altitude : < 1000 m Insulation class : H Max Winding Temperature : 150°C (according to IEC 60034-1)
U	DC voltage supply when motor is loaded	48	V	
M _o	Low speed torque **	23	N.m	
I _o	Permanent current at low speed	297	A _{rms}	
M _p	Max. torque **	55	Nm	
I _p	Max. current	861	A _{rms}	Number of poles : 10 Electrical frequency @N _p 667 Hz Efficiency : at rated torque : 94.7 % at 75% of rated torque : 94.8 %
N _p	Max. speed	8000	rpm	
J	Rotor inertia	0.0032	kg.m ²	
K _e	Back emf constant at 1000 rpm (25°C)*	4.9	V _{rms}	
K _t	Torque sensitivity (rotor 25°C)	0.0775	Nm/A _{rms}	
R _b	Winding resistance(25°C) *	0.00221	Ω	
L	Winding inductance *	0.017	mH	

All data are given in typical values under standard conditions.

* Phase to Phase

Characteristics are given for an optimal drive of the motor.

** General tolerances ±7.5 %, rotor at 25°C



BRUSHLESS MOTOR
NX82WMSC Parameters
ELECTRONIC DRIVE
Drive 300/870 Arms



No UL certification

Main characteristics

Rated power **	12.6	kW	Ps1
Peak power **	31.6	kW	Ps6
Low speed torque **	23	N.m	Mo
Low speed peak torque **	55	N.m	MoS6
Nominal speed (S1)	6200	rpm	Nb
Max speed ****	8000	rpm	Nmax
DC voltage supply when motor is loaded	48	Vdc	Ū
Permanent current at low speed	297	Arms	Io
S6 current at low speed	861	Arms	IoS6

Mechanical parameters

Rotor inertia	0.0032	kg.m ²	J
Motor mass	13	kg	M
Maximum speed with Drive	8000	rpm	Nmax
Maximum mechanical speed	8000	rpm	Nmec

Electrical parameters

Number of poles	10		
Winding resistance (25°C) *	0.00221	Ω	Rb
Back EMF voltage/ 1000 rpm *	4.9	Vrms / 1000 rpm	ke
Back EMF voltage / (rad/s) *	0.0468	Vrms / (rad/s)	ku
Torque constant	0.0775	N.m / Arms	Kt
Short circuit current	606	Arms	Icc
Inductance Lq (Back EMF voltage axis) *	0.017	mH	Lq
Inductance Ld *	0.0178	mH	Ld
Optimal phasing at permanent current	10	electrical degree	ψo
Optimal phasing at S6 current	20	electrical degree	ψm

Thermal parameters

Motor thermal resistance	0.16	K/W	Rth
Motor thermal time constant	150	s	Tth
Winding thermal time constant	55	s	Tthw
Water cooling / Minimum flow:	1.1 l/min		
Maximum Inlet Temperature:			
Max. absolute pressure:	5 bars		
Thermal class according to IEC 60034-1	H		

* Phase to phase

** Tolerances ± 7.5% and rotor at 25°C