

PS65 Proximity Sensors

Catalog MSG33-2376/US





Application

The PS65 sensor belongs to the Parker family of accessories provided to complement electronic control systems. The PS65 is a magnetic proximity sensor for mobile hydraulic applications and will sense magnetic objects. The sensor may be combined with our complementary magnet target. The sensor has 6 inch leads with an attached Deutsch connector. To make the sensor suitable for mobile equipment, we have focused upon properties such as reliability and ease of installation.

Properties


Reliability

The PS65 has a threaded aluminum construction for strength and corrosion resistance. The sensor uses non-contact technology, through the use of an internal reed switch, for trouble free operation. Switch activation is a function of the strength of the actuator (magnet), how close it is to other ferrous objects, and the air gap distance. The sensor is very robust and able to withstand rugged applications.


Installation

The PS65 is well designed for the mobile hydraulics industry. The 2 pin connector is a sealed Deutsch DTM type designed for automotive use. This connector combined with potted electronics gives the sensor excellent protection for exposed outdoor applications. The threaded body and included stainless steel jam nuts make alignment simple. These features provide for easy installation and removal, even in field conditions.

PS65 dimensions



Complementary magnetic target dimensions





General

Weight 23 g

Temperature range -40°C to 105°C Operating life 10 million cycles

Air gap Max 1/2" (using magnet target listed below)

Mechanical characteristics

Switch type Normally closed Connector Deutsch DTM

Electrical characteristics

Contact resistance (initial) $Max\ 200\ m\Omega$ $Min\ 200\ VDC$ $Switching\ voltage$ $Max\ 100\ VAC/VDC$ $Switching\ current\ DC$ $Max\ 300\ mA$ $Max\ 0.4\ ms$

Ordering part number

PS65 154482ECD Magnet target 01143ECD

Environmental protection

Mechanical

Shock 1m drop Vibration 30 Gs

Climate

Sealing IP6K9K

Chemical environment

Liquids (resistance) standard automotive



WARNING - USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

- This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide
 product or system options for further investigation by users having technical expertise.
- The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components
 and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The
 user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the
 product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.
- To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

OFFER OF SALE

The items described in this document are hereby offered for sale by Parker-Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the detailed "Offer of Sale" available from your Parker representative or at www.parker.com.



WARNING - California Proposition 65

This product can expose you to chemicals including CHROMIUM (HEXAVALENT COMPOUNDS), NICKEL COMPOUNDS, EPICHLOROHYDRIN which is known to the State of California to cause cancer and EPICHLOROHYDRIN which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Parker Motion Systems International Sales Offices

North America

Motion Systems Group Headquarters

6035 Parkland Boulevard Cleveland, OH 44124-4141 USA

Tel: 216-896-3000 Fax: 216-896-4031

Parker Canada Division

160 Chisholm Drive Milton Ontario Canada L9T 3G9 Tel: 905-693-3000 Fax: 905-876-1958

Parker Hannifin de México

Industrial Hydraulic Sales
Eje Uno Norte No.100
Parque Industrial Toluca 2000
Toluca, Edo, de Mexico CP 50100
Tel: 52 722 275 4200
Fax: 52 722 279 9308

Parker Hannifin de México

Mobile Hydraulic Sales Via de FFCC a Matamoraos 730 Apodaca, NL, de Mexico CP 66600

Tel: 52 81 8156 6000 Fax: 52 81 8156 6068

Europe

Motion Systems Group Headquarters

La Tuilière 6 1163 Etoy - Switzerland Tel: 41 21 821 8500 Fax: 41 21 821 8580

South Africa

Parker Hannifin Africa Ptv Ltd

P.O. Box 1153 ZA-Kempton Park 1620, Republic of South Africa Tel: 27 11 961 0700 Fax: 27 11 392 7213

Mobile Sales

Mobile Sales Organization and Global Sales

850 Arthur Avenue Elk Grove Village, IL 60007 USA

Tel: 847-258-6200 Fax: 847-258-6299

Industrial Sales

Central Region

1042 Maple Avenue Unit 331 Lisle, IL 60532 USA Tel: 630-964-0796

Great Lakes Region

6035 Parkland Boulevard Cleveland, OH 44124-4141 USA

Tel: 216-896-2740 Fax: 866-498-7507

Gulf Region

20002 Standing Cypress Drive Spring, TX 77379 USA Tel: 817-473-4431 Fax: 888-227-9454

Southwest Region

700 S. 4th Avenue Mansfield, TX 76063 USA Tel: 817-473-9341 Fax: 817-473-2680

Mid Atlantic and Southeast Regions

1225 Old Alpharetta Road Suite 290

Alpharetta, GA 30005 USA

Tel: 770-619-9767 Fax: 770-619-9806

Midwest Region

8145 Lewis Road Minneapolis, MN 55427 USA Tel: 763-513-3535

Fax: 763-513-3535

Northeast Region

P.O. Box 396 Pine Brook, NJ 07058 USA Tel: 973-227-2565

Fax: 973-227-2467

Northwest Region

6458 North Basin Avenue Portland, OR 97217 USA Tel: 503-283-1020 Fax: 866-611-7308

Pacific Region

8460 Kass Drive Buena Park, CA 90621 Tel: 714-228-2510 Fax: 714-228-2511

Asia Pacific

Parker Hannifin Shanghai Ltd

280 Yunqiao Road, Jin Qiao Export Processing Zone Shanghai 201206, China Tel: 86 21 2899 5000 Fax: 86 21 6445 9917

Parker Hannifin Hong Kong Ltd

8/F, Kin Yip Plaza 9 Cheung Yee Street Cheung Sha Wan, Hong Kong Tel: 852 2428 8008 Fax: 852 2425 6896

Parker Hannifin Korea Ltd

9F KAMCO Yangjae Tower 949-3 Dogok1-dong, Gangnam-gu

Seoul, 135-860, Korea Tel: 82 2 559 0400 Fax: 82 2 556 8187

Parker Hannifin India Pvt Ltd

Plot No. EL-26, MIDC TTC Industrial Area Mahape, Navi Mumbai, 400 709 India

Tel: 91 22 6513 7081 Fax: 91 22 2768 6841

Parker Hannifin Australia

Parker Hannifin Pty Ltd. 9 Carrington Road Castle Hill, NSW 2154, Australia

Tel: 612 9634 7777 Fax: 612 9842 5111

Latin America

Parker Hannifin Ind. e Com. Ltda Hydraulics Division

Av. FredericoRitter, 1100 94930-000 Cachoeirinha RS, Brazil

Tel: 55 51 3470 6090 Fax: 55 51 3470 9281

Parker Hannifin Argentina S.A.I.C.

Stephenson 2711

1667-Tortuguitas-Malvinas Argentinas Pcia. de Buenos Aires, Argentina

Tel: 54 3327 44 4129 Fax: 54 3327 44 4199

Pan American Division

7400 NW 19th Street, Suite A Miami, FL 33126 USA Tel: 305-470-8800

Tel: 305-470-8800 Fax: 305-470-8808

© 2013-2020 Parker Hannifin Corporation. All rights reserved.



Parker Hannifin Corporation
Electronic Controls Division
850 Arthur Avenue
Elk Grove Village, IL, 60007 USA
phone 800 221 9257
ecdinfo@parker.com
www.parker.com/ecd

MSG33-2376/US

01/2020

Your Local Authorized Parker Distributor