

PVC PRESSURE HOSE WATER



HSL TURFMASTER

The Parker Turfmaster premium quality hose is suitable for a variety of general purpose water applications. It's unique tube and cover gives the product excellent flexibility, in particular at low temperatures, which makes it ideal for the rural areas of Australia which experience large variations in temperature. This product is suitable for parks and gardens, farms, nurseries, and as a premium quality garden hose.

FEATURES:

- ♦ Excellent flexibility
- ♦ All virgin PVC tube and cover
- ♦ Special blend of stabilizers provides
- ♦ Superior UV resistance
- ♦ Superior kink resistance
- ♦ Lifetime manufacturing warranty
- ♦ Made in Australia



ID (mm)	OD (mm)	Working Pressure (psi)	Min Bend Radius (mm)	Weight (kg/mtr)	Coil Lengths (Mtrs)	Part No
12.0	17.0	145psi	85	0.15	20, 35, 100, 200	HSL-012-***
19.0	25.0	145psi	125	0.25	20, 35, 100	HSL-020-***
25.0	31.0	145psi	155	0.34	20, 35, 100	HSL-025-***

ID & OD dimensions are subject to the following tolerances:
+/- 0.4 mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Virgin PVC compounds
Colour:	Green tube & Clear cover
Ink Branding:	M PARKER (SIZE)MM RCW WP (1.0) MPa AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.