

PVC SUCTION HOSE OIL



OFX OILFLEX

This heavy duty hose is manufactured with Parker's unique PVC/Rubber compound formulation that provides superior resistance to mild chemicals, sullage and petroleum based products for suction and low pressure delivery applications. It is designed to maintain flexibility at -10°C for ease of handling. Excellent durability.



FEATURES:

- ♦ Excellent cold temperature flexibility
- ♦ Good crush resistance
- ♦ High impact resistance
- ♦ Blue UV stabilized hose
- ♦ Chemical and Petrol resistant
- ♦ Australian made

ID (mm)	OD (mm)	Working Pressure (psi)	Vacuum Rating (mmHg)	Min Bend Radius (mm)	Weight (kg/mtr)	Part No
25.5	33.5	130psi	675	60	0.54	OFX-025-***
32.2	40.6	120psi	675	95	0.63	OFX-032-***
38.5	47.5	105psi	675	120	0.71	OFX-038-***
51.1	61.2	95psi	675	180	1.08	OFX-050-***
64.4	75.4	95psi	675	280	1.48	OFX-063-***
76.2	87.6	85psi	675	340	1.80	OFX-075-***
102.2	115.2	80psi	675	560	2.90	OFX-100-***

ID & OD dimensions are subject to the following tolerances: +/- 0.5 mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Flexible / Rigid PVC
Colour:	Blue
Ink Branding:	PARKER OFX OILFLEX (SIZE)MM MADE IN AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 3:1. All W.P. ratings are at 20°C.