

PVC PRESSURE HOSE AIR / WATER



SPA SUPER PREMI-AIR

Parker Super Premi-Air hose is a premium, high quality air hose. The PVC construction ensures lightweight and flexibility for easy handling. Suitable for general purpose air & water lines, ideal for high pressure air lines and compressors.



FEATURES:

- ♦ Lightweight
- ♦ Excellent flexibility
- ♦ Higher working pressures with a safety factor of 4:1
- ♦ Meets or exceeds AS/NZS 2554 Class B
- ♦ Australian made

ID (mm)	OD (mm)	Working Pressure (psi)	Min Bend Radius (mm)	Weight (kg/mtr)	Coil Lengths (Mtrs)	Part No
6.0	11.6	305	70	0.10	20, 60, 100, 300	SPA-006-***
8.0	14.4	305	100	0.15	20, 50, 100, 300	SPA-008-***
10.0	15.6	305	120	0.17	20, 30, 50, 100, 200	SPA-010-***
12.0	18.9	305	150	0.21	20, 30, 50, 100, 200	SPA-012-***
20.0	29.4	305	240	0.53	20, 30, 50, 100, 200	SPA-020-***
25.0	34.4	305	300	0.63	20, 50, 60, 100	SPA-025-***
32.0	41.6	305	380	0.87	20, 40	SPA-032-***
38.0	50.0	305	480	1.14	20, 40	SPA-038-***
50.0	63.0	305	600	1.62	20, 40	SPA-050-***

ID & OD dimensions are subject to the following tolerances:
6-20mm +/- 0.4mm, 25-32mm +/-0.6mm, 38-50mm +/-1.0mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Virgin PVC
Colour:	Yellow cover with two Blue stripes and Black tube
Ink Branding:	M PARKER SUPER PREMI-AIR (SIZE)MM WP (2.1) MPa AS/NZS 2554 MADE IN AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.