

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 1 of 10

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

EONIROMONTAPPLICATOR

1.2. Relevant identified uses of the substance or mixture and uses advised against**Use of the substance/mixture**

Cutting oil

1.3. Details of the supplier of the safety data sheet

Company name:	Jokisch GmbH	
	Germany	
Street:	Industriestraße 5	
Place:	D-33813 Oerlinghausen	
Telephone:	+49(0)5202/9734-0	Telefax: +49(0)5202/9734-49
E-mail:	info@jokisch-fluids.de	
Contact person:	Regulatory affairs	
E-mail:	MSDS@jokisch-fluids.de	
Internet:	www.jokisch-fluids.de	
Responsible Department:	Environmental Department	

1.4. Emergency telephone number:

Emergency telephone number (24h) + 44 1235 239670 (en) Emergency telephone number (24h) + 44 1235 239670 (en) Emergency telephone number (24h) + 44 1235 239670 (en)

Further Information

Reserved for industrial and professional use.

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Regulation (EC) No 1272/2008**

Aquatic Chronic 3; H412

Full text of hazard statements: see SECTION 16.

2.2. Label elements**Regulation (EC) No 1272/2008****Hazard statements**

H412 Harmful to aquatic life with long lasting effects.

Precautionary statements

P273 Avoid release to the environment.

P501 Dispose of contents/container to .

Special labelling of certain mixtures

EUH208 Contains Benzenesulfonic acid, di-C10-C14-alkyl derivs., calcium salts. May produce an allergic reaction.

2.3. Other hazards

Avoid release to the environment.

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

High slip hazard because of leaking or spilled product.

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 2 of 10

Relevant ingredients

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	Classification (Regulation (EC) No 1272/2008)			
25307-17-9	2,2'-(Octadec-9-enylimino)bisethanol			0.1 - < 1 %
	246-807-3		01-2119510876-35	
	Acute Tox. 4, Skin Corr. 1B, Aquatic Acute 1, Aquatic Chronic 1; H302 H314 H400 H410			

Full text of H and EUH statements: see section 16.

Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity
	Specific Conc. Limits, M-factors and ATE		
25307-17-9	246-807-3	2,2'-(Octadec-9-enylimino)bisethanol	0.1 - < 1 %
	oral: LD50 = 1000-1587 mg/kg Aquatic Acute 1; H400: M=10 Aquatic Chronic 1; H410: M=1		

Further Information

Full text of H- and EUH-statements: see section 16.

SECTION 4: First aid measures**4.1. Description of first aid measures****General information**

Seek medical attention if problems persist. No administration in cases of unconsciousness or cramps. First aider: Pay attention to self-protection!
Symptoms can occur only after several hours.

After inhalation

Move victim to fresh air. Put victim at rest and keep warm.

After contact with skin

Remove contaminated, saturated clothing immediately. After contact with skin, wash immediately with plenty of water and soap. Seek medical attention if problems persist.

After contact with eyes

In case of contact with eyes, rinse immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart. Consult an ophthalmologist.

After ingestion

Do NOT induce vomiting.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

Water fog. Extinguishing powder. Carbon dioxide. Foam.

Unsuitable extinguishing media

High power water jet.

5.2. Special hazards arising from the substance or mixture

In case of fire may be liberated:

Carbon dioxide (CO₂).

Carbon monoxide

Nitrogen oxides (NO_x).



Safety Data Sheet

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 3 of 10

5.3. Advice for firefighters

Do not inhale explosion and combustion gases. Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General advice

Wear personal protection equipment. Do not breathe gas/fumes/vapour/spray. Provide adequate ventilation.

For non-emergency personnel

Special danger of slipping by leaking/spilling product.

For emergency responders

Self-protection of the first aider Remove affected person from the danger area and lay down. Do not leave affected person unattended. Remove all sources of ignition. Use appropriate respiratory protection.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Prevent spread over a wide area (e.g. by containment or oil barriers). Treat the recovered material as prescribed in the section on waste disposal.

Collect in closed containers for disposal.

6.3. Methods and material for containment and cleaning up

For containment

Absorb with liquid-binding material (sand, diatomaceous earth, acid- or universal binding agents).

Clean contaminated articles and floor according to the environmental legislation.

Clean with detergents. Avoid solvent cleaners.

6.4. Reference to other sections

Disposal: see section 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Avoid oil mist

Use only in well-ventilated areas.

When using do not eat, drink or smoke.

Further information on handling

High slip hazard because of leaking or spilled product.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep the packing dry and well sealed to prevent contamination and absorption of humidity.

Recommended storage temperature: 5-40 °C

Hints on joint storage

Keep away from food, drink and animal feedingstuffs.

Maximum period of storage (time): 3

Further information on storage conditions

Protect from sunlight. Store in a well-ventilated place.

7.3. Specific end use(s)

Observe technical data sheet.

Reserved for industrial and professional use.

SECTION 8: Exposure controls/personal protection

Safety Data Sheet

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 4 of 10

8.1. Control parameters

DNEL/DMEL values

CAS No	Substance	Exposure route	Effect	Value
25307-17-9	2,2'-(Octadec-9-enylimino)bisethanol			
Worker DNEL, long-term		inhalation	systemic	2,96 mg/m ³
Worker DNEL, long-term		dermal	systemic	0,42 mg/kg bw/day
Consumer DNEL, long-term		inhalation	systemic	0,522 mg/m ³
Consumer DNEL, long-term		dermal	systemic	0,15 mg/kg bw/day
Consumer DNEL, long-term		oral	systemic	0,15 mg/kg bw/day

PNEC values

CAS No	Substance	Value
25307-17-9	2,2'-(Octadec-9-enylimino)bisethanol	
Freshwater		0,214 mg/l
Marine water		0,0214 mg/l
Freshwater sediment		1,692 mg/kg
Marine sediment		0,1692 mg/kg
Secondary poisoning		2 mg/kg
Micro-organisms in sewage treatment plants (STP)		1,5 mg/l
Soil		5,0 mg/kg

Additional advice on limit values

Does not contain substances above concentration limits fixing an occupational exposure limit.

8.2. Exposure controls



Appropriate engineering controls

If local exhaust ventilation is not possible or not sufficient, the entire working area should be ventilated by technical means.

Individual protection measures, such as personal protective equipment

Eye/face protection

EN 166

Hand protection

Protect skin by using skin protective cream.
Wash hands before breaks and after work.

Skin protection

Chemical resistant safety shoes. Take off immediately all contaminated clothing.
Thorough skin-cleansing after handling the product. Set out skin protection guidelines.

Respiratory protection

If technical exhaust or ventilation measures are not possible or insufficient, respiratory protection must be worn.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 5 of 10

Environmental exposure controls

Do not allow to enter into surface water or drains.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state: liquid
Colour: amber coloured
Odour: characteristic

	Test method
Boiling point or initial boiling point and boiling range:	not determined
Lower explosion limits:	0,6 vol. %
Upper explosion limits:	6,5 vol. %
Flash point:	>180 °C DIN EN 57
pH-Value:	not applicable
Viscosity / kinematic: (at 40 °C)	87 mm ² /s ASTM D 7042
Vapour pressure:	not determined
Density (at 20 °C):	0,90 g/cm ³ EN ISO 12185

9.2. Other information

No information available.

SECTION 10: Stability and reactivity**10.2. Chemical stability**

The product is chemically stable under recommended conditions of storage, use and temperature.

10.3. Possibility of hazardous reactions

No hazardous reaction when handled and stored according to provisions.

10.4. Conditions to avoid

Protect against: heat.

10.5. Incompatible materials

The following must be prevented: Oxidizing agents, strong. acid.

10.6. Hazardous decomposition products

Hazardous decomposition products: none

SECTION 11: Toxicological information**11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008****Toxicokinetics, metabolism and distribution**There are no data available on the preparation/mixture itself.
Data apply to the main component.**Acute toxicity**

Based on available data, the classification criteria are not met.

ATEmix calculated

ATE (oral) > 2000 mg/kg; ATE (dermal) > 2000 mg/kg; ATE (inhalation vapour) > 20 mg/l; ATE (inhalation dust/mist) > 5 mg/l

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 6 of 10

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
25307-17-9	2,2'-(Octadec-9-enylimino)bisethanol				
	oral	LD50 1000-1587 mg/kg	Rat	ECHA	

Irritation and corrosivity

Skin corrosion/irritation: Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation: Based on available data, the classification criteria are not met.

Sensitising effects

Based on available data, the classification criteria are not met.

Contains Benzenesulfonic acid, di-C10-C14-alkyl derivs., calcium salts. May produce an allergic reaction.

Carcinogenic/mutagenic/toxic effects for reproduction

Germ cell mutagenicity: Based on available data, the classification criteria are not met.

Carcinogenicity: Based on available data, the classification criteria are not met.

Reproductive toxicity: Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

Additional information on tests

No risks worthy of mention. Practical experience.

The statement is derived from the properties of the single components.

The classification was undertaken in accordance with the calculation method governed by the Preparations Directive (1999/45/EC).

11.2. Information on other hazards**Endocrine disrupting properties**

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

SECTION 12: Ecological information**12.1. Toxicity**

Harmful to aquatic life with long lasting effects.

The statement is derived from the properties of the components.

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential**Partition coefficient n-octanol/water**

CAS No	Chemical name	Log Pow
25307-17-9	2,2'-(Octadec-9-enylimino)bisethanol	3,4

12.4. Mobility in soil

in delivery condition: liquid

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

The components in this formulation do not meet the criteria for classification as PBT or vPvB.

12.6. Endocrine disrupting properties



Safety Data Sheet

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 7 of 10

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

12.7. Other adverse effects

Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal recommendations

Do not allow to enter into surface water or drains. Dispose of contents/container to an appropriate recycling or disposal facility. Waste disposal according to directive 2008/98/EC, covering waste and dangerous waste. Non-contaminated packages may be recycled.

List of Wastes Code - residues/unused products

120107 WASTES FROM SHAPING AND PHYSICAL AND MECHANICAL SURFACE TREATMENT OF METALS AND PLASTICS; wastes from shaping and physical and mechanical surface treatment of metals and plastics; mineral-based machining oils free of halogens (except emulsions and solutions); hazardous waste

List of Wastes Code - used product

120109 WASTES FROM SHAPING AND PHYSICAL AND MECHANICAL SURFACE TREATMENT OF METALS AND PLASTICS; wastes from shaping and physical and mechanical surface treatment of metals and plastics; machining emulsions and solutions free of halogens; hazardous waste

Contaminated packaging

Non-contaminated packages may be recycled.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1. UN number or ID number: No dangerous good in sense of these transport regulations.
14.2. UN proper shipping name: No dangerous good in sense of these transport regulations.
14.3. Transport hazard class(es): No dangerous good in sense of these transport regulations.
14.4. Packing group: No dangerous good in sense of these transport regulations.

Inland waterways transport (ADN)

14.1. UN number or ID number: No dangerous good in sense of these transport regulations.
14.2. UN proper shipping name: No dangerous good in sense of these transport regulations.
14.3. Transport hazard class(es): No dangerous good in sense of these transport regulations.
14.4. Packing group: No dangerous good in sense of these transport regulations.

Marine transport (IMDG)

14.1. UN number or ID number: No dangerous good in sense of these transport regulations.
14.2. UN proper shipping name: No dangerous good in sense of these transport regulations.
14.3. Transport hazard class(es): No dangerous good in sense of these transport regulations.
14.4. Packing group: -

Other applicable information (marine transport)

Not restricted

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number or ID number: No dangerous good in sense of these transport regulations.
14.2. UN proper shipping name: No dangerous good in sense of these transport regulations.
14.3. Transport hazard class(es): No dangerous good in sense of these transport regulations.
14.4. Packing group: -

Other applicable information (air transport)

Not restricted

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No



Safety Data Sheet

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 8 of 10

14.6. Special precautions for user

Personal protection equipment: see section 8

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

Restrictions on use (REACH, annex XVII):

Entry 3

Directive 2010/75/EU on industrial emissions: 0,0

Directive 2004/42/EC on VOC in paints and varnishes: 0,0

Information according to Directive 2012/18/EU (SEVESO III): Not subject to 2012/18/EU (SEVESO III)

National regulatory information

Employment restrictions: Observe restrictions to employment for juveniles according to the 'juvenile work protection guideline' (94/33/EC).

Water hazard class (D): 2 - obviously hazardous to water

15.2. Chemical safety assessment

For the following substances of this mixture a chemical safety assessment has been carried out:

SECTION 16: Other information

Changes

This data sheet contains changes from the previous version in section(s): 1,2,3,4,5,6,7,8,11,12,13,15,16.

AICS (Australien), DSL (Kanada), IECSC (China), REACH (Europäische Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (Neuseeland), PICCS (Philippinen), TSCA (USA)

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 9 of 10

Abbreviations and acronyms

Acute Tox: Acute toxicity
 Skin Corr: Skin corrosion
 Aquatic Acute: Acute aquatic hazard
 Aquatic Chronic: Chronic aquatic hazard
 CLP: Classification, labelling and Packaging
 REACH: Registration, Evaluation and Authorization of Chemicals
 GHS: Globally Harmonised System of Classification, Labelling and Packaging of Chemicals
 UN: United Nations
 CAS: Chemical Abstracts Service
 DNEL: Derived No Effect Level
 DMEL: Derived Minimal Effect Level
 PNEC: Predicted No Effect Concentration
 ATE: Acute toxicity estimate
 LC50: Lethal concentration, 50%
 LD50: Lethal dose, 50%
 LL50: Lethal loading, 50%
 EL50: Effect loading, 50%
 EC50: Effective Concentration 50%
 ErC50: Effective Concentration 50%, growth rate
 NOEC: No Observed Effect Concentration
 BCF: Bio-concentration factor
 PBT: persistent, bioaccumulative, toxic
 vPvB: very persistent, very bioaccumulative
 ADR: Accord européen sur le transport des marchandises dangereuses par Route
 (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 RID: Regulations concerning the international carriage of dangerous goods by rail
 ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
 (Accord européen relatif au transport international des marchandises dangereuses par voies de navigation
 intérieures)
 IMDG: International Maritime Code for Dangerous Goods
 EmS: Emergency Schedules
 MFAG: Medical First Aid Guide
 IATA: International Air Transport Association
 ICAO: International Civil Aviation Organization
 MARPOL: International Convention for the Prevention of Marine Pollution from Ships
 IBC: Intermediate Bulk Container
 VOC: Volatile Organic Compounds
 SVHC: Substance of Very High Concern

Classification for mixtures and used evaluation method according to Regulation (EC) No 1272/2008 [CLP]

Classification	Classification procedure
Aquatic Chronic 3; H412	Calculation method

Relevant H and EUH statements (number and full text)

H302 Harmful if swallowed.
 H314 Causes severe skin burns and eye damage.
 H400 Very toxic to aquatic life.
 H410 Very toxic to aquatic life with long lasting effects.
 H412 Harmful to aquatic life with long lasting effects.
 EUH208 Contains Benzenesulfonic acid, di-C10-C14-alkyl derivs., calcium salts. May produce an allergic reaction.

Further Information

The information is based on the present level of our knowledge. It does not, however, give assurance of product properties and establishes no contract legal rights.



Safety Data Sheet

according to Regulation (EC) No 1907/2006

EONIROMONTAPPLICATOR

Revision date: 30.01.2025

Product code: 55

Page 10 of 10

(The data for the relevant ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)