

SmogHog® Machine Mount Media Mist Collector

SmogHog is the most recognized and trusted name for effective removal of mist and smoke within the metalworking industry. Our mist collection technologies have been cleaning the air and recycling machine fluids for companies around the world for half a century.

The SmogHog SHM Machine Mount is a self-contained mist collector designed to be mounted directly onto a machining center saving floor space, reducing installation complexity of duct runs, and decreasing operational cost.

Filter Technology and Performance. PEACH Saturated Depth Coalescing™ media provides best in class filtration efficiency, removing over 99% of contaminants, and delivering long filter life.

Flexible Configurations. Engineered to order per your requirements combined with the flexibility to mount the unit on the top or side of the machine along with inlet locations on three sides to save time and money during installation while providing optimal performance in your plant.

Technical Expertise. Our application engineers and technical experts recommend solutions that are right for your application. We have the broadest portfolio of equipment with the knowledge to understand the full scope of the issues faced in the plant and which technology will be most effective in solving mist and smoke challenges.

Control Technology. The SHM easily integrates with machine tool controls for automated operation. The SHM-08 advanced unit includes a remote touchscreen controller and Electronically Commutated (EC) blower for automated airflow control to help consume less energy than conventional blowers, therefore greatly reducing operational costs.

Easy Service and Maintenance. Designed with service and reliable operation in mind. The patent pending filter design offers a tool-free, easy to service system that simplifies maintenance and are just a few features that will save you time and money.



Model SHM-05



10 YEAR
WARRANTY

SmogHog® Machine Mount Media Mist Collector




PEACH Saturated Depth Coalescing™ technology provides an open 3D depth matrix structure which allows liquids to saturate the media depth and grow to fullest potential then drain with gravity when the droplet is ready, all while maintaining a low differential pressure.

The PEACH media is a 100% proprietary synthetic, multi-layered media that is engineered specifically for capturing and draining oil mist and coolant contaminants. The unique fiber structure of

PEACH media separates the liquid droplets from the airstream in three distinct manners. Multiple airflow paths increase the virtual filtration area of the media extending the opportunity for contaminants to be removed.


The benefits include high efficiency, extended service life, and lower pressure drop over extended periods of time.

Three Airflow Paths Remove Over 99% of Contaminants



Radial

Air passes directly through the thickness of the media impacting the fiber structure removing contaminant



Axial

Media structure forces a large percentage of airflow to take a stair-step path improving particle removal



Helical

The wrapped structure of the fiber matrix creates a corkscrew air pattern that increases dwell time and resulting particle capture



Specifications

Model	Cabinet Dimensions			Filter Specifications		Voltage	Nominal
	Width	Depth	Height*	Qty	Surface Area		Airflow
	(in)	(in)	(in)		(ft2)		(CFM)
SHM-05C	30-1/8	23-19/32	35-7/16	4	17.2	200-240,460V/3PH/50-60Hz	300-500
SHM-08C	37	23-19/32	35-7/16	6	25.8	200-240,460V/3PH/50-60Hz	500-800
SHM-08C Advanced	37	23-19/32	39-15/16	6	25.8	200-240, 380-480V/3PH/50-60Hz	500-800

* Add 6.5" for after filter option. Based on side inlet configuration and drain sump

Options and Accessories

- ASHRAE 95% Oil Mist or HEPA Safety After Filters
- Remote On/Off Disconnect Switch
- Side Mount Bracket
- Side Mount Bracket
- Drain Loop Trap
- Mounting Vibration Isolators
- Flex Duct and Duct Accessories
- Custom Paint Colors