




Model Number	Nominal Size (Inches) W x H x D	Actual size (Inches) W x H x D	Rated Air Flow (CFM)	Initial Resistance (In. W.G.)	MERV	Media Area (Square Feet)
RS-902-PH	24 x 24 x 6	23-3/8 x 23-3/8 x 5-7/8	1000	0.67	14	27
RS-916-PH	20 x 24 x 6	19-3/8 x 23-3/8 x 5-7/8	800	0.67	14	22
RS-914-PH	20 x 20 x 6	19-3/8 x 19-3/8 x 5-7/8	700	0.67	14	17
RS-901-PH	12 x 24 x 6	11-3/8 x 23-3/8 x 5-7/8	500	0.67	14	13
RS-802-PH	24 x 24 x 6	23-3/8 x 23-3/8 x 5-7/8	1000	0.44	13	27
RS-816-PH	20 x 24 x 6	19-3/8 x 23-3/8 x 5-7/8	800	0.44	13	22
RS-814-PH	20 x 20 x 6	19-3/8 x 19-3/8 x 5-7/8	700	0.44	13	17
RS-801-PH	12 x 24 x 6	11-3/8 x 23-3/8 x 5-7/8	500	0.44	13	13
RS-602-PH	24 x 24 x 6	23-3/8 x 23-3/8 x 5-7/8	1000	0.20	11	27
RS-616-PH	20 x 24 x 6	19-3/8 x 23-3/8 x 5-7/8	800	0.20	11	22
RS-614-PH	20 x 20 x 6	19-3/8 x 19-3/8 x 5-7/8	700	0.20	11	17
RS-601-PH	12 x 24 x 6	11-3/8 x 23-3/8 x 5-7/8	500	0.20	11	13
RS-502-PH	24 x 24 x 6	23-3/8 x 23-3/8 x 5-7/8	1000	0.15	10	27
RS-516-PH	20 x 24 x 6	19-3/8 x 23-3/8 x 5-7/8	800	0.15	10	22
RS-514-PH	20 x 20 x 6	19-3/8 x 19-3/8 x 5-7/8	700	0.15	10	17
RS-501-PH	12 x 24 x 6	11-3/8 x 23-3/8 x 5-7/8	500	0.15	10	13

STANDARD CONSTRUCTION

1. High Efficiency, High Loft Microglass Filter Media
2. Expanded Metal Pleat Supports
3. Adhesive Seal on All Four Media Pack Sides
4. 24 Gauge Galvanized Steel Cell Sides
5. Plastic Fingers Maintain Pleat Spacing
6. Diagonal Support Braces on Air Entering and Air Leaving Sides for Additional Rigidity
7. 3/4" Header on Air Entering Side Standard
8. 1-1/8" 'C' Style Header Optional
(Add 'CH' Suffix on the Model Number)

NOTES

1. MERV per ASHRAE 52.2-2012
Tested at 492 FPM on 24x24 Standard Size
2. Final Resistance: 1.5" W.G.
3. Rated Velocity 6" Deep - 500 FPM
4. Classified per UL Standard 900 for Flammability
5. Maximum Operating Temperature: 180 deg. F
6. Optional Gasket Available
U - Upstream Gasket (Ex: R-904-PH-U)
D - Downstream Gasket
UD- Both Sides
SA - Side Access Gasket (One Vertical Side)
7. Special sizes not available



100 River Ridge Circle
Jeffersonville, IN 47130
P: 866-247-4827
F: 866-601-1809
www.clcair.com/airguard

CONTACT FACTORY TO
VERIFY REVISION LEVEL

TOLERANCES UNLESS OTHERWISE SPECIFIED

FRACTIONAL -
DECIMAL -
ANGLES -

ALL DIMENSIONS IN INCHES

DRAWING NAME

VARI-PAK PH 6"

APPROVED BY

K. O.

SPECIFICATION NO.

MKT-B-00632

PAGE 1 OF 1

SCALE

NONE

DWG. SIZE

A

REVISION

C

REVISION DATE

09-29-16

CONFIDENTIAL - DO NOT COPY. THIS MATERIAL IS TRADE SECRET AND PROPRIETARY BEING EXCLUSIVELY OWNED BY CLCAIR. THE EXPRESSION OF THE INFORMATION CONTAINED HEREIN IS PROTECTED UNDER FEDERAL COPYRIGHT LAWS AND ALL COPYING IS PROHIBITED AND MAY BE SUBJECT TO CRIMINAL PENALTIES.