

# Nitrogen Generators

for LC/MS applications - with optional economy mode



The Parker domnick hunter LCMS nitrogen gas generators employ robust, field proven technology to meet the drying, sheath and nebulisation gas requirements of today's latest LC/MS instrumentation. Two models operate at flow rates of 20 and 30 L/min.

The LCMS generators provide a continuous stream of high purity nitrogen from a single 'plug & play' unit. Models are available with and without an integral oil free compressor, are extremely quiet in operation and are fully approved for use by major instrumentation manufacturers.

Innovative design and technology facilitate maximum instrument uptime, attractive return on investment and proven analytical performance, eliminating the need for other modes of supply.

A range of tailored service contracts, extended warranties and global manufacturing capabilities provide comprehensive aftermarket support.



## Product Features:

- **Ultra high purity, organic free, nitrogen**
- **Produces a continuous supply of LC/MS grade nitrogen 24 hours a day**
- **Integral oil free compressor, with noise reduction technology**
- **Eliminate inconvenient and potentially dangerous nitrogen cylinders**
- **Compact, reliable with minimal operator attention and maintenance**
- **Phthalate-free componentry**



ENGINEERING YOUR SUCCESS.

Product Selection

Model	Flow Rate	Purity*	Air Inlet @ 8.5 bar g (123.3 psi g)	Delivery Pressure		Integral Compressor
	L/min	%	L/min	bar g	psi g	
LCMS20-0	20	>99	70	7	101.5	NO
LCMS20-1	20	>99	n/a	7	101.5	YES
LCMS30-0	30	>99	130	7	101.5	NO
LCMS30-1	30	>99	n/a	7	101.5	YES

\*Purity with respect to oxygen

Note: Add suffix 'E' for 207-253V 50/60Hz ie. LCMS20-0-E  
Add suffix 'W' for 103 -126V 60Hz ie. LCMS20-0-W

Technical Data

Ambient Temperature Range	5 - 40°C (41 - 104°F)
Inlet Air Quality *	Clean dry compressed air ISO8573-1:2001 Class 2.-. 1
Supply Voltage Range	103 - 126V 60Hz 207 - 253V 50/60Hz
Port Connections Nitrogen Outlet / Air Inlet *	¼" Compression Fitting

\*Non compressor models only

LCMS-ECOMax Add-on-Module (Optional Extra)

Product	Description	Compatibility	Installation	Height (H)		Width (W)		Depth (D)		Weight	
				mm	in	mm	in	mm	in	Kg	lb
LCMS-ECOMax-230V	Enables economy mode cycle supplying nitrogen gas only when required, whilst maintaining constant purity	LCMS20-30 models with and without integral compressor	All required fittings supplied with ECOMax module	103	4.06	303	11.93	408	16.06	7.8	17.2

Weights and Dimensions

Model	Height (H)		Width (W)		Depth (D)		Weight (with compressor)	
	mm	in	mm	in	mm	in	kg	lb
LCMS 20-1	705	27.8	510	20.1	826	32.5	129	284
LCMS 30-1	705	27.8	510	20.1	826	32.5	129	284

Model	Height (H)		Width (W)		Depth (D)		Weight (without compressor)	
	mm	in	mm	in	mm	in	kg	lb
LCMS 20-0	705	27.8	510	20.1	559	22.0	89	196
LCMS 30-0	705	27.8	510	20.1	760	22.9	135	298

Preventative Maintenance

Preventative Maintenance Kit	Part Number	Change Frequency
Filter Kit- all models	606272251	12 months
Compressor Kit 230V - Option 1 models	606272253	8,000 hours or 24 months (whichever comes first)
Compressor Kit 120V - Option 1 models	606272261	8,000 hours or 24 months (whichever comes first)

Optional Extras

Description	Part Number	Required for
Installation kit	IK7572	Suitable for all LCMS nitrogen generators

www.parker.com/gsf



European Headquarters  
La Tuilière 6, 1163 Etoy,  
Switzerland  
Tel: +41 21 821 85 00

EMEA Product Information Centre  
Free phone: 00 800 27 27 5374  
(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)  
US Product Information Centre  
Toll-free number: 1-800-27 27 537