










Description	Threaded cable joint	Body colour coding	Figures switching	Order no.
Plug EN 175301-803 ¹⁾ , design type AF, protection class IP65 voltages up to 250 V	PG 9	black, B grey, A	Fig. 1	5001710 5001711
	PG11	black, B grey, A	Fig. 1	5001716 5001717
Plug with LED insert 24 V	PG11	black, B grey, A	Fig.1 and Fig. 3	5001571 5001572
Plug with lamp insert 110 V	PG11	black, B grey, A	Fig.1 and Fig. 4	5001573 5001574
Plug with lamp insert 230 V	PG11	black, B grey, A	Fig.1 and Fig. 4	5001575 5001576
Plug with LED insert 24 V and supressing circuitry	PG11	black, B grey, A	Fig.1 and Fig. 5	5001708 5001709
Plug with rectifier. Rectifier with 4 silicon diodes in bridge circuit. Varistor in alternating current side to protect the diodes against power peaks	PG11	black, B grey, A	Fig.1 and Fig. 6	5001737 5001738
Plug with pull relief and translucent cover	PG11	black, B grey, A	Fig. 2	5001723 5001724
Application with bridge rectifier suitable for 5001723 and 5001724	—	—	Fig. 2 and Fig. 7	5001727
Application with bridge rectifier and lamp suitable for 5001723 and 5001724	—	—	Fig. 2 and Fig. 8	5001734



¹⁾ EN 175301-803 (new) corresponding with DIN 43650 (old).

Central connector



Description	Order No.
DIN 43563 6+PE	5004072

4