



# COMPOUND DATA SHEET

Parker O-Ring & Engineered Seals Division, North America

---

## MATERIAL REPORT

Report Date: 11/15/23

**Title:** Evaluation of Parker Compound

**Elastomer Type:** Fluorocarbon (FFKM) FF362-75

**Purpose:** To obtain typical test data.

**Color:** White

**Recommended Temperature Range:** 5°F to 608°F

**Conclusions:** Parker compound FF362-75 is a white, high temperature, ultra-high purity perfluorinated elastomer. FF362-75 seals resist compression set and offer temperature resistance up to 608 F.

**Recommended For:** Aliphatic and aromatic hydrocarbons, chlorinated hydrocarbons, polar solvents (acetone, methylethylketone, dioxane), inorganic and organic acids, bases (under appropriate temperatures), water and steam (under appropriate temperatures), petroleum oil, wet/dry chlorine.

**Not Recommended For:** Fluorinated refrigerants (R11, R12, R13, R113, R114), heat transfer fluids (Fomblin, Novec, ect) uranium hexafluoride, molten metals, gaseous and alkali metals

*"Purchaser use only. Reproduce only in full. Data pertains to items referenced only."  
"The recording of false, fictitious, or fraudulent statements or entries in this report may be punishable as a felony under federal law."*

**Original Physical Properties**

Hardness, Shore A, pts.

Tensile Strength, psi

Ultimate Elongation

Modulus at 100% Elongation

Specific Gravity

**Test Method**

ASTM D2240

ASTM D1414

ASTM D1414

ASTM D1414

ASTM D297

**Test Results**

75

1669

284

462

2.33

**Compression Set****22 hrs. @ 200°C (392°F)****70 hrs. @ 200°C (392°F)****168 hrs. @ 200°C (392°F)****22 hrs. @ 300°C (572°F)**

ASTM D395 Method B

12

16

19

25