

eREADY PUMP F1e FIXED DISPLACEMENT

Parker's upgraded F1e series and eReady Pump series deliver exceptional performance, durability, and reliability.

The eReady Pump reduces pressure pulsation by up to 40 %, lowering noise levels and minimizing vibrations for quieter operations, while also decreasing sound wave intensity from rapid pressure changes.

Frame size	61	81
Displacement [cm ³ /rev]	59.5	81.6
Interface	(ISO 14/ DIN 5462) C	(ISO 14/ DIN 5462) C
Max operating pressure [bar] ¹⁾	400	400
Max selfpriming speed [rpm]	2400	2200
Noise reduction		
Reduced noise level [dBA]	<-6	<-6
Pressure pulsation	<-40 %	<-40 %
Max input power ¹⁾ [kW]	83	105
Weight [kg]	8.5	12.5

¹⁾ Max 6 seconds in any one minute

Suction fittings

Available in straight, 45°, 90° or 145°.



Features and benefits:

- Silent operation
- Unbeatable efficiency
- High & Low speed capability
- Consistent performance over lifetime
- High pressure rating

Intended applications:

- Cargo cranes
- Hook loaders
- Skip loaders
- Forestry cranes
- Multipurpose vehicles



Unbeatable efficiency



Silent operation



High & Low speed capability

Parker Hannifin Corporation
Hydraulic Pump & Motor Europe

www.parker.com/msge

© 2025 Parker Hannifin Corporation

