Model 603AV

Mass Flow Controller

aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding

Porter's Model 603AV Series II Mass Flow Controller (MFCs) is designed for precise control of virtually all conventional process gases. The MFC consists of a thermal mass flow sensor, a precise control valve and a microprocessor based PID controller with signal and fieldbus conversion. Based on the setpoint input value, the flow controller swiftly adiusts to the desired flow rate. The mass flow rate is provided as analog signal or digitally via RS232 or various fieldbus options. Each unit is specifically sized and calibrated depending on the types of gas and the process conditions of the application.



Product Features:

- Full Scale Flow Ranges from 200 ml/min to 1670 ml/min
- Operating Pressures up to 928
 PSIA
- High accuracy and repeatability
- Storage of max. 8 calibration curves


- User configurable control characteristics
- Flow Parameter Adjust functionality up to 150 PSIA
- Effective Rangeability <180:1
- Analog or digital: RS232,
 DeviceNet[™], ProfibusDP[®],
 Modbus-RTU



500/600 Series II Flowmeter Products


Thermal Mass Flow Measuring Principle

The Mass Flow Sensing System consists of a stainless steel capillary tube with two precision heater and temperature sensing elements wound around the outside of the tube. As gas flows through the capilliary tube, heat is displaced to the downstream temperature sensor creating a differential between the two sensors. The difference is directly proportional to mass flow through the tube. In the main flow channel, a patented laminar flow element package creates a restriction that forces a fixed percentage of the total flow through the sensor for temperature differential detection.



State of the Art Digital Design

Porter's Series II Mass Flow products are equipped with a microprocessor based digital pc-board offering high accuracy, excellent temperature stability and fast MFC response time. The basic digital pc-board contains all of the general functions needed for measurement and control. RS232 communication and analog I/O are included. An optional integrated communication interface board provides DeviceNet[™], Profibus-DP® or Modbus-RTU.



Models and Flow Ranges

Model	Minimum	Nominal	Maximum
603AV - U	4 to 200 I/min	10 to 500 l/min	15 to 750 l/min
603AV - V	8 to 400 l/min	20 to 1000 l/min	1670 l/min

All flow ranges are at standard conditions of 14.7 PSIA and 70°F (21.1°C)

Specifications

Measurement / Control System

Accuracy (incl. linearity) (based on actual calibration)	Standard: ±0.5% Reading plus ±0.1% Full Scale	
Turndown	1 : 50 (in digital mode up to 1 : 187.5)	
Repeatability	<0.2% Reading	
Settling Time (Controller)	Standard: 2-4 seconds	
Control Stability <±0.1% Full Scale (typical for 1 l/min N ₂)		
Operating Temperature	-10 to +70°C	
Temperature Sensitivity	Zero: <0.05% Full Scale/°C; span: <0.05% Reading/°C	
Pressure Sensitivity	0.1%/ATM typical N2; 0.01%/ATM typical H ₂	
Leak Integrity, outboard	Tested < 2 x 10-9 mbar l/s He	
Attitude Sensitivity Max. error at 90° off horizontal 0.2% at 1 ATM, typ		
Warm-Up Time 30 min. for optimum accuracy 2 min. for accuracy ±2% Full Scale		

Mechanical Parts

Material (wetted parts)	Stainless steel 316L or equivalent	
Surface Quality (wetted parts)	Ra= 0.8µm typical	
Process Connections	Compression or face seal fittings	
Seals	Standard: Viton Options: EPDM, Kalrez (FFKM)	
Ingress Protection (housing)	IP40	


Electrical Properties

Power Supply	+15-24 Vdc	
Power Consumption	Meter: 70 mA; Controller: max. 320 mA; Add 50 mA for Profibus, if applicable	
Analog Output/Command	0-5 (10) Vdc or 0 (4)-20 mA - specify - (Sourcing output)	
igital Communication Standard: RS232 Options: Profibus-DP®, DeviceNet™, EtherCAT®, Modi		

Electrical Connection

Analog/RS232	9-pin D-connector (male)	
Profibus-DP®	Bus: 9-pin D-connector (female) Power: 9-pin D-connector (male)	
DeviceNet™	5-pin M12-connector (male)	
EtherCAT®	2 x RJ45 modular jack (in/out)	
Modbus-RTU/FLOW-BUS	RJ45 modular jack	
Technical specifications and dimensions subject to change without notice.		

Dimensions




Compression	Size A
Fitting 10 mm OD	1.220 (31.0)
Fitting 12 mm OD	1.319 (33.5)
Fitting 20 mm OD	1.437 (36.5)
Fitting 25 mm OD	1.654 (42.0)
Fitting 3/8" OD	1.209 (30.7)
Fitting 1/2" OD	1.319 (33.5)
Fitting 3/4" OD	1.370 (34.8)
	1/2"BSPP
Face-Seal Male	Α
Fitting 1/2" inlet	1.087 (27.6)
Fitting 3/4" inlet	1.437 (36.5)


1/2"BSPP

(Millimeters)

Ordering Information



Hook-up Diagram for Analog or RS232 Communication




Note: Pin 4 and Pin 8 should be seperatly and connected to power common at the power supply.


Note: When using a unit configured for a fieldbus or RS232 I/O, it is not possible to operate the instrument using analog I/O without changing the "control mode" parameter. (See users manual)

Note: For hookup details of modbus, Profibus or DeviceNet communications, see users manual.

Note: Do not connect external valve to instruments configured as flow meters

Note: Valve out signal is 0 - 10 Vdc, .1mA





MARNING - USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

Offer of Sale

The items described in this document are hereby offered for sale by Parker-Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the detailed "Offer of Sale" elsewhere in this document or available at www.parker.com/offerofsale.

WS-0032 Rev. B 10/13

Parker Hannifin Corporation **Porter Instrument Division** 245 Township Line Road Hatfield, PA 19440 phone 215 723 4000 fax 215 723 2199 industrial@parker.com

www.parker.com/porter

