

# Compound S0614

VMQ, red

## Compound Data Sheet

Creator

DM / 06.08.2021

Print-Date

29.03.2023

Status

Release

Data created electronically. This document is not subject to change management.  
Not signed.

## Physical properties

Test	Norm	Specimen	Ref. Value	Typ. Value	Unit
Hardness	DIN ISO 48-4	> 6 mm	80 ± 5	81	Shore A
Density	DIN EN ISO 1183-1		1.46 ± 0.03	1.46	g/cm <sup>3</sup>
Tensile strength	DIN 53 504	S2	≥ 6.5	7.1	N/mm <sup>2</sup>
Ultimate elongation	DIN 53 504	S2	≥ 160	174	%
Modulus 100%	DIN 53 504	S2	≥ 4.0	4.4	N/mm <sup>2</sup>
Compression Set 70h/150°C	DIN ISO 815-1	25 % Deformation, Test specimen B, Methode A		18	%
TR10	ISO 2921	2 mm		-47	°C

## Approvals

MIL-ZZ-R-765 B CLASS 2A, 2B, GRADE 80

## Aging Tests

Medium	Time (h)	Temp. (°C)	Norm	Properties		Typical value	
				Δ Hardness (ShA)	Δ Volume (%)	Δ RF (%)	Δ RD (%)
ASTM-1	168	125	DIN ISO 1817	-4.0	+1.9		
air	336	200	DIN 53 508	+5.0			

The test results are mean values and represent typical material properties. They are not to be used as specification values.  
These test results are gained under usual laboratory conditions and do not necessarily correspond to results measured on finished goods.  
The compound information does not release the user from the necessity to conduct his own testing.

We reserve the right to make technical alterations.

© 2020, Parker-Hannifin Corporation. All Rights Reserved. Subject to change.



Parker Hannifin Manufacturing Germany GmbH & Co.KG  
Engineered Materials Group Europe  
Prädifa Technology Division  
Arnold-Jäger-Str. 1  
74321 Bietigheim-Bissingen • Germany  
Tel. +49 (0) 7142 351-0 • Fax +49 (0) 7142 351-293