










# SENSOCONTROL PRODUCTS

Product	Description	Tech Features	QR Code
 <p>ServiceJunior</p>	Parker's ServiceJunior is ideal to digitally measure and display pressure with high precision in any hydraulic or pneumatic system.	<ul style="list-style-type: none"> <li>- Easy to use, robust and reliable</li> <li>- Measurement ranges up to 1000 bar</li> <li>- Accuracy up to 0.1%</li> <li>- Data logger function optional</li> </ul>	
 <p>ServiceJunior CONNECT</p>	The Parker ServiceJunior CONNECT is a compact, digital pressure gauge designed for precise pressure measurement in hydraulic and pneumatic systems. This user-friendly device features a high-resolution display and Bluetooth connectivity, allowing for easy data transfer and real-time monitoring via compatible mobile devices and software applications.	<ul style="list-style-type: none"> <li>- Capture minimum/maximum pressure changes at a rate 10ms</li> <li>- Digital readout more accurate than mechanical</li> <li>- Exportable records and proof-of-work statements</li> <li>- Set alarms, create/view graphs, create asset records</li> </ul>	
 <p>ServiceJunior (with Data Logger)</p>	The Parker ServiceJunior with Data Logger is a versatile and compact digital pressure gauge designed for accurate pressure measurement and data recording in hydraulic and pneumatic systems. This advanced device features a high-resolution display for clear readings and an integrated data logger that captures and stores pressure data over time.	<ul style="list-style-type: none"> <li>- Digital pressure measurement with backlit display</li> <li>- Measurement range up to 1000 bar</li> <li>- Accuracy up to 0.1%</li> <li>- Data logger function with integrated memory</li> <li>- Pressure peak measurement with 10ms scanning rate</li> </ul>	
 <p>Serviceman Plus</p>	The Serviceman Plus is a robust, portable and easy-to-use measuring device. With a scan rate of 1 ms and the ability to read pressure, flow, temperature and RPM, it is versatile for use with mobile/industrial systems. The Serviceman Plus is available in two designs: One with two inputs for analog sensors and the other with CAN interface for up to three CAN sensors.	<ul style="list-style-type: none"> <li>- Easy to use, robust, and reliable</li> <li>- Automatic sensor recognition</li> <li>- Up to 3 sensors</li> <li>- PC connection</li> <li>- SensoWin® 7.1 PC software</li> </ul>	
 <p>Service Master Compact</p>	The Service Master COMPACT provides real-time monitoring and diagnostics of key parameters such as pressure, temperature, and flow rate, enabling proactive issue detection. The device, available in three versions, is compatible with various Parker sensors and comes with complimentary SensoWin® 7 software.	<ul style="list-style-type: none"> <li>- Easy to use, robust, and reliable</li> <li>- 3 versions for up to 6 sensors with sensor recognition and 2 auxiliary sensors</li> <li>- SensoWin® 7.6 PC software</li> </ul>	
 <p>Service Master CONNECT</p>	The Parker Service Master CONNECT is a powerful diagnostic measuring device for mobile, stationary hydraulic applications with up to 100 channels.	<ul style="list-style-type: none"> <li>- Intuitive operation, robust and reliable</li> <li>- Modular system with individually exchangeable measuring modules</li> <li>- Record, save and analyze measurement data</li> <li>- SensoWin® 7.6 PC software</li> </ul>	

## Additional QR Code Links



SensoWin Setup



Flow Meters



The Parker Service Master  
CONNECT Firmware



Link to Parker.com for sensors

