

# 930 Series

## UHP Stainless Steel Diaphragm Valve Welded

aerospace  
climate control  
electromechanical  
filtration  
fluid & gas handling  
hydraulics  
pneumatics  
process control  
sealing & shielding

### Value Proposition:

The 930 Series valves are designed for ultra high purity applications for Semiconductor OEM and process wafer manufacturing.

The 930 Series is available with a variety of manual operators and air operated actuators. The air operated actuators are provided with an LP (125 PSI) or an MP (300 PSI) operating range.

The 300 psig operating pressure for both the manual and the AOPMP (mid-pressure) valves offers an extended application range for this product series.



### Contact Information:

Parker Hannifin Corporation  
**Veriflo Division**  
250 Canal Blvd  
Richmond, California 94804

phone 510 235 9590  
fax 510 232 7396  
veriflo.sales@parker.com

www.parker.com/veriflo  
Mobile App: m.parker.com/veriflo

### Product Features:


- Standard surface finish 5 micro inch Ra
- Internally threadless and springless
- Fully functional from vacuum to 300 psig
- High cycle life (including corrosive service)
- 100% Helium leak tested
- Standard full internal electropolish
- Minimal particle generation and particle entrapment areas
- Vericlean™, Veriflo's low sulfur high purity 316L Stainless Steel enhances electropolishing, welding, and corrosion resistance



ENGINEERING YOUR SUCCESS.

# 930 Series

## Dimensional Drawings



Actuator Style	Actuator Diameter (A)	Height (B)	Lever Radius (C)
AOPLPNC	1.12	3.35	-
AOPLPNO	1.29	2.97	-
AOPMPNC	1.55	3.37	-
G	-	*	-
I	1.70	2.58	-
L	-	2.56	1.75
M	-	2.56	.75
S	2.00	2.83	-

\* See dimensional drawing.

Port Style	End-To-End Length (D)	Square Body Size (E)
FS	2.78	1.125
FS8	4.14	1.25
TS	1.75	1.125
TS6	2.24	1.125
TS8	2.24	1.25

# 930 Series

## Ordering Information

Build a 930 Series valve by replacing the numbered symbols with an option from the corresponding tables below

Contact factory for most up to date lead time information.

Blue = Configurations that have selections in blue will require a price quote and lead time from the factory.

Sample: **9 30 AOPLPNC S FS FM VESP**  
Finished Order: **930AOPLPNCFSFMVESP**

**1 Basic Series**  
30 = 930

**2 Type**  
AOPLPNC = Air Operated, Low Pressure, Normally Closed *Air Connection is 1/8" NPT*  
AOPLPNO = Air Operated, Low Pressure, Normally Open *Air Connection is 1/8" NPT*  
AOPLP1NC = Air Operated, Low Pressure, Normally Closed *Air Connection is 1/8" Tube*  
AOPLP1NO = Air Operated, Low Pressure, Normally Open *Air Connection is 1/8" Tube*  
AOPMP1NC = Air Operated, Medium Pressure, Normally Closed *Air Connection is 1/8" Tube*  
G = Toggle  
I = Indicating Hand wheel  
K = LockOut-TagOut Manual Valve  
L = Lever  
M = Mini-Lever  
S = Spin Handwheel

**3 Body Material**  
S = 316L Stainless Steel


**4 Port Style**  
FS = 1/4" Face Seal *Standard only when configured as FSFS*  
FS8 = 1/2" Face Seal  
TS = 1/4" Tube Stub *Standard only when configured as TSTS*  
TS6 = 3/8" Tube Stub  
TS8 = 1/2" Tube Stub  
*Note: 1/2" Connections: Use a larger size body, please see dimensional drawings.*  
*Note: Combinations of Port Style options may have an extended lead time.*  
*Note: For Multiport: See 25000178 Valve Selection Guide. All Multiport configurations are Special Order.*

**5 Port Configuration**  
M = Male Face Seal  
F = Female Face Seal

**6 Optional Features**  
This section can have multiple options

BK = Black Lever  
LK = LockOut-TagOut *LK includes LockOut-TagOut bracket for G-Type Valve; LOTO Clamp for M type Valve*  
LSC = Limit Switch Closed *Available with AOPLPNC or AOPMP1NC options only*  
LSO = Limit Switch Open *Available with AOPLPNC or AOPMP1NC options only*  
PM = Panel Mount *Not available on I and AOP versions*  
RD = Red Lever  
VESP = Vespel® Seat *Recommended for Nitrous Oxide (N2O) Service*  
2.3 = 1/4" Fixed Male Face Seal (2 Port Only)  
PEEK = PEEK™ Seat  
NPNO = NPN Proximity Switch, 8" Long Cable *Available with Normally Open or Normally Closed Actuators*  
NPNO1 = NPN Proximity Switch, 40" Long Cable *Available with Normally Open or Normally Closed Actuators*

### NPN CONNECTOR PIN CONFIGURATION:



# 930 Series

## Specifications

Materials of Construction	
<b>Wetted</b>	
Body	VeriClean™ 316L Stainless Steel
Diaphragm	Elgiloy® or equivalent
Seat Options	PCTFE (std), PEEK™ or Vespel®
<b>Non-wetted</b>	
Cap	17-4 Stainless Steel
Nut	316L Stainless Steel
Actuator Housing	Anodized Aluminum
Operating Conditions	
<i>(Operating limits based upon pressure applied at inlet port.)</i>	
Maximum Pressure	
AOPLP, G	125 psig (8.6 barg)
AOPMP, K, L, I, M, S	300 psig (20.7 barg)
Minimum Pressure	Vacuum
AOP Actuation Pressure	75 psig (5.2 barg) nominal
Temperature	-40°F to 150°F (-40°C to 66°C)
Bake Out	250°F (121°C) in the open position

For additional information on materials of construction, functional performance and operating conditions, please contact factory.

Vespel® is a registered trademark of DuPont Performance Elastomers L.L.C.  
 Elgiloy® is a registered trademark of Elgiloy Company  
 VeriClean™ is a trademark of Parker Hannifin Corporation  
 PEEK™ is a trademark of Victrex plc.

Functional Performance	
<b>Design</b>	
Proof Pressure	
AOPLP, G	188 psig (13.0 barg)
AOPMP, K, L, I, M, S	450 psig (31.0 barg)
Burst Pressure	
AOPLP, G	375 psig (25.9 barg)
AOPMP, K, L, I, M, S	900 psig (62.1 barg)
Design Pressure <sup>(1)</sup>	
AOPLP, G	151 psig (10.4 barg)
AOPMP, K, L, I, M, S	330 psig (22.8 barg)
<b>Flow Capacity</b>	
AOP	C <sub>v</sub> 0.3
Lever	C <sub>v</sub> 0.22
<b>Leak Rate</b>	
Internal	≤ 1 X 10 <sup>-9</sup> scc/sec He
External	≤ 2 X 10 <sup>-10</sup> scc/sec He
Internal Volume	2.64 cc
Approx. Weight	1.75 lbs. (0.80 kg)
Limit Switch (Optional)	
Type	Single Pole, Single Throw (SPST) momentary action, non-adjustable
Rating	
AOPLPLSC, AOPMPLSC	1/4 amp at 115 vac (normally closed)
AOPLPLSO, AOPMPLSO	1/2 amp at 115 vac (normally open)
Wire Length	7 inch lead
Wire Type	26 AWG, UL Style 1061 or equal, twisted pair
Wire Ends	1/8" strip tinned ends

1. Design pressure per KOSHA Guide D-5-2012, Para. 6.2.

### OFFER OF SALE:

The items described in this document are hereby offered for sale by Parker-Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the detailed "Offer of Sale" elsewhere in this document or available at [www.parker.com/veriflo](http://www.parker.com/veriflo)



### WARNING USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE. THIS DOCUMENT IS FOR REFERENCE ONLY. PLEASE CONSULT FACTORY FOR LATEST PRODUCT DRAWINGS AND SPECIFICATIONS

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

The products described herein, including without limitation, product features, specifications, designs, availability and pricing are subject to change by Parker Hannifin Corp and its subsidiaries at any time without notice.

Proposition 65 Warning: This product contains chemicals known to the state of California to cause cancer or birth defects or other reproductive harm.

© 2009 Parker Hannifin Corporation



Use mobile device to scan this QR Code.

LitPN: 25000159

Rev: N

Date of Issue 02/2020



ENGINEERING YOUR SUCCESS.