

For additional information see Technical Tips on pages BC2-BC3.

		VALVE			
		Parker	Waterman	FPS	CEC
CAVITY	Parker	X	X		
	Waterman	X	X		
	FPS				
	CEC				X

Hydraulic Oil 150 SSU @ 100°F (32 cSt)

Flow (Q)	Flow (LPM)	Flow (GPM)	Pressure Drop (PSI)	Pressure Drop (Bar)
0	0	0	0	0
10	19	5	20	1.4
20	38	10	40	2.8
30	57	15	60	4.1
40	76	20	80	5.5
50	95	25	100	6.9
60	114	30	120	8.3

Diagram illustrating the connection between a **B12** 12 Size, a **3** 3-Way Cavity, and a **12T** Port Size.

Code	Port Size
12T	SAE - 12/Steel (5000PSI)

Weight: 2.0 kg (4.5 lbs.)

Technical Data	TD
Bodies & Cavities	BC
Coils & Electronics	CE
Proportional Valves	PV
Solenoid Valves	SV
Directional Controls	DC
Logic Elements	LE
Pressure Controls	PC
Flow Controls	FC
Load/Motor Controls	LM
Shuttle Valves	SH
Check Valves	CV