

Specifications:

Diesel Applications

Height: 75900MAX: 16.5" (41.9 cm)
 751000MAX: 22.0" (55.9 cm)
 75900MAXM: 15.8" (40.1 cm)
 751000MAXM: 21.8" (55.4 cm)

Width: 18.75" (47.6 cm) with Bracket

Depth: 10.8" (27.4 cm) with Bracket

Weight: 75900MAX: 23.0 lbs (10.4 kg)
 751000MAX: 30 lbs (13.6 kg)
 75900MAXM: 23.0 lbs (10.4 kg)
 751000MAXM: 30 lbs (13.6 kg)

Valve Male Fittings:
 7/8"-14 UNF-2A
 (SAE J514 37° Flare)


Service Clearance (Top):
 75900MAX: 5.0" (12.7 cm)
 751000MAX: 10.0" (25.4 cm)

Vacuum Installation Recommended
Maximum Head Pressure: 15 psi (1.03 bar)


Max Flow Rate:
 75900MAX: 180 gph (682 lph)
 751000MAX: 360 gph (1362 lph)

MA/MAM Model Superseded to VMA/VMAM Model.
 See RSL0428 MA-VMA Change Notification
 for available assembly crosses.


Dimensions:




75900MAX/ 751000MAX Top




751000MAX Front



75900MAXP Profile



75900MAXM Profile




751000MAXM Profile



PARTS

Turbine Series - 75900/1000MAX/M/P

1



Part #	Description
1A	Mounting Bracket - 75900MAX - Bracket only (Beige Color)
1B	Mounting Bracket - 751000MAX - Bracket only (Beige Color)

2A	RK19669	Vacuum Gauge (30" Hg) - 3 needles: Theshold (red), Max Change Out (Red - Adjustable), Gauge (Black)
	RK19667	Optional - Compound Gauge Kit (Vacuum 30" HG / Pressure 15psi)

3A	RK 19473 RK 19506	6-Port Ball Valve Valve Service Kit - Includes Handle/Stem/O-rings/Gasket
----	----------------------	--

4A	RK 19475	Rigid Tubing Kit - Includes (1ea.) Tube, Ferrule and Fitting
----	----------	--

5A		Turbine Fuel Filter - 900MA Series See Cutsheet RSL0293 for available Parts and Accessories
5B		Turbine Fuel Filter - 1000MA Series See Cutsheet RSL0293 for available Parts and Accessories

Accessories and Parts Available (Not Shown)

6A	RK 11-1952	Complete Seal Service Kit - 900MA/1000MA Series Filters (Requires 2)
6B	RK 21069 RK23191	WIF Probe (pig tail) - 1/2"-20 UNF - Requires 6C WIF Probe (Steel/pig tail) - 1/2"-20 UNF - Requires 6C
6C	RK 14329 RK 14321	Water Detection Module - 12 vdc Water Detection Module - 24 vdc


7A		Bowl Gasket - Included in 6A
7B	RK 11-1606-1	MA Bowl Kit (Clear) - Includes 7A, 7E & 7H (Gasket & O-ring only)
7C	RK 11734-03	MAM Bowl Kit (Metal) - Includes 7A, 7D & 7G
7D	RK 20022	Metal Bowl Plug Kit (MAM) (O-ring Included in 6A)
7E	RK 20126	Plastic Bowl Plug Kit (MA) (O-ring Included in 6A)
7F	RK 11868	Heat Deflector Kit (MA) - Includes 7H
7G		Drain Plug (MAM) - <i>Contact Technical Support</i>
7H	RK 11-1910	Drain Plug Kit (MA) (Gasket & O-ring Included in 6A)

8A	2040V2 2040V10 2040V30	900MA/MAM Replacement Element 2 micron 900MA/MAM Replacement Element 10 micron 900MA/MAM Replacement Element 30 micron
8B	2020V2 2020V10 2020V30	1000MA/MAM Replacement Element 2 micron 1000MA/MAM Replacement Element 10 micron 1000MA/MAM Replacement Element 30 micron


2




3



4



5



See **RSL0293**
For 900MA/1000MA Parts Breakdown

Valve Operations

