

Specifications:

Height: DFBO-10-IN 21.34" (54.2 cm)
 DFBO-14-IN 25.3" (64.26 cm)
 DFBO-10-MA 22.66" (57.56 cm)
 DFBO-14-MA 26.8" (68.07 cm)

Width: 21.62" (54.9 cm)

Depth: 8.81" (22.38 cm)

Weight: DFBO-10-IN: 80 lbs
 DFBO-14-IN: 85 lbs
 DFBO-10-MA: 80 lbs
 DFBO-14-MA: 85 lbs

Ports: 1.0" NPT Female (Inlet and Outlet)

Service Clearance (Drop-down): 1.13" (2.87 cm)

Max Pressure: 150 psi (10.0 bar) (IN)
 100 psi (7.0 bar) (MA)


Max Flow Rate Vacuum: DFBO-10 (Single) 11.9 gpm (45 lpm); (Dual) 15.9 gpm (60 lpm).
 Pressure: DFBO-10 (Single) 18.5 gpm (70 lpm); (Dual) 26.4 gpm (100 lpm).
 Vacuum: DFBO-14 (Single) 15.9 gpm (60 lpm); (Dual) 21.1 gpm (80 lpm).
 Pressure: DFBO-14 (Single) 23.8 gpm (90 lpm); (Dual) 34.3 gpm (130 lpm).

Fuel Type: Diesel (up to B20)

Create a Part Number


Housing Type	Housing Size	Assembly Type
Dual FBO Assembly	10" Height 14" Height	Delta-P Indicator (0-15 PSID) Vacuum Gauge (0-30" Hg)
DFBO	10 14	IN MA

Mounting Information:




ASSEMBLY	DESCRIPTION
DFBO-10-IN	10" Assy., Drain Valve, Delta-P Indicator, Sight Glass, 25 micron Coalescer/Separator filter
DFBO-10-MA	10" Assy., Drain Valve, Vacuum Gauge, 25 micron Coalescer/Separator filter
DFBO-14-IN	14" Assy., Drain Valve, Delta-P Indicator, Sight Glass, 25 micron Coalescer/Separator filter
DFBO-14-MA	14" Assy., Drain Valve, Vacuum Gauge, 25 micron Coalescer/Separator filter


Dimensions:




DFBO-10-IN SHOWN
Front




DFBO-10-MA SHOWN
Profile



DFBO-14-MA SHOWN
Front



DFBO-14-IN SHOWN
Profile



DFBO-10-IN SHOWN



PARTS

DFBO Series

1




1A



1B

2




2A


2B

2C

3



3A




3B




3C

4



4A



4B

Part # Description

1A	RK19669	Vacuum Gauge Kit (0-30" Hg) (Marine)
1B	72694	Differential Pressure Indicator (0-15 PSID) (Industrial)
	72783	Differential Pressure Indicator (0-30 PSID) (Industrial)

2A	73354002	DFBO Vent Valve Kit (Black)
2B	73341	Valve O-ring Kit
2C	0V-13	FBO Bowl/Housing Viton® O-ring

Racor FBO Elements are printed with codes. Use Code Key to find replacement part#.
FILTER CODE EXAMPLES: C10/1 = FBO 60327; F14/10 = FBO 60357; W10/25 = FBO 60335

Filter Type

Coalescer/Separator	Particulate	Water Absorber
C	F	W

Housing Size

10" Height	14" Height
10/	14/

Micron Size

1 Micron	5 Micron	10 Micron	25 Micron
1	5	10	25

3A	FBO-10 Replacement Elements Includes 2B	Micron	Coalescer/Separator C	Particulate F	Water Absorber W
	10/	1	FBO 60327	FBO 60330	FBO 60333
		5	FBO 60328	FBO 60331	FBO 60334
		10	FBO 60353	FBO 60354	FBO 60355
		25	FBO 60329	FBO 60332	FBO 60335
3A	FBO-14 Replacement Elements Includes 2B	Micron	Coalescer/Separator C	Particulate F	Water Absorber W
	14/	1	FBO 60336	FBO 60339	FBO 60342
		5	FBO 60337	FBO 60340	FBO 60343
		10	FBO 60356	FBO 60357	FBO 60358
		25	FBO 60338	FBO 60341	FBO 60344
3B	72609	FBO-10 Bowl/Housing (Black)			
	72610	FBO-14 Bowl/Housing (Black)			
3C	72710	1/2" NPT Brass Sight Glass (Industrial)			

4A	RK73301001	DFBO Flange (White) - Includes 2B
4B	73225-.5	1/2" NPT Brass Locking Ball Valve (Industrial)

Additional Parts Available (Not Shown)

5A	RK23191	WIF Sensor (Steel) - 1/2"-20 SAE Thread (pigtail wires) - Requires 5B
	RK23191-03	WIF Sensor (Steel) - 1/2"-20 SAE Thread - Requires 5B
5B	RK18-1656	1/2"-14 NPT - 1/2"-20 SAE Steel Adapter - Sight Glass Port - Use with 5A