



RS and AXEM Series

DC Servo Motors



ENGINEERING YOUR SUCCESS.



WARNING — USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

- This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.
- The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.
- To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

High Performance DC Servo Motor - RS Series

Overview 4

Technical Data 5

Dimensions..... 6

Options 8

Order Code 9

Pancake DC Servo Motor - AXEM Series

Overview 10

Technical Data 11

Dimensions..... 11

High Performance DC Servo Motor - RS Series

Overview

Description

Using high energy magnets, RS DC motors are particularly suitable for applications which require a very compact solution or a high dynamic level. Characteristics and advantages

- High performance characteristics
- Excellent low-speed functioning
- High compactness
- Very long service life
- Rare earth magnets
- Tacho and brake in option

Features

- **Shaft**
 - RS2 to RS4: Smooth full shaft
 - RS5 and RS6: Full keyed shaft
- **2nd Shaft end**
 - RS2 to RS3: possibility to mount standard tacho or encoder
 - RS5 and RS6: possibility to mount standard tacho, adaptation for encoder mounting in option
- **Output cables 1 m without connector**
- **Options**
 - Brake (RS2 to RS6)
 - Tachometer
 - Adaptation 2nd shaft end for encoder mounting (RS5 and RS6)




Technical Characteristics - Overview

Motor type	DC motors with rare earth magnets
Number of poles	4
Protection degree	<ul style="list-style-type: none"> • RS2 to RS4: IP40 • RS5 and RS6: IP54
Insulation	Class F
Torque at low speed	0.22 ... 13 Nm
Permanent current at low speed	4.1 ... 28 A
Rated voltage	25.4 ... 105 V
Rated speed	2000 ... 3000 min ⁻¹
Rotor inertia	195 ... 8300 kgmm ²

Technical Data

Torque at low speed M_0 [Nm]	Permanent current at low speed I_0 [A]	Rated Voltage U [V]	Rated Speed N [min ⁻¹]	Rotor Inertia [kgmm ²]	Product Code		
0.225	4.1	25.4	3000	195	RS220FR1	■	00
0.232	2.8	38.6	3000	195	RS220KR1	■	00
0.31	5.6	24	3000	26	RS230CR1	■	00
0.39	6	27.6	3000	325	RS240BR1	■	00
0.54	4.5	49	3000	83	RS320HR1	■	00
0.78	5.9	51	3000	110	RS330ER1	■	00
0.98	6.9	53	3000	140	RS340CR1	■	00
0.48	3.6	60	3000	137	RS410RR1	■	00
0.93	6.2	60	3000	225	RS420JR1	■	00
1.3	8.1	43	2000	310	RS430FR1	■	00
1.36	6.6	78	3000	310	RS430HR1	■	00
1.74	7	90	3000	400	RS440GR1	■	00
1.9	7.9	82	2700	1 000	RS510LR1	■	00
3.1	10.9	92	2700	1 350	RS520GR1	■	00
4	13	97	2700	1 700	RS530ER1	■	00
5	15	104	2700	2 050	RS540CR1	■	00
8	22.3	100	2400	5 300	RS620GR1	■	00
10.8	25	100	2000	6 800	RS630FR1	■	00
13	28	105	2000	8 300	RS640ER1	■	00

RS5 and RS6



RS5 and RS6 with brake, tacho and encoder dimensions

Motor	P	N	C	D	LC	E	T	B1	PB	L	F	B2	S	M	MGxJ	HC	Weight [kg]	Fr ⁽¹⁾ [daN]	Fa ⁽¹⁾ [daN]
RS510	97	95	21.5	19	30	40	3	96	25	151	91	96	7	115	M6x18	6	5.1	70	23
RS520	97	95	21.5	19	30	40	3	96	25	180	91	96	7	115	M6x18	6	6.3	70	23
RS530	97	95	21.5	19	30	40	3	96	25	209	91	96	7	115	M6x18	6	7.5	70	23
RS540	97	95	21.5	19	30	40	3	96	25	238	91	96	7	115	M6x18	6	8.7	70	23
RS620	120	110	27	24	40	50	3.5	117	30	246	93	117	10	130	M8x20	8	11.5	80	26
RS630	120	110	27	24	40	50	3.5	117	30	284	93	117	10	130	M8x20	8	14	80	26
RS640	120	110	27	24	40	50	3.5	117	30	321	93	117	10	130	M8x20	8	16.3	80	26

⁽¹⁾ Fr and Fa not cumulative

Options

Tachometers and brakes						
Motors	Tachometer		Brakes [Voltage 24 VDC +/- 10 %]			
			Holding torque [Nm]		Inertia [kgmm ²]	Weight [kg]
	Model	EMF [V/1000 min ⁻¹]	20 °C	100 °C		
RS2	TBN 206	6	0.6	0.55	2	0.2
RS3	TBN 206	6	1.5	1.4	10	0.18
RS4	TBN 206	6	1.5	1.4	10	0.18
RS5	TBN 306	6	6	5.5	53	0.45
RS6	TBN 306	6	12	11.5	157	0.9

Encoders					
Model	Associated motors	Pulse per rev	Encoder reference	Mounting kit reference	Connector reference
C2	RS2 / RS3 / RS4	500	220215P0001	220071R0025	
	RS2 / RS3 / RS4	1000	220215P0004	220071R0025	

Other encoders: on request

Order Code

RS Series

	1	2	3	4	5	6	7
Order example	RS	220	F	R	1	0	11

1	Motor type	
	RS	Motor with neodyme magnets
2	Motor size and length	
	220	
	230	see table "Technical data"
	320	
	...	
3	Winding	
	F	Depend of motor size, speed and
	L	voltage/current,
	H	see table "Technical data"
	...	
4	Fix code	
	R	
5	Mechanical features	
	1	Output cables (standard)
6	Options	
	0	No accessories (standard)
	1	Tacho
	2	Brake (RS2 to RS6)
	3	Tacho + brake (RS2 to RS6)
	4	Encoder adaptation ⁽¹⁾ (size 5 and 6 only)
	5	Tacho + Encoder adaptation (size 5 and 6 only)
	6	Brake + Encoder adaptation (size 5 and 6 only)
	7	Tacho + Brake + Encoder adaptation (size 5 and 6 only)
7	Customer specification	
	00	Standard catalogue definition - smooth shaft (size 1 -> 4) - shaft with key way (size 5-6)

⁽¹⁾ Encoder adaptation is standard for RS2, RS3 and RS4.

Pancake DC Servo Motor - AXEM Series

Overview

Description

The AXEM motor, with more than 2 million units produced, is one of the most widespread servo motors in the world. With its disk rotor, composed solely of copper and insulator the Axem motor achieves high dynamics and excellent regulation of motion at low speed, as well as silent and vibration-free functioning.

It is robust, efficient, and low maintenance.

Advantages

- Very low speed modulation
- Exceptional regulation at low speed
- High dynamic characteristics
low rotor inertia
- Silent and vibration-free functioning
- Maintenance free
- Disk rotor
- Protection: IP44
- Class F insulation

Applications

- Factory Automation
- Life Science Diagnostic



Technical Characteristics - Overview

Nominal torque	0.14...19.2 Nm
Nominal current	6.4...44 A
Nominal voltage	14...178 V
Nominal speed	3000, 4800 min ⁻¹
Inertia	29...7400 kgmm ²




Technical Data

Motor	Nominal torque [Nm]	Nominal current [A]	Nominal voltage [V]	Nominal speed [min ⁻¹]	Inertia [kgmm ²]
F9M4R	0.14	6.4	22	4800	35
F9M2	0.282	11	14	3000	29
F9M4	0.346	6.7	26	3000	35
F9M4H	0.537	6.5	35	3000	34
MC19P	3.2	14.5	83	3000	1000
MC19S	3.2	7.3	165	3000	1000
MC24P	7.3	18.9	136	3000	3200
MC27P	14.3	33	152	3000	7400


Tachy		
Type	Associated motor	EMF [V/1000 min ⁻¹]
F9T	F9	3
FC12T	MC	6
TBN 206	F9	6
TBN 420	MC	20

Dimensions


F9 dimensions					
Motor	L1 [mm]	L2 [mm]	Weight [kg]	Fr ⁽¹⁾ [daN]	Fa ⁽¹⁾ [daN]
F9M4R	34	46.5	1.1	14	2.5
F9M2	52.5	65	2.3	14	2.5
F9M4	52.5	65	2.3	14	2.5
F9M4H	64	76.5	2.8	14	2.5

F9: $\varnothing B = \varnothing 110$ 

MC19 dimensions			
Motor	Weight [kg]	Fr ⁽¹⁾ [daN]	Fa ⁽¹⁾ [daN]
MC19	9.7	60	35

⁽¹⁾ Fr and Fa not cumulative

MC24 - MC27 dimensions			
Motor	Weight [kg]	Fr ⁽¹⁾ [daN]	Fa ⁽¹⁾ [daN]
MC24	23	80	45
MC27	35	90	50

⁽¹⁾ Fr and Fa not cumulative



European Headquarters
La Tuilière 6, 1163 Etoy,
Switzerland
Tel: +41 21 821 85 00

Your authorized distributor