

Turbine Series - 900FV/1000FV

FUEL

Specifications: Diesel Applications

Height: 900FV: 17.12" (43.47 cm)
1000FV: 22.23" (56.47 cm)

Width: 8.68" (22.00 cm)

Depth: 7.96" (20.23 cm)

Weight: 900FV: 10.0 lbs (4.5 kg)
1000FV: 10.8 lbs (4.9 kg)

Ports: 1 5/16"-12 UN-2B (SAE 1926-1)
2X 3/4" NPTF Adapters Supplied
2X Port Plugs Supplied

Service Clearance (Top): 900FV: 5.0" (12.7 cm)
1000FV: 10.0" (25.4 cm)

Vacuum Installation Recommended
Maximum Head Pressure: 15 psi (1.03 bar)

Max Flow Rate: 900FV: 90 gph (340 lph)
1000FV: 180 gph (681 lph)

Create a Part Number

Housing Type

Turbine Model
90 GPH Flow Rate

Turbine Model
180 GPH Flow Rate

Accessory Options

12 VDC Heater (325 watt)

24 VDC Heater (325 watt)

Filtration Rating




10 micron

900FV 1000FV

12 24








10

Dimensions:



PARTS

Turbine - 900FV/1000FV Series



Part #	Description
1A	RK11-2076 T-handle/Lid Kit - Includes 1B, 1C & 1D
1B	T-handle O-ring - Included in 8A
1C	900FV/1000FV Lid
1D	Lid Gasket - Included in 8A

2A	2040V2 2040V2LL 2040V10 2040V30	900FV Service Filter 2 micron - Includes 1B & 1D 900FV Service Filter 2 micron (Long Life) - Includes 1B & 1D 900FV Service Filter 10 micron - Includes 1B & 1D 900FV Service Filter 30 micron - Includes 1B & 1D
2B	2020V2 2020V2LL 2020V10 2020V30	1000FV Service Filter 2 micron - Includes 1B & 1D 1000FV Service Filter 2 micron (Long Life) - Includes 1B & 1D 1000FV Service Filter 10 micron - Includes 1B & 1D 1000FV Service Filter 30 micron - Includes 1B & 1D

3	RK11-2092 RK11-2093	Heater Kit - 12 vdc, 325 watt - Includes O-ring & Nut Heater Kit - 24 vdc, 325 watt - Includes O-ring & Nut
---	------------------------	--

4A	RK11-2077	Bracket Kit - Includes Bracket, Bolt, Washer, & Nut
4B	RK 11-1679	Feed-thru Plug - O-ring Included in 8A
4C	RK11-2078	Vacuum Gauge Port Plug
4D	RK11-2079	Valve Rebuild Kit

5A		Checkball and Gasket - Included in 5B & 8A
5B	RK11-2080	Centrifuge/Baffle/Checkball/Gasket Kit - Includes 6A Checkball and Gasket - Included in 8A

6A		Bowl Gasket - Included in 8A
6B	RK11-2081	Bowl Kit - Includes 6A, 6C, 6D, 6E & 6F
6C	RK 20126	Bowl Plug (O-ring Included in 8A)
6D		Self-venting Drain (Gasket Included in 8A)
6E		Bowl Ring
6F	RK 11542	Cap Screw Bowl Fasteners (set of 4)

7	RK11-2083	Mounting Bracket Kit - Includes Bracket & 4 bolts
---	-----------	--

Accessories and Parts Available - **Not Shown**

8A	RK 11-1952	Complete Seal Service Kit - 900FV/1000FV Series Filters
8B	RK11-2085	900FV/1000FV Port Plug & Adapter Kit
8C	RK19671 RK19672 RK033092 RK 19667	Stainless Steel T-handle with Vacuum Gauge Vacuum Gauge (30" Hg) - 1/4" NPT back mount Vacuum Gauge (30" Hg) - 1/4" NPT Remote mount Compound Gauge - pressure (15 PSI) and vacuum (30" Hg)
8D	RK 14329 RK 14321	Water Detection Module - 12 vdc Water Detection Module - 24 vdc
8E	RK30880E	WIF Sensor/Detection Kit - 1/2"-20 UNF
8F	RK11-1978	Checkball Spring Kit - For use with Primer Pump Kit 8G
8G	RKP1912-IM RKP1924	Primer Pump Kit - 12 vdc - Adds 3.25" (8.26 cm) to Height Primer Pump Kit - 24 vdc - Adds 3.25" (8.26 cm) to Height