


PAINTSTOP™ PLEATED FILTERS:

Premium Filtration for Aerospace Paint Booths

Stage-two and stage-three overspray filtration that protects your finish

In aerospace and paint overspray remediation applications, the quality of a painted finish is non-negotiable. Parker's PaintStop™ line of pleated filters provides NESHAP-compliant, high-performance filtration for paint spray booths, effectively capturing liquid and solid overspray to control paint emissions and maintain pristine conditions for exterior aircraft components. Designed for stage-two and stage-three booth configurations, **PaintStop II** and **PaintStop III** filters offer unmatched performance in the most demanding environments



Key Features

NESHAP Compliant

Meets stringent environmental standards for aerospace coatings applications.

EPA Method 319 Tested

Proven performance in capturing both liquid and solid overspray particles.

Two Product Options

- **PaintStop II:** Ideal for two-stage filtration systems
- **PaintStop III:** Designed for three-stage systems requiring added protection

High-Efficiency Synthetic Media

100% synthetic fiber construction delivers consistent filtration with uniform pleat spacing for optimized dirt holding.

Robust Construction

- Die-cut finger separators for pleat stability
- Moisture-resistant beverage board frame
- Corrosion-resistant galvanized steel support grid

Lower Pressure Drop

Engineered to outperform competitors with better airflow and longer filter life.

Delivering Consistent Quality in Every Spray Cycle

Parker PaintStop intake filters serve as the first line of defense against contaminants that could damage delicate painted surfaces.




PAINTSTOP™ FILTERS:

Built for Performance. Backed by Parker.

When you choose Parker, you're partnering with a global leader in HVAC and industrial filtration. Our PaintStop™ filters are more than just components – they're a critical part of your quality control system. PaintStop filters:

- **Extend system life** by protecting downstream HEPA filters
- **Captures paint overspray**, preventing contaminants from exiting the booth and into the environment
- **Support compliance** with EPA Method 319 and aerospace regulations
- **Improve booth performance** with even airflow and minimal resistance



PaintStop II and PaintStop III Product Specifications

Nominal Size (W x H x D) Inches	Actual Size (W x H x D) Inches	Airflow	PaintStop II Initial Resistance	PaintStop II MERV	PaintStop III Initial Resistance	PaintStop III MERV	Media Area High Cap (Square Feet)
20 x 20 x 2	19-1/2 x 19-1/2 x 1-3/4	333	0.06	11	n/a	n/a	12.4
20 x 25 x 2	19-1/2 x 24-1/2 x 1-3/4	417	0.06	11	n/a	n/a	15.5
24 x 24 x 2	23-3/8 x 23-3/8 x 1-3/4	480	0.06	11	n/a	n/a	17.9
20 x 20 x 4	19-1/2 x 19-1/2 x 3-3/4	333	0.04	11	0.08	14	18.7
20 x 25 x 4	19-1/2 x 24-1/2 x 3-3/4	417	0.04	11	0.08	14	23.5
24 x 24 x 4	23-3/8 x 23-3/8 x 3-3/4	480	0.04	11	0.08	14	27.4

NOTES:

1. MERV 10 ASHRAE Standard 52.2-2017
2. Rated face velocity: 120 FPM
3. Recommended final resistance: 0.50" to 1.00" W.G.
4. Continuous operating temperature: 225°F
5. Classified per UL 900 for flammability resistance

Ordering Information

PaintStop filters are available in standard and custom sizes to meet a wide range of paint booth specifications. Contact your Parker representative at **866-247-4827** or visit parker.com/hvac for ordering assistance.

Parker Hannifin Corporation
HVAC Filtration Division
100 River Ridge Circle
Jeffersonville, Indiana 47130
phone 866 247 4827
www.parker.com/HVAC

Supercode PaintStop Bulletin 8/25

© 2025 Parker Hannifin Corporation

