



aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding



Parker icountBS (IBS)

Portable and laboratory bottle sampling for hydraulic oil and fuel systems



ENGINEERING YOUR SUCCESS.

icount Bottle Sampler: Advanced contamination testing

The revolutionary icountBS is an advanced, fully contained bottle sampling system that ensures fast, accurate and repeatable detection of contamination in hydraulic oils and hydrocarbon fuels.

Compact and portable, the icountBS is ideal for use in the laboratory and in on-line and off-line applications. The system is fully accredited to all

particle counting standards - ISO, NAS, AS and GOST - including the latest ISO medium dust certification and is backed by Parker Hannifin's global customer support network.

The icountBS uses proven laser particle detection technology, with intuitive touch screen control, integrated long life rechargeable battery and a robust easy to clean

enclosure, to deliver exceptional product quality and performance.

The icountBS is quick to setup and use, delivers rapid test results and offers a wide range of features to help you improve the reliability, productivity and profitability of your production equipment.



The icountBS features a backlit 256 colour, high resolution touch screen and uses Windows® CE based menus.



Wherever, whenever you need to be 100% sure of oil and fuel quality

The icountBS has been developed using the latest industrial design and manufacturing techniques, creating a system that integrates state of the

art technology with dependable and precise measurement and analysis processes. Built by engineers, for engineers, the icountBS gives you a

valuable and extremely effective tool for use in many different applications.



Agriculture: Designed for a wide range of agricultural machinery monitoring and testing procedures to ensure reduced downtime.



Defence: Designed for use in defence airfield fuel supply and storage points, military laboratories and equipment maintenance zones.



Aerospace: Monitoring of hydraulic ground support equipment, airframe laboratories and aerospace testing facilities.



Oil and Gas: Ideal for use in fuel refineries (DEF STAN 9191), fuel farm storage, fuel laboratories and airport fuel transfer.



Construction: Ideal for use in construction machinery development and test laboratories



Marine: Suitable for shipyard and dockyard diagnostic centres and marine service environments.



Power Generation: Suitable for monitoring hydraulic gearbox (wind energy pitch and braking systems) quality as part of a planned maintenance programme.



Industrial: Test rigs, hydraulic benches and hydraulic controlled production lines, as well as hydraulic system test laboratories, all benefit from the IBS.

How the icountBS works

Our design, manufacturing and applications engineers have over 20 years experience working with advanced contamination and particle detection technologies. As a result, the latest version of the icountBS has been developed to meet the needs of customers throughout industry, both today and in the future.

Precision and repeatability




The icountBS is capable of entrapped gas suppression and automatically ensures that each oil sample is carefully regulated prior to test.

Every sample is degassed using suppressed, cleaned air and then delivered to the measurement cell through a fixed displacement pumping system.

This eliminates many of the variables

associated with traditional methods of contamination monitoring. Control and accuracy is further enhanced with an easy to use interactive touch screen display.

The backlit 256 colour high resolution screen uses intuitive Windows® CE based menus for quick and simple stylus operation, with the stylus being stored neatly in the base of the icountBS.



Laser power

At the heart of the system is a sophisticated laser detector, using a light obscuration flow cell, providing continuous measurement of fluid flow passing through a sample tube.




Fig 1. A controlled column of contaminated fluid enters the laser optical scanning chamber, which is designed to ensure balanced flow and fluid distribution for consistent results.




Fig 2. The laser is projected through the oil column onto a highly sensitive photo diode cell.





Fig 3. The shadow cast on the photo diode by contaminants in the oil creates a measurable change in the light intensity.

Fig 4. icountBS test procedure schematic



Tough and reliable

The icountBS is built to ensure a long and trouble free operating life. Its robust moulded enclosure will withstand constant use and is easy to clean.



Fig 4. The IBS oil sampling probe automatically lowers into the bottle once the test begins.

For optimum operational flexibility the icountBS can be powered either via an internal rechargeable lithium ion battery, or direct from a mains supply.

Internally, a high filtration air line filter removes impurities from air supply, while vane-type deflectors and drain valves improve efficiency still further.



Fig 5. IBS' high filtration air filter.

The integrated 12VDC compressor pressurises the sampling and measurement chambers quickly, with a compact syringe pump providing consistent oil or fuel samples.



Fig 6. IBS' integrated 12VDC compressor.

Benefits

- Low cost solution for monitoring fluid life and reducing machine downtime
- Easy to set up and use
- Powerful analysis options
- Proven, reliable technology
- Independent monitoring of contamination
- Calibration to ISO procedures
- Selectable number of samples taken in one time: 1, 2, 3, 4 or 5 tests
- Mineral fluid/fuel compatible construction
- Percentage saturation reporting (for the moisture sensor option)
- Testing capability of up to 500 continuous tests (override auto warning option available)
- Data exporting method to USB (in XML format)
- Modular design for easy servicing
- On-board high quality pump and motor configuration
- High resolution colour touch-screen panel and the IBS comes complete with its own stylus
- Integrated printer (selectable on/off feature)
- Self-diagnostic software
- Power-saving sleep mode with integrated wake up/power button
- On- and off-line pressure capability: see Ordering Information for options
- Integration package into the Parker MiniLab Environment: see Ordering Information for options

Contamination Standards Table

MTD	ACFTD
ISO 4406 : 1999	ISO 4406 : 1987
NAS 1638	ISO 4406 : 1991
AS4059E (Differential)	NAS 1638
AS4059E (Cumulative)	AS4059E (Differential)
Jet Fuel (contact Parker)	AS4059E (Cumulative)
	GOST 17216 : 2001

- 8 fixed channel size analysis
- Integrated relative humidity moisture sensor
- Selectable test sample sizes: 10, 20, 30, 40, 50, 60, 80 and 100ml
- Selectable flush sample sizes: 10, 15, 20, 25, 50 and 100ml

Features that boost your productivity



- 1** **Wake up switch**
Power button wake up switch: momentary LED illuminated switch, battery charger indicator.
- 2** **Printer access**
Internal thermal printer which uses a thermal printer paper reel.
- 3** **Stylus holder**
Plastic stylus in holder.
- 4** **Pressure chamber**
Front door with polycarbonate window.
- 5** **High resolution touch screen**
Intuitive touch screen display backlight 256 colour STN transmissive resolution – 302x3 (R.G.B) (H) X 240 (W) dots with active display area 115 (H) X 86 (W) mm. IBS mk 2 operating on Windows® CE system.
- 6** **Power supply**
Long life regulated 12 VDC power supply, with an M12, 4 pin connector, plus a rechargeable Lithium ion battery unit for use onsite or in remote locations.
- 7** **Body panels**
Body panels are made of resin composite.



Control Panel

KEY

- 1** Emergency air release
- 2** 4mm vapour release port
- 3** 6mm oil drain port
- 4** External air supply
- 5** External on-line oil supply (if fitted)
- 6** Long life Lithium Ion battery
- 7** USB connections A and B
- 8** Mains on/off and power socket
- 9** Ventilation fan (DO NOT BLOCK)

Product Specification

Dimensions are given in mm (inches)



Sample handling and preparation

Bottle cleanliness

Bottles should have sealing screw caps, with both parts cleaned to a suitable level in accordance with ISO3722. Standard Parker Hannifin bottles (supplied in pairs as part number ACC6NW001) are supplied clean to ISO 13/11 or better in a Class 10,000 Clean Room. The bottle should remain capped until the time of sample filling and be re-capped immediately afterwards.



Sample mixing

Sedimentation of contaminant in a sample will occur, the rate of which is dependent upon both the fluid and particle characteristics.

Other methods of sample agitation have not been provided, as they are likely inconsistently to distort the analysis of results. Where facilities are available, mixing can be achieved using 'paint shakers' and/or an ultrasonic bath. Take care when using ultrasonic baths to avoid distortion of the result by prolonged use, which could cause the breakdown of contaminants.

Bottle samples can be sufficiently stirred by swirling and tumbling by hand, end-over-end. Samples should be analysed, without delay, once agitated.

Results

The first result from a bottle sample should be disregarded, as it could be distorted by fluid from a previous sample. Samples from different parts of a system will give different results.

Consideration should be given to what monitoring is desired and where to extract samples from for suitable trend monitoring to be performed.


It is important that whatever practices you adopt, you must perform them consistently.

CMC Service Centres: Global Support for CMC products

Parker's fluid Condition Monitoring Service Centres can be found in ten locations around the globe, on almost every continent. Our experience and expertise in fluid condition monitoring and analysis ensure we are the authority within our industry.

Each location offers first class aftermarket support for condition monitoring products giving:

- Direct contact for end users.
- Quick and confident technical support to help you maintain an efficient and trouble free monitoring process.
- Faster turn around for annual calibration verification, eliminating the need for product to be returned to the country of manufacture.



Size	Counts	Code
A: 24um(c)	300	9
B: 26um(c)	100	27
C: 214um(c)	0	20
D: 221um(c)	0	20
E: 238um(c)	0	20
F: 270um(c)	0	20

Important Information

WARNING-USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

– This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

– The user, through their own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the applications are met.

– The user must analyse all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalogue and in any other materials provided from Parker or its subsidiaries or authorised distributors.

– To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems. The operation of the products described here in is subject to the operating and safety procedures details of which are available upon request.

Sales conditions

The items described in this document are available for sale by Parker Hannifin Corporation, its subsidiaries or its authorized distributors. Any sale contract entered into by Parker will be governed by the provisions stated in Parker's standard terms and conditions of sale (copy available upon request).

Viewing/Exporting test results




Select **Browse Tests** from the main **Test Set-up** screen.



List of **Saved Tests** is shown.



Select individual results and show date. You can double-click the test name to view that test result.



Click **Browse Tests** to view more test results.



Export results: Highlight the test result(s) you would like to export using the stylus.



Plug in USB in the back of the icoountBS.



Press **Export**. The **Export Complete** message confirms a successful export.

Test results (Importing data)

You can import the test results from the bottle sampler into a spreadsheet.

Please Note: The example shown is for Microsoft Excel®. Other spreadsheet software is available. Please contact Parker Hannifin for advice.



Plug USB drive from IBS2 into your PC.



Open your PC spreadsheet programme (for example Microsoft Excel®).

Technical Specifications

Feature	Specification																																																																																
Principle of operation	Laser diode optical detection of actual particulates																																																																																
Dimensions	H 530mm x W 210mm x D 410mm																																																																																
Weight	Approx 18kg																																																																																
Operating temperature and humidity	+5°C to +60°C (-41°F to +140°F) 20-85% RH (tested at 30°C (86°F), non-condensing)																																																																																
Storage temperature and humidity	-40°C to +90°C (-40°F to +194°F) 10-90% RH (tested at 30°C (86°F), non-condensing)																																																																																
Moisture sensor calibration	±5% RH (over a compensated temperature range of +10°C to +80°C (+50°F to +176°F))																																																																																
Moisture sensor stability	±2% RH typical at 50% RH in one year																																																																																
International codes	ISO 7 to 21, NAS 0 to 12, AS 0 to 12																																																																																
Contamination standards	Refer to Parker 'Guide to Contamination Standards' (DD0000015) on CD MTD : ISO 4406:1999; NAS 1638; AS4059E (Differential); AS4509E (Cumulative) ACFTD : ISO 4406:1987; ISO4406:1991; NAS 1638; AS4509E (Differential); AS4509E (Cumulative); GOST 17216 : 2001																																																																																
Channel sizes	<table border="1"> <thead> <tr> <th colspan="5">Channel Sizes: MTD µm(c)</th> </tr> <tr> <th>ISO 4406:1999</th> <th>NAS 1638</th> <th>AS4059E (Diff)</th> <th>AS4059E (Cum)</th> <th>Jet Fuel</th> </tr> </thead> <tbody> <tr> <td>>4</td> <td>4-6</td> <td>4-6</td> <td>>6</td> <td>>4</td> </tr> <tr> <td>>6</td> <td>6-14</td> <td>6-14</td> <td>>21</td> <td>>6</td> </tr> <tr> <td>>14</td> <td>14-21</td> <td>14-21</td> <td>>70</td> <td>>14</td> </tr> <tr> <td>>21</td> <td>21-38</td> <td>21-38</td> <td>-</td> <td>>21</td> </tr> <tr> <td>>38</td> <td>38-70</td> <td>38-70</td> <td>-</td> <td>>25</td> </tr> <tr> <td>>70</td> <td>>70</td> <td>>70</td> <td>-</td> <td>>30</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th colspan="5">Channel Sizes: ACFTD µm(c)</th> </tr> <tr> <th>ISO 4406:1987</th> <th>NAS 1638</th> <th>AS4059E (Diff)</th> <th>AS4059E (Cum)</th> <th>GOST 17216:2001</th> </tr> </thead> <tbody> <tr> <td>>2</td> <td>2-5</td> <td>2-5</td> <td>>5</td> <td>>2-5</td> </tr> <tr> <td>>5</td> <td>5-15</td> <td>5-15</td> <td>>15</td> <td>>5-10</td> </tr> <tr> <td>>15</td> <td>15-25</td> <td>15-25</td> <td>>25</td> <td>>10-25</td> </tr> <tr> <td>>25</td> <td>25-50</td> <td>25-50</td> <td>>100</td> <td>>25-50</td> </tr> <tr> <td>>50</td> <td>50-100</td> <td>50-100</td> <td>-</td> <td>>50-100</td> </tr> <tr> <td>>100</td> <td>>100</td> <td>>100</td> <td>-</td> <td>>100-200</td> </tr> </tbody> </table>	Channel Sizes: MTD µm(c)					ISO 4406:1999	NAS 1638	AS4059E (Diff)	AS4059E (Cum)	Jet Fuel	>4	4-6	4-6	>6	>4	>6	6-14	6-14	>21	>6	>14	14-21	14-21	>70	>14	>21	21-38	21-38	-	>21	>38	38-70	38-70	-	>25	>70	>70	>70	-	>30	Channel Sizes: ACFTD µm(c)					ISO 4406:1987	NAS 1638	AS4059E (Diff)	AS4059E (Cum)	GOST 17216:2001	>2	2-5	2-5	>5	>2-5	>5	5-15	5-15	>15	>5-10	>15	15-25	15-25	>25	>10-25	>25	25-50	25-50	>100	>25-50	>50	50-100	50-100	-	>50-100	>100	>100	>100	-	>100-200
Channel Sizes: MTD µm(c)																																																																																	
ISO 4406:1999	NAS 1638	AS4059E (Diff)	AS4059E (Cum)	Jet Fuel																																																																													
>4	4-6	4-6	>6	>4																																																																													
>6	6-14	6-14	>21	>6																																																																													
>14	14-21	14-21	>70	>14																																																																													
>21	21-38	21-38	-	>21																																																																													
>38	38-70	38-70	-	>25																																																																													
>70	>70	>70	-	>30																																																																													
Channel Sizes: ACFTD µm(c)																																																																																	
ISO 4406:1987	NAS 1638	AS4059E (Diff)	AS4059E (Cum)	GOST 17216:2001																																																																													
>2	2-5	2-5	>5	>2-5																																																																													
>5	5-15	5-15	>15	>5-10																																																																													
>15	15-25	15-25	>25	>10-25																																																																													
>25	25-50	25-50	>100	>25-50																																																																													
>50	50-100	50-100	-	>50-100																																																																													
>100	>100	>100	-	>100-200																																																																													
Calibration	MTD : via a certified primary ISO 11171 automatic particle detector using ISO 11943 principles, with particle distribution reporting to ISO 4406:1996 ACFTD : fully traceable to gravimetric first principles																																																																																
Recalibration	Contact Parker Hannifin for advice																																																																																
Fluid compatibility	Mineral-based oils and petroleum-based fuel - Contact Parker Hannifin for advice																																																																																
Fluid management	Selectable on screen between 10 to 100ml																																																																																
Viscosity range	1 to 300cSt																																																																																
Working pressure	3 bar maximum input pressure, if used on-line. Contact Parker Hannifin for further advice																																																																																
Flow range through icountBS2	Test: 60ml/min																																																																																
Connection interface (On Line)	INLET: 6mm push-fit, DRAIN: 4mm push-fit																																																																																
Fluid operating temperature (Oil)	+5°C to +80°C (-41°F to 176°F)																																																																																
Fluid operating temperature (Fuel)	+20°C to +70°C (-4°F to 158°F)																																																																																
Sample bottle size	See Parker ACC Spares list. Contact Parker Hannifin for advice																																																																																
Flush sample size	Selectable option within the icountBS Software: 10ml to 100ml																																																																																
Memory storage	500 tests (Integrated Warning Level)																																																																																
Printer	Thermal dot line printer - see ACC spares list for replacement paper																																																																																
Battery type	Polymer Lithium Ion Battery pack (ACC6NW032)																																																																																
Power requirements	Integrated supply into the icountBS unit																																																																																
Certification	CE Certified. Supplied with EC Declaration of Conformity Certificate																																																																																

Ordering Information

The icountBS is supplied with the following components:

- 250ml Bottle Kit (x2)
- Vapour/Waste Bottle (1000ml)
- 4mm and 6mm Blanking Plug
- CD manual
- Either UK, US or EUR Power Lead
- Spare Printer Roll
- Stylus Pen
- Battery with battery compartment panel
- Drip Tray

Key	Version		Options		Region	Part number
IBS	Mk II	3	MS/Online	000	EUR	IBS3000EUR*
IBS	Mk II	3	MS/Online	000	UK	IBS3000UK*
IBS	Mk II	3	MS/Online	000	USA	IBS3000USA*
IBS	Mk II	3	MS	100	EUR	IBS3100EUR
IBS	Mk II	3	MS	100	UK	IBS3100UK
IBS	Mk II	3	MS	100	USA	IBS3100USA
IBS (contact Parker)	Mk II	3	Fuel	100F	EUR	IBS3000FEUR*

Note: Transit Case Option.

*Please contact Parker for lead times

Transportation packaging specialists have been utilised to create a tailor-made shipping carton for the icountBS Mark II. If a plastic storage/presentation case is required, please see the accessory section below.

Accessory Part Numbers

Description	Part number
Power pack (UK 2m cable)	ACC6NW023
Power pack (US 2m cable)	ACC6NW024
Power pack (EUR 2m cable)	ACC6NW025



250ml Sample bottle kit (x2)	ACC6NW001
250ml Sample bottle kit (x50)	ACC6NW002



Vapour / waste bottle ACC6NW003



Printer paper reel ACC6NW005



On-line adaptor kit ACC6NW022

If the On-Line facility is not selected when the unit is initially purchased, it is available as an aftermarket upgrade. For details, please contact Parker.

Description	Part number
icountBS2 manual on CD	ACC6NW012



Verification Fluid SERMISC049



Battery Pack ACC6NW032



VTC Pen Drive ACC6NW033



Transit Case ACC6NW020

A robust plastic storage/presentation case is available to order as an optional accessory.



Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates,
Dubai

Tel: +971 4 8127100
parker.me@parker.com

AT – Austria, Wiener Neustadt

Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe,

Wiener Neustadt
Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AZ – Azerbaijan, Baku

Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles

Tel: +32 (0)67 280 900
parker.belgium@parker.com

BY – Belarus, Minsk

Tel: +375 17 209 9399
parker.belarus@parker.com

CH – Switzerland, Etoy

Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CZ – Czech Republic, Klecany

Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst

Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup

Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid

Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa

Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve

Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens

Tel: +30 210 933 6450
parker.greece@parker.com

HU – Hungary, Budapest

Tel: +36 1 220 4155
parker.hungary@parker.com

IE – Ireland, Dublin

Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IT – Italy, Corsico (MI)

Tel: +39 02 45 19 21
parker.italy@parker.com

KZ – Kazakhstan, Almaty

Tel: +7 7272 505 800
parker.easteurope@parker.com

NL – The Netherlands, Oldenzaal

Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Asker

Tel: +47 66 75 34 00
parker.norway@parker.com

PL – Poland, Warsaw

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal, Leca da Palmeira

Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest

Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow

Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga

Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SK – Slovakia, Banská Bystrica

Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto

Tel: +386 7 337 6650
parker.slovenia@parker.com

TR – Turkey, Istanbul

Tel: +90 216 4997081
parker.turkey@parker.com

UA – Ukraine, Kiev

Tel: +380 44 494 2731
parker.ukraine@parker.com

UK – United Kingdom, Warwick

Tel: +44 (0)1926 317 878
parker.uk@parker.com

ZA – South Africa, Kempton Park

Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

North America

CA – Canada, Milton, Ontario

Tel: +1 905 693 3000

US – USA, Cleveland

Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill

Tel: +61 (0)2-9634 7777

CN – China, Shanghai

Tel: +86 21 2899 5000

HK – Hong Kong

Tel: +852 2428 8008

IN – India, Mumbai

Tel: +91 22 6513 7081-85

JP – Japan, Tokyo

Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul

Tel: +82 2 559 0400

MY – Malaysia, Shah Alam

Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington

Tel: +64 9 574 1744

SG – Singapore

Tel: +65 6887 6300

TH – Thailand, Bangkok

Tel: +662 186 7000-99

TW – Taiwan, Taipei

Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires

Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos

Tel: +55 800 727 5374

CL – Chile, Santiago

Tel: +56 2 623 1216

MX – Mexico, Apodaca

Tel: +52 81 8156 6000

