


PECO Series PGC2

PEACH® GEMINI
 PEACH DEPTH STYLE
 GAS FILTER-COALESCING CARTRIDGES


for use in PECO Series GEM2
 PEACH Gemini PuraSep® 2 vessels



The PEACH Gemini, Series PGC2, cartridge is specifically designed for use with the PEACH Gemini PuraSep vessel in natural gas filter-coalescing applications. Its unique patented design provides dual flow path filtration with all the added benefits of PEACH technology. Gas flows outside-to-inside through the 1st Stage of the cartridge where

solid contaminant is captured and liquids are pre-coalesced. Then, as gas travels through the inside diameter of the cartridge at the chevron seal, a smooth transition is made and the gas flows inside-to-outside through the 2nd Stage of the cartridge removing coalesced liquids down to 0.3 microns.

PEACH® is a patented manufacturing process for making a unique depth style filter cartridge. Through thermal bonding, spiral layers of engineered filtration media are applied to conform and overlap each previous layer forming a conical helix pattern. This filter structure results in a gradient density pattern that provides an extraordinary flow path in radial, axial and helical directions. This tortuous flow path yields high contaminant loading, structural strength, maximum efficiency, and an overall outstanding filtration performance.



Removes Contaminants such as:

Asphaltenes, Coal Fines, Dirt, Iron Sulfides, Molecular Sieve Dust, Pipe Scale, Salts, Sand, Wear Metals

Coalesces Aerosol Liquid Droplets such as:

Amine, Condensate, Glycol, Lubricating Oils, Water, Low Surface Tension Fluid



ENGINEERING YOUR SUCCESS.

MATERIALS

COALESCING MEDIA	PEACH Polyester or Polypropylene
CORE	Plated Steel
END CAPS	Polyester or Polypropylene
SEAL	Buna-N, Viton, EPDM, HNBR, TCV

OPERATING DATA

FLOW DIRECTION: 1st Stage: Outside-to-Inside
2nd Stage: Inside-to-Outside

MAX. TEMP: Polypropylene 180°F / 82°C
Polyester 240°F / 116°C

MAX. DIFFERENTIAL PRESSURE: 25 psid / 1.7 bar

RECOMMENDED CHANGE-OUT

DIFFERENTIAL PRESSURE: 12–14 psi / 0.8–1.0 bar

NOMINAL DIMENSIONS

SIZE	O.D.	LENGTH
373	4.6" / 117mm	73" / 1854mm
382	4.6" / 117mm	82" / 2083mm
394	4.6" / 117mm	94" / 2388mm

ORDERING INFORMATION

PGC2	—	373	—		—	V		C		PL-20
SERIES		SIZE		MEDIA/END CAPS		SEAL		CORE		PERFORMANCE LEVEL
		373		Blank = polyester PP = polypropylene		Blank = Buna-N V = Viton EPDM = Ethylene Propylene Diene Monomer HNBR = Hydrogenated Buna TCV = Teflon® Coated Viton®				Blank = Standard recipe PL-20 = PL-20 recipe PL-23 = PL-23 recipe

• Teflon® and Viton® are registered trademarks of E. I. du Pont de Numours and Company.

© 2019 Parker Hannifin Corporation
DS-OG-PEACHGEMINI-PGC2-190726



PERFORMANCE

STANDARD RECIPE:

99.99% of 0.3 micron & larger solid particles
99.8% of 0.3 micron & larger liquid droplets
≤ 50 PPB (wt) effluent

PL-20 RECIPE

99.99% of 0.3 micron & larger solid particles
99.99% of 0.3 micron & larger liquid droplets
≤ 8 PPB (wt) effluent

PL-23 RECIPE

99.99% of 0.3 micron & larger solid particles
99.98% of 0.1 micron & larger liquid droplets
99.99% of 0.3 micron & larger liquid droplets
≤ 2 PPB (wt) effluent

Parker Hannifin Corporation
Industrial Process Filtration Division
Phone 940-325-2575 | Toll Free 1-800-877-7326
Email IPF_AM_TechSupport@parker.com
www.parker.com/ipf