



FUSOR[®] REPAIR ADHESIVES

Adhesives, Sealers & Sound Control
for Collision Repair



Crash Tested OEM Approved & Recommended



METAL ADHESIVES 3

PLASTIC ADHESIVES 5

SEALERS AND FOAMS 9

SPECIALTY PRODUCTS / ACCESSORIES 14

110B = 7.1 oz (210 mL)
111B = 1.7 oz (50 mL)

METAL BONDING ADHESIVE (FAST)

**BARE
METAL**

BARE METAL



Applications:

Patch panel bonding and weld bonding of properly prepared dissimilar metals, cab corners, panel sections and aluminum trailer repair patches.

Substrates:

Bare Metal, Steel, Aluminum

Chemistry/Color:

Acrylic 2K/Green

**TECH
TIP**

For best results, apply over sanded raw substrate. Remove zinc coating.

Features & Benefits:

- Fast cure
- No welding required
- Excellent corrosion protection

OEM Approvals & Recommendations:

GM, Ford, Honda/Acura, Mazda, Nissan

Shelf Life/Case Quantity:

- 12 months from DOM
- 6 (210 mL) or 12 (50 mL)



Work Time: 5 minutes

Clamp Time: 20 minutes

Cure Time: 2 hours

Technical data reported @ 70°F (21°C) unless noted.

108B = 7.1 oz (210 mL)
109B = 1.7 oz (50 mL)

METAL BONDING ADHESIVE (MEDIUM)

**BARE
METAL**

BARE METAL



Applications:

Panel bonding, weld and rivet bonding of quarter panels, rear body panels, roof panels, door skins, van side panels and outer truck bed panels.

Substrates:

Bare Metal, Steel, Aluminum

Chemistry/Color:

Acrylic 2K/Green



Work Time: 40 minutes

Clamp Time: 2 hours

Cure Time: 4 hours

Features & Benefits:

- Six to eight times faster than epoxy or urethane panel bonders
- No welding required
- Excellent corrosion protection
- Can be riveted and resistance welded

OEM Approvals & Recommendations:

GM, Ford, Honda/Acura, Mazda, Nissan, Infiniti, Western Star

Shelf Life/Case Quantity:

- 12 months from DOM
- 6 (210 mL) or 12 (50 mL)

**TECH
TIP**

For best results, apply over sanded raw substrate. Remove zinc coating.

Technical data reported @ 70°F (21°C) unless noted.

112B = 7.1 oz (210 mL)

METAL BONDING ADHESIVE (SLOW)

**BARE
METAL**

BARE METAL



Applications:

Panel bonding, weld and rivet bonding of quarter panels, rear body panels, roof panels, door skins, van side panels and outer truck bed panels.

Substrates:

Bare Metal, Steel, Aluminum

Chemistry/Color:

Acrylic 2K/Gray



Work Time: 70 minutes

Clamp Time: 3 hours

Cure Time: 8 hours

Features & Benefits:

- Long open time for large panel replacement
- Ideal for hot temperature conditions
- Excellent corrosion protection
- Can be riveted and resistance welded

OEM Approvals & Recommendations:

Chrysler/Fiat, Honda/Acura

Shelf Life/Case Quantity:

- 12 months from DOM
- 6 (210 mL)

**TECH
TIP**

For best results, apply over sanded raw substrate. Remove zinc coating.

Technical data reported @ 70°F (21°C) unless noted.

METAL ADHESIVES

208B = 7.1 oz (210 mL)

PANEL BONDING ADHESIVE (SLOW)

BARE METAL

BARE METAL



Applications:

Metal and plastic panel bonding, weld and rivet bonding of quarter panels, rear body panels, roof panels, door skins, van side panels and outer truck bed panels.

Substrates:

Bare Metal, Steel, Aluminum, FRP, SMC

Chemistry/Color:

Epoxy 2K/Gray

"Great cross-bonder for many different substrates."

Features & Benefits:

- Paint and sand with no need to remove adhesive squeeze out
- Low odor
- Bonds plastic, e-coat and bare metals
- Excellent corrosion protection

OEM Approvals & Recommendations:

Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)



Work Time: 90 minutes

Clamp Time: 4 hours / 30 minutes @ 140°F (60°C)

Paint Time: Immediately

Cure Time: 24 hours / 1 hour @ 140°F (60°C)

Technical data reported @ 70°F (21°C) unless noted.

2098 = 7.1 oz (210 mL)

CRASH DURABLE STRUCTURAL ADHESIVE (SLOW)

BARE METAL

BARE METAL



Applications:

Metal and plastic panel bonding, weld and rivet bonding of replacement structural and non-structural auto body panels.

Substrates:

Bare Metal, Steel, Aluminum, FRP

Chemistry/Color:

Epoxy 2K/Blue



Features & Benefits:

- High impact strength performance
- Excellent corrosion protection
- Versatile and easy to use
- Bonds plastic, e-coat and bare metals
- Weld immediately

OEM Approvals & Recommendations:

Chrysler/Fiat, GM, Honda/Acura, Tesla

Shelf Life/Case Quantity:

- 18 months from DOM
- 6 (210 mL)



Work Time: 90 minutes

Clamp Time: 6 hours / 30 minutes @ 140°F (60°C)

Paint Time: 24 hours / 30 minutes @ 140°F (60°C)

Cure Time: 24 hours / 2 hours @ 140°F (60°C)

Technical data reported @ 70°F (21°C) unless noted.

Use Fusor 423 Mixing Tip.

132 = 7.1 oz (210 mL)
133 = 1.7 oz (50 mL)

PLASTIC REPAIR ADHESIVE (SUPER FAST) SANDABLE



Applications:

Structural and cosmetic repair of bumpers, bumper tabs, emblems, door trims, interior and exterior plastic repairs and cosmetic repairs.

Substrates:

All types of plastic, SMC, Fiberglass, E-coat, Primed and painted metals

Chemistry/Color:

Urethane 2K/Black



Work Time: 1 minute

Clamp Time: 10 minutes

Sand Time: 10 minutes

Paint Time: 10 minutes

Features & Benefits:

- No need for plastic identification with use of Fusor 602EZ
- Undetectable feather edge
- Faster than plastic welding
- Stronger than stapling
- Urethane chemistry for all structural and cosmetic repairs on bumpers

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL) or 12 (50 mL)

Technical data reported @ 70°F (21°C) unless noted.

142 = 7.1 oz (210 mL)
143 = 1.7 oz (50 mL)

PLASTIC REPAIR ADHESIVE (FAST) SANDABLE



Applications:

Structural and cosmetic repair of bumpers, bumper tabs, emblems, door trims, interior and exterior plastic repairs and cosmetic repairs.

Substrates:

All types of plastic, SMC, Fiberglass, E-coat, Primed and painted metals

Chemistry/Color:

Urethane 2K/Black



Work Time: 1 minute

Clamp Time: 10 minutes

Sand Time: 20 minutes

Paint Time: 30 minutes

Features & Benefits:

- No need for plastic identification with use of Fusor 602EZ
- Undetectable feather edge
- Faster than plastic welding
- Stronger than stapling
- Urethane chemistry for all structural and cosmetic repairs on bumpers

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL) or 12 (50 mL)

Technical data reported @ 70°F (21°C) unless noted.

152 = 7.1 oz (210 mL)

PLASTIC REPAIR ADHESIVE (MEDIUM) SANDABLE



Applications:

Structural and cosmetic repair of bumpers, bumper tabs, emblems, door trims, interior and exterior plastic repairs and cosmetic repairs.

Substrates:

All types of plastic, SMC, Fiberglass, E-coat, Primed and painted metals

Chemistry/Color:

Urethane 2K/Black



Work Time: 3 minutes

Clamp Time: 30 minutes /
5 minutes at 140°F (60°C)

Sand Time: 90 minutes /
3 minutes at 140°F (60°C)

Paint Time: 2 hours / 60 minutes
with heat cure

Features & Benefits:

- No need for plastic identification with use of Fusor 602EZ
- Undetectable feather edge
- Faster than plastic welding
- Stronger than stapling
- Urethane chemistry for all structural and cosmetic repairs on bumpers
- Enough work time for larger repairs; ideal for hot temperature conditions
- On demand cure with heat

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Technical data reported @ 70°F (21°C) unless noted.

PLASTIC ADHESIVES

114LG = 7.1 oz (210 mL)

PLASTIC FINISHING ADHESIVE (FAST)

SANDABLE



Applications:

Finishing adhesive for cosmetic repair of all plastic bumpers and body panels.

Substrates:

PP, Fiberglass, Metton®, Telene®, SMC, TEO, Urethane, Carbon fiber

Chemistry/Color:

Epoxy 2K/Red

Features & Benefits:

- No plastic identification is required
- No adhesion promoters needed
- Epoxy formula sands to a perfect feather edge in 20 minutes or less

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)



Work Time: 2 minutes

Sand Time: 20 minutes

Paint Time: 60 minutes

Technical data reported @ 70°F (21°C) unless noted.

100EZ = 7.1 oz (210 mL)
101EZ = 1.7 oz (50 mL)

PLASTIC REPAIR ADHESIVE (HEAT SET)

SANDABLE



Applications:

Structural and cosmetic repair of auto and heavy duty truck composite, fiberglass, SMC and carbon fiber panels.

Substrates:

Rigid Plastics, SMC, GTX, Fiberglass, Metton®, Carbon Fiber

Chemistry/Color:

Epoxy 2K/Beige

Features & Benefits:

- One product for all body panels
- Easily sands to a feather edge to provide undetectable repairs
- No bull's-eyes, read-throughs or halos

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Nissan, Volvo Truck

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL) or 12 (50 mL)



Work Time: 40 minutes

Sand Time: 10 minutes @ 180°F (82°C)

Paint Time: 60 minutes @ 180°F (82°C)

Cure Time: 60 minutes @ 180°F (82°C)

TECH TIP

Use with Fusor 702 Fiberglass Cloth

Technical data reported @ 70°F (21°C) unless noted.



Official Partner of
Hendrick Motorsports

©2024 HMS Holdings, LLC

141 = 7.1 oz (210 mL)
140 = 1.7 oz (50 mL)

CLEAR PLASTIC BONDING ADHESIVE (FAST) SANDABLE



Applications:

Repair bumper and headlight tabs, bond emblems, body side moldings, plastic backer panels, decorative vents, wheel opening moldings, rear wind deflectors and ground effects.

Substrates:

Plastics, Primed and painted metals, Glass, Wood, Other surfaces



Work Time: 1 minute

Clamp Time: 5 minutes

Sand Time: 30 minutes

Paint Time: 30 minutes

Chemistry/Color:

Urethane 2K/Clear

Features & Benefits:

- Clear urethane, non-yellowing structural adhesive
- Fast cure
- High-strength, flexible bond

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL) or 12 (50 mL)

Technical data reported @ 70°F (21°C) unless noted.

147 = 7.1 oz (210 mL)

PLASTIC BONDING ADHESIVE (MEDIUM) STRUCTURAL



Applications:

Installation and bonding of small body panels, spoilers, ground effects and headlight buckets.

Substrates:

SMC, Fiberglass, Carbon Fiber, Plastics, Primed Metal



Work Time: 5 minutes

Clamp Time: 90 minutes /
15 minutes @ 140°F (60°C)

Paint Time: 90 minutes /
15 minutes @ 140°F (60°C)

Chemistry/Color:

Urethane 2K/Brown

Features & Benefits:

- High-strength structural adhesive
- Easy to apply, urethane non-sag formula
- Provides faster cure time for smaller interior and exterior parts

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura

Shelf Life/Case Quantity:

- 12 months from DOM
- 6 (210 mL)

Technical data reported @ 70°F (21°C) unless noted.

127EZ = 7.1 oz (210 mL)

PLASTIC BONDING ADHESIVE (SLOW) STRUCTURAL



Applications:

Plastic body panels, spoilers and ground effects; excellent for cab extenders, wood and other surfaces.

Substrates:

SMC, Fiberglass, Carbon Fiber, Plastics, Primed Metal, Metton®

Chemistry/Color:

Urethane 2K/Off White



Work Time: 50 minutes

Clamp Time: 5 hours /
30 minutes @ 140°F (60°C)

Paint Time: 4 hours /
30 minutes @ 140°F (60°C)

Features & Benefits:

- High-strength urethane structural adhesive
- Provides enough work time for bonding large primed metal or plastic parts
- Easy to apply, non-sag formula

OEM Approvals & Recommendations:

GM, Peterbilt, Volvo

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Technical data reported @ 70°F (21°C) unless noted.

PLASTIC ADHESIVES

T21 = 7.1 oz (210 mL)

COMPOSITE ADHESIVE (SLOW)

STRUCTURAL/SANDABLE



Applications:

Bonding of fairings, body panels, spoilers, ground effects, wind deflectors, roofs and fender liners; repairs cracks, punctures and tears.

Substrates:

Plastics, SMC, Fiberglass, Primed Metals, Metton®

Work Time: 45 minutes

Clamp Time: 4 hours / 20 minutes @ 180°F (82°C)

Sand Time: 60 minutes @ 180°F (82°C)

Paint Time: 60 minutes @ 180°F (82°C)



Chemistry/Color:

Epoxy 2K/Gray

Features & Benefits:

- One product bonds and finishes all plastic panels
- OEM epoxy formula
- Great for heavy-duty truck repair
- High strength
- Excellent gap-filling properties

OEM Approvals & Recommendations:

Ford, GM, Kenworth, Mack, Navistar, Paccar, Peterbilt, Volvo Truck, Freightliner

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Technical data reported @ 70°F (21°C) unless noted.

Use Fusor 423 Mixing Tip.

T22 = 7.1 oz (210 mL)

TRUCK PLASTIC BONDING ADHESIVE (FAST)

STRUCTURAL



Applications:

Installation of hood panels, roof panels, fenders, fender liners, fairings, spoilers, wind deflectors, cab extenders, ground effects, headlamp buckets and other body panels.

Substrates:

SMC, Fiberglass, Carbon Fiber, Plastics, Primed Metal, Metton®

Chemistry/Color:

Urethane 2K/Beige

Features & Benefits:

- Easy to apply, non-sag formula
- Substantially stronger than conventional adhesives

OEM Approvals & Recommendations:

Kenworth, Peterbilt

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)



Work Time: 5 minutes

Clamp Time: 60 minutes / 15 minutes @ 140°F (60°C)

Technical data reported @ 70°F (21°C) unless noted.

T23 = 7.1 oz (210 mL)

TRUCK PLASTIC BONDING ADHESIVE (MEDIUM)

STRUCTURAL



Applications:

Installation of hood panels, roof panels, fenders, fender liners, fairings, spoilers, wind deflectors, cab extenders, ground effects, headlamp buckets and other body panels.

Substrates:

SMC, Fiberglass, Carbon Fiber, Plastics, Primed Metal, Metton®

Chemistry/Color:

Urethane 2K/Beige

Features & Benefits:

- Easy to apply, non-sag formula
- Substantially stronger than conventional adhesives

OEM Approvals & Recommendations:

Kenworth, Peterbilt

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)



Work Time: 20 minutes

Clamp Time: 3 hours / 22 minutes @ 140°F (60°C)

Technical data reported @ 70°F (21°C) unless noted.

123 = 7.1 oz (210 mL)
126 = 1.7 oz (50 mL)

NON-SAG SEAM SEALER (FAST)

**BARE
METAL**

**FULL/HEAVY
BODIED**



Applications:
Duplicates factory look on the following seams: truck beds, tooled door skin, floor pan, core support and any other application in which a non-sag cosmetic seam sealer is required and where fast work time is desired.

Substrates:
Bare Metal or Primed surfaces

Chemistry/Color:
Urethane 2K/White



Includes two Fusor ribbon spreaders

Features & Benefits:

- Duplicates factory appearance
- Can be used with or without primer
- Bright white color

OEM Approvals & Recommendations:
Honda/Acura, Tesla

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL) or 12 (50 mL)

Work Time: 3 minutes

Paint Time: 10 minutes
(Paint within 24 hours or scuff before painting)



Technical data reported @ 70°F (21°C) unless noted.

123SL = 7.1 oz (210 mL)

NON-SAG SEAM SEALER (SLOW)

**BARE
METAL**

**FULL/HEAVY
BODIED**



Applications:
Duplicates factory look on the following seams: truck beds, tooled door skin, floor pan, core support and any other application in which a non-sag cosmetic seam sealer is required and where a slow work time is desired.

Substrates:
Bare Metal or Primed surfaces

Chemistry/Color:
Urethane 2K/White



Includes two Fusor ribbon spreaders

Features & Benefits:

- Duplicates factory appearance
- Longer work time

OEM Approvals & Recommendations:
Honda/Acura, Tesla

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Work Time: 45 minutes

Paint Time: 90 minutes
(Paint within 24 hours or scuff before painting)



Technical data reported @ 70°F (21°C) unless noted.

123EZ = 7.1 oz (210 mL)

NON-SAG SEAM SEALER (MEDIUM)

**BARE
METAL**

**FULL/HEAVY
BODIED**



Applications:
Duplicates factory look on the following seams: truck beds, tooled door skin, floor pan, core support and any other application in which a non-sag cosmetic seam sealer is required and where medium work time is desired.

Substrates:
Bare Metal or Primed Surfaces

Chemistry/Color:
Epoxy 2K/Blue



Includes two Fusor ribbon spreaders

Features & Benefits:

- Duplicates factory appearance
- Longer work time
- Sandable

OEM Approvals & Recommendations:
GM, Ford, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Work Time: 10 minutes /
5 minutes @ 90°F (32°C)

Sand Time: 30 minutes

Paint Time: 30 minutes; (Paint within 24 hours or scuff before painting)

Cure Time: 24 hour



Technical data reported @ 70°F (21°C) unless noted.

SEALERS AND FOAMS

019 = 7.1 oz (210 mL)

BARE METAL BRUSHABLE SEAM SEALER (MEDIUM)

BARE METAL

FULL/HEAVY BODIED



Applications:

Truck bed seams, tooled door skin seams, floor pan seams, core support seams and other applications where bare metal, brushable cosmetic seam sealer is required.

Substrates:

Bare Metal

Chemistry/Color:

Acrylic 2K/Green



Includes two Fusor ribbon spreaders

Features & Benefits:

- Acrylic formula provides corrosion protection
- Perfect match to OEM brushed appearance

OEM Approvals & Recommendations:

Chrysler/Fiat, Honda/Acura

Shelf Life/Case Quantity:

- 18 months from DOM
- 6 (210 mL)

Work Time: 6 minutes

Sand Time: 10 minutes

Paint Time: 10 minutes; (Paint within 24 hours or scuff before painting)

Cure Time: 2 hour



Technical data reported @ 70°F (21°C) unless noted.

129 = 7.1 oz (210 mL)

CONTROLLED FLOW SEAM SEALER (FAST)

BARE METAL

CONTROLLED FLOW



Applications:

Excellent for roof channels, door seams, drip rails and truck bed floor seams and trunk seams.

Substrates:

Bare Metal

Chemistry/Color:

Epoxy 2K/Beige



Includes two Fusor ribbon spreaders

Features & Benefits:

- Epoxy formula provides smooth continuous beads
- No tooling required for factory look
- Sandable
- Can be used with or without primer

OEM Approvals & Recommendations:

Ford, Chrysler/Fiat, GM, Honda/Acura

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Work Time: 5 minutes

Sand Time: 30 minutes

Paint Time: 30 minutes; (Paint within 24 hours or scuff before painting)

Cure Time: 1 hour



Technical data reported @ 70°F (21°C) unless noted.

122EZ = 7.1 oz (210 mL)

**SELF LEVELING SEAM SEALER
(MEDIUM)****SELF LEVELING****Applications:**

Drip rails, trunks, core support to aprons, roof seams and quarter panel to rear deck.

Substrates:

Apply over 2K primers. Do not use acid-etch primers. Do not use a cleaner after sanding.

Chemistry/Color:

Epoxy 2K/Blue

Features & Benefits:

- Perfectly matches factory flow-grade seams
- No tooling required
- Permanently flexible
- Sandable
- Color changes to indicate cure

OEM Approvals & Recommendations:

Ford, Honda/Acura, Tesla

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)



Work Time: 8 minutes

Sand Time: 30 minutes

Paint Time: 30 minutes; (Paint within 24 hours or scuff before painting)

Cure Time: 24 hour

Technical data reported @ 70°F (21°C) unless noted.

231 = 7.1 oz (210 mL)

**SOUND DAMPENING
MATERIAL (SLOW)****BARE
METAL****DAMPENING****Applications:**

Sound dampening and sealing of: roof bows and roof skin, door skin and intrusion beam, quarter panel and inner structure, hoods and deck lids to inner structure. Ideal for overhead and vertical applications where a non-sag material is required.

Substrates:

Bare Metal or primed surfaces

Chemistry/Color:

Urethane 2K/Black

Features & Benefits:

- Matches OEM performance
- Flexible seal with no shrinkage or read-through; non-expanding
- Extended work time for large applications
- Non-sag formula remains in position on vertical and overhead surfaces
- Excellent adhesion to metal, e-coat and existing NVH materials

OEM Approvals & Recommendations:

Honda/Acura, Tesla

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)



Work Time: 60 minutes

Cure Time: 24 hours

Technical data reported @ 70°F (21°C) unless noted.



SEALERS AND FOAMS

800DTM (neutral) = 10 oz (296 mL)

801DTM (white) = 10 oz (296 mL)

803DTM (black) = 10 oz (296 mL)

DIRECT-TO-METAL SEALER

BARE METAL

FULL/HEAVY BODIED



Applications:

Duplicates factory seams where a non-sag, toolable/brushable seam sealer is required.

Substrates:

Bare Metal, Cold rolled steel, E-coat, Aluminum

Chemistry/Color:

Silane Terminated Polymer 1K
Neutral (800DTM)
White (801DTM)
Black (803DTM)

Features & Benefits:

- Single component direct-to-metal; no substrate primer required
- Non-sag
- Holds brush marks without die back
- Weld thru with no burn back

OEM Approvals & Recommendations:

Ford, GM, Honda/Acura, Nissan, Volvo Truck, Infiniti

Shelf Life/Case Quantity:

- 15 months from DOM
- 12 (296 mL)

TECH TIP

For ultimate corrosion protection, priming substrate is recommended.



Skin Time*: 25 minutes, 50% RH

Paint Time: Immediately or up to 30 days without a scuff (Test with paint system)

Technical data reported @ 70°F (21°C) unless noted.

*Varies with temperature/humidity.

802HD PLUS = 10.1 oz (298 mL)

804HD PLUS = 10.1 oz (298 mL)

805HD PLUS = 10.1 oz (298 mL)

806HD PLUS = 10.1 oz (298 mL)

HIGH DEFINITION SPRAYABLE SEALER

BARE METAL

SPRAYABLE



Applications:

Creates flexible textured seams on floor pans, trunk pans and strut towers.

Substrates:

Bare Metal, Primed Metals, SMC, Fiberglass, Epoxy and urethane primers

Chemistry/Color:

Silane Terminated Polymer 1K
White (802HD PLUS)
Gray (804HD PLUS)
Black (805HD PLUS)
Beige (806HD PLUS)

Features & Benefits:

- Extremely flexible – won't crack or peel
- Perfectly matches all OEM seams and textures with use of Fusor 312 Sprayable Seam Sealer Applicator

OEM Approvals & Recommendations:

Chrysler/Fiat, Ford, GM, Honda/Acura, Porsche

Shelf Life/Case Quantity:

- 15 months from DOM
- 12 (298 mL)

TECH TIP

For ultimate corrosion protection, priming substrate is recommended.



Skin Time*: 25 minutes, 50% RH

Paint Time: Immediately or up to 30 days without a scuff (Test with paint system)

Technical data reported @ 70°F (21°C) unless noted.

*Varies with temperature/humidity.

121 = 7.1 oz (210 mL)
124 = 1.7 oz (50 mL)

FLEXIBLE FOAM (SUPER FAST)

FLEXIBLE



Applications:
Sound dampening, sealing and filling of voids in vehicle where air and wind noise would enter vehicle cabin, along with gas tank filler area.

Substrates:
Apply over 2K primers



Work Time: 10 seconds
Full Expansion: 3 minutes
Paint Time: 10 minutes
Cure Time: 1 hour

TECH TIP

Remove mixing tip immediately after dispensing and replace threaded nut and plug.

Chemistry/Color:
Urethane 2K/Black

Features & Benefits:

- Matches OEM sound dampening foams
- Retains its memory with no shrinkage
- Expands to 10 times its size
- Will not absorb moisture or cause corrosion

OEM Approvals & Recommendations:
Chrysler/Fiat, Ford, GM, Honda/Acura, Tesla, Volvo Truck

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL) or 12 (50 mL)

Technical data reported @ 70°F (21°C) unless noted.

130 = 7.1 oz (210 mL)

RIGID FOAM (SUPER FAST)

RIGID



Applications:
Sound dampening, vibration dampening, reinforcement, sealing and filling of: fender rails, pillars, rocker panels, quarter panels and floors.

Substrates:
Apply over 2K primers



Work Time: 10 seconds
Full Expansion: 4 minutes
Paint Time: 10 minutes

TECH TIP

Remove mixing tip immediately after dispensing and replace threaded nut and plug.

Chemistry/Color:
Urethane 2K/Beige

Features & Benefits:

- Matches OEM sound dampening foams commonly found in pillars, front rails, rockers and rear supports
- Expands to 10 times its size
- Provides NVH properties for a quieter ride
- Tough compressive strength for maximum energy absorption
- Super fast application, providing full foam expansion in 4 minutes

OEM Approvals & Recommendations:
Chrysler/Fiat, Ford, Honda/Acura, Tesla

Shelf Life/Case Quantity:

- 24 months from DOM
- 6 (210 mL)

Technical data reported @ 70°F (21°C) unless noted.



SPECIALITY PRODUCTS/ACCESSORIES

602EZ = 9 oz (255 mL)

SURFACE MODIFIER



Applications:

Increases adhesion for plastic bumper repair and painting plastic parts. Also improves adhesion for double-sided tape.

Substrates:

All plastic bumper covers, Emblems, Moldings, Primed Metals, Painted Metals

TECH TIP

Very light coat, clean nozzle after each use.

Features & Benefits:

- Open time from 10 minutes to 24 hours
- California compliant
- No need for plastic identification when used with Fusor 132/133, 142/143, 152 or 141/140 adhesives

OEM Approved & Recommended

Shelf Life/Case Quantity:

- 18 months from DOM
- 6 (9 oz)

700 = 4" x 12' (101.6 mm X 3.7 m)

REINFORCING MESH



Applications:

Use for backing patches, bumper tabs and other reinforcements on plastic bumper covers.

Substrates:

Plastic Bumpers, Bumper Tabs

Features & Benefits:

- Use with Fusor 132/133, 142/143, 152, 141/140 adhesives
- Use with Fusor 602EZ
- Use with Fusor 704 roller
- Finish with Fusor 114LG adhesive

Case Quantity: 12

702 = 4" x 12' (101.6 mm x 3.7 m)

FIBERGLASS CLOTH



Applications:

Use for structural backing support, pyramid patches and other reinforcements on SMC and fiberglass panels.

Substrates:

SMC, Fiberglass

Features & Benefits:

- Helps eliminate bull's-eyes in SMC repair
- Use with Fusor 100EZ/101EZ adhesives
- Use with Fusor 704 roller

Case Quantity: 12



703 = 32 oz (946.3 mL) Bottle

ADHESION PREP/CLEANER



Applications:

Removes silicones and contaminants. Use prior to applying adhesives, sealers and coatings. Removes brake dust from wheels.

Shelf Life/Case Quantity:

- 36 months from DOM
- 12 (32 oz)

704 = 3" (76.2 mm) Roller

SATURATION ROLLER



Applications:

Use with Fusor 700 and 702 for maximum adhesive saturation.

Features & Benefits:

- Ideal for building SMC pyramid patches
- Helps compact the surface for strong repairs
- 3" (76.2 mm) anodized aluminum

Case Quantity: 6

300

MANUAL 1.7 oz (50 mL) DISPENSING APPLICATOR



Applications:

For use with 1.7 oz (50 mL) cartridges.

Features & Benefits:

- Dispenses both 1:1 and 2:1 cartridges with no conversion necessary
- Sturdy, high-quality, compact

Case Quantity: 1

SPECIALITY PRODUCTS/ACCESSORIES

502

HIGH PERFORMANCE MANUAL APPLICATOR (210 mL)



Applications:

For use with 7.1 oz (210 mL) cartridges.

Features & Benefits:

- Dispenses 1:1 and 2:1 cartridges
- 26:1 thrust ratio allows for easy dispensing of high viscosity adhesive
- Simplistic design allows for easy cartridge insertion and ejection
- Composite support provide excellent cartridge stability

Case Quantity: 1

504

HIGH PERFORMANCE PNEUMATIC APPLICATOR (210 mL)



Applications:

For use with 7.1 oz (210 mL) cartridges.

Features & Benefits:

- Dispenses 1:1 and 2:1 cartridges
- For fast and easy application of long beads

Case Quantity: 1

312

SPRAYABLE SEAM SEALER APPLICATOR (281 mL)



Applications:

For use with Fusor HD PLUS sealers.

Features & Benefits:

- When used with Fusor HD PLUS Sprayable Seam Sealers, matches all OEM seam sealers, textured coatings and sound deadening applications
- Material and air flow adjustment controls allow for factory match seams

Case Quantity: 1

TECH TIP

Use small diaphragm air regulator for more control.

When finished spraying, be sure to close all valves on applicator before storing.

313

MANUAL SEAM SEALER APPLICATOR (296 mL)**Applications:**


For use with Fusor DTM sealers.

Features & Benefits:

- 26:1 thrust ratio allows for easy dispensing of high viscosity adhesives

Case Quantity: 1

400R

POWER 1.7 oz (50 mL) CARTRIDGE THREADED MIXING TIPS**Applications:**

For use with all 2:1 and 1:1, 1.7 oz (50 mL) cartridges.

Features & Benefits:

- Size: 0.21" x 6.0" x 19-element (5.3 mm x 152.4 mm x 19-element)
- Thread mount
- 12 per package

401T

POWER 7.1 oz (210 mL) CARTRIDGE MIXING TIPS WITH INTEGRAL THREADS**Applications:**

For use with most 1:1 and 2:1, 7.1 oz (210 mL) cartridges. Use Fusor 423 Mixing Tip for Fusor T21 and 2098.

Features & Benefits:

- Size: 0.34" x 5.8" x 24-element (8.6 mm x 147.3 mm x 24-element)
- Integral threads for easy installation
- 12 per package

SPECIALITY PRODUCTS/ACCESSORIES

412

NOZZLE FOR 800DTM SERIES SEALERS



Applications:


For use with Fusor 800DTM, 801DTM and 803DTM sealers.

Features & Benefits:

- Size: 0.875" x 4.125" (22.22 mm x 104.77 mm)
- Threaded nozzles
- 12 per package

423

POWER MIXING TIPS



Applications:

For use with Fusor T21 and 2098.

Features & Benefits:

- Size: 0.5" x 9" x 18-element (12.7 mm x 228.6 mm x 18-element)
- Larger size for easier dispensing of thicker material
- 12 per package



907

CABINET

**Applications:**

Allows easy accessibility, stocking and storage of Fusor adhesives and accessories.

Features & Benefits:

- Keeps Fusor products dust free
- Makes evaluating inventory easier
- Size: 20" w x 35" h x 12" d (0.51 m x 0.89 m x 0.3 m)
- Complete with shelf and mixing tip container
- Black



Legendary **Performance.**

Legendary **Innovation.**



Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275-5673
www.parker.com/APS

**For more information on Fusor products that
are OEM approved and recommended,
visit Fusor.com/OEMRepair.**

PC3000 OD 06/26 Rev.20

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2026 Parker Hannifin Corporation

