




QUICK COUPLING PRODUCTS

Quick Couplings, Swivels, Valves,
Diagnostic Sensors and Equipment
Catalog 3800 USA | December 2025

PDF Update: December 9, 2025



FOR MOST UPDATED
CATALOG SCAN WITH
CAMERA



Quick Coupling Division Locations



Minneapolis, MN



Grantsburg, WI



Chetek, WI



Union City, PA



WARNING

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

- This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.
- The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.
- To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

Offer of Sale

The items described in this document are hereby offered for sale by Parker Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the "Offer of Sale."

Table of Contents

Pneumatic Quick Couplings

Introduction	A-1
--------------------	-----

Coupling Selection & Ordering Guide	A-2
---	-----

Interchange Match-up Chart	A-4
----------------------------------	-----

General Purpose Couplings

Industrial Interchange Nipples.....	A-5
-------------------------------------	-----

20 Series	A-8
-----------------	-----

30 Series	A-11
-----------------	------

Rectus 21, 23, 30 Series (formerly HF Series)	A-14
--	------

Tru-Flate Design, Automotive Interchange 10 Series	A-18
---	------

ARO 210 Interchange 50 Series	A-23
--	------

Universal Coupler (accepts Industrial Interchange, Tru-Flate, and 50 Series Nipples) UC Series	A-26
---	------

Lincoln “Long Stem” Interchange 70 Series	A-28
--	------

European High Flow Interface Rectus 25 Series (formerly RF Series)	A-30
---	------

Schrader Twist-Lock Interchange TL Series	A-33
--	------

Snap-tite Design IH Series	A-36
-------------------------------------	------

Special Purpose Couplings

Tool-Mate Series (Non-Marring) Rectus 25 and Industrial Interchange Styles	A-38
---	------

Tool-Mate Series (Non-Marring, Exhaust) Rectus 25 and Industrial Interchange Styles	A-40
--	------

E-z-mate Series (Exhaust) Industrial Interchange.....	A-42
--	------

GF Series

Natural & Propane Gas	A-45
-----------------------------	------

Hydraulic Quick Couplings

Introduction.....	B-2
-------------------	-----

Coupling Selection & Ordering Guide.....	B-3, 4
--	--------

General Purpose Couplings

60 Series	B-5
-----------------	-----

Couplers.....	B-7
---------------	-----

Nipples.....	B-9
--------------	-----

60 Series Steam	B-11
-----------------------	------

Couplers.....	B-11
---------------	------

Nipples.....	B-11
--------------	------

6600 Series	B-12
-------------------	------

Couplers.....	B-13
---------------	------

Nipples.....	B-13
--------------	------

H & PH Series	B-15
---------------------	------

H Couplers	B-18
------------------	------

H Nipples.....	B-22
----------------	------

PH Couplers	B-21
-------------------	------

PH Nipples.....	B-25
-----------------	------

EA Series	B-26
-----------------	------

Couplers.....	B-28
---------------	------

Nipples.....	B-29
--------------	------

SM Series.....	B-30
----------------	------

Couplers.....	B-31
---------------	------

Nipples.....	B-32
--------------	------

HP Series	B-33
-----------------	------

Couplers.....	B-34
---------------	------

Nipples.....	B-34
--------------	------

4000 Series	B-35
-------------------	------

Couplers.....	B-36
---------------	------

Nipples.....	B-37
--------------	------

4200 Series	B-38
-------------------	------

Couplers.....	B-39
---------------	------

Nipples.....	B-39
--------------	------

* UC Series is a replacement for the HA Series.

Non-Spill Couplings

NS Series.....	B-40
Couplers.....	B-41
Nipples.....	B-41
NSS Series.....	B-42
Couplers.....	B-43
Nipples.....	B-44
FF/FC Series.....	B-46
Couplers.....	B-47
Nipples.....	B-48
FC Nipples.....	B-49
FEM/FEC Series	B-50
Couplers.....	B-51
Nipples.....	B-53
FEC Nipples.....	B-55
FH Series	B-56
Couplers.....	B-57
Nipples.....	B-57
FS Series.....	B-58
Couplers.....	B-59
Nipples.....	B-59

Instrumentation Couplings

CPI Series	B-61
Couplers.....	B-62
Nipples.....	B-63

Connect Under Pressure Couplings

59 Series.....	B-66
Couplers.....	B-67
Nipples.....	B-67
FET Series.....	B-68
Couplers.....	B-69
Nipples.....	B-70
6100 Series	B-72
Couplers.....	B-73
Nipples.....	B-73



8200 Series	B-75
Couplers.....	B-76
Nipples.....	B-76
9200 Series	B-77
Couplers.....	B-78
Nipples.....	B-78
5000 Series	B-79
Couplers.....	B-80
Nipples.....	B-80
75 Series	B-81
Couplers.....	B-83
Nipples.....	B-83

High Pressure Couplings

71 Series	B-84
Couplers.....	B-86
Nipples.....	B-87
3000 Series	B-88
Couplers.....	B-89
Nipples.....	B-89
TC Series	B-90
Couplers.....	B-90
Nipples.....	B-90
1141 Series.....	B-91
Couplers.....	B-91
Nipples.....	B-91

High Flow Couplings

ST Series.....	B-92
Couplers.....	B-93
Nipples.....	B-94
1163 Series.....	B-95
Couplers.....	B-95
Nipples.....	B-95
HO Series.....	B-96
Couplers.....	B-96
Nipples.....	B-96

Mold Coolant Line Couplings

Moldmate Series.....	B-97
Couplers.....	B-98
Sub Assemblies & Replacement Parts	B-99
Nipples.....	B-101

Miniature

Rectus 21 DSO Series	B-103
(Formerly DM Series)	
Couplers.....	B-104
Nipples.....	B-104

SensoControl Diagnostic and Industrial Catalog.....

B-106

Test Port Couplings

PD Series	B-107
Couplers.....	B-108
Nipples.....	B-108
PDP Series	B-111
Couplers.....	B-112
Nipples.....	B-112
EMA3 Series.....	B-113
Nipples.....	B-113
Gauge Adapters & Union.....	B-113
Transducer Adapters	B-114
Flexible Hose	B-114
PDFS Series - Fluid Sampling	B-116
Couplers.....	B-116
Nipples.....	B-116
Diagnostic Fittings - Tee Fittings	B-117

Promotional Products-Keychains

B-118

Swivels

PS Series

Introduction	C-1
Seal Options	C-1
How To Order	C-2
Repair Kits	C-2
In-Line.....	C-3
90°	C-7

S Series

Introduction	C-14
Repair Kits	C-14
How To Order	C-15
90°	C-16

Valves

Introduction	D-1
--------------------	-----

Check Valves

Selection Guide & General

Technical Information	D-2
-----------------------------	-----

DT Series.....	D-3
----------------	-----

Ordering Information	D-7
----------------------------	-----

CV Series	D-8
-----------------	-----

Ordering Information	D-10
----------------------------	------

DC Series	D-11
-----------------	------

Ordering Information	D-13
----------------------------	------

CPIFF Series (soft seat)	D-14
--------------------------------	------

S6C Series (soft seat).....	D-16, D-17
-----------------------------	------------

3C Series (soft seat).....	D-16, D-17
----------------------------	------------

2600 Series (swing type)	D-18
--------------------------------	------

Pressure/Vacuum Relief Valves

H1 & HM1 Series	D-19
-----------------------	------

Ordering Information	D-19
----------------------------	------

PV Series.....	D-20
----------------	------

Ordering Information	D-20
----------------------------	------

Thermal Bypass Valves

TH Series	D-21
-----------------	------

Ordering Information	D-22
----------------------------	------

Appendices

Fluid Compatibility Chart	I
---------------------------------	---

Part Number Index.....	XI
------------------------	----

Safety Guide	XXV
--------------------	-----

Offer of Sale	XXVIII
---------------------	--------

Glossary of Terms	XXX
-------------------------	-----



If you have questions about the products contained in this catalog, or their applications, please contact:

Quick Coupling Division

phone 763 544 7781

parker.com/qcd

Extra care is taken in the preparation of this literature, but Parker is not responsible for any inadvertent typographical errors or omissions. Information in this catalog is only accurate as of the date of publication. For a more current information base, please consult the division web site at parker.com/qcd.

Pneumatic Quick Couplings

Table of Contents

Introduction	A-1
Coupling Selection & Ordering Guide	A-2
Interchange Match-up Chart	A-4
General Purpose Couplings	
Industrial Interchange Nipples.....	A-5
20 Series	A-8
30 Series	A-11
Rectus 21, 23, 30 Series (formerly HF Series)	A-14
Tru-Flate Design, Automotive Interchange 10 Series	A-18
ARO 210 Interchange 50 Series	A-23
Universal Coupler (accepts Industrial Interchange, Tru-Flate, and 50 Series Nipples) UC Series	A-26
Lincoln "Long Stem" Interchange 70 Series	A-28
European High Flow Interface Rectus 25 Series (formerly RF Series)	A-30
Schrader Twist-Lock Interchange TL Series	A-33
Snap-tite Design IH Series	A-36
Special Purpose Couplings	
Tool-Mate Series (Non-Marring) Rectus 25 and Industrial Interchange Styles. A-38	
Tool-Mate Series (Non-Marring, Exhaust) Rectus 25 and Industrial Interchange Styles. A-40	
E-z-mate Series (Exhaust) Industrial Interchange.....	A-42
GF Series Natural & Propane Gas	A-45

PNEUMATIC QUICK COUPLINGS

Single Shut-Off Coupling

Single Shut-Off couplings are primarily used for pneumatic applications, connecting air tools, hoses, or other implements to compressed air supplies. They are also used with other gases, and with the exception of the E-z-mate Series can be used with low pressure fluids. The coupler half contains a shut-off valve that is automatically opened when a mating nipple is inserted and automatically closes when the nipple is removed.

Parker Single Shut-Off couplings come in three basic designs: general purpose/manual connect, general purpose/push-to-connect, and special purpose.

The standard seal material for all Parker Single Shut-Off couplers is Nitrile. Ethylene Propylene, Fluorocarbon, and Neoprene seals are available as options. See the comprehensive Fluid Compatibility Chart that provides guidelines for seal and body material selection. When there is need for further assistance in selecting the appropriate seal material, please consult the Quick Coupling Division.

General Ordering Information

When ordering Parker coupler bodies and nipples, please state the part number of each type of coupler body and each type of nipple desired. List coupler bodies and nipples as separate items rather than in combinations. Be sure to double check thread or hose sizes of items required.

Many of Parker's coupling products are available with unique non-standard options well suited to very specific applications. Examples of unusual end use applications might include: high temperatures (above 250° F), extremely caustic/corrosive solutions passing through the coupling, external/environmental corrosion situations, or other high wear and tear situations such as dragging the product along the ground. It is always recommended that the Quick Coupling Division be contacted with any questions concerning specific product application needs.

Checklist for Selecting Quick Couplings

- ☐ What are the functional requirements of the coupling?
- ☐ What is the maximum working pressure of the application?
- ☐ Which seals and body material are compatible with the system's fluid?
- ☐ Is the application static or dynamic?
- ☐ What size coupler/hose is required?
- ☐ What is the maximum pressure drop suitable for the application?
- ☐ Does the application require the ability to connect and disconnect under pressure?
- ☐ What is the media temperature and ambient temperature?
- ☐ What end configurations are required?
- ☐ Is an industry interchange coupler required?
- ☐ Is air inclusion and fluid loss a concern in the application?

Pneumatic Coupling Selection Guide

Pneumatic Coupling Selection Guide (by Interchange)

Body Size (in.)	Connection Style	Material*				Locking Mechanism	Std Seal Material	Std Seal Temp Range	Rated Pressure	Coupler Series
		B	S	SS	P					
Industrial Interchange Couplers (General)										
1/4 to 1/2	Manual Sleeve	■	■	■		Ball	Nitrile	40° to +250° F	300 psi	20 Series
1/8 to 3/8	Push-to-Connect	■	■			Ball	Nitrile	40° to +250° F	300 psi	Rectus 21, 23, 30 Series
1/4 to 3/4	Push-to-Connect	■				Pawl	Nitrile	40° to +250° F	300 psi	30 Series
1/4	Push-to-Connect	■				Ball	Nitrile	40° to +250° F	150 psi	Universal Series
Industrial Interchange Couplers (Special Purpose)										
1/4 & 3/8	Push-to-Connect		■		■	Fingers	Nitrile	40° to +250° F	300 psi	Tool-Mate (PBH) (non-marring)
1/4 to 1/2	Push-to-Connect		■		■	Fingers	Nitrile	40° to +250° F	300 psi	Tool-Mate (PBS) (non-marring, exhaust)
1/4 to 3/4	Push-to-Connect		■			Ball	Nitrile	40° to +250° F	300 psi	E-z-mate (exhaust)
Tru-Flate Interchange Couplings										
1/4 to 1/2	Manual Sleeve	■	■			Ball	Nitrile	40° to +250° F	300 psi	10 Series
1/4	Push-to-Connect	■				Ball	Nitrile	40° to +250° F	150 psi	Universal Series
ARO 210 Interchange Couplings										
1/4	Manual Sleeve	■	■			Ball	Nitrile	40° to +250° F	300 psi	50 Series
1/4	Push-to-Connect	■				Ball	Nitrile	40° to +250° F	150 psi	Universal Series
Lincoln “Long Stem” Interchange Couplings										
1/4	Manual Sleeve	■				Ball	Nitrile	40° to +250° F	300 psi	70 Series

* **Material Code:** **B** = Brass, **S** = Steel, **SS** = Stainless Steel, **P** = Plastic

Optional Materials and Features:
(add code to part number)

Contact QCD for availability and additional options.
To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Applies to
prefi B	Brass body	Nipples (std is steel) Couplers (3/8" & 1/2" sizes only)
suffix N	Stainless steel springs, locking balls & brass valves	Couplers (10, 20, 30, 50 & 70 Series)
suffix -SL	Sleeve-Lok	Couplers (10, 20, 30, 50 & 70 Series)
suffix R	Grip Ring sleeve	Couplers (10 & 20 Series)
suffix W	Ethylene Propylene seal material (-65° to + 400° F)	Couplers
suffix Y	Fluorocarbon seal material (-30° to + 400° F)	Couplers

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Coupling Selection Guide - continued

Pneumatic Coupling Selection Guide (by Interchange)

Body Size (in.)	Connection Style	Material*				Locking Mechanism	Std Seal Material	Std Seal Temp Range	Rated Pressure	Coupler Series
		B	S	SS	P					
Common High-Flow European Interchange Couplings										
1/4	Push-to-Connect	■	■			Ball	Nitrile	40° to +250° F	300 psi	Rectus 25 Series
1/4	Push-to-Connect		■		■	Fingers	Nitrile	40° to +250° F	300 psi	Tool-Mate (PER) (non-marring)
1/4	Push-to-Connect		■		■	Fingers	Nitrile	40° to +250° F	300 psi	Tool-Mate (PES) (non-marring, exhaust)
Schrader Twist -Lock Interchange Couplings										
1/4 & 1/2	Push-to-Connect	■	■			Cam	Nitrile	40° to +250° F	300 psi	TL Series
Special Purpose - Natural and Propane Gas Couplings										
1/2 to 1-1/4	Manual Sleeve	■				Ball	Fluorocarbon	32° to +200° F	60 psi max	GF Series



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose


Interchange Match-up Chart

Popular Coupling Designs


Parker's Quick Coupling Division manufactures quick couplings to interchange with popular designs that have become accepted standards in the industry today. The actual size nipple chart below can be used to help select Parker Quick Couplings that will interchange with specific nipple designs and sizes.

10 Series


(Tru-Flate Automotive Interchange)



1/4" Body Size




3/8" Body Size




1/2" Body Size

Twist-Lock (Schrader Interchange)




1/4" Body Size




1/2" Body Size


20 Series, 30 Series, Rectus 21, 23, 30 Series, E-z-mate (Industrial Interchange)




1/8" Body Size




1/4" Body Size



3/8" Body Size




1/2" Body Size




3/4" Body Size

50 Series (ARO-210 Interchange)



1/4" Body Size


70 Series (Lincoln Interchange)



1/4" Body Size

Rectus 25 Series

(European Interchange)



1/4" Body Size

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Industrial Interchange Nipples

A-A-59439, MIL- C-4109F Design

Non-valved, straight through

A-5



Pneumatic Quick Couplings

General Purpose

Parker Industrial Interchange Nipples are compatible for use with 20 Series, 30 Series, Rectus 21, 23, 30 Series, Universal or E-z-mate couplers. The standard male tip of the pneumatic industry, these nipples are interchangeable with similar nipples manufactured to the same requirements.



Features:

- Conforms to A-A-59439 (MIL-C-4109F, ISO 6150-B) requirements for global interchangeability
- Steel nipples have hardened wear points and load-bearing areas
- Unvalved style nipple mates with valved couplers

Applications include:

- Air compressors
- Pneumatic tools
- Drop-down air lines

Optional Material:

(add code to part number)

Code	Description	Part Number Example
prefi B	Brass body	BH1E

Contact QCD for availability and additional options.

Nipples - Female Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Part Number Stainless Steel (303) **	Thread Size	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	-	H1C	-	1/8-27 NPTF	1.48	0.71	0.58	0.50	0.03
1/4	BH3C	H3C	SH3C	1/4-18 NPTF	1.56	0.80	0.72	0.62	0.05
1/4	-	H3C-E	SH3C-E	3/8-18 NPTF	1.60	0.83	0.94	0.81	0.08
3/8	-	H1E	-	1/4-18 NPTF	1.60	0.69	0.72	0.62	0.06
3/8	BH3E	H3E	-	3/8-18 NPTF	1.72	0.74	0.94	0.81	0.10
3/8	-	H3E-F	-	1/2-14 NPTF	1.89	0.90	1.16	1.00	0.13
1/2	-	H1F	-	3/8-18 NPTF	2.03	0.79	0.94	0.81	0.12
1/2	BH3F	H3F	-	1/2-14 NPTF	2.20	0.83	1.16	1.00	0.19
1/2	-	H3F-G	-	3/4-14 NPTF	2.30	1.05	1.44	1.25	0.26
3/4	-	H3G-F	-	1/2-14 NPTF	2.22	1.06	1.16	1.00	0.23
3/4	-	H3G	-	3/4-14 NPTF	2.18	1.02	1.44	1.25	0.34
3/4	-	H3G-J	-	1-11 1/2 NPTF	2.41	1.25	1.80	1.63	0.47

* This dimension represents the portion of the nipple that is exposed when the nipple is connected to a Parker 20 Series coupler.

**Prop 65 Warning does not apply to stainless steel part numbers.

Pneumatic Quick Couplings

General Purpose

Industrial Interchange Nipples

A-A-59439,

MIL- C-4109F Design

Non-valved, straight through



Nipples - Male Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Part Number Stainless Steel (303) **	Thread Size	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	-	H0C	-	1/8-27 NPTF	1.68	0.92	0.58	0.50	0.05
1/4	BH2C	H2C	SH2C	1/4-18 NPTF	1.56	0.89	0.65	0.56	0.06
1/4	-	H2C-E	SH2C-E	3/8-18 NPTF	1.90	1.14	0.80	0.69	0.07
3/8	-	H00E	-	1/8-27 NPTF	1.68	0.73	0.72	0.62	0.08
3/8	-	H0E	-	1/4-18 NPTF	1.90	0.95	0.72	0.62	0.08
3/8	BH2E	H2E	-	3/8-18 NPTF	1.90	0.95	0.80	0.69	0.09
3/8	-	H2E-F	-	1/2-14 NPTF	2.03	1.09	1.02	0.88	0.15
1/2	-	H0F	-	3/8-18 NPTF	2.20	0.96	0.79	0.69	0.16
1/2	BH2F	H2F	-	1/2-14 NPTF	2.35	1.09	1.01	0.88	0.18
1/2	-	H2F-G	-	3/4-14 NPTF	2.40	1.16	1.22	1.06	0.24
3/4	-	H2G-F	-	1/2-14 NPTF	2.32	1.16	1.16	1.00	0.22
3/4	BH2G	H2G	-	3/4-14 NPTF	2.28	1.12	1.22	1.06	0.28
3/4	-	H2G-J	-	1-11 1/2 NPTF	2.56	1.40	1.52	1.31	0.36

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Industrial Interchange Nipples
A-A-59439,
MIL- C-4109F Design
 Non-valved, straight through

A-7



Pneumatic Quick Couplings

General Purpose

Nipples - Standard Hose Barb



Body Size (in.)	Part Number Brass	Part Number Steel	Part Number Stainless Steel (303) **	Hose I.D.	Length (in.)	Exposed Length*	Largest Diameter	Weight (lbs.)
1/4	-	H8C	-	1/4	1.72	0.95	0.46	0.04
1/4	-	-	SH8C	1/4	2.09	1.33	0.56	0.04
1/4	-	H8C-D	-	5/16	1.96	1.20	0.50	0.04
1/4	-	H9C	SH9C	3/8	1.96	1.20	0.50	0.05
3/8	-	H5E	-	3/8	1.85	0.90	0.59	0.07
3/8	-	H6E	-	1/2	2.09	1.14	0.68	0.08
1/2	-	H4F	-	3/8	2.36	1.12	0.66	0.10
1/2	-	H5F	-	1/2	2.36	1.12	0.66	0.11
1/2	-	H5F-G	-	3/4	2.95	1.71	0.87	0.18
3/4	-	H5G-F	-	1/2	2.47	1.31	0.93	0.19
3/4	BH5G	H5G	-	3/4	3.00	1.84	0.93	0.25
3/4	-	H5G-J	-	1	3.24	2.08	1.24	0.36

Nipples - Push-Lok Hose Barb**



Body Size (in.)	Part Number Brass	Part Number Steel	Hose I.D.	Length (in.)	Exposed Length*	Largest Diameter	Weight (lbs.)
1/4	BH8CP	H8CP	1/4	1.74	0.97	0.69	0.04
1/4	-	H9CP	3/8	1.96	1.19	0.86	0.05
3/8	-	H4EP	1/4	1.87	0.92	0.69	0.06
3/8	-	H5EP	3/8	2.02	1.07	0.86	0.07
3/8	-	H6EP	1/2	2.21	1.27	0.97	0.09
1/2	-	H4FP	3/8	2.36	1.11	0.86	0.11
1/2	-	H5FP	1/2	2.48	1.24	0.97	0.11
1/2	-	H6FP	5/8	2.95	1.71	1.14	0.14

* This dimension represents the portion of the nipple that is exposed when the nipple is connected to a Parker 20 Series coupler.

** Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

20 Series Couplers Accepts Industrial Interchange Nipples

Manual sleeve, single shut-off



20 Series Pneumatic Couplers mate with Industrial Interchange nipples, the standard male tip of the pneumatic industry. Available options include Sleeve-Lok, stainless steel locking balls and springs, and grip-ring sleeve.




Features:

- Mates with Industrial Interchange nipples manufactured to A-A-59439 (MIL-C-4109F, ISO 6150-B) global standards
- 1/4" body size has a brass body and steel valve, 3/8" body size has all steel construction
- Tubular valve delivers high flow with minimal pressure drop
- Integral sleeve guard resists accidental disconnection
- Standard seal is Nitrile

Applications include:

- Air compressors
- Pneumatic tools
- Water
- Grease
- Paint

Performance



20 Series Specification

Body Size	1/4	3/8	1/2
Rated Pressure (psi)	300		
Temperature Range (std seals)	-40° to +250° F		
Locking Device	4 balls	8 balls	8 balls
Vacuum Data (in. Hg.)	—		
Disconnected (coupler only)	Not Recommended		
Connected	27.4		

20 Series Repair Kits

Body Size	Seal Material	Part No.
1/4	Nitrile	21K
1/4	Ethylene Propylene	21KW
1/4	Fluorocarbon	21KY
3/8	Nitrile	14K
3/8	Ethylene Propylene	14KW
3/8	Fluorocarbon	14KY
1/2	Nitrile	16K
1/2	Ethylene Propylene	16KW
1/2	Fluorocarbon	16KY
3/4	Nitrile	38K
3/4	Ethylene Propylene	38KW
3/4	Fluorocarbon	38KY

20 Series Couplers Accepts Industrial Interchange Nipples

A-9

Pneumatic Quick Couplings

General Purpose

Manual sleeve, single shut-off



20 Series Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Part Number Stainless Steel (303) **	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B23A	-	-	1/8-27 NPTF	1.83	0.90	0.75	0.20
1/4	B23	-	S23	1/4-18 NPTF	1.83	0.90	0.75	0.19
1/4	B23E	-	-	3/8-18 NPTF	1.95	0.94	0.81	0.20
3/8	-	25C	-	1/4-18 NPTF	2.22	1.06	0.88	0.30
3/8	B25*	25	-	3/8-18 NPTF	2.28	1.06	0.88	0.32
3/8	-	25F	-	1/2-14 NPTF	2.55	1.16	1.00	0.34
1/2	-	17E	-	3/8-18 NPTF	2.74	1.19	1.00	0.46
1/2	B17*	17	-	1/2-14 NPTF	2.96	1.19	1.00	0.50
1/2	-	17G	-	3/4-14 NPTF	3.19	1.44	1.25	0.56

20 Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Part Number Stainless Steel (303) **	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B22A	-	-	1/8-27 NPTF	1.89	0.90	0.75	0.18
1/4	B22	-	S22	1/4-18 NPTF	2.05	0.90	0.75	0.18
1/4	B22E	-	-	3/8-18 NPTF	2.08	0.90	0.75	0.19
3/8	-	24C	-	1/4-18 NPTF	2.36	1.06	0.88	0.26
3/8	B24*	24	-	3/8-18 NPTF	2.39	1.06	0.88	0.29
3/8	-	24F	-	1/2-14 NPTF	2.55	1.16	0.88	0.29
1/2	-	16E	-	3/8-18 NPTF	2.93	1.19	1.00	0.42
1/2	B16*	16	-	1/2-14 NPTF	3.08	1.19	1.00	0.47
1/2	-	16G	-	3/4-14 NPTF	3.21	1.30	1.13	0.56

* Coupler has brass body and steel sleeve.

** Prop 65 Warning does not apply to stainless steel part numbers.



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

20 Series Couplers Accepts Industrial Interchange Nipples

Manual sleeve, single shut-off



Optional Materials and Features: (add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
prefi B	Brass body (Couplers - 3/8" & 1/2" sizes only)	B24C
suffix N	Stainless steel springs, locking balls & brass valves (Couplers)	B24N
suffix -SL	Sleeve-Lok (Couplers)	24-SL
suffix R	Grip Ring sleeve (Couplers)	24R
suffix W	Ethylene Propylene seal material (-65° to + 400° F) (Couplers)	24W
suffix Y	Fluorocarbon seal material (-30° to + 400° F) (Couplers)	24Y

Couplers - Standard Hose Barb



Body Size (in.)	Part Number Brass	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B20-3B	-	1/4	2.49	0.90	0.75	0.18
1/4	B20-4B	-	5/16	2.49	0.90	0.75	0.18
1/4	B20-5B	-	3/8	2.49	0.90	0.75	0.18
3/8	-	24-5B	3/8	2.60	1.06	0.88	0.27
3/8	-	24-6B	1/2	2.60	1.06	0.88	0.28
1/2	-	16-5B	3/8	3.14	1.19	1.00	0.41
1/2	-	16-6B	1/2	3.14	1.19	1.00	0.43
1/2	-	16-7B	3/4	3.60	1.19	1.00	0.48

Couplers - Push-Lok Hose Barb*



Body Size (in.)	Part Number Brass	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B20-3BP	-	1/4	2.32	0.90	0.75	0.18
1/4	B20-5BP	-	3/8	2.47	0.90	0.75	0.19
3/8	-	24-5BP	3/8	2.88	1.06	0.88	0.27
1/2	-	16-5BP	3/8	3.35	1.19	1.00	0.41
1/2	-	16-6BP	1/2	3.46	1.19	1.00	0.43

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

Note: See Table of Contents for pneumatic Industrial Interchange nipples used with 20 Series couplers.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

30 Series Couplers Accepts Industrial Interchange Nipples

Manual sleeve, single shut-off



30 Series Pneumatic Couplers mate with Industrial Interchange nipples, the standard male tip of the pneumatic industry. The couplers have brass bodies. Standard seal is Nitrile.





Features:

- Mates with Industrial Interchange nipples manufactured to A-A-59439 (MIL-C-4109F, ISO 6150-B) global standards
- Tubular valve delivers high flow with minimal pressure drop
- Push-to-connect operation
- Options include Sleeve-Lok, brass valve for added corrosion resistance, and alternative seal materials

Applications include:

- Air compressors
- Pneumatic tools
- Water
- Grease
- Paint

Performance



30 Series Specification

Body Size	1/4	3/8	1/2	3/4
Rated Pressure (psi)	300			
Temperature Range (std seals)	-40° to +250° F			
Locking Device	3 pawls	3 pawls	6 pawls	6 pawls
Vacuum Data (in. Hg.)	-			
Disconnected (coupler only)	Not Recommended			
Connected	27.4			

30 Series Repair Kits

Body Size	Seal Material	Part No.
1/4	Nitrile	21K
1/4	Ethylene Propylene	21KW
1/4	Fluorocarbon	21KY
3/8	Nitrile	14K
3/8	Ethylene Propylene	14KW
3/8	Fluorocarbon	14KY
1/2	Nitrile	16K
1/2	Ethylene Propylene	16KW
1/2	Fluorocarbon	16KY
3/4	Nitrile	38K
3/4	Ethylene Propylene	38KW
3/4	Fluorocarbon	38KY

Pneumatic Quick Couplings

General Purpose

30 Series Couplers Accepts Industrial Interchange Nipples

Manual sleeve, single shut-off



Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B33A	1/8-27 NPTF	1.96	1.20	0.75	0.30
1/4	B33	1/4-18 NPTF	1.96	1.20	0.75	0.28
1/4	B33E	3/8-18 NPTF	2.03	1.20	0.81	0.30
3/8	B35C	1/4-18 NPTF	2.26	1.39	0.88	0.42
3/8	B35	3/8-18 NPTF	2.33	1.39	0.88	0.42
3/8	B35F	1/2-14 NPTF	2.57	1.39	1.00	0.46
1/2	B37E	3/8-18 NPTF	2.76	1.52	1.00	0.56
1/2	B37	1/2-14 NPTF	3.00	1.52	1.00	0.66
1/2	B37G	3/4-14 NPTF	3.12	1.52	1.25	0.73
3/4	B39F	1/2-14 NPTF	2.85	1.90	1.31	0.15
3/4	B39	3/4-14 NPTF	2.99	1.90	1.31	1.10
3/4	B39J	1-11 1/2 NPTF	3.18	1.90	1.63	1.24

Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B32A	1/8-27 NPTF	2.03	1.20	0.75	0.27
1/4	B32	1/4-18 NPTF	2.18	1.20	0.75	0.28
1/4	B32E	3/8-18 NPTF	2.18	1.20	0.75	0.28
3/8	B34C	1/4-18 NPTF	2.38	1.39	0.88	0.36
3/8	B34	3/8-18 NPTF	2.44	1.39	0.88	0.39
3/8	B34F	1/2-14 NPTF	2.57	1.39	0.88	0.41
1/2	B36E	3/8-18 NPTF	2.92	1.52	1.00	0.58
1/2	B36	1/2-14 NPTF	3.09	1.52	1.00	0.61
1/2	B36G	3/4-14 NPTF	3.12	1.52	1.13	0.67
3/4	B38	3/4-14 NPTF	2.95	1.90	1.31	0.91
3/4	B38J	1-11 1/2 NPTF	3.12	1.90	1.31	0.99

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

30 Series Couplers Accepts Industrial Interchange Nipples

Manual sleeve, single shut-off



Couplers - Standard Hose Barb



Body Size (in.)	Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B30-3B	1/4	2.62	1.20	0.75	0.27
1/4	B30-4B	5/16	2.62	1.20	0.75	0.27
1/4	B30-5B	3/8	2.62	1.20	0.75	0.28
3/8	B34-5B	3/8	2.65	1.39	0.88	0.39
3/8	B34-6B	1/2	2.65	1.39	0.88	0.41
1/2	B36-6B	1/2	3.13	1.52	1.00	0.59
1/2	B36-7B	3/4	3.60	1.52	1.00	0.65
3/4	B38-7B	3/4	3.69	1.90	1.31	0.93
3/4	B38-8B	1	3.93	1.90	1.31	1.03

Couplers - Push Lok Hose Barb*



Body Size (in.)	Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B30-3BP	1/4	2.45	1.20	0.75	0.27
1/4	B30-5BP	3/8	2.60	1.20	0.75	0.29
3/8	B34-5BP	3/8	2.82	1.39	0.88	0.40
1/2	B36-6BP	1/2	3.46	1.52	1.00	0.56

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix N	Stainless steel springs, locking balls & brass valves (Couplers)	B34N
suffix -SL	Sleeve-Lok (Couplers)	B34-SL
suffix W	Ethylene Propylene seal material (-65° to + 400° F) (Couplers)	B34W
suffix Y	Fluorocarbon seal material (-30° to + 400° F) (Couplers)	B34Y



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

Rectus 21, 23, 30 Series Couplers Accepts Industrial Interchange Nipples Formerly HF Series

Push-to-connect sleeve, single shut-off



Rectus 21, 23, 30 Series Pneumatic Quick Couplers connect with Industrial Interchange nipples, the standard male tip of the pneumatic industry. The 1/8" and 1/4" couplers have nickel plated brass construction, a corrosion resistant valve, stainless steel locking balls and a stainless steel valve spring. The 3/8" couplers have nickel plated steel construction, a corrosion resistant valve, stainless steel locking pins and a stainless steel valve spring.



Features:


- Integral sleeve guard protects against accidental disconnection
- Push-to-connect operation
- Slim profile

Applications include:

- Air compressors
- Pneumatic tools
- Drop-down air lines

Performance


Rectus 21, 23, 30 Series (1/8" & 1/4" sizes)



Rectus 21, 23, 30 Series Specification

Body Size	1/8	1/4	3/8
Rated Pressure (psi)	250	300	300
Temperature Range (std seals)	-4° to +212° F		
Locking Device	5 balls	4 balls	6 balls
Vacuum Data (in. Hg.)	—		
Disconnected (coupler only)	Not Recommended		

Rectus 21, 23, 30 Series (3/8" sizes)



Pneumatic Quick Couplings

General Purpose

Rectus 21, 23, 30 Series Couplers
Accepts Industrial Interchange Nipples
Formerly HF Series

Push-to-connect sleeve, single shut-off



1/8" Body Size Couplers - Female Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/8	21KAIN10MPN	HF-121-2FP	1/8-27 NPSF	1.42	0.63	0.55	0.06
1/8	21KAIN13MPN	HF-121-4FP	1/4-18 NPSF	1.81	0.63	0.67	0.10

1/8" Body Size Couplers - Male Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/8	21KAAN10MPN	HF-121-2MP	1/8-27 NPT	1.50	0.63	0.55	0.06
1/8	21KAAN13MPN	HF-121-4MP	1/4-18 NPT	1.61	0.63	0.55	0.07

1/8" Body Size Nipples - Female Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/8	21SFIN10MXN	HF-124-2FP	1/8-27 NPSF	1.08	0.58	0.50	0.03
1/8	21SFIN13MXN	HF-124-4FP	1/4-18 NPSF	1.34	0.78	0.67	0.07

1/8" Body Size Nipples - Male Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/8	21SFAN10MXN	HF-124-2MP	1/8-27 NPT	1.06	0.51	0.44	0.03
1/8	21SFAN13MXN	HF-124-4MP	1/4-18 NPT	1.25	0.63	0.56	0.05

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

Rectus 21, 23, 30 Series Couplers
Accepts Industrial Interchange Nipples
Formerly HF Series

Push-to-connect sleeve, single shut-off



1/4, 3/8" Body Size Couplers - Female Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	New Part No. Nickel Plated Steel	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	23KAIN13MPN	-	HF-251-4FP	1/4-18 NPSF	2.19	0.99	0.81	0.26
1/4	23KAIN17MPN	-	HF-251-6FP	3/8-18 NPSF	2.34	0.99	0.81	0.27
3/8	-	30KAIN13SPN	HF-371-4FP	1/4-18 NPSF	2.17	1.19	0.87	0.33
3/8	-	30KAIN17SPN	HF-371-6FP	3/8-18 NPSF	2.30	1.19	0.87	0.31
3/8	-	30KAIN21SPN	HF-371-8FP	1/2-14 NPSF	2.48	1.19	0.94	0.35

1/4, 3/8" Body Size Couplers - Male Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	New Part No. Nickel Plated Steel	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	23KAAN13MPN	-	HF-251-4MP	1/4-18 NPTF	2.34	0.99	0.81	0.25
1/4	23KAAN17MPN	-	HF-251-6MP	3/8-18 NPTF	2.37	0.99	0.81	0.26
3/8	-	30KAAN13SPN	HF-371-4MP	1/4-18 NPTF	2.07	1.19	0.87	0.32
3/8	-	30KAAN17SPN	HF-371-6MP	3/8-18 NPTF	2.07	1.19	0.87	0.30
3/8	-	30KAAN21SPN	HF-371-8MP	1/2-14 NPTF	2.24	1.19	0.87	0.33

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

Rectus 21, 23, 30 Series Couplers
Accepts Industrial Interchange Nipples
Formerly HF Series

Push-to-connect sleeve, single shut-off



1/4, 3/8" Body Size Couplers - Standard Hose Barb



Body Size (in.)	New Part Number Nickel Plated Brass	New Part No. Nickel Plated Steel	Old Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	23KATF06MPN	-	HF-251-4HB	1/4	2.81	0.99	0.81	0.26
1/4	23KATF10MPN	-	HF-251-6HB	3/8	2.81	0.99	0.81	0.27
3/8	-	30KATF10SPN	HF-371-6HB	3/8	2.60	1.19	0.83	0.31
3/8	-	30KATF13SPN	HF-371-8HB	1/2	2.60	1.19	0.83	0.34

1/4, 3/8" Body Size Couplers - Push-Lok Hose Barb*



Body Size (in.)	New Part Number Nickel Plated Brass	New Part No. Nickel Plated Steel	Old Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	23KATP06MPN	-	HF-251-4PL	1/4	2.64	0.99	0.81	0.26
1/4	23KATP10MPN	-	HF-251-6PL	3/8	2.78	0.99	0.81	0.27
3/8	-	30KATP10SPN	HF-371-6PL	3/8	2.54	1.19	0.83	0.33
3/8	-	30KATP13SPN	HF-371-8PL	1/2	2.68	1.19	0.83	0.31

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

10 Series Couplers Tru-Flate Design (Automotive Interchange)

Manual sleeve, single shut-off



Parker's 10 Series Pneumatic Couplers are the original Tru-Flate design, commonly referred to as the automotive interchange. 1/4" body size has a brass body, while standard 3/8" and 1/2" body sizes have all steel construction. Sleeve options include Sleeve-Lok and Grip-Ring sleeve.




Features:

- Integral sleeve guard resists accidental disconnection
- Tubular valve delivers high air flow with minimal pressure drop
- 3/8" and 1/2" size options include brass body with steel sleeve
- Brass body option with stainless steel springs and locking balls is available for added corrosion resistance
- Standard seal is Nitrile
- Steel nipples are case hardened

Applications include:

- Air compressors
- Pneumatic tools
- Water
- Grease
- Paint

Performance



10 Series Specification

Body Size	1/4	3/8	1/2
Rated Pressure (psi)	300		
Temperature Range (std seals)	-40° to +250° F		
Locking Device	4 balls	8 balls	8 balls
Vacuum Data (in. Hg.)	—		
Disconnected (coupler only)	Not Recommended		
Connected	27.4		

10 Series Repair Kits

Body Size	Seal Material	Part No.
1/4	Nitrile	21K
1/4	Ethylene Propylene	21KW
1/4	Fluorocarbon	21KY
3/8	Nitrile	14K
3/8	Ethylene Propylene	14KW
3/8	Fluorocarbon	14KY
1/2	Nitrile	16K
1/2	Ethylene Propylene	16KW
1/2	Fluorocarbon	16KY

Pneumatic Quick Couplings

General Purpose

10 Series Couplers Tru-Flate Design (Automotive Interchange)

Manual sleeve, single shut-off



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
prefi B	Brass body (Couplers - 3/8" & 1/2" sizes only)	B14F
suffix N	Stainless steel springs, locking balls & brass valves (Couplers)	B15N
suffix -SL	Sleeve-Lok (Couplers)	15-SL
suffix R	Grip Ring sleeve (Couplers)	15R
suffix W	Ethylene Propylene seal material (-65° to + 400° F) (Couplers)	B15W
suffix Y	Fluorocarbon seal material (-30° to + 400° F) (Couplers)	B15Y

10 Series Nipples - Female Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Thread Size	Length (in.)	Exposed Length**	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	-	1C	1/8-27 NPTF	1.28	0.55	0.58	0.50	0.05
1/4	B3C	3C	1/4-18 NPTF	1.47	0.74	0.72	0.62	0.05
1/4	-	3C-E	3/8-18 NPTF	1.50	0.77	0.94	0.81	0.07
3/8	-	1E	1/4-18 NPTF	1.60	0.67	0.72	0.62	0.07
3/8	-	3E	3/8-18 NPTF	1.68	0.77	0.94	0.81	0.10
1/2	-	1F	3/8-18 NPTF	2.05	0.83	0.94	0.81	0.13
1/2	-	3F	1/2-14 NPTF	2.27	1.05	1.16	1.00	0.18
1/2	-	H3F-G	3/4-14 NPTF	2.38	1.13	1.44	1.25	0.26

10 Series Nipples - Male Pipe Thread



Body Size (in.)	Part No. Brass	Part No. Steel	Part No. Stainless***	Thread Size	Length (in.)	Exposed Length**	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	-	0C	-	1/8-27 NPTF	1.47	0.74	0.58	0.50	0.04
1/4	B2C	2C	S2C	1/4-18 NPTF	1.62	0.89	0.65	0.56	0.06
1/4	-	2C-E	-	3/8-18 NPTF	1.72	0.99	0.80	0.69	0.05
3/8	-	0E	-	1/4-18 NPTF	1.88	0.95	0.72	0.62	0.08
3/8	-	2E	-	3/8-18 NPTF	1.90	0.98	0.80	0.69	0.09
1/2	-	0F	-	3/8-18 NPTF	2.33	1.12	0.79	0.69	0.13
1/2	-	2F	-	1/2-14 NPTF	2.48	1.27	1.01	0.88	0.17
1/2	-	H2F-G	-	3/4-14 NPTF	2.40	1.29	1.22	1.06	0.24

** This dimension represents portion of nipple that is exposed when nipple is inserted in a Parker 10 Series coupler

*** Prop 65 Warning does not apply to stainless steel part numbers



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

10 Series Couplers Tru-Flate Design (Automotive Interchange)

Manual sleeve, single shut-off



10 Series Nipples - Standard Hose Barb



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Exposed Length**	Largest Diameter	Weight (lbs.)
1/4	8C	1/4	1.63	0.90	0.45	0.04
1/4	9C	3/8	2.00	1.27	0.55	0.05
3/8	5E	3/8	1.81	0.98	0.59	0.07
1/2	H4F	3/8	2.36	1.29	0.66	0.08
1/2	5F	1/2	2.36	1.60	0.66	0.11
1/2	H5F-G	3/4	2.95	1.91	0.87	0.18

** This dimension represents portion of nipple that is exposed when nipple is inserted in a Parker 10 Series coupler

10 Series Nipples - Push-Lok Hose Barb*



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Exposed Length**	Largest Diameter	Weight (lbs.)
1/4	8CP	1/4	1.66	0.93	0.45	0.04
1/4	9CP	3/8	1.98	1.25	0.86	0.05
3/8	5EP	3/8	1.98	1.06	0.59	0.08
1/2	H4FP	3/8	2.52	1.27	0.86	0.11
1/2	H5FP	1/2	2.66	1.42	0.97	0.11

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps

**This dimension represents portion of nipple that is exposed when nipple is inserted in a Parker 10 Series coupler

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

10 Series Couplers Tru-Flate Design (Automotive Interchange)

A-21



Pneumatic Quick Couplings

General Purpose

Manual sleeve, single shut-off

10 Series Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B 13A	-	1/8-27 NPTF	1.83	0.90	0.75	0.19
1/4	B 13	-	1/4-18 NPTF	1.83	0.90	0.75	0.19
1/4	B 13E	-	3/8-18 NPTF	1.95	0.94	0.81	0.31
3/8	-	15C	1/4-18 NPTF	2.22	1.06	0.88	0.30
3/8	B 15*	15	3/8-18 NPTF	2.28	1.06	0.88	0.34
3/8	-	15F	1/2-14 NPTF	2.55	1.16	1.00	0.46
1/2	-	17E	3/8-18 NPTF	2.74	1.19	1.00	0.46
1/2	B 17*	17	1/2-14 NPTF	2.96	1.19	1.00	0.50
1/2	-	17G	3/4-14 NPTF	3.19	1.44	1.25	0.20

* Coupler has brass body and steel sleeve

10 Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B 12A	-	1/8-27 NPTF	1.89	0.90	0.75	0.17
1/4	B 12	-	1/4-18 NPTF	2.05	0.90	0.75	0.18
1/4	B 12E	-	3/8-18 NPTF	2.08	0.90	0.75	0.19
3/8	-	14C	1/4-18 NPTF	2.36	1.06	0.88	0.26
3/8	B 14*	14	3/8-18 NPTF	2.39	1.06	0.88	0.27
3/8	-	14F	1/2-14 NPTF	2.55	1.06	0.88	0.28
1/2	-	16E	3/8-18 NPTF	2.93	1.19	1.00	0.42
1/2	B 16*	16	1/2-14 NPTF	3.08	1.19	1.00	0.45
1/2	-	16G	3/4-14 NPTF	3.21	1.30	1.13	0.50

* Coupler has brass body and steel sleeve



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

10 Series Couplers Tru-Flate Design (Automotive Interchange)

Manual sleeve, single shut-off



10 Series Couplers - Standard Hose Barb



Body Size (in.)	Part Number Brass	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B10-3B	-	1/4	2.49	0.90	0.75	0.18
1/4	B10-4B	-	5/16	2.49	0.90	0.75	-
1/4	B10-5B	-	3/8	2.49	0.90	0.75	0.18
3/8	-	14-5B	3/8	2.60	1.06	0.88	0.26
3/8	-	14-6B	1/2	2.60	1.06	0.88	0.27
1/2	-	16-5B	3/8	3.14	1.19	1.00	0.41
1/2	-	16-6B	1/2	3.14	1.19	1.00	0.43
1/2	-	16-7B	3/4	3.60	1.19	1.00	0.48

Add suffix "N" to brass coupler part number for stainless steel springs and locking balls (ie B15N).

Add suffix "-SL" for Sleeve-Lok option.

Add suffix "R" for grip-ring sleeve (1/4" size only).

10 Series Couplers - Push-Lok Hose Barb*



Body Size (in.)	Part Number Brass	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B10-3BP	-	1/4	2.32	0.90	0.75	0.19
1/4	B10-4BP	-	3/8	2.47	0.90	0.75	0.19
3/8	-	14-5BP	3/8	2.88	1.06	0.88	0.26
1/2	-	16-5BP	3/8	3.35	1.19	1.00	0.40
1/2	-	16-6BP	1/2	3.46	1.19	1.00	0.43

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

50 Series Couplers ARO 210 Interchange

Manual sleeve, single shut-off



50 Series Pneumatic Couplers are interchangeable with ARO's 210 series. Couplers have brass bodies. Nipples are constructed of steel. Sleeve-Lok is an optional feature.




Features:

- Tubular valve delivers high air flow with minimal pressure drop
- Stainless steel springs and locking balls option is available for added corrosion resistance
- Standard seal is Nitrile

Applications include:

- Air compressors
- Pneumatic tools
- Water
- Grease
- Paint

Performance



50 Series Specification

Body Size	1/4
Rated Pressure (psi)	300
Temperature Range (std seals)	-40° to +250° F
Locking Device	4 balls
Vacuum Service	Not Recommended

50 Series Repair Kits

Body Size	Seal Material	Part No.
1/4	Nitrile	21K
1/4	Ethylene Propylene	21KW
1/4	Fluorocarbon	21KY

Optional Materials and Features: (add code to part number)

Contact QCD for availability and additional options.
 To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix N	Stainless steel springs, locking balls & brass valves (Couplers)	B52N
suffix -SL	Sleeve-Lok (Couplers)	B52-SL
suffix W	Ethylene Propylene seal material (-65° to + 400° F) (Couplers)	B52W
suffix Y	Fluorocarbon seal material (-30° to + 400° F) (Couplers)	B52Y

Pneumatic Quick Couplings

General Purpose

50 Series Couplers ARO 210 Interchange

Manual sleeve, single shut-off



50 Series Nipples - Female Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Exposed Length**	Wrench Flats	Weight (lbs.)
1/4	A3C	1/4-18 NPTF	1.47	0.72	0.66	0.62	0.04

50 Series Nipples - Male Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Exposed Length**	Wrench Flats	Weight (lbs.)
1/4	A2C	1/4-18 NPTF	1.62	0.65	0.82	0.56	0.05

50 Series Nipples - Standard Hose Barb



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Exposed Length**	Wrench Flats	Weight (lbs.)
1/4	A8C	1/4	1.63	0.43	0.82	0.62	0.03

50 Series Nipples - Push-Lok Hose Barb*



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Exposed Length**	Wrench Flats	Weight (lbs.)
1/4	A8CP	1/4	1.65	0.67	0.87	0.62	0.03

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

**This dimension represents portion of nipple that is exposed when nipple is inserted in a Parker 50 Series coupler

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

50 Series Couplers ARO 210 Interchange

Manual sleeve, single shut-off



50 Series Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B53	1/4-18 NPTF	1.83	0.90	0.75	0.20
1/4	B53E	3/8-18 NPTF	1.95	0.94	0.81	0.21

50 Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B52	1/4-18 NPTF	2.05	0.90	0.75	0.20
1/4	B52E	3/8-18 NPTF	2.08	0.90	0.75	0.21

50 Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B50-3BP	1/4	2.32	0.90	0.75	0.19
1/4	B50-5BP	3/8	2.47	0.90	0.75	0.20

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

Universal Couplers

Accepts three types of Nipples

Push-to-connect sleeve, single shut-off



UC Series Pneumatic Quick Couplers connect with Industrial Interchange, 10 series (Tru-Flate), and 50 series (ARO 210) style nipples. While the best performance is obtained by matching like series couplers and nipples, the Universal Coupler permits multiple series nipples to mate with one coupler.




Features:

- Sleeve guard protects against accidental disconnection
- Push-to-connect operation
- Brass construction
- One coupler connects with three nipple styles
- UC Series is a replacement for the HA Series

Applications include:


- Air compressors
- Pneumatic tools
- Drop-down air lines

Performance



UC Series Specification

Body Size	1/4
Rated Pressure (psi)	150
Temperature Range (std seals)	-40° to +250° F
Locking Device	4 balls
Vacuum Service	Not Recommended



Pneumatic Quick Couplings

General Purpose

Universal Couplers

Accepts three types of Nipples

Push-to-connect sleeve, single shut-off



Universal Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	UC-251-4FP	1/4-18 NPSF	2.06	0.98	0.81	0.23
1/4	UC-251-6FP	3/8-18 NPSF	2.21	0.98	0.81	0.23

Universal Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	UC-251-4MP	1/4-18 NPTF	2.21	0.98	0.81	0.22
1/4	UC-251-6MP	3/8-18 NPTF	2.24	0.98	0.81	0.23



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

70 Series Couplers Lincoln (Long) Interchange

Manual sleeve, single shut-off



70 Series Pneumatic Couplers are interchangeable with Lincoln's "Long Stem" series couplings. Couplers have brass bodies and steel valves. Nipples are constructed of steel. Sleeve-Lok is an optional feature.




Features:

- Integral sleeve guard resists accidental disconnection
- Tubular valve delivers high air flow with minimal pressure drop
- Standard seal is Nitrile

Applications include:

- Air compressors
- Pneumatic tools
- Water
- Grease
- Paint

Performance



70 Series Specification

Body Size	1/4
Rated Pressure (psi)	300
Temperature Range (std seals)	-40° to +250° F
Locking Device	4 balls
Vacuum Service	Not Recommended

70 Series Repair Kits

Body Size	Seal Material	Part No.
1/4	Nitrile	21K
1/4	Ethylene Propylene	21KW
1/4	Fluorocarbon	21KY

Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix N	Stainless steel springs, locking balls & brass valves (Couplers)	B72N
suffix -SL	Sleeve-Lok (Couplers)	B72-SL
suffix W	Ethylene Propylene seal material (-65° to + 400° F) (Couplers)	B72W
suffix Y	Fluorocarbon seal material (-30° to + 400° F) (Couplers)	B72Y

Pneumatic Quick Couplings

General Purpose

70 Series Couplers Lincoln (Long) Interchange

Manual sleeve, single shut-off



70 Series Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B73	1/4-18 NPTF	2.40	0.90	0.75	0.25

70 Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	B72	1/4-18 NPTF	2.62	0.90	0.75	0.25

70 Series Nipples - Female Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	L3C	1/4-18 NPTF	2.10	0.77	0.65	0.56	0.05

70 Series Nipples - Male Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	L2C	1/4-18 NPTF	2.25	0.92	0.65	0.56	0.06

* This dimension represents portion of nipple that is exposed when nipple is inserted in a Parker 70 Series coupler.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

Rectus 25 Series Couplers

High Flow European Interface

Formerly RF Series

Push-to-connect sleeve, single shut-off



Rectus 25 Series Pneumatic Couplers are designed to increase flow and reduce pressure drop through the coupling. Rectus 25 nipples have up to 2-1/2 times larger flow area than standard industrial interchange nipples. The increased flow results in greater tool efficiency and decreased air costs. Couplers are nickel plated brass and nipples are steel.



Features:


- Aerodynamic valve design
- Flow rates on 1/4" is greater than many 3/8" body size couplers
- Integral sleeve guard protects against accidental disconnection
- Functionally interchanges with a common high-flow European design. 1/4 Rectus 25 interchanges with CEJN 320
- Standard seal is Nitrile

Applications include:

- Air compressors
- Pneumatic tools
- Drop-down air lines

Performance

**Rectus 25 Series (1/4" body size)
with 1/4" Female NPSF**



Rectus 25 Series Specification

Body Size	1/4
Rated Pressure (psi)	300
Temperature Range (std seals)	-4° to +212° F
Locking Device	4 balls
Vacuum Service	Not Recommended

Rectus 25 Series Couplers

High Flow European Interface

Formerly RF Series

A-31



Pneumatic Quick Couplings

General Purpose

Push-to-connect sleeve, single shut-off

Couplers - Female Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	25KAIN13MPN	RF-251-4FP	1/4-18 NPSF	2.19	0.99	0.81	0.26
1/4	25KAIN17MPN	RF-251-6FP	3/8-18 NPSF	2.34	0.99	0.81	0.27

Couplers - Male Pipe Thread



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	25KAAN13MPN	RF-251-4MP	1/4-18 NPTF	2.34	0.99	0.81	0.24
1/4	25KAAN17MPN	RF-251-6MP	3/8-18 NPTF	2.37	0.99	0.81	0.25

Couplers - Standard Hose Barb



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	25KATF06MPN	RF-251-4HB	1/4	2.81	0.99	0.81	0.26
1/4	25KATF10MPN	RF-251-6HB	3/8	2.81	0.99	0.81	0.27

Couplers - Push-Lok Hose Barb*



Body Size (in.)	New Part Number Nickel Plated Brass	Old Part Number Brass	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	25KATP06MPN	RF-251-4PL	1/4	2.64	0.99	0.81	0.26
1/4	25KATP10MPN	RF-251-6PL	3/8	2.78	0.99	0.81	0.27

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

Rectus 25 Series Couplers High Flow European Interface Formerly RF Series

Push-to-connect sleeve, single shut-off



Nipples - Female Pipe Thread



Body Size (in.)	New Part Number Steel	Old Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	25SF1N13SXZ	RF-254-4FP	1/4-18 NPTF	1.45	0.72	0.62	0.06
1/4	25SF1N17SXZ	RF-254-6FP	3/8-18 NPTF	1.50	0.94	0.81	0.09

Nipples - Male Pipe Thread



Body Size (in.)	New Part Number Steel	Old Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	25SFAN13SXZ	RF-254-4MP	1/4-18 NPTF	1.60	0.65	0.56	0.05
1/4	25SFAN17SXZ	RF-254-6MP	3/8-18 NPTF	1.67	0.75	0.69	0.08

Nipples - Standard Hose Barb



Body Size (in.)	New Part Number Steel	Old Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Weight (lbs.)
1/4	25SFTF06SXZ	RF-254-4HB	1/4	1.66	0.50	0.04
1/4	25SFTF10SXZ	RF-254-6HB	3/8	1.66	0.50	0.05

Nipples - Push-Lok Hose Barb*



Body Size (in.)	New Part Number Steel	Old Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Weight (lbs.)
1/4	25SFTP06SXN	RF-254-4PL	1/4	1.69	0.50	0.04
1/4	25SFTP10SXN	RF-254-6PL	3/8	1.83	0.50	0.05

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

TL Series Couplers Schrader Twist-Lock Interchange

Push-to-connect sleeve, single shut-off



TL Series Pneumatic Couplers are interchangeable with Schrader Twist-Lock style couplings. Couplers have brass bodies and steel sleeves. Nipples are constructed of steel.




Features:

- Designed to resist accidental disconnection
- Push-to-connect, twist sleeve 1/8 turn to disconnect
- Tubular valve delivers high air flow with minimal pressure drop
- Standard seal is Nitrile

Applications include:

- Air compressors
- Pneumatic tools
- Water
- Grease
- Paint

Performance



TL Series Specification

Body Size	1/4	1/2
Rated Pressure (psi)	300	
Temperature Range (std seals)	-40° to +250° F	
Locking Device	CAM	
Vacuum Service	Not Recommended	

TL Series Repair Kits

Body Size	Seal Material	Part No.
1/4	Nitrile	21K
1/4	Ethylene Propylene	21KW
1/4	Fluorocarbon	21KY
1/2	Nitrile	16K
1/2	Ethylene Propylene	16KW
1/2	Fluorocarbon	16KY

How To Order

TL - 251 - 4 FP

Port Configuration
 FP - Female Pipe
 MP - Male Pipe
 HB - Standard Hose Barb
 PL - Push-Lok Hose Barb

Port Size (1/16 of an inch)

Unit
 1 - Valved Coupler
 4 - Unvalved Nipple

Body Size
 25 - 1/4"
 50 - 1/2"

TL Series

Pneumatic Quick Couplings

General Purpose

TL Series Couplers Schrader Twist-Lock Interchange

Push-to-connect sleeve, single shut-off



Optional Seal Materials:
(add code to part number)

Contact QCD for availability and additional options.
To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix W	Ethylene Propylene seal material (-65° to + 400° F) (Couplers)	TL-251-4FPW
suffix Y	Fluorocarbon seal material (-30° to + 400° F) (Couplers)	TL-251-4FPY

Couplers - Female Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	TL-251-4FP	1/4-18 NPTF	2.01	1.12	0.75	0.21
1/2	TL-501-6FP	3/8-18 NPTF	2.55	1.50	1.13	0.44
1/2	TL-501-8FP	1/2-14 NPTF	2.78	1.50	1.13	0.44
1/2	TL-501-12FP	3/4-14 NPTF	2.91	1.50	1.13	0.44

Couplers - Male Thread



Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	TL-251-4MP	1/4-18 NPTF	2.23	1.12	0.75	0.21
1/4	TL-251-6MP	3/8-18 NPTF	2.26	1.12	0.75	0.22
1/2	TL-501-6MP	3/8-18 NPTF	2.71	1.50	1.13	0.39
1/2	TL-501-8MP	1/2-14 NPTF	2.88	1.50	1.13	0.40

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

TL Series Couplers Schrader Twist-Lock Interchange

Push-to-connect sleeve, single shut-off



Nipples - Female Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	TL-254-2FP	1/8-27 NPTF	1.50	0.58	0.50	0.04
1/4	TL-254-4FP	1/4-18 NPTF	1.60	0.72	0.63	0.06
1/2	TL-504-4FP	1/4-18 NPTF	1.90	0.80	0.69	0.12
1/2	TL-504-6FP	3/8-18 NPTF	1.75	0.94	0.81	0.13

Nipples - Male Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	TL-254-2MP	1/8-27 NPTF	1.68	0.58	0.50	0.05
1/4	TL-254-4MP	1/4-18 NPTF	1.72	0.65	0.56	0.06
1/2	TL-504-4MP	1/4-18 NPTF	1.90	0.80	0.69	0.12
1/2	TL-504-6MP	3/8-18 NPTF	1.90	0.80	0.69	0.12
1/2	TL-504-8MP	1/2-14 NPTF	2.06	1.01	0.88	0.16
1/2	TL-504-12MP	3/4-14 NPTF	2.12	1.22	1.06	0.22

Nipples - Standard Hose Barb



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Weight (lbs.)
1/4	TL-254-4HB	1/4	1.83	0.50	0.03
1/4	TL-254-6HB	3/8	1.83	0.50	0.04
1/2	TL-504-4HB	1/4	2.06	0.67	0.07
1/2	TL-504-6HB	3/8	2.06	0.67	0.08
1/2	TL-504-8HB	1/2	2.06	0.67	0.10



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

General Purpose

IH Series Snap-tite Design

Manual sleeve, single shut-off



IH couplers are steel with a cylindrical valve designed specifically for pneumatic use. When paired with an unvalved/plain H Series nipple, it functions as a durable single shut-off connection. Standard seal is nitrile.





Features:

- Sizes 1/4" - 3/4"
- Steel body material
- Standard seal material is nitrile with other options available
- Optional sleeve lock helps to prevent accidental disconnection
- Manually operated sleeve provides secure connection
- Coupler has 360° cylindrical valve contact

Applications include:

- Industrial air lines
- Pneumatic tools

Performance



Cylindrical Pneumatic Valve

IH Series Working Pressures (psi)

Valved on coupler and unvalved nipple (Single Shut-off)

Body Size	1/4	3/8	1/2	3/4
Steel	6500	4500	4000	3500

NOTE: Pressure ratings were established under static pressure conditions. Therefore, pressure ratings for any given flow, pressure surge and/or vibration may vary from these ratings. Burst pressures listed were taken at the point at which failure rendered the quick disconnect inoperative. (Proof pressure equals 1-1/2 times the working pressure; burst pressure equals 2 times working pressure.)

Pneumatic Quick Couplings

General Purpose

IH Series Snap-tite Design

Manual sleeve, single shut-off



IH Series Couplers - Valved



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Sleeve Lock
1/4	VIHC4-4F	1/4-18 NPTF (female)	1.65	1.19	1.00	
1/4	VIHC4-4FSL	1/4-18 NPTF (female)	1.65	1.19	1.00	Yes
1/4	VIHC4-4M	1/4-18 NPT (male)	2.09	1.02	0.88	
1/4	VIHC4-4MSL	1/4-18 NPT (male)	2.09	1.02	0.88	Yes
3/8	VIHC6-6F	3/8-18 NPTF (female)	1.90	1.19	1.00	
3/8	VIHC6-6FSL	3/8-18 NPTF (female)	1.90	1.19	1.00	Yes
3/8	VIHC6-6M	3/8-18 NPT (male)	2.19	1.19	1.00	
3/8	VIHC6-6MSL	3/8-18 NPT (male)	2.19	1.19	1.00	Yes
1/2	VIHC8-8F	1/2-14 NPTF (female)	2.09	1.39	1.19	
3/4	VIHC12-12F	3/4-14 NPTF (female)	2.42	1.73	1.50	

H Series Nipples - Unvalved / Plain



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats
1/4	PHN4-4F	1/4-18 NPTF (female)	1.32	0.73	0.88
1/4	PHN4-4M	1/4-18 NPT (male)	0.78	0.65	0.56
3/8	PHN6-6F	3/8-18 NPTF (female)	1.52	0.94	0.81
3/8	PHN6-6M	3/8-18 NPT (male)	0.98	0.80	0.69
1/2	PHN8-8F	1/2 -14 NPTF (female)	1.72	1.15	1.00
1/2	PHN8-8M	1/2 -14 NPTF (male)	1.01	1.02	0.88
3/4	PHN12-12F	3/4 -14 NPT (female)	1.92	1.37	1.19
3/4	PHN12-12M	3/4 -14 NPT (male)	1.14	1.22	1.06

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

Special Purpose

Tool-Mate Series Couplers (Standard) Rectus 25 and Industrial Interchange Styles

Non-marring, push-to-connect sleeve



Tool-Mate Series are light weight and easy to operate with a non-marring body. Couplers are constructed of Polyamide material with galvanized steel port ends. Springs, balls and pins are stainless steel and locking fingers are polyacetate. Grey body color designates standard, non-venting style coupler.



Features:


- Push-to-connect operation, pull sleeve in the direction of the arrow to release the nipple
- PBH part number (yellow ring) couplers connect with Industrial Interchange nipples
- PER part number (green ring) couplers connect with Rectus 25 series nipples
- Standard seal is Nitrile

Applications include:

- Industrial air lines
- Drop-down air lines

Performance

Tool-Mate Series Standard (1/4" & 3/8" sizes)



Tool Mate Standard Series Specification

Body Size	1/4	3/8
Rated Pressure (psi)	300	
Temperature Range (std seals)	0° to +160° F	
Vacuum Service	Not Recommended	

How To Order

PBH - 251 - 4 FP

- Port Configuration
 - FP - Female Pipe
 - MP - Male Pipe
- Port Size (1/16 of an inch)
 - 4 - 1/4"
 - 6 - 3/8"
 - 8 - 1/2"
- Unit
 - 1 - Valved Coupler
- Body Size
 - 25 - 1/4"
 - 37 - 3/8"

Tool-Mate Series (Non-venting)
 PBH - Industrial Interchange
 PER - Rectus 25 Interchange

Pneumatic Quick Couplings

Special Purpose

Tool-Mate Series Couplers (Standard) Rectus 25 and Industrial Interchange Styles

Non-marring, push-to-connect sleeve



Industrial Interchange - Female Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PBH-251-4FP	1/4-18 NPTF	2.60	1.19	0.67	0.13
1/4	PBH-251-6FP	3/8-18 NPTF	2.67	1.19	0.91	0.15
3/8	PBH-371-4FP	1/4-18 NPTF	2.95	1.38	0.67	0.21
3/8	PBH-371-6FP	3/8-18 NPTF	2.95	1.38	0.83	0.20
3/8	PBH-371-8FP	1/2-14 NPTF	3.17	1.38	0.99	0.22

Industrial Interchange - Male Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PBH-251-4MP	1/4-18 NPTF	2.97	1.19	0.67	0.14
1/4	PBH-251-6MP	3/8-18 NPTF	2.99	1.19	0.91	0.19
3/8	PBH-371-6MP	3/8-18 NPTF	3.39	1.38	0.83	0.23

Rectus 25 Interchange - Female Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PER-251-4FP	1/4-18 NPTF	2.83	1.25	0.83	0.17
1/4	PER-251-6FP	3/8-18 NPTF	2.83	1.25	0.83	0.15

Rectus 25 Interchange - Male Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PER-251-4MP	1/4-18 NPTF	2.36	1.25	0.83	0.19



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

Special Purpose

Tool-Mate Series Couplers (Exhaust) Rectus 25 and Industrial Interchange Styles

Non-marring, push-to-connect sleeve



Tool-Mate Series are light weight and easy to operate with a non-marring body. Exhaust style couplers allow disconnection at zero pressure to avoid dangerous hose whip. Couplers are constructed of Polyamide material with galvanized steel port ends. Springs, balls and pins are stainless steel and locking fingers are polyacetate. Black body color designates venting, exhaust style coupler.



Features:


- Meets ISO 4414 requirements for a controlled pressure release system
- Push-to-connect operation, two step disconnection as indicated by the arrows, provides safe venting of downstream pressure
- PBS part number (yellow ring) couplers connect with Industrial Interchange nipples
- PES part number (green ring) couplers connect with Rectus 25 series nipples
- Standard seal is Nitrile

Applications include:

- Pneumatic tools
- Drop-down air lines

Performance

Tool-Mate Series Exhaust (1/4", 3/8" & 1/2" sizes)



Tool Mate Exhaust Series Specification

Body Size	1/4	3/8	1/2
Rated Pressure (psi)	300		
Temperature Range (std seals)	0° to +160° F		
Vacuum Service	Not Recommended		

How To Order

PBS - 251 - 4 FP

Port Configuration

FP - Female Pipe

MP - Male Pipe

Port Size (1/16 of an inch)

4 - 1/4"

6 - 3/8"

8 - 1/2"

12 - 3/4"

Unit

1 - Valved Coupler

Body Size

25 - 1/4"

37 - 3/8"

50 - 1/2"

Tool-Mate Series (Exhaust)

PBS - Industrial Interchange

PES - Rectus 25 Interchange

Pneumatic Quick Couplings

Special Purpose

Tool-Mate Series Couplers (Exhaust) Rectus 25 and Industrial Interchange Styles

Non-marring, push-to-connect sleeve



Exhaust Industrial Interchange - Female Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PBS-251-4FP	1/4-18 NPTF	2.60	1.19	0.67	0.13
1/4	PBS-251-6FP	3/8-18 NPTF	2.67	1.19	0.91	0.15
3/8	PBS-371-6FP	3/8-18 NPTF	2.95	1.38	0.82	0.20
3/8	PBS-371-8FP	1/2-14 NPTF	3.17	1.38	0.99	0.22
1/2	PBS-501-6FP	3/8-18 NPTF	3.25	1.62	1.18	0.50
1/2	PBS-501-8FP	1/2-14 NPTF	3.36	1.62	1.18	0.50
1/2	PBS-501-12FP	3/4-14 NPTF	3.66	1.62	1.18	0.50

Exhaust Industrial Interchange - Male Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PBS-251-4MP	1/4-18 NPTF	2.97	1.19	0.67	0.14
1/4	PBS-251-6MP	3/8-18 NPTF	2.99	1.19	0.91	0.19
3/8	PBS-371-6MP	3/8-18 NPTF	3.39	1.38	0.82	0.23
3/8	PBS-371-8MP	1/2-14 NPTF	3.39	1.38	0.91	0.28
1/2	PBS-501-8MP	1/2-14 NPTF	3.70	1.62	1.18	0.50

Exhaust Rectus 25 Interchange - Female Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PES-251-6FP	3/8-18 NPTF	2.83	0.83	0.83	0.15

Exhaust Rectus 25 Interchange - Male Pipe Thread



Body Size (in.)	Part Number	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	PES-251-4MP	1/4-18 NPTF	2.36	1.25	0.83	0.19



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

Special Purpose

E-z-mate Series Couplers (Exhaust)

Accepts Industrial Interchange Nipples

Push-to-connect sleeve



E-z-mate Series are exhaust type quick couplers that are designed to safely relieve air pressure prior to disconnection. When the valve sleeve is twisted to shut off air flow, it automatically vents downstream allowing for disconnection at zero pressure and eliminating the risk of "hose whip".



Features:

- Self-locking valve sleeve protects against accidental disconnection
- Push-to-connect operation
- Meets ISO 4414 requirements for a controlled pressure release system
- Connection and disconnection at zero pressure
- Brass material option - contact QCD for availability

Applications include:

- Pneumatic tools
- Drop-down air lines



Operation

Parker E-z-mate couplings combine push-to-connect, exhaust-style action with a self-locking valve sleeve to guard against accidental disconnection. Simply follow the direction of the On-Off arrow stamped on the valve sleeve. It's that easy.

To connect, push the nipple into the coupler. The black locking sleeve automatically slides forward securely locking the nipple in place. No air is allowed to flow through the coupling at this point. The valve sleeve is then rotated clockwise (when viewed from the coupler port end) to open flow and automatically engage the sleeve-lock mechanism.

To disconnect, rotate the valve sleeve counter clockwise (when viewed from the coupler end). The flow of air through the coupling will be shut off and all downstream air is vented to the atmosphere. The locking sleeve may now be retracted and the nipple removed. Lubricate sleeve as part of periodic maintenance to coupler.

Performance



E-z-mate Series Specification

Body Size	1/4	3/8	1/2	3/4
Rated Pressure (psi)	300			
Temperature Range (std seals)	-40° to +250° F			
Locking Device	4 balls	4 balls	6 balls	8 balls
Force required to connect (lbs.)	Less than 10			
Vacuum Service	Not Recommended			

EZ - 251 - 4 FP

Port Configuration
FP - Female Pipe
MP - Male Pipe
HB - Standard Hose Barb
PL - Push-Lok Hose Barb

Port Size (1/16 of an inch)

Unit
1 - Valved Coupler

Body Size
25 - 1/4"
37 - 3/8"
50 - 1/2"
75 - 3/4"

E-z-mate Series

Pneumatic Quick Couplings

Special Purpose

E-z-mate Series Couplers (Exhaust)

Accepts Industrial
Interchange Nipples

Push-to-connect sleeve



E-z-mate Series Couplers - Female Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	EZ-251-4FP	1/4-18 NPTF	2.25	1.00	0.75	0.25
1/4	EZ-251-6FP	3/8-18 NPTF	2.68	1.01	0.88	0.29
3/8	EZ-371-6FP	3/8-18 NPTF	2.53	1.18	0.88	0.38
3/8	EZ-371-8FP	1/2-14 NPTF	3.00	1.30	1.12	0.50
1/2	EZ-501-8FP	1/2-14 NPTF	3.01	1.38	1.12	0.65
1/2	EZ-501-12FP	3/4-14 NPTF	3.44	1.59	1.38	0.70
3/4	EZ-751-12FP	3/4-14 NPTF	3.01	1.57	1.38	0.76
3/4	EZ-751-16FP	1-11 1/2 NPTF	3.52	1.80	1.56	0.92

E-z-mate Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	EZ-251-4MP	1/4-18 NPTF	2.85	1.00	0.75	0.30
1/4	EZ-251-6MP	3/8-18 NPTF	2.87	1.00	0.75	0.31
3/8	EZ-371-6MP	3/8-18 NPTF	3.10	1.18	0.88	0.44
1/2	EZ-501-8MP	1/2-14 NPTF	3.62	1.38	1.12	0.73
3/4	EZ-751-12MP	3/4-14 NPTF	4.04	1.57	1.38	0.90

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

Special Purpose

E-z-mate Series Couplers (Exhaust)

Accepts Industrial
Interchange Nipples

Push-to-connect sleeve



E-z-mate Series Couplers - Standard Hose Barb



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	EZ-251-4HB	1/4	3.20	1.00	0.75	0.28
1/4	EZ-251-6HB	3/8	3.20	1.00	0.75	0.29
3/8	EZ-371-6HB	3/8	3.43	1.18	0.88	0.42
1/2	EZ-501-8HB	1/2	4.06	1.40	1.12	0.70

E-z-mate Series Couplers - Push-Lok Hose Barb*



Body Size (in.)	Part Number Steel	Hose I.D.	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	EZ-251-4PL	1/4	3.03	1.00	0.75	0.28
1/4	EZ-251-6PL	3/8	3.18	1.00	0.75	0.29
3/8	EZ-371-6PL	3/8	3.38	1.18	0.88	0.42
1/2	EZ-501-8PL	1/2	3.91	1.38	1.12	0.70

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Pneumatic Quick Couplings

Special Purpose

GF Series Natural & Propane Gas

Safety fuse nipple



GF/GF-1 Series couplings are valved on the coupler half and will automatically shut off gas flow when coupling is disconnected and automatically open on connection. They also incorporate a safety fuse in the nipple that will shut off the gas supply to your application in the event temperatures exceed 350°F.



Features:

- Superior flow capacity
- 0.5 psi max pressure rating (25 psi max pressure rating on 3/4" body size only)
- 1/2" - 1-1/4" size range
- Certified to ANSI Z21-41-2011, CSA 6.9-2011 for use with natural, manufactured and mixed gases, liquefied petroleum gases and LP gas-air mixtures
- On-site CSA certified lab and qualified inspection personnel
- Fusible link internal to the nipple protects against gas-fed fires

Applications include:

- Small Gas Appliances



GF Series Specification

Body Size	1/2	3/4	1	1-1/4
Flow Capacity*	99,600 Btu/hr	212,000 Btu/hr	378,000 Btu/hr	475,000 Btu/hr
Temperature Range: Standard GF/GF-1 (indoor use) temperature range: 32°F to 200°F. Contact QCD for low temperature version (outdoor use) temperature range; -40°F to 200°F				

*Based on a 1000 Btu per cubic foot gas with a specific gravity of 0.64 at a pressure drop of 0.3 in. w.c.

Pneumatic Quick Couplings

Special Purpose

GF Series Natural & Propane Gas

Safety fuse nipple



GF Series - Couplers



Body Size (in.)	Part Number Brass	Port End	Length (in.)	Connected Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/2	BVGF-1C8-8F	1/2-14 NPTF	2.47	3.39	1.42	1.00	0.326
3/4	BVGF-1C12-12F	3/4-14 NPTF	2.51	3.48	1.66	1.31	0.534
1	BVGFC16-16F	1-11-1/2 NPTF	2.69	3.91	2.03	1.88	1.150
1-1/4	BVGFC20-20F	1-1/4-11-1/2 NPTF	3.54	4.88	2.25	2.00	1.568

GF Series - Nipples



Body Size (in.)	Part Number Brass	Port End	Length (in.)	Connected Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/2	BPGF-1N8-8F	1/2-14 NPTF	1.55	3.39	1.13	1.00	0.154
3/4	BPGF-1N12-12F	3/4-14 NPTF	1.79	3.48	1.34	1.19	0.212
1	BPGFN16-16F	1-11-1/2 NPTF	2.10	3.91	1.65	1.50	0.380
1-1/4	BPGFN20-20F	1-1/4-11-1/2 NPTF	2.22	4.88	2.06	1.88	0.576

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Table of Contents

Introduction	B-2
---------------------------	------------

Coupling Selection & Ordering Guide	B-3, 4
--	---------------

General Purpose Couplings

60 Series	B-5
-----------------	-----

Couplers	B-7
----------------	-----

Nipples	B-9
---------------	-----

60 Series Steam	B-11
-----------------------	------

Couplers	B-11
----------------	------

Nipples	B-11
---------------	------

6600 Series	B-12
-------------------	------

Couplers	B-13
----------------	------

Nipples	B-13
---------------	------

H & PH Series	B-15
---------------------	------

H Couplers	B-18
------------------	------

H Nipples	B-22
-----------------	------

PH Couplers	B-21
-------------------	------

PH Nipples	B-25
------------------	------

EA Series	B-26
-----------------	------

Couplers	B-28
----------------	------

Nipples	B-29
---------------	------

SM Series	B-30
-----------------	------

Couplers	B-31
----------------	------

Nipples	B-32
---------------	------

HP Series	B-33
-----------------	------

Couplers	B-34
----------------	------

Nipples	B-34
---------------	------

4000 Series	B-35
-------------------	------

Couplers	B-36
----------------	------

Nipples	B-37
---------------	------

4200 Series	B-38
-------------------	------

Couplers	B-39
----------------	------

Nipples	B-39
---------------	------

Non-Spill Couplings

NS Series	B-40
-----------------	------

Couplers	B-41
----------------	------

Nipples	B-41
---------------	------

NSS Series	B-42
------------------	------

Couplers	B-43
----------------	------

Nipples	B-44
---------------	------

FF/FC Series	B-46
--------------------	------

Couplers	B-47
----------------	------

Nipples	B-48
---------------	------

FC Nipples	B-49
------------------	------

FEM/FEC Series	B-50
----------------------	------

Couplers	B-51
----------------	------

Nipples	B-53
---------------	------

FEC Nipples	B-55
-------------------	------

FH Series	B-56
-----------------	------

Couplers	B-57
----------------	------

Nipples	B-57
---------------	------

FS Series	B-58
-----------------	------

Couplers	B-59
----------------	------

Nipples	B-59
---------------	------

Instrumentation Couplings

CPI Series	B-61
------------------	------

Couplers	B-62
----------------	------

Nipples	B-63
---------------	------

Connect Under Pressure Couplings

59 Series	B-66
-----------------	------

Couplers	B-67
----------------	------

Nipples	B-67
---------------	------

FET Series	B-68
------------------	------

Couplers	B-69
----------------	------

Nipples	B-70
---------------	------

6100 Series	B-72
-------------------	------

Couplers	B-73
----------------	------

Nipples	B-73
---------------	------

8200 Series	B-75
-------------------	------

Couplers	B-76
----------------	------

Nipples	B-76
---------------	------

9200 Series	B-77
-------------------	------

Couplers	B-78
----------------	------

Nipples	B-78
---------------	------

5000 Series	B-79
-------------------	------

Couplers	B-80
----------------	------

Nipples	B-80
---------------	------

75 Series	B-81
-----------------	------

Couplers	B-83
----------------	------

Nipples	B-83
---------------	------

High Pressure Couplings

71 Series	B-84
Couplers.....	B-86
Nipples.....	B-87
3000 Series.....	B-88
Couplers.....	B-89
Nipples.....	B-89
TC Series	B-90
Couplers.....	B-90
Nipples.....	B-90
1141 Series.....	B-91
Couplers.....	B-91
Nipples.....	B-91

High Flow Couplings

ST Series.....	B-92
Couplers.....	B-93
Nipples.....	B-94
1163 Series.....	B-95
Couplers.....	B-95
Nipples.....	B-95
HO Series.....	B-96
Couplers.....	B-96
Nipples.....	B-96

Mold Coolant Line Couplings

Moldmate Series.....	B-97
Couplers.....	B-98
Sub Assemblies & Replacement Parts	B-99
Nipples.....	B-101

Miniature

Rectus 21 DSO Series	B-103
(Formerly DM Series)	
Couplers.....	B-104
Nipples.....	B-104

SensoControl Diagnostic and Industrial Catalog	B-106
---	-------

Test Port Couplings

PD Series	B-107
Couplers.....	B-108
Nipples.....	B-108
PDP Series	B-111
Couplers.....	B-112
Nipples.....	B-112
EMA3 Series.....	B-113
Nipples.....	B-113
Gauge Adapters & Union.....	B-113
Transducer Adapters	B-114
Flexible Hose	B-114
PDFS Series - Fluid Sampling	B-116
Couplers.....	B-116
Nipples.....	B-116
Diagnostic Fittings - Tee Fittings	B-117

HYDRAULIC QUICK COUPLINGS

Double Shut-Off and Straight-Thru Couplings

Parker hydraulic couplings have a wide variety of designs, each tailored to a particular application or use. This catalog is arranged according to those categories. In each section the construction of a specific design will be detailed. However, based on the valving of the coupling, hydraulic couplings generally fall into one of two groups, either Double Shut-Off or Straight-Thru.

Double Shut-Off couplings are used extensively when it is important to minimize fluid loss upon disconnection. Both halves of the coupler, the body and the nipple, contain shut-off valves. These valves open automatically when the body and nipple are connected, and close automatically when the two halves are disconnected—keeping fluid loss to a minimum.

Parker Straight-Thru couplings have no valves in either half and are ideal for maximum flow application. Their smooth, open bore offers the lowest pressure drop of any quick disconnect coupling, and allows them to be thoroughly cleaned. Since there are no valves in either half, fluid flow should be shut off before the coupling is disconnected.

Rated Pressure

Rated pressure for the Parker hydraulic couplings range from 30 to 15,000 psi, depending on the coupling series, size and materials. Rated pressures as shown in this catalog are defined by ISO 5598, as “the qualified operating pressures which are recommended for a component or a system by the manufacturer.” Parker “Rated Pressures” have been established on the basis of laboratory tests which include, but are not limited to, static burst tests and multiple cycle impulse tests. System characteristics such as high cycling rates and high amplitude shocks either hydraulic or mechanical, can reduce the functioning life of a coupling, even if the system’s nominal pressure falls within the rated pressure range of the coupling.

For assistance in analyzing your application, contact your nearest Parker sales office or the Quick Coupling Division in Minneapolis.

Refer to the Safety Guide at the end of this catalog for considerations when selecting a Quick Coupling.

Refer to the Fluid Compatibility Chart (note Table of Contents) for seal selection assistance for both Double Shut-Off and Straight-Thru couplings.

Checklist for Selecting Quick Couplings

- ☐ What are the functional requirements of the coupling?
- ☐ What is the maximum working pressure of the application?
- ☐ Which seals and body material are compatible with the system’s fluid?
- ☐ Is the application static or dynamic?
- ☐ What size coupler is required?
- ☐ What is the maximum pressure drop suitable for the application?
- ☐ Does the application require the ability to connect and disconnect under pressure?
- ☐ What is the media temperature and ambient temperature?
- ☐ What end configurations are required?
- ☐ Is an industry interchange coupler required?
- ☐ Is air inclusion and fluid loss a concern in the application?

Hydraulic Coupling Selection Guide

Body Size (in.)	Valving Style	A	B	S	S3	S6	HP	TP	Locking Style	Std Seal Material*	Std Seal Temp Range	Rated Pressure	Coupling Series
General Purpose													
1/8 to 2-1/2	Poppet		■	■	■	■			Ball	Nitrile	-40° to +250° F	800-5000 psi	60 Series
1/4 to 1	Poppet		■						Ball	Ethylene Propylene	-65° to +400° F		60 Series (steam)
1/4 to 1	Poppet			■					Ball	Nitrile	-40° to +250° F	4000-5000 psi	6600 Series
1/4 to 4	Poppet/Unvalved	■	■	■		■			Ball	Nitrile	-40° to +250° F	150-11,000 psi	H Series
1/4 to 3/4	Valved/Unvalved		■	■		■			Ball	Nitrile	-40° to +250° F	vacuum - 3000 psi	EA Series
1/4 to 3/4	Poppet			■					Ball	Nitrile	-40° to +250° F	4500-6000 psi	SM Series
1 to 1-1/2	Poppet			■					Ball	Nitrile	-40° to +250° F	5000 psi	HP Series
1/4 to 1	Poppet/Ball			■					Ball	Nitrile	-40° to +250° F	3000 psi	4000 Series
3/8 to 1/2	Poppet/Ball			■					Ball	Nitrile	-40° to +250° F	3000 psi	4200 Series
Non-Spill													
3/8 to 1/2	Flush Face					■			Ball	Ethylene Propylene	-70° to +250° F	300-2000 psi	NSS Series
3/8 to 1	Flush Face			■					Ball	Nitrile	-40° to +250° F	2500 psi	NS Series
1/4 to 1	Flush Face			■					Ball	Nitrile/ Polyurethane	-40° to +250° F	3000-5000 psi	FF Series
1/4 to 1	Flush Face			■					Ball	Nitrile/ Polyurethane	-40° to +250° F	3000-5000 psi	FEM Series
1/4 to 1	Flush Face					■			Ball	Fluorocarbon	-15° to +400° F	2000 psi	FS Series
Non-Spill Connect Under Pressure													
3/8 to 1-1/2	Flush Face			■					Acme Threads	Nitrile/ Polyurethane	-40° to +250° F	5000-6000 psi	59 Series
3/8 to 2	Flush Face			■					Threads	Nitrile/ Polyurethane	-40° to +250° F	5000-6000 psi	FET Series
3/8 to 3/4	Flush Face			■					Ball	Nitrile/ Polyurethane	-40° to +250° F	3000 psi	FC Series
1/2 to 3/4	Flush Face			■					Ball	Nitrile/ Polyurethane	-40° to +250° F	3000 psi	FEC Series
3/4 to 1-1/2	Flush Face		■						Threads	Nitrile	-20° to +200° F	2000-3000 psi	6100 Series

Materials: A - Aluminum B - Brass S - Steel S3 - 303 Stainless S6 - 316 Stainless HP - High Pressure Stainless Steel TP - Thermoplastic



Hydraulic Coupling Selection Guide - continued

Body Size (in.)	Valving Style	A	B	S	S3	S6	HP	TP	Locking Style	Std Seal Material*	Std Seal Temp Range	Rated Pressure	Coupling Series
Instrumentation													
1/4	Poppet/Unvalved					■			Ball	Fluorocarbon	-15° to +400° F	250-3000 psi	CPI Series
3/8	Poppet/Unvalved					■			Ball	Fluorocarbon	-15° to +400° F	250-1500 psi	CPI Series
1/2	Poppet/Unvalved					■			Ball	Fluorocarbon	-15° to +400° F	250-750 psi	CPI Series
Connect Under Pressure													
1/2	Poppet			■					Ball	Nitrile	-40° to +250° F	3000 psi	8200 Series
1/2	Poppet			■					Ball	Nitrile	-40° to +250° F	3000 psi	9200 Series
1/2	Ball			■					Threads	Nitrile	-40° to +250° F	2500 psi	5000 Series
3/4 to 4	Poppet			■		■			Threads	Nitrile	-40° to +250° F	5000 psi	75 Series
High Pressure													
1/4 to 2	Flush Face			■		■	■		Ball	Nitrile	-40° to +250° F	10,000 psi	71 Series
3/8	Flush Face			■					Ball	Nitrile	-40° to +250° F	10,000 psi	FH Series
1/4 to 3/8	Ball			■					Threads	Polyurethane	-22° to +230° F	10,000 psi	3000 Series
3/8	Poppet			■					Ball	Fluorocarbon	-15° to +400° F	10,000 psi	TC Series
1/4	Poppet				■				Threads	Polyurethane	-30° to +180° F	10,000 psi	1141 Series
High Flow													
1/8 to 1-1/2	Unvalved		■	■	■				Ball	Nitrile	-40° to +250° F	2500-6700 psi	ST Series
1/4 to 1/2	Unvalved			■					Ball	Nitrile	-40° to +250° F	10,000-15,000 psi	HO Series
3/4	Unvalved		■						Ball	Nitrile	-40° to +250° F	200 psi	1163 Series
Mold Coolant													
1/4 to 1/2	Valved/Unvalved		■						Ball	Silicone	-20° to +400° F	200 psi	Moldmate
Miniature													
1/8	Poppet		■						Ball	Fluorocarbon	-15° to +400° F	250 psi	Rectus 21 DSO Series

Materials: A - Aluminum B - Brass S - Steel S3 - 303 Stainless S6 - 316 Stainless HP - High Pressure Stainless Steel TP - Thermoplastic

*Seal Material Options

Seal Code	Seal Material	Optional for the Following Series
W	Ethylene Propylene	60, 6600, 4000, 4200, 6100, 5000, 8200, 9200, ST, CPI
Y	Fluorocarbon	60, 6600, 4000, 4200, 6100, 5000, 8200, 9200, ST, Moldmate
Z	Neoprene	60, 6600, 4000, 4200, 6100, 5000, 8200, 9200, ST, CPI
E5	Ethylene Propylene	SM, HP, NS, FF, FEM, FH, FS, HO, CPI
E4	Fluorocarbon	SM, HP, NS, FF, FEM, FH, HO
E12	Neoprene	SM, HP, NS, FF, FEM, FH, FS, HO, CPI
E35	Perfluoro elastomer	SM, HP, NS, FF, FEM, FH, FS, CPI (Contact QCD)
E	Ethylene Propylene	H, EA, 71, 75, CPI
V	Fluorocarbon	H, EA, 71, 75

To select proper seal materials, see Fluid Compatibility Chart or contact QCD. Contact QCD for additional seal material options.

Hydraulic Quick Couplings

General Purpose

60 Series ISO 7241, Series B

Manual Sleeve, Poppet Valve



60 Series double shut-off couplings are versatile for use across a spectrum of hydraulic applications where fluid lines require connection and disconnection. Couplers and nipples are available in a wide range of sizes and materials.

Features:

- Accepts ISO 7241-1, Series B compliant nipples
- Poppet valves along with a metal to metal valve stop maintains valve alignment and prevents flow checking
- Steel, brass, and stainless steel material options
- Brass couplers have double O-rings and stainless steel locking balls
- Steel coupler sleeve and steel nipple body are hardened to be wear resistant
- Standard end configurations include female pipe and straight thread ORB
- Optional Sleeve-Lok and alternative seal materials available

Applications include:

- Industrial hydraulic lines
- Food and chemical processing
- Water and coolant lines
- Mobile equipment
- May be used with some gases



General Purpose Specification

Industry Standard: Parker 60 Series couplings comply with ISO 7241 Series B Standard.

ANSI/ISO Pressure Rating: Dynamic applications with normal to moderate hydraulic shocks such as general industrial equipment, hydraulic presses, agricultural equipment, etc. Impulse tested at a multiple (125% to 133%) of rated pressure.

Low Cycle, Non-pulsating Pressure Rating: Applications with lower cycle life and no severe cyclic pressure fluctuations, essentially steady pressure during an operating cycle. Typical applications include hydraulic jacks, mine roof support systems, and high pressure fluid transfer (pumping water or slurry in oil wells). Minor pump ripple is considered non-pulsating. Impulse tested at rated pressure.

Body Size	1/8	1/4	3/8	1/2	3/4	1	1 1/2	2 1/2	1/8	1/4	3/8	1/2	3/4	1	1 1/2	2 1/2
Rated Pressure (psi)									Rated Pressure (psi)							
Brass	1000	1000	1000	1000	1000	1000	800	800	3000	3700	2700	3500	2200	1500	1500	1200
Stainless steel	2000	2000	1500	1500	1500	1000	1000	1000	5000	5000	5000	5000	3000	3000	1500	1500
Steel	5000	5000	4000	4000	2500	2000	1000	1000	5000	5000	4000	4000	2500	2000	1500	1500
Steel w/ HD nipple	N/A	5000	4000	4000	3000	3000	N/A	N/A	5000	5000	4000	4000	3000	3000	N/A	N/A

Seal Temperature Range: **Nitrile:** -40°F to +250°F (Standard seal for Brass, Steel, & 303 Stainless Steel couplings).

Fluorocarbon: -15°F to +400°F (Standard seal for 316 Stainless Steel couplings).

Other Seal materials: Contact the Division for availability.

Vacuum Data: 27.4 inches Hg (-0.9 Bar) both connected and disconnected.

(1-1/2" and 2-1/2" body size 60 Series couplings are not recommended for service in disconnected mode)

Body Size	1/8	1/4	3/8	1/2	3/4	1	1 1/2	2 1/2
Rated Flow (gpm)	.8	3	6	12	28	50	100	200

Hydraulic Quick Couplings

General Purpose


60 Series ISO 7241, Series B

Manual Sleeve, Poppet Valve




Performance


60 Series (1/8" & 1/4")
Test Fluid: Oil - 150 SUS




60 Series (3/8" & 1/2")
Test Fluid: Oil - 150 SUS



60 Series (3/4" & 1")
Test Fluid: Oil - 150 SUS



60 Series (1-1/2" & 2-1/2")
Test Fluid: Oil - 200 SUS



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -VA	Valve actuator (Nipples)	H3-63-VA
suffix -SL	Sleeve-Lok (Couplers)	H3-62-SL
prefi HD	Heavy duty (Steel Nipples)	HDH3-63
suffix W	Ethylene Propylene seal material (EPR)	H3-63W
suffix Y	Fluorocarbon seal material	H3-62Y
suffix Z	Neoprene seal material	H3-63Z

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

60 Series ISO 7241, Series B

Manual Sleeve, Poppet Valve



Couplers - Brass, Steel, 303 Stainless - Female Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Part Number Type 303 Stainless**	Weight (lbs.)	Thread Size	Overall Length (in.)	Wrench Flats	Largest Diameter
1/8	BH1-60	0.16	H1-62	0.16	SH1-62	0.16	1/8-27 NPTF	1.90	0.68	0.96
1/8	-	-	H1-62-T4	0.18	SH1-62-T4	0.10	7/16-20 ORB	2.06	0.68	0.96
1/4	BH2-60	0.32	H2-62	0.30	SH2-62	0.30	1/4-18 NPTF	2.26	0.81	1.14
1/4	-	-	H2-62-T6	0.31	SH2-62-T6	0.31	9/16-18 ORB	2.41	0.81	1.14
3/8	BH3-60	0.43	H3-62	0.40	SH3-62	0.40	3/8-18 NPTF	2.49	0.88	1.40
3/8	-	-	H3-62-T8	0.51	SH3-62-T8	0.51	3/4-16 ORB	2.75	1.00	1.40
1/2	BH4-60	0.80	H4-62	0.73	SH4-62	0.75	1/2-14 NPTF	2.87	1.12	1.77
1/2	-	-	H4-62-T10	0.78	SH4-62-T10	0.75	7/8-14 ORB	3.05	1.12	1.77
3/4	BH6-60	1.31	H6-62	1.30	SH6-62	1.31	3/4-14 NPTF	3.56	1.31	2.14
3/4	-	-	H6-62-T12	1.39	SH6-62-T12	1.34	1-1/16 - 12 ORB	3.56	1.31	2.14
1	BH8-60	1.95	H8-62	1.95	SH8-62	1.95	1 - 11 1/2 NPTF	4.18	1.62	2.52
1	-	-	H8-62-T16	1.95	SH8-62-T16	1.95	1-5/16 - 12 ORB	4.18	1.62	2.52

Couplers - Brass, Steel, 303 Stainless - Female Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Part Number Type 303 Stainless**	Weight (lbs.)	Thread Size	Overall Length (in.)	Wrench Flats	Largest Diameter
1-1/2	BH12-60L	4.58	H12-62L	4.70	SH12-62L	4.68	1-1/4 - 11 1/2 NPTF	4.86	2.38*	3.00
1-1/2	BH12-60N	4.58	H12-62N	4.70	SH12-62N	4.68	1-1/2 - 11 1/2 NPTF	4.86	2.38*	3.00
1-1/2	-	4.61	H12-62-T20	4.72	SH12-62-T20	4.71	1-5/8 - 12 ORB	4.86	2.38*	3.00
1-1/2	-	4.61	H12-62-T24	4.72	SH12-62-T24	4.71	1-7/8 - 12 ORB	4.86	2.38*	3.00
2-1/2	BH2016-60	11.06	H2016-62	10.58	SH2016-62	-	2 - 11 1/2 NPTF	5.57	3.75	4.10
2-1/2	BH2020-60	11.42	H2020-62	10.91	SH2020-62	-	2 1/2 - 8 NPTF	6.04	3.75	4.10
2-1/2	BH2024-60	-	H2024-62	-	SH2024-62	-	3 - 8 NPTF	6.69	4.00	4.35

* Wrench Flat on 303 Stainless is 2.50 in.

** Prop 65 Warning does not apply to stainless steel part numbers

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

60 Series ISO 7241, Series B

Manual Sleeve, Poppet Valve



Couplers and Nipples - 316 Stainless - Female Thread



Body Size (in.)	Coupler Part No. Type 316 Stainless**	Weight (lbs.)	Thread Size	Overall Length (in.)	Wrench Flats	Largest Diameter	Nipple Part No. Type 316 Stainless**	Weight (lbs.)	Overall Length (in.)	Exposed Length**	Wrench Flats	Largest Diameter
1/8	SSH1-62Y	0.15	H1-62	1.90	0.68	0.96	SSH1-63Y	0.04	1.26	0.44	0.56	0.65
1/8	SSH1-62Y-T4	0.17	7/16-20 ORB	2.06	0.68	0.96	SSH1-63Y-T4	0.06	1.41	0.59	0.69	0.78
1/4	SSH2-62Y	0.30	1/4-18 NPT	2.26	0.81	1.14	SSH2-63Y	0.08	1.54	0.55	0.75	0.87
1/4	SSH2-62Y-T6	0.31	9/16-18 ORB	2.41	0.81	1.14	SSH2-63Y-T6	0.10	1.69	0.70	0.88	1.01
3/8	SSH3-62Y	0.40	3/8-18 NPT	2.49	0.88	1.40	SSH3-63Y	0.12	1.68	0.54	0.88	1.01
3/8	SSH3-62Y-T8	0.51	3/4-16 ORB	2.75	1.00	1.40	SSH3-63Y-T8	0.14	1.94	0.80	1.00	1.15
1/2	SSH4-62Y	0.76	1/2-14 NPT	2.87	1.12	1.77	SSH4-63Y	0.24	1.94	0.69	1.12	1.30
1/2	SSH4-62Y-T10	0.78	7/8-14 ORB	3.05	1.12	1.77	SSH4-63Y-T10	0.27	2.12	0.87	1.19	1.37
3/4	SSH6-62Y	1.33	3/4-14 NPT	3.56	1.31	2.14	SSH6-63Y	0.46	2.43	0.79	1.38	1.59
3/4	SSH6-62Y-T12	1.40	1-1/16 - 12 ORB	3.56	1.31	2.14	SSH6-63Y-T12	0.50	2.54	0.90	1.34	1.59
1	SSH8-62Y	1.95	1 - 11 1/2 NPT	4.18	1.62	2.52	SSH8-63Y	0.76	2.91	0.99	1.62	1.88
1	SSH8-62Y-T16	1.95	1-5/16 - 12 ORB	4.18	1.62	2.52	SSH8-63Y-T16	0.80	2.91	0.99	1.62	1.88
1-1/2	SSH12-62LY	4.68	1-1/4 - 11 1/2 NPT	4.86	2.38	3.00	SSH12-63LY	-	4.76	2.69	2.38	2.75
1-1/2	SSH12-62NY	4.68	1-1/2 - 11 1/2 NPT	4.86	2.38	3.00	SSH12-63NY	-	4.76	2.69	2.38	2.75
1-1/2	SSH12-62Y-T20	4.71	1-5/8 - 12 ORB	4.86	2.38	3.00	SSH12-63Y-T20	-	4.76	2.69	2.38	2.75
1-1/2	SSH12-62Y-T24	4.71	1-7/8 - 12 ORB	4.86	2.38	3.00	SSH12-63Y-T24	-	4.76	2.69	2.38	2.75
2-1/2	SSH2016-62Y	-	2 - 11 1/2 NPT	5.57	3.75	4.10	SSH2016-63Y	-	5.48	2.90	3.75	4.10
2-1/2	SSH2020-62Y	-	2 1/2 - 8 NPT	6.04	3.75	4.10	SSH2020-63Y	-	5.95	3.37	3.75	4.10
2-1/2	SSH2024-62Y	-	3 - 8 NPT	6.69	4.00	4.35	SSH2024-63Y	-	6.87	4.29	4.00	4.35

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

** Prop 65 Warning does not apply to stainless steel part numbers

Hydraulic Quick Couplings

General Purpose

60 Series ISO 7241, Series B

Manual Sleeve, Poppet Valve



Nipples - Brass, Steel, 303 Stainless - Female Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Part Number Type 303 Stainless**	Weight (lbs.)	Thread Size	Overall Length (in.)	Exposed Length*	Wrench Flats	Largest Dia
1/8	BH1-61	0.04	H1-63	0.03	SH1-63	0.03	1/8-27 NPTF	1.26	0.44	0.56	0.65
1/8	-	0.06	H1-63-T4	0.05	SH1-63-T4	-	7/16-20 ORB	1.41	0.59	0.69	0.78
1/4	BH2-61	0.09	H2-63	0.08	SH2-63	0.08	1/4-18 NPTF	1.54	0.55	0.75	0.87
1/4	-	0.11	H2-63-T6	0.10	SH2-63-T6	0.10	9/16-18 ORB	1.69	0.70	0.88	1.01
3/8	BH3-61	0.10	H3-63	0.12	SH3-63	0.12	3/8-18 NPTF	1.68	0.54	0.88	1.01
3/8	-	0.12	H3-63-T8	0.16	SH3-63-T8	0.16	3/4-16 ORB	1.94	0.80	1.00	1.15
1/2	BH4-61	0.25	H4-63	0.24	SH4-63	0.24	1/2-14 NPTF	1.94	0.69	1.12	1.30
1/2	-	0.28	H4-63-T10	0.27	SH4-63-T10	0.27	7/8-14 ORB	2.12	0.87	1.19	1.37
3/4	BH6-61	0.50	H6-63	0.46	SH6-63	0.45	3/4-14 NPTF	2.43	0.79	1.38	1.59
3/4	-	0.55	H6-63-T12	0.46	SH6-63-T12	0.50	1-1/16 - 12 ORB	2.54	0.90	1.34	1.59
1	BH8-61	0.76	H8-63	0.76	SH8-63	0.76	1 - 11 1/2 NPTF	2.91	0.99	1.62	1.88
1	-	0.80	H8-63-T16	0.80	SH8-63-T16	0.80	1-5/16 - 12 ORB	2.91	0.99	1.62	1.88

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

Nipples - Brass, Steel, 303 Stainless - Female Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Part Number Type 303 Stainless**	Weight (lbs.)	Thread Size	Overall Length (in.)	Exposed Length*	Wrench Flats	Largest Dia
1-1/2	BH12-61L	2.96	H12-63L	3.10	SH12-63L	3.06	1-1/4 - 11 1/2 NPTF	4.76	2.69	2.38†	2.75†
1-1/2	BH12-61N	2.96	H12-63N	3.10	SH12-63N	3.06	1-1/2 - 11 1/2 NPTF	4.76	2.69	2.38†	2.75†
1-1/2	-	-	H12-63-T20	3.15	SH12-63-T20	3.14	1-5/8 - 12 ORB	4.76	2.69	2.38†	2.75†
1-1/2	-	-	H12-63-T24	3.15	SH12-63-T24	3.14	1-7/8 - 12 ORB	4.76	2.69	2.38†	2.75†
2-1/2	BH2016-61	7.78	H2016-63	7.90	SH2016-63	7.92	2 - 11 1/2 NPTF	5.48	2.90	3.75	4.10
2-1/2	BH2020-61	8.12	H2020-63	8.16	SH2020-63	8.16	2-1/2 - 8 NPTF	5.95	3.37	3.75	4.10
2-1/2	BH2024-61	-	H2024-63	-	SH2024-63	-	3 - 8 NPTF	6.87	4.29	4.00	4.35

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

† Largest diameter on Brass is 2.96" across Hex Corners ‡ Hex on 303 Stainless is 2.50 in.

** Prop 65 Warning does not apply to stainless steel part numbers



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

60 Series ISO 7241, Series B

Manual Sleeve, Poppet Valve



60 Series Couplers - Replacement Parts		
Body Size	O-Rings - Nitrile	Back-Up Rings
1/8	50001-013-0010	H67A-28
1/4	50001-015-0010	H67C-28
3/8	50001-116-0010	4118007
1/2	50001-213-0010	4128002
3/4	50001-218-0010	4148001
1	50001-222-0010	4158001
1-1/2	50001-124-0010 (Valve)	-
1-1/2	50001-138-0260 (Fitting)	-
1-1/2	50001-224-0010 (Body 2 req.)	-
2-1/2	50001-133-0010 (Valve)	-
2-1/2	50001-234-0260 (Fitting)	-
2-1/2	50001-333-0010 (Body)	-

60 Series - Repair Kits				
Couplers			Nipples	
Body Size	Repair Kit Part No.	Used for Part No.	Repair Kit Part No.	Repair Kit Part No.
3/8	H67E-62K	H3-62	H67E-63K	H3-63
3/8	BH67E-60K	BH3-60	BH67E-61K	BH3-61
3/8	SH67E-62K	SH3-62	SH67E-63K	SH3-63
3/8	SSH67E-62KY	SSH3-62Y	SSH67E-63KY	SSH3-63Y
1/2	H67F-62K	H4-62	H67F-63K	H4-63
1/2	BH67F-60K	BH4-60	BH67F-61K	BH4-61
1/2	SH67F-62K	SH4-62	SH67F-63K	SH4-63
1/2	SSH67F-62KY	SSH4-62Y	SSH67F-63KY	SSH4-63Y
3/4	H67G-62K	H6-62	H67G-63K	H6-63
3/4	BH67G-60K	BH6-60	BH67G-61K	BH6-61
3/4	SH67G-62K	SH6-62	SH67G-63K	SH6-63
3/4	SSH67G-62KY	SSH6-62Y	SSH67G-63KY	SSH6-63Y
1	H67J-62K	H8-62	H67J-63K	H8-63
1	BH67J-60K	BH8-60	BH67J-61K	BH8-61
1	SH67J-62K	SH8-62	SH67J-63K	SH8-63
1	SSH67J-62KY	SSH8-62Y	SSH67J-63KY	SSH8-63Y

60 Series Dust Plugs and Caps



Body Size (in.)	Coupler Dust Plug Aluminum	Coupler Dust Plug Rubber	Nipple Dust Cap Aluminum	Nipple Dust Cap Rubber
1/8	H1-65	H1-65M	H1-66	H1-66M
1/4	H2-65	H2-65M	H2-66	H2-66M
3/8	H3-65	H3-65M	H3-66	H3-66M
1/2	H4-65	H4-65M	H4-66	H4-66M
3/4	H6-65	H6-65M	H6-66	H6-66M
1	H8-65	H8-65M	H8-66	H8-66M
1-1/2	H12-65	-	H12-66	-
2-1/2	H20P-65	-	H20P-66	-

Hydraulic Quick Couplings

General Purpose

60 Series (Steam) ISO 7241, Series B

Manual Sleeve, EP seal



60 Series Steam couplings are brass with stainless steel locking balls and ethylene propylene seals to withstand temperatures up to 400 F. 1/4 to 1 inch body sizes. 3/8 inch size couplers have a grip-ring sleeve.



Features:

- Accepts ISO 7241-1, Series B compliant nipples
- Poppet valves along with a metal to metal valve stop maintains valve alignment and prevents flow checking
- Brass couplers have double O-rings and stainless steel locking balls
- Standard end configuration is female pipe thread

Applications include:

- Steam systems
- Cleaning equipment

60 Series (Steam) Specification

Body Size	1/4 to 1
Standard Seal Material	Ethylene Propylene
Temperature Range	up to +400°

Repair Kits - Steam Coupling

Body Size	Repair Kit Part No.	Used for Part No.
3/8	H68E-67K	H3-68
3/8	H69E-67K	H3-69

60 Series (Steam) Couplers - Female Pipe Thread



H3-68 has
grip-ring sleeve

Body Size (in.)	Part Number Brass	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	BH2-60-STM	1/4-18 NPTF	2.26	1.14	0.81	0.30
3/8*	H3-68	3/8-18 NPTF	2.50	1.77	0.88	0.50
1/2	BH4-60-STM	1/2-14 NPTF	2.87	1.77	1.12	0.75
3/4	BH6-60-STM	3/4-14 NPTF	3.56	2.14	1.31	1.31
1	BH8-60-STM	1-11 1/2 NPTF	4.18	2.52	1.62	1.95

* See Photo for 3/8 inch size coupler configuration.

60 Series (Steam) Nipples - Female Pipe Thread



Body Size (in.)	Part Number Brass	Thread Size	Overall Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	BH2-61-STM	1/4 - 18 NPTF	1.54	0.65	0.87	0.75	0.08
3/8	H3-69	3/8 - 18 NPTF	1.68	0.52	1.01	0.88	0.13
1/2	BH4-61-STM	1/2 - 14 NPTF	1.94	0.69	1.30	1.12	0.24
3/4	BH6-61-STM	3/4 - 14 NPTF	2.43	0.79	1.59	1.38	0.46
1	BH8-61-STM	1 - 11 1/2 NPTF	2.91	0.99	1.88	1.62	0.76

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

Hydraulic Quick Couplings

General Purpose

6600 Series ISO 7241 Series A

Manual Sleeve, Poppet Valve



The 6600 Series are versatile for use in a wide range of hydraulic applications where fluid lines require connection and disconnection for equipment operation or maintenance.



Features:

- Accepts ISO 7241-1, Series A compliant nipples
- Poppet valves and a metal perch to maintain valve alignment and prevent flow checking
- Coupler sleeve and nipple body are hardened to be damage resistant
- Standard end configurations include female pipe and straight thread ORB
- Protective zinc plating with clear trivalent chromate finish




Applications include:

- Truck trailer connections
- Mobile applications
- Attachments

6600 Series Specification

Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
1/4	0.8	5000 psi	-40° F to +250° F	Steel	Manual Connect	Nitrile
3/8	6	4000 psi				
1/2	12	4000 psi				
3/4	28	4000 psi				
1	50	4000 psi				

Performance



6600 Series ISO 7241 Series A

Manual Sleeve, Poppet Valve



Hydraulic Quick Couplings

General Purpose

6600 Series Couplers



Body Size (in.)	Coupler Part Number	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	6601-2-4	1/8-27 NPTF	Poppet	1.85	1.08	0.88	0.27
1/4	6601-4-4	1/4-18 NPTF	Poppet	1.85	1.08	0.88	0.26
3/8	6601-6-6	3/8-18 NPTF	Poppet	2.18	1.27	1.06	0.39
3/8	6608-6-6	9/16-18 ORB	Poppet	2.18	1.27	1.06	0.38
1/2	6601-8-10	1/2-14 NPTF	Poppet	2.75	1.52	1.25	0.67
1/2	6601-12-10	3/4-14 NPTF	Poppet	2.88	1.52	1.38	0.71
1/2	6608-8-10	3/4-16 ORB	Poppet	2.74	1.52	1.25	0.67
1/2	6608-10-10	7/8-14 ORB	Poppet	2.79	1.52	1.25	0.64
1/2	6608-12-10	1 1/16-12 ORB	Poppet	3.01	1.52	1.38	0.77
3/4	6601-12-12	3/4-14 NPTF	Poppet	3.36	1.90	1.62	1.31
3/4	6608-12-12	1 1/16-12 ORB	Poppet	3.35	1.90	1.62	1.31
1	6601-16-16	1-11 1/2 NPTF	Poppet	4.11	2.14	1.88	1.93
1	6608-16-16	1 5/16-12 ORB	Poppet	4.11	2.14	1.88	1.75

6600 Series Nipples



Body Size (in.)	Nipple Part Number	Port End	Valve Type	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	6602-2-4	1/8-27 NPTF	Poppet	1.41	0.50	0.50	0.88	0.27
1/4	6602-4-4	1/4-18 NPTF	Poppet	1.41	0.58	0.58	0.88	0.26
3/8	6602-6-6	3/8-18 NPTF	Poppet	1.63	0.72	0.72	1.06	0.39
3/8	6610-6-6	9/16-18 ORB	Poppet	1.63	0.72	0.72	1.06	0.38
1/2	6602-8-10	1/2-14 NPTF	Poppet	2.08	0.78	0.78	1.25	0.67
1/2	6602-12-10	3/4-14 NPTF	Poppet	2.30	0.78	0.78	1.38	0.71
1/2	6610-8-10	3/4-16 ORB	Poppet	2.08	0.76	0.76	1.25	0.67
1/2	6610-10-10	7/8-14 ORB	Poppet	2.08	0.82	0.82	1.25	0.64
1/2	6610-12-10	1 1/16-12 ORB	Poppet	2.30	1.04	1.04	1.38	0.77
3/4	6602-12-12	3/4-14 NPTF	Poppet	2.55	1.18	1.18	1.62	1.31
3/4	6610-12-12	1 1/16-12 ORB	Poppet	2.55	1.18	1.18	1.62	1.31
1	6602-16-16	1-11 1/2 NPTF	Poppet	3.10	1.34	1.34	1.88	1.93
1	6610-16-16	1 5/16-12 ORB	Poppet	3.10	1.34	1.34	1.88	1.75

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

6600 Series ISO 7241 Series A

Manual Sleeve, Poppet Valve



6600 Series Replacement Parts

	1/4	3/8	1/2	3/4	1
O-Rings - Nitrile	50001-112-0010	50001-115-0010	50001-211-0010	50001-123-0010	50001-126-0010
Back-up Rings	4118006	4118005	50-140-4	4138001	4148002

60 Series Dust Plugs and Caps



Body Size (in.)	Dust Plug (Coupler)	Color/Material	Dust Cap (Nipple)	Weight (lbs.)
1/4	H1-65M	Black Rubber	H1-66M	0.02
3/8	TR-37	Black Rubber	TR-37	0.04
1/2	5205-4M	Black Rubber	5209-4M	0.04
3/4	6659-12M	Black Rubber	6657-12M	0.06
1	6659-16M	Black Rubber	6657-16M	0.08

Optional Materials and Features: (add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -SL	Sleeve-Lok (Couplers)	6601-6-6-SL
suffix W	Ethylene Propylene seal material (EPR)	6601-6-6W
suffix Y	Fluorocarbon seal material	6601-6-6Y
suffix Z	Neoprene seal material	6601-6-6Z

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series, original Snap-tite design couplings have been proven by years of use on hydraulic applications.

H Series is best suited for general purpose fluid applications where either single or double shut-off valving is desired. A wide range of sizes, materials and end configurations are available.


PH version couplers and nipples are valved with a connect-under-pressure feature. These steel couplers and nipples allow connection with H Series valved couplers and nipples when there is a residual pressure on the PH coupler/nipple side. It is recommended that only one half of the connection (coupler or nipple) be PH version, not both.

Features:


- Sizes 1/4" - 4"
- Available in steel, brass, aluminum and 316 stainless steel
- Standard seal material is nitrile with other options available
- Optional sleeve lock helps to prevent accidental disconnection
- Double-shut-off version has low pressure drop
- Manually operated sleeve provides secure connection
- Designed to MIL-C 51234
- Double shut-off coupling: Valve coupler and valve nipple
- Single shut-off coupling: Valve coupler and plain nipple

Applications include:

- Industrial hydraulic lines
- Water and coolant lines
- Mobile equipment



H Series Version
Poppet Valve



PH Series Version
Connect Under Pressure Poppet Valve

H & PH Series Working Pressures (psi)

Valved on both coupler and nipple (Double Shut-off) | Valved on one half and Unvalved/ Plain on other half (Single Shut-off)

Body Size	1/4	3/8	1/2	3/4	1	1-1/4	1-1/2	2	2-1/2	3	4
Steel	6500	4500	4000	3500	2000	1750	1500	1500	1000	750	500
Aluminum	2250	2250	1750	1750	1500	375	375	300	300	200	150
Brass	2250	2250	2000	2000	1750	350	350	400	400	200	150
Stainless Steel	5000	4000	3750	2000	2000	1500	1500	500	400	400	300
Unvalved/Plain on both coupler and nipple (Straight Through)											
Steel	11000	11000	11000	9000	6000	5000	5000	4000	1000	750	500
Aluminum	4000	4000	4000	3500	3000	1000	1000	750	300	200	150
Brass	4000	4000	4000	3500	3000	1000	1000	750	300	200	150
Stainless Steel	10000	8000	8000	7000	4000	3000	3000	1000	400	400	300

NOTE: Pressure ratings were established under static pressure conditions. Therefore, pressure ratings for any given flow, pressure surge and/or vibration may vary from these ratings. Burst pressures listed were taken at the point at which failure rendered the quick disconnect inoperative. (Proof pressure equals 1-1/2 times the working pressure; burst pressure equals 2 times working pressure.)

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design


Manual Sleeve, Valved or Unvalved



Performance


PH Series

Valved and Valved (Double Shut-off)




H Series


Valved and Valved (Double Shut-off)



Repair Kits



Valved and Plain (Single Shut-off)



Repair kits include valve spring, valve stop and valve. O-ring installed on 3/8" to 1". 1/4" unit is non-field repairable.

Note: Not all configurations are standard product offering. Contact QCD for price and delivery.

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved




Valve Options		
	H Series Hydraulic Coupler/Nipple	PH Series Hydraulic Coupler/Nipple
Valve Styles	• Poppet Valve • Unvalved/Plain	• Connect-Under-Pressure Poppet Valve
Connection Types	• Double Shut-off • Single Shut-off • Straight Through/Unvalved	• Double Shut-off (connects with valved H Series Coupler or Nipple)
Body Sizes	1/8" - 4"	3/8" - 1"
Materials	• Steel • 316 Stainless Steel • Aluminum • Brass	• Steel

Replacement Coupler Interface Seals		
Body Size	Nitrile	Fluorocarbon
1/4	H4-56-9	H4-56-9V
3/8	H6-56-9	H6-56-9V
1/2	H8-56-9	H8-56-9V
3/4	H12-56-9	H12-56-9V
1	H16-56-9	H16-56-9V
1-1/4	H20-56-9	H20-56-9V

Replacement Valve Seals			
Body Size	Nitrile	Fluorocarbon	Ethylene Propylene
1-1/4	H20-55A	H20-55V	H20-55E
1-1/2	H24-55A	H24-55V	H24-55E
2	H32-55A	H32-55V	H32-55E

Ordering Guide



Note: Not all configurations are standard product offering. Contact QCD for price and delivery.

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series Couplers (Aluminum, Brass, Steel) - Female Thread



Body Size (in.)	Part Number Aluminum	Part Number Brass	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	-	-	VHC4-2F	Valved	1/8-27 NPTF	1.65	1.00	0.88
1/4	APHC4-4F	BPHC4-4F	PHC4-4F	Non-Valved	1/4-18 NPTF	1.34	1.02	0.88
1/4	AVHC4-4F	BVHC4-4F	VHC4-4F	Valved	1/4-18 NPTF	1.65	1.19	1.00
1/4	-	-	VHC4-4EF	Valved	7/16-20 UNF	1.80	1.02	0.88
3/8	APHC6-6F	BPHC6-6F	PHC6-6F	Non-Valved	3/8-18 NPTF	1.50	1.19	1.00
3/8	AVHC6-6F	BVHC6-6F	VHC6-6F	Valved	3/8-18 NPTF	1.90	1.19	1.00
3/8	-	-	VHC6-6EF	Valved	9/16-18 UNF	2.20	1.19	1.00
1/2	-	BPHC8-8F	PHC8-8F	Non-Valved	1/2-14 NPTF	1.62	1.39	1.19
1/2	AVHC8-8F	BVHC8-8F	VHC8-8F	Valved	1/2-14 NPTF	2.09	1.39	1.25
1/2	-	-	VHC8-8EF	Valved	3/4-16 UNF	2.19	1.39	1.25
3/4	-	BPHC12-12F	PHC12-12F	Non-Valved	3/4-14 NPTF	1.91	1.73	1.50
3/4	-	BVHC12-12F	VHC12-12F	Valved	3/4-14 NPTF	2.42	1.73	1.50
3/4	-	-	VHC12-12EFV	Valved	1-1/16 - 12 UNF	2.92	1.73	1.50
1	-	BPHC16-16F	PHC16-16F	Non-Valved	1 - 11-1/2 NPTF	2.07	2.17	1.88
1	-	BVHC16-16F	VHC16-16F	Valved	1 - 11-1/2 NPTF	2.67	2.17	1.88
1	-	-	VHC16-16EF	Valved	1-5/16 - 12 UNF	2.94	2.17	1.88
1-1/4	-	BPHC20-20F	PHC20-20F	Non-Valved	1-1/4 - 11-1/2 NPT	2.28	2.31	2.00
1-1/4	-	BVHC20-20F	VHC20-20F	Valved	1-1/4 - 11-1/2 NPT	3.54	2.31	2.00
1-1/2	-	BPHC24-24F	PHC24-24F	Non-Valved	1-1/2 - 11-1/2 NPT	2.57	2.89	2.50
1-1/2	-	BVHC24-24F	VHC24-24F	Valved	1-1/2 - 11-1/2 NPT	3.27	3.18	2.75
2	-	BPHC32-32F	PHC32-32F	Non-Valved	2 - 11-1/2 NPT	2.48	3.75	3.25
2	-	BVHC32-32F	VHC32-32F	Valved	2 - 11-1/2 NPT	3.92	4.33	3.75

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



Hydraulic Quick Couplings

General Purpose

H Series Couplers (316 Stainless Steel) - Female Thread



Body Size (in.)	Part Number Stainless Steel**	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	SVHC4-2F	Valved	1/8-27 NPSF*	1.65	1.00	0.88
1/4	SPHC4-4F	Non-Valved	1/4-18 NPSF*	1.34	1.02	0.88
1/4	SVHC4-4F	Valved	1/4-18 NPSF*	1.65	1.19	1.00
3/8	SPHC6-6F	Non-Valved	3/8-18 NPSF*	1.50	1.19	1.00
3/8	SVHC6-6F	Valved	3/8-18 NPSF*	1.90	1.19	1.00
1/2	SPHC8-8F	Non-Valved	1/2-14 NPSF*	1.62	1.39	1.19
1/2	SVHC8-8F	Valved	1/2-14 NPSF*	2.09	1.39	2.09
3/4	SPHC12-12F	Non-Valved	3/4-14 NPSF*	1.91	1.73	1.50
3/4	SVHC12-12F	Valved	3/4-14 NPSF*	2.42	1.73	1.50
1	SPHC16-16F	Non-Valved	1 - 11-1/2 NPSF*	2.07	2.17	1.88
1	SVHC16-16F	Valved	1 - 11-1/2 NPSF*	2.67	2.17	1.88
1-1/4	SPHC20-20F	Non-Valved	1-1/4 - 11-1/2 NPT	2.28	2.31	2.00
1-1/4	SVHC20-20F	Valved	1-1/4 - 11-1/2 NPT	3.54	2.31	2.00
1-1/2	SPHC24-24F	Non-Valved	1-1/4 - 11-1/2 NPT	2.57	2.89	2.50
1-1/2	SVHC24-24F	Valved	1-1/2 - 11-1/2 NPT	3.27	3.18	2.75
2	SPHC32-32F	Non-Valved	2 - 11-1/2 NPT	2.48	3.75	3.25
2	SVHC32-32F	Valved	2 - 11-1/2 NPT	3.92	4.33	3.75

*NPSF thread may be substituted with equivalent NPT thread

** Prop 65 Warning does not apply to stainless steel part numbers

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series Couplers (Aluminum, Brass, Steel) - Male Thread



Body Size (in.)	Part Number Aluminum	Part Number Brass	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	-	-	VHC4-2M	Valved	1/8-27 NPT	1.90	1.00	0.88
1/4	AVHC4-4M	BVHC4-4M	VHC4-4M	Valved	1/4-18 NPT	2.09	1.02	0.88
3/8	AVHC6-6M	-	VHC6-6M	Valved	3/8-18 NPT	2.19	1.19	1.00
3/8	-	BVHC6-6M	-	Valved	3/8-18 NPT	2.19	1.19	1.00
1/2	-	BVHC8-8M	-	Valved	1/2-14 NPT	2.57	1.39	1.25
1/2	-	-	VHC8-8M	Valved	1/2-14 NPT	2.46	1.39	1.25
3/4	-	BVHC12-12M	VHC12-12M	Valved	3/4-14 NPT	2.88	1.73	1.50
1	-	BVHC16-16M	VHC16-16M	Valved	1-11-1/2 NPT	3.21	2.17	1.88
2	-	-	VHC32-32M	Valved	2-11-1/2 NPT	4.54	4.33	3.75

H Series Couplers (316 Stainless Steel) - Male Thread



Body Size (in.)	Part Number Stainless Steel*	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	SVHC4-4M	Valved	1/4-18 NPT	2.09	1.02	0.88
3/8	SVHC6-6M	Valved	3/8-18 NPT	2.19	1.19	1.00
1/2	SVHC8-8M	Valved	1/2-14 NPT	2.57	1.39	1.25
3/4	SVHC12-12M	Valved	3/4-14 NPT	2.88	1.73	1.50
1	SVHC16-16M	Valved	1 - 11-1/2 NPT	3.21	2.17	1.88

* Prop 65 Warning does not apply to stainless steel part numbers

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series Couplers (Steel) - Male SAE 37 Degree Flare



Body Size (in.)	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	VHC4-4EM	Valved	7/16-20 UNF	2.80	1.02	0.88
3/8	VHC6-6EM	Valved	9/16-18 UNF	2.24	1.19	1.00
1/2	VHC8-8EM	Valved	3/4-16 UNF	2.46	1.39	1.25
3/4	VHC12-12EM	Valved	1-1/6 - 12 UNF	3.05	1.73	1.50

PH Series Connect-Under-Pressure Couplers (Steel) - Female Thread



Body Size (in.)	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
3/8	VPHC6-6F	Valved	3/8-18 NPTF	1.90	1.19	1.00
1/2	VPHC8-8F	Valved	1/2-14 NPTF	2.09	1.39	1.19
3/4	VPHC12-12EF	Valved	1-1/16 - 12 UNF	2.92	1.73	1.50
3/4	VPHC12-12F	Valved	3/4-14 NPTF	2.42	1.73	1.50



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series Nipples (Aluminum, Brass, Steel) - Female Thread



Body Size (in.)	Part Number Aluminum	Part Number Brass	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	-	BPHN4-2F	PHN4-2F	Non-Valved	1/8-27 NPTF	1.11	0.62	0.56
1/4	-	-	VHN4-2F	Valved	1/8-27 NPTF	1.59	1.00	0.88
1/4	APHN4-4F	BPHN4-4F	-	Non-Valved	1/4-18 NPTF	1.32	0.73	0.88
1/4	AVHN4-4F	BVHN4-4F	-	Valved	1/4-18 NPTF	1.59	1.02	0.88
1/4	-	-	PHN4-4F	Non-Valved	1/4-18 NPTF	1.32	0.73	0.63
1/4	-	-	VHN4-4F	Valved	1/4-18 NPTF	1.65	1.19	1.00
3/8	APHN6-6F	BPHN6-6F	-	Non-Valved	3/8-18 NPTF	1.52	0.94	1.00
3/8	-	-	PHN6-6F	Non-Valved	3/8-18 NPTF	1.52	0.94	0.81
3/8	AVHN6-6F	BVHN6-6F	VHN6-6F	Valved	3/8-18 NPTF	1.84	1.19	1.00
1/2	AVHN8-8F	-	-	Valved	1/2-14 NPTF	1.98	1.19	1.00
1/2	-	BPHN8-8F	PHN8-8F	Non-Valved	1/2-14 NPTF	1.72	1.15	1.00
1/2	-	BVHN8-8F	VHN8-8F	Valved	1/2-14 NPTF	1.98	1.39	1.25
1/2	-	-	VHN8-8EF	Valved	3/4-16 UNF	2.08	1.39	1.25
3/4	-	BPHN12-12F	PHN12-12F	Non-Valved	3/4-14 NPTF	1.92	1.37	1.19
3/4	-	BVHN12-12F	VHN12-12F	Valved	3/4-14 NPTF	2.29	1.73	1.50
3/4	-	-	VHN12-12EF	Valved	1-1/16 - 12 UNF	2.79	1.73	1.50
1	-	BPHN16-16F	PHN16-16F	Non-Valved	1 - 11-1/2 NPTF	2.10	1.73	1.50
1	-	BVHN16-16F	VHN16-16F	Valved	1 - 11-1/2 NPTF	2.55	2.17	1.88
1	-	-	VHN16-16EF	Valved	1-5/16 - 12 UNF	2.82	2.17	1.88
1-1/4	-	BPHN20-20F	PHN20-20F	Non-Valved	1-1/4 - 11-1/2 NPTF	2.22	2.17	1.88
1-1/4	-	BVHN20-20F	VHN20-20F	Valved	1-1/4 - 11-1/2 NPTF	3.41	2.31	2.00
1-1/2	-	BPHN24-24F	PHN24-24F	Non-Valved	1-1/2 - 11-1/2 NPTF	2.44	2.46	2.13
1-1/2	-	BVHN24-24F	VHN24-24F	Valved	1-1/2 - 11-1/2 NPTF	3.11	3.18	2.75
2	-	BPHN32-32F	PHN32-32F	Non-Valved	2 - 11-1/2 NPTF	2.60	3.18	2.75
2	-	BVHN32-32F	VHN32-32F	Valved	2 - 11-1/2 NPTF	3.72	4.33	3.75

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series Nipples (316 Stainless Steel) - Female Thread



Body Size (in.)	Part Number Stainless Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	SPHN4-2F	Non-Valved	1/8-27 NPSF*	1.11	0.62	0.56
1/4	SVHN4-2F	Valved	1/8-27 NPSF*	1.59	1.00	0.56
1/4	SPHN4-4F	Non-Valved	1/4-18 NPSF*	1.32	0.73	0.63
1/4	SVHN4-4F	Valved	1/4-18 NPSF*	1.59	1.02	0.88
3/8	SPHN6-6F	Non-Valved	3/8-18 NPSF*	1.52	0.94	0.81
3/8	SVHN6-6F	Valved	3/8-18 NPSF*	1.84	1.19	1.00
1/2	SPHN8-8F	Non-Valved	1/2-14 NPSF*	1.72	1.15	2.00
1/2	SVHN8-8F	Valved	1/2-14 NPSF*	1.98	1.39	1.25
3/4	SPHN12-12F	Non-Valved	3/4-14 NPSF*	1.92	1.37	1.19
3/4	SVHN12-12F	Valved	3/4-14 NPSF*	2.29	1.73	1.50
1	SPHN16-16F	Non-Valved	1 - 11-1/2 NPSF*	2.10	1.73	1.50
1	SVHN16-16F	Valved	1 - 11-1/2 NPSF*	2.55	2.17	1.88
1-1/4	SPHN20-20F	Non-Valved	1-1/4 - 11-1/2 NPTF	2.22	2.17	1.88
1-1/4	SVHN20-20F	Valved	1-1/4 - 11-1/2 NPTF	3.41	2.31	1.88
1-1/2	SPHN24-24F	Non-Valved	1-1/2 - 11-1/2 NPTF	2.44	2.46	2.13
1-1/2	SVHN24-24F	Valved	1-1/2 - 11-1/2 NPTF	3.11	3.18	3.75
2	SPHN32-32F	Non-Valved	2 - 11-1/2 NPTF	2.60	3.18	2.75
2	SVHN32-32F	Valved	2 - 11-1/2 NPTF	3.72	4.33	3.75

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



H Series Nipples (Aluminum, Brass, Steel) - Male Thread



Body Size (in.)	Part Number Aluminum	Part Number Brass	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	-	BPHN4-2M	-	Non-Valved	1/8-27 NPT	1.22	0.64	0.56
1/4	-	-	PHN4-2M	Non-Valved	1/8-27 NPT	1.11	0.62	0.56
1/4	-	-	VHN4-2M	Valved	1/8-27 NPT	1.85	1.00	0.88
1/4	APHN4-4M	BPHN4-4M	PHN4-4M	Non-Valved	1/4-18 NPT	0.78	0.65	0.56
1/4	AVHN4-4M	BVHN4-4M	VHN4-4M	Valved	1/4-18 NPT	2.03	1.02	0.88
1/4	-	BPHN6-6M	PHN6-6M	Non-Valved	3/8-18 NPT	0.98	0.80	0.69
3/8	AVHN6-6M	BVHN6-6M	VHN6-6M	Valved	3/8-18 NPT	2.13	1.19	1.00
3/8	-	BPHN8-8M	PHN8-8M	Non-Valved	1/2-14 NPT	1.01	1.02	0.88
3/8	-	BVHN8-8M	VHN8-8M	Valved	1/2-14 NPT	2.46	1.39	1.25
1/2	-	BPHN12-12M	PHN12-12M	Non-Valved	3/4-14 NPT	1.14	1.22	1.06
1/2	-	BVHN12-12M	VHN12-12M	Valved	3/4-14 NPT	2.75	1.73	1.50
1/2	-	BPHN16-16M	-	Non-Valved	1-11-1/2 NPT	1.16	1.59	1.38
1/2	-	-	PHN16-16M	Non-Valved	1-11-1/2 NPT	1.16	1.73	1.88
3/4	-	BVHN16-16M	VHN16-16M	Valved	1-11-1/2 NPT	3.09	2.17	1.88
3/4	-	-	VHN20-20M	Valved	1-1/4 - 11-1/2 NPT	3.46	2.31	2.00
3/4	-	-	PHN32-32M	Non-Valved	2 - 11-1/2 NPT	2.03	2.89	2.50

H Series Nipples (316 Stainless Steel) - Male Thread



Body Size (in.)	Part Number Stainless Steel*	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	SPHN4-2M	Non-Valved	1/8-27 NPT	1.22	0.64	0.56
1/4	SPHN4-4M	Non-Valved	1/4-18 NPT	0.78	0.65	0.56
1/4	SVHN4-4M	Valved	1/4-18 NPT	2.03	1.02	0.88
3/8	SPHN6-6M	Non-Valved	3/8-18 NPT	0.98	0.80	0.69
3/8	SVHN6-6M	Valved	3/8-18 NPT	2.13	1.19	1.00
1/2	SPHN8-8M	Non-Valved	1/2-14 NPT	1.01	1.02	0.88
1/2	SVHN8-8M	Valved	1/2-14 NPT	2.46	1.39	1.25
3/4	SVHN12-12M	Valved	3/4-14 NPT	2.75	1.73	1.50
1	SVHN16-16M	Valved	1 - 11-1/2 NPT	3.09	2.17	1.80
1-1/4	SVHN20-20M	Valved	1-1/4 - 11-1/2 NPT	3.46	2.31	2.00

* Prop 65 Warning does not apply to stainless steel part numbers

H & PH Series Snap-tite Design

Manual Sleeve, Valved or Unvalved



Hydraulic Quick Couplings

General Purpose

H Series Nipples (Steel) - Male SAE 37 Degree Flare



Body Size (in.)	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	VHN4-4EM	Valved	7/16-20 UNF	2.02	1.02	0.88
3/8	VHN6-6EM	Valved	9/16-18 UNF	2.24	1.19	1.00
1/2	VHN8-8EM	Valved	3/4-16 UNF	2.35	1.39	1.25
3/4	VHN12-12EM	Valved	1-1/6 - 12 UNF	2.92	1.73	1.50

PH Series Connect-Under-Pressure Nipples (Steel)



Body Size (in.)	Part Number Steel	Valved or Non-Valved (Plain)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/2	VPHN8-8F	Valved	1/2-14 NPTF (Female)	1.98	1.39	1.19
1/2	VPHN8-8EM	Valved	3/4-16 UNF (Male)	2.35	1.39	1.19

H Series Dust Plugs and Caps



Body Size (in.)	Coupler Dust Plug Plastic	Coupler Dust Plug Aluminum	Nipple Dust Cap Plastic	Nipple Dust Cap Aluminum	Nipple Pressure Cap
1/4	PDP-4	AMPH-4	PDC-4	ADCH-4	MCH-4
3/8	PDP-6	AMPH-6	PDC-6	ADCH-6	MCH-6
1/2	PDP-8	AMPH-8	PDC-8	ADCH-8	MCH-8
3/4	PDP-12	AMPH-12	PDC-12	ADCH-12	MCH-12
1	PDP-16	AMPH-16	PDC-16	ADCH-16	MCH-16
1-1/4	-	AMPH-20	-	ADCH-20	MCH-20
1-1/2	-	AMPH-24	-	ADCH-24	MCH-24
2	-	AMPH-32	-	ADCH-32	MCH-32
2-1/2	-	AMPH-40	-	ADCH-40	MCH-40
3	-	AMPH-48	-	ADCH-48	MCH-48

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

EA Series Vacuum Couplings

Vacuum to Medium Pressure



EA Series couplings are designed specifically for vacuum and medium pressure service, providing a dependable means for speeding fluid line changeover in autoclave applications. Single and double shut off combination



Features:

- Vacuum capability
- Available in a variety of materials
- Wide range of sizes
- Nitrile is standard seal material, other options available
- Double shut-off coupling: Valve coupler and valve nipple
- Single shut-off coupling: Valve coupler and plain nipple

Applications include:

- Aircraft fabrication
- Plastic molding
- Horizontal boring and dewatering

EA Series Specification

Body Size	Force to Connect (Double Shut Off)		Spillage on Disconnect (Double Shut Off)	
	Internal Pressure (psi)	Force to Connect (lbs)	With 10 psi Internal Pressure (cc or ml)	With 50 psi Pressure (cc or ml)
1/4	200	50	1.2	1.5
3/8	200	60	1.4	2.5
1/2	200	95	4.2	4.6
3/4	100	95	10.5	11.6

EA Series Specification

Body Size	Steel		316 Stainless Steel		Brass	
	Maximum Working (psi)	Minimum Burst (psi)	Maximum Working (psi)	Minimum Burst (psi)	Maximum Working (psi)	Minimum Burst (psi)
1/4	3000	6000	3000	6000	1500	3000
3/8	3000	6000	3000	6000	1500	3000
1/2	3000	6000	3000	6000	1500	3000
3/4	2000	4000	2000	4000	1500	3000

Pressure ratings were established under static pressure conditions. Therefore, pressure ratings for any given flow, pressure surge and/or vibration may vary from those ratings.

Vacuum Capability at Standard Barometric Conditions

	1/4		3/8		1/2		3/4	
	in.hg	atm	in.hg	atm	in.hg	atm	in.hg	atm
Connected	29.7	0.99	29.7	0.99	29.7	0.99	29.7	0.99
Coupler or Nipple Alone (disconnected)	29.7	0.99	29.7	0.99	29.7	0.99	29.7	0.99

Hydraulic Quick Couplings

General Purpose


EA Series Vacuum Couplings

Vacuum to Medium Pressure




Performance

**EA Series Valved & Valved
(Double Shut-off)**




**EA Series Valved & Plain
(Single Shut-off)**



EA Series Repair Kits and Replacement Parts

Body Size	Part Number	Description	Seal Material
1/2	VEAC8-SPK	Coupler Valve Repair Kit	Nitrile
1/2	VEAN8-SPK	Nipple Valve Repair Kit	Nitrile
1/4	EA4-58AS	Coupler Interface Seal	Afla
1/2	EA8-58V	Coupler Interface Seal	Fluorocarbon
3/4	EA12-58A	Coupler Interface Seal	Nitrile

Repair Kits



Optional Seal Materials for Couplers and Valved Nipples
(add code to part number)

Code	Description	Part Number Example
suffix V	Fluorocarbon seal material	VEAN4-4 FV
suffix E	Ethylene Propylene seal material (EPR)	VEAC6-6 ME
suffix AS	Aflas seal material	VEAC6-6 FAS

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Hydraulic Quick Couplings

General Purpose

EA Series Vacuum Couplings

Vacuum to Medium Pressure



EA Series Couplers (Brass, Steel, 316 Stainless Steel) - Female Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Port End	Part Number 316 Stainless Steel**	Port End*	Valved or Non-Valved (Plain)	Length (in.)	Largest Dia	Wrench Flats
1/4	BPEAC4-4F	PEAC4-4F	1/4-18 NPTF	SPEAC4-4F	1/4-18 NPSF	Non-Valved	1.33	1.13	0.88
1/4	BVEAC4-4F	VEAC4-4F	1/4-18 NPTF	SVEAC4-4F	1/4-18 NPSF	Valved	1.61	1.13	0.88
3/8	BPEAC6-6F	PEAC6-6F	3/8-18 NPTF	-	-	Non-Valved	1.58	1.31	1.00
3/8	BVEAC6-6F	VEAC6-6F	3/8-18 NPTF	-	-	Valved	1.86	1.31	1.00
1/2	BPEAC8-8F	PEAC8-8F	1/2-14 NPTF	-	-	Non-Valved	1.70	1.44	1.19
1/2	BVEAC8-8F	VEAC8-8F	1/2-14 NPTF	SVEAC8-8F	1/2-14 NPSF	Valved	2.09	1.44	1.19
3/4	BPEAC12-12F	-	3/4-14 NPTF	SPEAC12-12F	3/4-14 NPSF	Non-Valved	2.41	1.88	1.50
3/4	BVEAC12-12F	VEAC12-12F	3/4-14 NPTF	SVEAC12-12F	3/4-14 NPSF	Valved	2.91	1.88	1.50

EA Series Couplers (Brass, Steel, 316 Stainless Steel) - Male Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Port End	Part Number 316 Stainless Steel**	Port End*	Valved or Non-Valved (Plain)	Length (in.)	Largest Dia	Wrench Flats
1/4	-	PEAC4-4M	1/4-18 NPTF	SPEAC4-4M	1/4-18 NPSF	Non-Valved	1.48	1.13	0.88
1/4	-	VEAC4-4M	1/4-18 NPTF	-	1/4-18 NPSF	Valved	2.05	1.13	0.88
3/8	BVEAC6-6M	VEAC6-6M	3/8-18 NPTF	-	-	Valved	2.15	1.31	1.00
1/2	BVEAC8-8M	VEAC8-8M	1/2-14 NPTF	SVEAC8-8M	1/2-14 NPSF	Valved	2.46	1.44	1.19
3/4	BVEAC12-12M	VEAC12-12M	3/4-14 NPTF	-	-	Valved	2.87	1.88	1.50

*May be substituted with NPT threads

Contact QCD for additional sizes, materials and end configurations.

** Prop 65 Warning does not apply to stainless steel part numbers

WARNING

This product can expose you to chemicals including Lead and DEHP, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov (This disclaimer also applies to the following page.)

EA Series Vacuum Couplings

Vacuum to Medium Pressure

Hydraulic Quick Couplings

General Purpose



EA Series Couplers (Brass, Steel, 316 Stainless Steel) - Female Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Port End	Part Number 316 Stainless Steel**	Port End*	Valved or Non-Valved (Plain)	Length (in.)	Largest Dia	Wrench Flats
1/4	-	-	-	SVEAN4-2F	1/8-27 NPSF	Valved	1.61	1.00	0.88
1/4	BPEAN4-4F	PEAN4-4F	1/4-18 NPTF	SPEAN4-4F	1/4-18 NPSF	Non-Valved	1.33	0.73	0.62
1/4	-	VEAN4-4F	1/4-18 NPTF	SVEAN4-4F	1/4-18 NPSF	Valved	1.61	1.00	0.88
3/8	BPEAN6-6F	PEAN6-6F	3/8-18 NPTF	-	-	Non-Valved	1.58	0.94	0.81
3/8	BVEAN6-6F	VEAN6-6F	3/8-18 NPTF	-	-	Valved	1.86	1.15	1.00
1/2	BPEAN8-8F	PEAN8-8F	1/2-14 NPTF	-	-	Non-Valved	1.70	1.15	1.00
1/2	BVEAN8-8F	VEAN8-8F	1/2-14 NPTF	SVEAN8-8F	1/2-14NPSF	Valved	2.09	1.31	1.19
3/4	BPEAN12-12F	-	3/4-14 NPTF	SPEAN12-12F	3/4-14 NPSF	Non-Valved	2.05	1.37	1.19
3/4	BVEAN12-12F	VEAN12-12F	3/4-14 NPTF	SVEAN12-12F	3/4-14 NPSF	Valved	2.29	1.73	1.50

EA Series Nipples (Brass, Steel, 316 Stainless Steel) - Male Thread



Body Size (in.)	Part Number Brass	Part Number Steel	Port End	Part Number 316 Stainless Steel**	Port End*	Valved or Non-Valved (Plain)	Length (in.)	Largest Dia	Wrench Flats
1/4	-	PEAN4-4M	1/4-18 NPTF	SPEAN4-4M	1/4-18 NPSF	Non-Valved	1.43	0.65	0.56
1/4	-	VEAN4-4M	1/4-18 NPTF	SVEAN4-4M	1/4-18 NPSF	Valved	2.21	1.02	0.88
3/8	BVEAN6-6M	VEAN6-6M	3/8-18 NPTF	-	-	Valved	2.15	1.15	1.00
1/2	BVEAN8-8M	VEAN8-8M	1/2-14 NPTF	SVEAN8-8M	1/2-14 NPSF	Valved	2.46	1.31	1.19
3/4	BVEAN12-12M	VEAN12-12M	3/4-14 NPTF	-	-	Valved	2.75	1.65	1.50

*May be substituted with NPT threads

Contact QCD for additional sizes, materials and end configurations.

** Prop 65 Warning does not apply to stainless steel part numbers

EA Series Dust Plugs and Caps



Body Size (in.)	Coupler Dust Plug Plastic	Coupler Dust Plug Aluminum	Nipple Dust Cap Plastic	Nipple Dust Cap Aluminum	Nipple Pressure Cap
1/4	PDP-4	AMPE-4	PDC-4	ADCE-4	MCE-4
3/8	PDP-6	AMPE-6	PDC-6	ADCE-6	MCE-6
1/2	PDP-8	AMPE-8	PDC-8	ADCE-8	MCE-8
3/4	PDP-12	AMPE-12	PDC-12	ADCE-12	MCE-12

Hydraulic Quick Couplings

General Purpose

SM Series High Pressure

Manual Sleeve, Poppet Valve



SM Series double shut-off couplings are versatile for use across a spectrum of hydraulic applications where fluid lines require connection and disconnection. Couplers and nipples are steel with nitrile seals and are available in 1/4 through 3/4 inch sizes.



Features:

- Rated pressures up to 6000 psi
- Poppet valves have captive seals to minimize seal washout
- Steel material with standard nitrile seals
- Standard end configurations include female pipe, straight thread ORB, and British pipe
- Alternative seal materials available



Applications include:

- Industrial hydraulic lines
- Mobile equipment

SM Series Specification

Body Size	1/4	1/2	3/4
Rated Pressure (psi)	6,000	6,000	4,500
Rated Flow (gpm)	3	12	28
Temperature Range (Nitrile Seals)	-40° to +250°F		

Performance



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -SL	Sleeve-Lok (Couplers)	SM-501-8FP-SL
suffix -E5	Ethylene Propylene seal material (EPR)	SM-501-8FP-E5
suffix -E4	Fluorocarbon seal material	SM-501-8FP-E4
suffix -E12	Neoprene seal material	SM-501-8FP-E12

Hydraulic Quick Couplings

General Purpose

SM Series High Pressure

Manual Sleeve, Poppet Valve



SM Series Couplers - Female Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	SM-251-4FP	1/4-18 NPTF	2.09	1.06	0.75	0.24
1/4	SM-251-4FB	G1/4 BSPP	2.24	1.06	0.75	0.26
1/4	SM-251-6FP	3/8-18 NPTF	2.24	1.06	0.94	0.28
1/4	SM-251-6FB	G3/8 BSPP	2.24	1.06	0.94	0.26
1/4	SM-251-6FO	9/16-18 ORB	2.24	1.06	0.75	0.25
1/2	SM-501-8FP	1/2-14 NPTF	3.00	1.56	1.25	0.70
1/2	SM-501-8FB	G1/2 BSPP	3.00	1.56	1.25	0.74
1/2	SM-501-8FO	3/4-16 ORB	3.16	1.56	1.25	0.70
1/2	SM-501-12FP	3/4-14 NPTF	3.07	1.56	1.37	0.81
1/2	SM-501-12FB	G3/4 BSPP	3.16	1.56	1.37	0.85
3/4	SM-751-12FO	1 1/16-12 ORB	3.89	2.22	1.62	1.78
3/4	SM-751-12FP	3/4-14 NPTF	3.77	2.22	1.62	1.83
3/4	SM-751-12FB	G3/4 BSPP	3.89	2.22	1.62	1.88
3/4	SM-751-16FP	1-11 1/2 NPTF	3.98	2.22	1.62	1.84
3/4	SM-751-16FB	G 1 BSPP	3.98	2.22	1.62	1.89
3/4	SM-751-16FO	1-5/16 - 12 ORB	3.98	2.22	1.62	1.89



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

SM Series High Pressure

Manual Sleeve, Poppet Valve



SM Series Nipples - Female Thread



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	SM-252-4FP	1/4-18 NPTF	1.49	0.50	0.87	0.75	0.08
1/4	SM-252-4FB	G1/4 BSPP	1.64	0.65	0.87	0.75	0.09
1/4	SM-252-6FP	3/8-18 NPTF	1.64	0.81	1.08	0.94	0.14
1/4	SM-252-6FB	G3/8 BSPP	1.64	0.81	1.08	0.94	0.14
1/4	SM-252-6FO	9/16-18 ORB	1.64	0.55	0.87	0.75	0.08
1/2	SM-502-8FO	3/4-16 ORB	2.14	0.72	1.23	1.06	0.16
1/2	SM-502-8FP	1/2-14 NPTF	2.01	0.45	1.23	1.06	0.15
1/2	SM-502-8FB	G1/2 BSPP	2.01	0.60	1.23	1.06	0.18
1/2	SM-502-12FP	3/4-14 NPTF	2.31	0.90	1.59	1.37	0.30
1/2	SM-502-12FB	G3/4 BSPP	2.63	1.07	1.59	1.37	0.34
3/4	SM-752-12FO	1 1/16-12 ORB	2.60	0.39	1.73	1.50	0.48
3/4	SM-752-12FP	3/4-14 NPTF	2.48	0.39	1.73	1.50	0.52
3/4	SM-752-12FB	G3/4 BSPP	2.60	0.53	1.73	1.50	0.56
3/4	SM-752-16FP	1-11 1/2 NPTF	2.69	0.67	1.88	1.62	0.56
3/4	SM-752-16FB	G 1 BSPP	2.69	0.67	1.88	1.62	0.68
3/4	SM-752-16FO	1-5/16 - 12 ORB	2.69	0.67	1.88	1.62	0.68

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

SM Series Dust Plugs and Caps



Body Size (in.)	Nipple Dust Cap	Color/Material	Coupler Dust Plug
1/4	N/A	Plastic	PL-25
1/4	CR-25	Black Rubber	PR-25
1/4	C-25	Aluminum	P-25
1/2	DC-50	Black Rubber	P-25
1/2	C-50	Aluminum	P-50
3/4	C-75	Aluminum	P-75

WARNING

This product can expose you to chemicals including DEHP, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

HP Series
High Pressure

Manual Sleeve, Poppet Valve



HP Series double shut-off couplings are designed for pressures up to 5000 psi. Couplers and nipples are steel with nitrile seals and are available in 1 and 1-1/2 inch sizes.




Features:

- Rated pressures up to 5000 psi
- Smooth flow path with minimal pressure drop
- Heat treated steel nipple and heavy duty sleeve withstand pressure surges
- Couplings have protective zinc with clear trivalent chromate finish
- Standard end configurations include female pipe and straight thread ORB
- Alternative seal materials available

Applications include:

- Industrial hydraulic lines
- Mobile equipment

Performance



HP Series Specification

Body Size	1	1-1/2
Rated Pressure (psi)	5,000	
Rated Flow (gpm)	50	100
Temperature Range (Std Seals)	-40° to +250°F	

Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -E5	Ethylene Propylene seal material (EPR)	HP-1001-16FP-E5
suffix -E4	Fluorocarbon seal material	HP-1001-16FP-E4
suffix -E12	Neoprene seal material	HP-1001-16FP-E12

Hydraulic Quick Couplings

General Purpose

HP Series High Pressure

Manual Sleeve, Poppet Valve



HP Series - Couplers



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1	HP-1001-16FP	1 11-1/2 NPSF	3.95	2.38	1.62	2.10
1	HP-1001-16FO	1 5/16-12 ORB	4.35	2.38	1.62	2.10
1-1/2	HP-1501-24FP	1 1/2-11 1/2 NPTF	4.93	3.00	2.25	4.40
1-1/2	HP-1501-24FO	1 7/8 -12 ORB	4.93	3.00	2.25	4.40

HP Series - Nipples



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1	HP-1002-16FP	1 11-1/2 NPSF	3.00	1.32	1.88	1.62	0.84
1	HP-1002-16FO	1 5/16-12 ORB	3.40	1.72	1.88	1.62	0.84
1-1/2	HP-1502-24FP	1 1/2-11 1/2 NPTF	4.06	0.99	2.63	2.25	1.85
1-1/2	HP-1502-24FO	1 7/8-12 ORB	4.06	0.99	2.63	2.25	1.85

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

HP Series Dust Plugs and Caps



Protective Caps for Coupler			Protective Caps for Nipple		
Part Number	Material*	Fits Coupler	Part Number	Material*	Fits Coupler
HPP-100	Aluminum	HP-1001	HPC-100	Aluminum	HP-1002
HPP-150	Aluminum	HP-1501	HPC-150	Aluminum	HP-1502

* Prop 65 Warning does not apply to aluminum.

WARNING

This product can expose you to chemicals including DEHP, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

4000 Series Couplers ISO 5675 Nipples (1/2" size)

Manual Sleeve, Poppet/Ball Valve



The 4000 Series brings to the industry a proven design for use on agricultural machinery and other rugged applications.



Features:

- 1/2" size accepts ISO 5675 universal tips
- 1/2" size accepts ISO 7241 nipples
- Basic operation where coupler sleeve is manually retracted to allow connection with male tip
- Critical parts are hardened
- Ball and poppet valve options
- Protective zinc plating with clear trivalent chromate finish



Applications include:

- Hydraulic Loaders
- Add-on hydraulic circuits

4000 Series Specification

Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
1/4	3	3000	-40° F to +250° F	Steel	Manual Connect	Nitrile
3/8	6					
1/2	12					
3/4	28					
1	50					

Performance



4050 Series Replacement O-Rings

Body Size	Material	Part Number	Durometer
1/4	Nitrile	50001-113-0260	90
3/8	Nitrile	50001-116-0260	90
1/2	Nitrile	50001-211-0260	90
3/4	Nitrile	50001-215-0010	70
1	Nitrile	50001-218-0260	90

Hydraulic Quick Couplings

General Purpose

4000 Series Couplers ISO 5675 Nipples (1/2"size)

Manual Sleeve, Poppet/Ball Valve



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix W	Ethylene Propylene seal material- EPR	4050-4PW
suffix Y	Fluorocarbon seal material	4050-4PY
suffix Z	Neoprene seal material	4050-4PZ

4000 Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	4050-2P	1/4-18 NPTF	Poppet	2.18	1.06	0.88	0.24
1/4	4050-2P-T8M	3/4-16 ORB (Male)	Poppet	1.80	1.06	0.88	0.21
1/4	4050-T6	9/16-18 ORB	Poppet	2.18	1.06	0.88	0.27
1/4	4050P-T6*	9/16-18 ORB	Poppet	2.43	1.33	0.88	0.33
3/8	4050-3P	3/8-18 NPTF	Poppet	2.31	1.33	0.94	0.51
1/2	4050-4	1/2-14 NPTF	Ball	2.60	1.50	1.06	0.58
1/2	4050-4P	1/2-14 NPTF	Poppet	2.60	1.50	1.06	0.58
1/2	4050-5	3/4-14 NPTF	Ball	2.69	1.50	1.13	0.71
1/2	4050-5P	3/4-14 NPTF	Poppet	2.69	1.50	1.13	0.71
1/2	4050-15	3/4-16 ORB	Ball	2.81	1.50	1.06	0.64
1/2	4050-15P	3/4-16 ORB	Poppet	2.81	1.50	1.06	0.64
1/2	4050-16	7/8-14 ORB	Ball	2.75	1.50	1.06	0.59
1/2	4050-16P	7/8-14 ORB	Poppet	2.75	1.50	1.06	0.59
1/2	4050-29BSPP	1/2-14 BSPP	Ball	2.68	1.50	1.06	0.59
3/4	4150-5	3/4-14 NPTF	Ball	3.06	1.87	1.38	1.00

* Special Push/Pull Sleeve

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

4000 Series Couplers ISO 5675 Nipples (1/2"size)

Manual Sleeve, Poppet/Ball Valve



8010 Series Nipples



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	4010-2P	1/4-18 NPTF	Poppet	1.48	0.71	0.87	0.75	0.08
1/4	4010-T6	9/16-18 ORB	Poppet	1.60	0.81	0.87	0.75	0.09
3/8	4010-3P	3/8-18 NPTF	Poppet	1.60	0.80	1.08	0.94	0.16
1/2	8010-4	1/2-14 NPTF	Ball	1.95	1.09	1.23	1.06	0.20
1/2	8010-4P	1/2-14 NPTF	Poppet	1.95	1.09	1.23	1.06	0.20
1/2	8010-5	3/4-14 NPTF	Ball	2.14	1.28	1.44	1.25	0.25
1/2	8010-5P	3/4-14 NPTF	Poppet	2.14	1.28	1.44	1.25	0.25
1/2	8010-15	3/4-16 ORB	Ball	1.95	1.20	1.23	1.06	0.20
1/2	8010-15P	3/4-16 ORB	Poppet	1.95	1.20	1.23	1.06	0.20
1/2	8010-16	7/8-14 ORB	Ball	1.95	1.18	1.23	1.06	0.25
1/2	8010-16P	7/8-14 ORB	Poppet	1.95	1.18	1.23	1.06	0.25
1/2	8010-29BSPP	1/2-14 BSPP	Ball	1.95	1.09	1.18	1.06	0.25
3/4	4110-5	3/4-14 NPTF	Ball	1.81	1.23	1.52	1.31	0.50
1	4010-6P	1-11 1/2 NPTF	Poppet	2.79	1.49	1.88	1.63	0.62

* This dimension represents the portion of the nipple that is exposed when the nipple and coupler are connected.

4000 Series Dust Caps and Plugs



Body Size (in.)	Dust Plug (Coupler)	Color/Material	Dust Plug (Nipple)	Weight (lbs.)
1/4	5205-2M	Black Rubber	5209-2M	0.02
3/8	5205-3M	Black Rubber	5209-3M	0.03
1/2	5205-4M	Black Rubber	5209-4M	0.04
1/2	5005-4	Steel w/Chain	5009-4	0.21
1/2	5205-4M-BU	Blue Rubber	5209-4M-BU	0.04
1/2	5205-4M-GR	Green Rubber	5209-4M-GR	0.04
1/2	5205-4M-RE	Red Rubber	5209-4M-RE	0.04
1/2	5205-4M-YE	Yellow Rubber	5209-4M-YE	0.04
3/4	5205-5M	Black Rubber	5209-5M	0.05
1	5205-6M	Black Rubber	5209-6M	0.06

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

General Purpose

4200 Series Couplers ISO 5675 Nipples (1/2" size)

Push/Pull/Breakaway Sleeve



The 4200 Series brings to the industry a proven design for use on agricultural machinery, construction equipment, and other rugged applications where a breakaway feature is desirable.



Features:

- 1/2" size accepts ISO 5675 universal tips
- Grooves in sleeve to accommodate retaining rings for bulkhead mounting
- One-handed push-to-connect operation when coupler is clamp mounted
- 1/2" body size couplers are compatible with 5001-4 and 5006-4 breakaway clamps
- Critical parts are hardened
- Ball and poppet valve options
- Protective zinc plating with clear trivalent chromate finish


Applications include:

- Hydraulic Loaders
- Add-on hydraulic circuits
- Implement breakaway
- Hydraulic tools

4200 Series Specifications

Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
3/8	6	3000	-40° F to +250° F	Steel	Push/pull/ breakaway	Nitrile
1/2	12					

Performance



4200 Series Dust Caps and Plugs



Body Size	Dust Plug (Coupler)	Color/Material	Dust Cap (Nipple)	Weight (lbs.)
3/8	5205-3M	Black Rubber	5209-3M	0.03
1/2	5205-4M	Black Rubber	5209-4M	0.04
1/2	5005-4	Steel w/Chain	5009-4	0.21
1/2	5205-4M-BU	Blue Rubber	5209-4M-BU	0.04
1/2	5205-4M-GR	Green Rubber	5209-4M-GR	0.04
1/2	5205-4M-RE	Red Rubber	5209-4M-RE	0.04
1/2	5205-4M-YE	Yellow Rubber	5209-4M-YE	0.04

Optional Materials and Features:

(add code to part number)

Code	Description	Part Number Example
suffix W	Ethylene Propylene seal material- EPR	4250-4PW
suffix Y	Fluorocarbon seal material	4250-4PY
suffix Z	Neoprene seal material	4250-4PZ

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

4250 Series Replacement O-Rings

Body Size	Material	Part Number	Durometer
3/8	Nitrile	50001-116-0260	90
1/2	Nitrile	50001-211-0260	90

Hydraulic Quick Couplings

General Purpose

4200 Series Couplers ISO 5675 Nipples (1/2" size)

Push/Pull/Breakaway Sleeve



4200 Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	4250-3P	3/8-18 NPTF	Poppet	2.31	1.31	0.81	0.39
1/2	4250-4	1/2-14 NPTF	Ball	2.68	1.50	0.94	0.55
1/2	4250-4P	1/2-14 NPTF	Poppet	2.68	1.50	0.94	0.55
1/2	4250-15	3/4-16 ORB	Ball	2.68	1.50	0.94	0.55
1/2	4250-15P	3/4-16 ORB	Poppet	2.68	1.50	0.94	0.55

8010 Series Nipples



Body Size (in.)	Nipple Part Number Steel	Port End	Valve Type	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	4010-3P	3/8-18 NPTF	Poppet	1.60	1.60	1.31	0.81	0.39
1/2	8010-4	1/2-14 NPTF	Ball	1.95	1.95	1.50	0.94	0.55
1/2	8010-4P	1/2-14 NPTF	Poppet	1.95	1.95	1.50	0.94	0.55
1/2	8010-15	3/4-16 ORB	Ball	2.06	2.06	1.50	0.94	0.55
1/2	8010-15P	3/4-16 ORB	Poppet	2.06	2.06	1.50	0.94	0.55

* This dimension represents the portion of the nipple that is exposed when the nipple and coupler are connected.

8010 Series Nipples - Connect Under Pressure



Body Size (in.)	Nipple Part Number Steel	Port End	Valve Type	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/2	8010-4P-DC	1/2-14 NPTF	DC Poppet	1.81	1.09	1.06	1.16	0.20
1/2	8010-15P-DC	3/4-16 ORB	DC Poppet	1.81	1.09	1.06	1.16	0.20

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

NS Series Push-to-Connect

Sleeve Lock



NS Series non-spill couplings are designed to minimize spillage and air inclusion when connecting or disconnecting. Couplers and nipples are steel with nitrile seals. 1/2 inch through 1 inch sizes utilize a PTFE back-up ring as additional support to the interface seal.



Features:

- Rated pressure up to 2500 psi
- Positive valve stop prevents flow checking
- Heat treated steel nipple and heavy duty sleeve withstand pressure surges
- Standard sleeve lock guards against accidental disconnection
- Couplings have protective zinc with clear trivalent chromate finish
- Standard end configurations include female pipe, straight thread ORB, and BSPP
- Alternative seal materials available

Applications include:

- Hydraulic hand tools
- Utility equipment
- Mining equipment
- Hydraulic tools

NS Series Specifications



Body Size	3/8	1/2	3/4	1
Rated Pressure (psi)	2,500			
Rated Flow (gpm)	10	12	30	50
Temperature Range (std seals)	-40° to +250°F			
Spillage (ml) (max. per disconnect)	0.020	0.070	0.150	0.220
Air Inclusion (ml) (max. per disconnect)	0.010	0.020	0.050	0.070

NS Series Dust Caps and Plugs



Body Size	Dust Plug (Coupler)
3/8	NR-37
1/2	NR-50
3/4	NR-75
1	NR-100

Performance



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -E5	Ethylene Propylene seal material (EPR)	NS-502-8FP-E5
suffix -E4	Fluorocarbon seal material	NS-502-8FP-E4

Hydraulic Quick Couplings

Non-Spill

NS Series Push-to-Connect

Sleeve Lock



Standard Port Configurations

FP - Female Pipe Thread

FO - Female Straight Thread

FB - Female British Standard Parallel Pipe

NS Series Couplers



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	NS-371-6FP	3/8-18 NPSF	2.10	1.13	1.06	0.36
3/8	NS-371-6FB	G3/8 BSPP	2.10	1.13	1.06	0.38
3/8	NS-371-8FO	3/4-16 UNF	2.20	1.13	1.06	0.40
1/2	NS-501-8FP	1/2-14 NPSF	2.88	1.56	1.25	0.84
1/2	NS-501-8FB	G1/2 BSPP	2.95	1.56	1.25	0.74
1/2	NS-501-10FO	7/8-14UNF	2.97	1.56	1.25	0.80
3/4	NS-751-12FP	3/4-14 NPSF	3.19	1.96	1.56	1.48
3/4	NS-751-12FB	G3/4 BSPP	3.38	1.96	1.56	1.54
3/4	NS-751-12FO	1 1/16-12 UN	3.51	1.96	1.56	1.58
1	NS-1001-16FP	1-11 1/2 NPSF	3.70	2.25	1.75	2.35
1	NS-1001-16FB	G 1 BSPP	3.81	2.25	1.75	2.36
1	NS-1001-16FO	1 5/16-12 UN	3.81	2.25	1.75	2.36

NS Series Nipples



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	NS-372-6FP	3/8-18 NPSF	1.70	1.17	1.08	0.94	0.16
3/8	NS-372-6FB	G3/8 BSPP	1.78	1.25	1.08	0.94	0.16
3/8	NS-372-8FO	3/4-16 UNF	1.91	1.38	1.23	1.06	0.20
1/2	NS-502-8FP	1/2-14 NPSF	1.81	0.69	1.23	1.06	0.20
1/2	NS-502-8FB	G1/2 BSPP	1.95	0.83	1.23	1.06	0.22
1/2	NS-502-10FO	7/8-14 UNF	2.14	1.02	1.23	1.06	0.23
3/4	NS-752-12FP	3/4-14 NPSF	2.25	1.12	1.59	1.37	0.48
3/4	NS-752-12FB	G3/4 BSPP	2.47	1.34	1.59	1.37	0.54
3/4	NS-752-12FO	1 1/16-12 UN	2.62	1.49	1.59	1.37	0.65
1	NS-1002-16FP	1-11 1/2 NSPF	2.64	1.54	1.88	1.62	0.72
1	NS-1002-16FB	G 1 BSPP	2.78	1.68	1.88	1.62	0.74
1	NS-1002-16FO	1 5/16-12 UN	2.78	1.68	1.88	1.62	0.80

* This dimension represents the portion that is exposed when the nipple is inserted into the mating Parker Coupler.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

NSS Series Push-to-Connect

High Flow, Stainless Steel



NSS couplings deliver high flow rates with excellent flow vs pressure drop characteristics to maintain optimum system performance and efficiency. Ideal for high-tech industry cooling applications, couplers and nipples are 316 stainless steel with ethylene propylene seals. Their compact body size and guided alignment save time and frustration when connecting fluid lines in confined spaces

Features:




- Non-spill valving ensures minimal fluid loss and low air inclusion
- Corrosion resistant stainless steel construction
- Easy push to connect operation with guided alignment
- High flow and compact size
- Standard end configurations include female straight thread ORB, Push-Lok® hose barb, A-Lok, bulkhead and panel mount options
- Alternative seal materials available

Applications include:

- Cooling lines
- Chemical transfer lines
- High purity systems
- Lab equipment



Performance



NSS Specifications

Body Size	3/8	1/2
Rated Pressure (psi)	2000	300
Rated Flow (gpm)	10	12
Temperature Range (std seals)	-70° to +250°F	
Standard Seal Material	Ethylene Propylene	Ethylene Propylene
Body/Sleeve/Valve Material	316 Stainless Steel	316 Stainless Steel
Spring Material	17-7 Stainless Steel	17-7 Stainless Steel
Locking Ball Material	303 Stainless Steel	303 Stainless Steel
Spillage (ml) (max. per disconnect)	0.020	0.070
Air Inclusion (ml) (max. per disconnect)	0.010	0.020

Hydraulic Quick Couplings


Non-Spill

NSS Series Push-to-Connect

High Flow, Stainless Steel




NSS Series Couplers - Female Thread



Body Size (in.)	Part Number Stainless Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	NSS-371-6FO	9/16 - 18 UNF	2.25	1.13	0.94	0.35
3/8	NSS-371-8FO	3/4 - 16 UNF	2.38	1.13	0.94	0.35
1/2	NSS-501-10FO	7/8 - 14 UNF	2.99	1.40	1.25	0.80
1/2	NSS-501-12FO	1 1/16 - 12 UNF	3.10	1.40	1.25	0.80

NSS Series Couplers - Push-Lok® Hose Barb*




Body Size (in.)	Part Number Stainless Steel	Hose I.D.	Length (in.)**	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	NSS-371-6HB	3/8	1.70	1.13	0.94	0.30
3/8	NSS-371-8HB	1/2	1.62	1.13	0.94	0.30
1/2	NSS-501-8HB	1/2	2.23	1.40	1.25	0.80
1/2	NSS-501-12HB	3/4	2.23	1.40	1.25	0.80

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

** Length is to end of body hex and does not include fitting end.

NSS Series Couplers - A-Lok® Compression Fitting*



Body Size (in.)	Part Number Stainless Steel	Port End	Length (in.)*	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)
3/8	NSS-371-6MA	3/8 A-Lok	1.75	1.13	0.94	0.69	0.35
3/8	NSS-371-8MA	1/2 A-Lok	1.67	1.13	0.94	0.88	0.37
1/2	NSS-501-8MA	1/2 A-Lok	2.23	1.40	1.25	0.88	0.80
1/2	NSS-501-12MA	3/4 A-Lok	2.23	1.40	1.25	1.13	0.80

* Length is to end of body hex and does not include fitting end.

Hydraulic Quick Couplings


Non-Spill

NSS Series Push-to-Connect

High Flow, Stainless Steel




NSS Series Couplers - A-Lok® Compression Fitting* / Bulkhead Mount



Body Size (in.)	Part Number SS	Port End	Length (in.)**	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Wrench Flats 3	Weight (lbs.)
3/8	NSS-371-6BMA	3/8 A-Lok	1.75	1.13	0.94	0.69	0.75	0.40
1/2	NSS-501-8BMA	1/2 A-Lok	2.06	1.40	1.25	0.88	0.94	0.80
1/2	NSS-501-12BMA	3/4 A-Lok	2.23	1.40	1.25	1.13	1.19	0.80


* Length is to end of body hex and does not include fitting end.

NSS Series Couplers - A-Lok® Compression Fitting* / Panel Mount




Body Size (in.)	Part Number SS	Port End	Length (in.)**	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Wrench Flats 3	Weight (lbs.)
3/8	NSS-371-6HMA	3/8 A-Lok	1.75	1.13	0.94	0.69	0.75	0.40
1/2	NSS-501-8HMA	1/2 A-Lok	2.23	1.40	1.25	0.88	0.94	0.80
1/2	NSS-501-12HMA	3/4 A-Lok	2.23	1.40	1.25	1.13	1.19	0.80

NSS Series Nipples - Female Thread



Body Size (in.)	Part Number SS	Port End	Length (in.)**	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Wrench Flats 3	Weight (lbs.)
3/8	NSS-372-6FO	9/16 - 18 UNF	1.75	1.13	0.94	0.69	0.75	0.40
3/8	NSS-372-8FO	3/4 - 16 UNF	2.06	1.40	1.25	0.88	0.94	0.80
1/2	NSS-502-10FO	7/8 - 14 UNF	2.23	1.40	1.25	1.13	1.19	0.80
1/2	NSS-502-12FO	1 1/16 - 12 UNF	2.06	1.40	1.25	0.88	0.94	0.80

NSS Series Nipples - Push-Lok® Hose Barb*



Body Size (in.)	Part Number SS	Hose I.D.	Length (in.)**	Largest Diameter	Wrench Flats 1	Weight (lbs.)
3/8	NSS-372-6HB	3/8	1.37	1.02	0.94	0.15
3/8	NSS-372-8HB	1/2	1.37	1.02	0.94	0.15
1/2	NSS-502-8HB	1/2	1.38	1.38	1.25	0.25
1/2	NSS-502-12HB	3/4	2.23	1.38	1.25	0.25

* Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

** Length is to end of body hex and does not include fitting end.

Hydraulic Quick Couplings

Non-Spill


NSS Series Push-to-Connect

High Flow, Stainless Steel



Code	Coupler and Nipple Seal Material Options	Part Number Example
suffix N	Nitrile - NBR	NSS-371-6HMA-N
suffix F	Fluorocarbon - FKM	NSS-371-6HMA-F
suffix C	Neoprene - CR	NSS-371-6HMA-C
suffix G	GFTL Fluorocarbon - FKM	NSS-371-6HMA-G
suffix P	Perfluoro elastomer - FFKM	NSS-371-6HMA-P
suffix L	Fluorosilicone - FVQM	NSS-371-6HMA-L


NSS Series Nipples - A-Lok® Compression Fitting*



Body Size (in.)	Part Number SS	Port End	Length (in.)*	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)
3/8	NSS-372-6MA	3/8 A-Lok	1.39	1.02	0.94	0.69	0.20
3/8	NSS-372-8MA	1/2 A-Lok	1.39	1.02	0.94	0.88	0.22
1/2	NSS-502-8MA	1/2 A-Lok	2.23	1.38	1.25	0.88	0.25
1/2	NSS-502-12MA	3/4 A-Lok	2.23	1.38	1.25	1.13	0.25

* Length is to end of body hex and does not include fitting end.


NSS Series Nipples - A-Lok® Compression Fitting* / Bulkhead Mount



Body Size (in.)	Part Number SS	Port End	Length (in.)*	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Wrench Flats 3	Weight (lbs.)
3/8	NSS-372-6BMA	3/8 A-Lok	1.39	1.02	0.94	0.69	0.75	0.25
1/2	NSS-502-8BMA	1/2 A-Lok	1.99	1.38	1.25	0.88	0.94	0.25
1/2	NSS-502-12BMA	3/4 A-Lok	2.23	1.38	1.25	1.13	1.19	0.25

* Length is to end of body hex and does not include fitting end.

NSS Series Nipples - A-Lok® Compression Fitting* / Panel Mount



Body Size (in.)	Part Number SS	Port End	Length (in.)*	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Wrench Flats 3	Weight (lbs.)
3/8	NSS-372-6HMA	3/8 A-Lok	1.39	1.02	0.94	0.69	0.75	0.25
1/2	NSS-502-8HMA	1/2 A-Lok	2.23	1.38	1.25	0.88	0.94	0.25
1/2	NSS-502-12HMA	3/4 A-Lok	2.23	1.38	1.25	1.13	1.19	0.25

* Length is to end of body hex and does not include fitting end.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

FF/FC Series

HTMA (3/8 size)

Push-to-Connect/Sleeve Lock



FF Series couplings eliminate spillage and air inclusion when connecting and disconnecting. The sleeve locking mechanism prevents accidental disconnection. 3/8" body size complies with Hydraulic Tool Manufacturers Association standards. FC nipples provide a connect-under-pressure option for trapped pressures up to 3000 psi on the nipple side.



Features:

- Flush, non-spill valving
- Hardened steel sleeves and nipple bodies
- Locking sleeve
- Sleeve-Lok design now standard
- Blow-out resistant seal
- Connect-under-pressure FC nipple option
- Standard zinc plating

Applications include:


- Hydraulic tools
- Mobile equipment
- Industrial hydraulics

FF Series Specifications


Body Size	Rated Pressure (psi)	Rated Flow (gpm)	Temperature Range	Spillage (ml) max. per disconnect	Air Inclusion (ml) max. per connect	Body Material	Sleeve Type	Seal Material
1/4	5000	3	-40° to +250°F	.015	.020	Steel	Push to Connect	Nitrile/ Polyurethane
3/8	5000	6		.015	.020			
1/2	3000	12		.080	.070			
3/4	3000	28		.150	.100			
1	3000	50		.200	.150			

Performance

FF Series (1/4", 3/8", 1/2")
Test Fluid: Oil - 200 SUS



FF Series (3/4" & 1")
Test Fluid: Oil - 200 SUS



Hydraulic Quick Couplings

Non-Spill

FF/FC Series

HTMA (3/8 size)

Push-to-Connect/Sleeve Lock



Standard Port Configurations


FP - Female Pipe Thread

FO - Female Straight Thread

MP - Male Pipe Thread

FB - Female British Standard Parallel Pipe

FF Series Couplers



Body Size (in.)	Coupler Part Number Steel	Thread Size	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	FF-251-4FP	1/4-18 NPSF	1.79	-	1.06	25 mm	0.23
1/4	FF-251-4MP	1/4-18 NPTF	1.84	-	1.06	25 mm	0.24
1/4	FF-251-6FO	9/16-18 UNF	1.91	-	1.06	25 mm	0.23
3/8	FEM-371-6FP	3/8-18 NPTF	3.06	5.02	1.26	30 mm	0.77
3/8	FEM-371-8FP	1/2-14 NPTF	3.17	5.23	1.26	30 mm	0.75
3/8	FEM-371-6FB	3/8-19 BSPP	3.06	5.02	1.31	30 mm	0.75
3/8	FEM-371-8FB	G1/2 BSPP	3.17	5.23	1.31	30 mm	0.75
3/8	FEM-371-8FO	3/4-16 UNF	3.06	5.02	1.26	30 mm	0.74
1/2	FF-501-8FP	1/2-14 NPSF	3.25	-	1.53	36 mm	1.18
1/2	FF-501-10FO	7/8-14 UNF	3.07	-	1.53	36 mm	1.075
3/4	FF-751-12FP	3/4-14 NPSF	3.50	-	1.94	45 mm	1.84
3/4	FF-751-12FO	1 1/16-12 UNF	3.75	-	1.94	45 mm	1.93
1	FF-1001-16FP	1-11 1/2 NPSF	4.14	-	2.25	48 mm	2.64
1	FF-1001-16FO	1 5/16-12 UNF	4.24	-	2.25	48 mm	2.68

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill


FF/FC Series

HTMA (3/8 size)

Push-to-Connect/Sleeve Lock



FF Series Nipples



Body Size (in.)	Coupler Part Number Steel	Thread Size	Length (in.)	Coupled Length	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	FF-252-4FP	1/4-18 NPSF	1.66	-	1.15	1.06	25 mm	0.16
1/4	FF-252-4MP	1/4-18 NPTF	1.72	-	1.18	1.06	25 mm	0.26
1/4	FF-252-6FO	9/16-18 UNF	1.66	-	1.15	1.06	25 mm	0.16
3/8	FEM-372-6FP	3/8-18 NPTF	2.59	5.02	-	1.26	30 mm	0.48
3/8	FEM-372-8FP	1/2-14 NPSF	2.69	5.23	-	1.26	30 mm	0.48
3/8	FEM-372-6FB	3/8-19 BSPP	2.59	5.02	-	1.26	30 mm	0.48
3/8	FEM-372-8FB	G1/2 BSPP	2.69	5.22	-	1.26	30 mm	0.47
3/8	FEM-372-8FO	3/4-16 UNF	2.59	5.02	-	1.26	30 mm	0.45
1/2	FF-502-8FP	1/2-14 NPSF	3.13	-	2.11	1.57	36 mm	0.87
1/2	FF-502-10FO	7/8-14 UNF	2.95	-	2.07	1.57	36 mm	0.77
3/4	FF-752-12FP	3/4-14 NPSF	3.38	-	2.47	1.73	45 mm	1.00
3/4	FF-752-12FO	1 1/16-12 UNF	3.58	-	2.47	1.73	45 mm	1.02
1	FF-1002-16FP	1-11 1/2 NPSF	3.85	-	2.60	2.17	48 mm	1.60
1	FF-1002-16FO	1 5/16-12 UNF	3.85	-	2.60	2.17	48 mm	1.70

* This dimension represents the portion of the nipple that is exposed when the nipple and coupler are connected.

Optional Materials and Features:

(add code to part number)

Optional seals include O-ring & Back-Up Ring, not Anti-Blow Out bonded seal. Contact QCD for availability and additional options. To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -E5	Ethylene Propylene seal material (EPR)	FF-501-8FP-E5
suffix -E4	Fluorocarbon seal material	FF-501-8FP-E4

FF Series Repair Kits

1/4" Nipple	FF-252-KIT	FF-252-KIT-E4	FF-252-KIT-E5
3/8" Nipple	FF-372-KIT	FF-372-KIT-E4	FF-372-KIT-E5
3/4" Nipple	FF-752-KIT	FF-752-KIT-E4	FF-752-KIT-E5
1/2" Nipple	FF-502-KIT	FF-502-KIT-E4	FF-502-KIT-E5
1" Nipple	FF-1002-KIT	FF-1002-KIT-E4	FF-1002-KIT-E5

Dust Caps - FF Series



Body Size	Coupler Dust Cap - Rubber	Nipple Dust Cap - Rubber
1/4	FR-25	FR-25
3/8	NR-50	NR-37
1/2	FR-501	FR-502
3/4	FR-751	FR-752
1	FR-1001	FR-1002

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

FF/FC Series

HTMA (3/8 size)

Push-to-Connect/Sleeve Lock



Hydraulic Quick Couplings

Non-Spill

Connect Under Pressure Operation

FC Series products operate slightly different from traditional non-spill couplings. With no pressure in the coupler and up to 3000 PSI of trapped pressure in the nipple, begin to couple the mating halves. Delay momentarily during connection to allow trapped pressure to equalize with the mating half before completing the connection.

FC Series nipples provide a connect-under-pressure option for trapped pressures up to 3000 psi on the nipple side.




Features:

- Connect-under-pressure nipple
- Flush, non-spill valving
- Hardened locking surface
- Blow-out resistant seal
- Protective zinc plating with clear trivalent chromate finish

Applications include:

- Hydraulic tools

Performance



FC Series Specifications

Body Size	Rated Pressure (psi)	Rated Connect-Under-Pressure Capability	Rated Flow (gpm)	Spillage (ml) max. per disconnect	Air Inclusion (ml) max. per connect
3/8	3000	3000	6	.015	.020
1/2	3000	3000	12	.020	.070
3/4	3000	1500	26	.150	.100

FC Series Nipples



* This dimension represents the portion of the nipple that is exposed when the nipple and coupler are connected.

Body Size (in.)	Part Number Steel	Mating Half	Port End	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	FC-372-6FP	FEM-371	3/8-18 NPSF	3.30	2.58	1.16	1.062	0.45
3/8	FC-372-8FO	FEM-371	3/4-16 UNF	3.30	2.58	1.16	1.062	0.42
3/8	FC-372-8FP	FEM-371	1/2-14 NPSF	3.30	2.58	1.16	1.062	0.42
1/2	FC-502-8FP	FF-501	1/2-14 NPSF	3.46	2.65	1.22	1.125	0.53
1/2	FC-502-10FO	FF-501	7/8-14 UNF	3.46	2.65	1.22	1.125	0.52
3/4	FC-752-12FO	FF-751	1 1/16-12 UNF	4.81	3.72	1.65	1.500	1.32
3/8	FC-752-12FP	FF-751	3/4-14 NPSF	4.81	3.72	1.65	1.500	1.34

Standard Port Configurations: **FP** - Female Pipe Thread **FO** - Female Straight Thread



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

FEM/FEC Series ISO 16028

Push-to-Connect



FEM Series couplings meet or exceed ISO 16028 design and performance requirements. The flush valves eliminate spillage and air inclusion when connecting and disconnecting. Coupler and nipple bodies have a modular design with increased flexibility for end port options. FEC nipples provide a connect-under-pressure option for trapped residual pressure.



Features:

- Flush, non-spill valving
- Global interchangeability with other ISO 16028 compliant couplings
- Hardened nipple bodies
- Sleeve-Lok design standard
- Connect-under-pressure FEC nipple option
- Protective zinc nickel plating

Applications include:

- Skid loader attachments
- Hydraulic tools

FEM Series Specifications



Body Size	Rated Pressure (psi)	Rated Flow (gpm)	Temperature Range	Spillage (ml) max. per disconnect	Air Inclusion (ml) max. per connect	Body Material	Sleeve Type	Seal Material
1/4	4568	3	-40° to +250°F	.015	.020	Steel	Push to Connect	Polyurethane and Nitrile
3/8	5000	6		.015	.020			
1/2	5000	12		.020	.070			
5/8	3625	20		.030	.070			
3/4	5000	26		.150	.100			
1	5000	50		.200	.150			

Materials of Construction

Body: Steel **Valve:** Flush Face Valving **Seal:** Polyurethane and Nitrile

Finish: 1/4", 5/8" - Zinc with clear trivalent | 3/8", 1/2", 3/4", 1" - Zinc Nickel

Performance



Code	Description	Part Number Example
suffix -E5	Ethylene Propylene seal material (EPR)	FEM-501-8FP-E5
suffix -E4	Fluorocarbon seal material	FEM-501-8FP-E4

FEM/FEC Series

ISO 16028




Push-to-Connect

Hydraulic Quick Couplings

Non-Spill



FEM Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	FEM-251-4FP	1/4-18 NPTF (Female)	1.96	3.98	1.16	27 mm	0.52
1/4	FEM-251-6FO	9/16-18 UNF (Female)	2.08	4.06	1.16	27 mm	0.51
3/8	FEM-371-6FP	3/8-18 NPTF (Female)	3.06	5.02	1.26	30 mm	0.77
3/8	FEM-371-6FB	3/8-19 BSPP (Female)	3.06	5.02	1.25	30 mm	0.76
3/8	FEM-371-6FO	9/16-18 UNF (Female)	3.06	5.02	1.25	30 mm	0.76
3/8	FEM-371-6MO	9/16-18 UNF (Male)	2.59	4.26	1.25	30 mm	0.66
3/8	FEM-371-8FP	1/2-14 NPTF (Female)	3.17	5.23	1.25	30 mm	0.74
3/8	FEM-371-8FO	3/4-16 UNF (Female)	3.06	5.02	1.26	30 mm	0.74
3/8	FEM-371-8FB	G1/2 BSPP (Female)	3.17	5.23	1.31	30 mm	0.75
3/8	FEM-371-8MF	3/4-16 UNF (Male)	2.45	4.41	1.25	30 mm	0.64
3/8	FEM-371-8MO	3/4-16 UNF (Male)	2.45	4.12	1.25	30 mm	0.66
3/8	FEM-371-10FO	7/8-14 UNF (Female)	3.17	5.23	1.25	30 mm	0.71
3/8	FEM-371-10MF	7/8-14 UNF (Male)	2.59	4.41	1.25	30 mm	0.69
1/2	FEM-501-8FP	1/2-14 NPTF (Female)	3.26	5.74	1.59	36 mm	1.22
1/2	FEM-501-8FO	3/4-16 UNF (Female)	3.26	5.74	1.59	36 mm	1.22
1/2	FEM-501-8FB	G1/2 BSPP (Female)	3.07	5.35	1.59	36 mm	1.14
1/2	FEM-501-10FO	7/8-14 UNF (Female)	3.08	5.38	1.59	36 mm	1.12
1/2	FEM-501-12FP	3/4-14 NPTF (Female)	3.25	5.74	1.50	36 mm	1.08
1/2	FEM-501-12FO	1 1/16-12 UNF (Female)	3.26	5.74	1.59	36 mm	1.11
1/2	FEM-501-12FB	G3/4 BSPP (Female)	3.25	5.71	1.59	36 mm	1.14
5/8	FEM-621-12FO	1 1/16-12 UNF (Female)	3.70	5.64	1.69	40 mm	1.34
3/4	FEM-751-12FP	3/4-14 NPTF (Female)	3.88	6.17	1.97	46 mm	2.04
3/4	FEM-751-12FO	1 1/16-12 UNF (Female)	4.04	6.48	1.97	46 mm	2.10
1	FEM-1001-16FP	1-11 1/2-NPTF (Female)	4.13	6.95	2.32	55 mm	3.19
1	FEM-1001-16FO	1 5/16-12 UNF (Female)	4.13	6.95	2.32	55 mm	3.14

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill



FEM/FEC Series

ISO 16028

Push-to-Connect





FEM Series Couplers - 90 Degree



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/2	FEM-501-C6FP	3/8-18 NPTF	3.26	5.74	1.59	32 mm	1.187
1/2	FEM-501-C6FO	9/16- 18 UNF	3.25	5.74	1.50	36 mm	1.17
1/2	FEM-501-C8FP	1/2- 14 NPTF	3.25	5.74	1.50	36 mm	1.12
1/2	FEM-501-C8FO	3/4-16 ORB	3.25	5.71	1.59	36 mm	1.187

FEM Series Couplers - Bulkhead



Body Size (in.)	Coupler Part Number	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	FEM-371-8BMF	3/4- 16 UNF	2.45	6.75	1.25	30 mm	0.71
3/8	FEM-371-16BMCL	M16-1.5	2.43	6.00	1.25	30 mm	0.65
3/8	FEM-371-18BMCL	M18-1.5	2.45	6.00	1.25	30 mm	0.66
1/2	FEM-501-8BMF	3/4- 16 UNF	2.42	7.02	1.50	36 mm	0.95
1/2	FEM-501-8BMS	13/16- 16 UNS	2.42	6.95	1.50	36 mm	1.00
1/2	FEM-501-C6FP	3/8-18 NPTF	3.26	5.74	1.59	32 mm	1.187
1/2	FEM-501-C8FO	3/4-16 ORB	3.25	5.71	1.59	36 mm	1.187
1/2	FEM-501-12BMF	1 1/16- 12 UNF	2.42	7.64	1.50	36 mm	1.10
1/2	FEM-501-12BMS	1 3/16- 12 UNS	4.07	7.34	1.50	36 mm	1.20

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill



FEM/FEC Series

ISO 16028

Push-to-Connect



FEM Series Nipples



Body Size (in.)	Nipple Part Number Steel	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	FEM-252-4FP	1/4 - 18 NPTF (Female)	1.71	3.98	0.96	22 mm	0.20
1/4	FEM-252-6FO	9/16 - 18 UNF (Female)	1.95	4.06	0.96	22 mm	0.19
3/8	FEM-372-6FP	3/8 - 18 NPTF (Female)	2.59	5.02	1.26	30 mm	0.48
3/8	FEM-372-6FB	3/8 - 19 BSPP (Female)	2.59	5.02	1.25	30 mm	0.48
3/8	FEM-372-6FO	9/16 - 18 UNF (Female)	2.59	5.02	1.25	30 mm	0.49
3/8	FEM-372-6MF	9/16 - 18 UNF (Male)	2.08	4.41	1.25	30 mm	0.38
3/8	FEM-372-6MO	9/16 - 18 UNF (Male)	2.12	4.26	1.25	30 mm	0.39
3/8	FEM-372-8FP	1/2 - 14 NPTF (Female)	2.69	5.23	1.25	30 mm	0.48
3/8	FEM-372-8FO	3/4 - 16 UNF (Female)	2.59	5.02	1.26	30 mm	0.45
3/8	FEM-372-8FB	G1/2 BSPP (Female)	2.69	5.22	1.26	30 mm	0.47
3/8	FEM-372-8MO	3/4 - 16 UNF (Male)	1.98	4.12	1.25	30 mm	0.40
3/8	FEM-372-10FO	7/8 - 14 UNF (Female)	2.69	4.41	1.25	30mm	0.44
3/8	FEM-372-10MF	7/8 - 14 UNF (Male)	2.12	4.41	1.25	30mm	0.43
1/2	FEM-502-8FP	1/2 - 14 NPTF (Female)	3.13	5.74	1.57	36 mm	0.84
1/2	FEM-502-8FO	3/4 - 16 UNF (Female)	3.13	5.74	1.57	36 mm	0.85
1/2	FEM-502-8FB	G1/2 BSPP (Female)	2.95	5.35	1.57	36 mm	0.77
1/2	FEM-502-10FO	7/8 - 14 UNF (Female)	2.95	5.38	1.57	36 mm	0.75
1/2	FEM-502-12FP	3/4 - 14 NPTF (Female)	3.13	5.74	1.57	36 mm	0.79
1/2	FEM-502-12FO	1 1/16 - 12 UN (Female)	3.13	5.74	1.57	36 mm	0.74
1/2	FEM-502-12FB	G3/4 BSPP (Female)	3.13	5.71	1.57	36 mm	0.76
5/8	FEM-622-12FO	1 1/16 - 12 UN (Female)	3.09	5.64	1.57	36 mm	0.72
3/4	FEM-752-12FP	3/4 - 14 NPTF (Female)	3.17	6.17	1.97	46 mm	1.35
3/4	FEM-752-12FO	1 - 1/16 12 UN (Female)	3.33	6.48	1.97	46 mm	1.42
1	FEM-1002-16FP	1-11 1/2 NPTF (Female)	3.70	6.95	2.32	55 mm	2.28
1	FEM-1002-16FO	1-5/16 12 UN (Female)	3.70	6.95	2.32	55 mm	2.34

* This dimension represents the portion of the nipple that is exposed when the nipple and coupler are connected.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill



FEM/FEC Series

ISO 16028

Push-to-Connect




FEM Series Nipples - 90 Degree



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
1/2	FEM-502-C6FP	3/8-18 NPTF	3.13	5.74	1.57	36 mm	0.82
1/2	FEM-502-C6FO	9/16-18 UNF	3.13	5.74	1.57	36 mm	0.88
1/2	FEM-502-C8FO	3/4-16 ORB	3.13	5.71	1.57	36 mm	0.82

FEM Series Nipples - Bulkhead



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	FEM-372-8BMF	3/4- 16 UNF	1.98	6.75	1.25	30 mm	0.44
3/8	FEM-372-16BMCL	M16-1.5	1.98	6.00	1.25	30mm	0.38
1/2	FEM-502-8BMF	3/4- 16 UNF	2.30	7.02	1.57	36 mm	0.67
1/2	FEM-502-8BMS	13/16- 16 UNS	2.30	6.95	1.57	36 mm	0.71
1/2	FEM-502-10BMF	7/8-14 UNF	3.85	7.24	1.38	31.75 mm	0.84
1/2	FEM-502-10BMS	1-14 UNS	3.85	7.24	1.38	31.75 mm	0.84
1/2	FEM-502-12BMF	1 1/16- 12 UNF	2.30	7.64	1.57	36 mm	0.81
1/2	FEM-502-12BMS	1 3/16- 12 UNS	2.30	7.34	1.57	36 mm	0.91

Dust Caps - FEM Series



Body Size (in.)	Nipple Dust Cap	Coupler Dust Cap	Material	Body Size (in.)	Nipple Dust Cap	Coupler Dust Cap	Material
1/4	CFE-252-PN	PFE-251-PN	PVC	5/8	CFE-622-PN	PFE-621-PN	PVC
3/8	CFE-372-PN	PFE-371-PN	PVC	3/4	CFE-752-PN	PFE-751-PN	PVC
1/2	CFE-502-PN	PFE-501-PN	PVC	1	CFE-1002-PN	PFE-1001-PN	PVC

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

FEM/FEC Series ISO 16028

Push-to-Connect



Connect Under Pressure Operation


FEC Series products operate slightly different from traditional non-spill couplings. With no pressure in the coupler and up to 3000 PSI of trapped pressure in the nipple, begin to couple the mating halves. Delay momentarily during connection to allow trapped pressure to equalize with the mating half before completing the connection.



Features:

- Connect-under-pressure nipple
- Hardened locking surface
- Steel construction, Chromium-6 Free plating for corrosion resistance
- Anti blowout bonded nipple seal
- Flush face valving

Performance




Applications include:

Parker FEC Series nipple provide connect-under-pressure capability with up to 3000 PSI of trapped pressure in the nipple and are ideal for applications where residual pressure makes reconnect difficult. Utilized primarily in the construction equipment market, FEC Series products are commonly found on hydraulic attachments used in skid steer applications. The FEC Series mates with the FEM Series interface ISO 16028 couplers.

FEC Series Specifications

Body Size	Rated Pressure (psi)	Rated Connect-Under-Pressure Capability	Rated Flow (gpm)	Spillage (ml) max. per disconnect	Air Inclusion (ml) max. per connect
1/2	3625	3000	12	.020	0.070
5/8	3625	1700	20	.003	0.070
3/4	5000	1500	26	.150	0.100

FEC Series Connect Under Pressure Nipples



Body Size (in.)	Part Number Steel	Mating Half	Port End	Length (in.)	Coupled Length	Largest Diameter	Wrench Flats
1/2	FEC-502-8FP	FEM-501	1/2-14 NPTF	3.50	5.82	1.22	1.125
1/2	FEC-502-10FO	FEM-501	7/8-14 UNF	3.50	5.82	1.22	1.125
1/2	FEC-502-12FO	FEM-501	1 1/16-12 UNF	3.79	6.36	1.65	1.500
5/8	FEC-622-12FO	FEM-621	1 1/16-12 UN	3.39	5.94	1.65	1.500
3/4	FEC-752-12FO	FEM-751	1 1/16-12 UN	4.56	7.72	1.96	1.81

Standard Port Configurations: **FP** - Female Pipe Thread **FO** - Female Straight Thread

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

FH Series HTMA (High Pressure)

Push-to-Connect/Sleeve Lock



FH Series high pressure, non-spill couplings have flush valves and are designed to minimize spillage and air inclusion when connecting or disconnecting. Couplers and nipples are steel with nitrile seals. Available in 3/8 inch size only, with red finish for easy identification. Will not connect with lower pressure flush face couplings



Features:


- Rated pressure up to 10,000 psi
- Push to connect operation
- Red finish on nipple body and coupler sleeve
- Standard sleeve lock guards against accidental disconnection
- Not interchangeable with lower pressure flush face couplings
- Standard end configurations include female pipe, male pipe, and BSPP threads
- Alternative seal materials available

Applications include:

- Hydraulic crimpers, cutters, benders, clamps, wedges
- Rescue equipment
- High pressure test equipment

Performance

FH Series (3/8")
Test Fluid: Oil - 200 SUS



FH Series Specifications

Body Size	3/8
Rated Pressure (psi)	10,000
Rated Flow (gpm)	6
Temperature Range	-40° to +250° F
Spillage (ML) (max. per disconnect)	0.020
Air Inclusion (ML) (max. per connect)	0.070

Materials of Construction

Body: Steel **Valve:** Flush Face Valving **Seal:** Anti Blow-out Nitrile/PTFE Bonded Seal (nipple only)

Finish: Chromium-6 Free plating

Optional Materials and Features:

(add code to part number)

Optional seals include O-ring & Back-Up Ring, not Anti-Blow Out bonded seal. Contact QCD for availability and additional options. To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -E5	Ethylene Propylene seal material (EPR)	FH-371-6FP-E5
suffix -E4	Fluorocarbon seal material	FH-371-6FP-E4

Hydraulic Quick Couplings

Non-Spill

FH Series HTMA (High Pressure)

Push-to-Connect/Sleeve Lock



FH Series Couplers



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	FH-371-6FP	3/8 -18 NPTF	2.63	1.23	1.12	0.44
3/8	FH-371-6MP	3/8 -18 NPTF	2.85	1.23	1.12	0.45
3/8	FH-371-6FB	G3/8 -BSPP	2.63	1.23	1.12	0.45

FH Series Nipples



Body Size (in.)	Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	FH-372-6FP	3/8-18 NPTF	2.12	1.23	1.00	0.26
3/8	FH-372-6FB	G3/8 -BSPP	2.12	1.23	1.00	0.28

Standard Port Configurations: **FP** - Female Pipe Thread **MP** - Male Pipe Thread **FB** - Female British Parallel Pipe

FH Series Dust Caps



Body Size (in.)	Coupler Dust Cap - Rubber	Nipple Dust Cap - Rubber
3/8	NR-50	NR-37

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

FS Series Stainless Steel

Flush Face Valves, Chemical Compatibility



FS Series dry disconnect couplings are ideal for closed system transfer and dispensing of chemicals and other fluids. The flush valves eliminate spillage and air inclusion when connecting and disconnecting to result in minimal environmental contamination.



Features:

- Flush, non-spill valves enable ease of cleaning
- 316 stainless steel material for chemical compatibility
- Push to connect operation
- Fluorocarbon standard seal material with options available

Applications include:

- Chemical dispensing systems
- Chemical processing
- Food processing
- Corrosive media transfer

Temperature Range (continuous)

Part No. Seal Suffix	Seal Compound	Temp° F Rating
None*	Fluorocarbon	-15 to 400
E5	Ethylene Propylene (EPR)	-65 to 300
E1	Nitrile	-40 to 250
E35	Perfluoroelastomer (Contact QCD)	-20 to 600

*Fluorocarbon is standard seal.

FS Series Specifications

Body Size	Rated Pressure (psi)	Rated Flow (gpm)	Spillage (ml) max. per disconnect	Air Inclusion (ml) max. per connect	CV
1/4	2000	3	.015	.010	0.90
3/8	2000	6	.015	.020	1.80
1/2	2000	12	.020	.070	3.00
3/4	2000	28	.150	.100	7.00
1	2000	50	.250	.182	10.1

Materials of Construction


Machined Parts: Stainless Steel, AISI type 316 **Springs:** Stainless Steel, AISI type 316 **Backup Washers:** PTFE

Locking Balls: 1/4 - 3/8": 302 SS | 1/2 - 3/4": 316 SS | 1": 440 SS


Elastomer Seals: Fluorocarbon is standard. Wide range is available.

Performance

FS Series (1/4", 3/8", 1/2")
Test Fluid: Water



FS Series (3/4" & 1")
Test Fluid: Water



Hydraulic Quick Couplings

Non-Spill

FS Series Stainless Steel

Flush Face Valves, Chemical Compatibility



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix - E5	Ethylene Propylene seal material- EPR)	FS-371-6FP-E5
suffix - E12	Neoprene seal material	FS-371-6FP-E12

Standard Port Configurations: **FP** - Female Pipe Thread **MP** - Male Pipe Thread **FO** - Female Straight Thread

FS Series Couplers - Female Thread



Body Size (in.)	Coupler Part Number Steel	Thread Size	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	FS-251-4FP	1/4-18 NPT	1.79	1.06	1.00	0.25
1/4	FS-251-4MP	1/4-18 NPTF	2.00	1.06	1.00	0.25
1/4	FS-251-6FO	9/16-18 UNF	1.92	1.06	1.00	0.24
3/8	FS-371-6FP	3/8-18 NPT	2.52	1.30	1.06	0.58
3/8	FS-371-8FO	3/4-16 UNF	2.83	1.30	1.06	0.63
1/2	FS-501-8FP	1/2-14 NPT	2.74	1.58	1.38	0.92
1/2	FS-501-10FO	7/8-14 UNF	2.86	1.58	1.38	0.96
3/4	FS-751-12FP	3/4-14 NPT	3.63	1.99	1.75	2.00
3/4	FS-751-12FO	1-1/16-12 UNF	3.73	1.99	1.75	2.04
1	FS-1001-16FP	1-11 1/2 NPT	4.14	2.25	1.87	2.76
1	FS-1001-16FO	1-5/16-12 UNF	4.24	2.25	1.87	2.80

FS Series Nipples - Female Thread



Body Size (in.)	Coupler Part Number Steel	Thread Size	Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	FS-252-4FP	1/4-18 NPT	1.66	1.14	1.06	1.00	0.18
1/4	FS-252-4MP	1/4-18 NPTF	1.87	1.34	1.06	1.00	0.18
1/4	FS-252-6FO	9/16-18 UNF	1.78	1.26	1.06	1.00	0.17
3/8	FS-372-6FP	3/8-18 NPT	2.31	1.71	1.08	0.94	0.26
3/8	FS-372-8FO	3/4-16 UNF	2.45	1.71	1.19	1.06	0.30
1/2	FS-502-8FP	1/2-14 NPT	2.75	2.03	1.30	1.12	0.44
1/2	FS-502-10FO	7/8-14 UNF	2.85	2.11	1.30	1.12	0.48
3/4	FS-752-12FP	3/4-14 NPT	3.38	2.37	1.65	1.50	1.02
3/4	FS-752-12FO	1-1/16-12 UNF	3.38	2.37	1.65	1.50	1.02
1	FS-1002-16FP	1-11 1/2 NPT	3.89	2.60	2.17	1.87	1.60
1	FS-1002-16FO	1-5/16-12 UNF	3.89	2.51	2.17	1.87	1.64

* This dimension represents the portion of the nipple that is exposed when the nipple and coupler are connected.

Hydraulic Quick Couplings

Non-Spill

FS Series Stainless Steel

Flush Face Valves, Chemical Compatibility



Dust Caps - FS Series



Body Size	Coupler Dust Cap - Rubber	Nipple Dust Cap - Rubber
1/4	FR-25	FR-25
3/8	NR-50	NR-37
1/2	FR-501	FR-502
3/4	FR-751	FR-752
1	FR-1001	FR-1002



FS Series Repair Kits

Repair kits are available for both coupler and nipple half of FS coupling. Kits include replacement elastomer seals, valve assembly and instructions to perform rebuild. Spline tool must be ordered separately to accomplish coupler half repair. Other tools required: Vise, Allen Wrench and Open End Wrench.

FS Repair Kits

TOOL Spline tool for Coupler Repair	Replacement Seals	
	No Suffix	Fluorocarbon Seals
	E5	Ethylene Propylene (EPR)
	E35	Perfluoroelastomer (Contact Factory for Seal Options).

Nipple Repair Kits

1/4	FS-252-KIT	FS-252-KIT-E5
3/8	FS-372-KIT	FS-372-KIT-E5
1/2	FS-502-KIT	FS-502-KIT-E5
3/4	FS-752-KIT	FS-752-KIT-E5
1	FS-1002-KIT	FS-1002-KIT-E5

Coupler Repair Kits

1/4	FS-251-KIT	FS-251-KIT
3/8	FS-371-KIT	FS-371-KIT-E5
1/2	FS-501-KIT	FS-501-KIT-E5
3/4	FS-751-KIT	FS-751-KIT-E5
1	FS-1001-KIT	FS-1001-KIT-E5

Spline Tool

FF/FS-251-TOOL
FF/FS-371-TOOL
FS-501-TOOL
FF/FS-751-TOOL
FF/FS-1001-TOOL

Hydraulic Quick Couplings

Instrumentation

CPI Series

Push-to-Connect



Features:

- Simple push-pull action to connect and disconnect lines – no tools required
- Reliable, leak-tight O-ring seals for vacuum or pressure systems
- Positive valve stops prevent flow checking
- Valve guide positively aligns valve with seat to prevent leakage
- Durable ball-locking mechanism assures reliable connection while distributing the load and providing alignment and swiveling action

Applications include:

- Chemical Processing
- Semiconductor Manufacturing
- Oil & Gas Refining

Rated Working Pressure (PSI)

Body Size	1/4"	3/8"	1/2"
Connected	3000	1500	750
Disconnected	3000	1500	750
Connect Under Pressure*	250	250	250

CPI Series Specification

Vacuum Rating	Parker CPI Series will handle vacuums up to 50 millitorr or .05 mm of Hg absolute pressure.
---------------	---

Materials of Construction

Machined Parts: Stainless Steel AISI type 316

Springs: Stainless Steel AISI type 302


Locking Balls: Stainless Steel AISI type 302

Retaining Rings: Stainless Steel AISI type 302


Seals: Fluorocarbon is standard (Other materials available)

Performance


1/4" CPI Flow Data (Water)



3/8" CPI Flow Data (Water)



1/2" CPI Flow Data (Water)



Hydraulic Quick Couplings


Instrumentation

CPI Series

Push-to-Connect




CPI Series Couplers - Tube Ends



*Substitute "Z" for CPI or "A" for A-LOK®

Body Size (in.)	Part Number Stainless Steel	Tube Size	A	Hex B	Diameter C	D	D1	Hex E
1/4	2*-Q4CY-SSP	1/8	1.44	0.62	0.86	0.61	0.60	0.44
1/4	4*-Q4CY-SSP	1/4	1.41	0.62	0.86	0.70	0.70	0.56
3/8	6*-Q6CY-SSP	3/8	1.63	0.75	0.98	0.78	0.76	0.69
1/2	8*-Q8CY-SSP	1/2	2.03	0.94	1.17	0.91	0.87	0.88


CPI Series Couplers - Bulkhead Tube Ends



*Substitute "Z" for CPI or "A" for A-LOK®


Body Size (in.)	Part Number Stainless Steel	Tube Size	A	Hex B	Diameter C	D	D1	Hex E
1/4	4*H-Q4CY-SSP	1/4	1.41	0.62	0.86	1.09	1.09	0.56
3/8	6*H-Q6CY-SSP	3/8	1.63	0.75	0.98	1.20	1.18	0.69
1/2	8*H-Q8CY-SSP	1/2	2.03	0.94	1.17	1.38	1.34	0.88

CPI Series Couplers - Male Pipe



Body Size (in.)	Part Number Stainless Steel	Thread Size/NPT	A	Hex B	Diameter C
1/4	2M-Q4CY-SSP	1/8	1.78	0.62	0.86
1/4	4M-Q4CY-SSP	1/4	1.97	0.62	0.86
3/8	4M-Q6CY-SSP	1/4	2.19	0.75	0.98
3/8	6M-Q6CY-SSP	3/8	2.19	0.75	0.98
1/2	8M-Q8CY-SSP	1/2	2.78	0.94	1.17

CPI Series Couplers - Female Pipe



Body Size (in.)	Part Number Stainless Steel	Thread Size/NPT	A	Hex B	Diameter C
1/4	2F-Q4CY-SSP	1/8	1.91	0.62	0.86
1/4	4F-Q4CY-SSP	1/4	2.22	0.75	0.86
3/8	4F-Q6CY-SSP	1/4	2.36	0.75	0.98
3/8	6F-Q6CY-SSP	3/8	2.38	0.88	0.98
1/2	8F-Q8CY-SSP	1/2	3.03	1.06	1.17

Hydraulic Quick Couplings


Instrumentation

CPI Series

Push-to-Connect




CPI Series Couplers - Push-Lok



Body Size (in.)	Part Number Stainless Steel	Hose I.D.	A	Hex B	Diameter C
1/2	6PL-Q8CY-SSP	3/8	3.00	0.94	1.17


CPI Series Valved Nipples - Tube Ends



*Substitute "Z" for CPI or "A" for A-LOK®


Body Size (in.)	Part Number Stainless Steel	Tube Size	A	Hex B	Diameter C	D	D1	Hex E
1/4	2*-Q4VY-SS	1/8	2.45	0.44	0.62	0.61	0.60	0.44
1/4	4*-Q4VY-SS	1/4	1.95	0.44	0.62	0.70	0.70	0.56
3/8	6*-Q6VY-SS	3/8	2.00	0.56	0.74	0.78	0.76	0.69
1/2	8*-Q8VY-SS	1/2	2.45	0.75	0.88	0.91	0.87	0.88

CPI Series Valved Nipples - Male Pipe



Body Size (in.)	Part Number Stainless Steel	Thread Size/NPT	A	Hex B	Diameter C
1/4	2M-Q4VY-SS	1/8	2.58	0.44	0.62
1/4	4M-Q4VY-SS	1/4	2.24	0.56	0.62
3/8	4M-Q6VY-SS	1/4	2.15	0.56	0.74
3/8	6M-Q6VY-SS	3/8	2.30	0.75	0.74
1/2	8M-Q8VY-SS	1/2	2.84	0.88	0.88

CPI Series Valved Nipples - Female Pipe



Body Size (in.)	Part Number Stainless Steel	Thread Size/NPT	A	Hex B	Diameter C
1/4	2F-Q4VY-SS	1/8	2.04	0.56	0.62
1/4	4F-Q4VY-SS	1/4	2.25	0.75	0.62
3/8	4F-Q6VY-SS	1/4	2.28	0.75	0.74
1/2	8F-Q8VY-SS	1/2	2.87	1.06	0.88

Hydraulic Quick Couplings

Instrumentation

CPI Series

Push-to-Connect




CPI Series Valved Nipples - Push-Lok



Body Size (in.)	Part Number Stainless Steel	Hose I.D.	A	Hex B	Diameter C
1/2	6PL-Q8VY-SS	3/8	3.56	0.75	0.88

CPI Series Non-Valved Nipples - Tube Ends



Body Size (in.)	Part Number Stainless Steel	Tube Size	A	Hex B	Diameter C	D	D1	Hex E
1/4	2*-Q4P-SS	1/8	2.45	0.44	0.62	0.61	0.60	0.44
1/4	4*-Q4P-SS	1/4	1.95	0.44	0.62	0.70	0.70	0.56
3/8	6*-Q6P-SS	3/8	2.00	0.56	0.74	0.78	0.76	0.69
1/2	8*-Q8P-SS	1/2	2.45	0.75	0.88	0.91	0.87	0.88

*Substitute "Z" for CPI or "A" for A-LOK®

**Non-valved nipples come with non-colored sleeves

CPI Series Non-Valved Nipples - Male Pipe



Body Size (in.)	Part Number Stainless Steel	Thread Size/NPT	A	Hex B	Diameter C
1/4	2M-Q4P-SS	1/8	2.58	0.44	0.62
1/4	4M-Q4P-SS	1/4	2.24	0.56	0.62
3/8	4M-Q6P-SS	1/4	2.15	0.56	0.74
3/8	6M-Q6P-SS	3/8	2.30	0.75	0.74
1/2	8M-Q8P-SS	1/2	2.84	0.88	1.88

CPI Series Non-Valved Nipples - Female Pipe



Body Size (in.)	Part Number Stainless Steel	Thread Size/NPT	A	Hex B	Diameter C
1/4	2F-Q4P-SS	1/8	2.04	0.56	0.62
3/8	4F-Q4P-SS	1/4	2.25	0.75	0.62
3/8	4F-Q6P-SS	1/4	2.28	0.75	0.74
1/2	8F-Q8P-SS	1/2	2.87	1.06	0.88

Hydraulic Quick Couplings


Instrumentation

CPI Series

Push-to-Connect




CPI Series - Coupler Protectors



Body Size (in.)	Part Number Stainless Steel	A	Hex B	Diameter C
1/4	CP-Q4C-SS	1.75	0.44	0.62
3/8	CP-Q6C-SS	1.78	0.56	0.74
1/2	CP-Q8C-SS	1.94	0.69	0.88

* Protectors are not pressure containing


CPI Series - Nipple Protectors



Body Size (in.)	Part Number Stainless Steel	A	Hex B	Diameter C
1/4	VP-Q4V-SSP	1.37	0.62	0.86
3/8	VP-Q6V-SSP	1.44	0.75	0.98
1/2	VP-Q8V-SSP	1.72	0.94	1.17

* Protectors are not pressure containing

Ordering Guide



Note: Some options are non-standards and will need to be quoted on special basis.

Hydraulic Quick Couplings

High Pressure

59 Series High pressure, Non-Spill

Screw-to-Connect



59 Series couplings are ideal for use in high pressure, high impulse applications that require the security of a threaded connection and the ability to connect and disconnect under pressure. The robust ACME thread has a double start and allows full connection to be quickly completed in 2-1/2 turns. An internal bearing between the collar and the body keeps resistance to a minimum for an easy connection.



Features:

- Up to 6000 psi operating pressure
- Connect under residual pressure up to 5000 psi
- Disconnect under residual pressure up to 2500 psi
- Double start ACME threads provide a quick and strong connection
- High impulse resistance
- High strength materials
- Zinc nickel coating for extended durability and corrosion resistance
- Flat-face, non-spill design
- Visual and tactile confirmation when full connection is complete

Applications include:


- Mobile drill rigs
- Oil field equipment
- Umbilical lines
- High impulse mobile circuits
- Excavator attachments

59 Series Specification


Temperature Range	Seal Material	Body Material	Valve Material	Sleeve Type	Plating
-40° to +250° F	Nitrile/Polyurethane	Steel	Stainless Steel	Thread to Connect	Zinc Nickel Plating/ FNC Coating

Performance

59 Series (1/2" & 3/4")
Test Fluid: Oil - 150 SUS



59 Series (1" & 1-1/2")
Test Fluid: Oil - 150 SUS



59 Series Nipple O-Ring

Body Size	Replacement External O-Ring on Nipple
1/2	4317-2-219
3/4	4317-2-224
1	4317-2-226
1 1/2	4317-2-234

Hydraulic Quick Couplings

High Pressure


59 Series

High pressure, Non-Spill

Screw-to-Connect




59 Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)	Rated Pressure (psi)
1/2	59-501-8FP	1/2 - 14 NPSF	3.70	2.05	1-1/2 in	1-7/8 in	1.35	6000
1/2	59-501-8FO	3/4 - 16 UNF	3.74	2.05	1-1/2 in	1-7/8 in	1.37	6000
3/4	59-751-12FP	3/4 - 14 NPTF	5.53	2.49	2-3/8 in	2 in	3.72	6000
3/4	59-751-12FO	1 1/16 - 12 UNF	5.34	2.49	2-3/8 in	2 in	3.68	6000
1	59-1001-16FP	1 - 11 1/2 NPTF	5.82	2.75	65 mm	2-3/16 in	4.82	6000
1	59-1001-16FO	1 5/16 - 12 UNF	5.82	2.75	65 mm	2-3/16 in	4.77	6000
1-1/2	59-1501-20FP	1 1/4 - 11 1/2 NPTF	7.08	3.74	90 mm	2-5/8 in	9.92	5000
1-1/2	59-1501-20FO	1 5/8 - 12 UNF	7.08	3.74	90 mm	2-5/8 in	9.67	5000
1-1/2	59-1501-24FP	1 1/2 - 11 1/2 NPTF	7.08	3.74	90 mm	2-5/8 in	9.92	5000
1-1/2	59-1501-24FO	1 7/8 - 12 UNF	7.08	3.74	90 mm	2-5/8 in	9.67	5000

59 Series Nipples



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)	Rated Pressure (psi)
1/2	59-502-8FP	1/2 - 14 NPSF	3.50	1.88	1-3/4 in	1-1/8 in	1.07	6000
1/2	59-502-8FO	3/4 - 16 UNF	3.50	1.88	1-1/2 in	1-7/8 in	1.07	6000
3/4	59-752-12FP	3/4 - 14 NPTF	4.65	2.31	55 mm	2 in	2.81	6000
3/4	59-752-12FO	1 1/16 - 12 UNF	4.77	2.31	55 mm	2 in	2.87	6000
1	59-1002-16FP	1 - 11 1/2 NPTF	5.12	2.75	65 mm	2-3/16 in	4.42	6000
1	59-1002-16FO	1 5/16 - 12 UNF	5.12	2.75	65 mm	2-3/16 in	4.38	6000
1-1/2	59-1502-20FP	1 1/4 - 11 1/2 NPTF	5.94	3.75	75 mm	2-5/8 in	8.33	5000
1-1/2	59-1502-20FO	1 5/8 - 12 UNF	5.94	3.75	75 mm	2-5/8 in	8.29	5000
1-1/2	59-1502-24FP	1 1/2 - 11 1/2 NPTF	5.94	3.75	75 mm	2-5/8 in	8.33	5000
1-1/2	59-1502-24FO	1 7/8 - 12 UNF	5.94	3.75	75 mm	2-5/8 in	8.29	5000

59 Series Nipple Dust Cap



Body Size	Nipple Dust Cap
1/2	595DC-01
3/4	597DC-01
1	5910DC-01
1-1/2	5915DC-01

59 Series Coupler Dust Plug



Body Size	Nipple Dust Cap
1/2	595DP-01
3/4	597DP-01
1	5910DP-01
1-1/2	5915DP-01

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Non-Spill

FET Series Connect Under Pressure

Screw-to-Connect



FET Series couplings are built to be used in high pressure, high impulse applications that require the security of a threaded connection and the ability to connect and disconnect under residual pressure. Interchanges with similar European style thread-to-connect couplings.



Features:

- Connect under residual pressure up to 5000 psi
- Disconnect under residual pressure up to 2500 psi
- High impulse resistance
- High strength materials
- FNC coating for extended durability and corrosion resistance
- Visual connection indicator

Applications include:

- Mobile drill rigs
- Oil field equipment
- Umbilical lines
- High impulse mobile circuits
- Excavator attachments

FET Series Specifications

Body Size (in)	Euro Size	Port End	Rated Pressure (psi)	Temperature Range	Body Material	Sleeve Type	Seal Material
3/8	9	Female ORB	6000	-40° to +250°F	Steel	Thread to Connect	Nitrile/ Polyurethane
		Female NPTF	6000				
1/2	13	Female ORB	6000				
		Female NPTF	6000				
5/8	15	Female ORB	5000				
		Female NPTF	5000				
3/4	17	Female ORB	5000				
		Female NPTF	5000				
		Code 62 Flange Head	6000				
		Code 62 Flange Pad	6000				
1	21	Female ORB	6000				
		Female NPTF	6000				
		Code 62 Flange Head	6000				
		Code 62 Flange Pad	6000				
1-1/2	30	Female ORB	5000				
		Female NPTF	5000				
		Code 62 Flange Head	5000				
		Code 62 Flange Pad	5000				
2	45	Female ORB	5000				
		Female NPTF	5000				

Hydraulic Quick Couplings

Non-Spill


FET Series Connect Under Pressure

Screw-to-Connect




Performance


FET Series (3/8", 1/2", 5/8" & 3/4")
Test Fluid: Oil - 150 SUS)



FET Series (1", 1-1/2" & 2")
Test Fluid: Oil - 150 SUS)



FET Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)
3/8	FET-371-8FO	3/4 - 16 UNF	3.83	1.65	38 mm	30 mm	0.91
3/8	FET-371-8FP	1/2 - 14 NPTF	3.91	1.65	38 mm	30 mm	0.92
1/2	FET-501-10FO	7/8 - 14 UNF	3.82	2.05	48 mm	1-1/2 in	1.40
1/2	FET-501-8FP	1/2 - 14 NPTF	3.70	2.05	48 mm	1-1/2 in	1.38
5/8	FET-621-12FO	1 1/16 - 12 UNF	4.66	2.12	50 mm	1-5/8 in	2.06
5/8	FET-621-12FP	3/4 - 14 NPTF	4.52	2.12	50 mm	1-5/8 in	2.03
3/4	FET-751-16FO	1 5/16 - 12 UNF	5.44	2.31	55 mm	2 in	3.30
3/4	FET-751-16FP	1 - 11 1/2 NPTF	5.44	2.31	55 mm	2 in	3.35
1	FET-1001-20FO	1 5/8 - 12 UNF	5.83	2.75	65 mm	2-3/16 in	4.72
1	FET-1001-20FP	1 1/4 - 11 1/2 NPTF	5.83	2.75	65 mm	2-3/16 in	4.76
1-1/2	FET-1501-24FO	1 7/8 - 12 UNF	7.08	3.75	85 mm	2-5/8 in	10.01
1-1/2	FET-1501-24FP	1 1/2 - 11 1/2 NPTF	7.08	3.75	85 mm	2-5/8 in	10.06
2	FET-2001-32FO	2 1/2 - 12 UN	11.67	7.52	-	3-3/4 in	33.73
2	FET-2001-32FP	2 - 11 1/2 NPTF	11.67	7.52	-	3-3/4 in	33.05

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings



Non-Spill

FET Series Connect Under Pressure

Screw-to-Connect




FET Series Couplers - Code 62 Flange



Body Size (in.)	Coupler Part Number Steel	Port End	Bolt Thread Size	Length (in.)	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)
3/4	FET-751-16SF	Flange Head	-	7.60	2.31	55 mm	2 in	4.17
3/4	FET-751-16SFP	Flange Pad	7/16 - 14 UNC	5.45	2.31	55 mm	2-3/4 in	4.82
1	FET-1001-20SF	Flange Head	-	7.78	2.75	65 mm	2-3/16 in	5.44
1	FET-1001-20SFP	Flange Pad	1/2 - 13 UNC	5.83	2.75	65 mm	3 in	6.90
1-1/2	FET-1501-24SF	Flange Head	-	9.83	3.75	85 mm	2-5/8 in	11.37
1-1/2	FET-1501-24SFP	Flange Pad	5/8 - 11 UNC	6.82	3.75	85 mm	2-5/8 in	13.31

FET Series Nipples



Body Size (in.)	Nipple Part Number Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)
3/8	FET-372-8FO	3/4 - 16 UNF	3.51	2.31	55 mm	2 in	4.17
3/8	FET-372-8FP	1/2 - 14 NPTF	5.45	2.31	55 mm	2-3/4 in	4.82
1/2	FET-502-10FO	7/8 - 14 UNF	7.78	2.75	65 mm	2-3/16 in	5.44
1/2	FET-502-8FP	1/2 - 14 NPTF	5.83	2.75	65 mm	3 in	6.90
5/8	FET-622-12FO	1 1/16 - 12 UNF	9.83	3.75	85 mm	2-5/8 in	11.37
5/8	FET-622-12FP	3/4 - 14 NPTF	6.82	3.75	85 mm	2-5/8 in	13.31
3/4	FET-752-16FO	1 5/16 - 12 UNF	7.60	2.31	55 mm	2 in	4.17
3/4	FET-752-16FP	1 - 11 1/2 NPTF	5.45	2.31	55 mm	2-3/4 in	4.82
1	FET-1002-20FO	1 5/8 - 12 UNF	7.78	2.75	65 mm	2-3/16 in	5.44
1	FET-1002-20FP	1 1/4 - 11 1/2 NPTF	5.83	2.75	65 mm	3 in	6.90
1-1/2	FET-1502-24FO	1 7/8 - 12 UNF	9.83	3.75	85 mm	2-5/8 in	11.37
1-1/2	FET-1502-24FP	1 1/2 - 11 1/2 NPTF	6.82	3.75	85 mm	2-5/8 in	13.31
2	FET-2002-32FO	2 1/2 - 12 UN	9.83	3.75	85 mm	2-5/8 in	11.37
2	FET-2002-32FP	2 - 11 1/2 NPTF	6.82	3.75	85 mm	2-5/8 in	13.31

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings



Non-Spill

FET Series Connect Under Pressure

Screw-to-Connect



FET Series Nipples - Code 62 Flange



Body Size (in.)	Coupler Part Number Steel	Port End	Bolt Thread Size	Length (in.)	Largest Diameter	Wrench Flats 1	Wrench Flats 2	Weight (lbs.)
3/4	FET-752-16SF	Flange Head	-	6.32	2.31	55 mm	2 in	3.10
3/4	FET-752-16SFP	Flange Pad	7/16 - 14 UNC	4.74	2.31	55 mm	2-3/4 in	4.33
1	FET-1002-20SF	Flange Head	-	6.70	2.75	65 mm	2-3/16 in	4.71
1	FET-1002-20SFP	Flange Pad	1/2 - 13 UNC	5.27	2.75	65 mm	3 in	6.78
1-1/2	FET-1502-24SF	Flange Head	-	7.77	3.75	75 mm	2-5/8 in	8.08
1-1/2	FET-1502-24SFP	Flange Pad	5/8 - 11 UNC	5.94	3.75	75 mm	2-5/8 in	12.17

FET Series Dust Caps and Plugs



Body Size	Nipple Dust Cap	Coupler Dust Plug
3/8	FET3DC-01	FET3DP-01
1/2	FET5DC-01	FET5DP-01
5/8	FET6DC-01	FET6DP-01
3/4	FET7DC-01	FET7DP-01
1	FET10DC-01	FET10DP-01
1-1/2	FET15DC-01	FET15DP-01
2	FET20DC-01	FET20DP-01

FET Series Nipple Replacement O-Ring

Body Size	O-Ring Part Number	Ref Nipple Part Number
3/8	50001-122-0160	FET-372
1/2	50001-219-0160	FET-502
5/8	50001-222-0160	FET-622
3/4	50001-224-0160	FET-752
1	50001-226-0160	FET-1002
1-1/2	50001-335-0160	FET-1502
2	50001-351-0160	FET-2002

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings


Connect Under Pressure

6100 Series Threaded Connection

Flush Valves, High Flow



6100 Series is a thread to connect, low spill coupling that can be connected under pressure. Coupler and nipple bodies are corrosion resistant brass. Couplers are available with a steel hex nut or heavy duty wing nut sleeve. A connection indicator groove on the nipple body indicates when the connection is complete and the valves are fully open.



Features:

- Rated pressures up to 3000 psi
- Thread to connect operation
- Bonded valve seal stays in place under full pressure connect and disconnect
- Visual connection indicator
- Rugged wing nut sleeve will withstand hammering to tighten or loosen
- Optional flange for secure bulkhead mounting
- Standard end configuration is female pipe thread
- Special part numbers apply for CO₂ transfer (contact QCD)

Applications include:

- Submersible pumps
- Oil field equipment
- Dump trailers
- Engine test stands
- Bulk liquid transfer

6100 Series Specifications


Body Size	3/4	3/4	1	1 - 1/4	1 - 1/2
Dash Number	-08	-12	-16	-20	-24
Rated Pressure (psi) *					
Female Half	3,000	3,000	3,000	2,750	2,000
Male Half	3,000	3,000	3,000	2,500	2,500
Complete Coupling Assembly	3,000	3,000	3,000	2,750	2,500
Rated Flow (gpm)	12	28	50	76	100
Temperature Range (std seals)	-20° to +200°F				
Seal Material**	Nitrile				

* Not recommended for continuous hydraulic impulse applications at rated pressures.


** Contact the Division for alternate seal material availability.

Performance

6100 Series (1/2" & 3/4")
Test Fluid: OIL 150 SUS



6100 Series (1", 1-1/4", 1-1/2")
Test Fluid: OIL 150 SUS



Hydraulic Quick Couplings

Connect Under Pressure

6100 Series Threaded Connection

Flush Valves, High Flow



6100 Series - Coupling Set with Wingnut



Body Size (in.)	Part Number with Flange Brass	Part Number Without Flange Brass	Thread Size	Overall Connected Length (in.)	Weight (lbs.)
3/4	6100-08	6120-08	1/2-14 NPTF	5.20	2.12
3/4	6100-12	6120-12	3/4-14 NPTF	5.32	2.00
1	6100-16	6120-16	1-11 1/2 NPTF	5.99	3.19
1-1/4	6100-20	6120-20	1 1/4-11 1/2 NPTF	6.48	4.25
1-1/2	6100-24	6120-24	1 1/2-11 1/2 NPTF	6.80	6.13

6100 Series - Coupling Set with Hex Nut



Body Size (in.)	Part Number with Flange Brass	Part Number Without Flange Brass	Thread Size	Overall Connected Length (in.)	Weight (lbs.)
3/4	6110-08	6130-08	1/2-14 NPTF	5.20	1.89
3/4	6110-12	6130-12	3/4-14 NPTF	5.20	1.83
1	6110-16	6130-16	1-11 1/2 NPTF	5.99	2.93
1-1/4	6110-20	6130-20	1 1/4-11 1/2 NPTF	6.33	4.12
1-1/2	6110-24	6130-24	1 1/2-11 1/2 NPTF	6.55	5.95

6100 Series Nipples



Body Size (in.)	Part Number Without Flange Brass	Part Number With Flange Brass	Thread Size	Overall Length (in.)	Wrench Flats	Hex Size	Weight (lbs.)
3/4	6105-08	6115-08	1/2-14 NPTF	3.11	1.18	1.62	0.75
3/4	6105-12	6115-12	3/4-14 NPTF	3.23	1.18	1.62	0.76
1	6105-16	6115-16	1-11 1/2 NPTF	3.55	1.56	1.88	1.30
1-1/4	6105-20	6115-20	1 1/4-11 1/2 NPTF	3.71	1.88	2.13	1.65
1-1/2	6105-24	6115-24	1 1/2-11 1/2 NPTF	4.12	2.18	2.50	2.61

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Connect Under Pressure

6100 Series Threaded Connection

Flush Valves, High Flow



6100 Series Couplers - Wingnut



Body Size (in.)	Part Number Brass	Thread Size	Overall Length (in.)	Wrench Flats	Wing Nut	Weight (lbs.)
3/4	6125-08	1/2-14 NPTF	3.22	1.16	4.06	1.30
3/4	6125-12	3/4-14 NPTF	3.22	1.16	4.06	1.26
1	6125-16	1-11 1/2 NPTF	3.87	1.43	4.38	1.96
1-1/4	6125-20	1 1/4-11 1/2 NPTF	4.16	1.78	5.20	2.84
1-1/2	6125-24	1 1/2-11 1/2 NPTF	4.34	2.00	5.32	3.72

6100 Series Couplers - Hex Nut



Body Size (in.)	Part Number Brass	Thread Size	Overall Length (in.)	Wrench Flats	Hex Size	Weight (lbs.)
3/4	6135-08	1/2-14 NPTF	3.22	1.16	1.75	1.07
3/4	6135-12	3/4-14 NPTF	3.22	1.16	1.75	1.07
1	6135-16	1-11 1/2 NPTF	3.87	1.43	2.13	1.89
1-1/4	6135-20	1 1/4-11 1/2 NPTF	4.16	1.78	2.50	2.56
1-1/2	6135-24	1 1/2-11 1/2 NPTF	4.34	2.00	2.75	3.15

6100 Series Nipple Dust Cap



Body Size	Nipple Dust Cap
3/4	6108
1	597DC-01
1-1/4	5910DC-01
1-1/2	5915DC-01

6100 Series Coupler Dust Plug



Body Size	Nipple Dust Plug
3/4	595DP-01
1	597DP-01
1-1/4	5910DP-01
1-1/2	5915DP-01

6100 Series - Mounting Flanges



Body Size	Part Number Steel	Bolt Hole Diameter	Bolt Circle Diameter
3/4	6107-08 (1 piece)	0.208	2.13
1	6107-16 (1 piece)	0.208	2.38
1-1/4	6107-20 (2 piece)	0.208	2.63
1-1/2	6107-24 (2 piece)	0.281	3.25

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Connect Under Pressure

8200 Series

Push/Pull/Breakaway Sleeve

Accepts ISO 5675 Nipples



Parker's 8200 Series unique valve design allows connection while either or both the coupler and nipple are under pressure. Valves in both halves remain closed, opening only when system pressure has been relieved on the female body and then reapplied. This pressure sequence may be done with either an open center or a closed center hydraulic system that has a control valve.



Features:

- Accepts ISO 5675 universal tips
- Connect under system pressure on the coupler side and residual pressure on the nipple side
- Sleeve designed to accommodate bracket mounting
- One-handed push-to-connect operation when coupler is clamp mounted
- 1/2" body size couplers are compatible with 5001-4 and 5006-4 breakaway clamps
- Critical parts are hardened
- Protective zinc plating with clear trivalent chromate finish

Applications include:


- Tractors
- Mid-sized agricultural equipment
- Agricultural attachments requiring breakaway

8200 Series Specification

Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
1/2	12	3000	-40° F to +250° F	Steel	Push/pull/break away	Nitrile

Performance

8200 Series (1/2")
Test Fluid: Oil - 200 SUS



8200 Series Replacement Parts

Body Size	Part Number	Description	Material
1/2	50005-211-0200	O-Ring	Nitrile

Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix W	Ethylene Propylene seal material - EPR (Couplers)	8250-15W
suffix Y	Fluorocarbon seal material (Couplers)	8250-15Y
suffix Z	Neoprene seal material (Couplers)	8250-15Z

Hydraulic Quick Couplings

Connect Under Pressure

8200 Series

Push/Pull/Breakaway Sleeve

Accepts ISO 5675 Nipples



8200 Series Couplers - Female Thread



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)	Complete Coupling Part Number
1/2	8250-4	1/2-14 NPSF	Poppet	3.29	1.50	0.87	0.63	8200-4
1/2	8250-15	3/4-16 ORB	Poppet	3.29	1.50	0.87	0.63	8200-15
1/2	8250-16	7/8-14 ORB	Poppet	3.29	1.50	0.87	0.63	8200-16

8010 Series Nipples - Female Thread



Body Size (in.)	Nipple Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)	Complete Coupling Part Number
1/2	8010-4	1/2-14 NPTF	Ball	1.95	1.23	1.06	0.20	8200-4
1/2	8010-4P	1/2-14 NPTF	Poppet	1.95	1.23	1.06	0.20	-
1/2	8010-15	3/4 -16 ORB	Ball	1.95	1.23	1.06	0.20	8200-15
1/2	8010-15P	3/4 -16 ORB	Poppet	1.95	1.23	1.06	0.20	-
1/2	8010-16	7/8 -14 ORB	Ball	1.95	1.23	1.06	0.25	8200-16
1/2	8010-16P	7/8 -14 ORB	Poppet	1.95	1.23	1.06	0.25	-

8200 Series Dust Caps and Plugs



Body Size (in.)	Dust Plug - Coupler	Color/Material	Dust Cap - Nipple	Weight (lbs.)
1/2	5205-4M	Black Rubber	5209-4M	0.04
1/2	5005-4	Steel w/Chain	5009-4	0.21
1/2	5205-4M-BU	Blue Rubber	5209-4M-BU	0.04
1/2	5205-4M-GR	Green Rubber	5209-4M-GR	0.04
1/2	5205-4M-RE	Red Rubber	5209-4M-RE	0.04
1/2	5205-4M-YE	Yellow Rubber	5209-4M-YE	0.04

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Connect Under Pressure

9200 Series Lever Actuated

Accepts ISO 5675 Nipples



The 9200 Series coupler allows zero pressure connection and disconnection while either or both the coupler and nipple are under pressure. A lever operated cam locks both coupler and nipple valves in the open or closed position. "Closed", the flow is shut off at the coupl , allowing easy connect and disconnect. Valves in the "Open" position are locked in place and unaffected by hyd aulic surges. Valves will automatically close if the coupling is accidentally disconnected.

Features:

- Accepts ISO 5675 universal tips
- Premier connect under pressure coupling
- Locked valves prevent flow checking
- Functionally can replace a double shut-off quick coupling and two high pressure ball valves
- Protective zinc plating with clear trivalent chromate finish

Applications include:

- Mobile equipment
- Industrial hydraulics
- Not recommended for use with gaseous or compressible media




9200 Series Specification

Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
1/2	12	3000	-40° F to +250° F	Steel	Push/pull/breakaway	Nitrile

Performance

9200 Series (1/2")
Test Fluid: Oil - 200 SUS



9200 Series Replacement Parts

Body Size	Part Number	Description	Weight (lbs.)
1/2	50001-211-0260	Interface O-Ring	0.01

Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix W	Ethylene Propylene seal material - EPR (Couplers)	9250-4-320W
suffix Y	Fluorocarbon seal material (Couplers)	9250-4-320Y
suffix Z	Neoprene seal material (Couplers)	9250-4-320Z

Hydraulic Quick Couplings

Connect Under Pressure

9200 Series Lever Actuated

Accepts ISO 5675 Nipples



9200 Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Orientation	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/2	9250-4-320*	1/2-14 NPTF	Poppet	Left hand – yellow grip	5.37	1.50	1.13	1.98
1/2	9250-6-320*	9/16-18 UNF	Poppet	Left hand – yellow grip	5.37	1.50	1.13	2.06
1/2	9250-15-320*	3/4-16 UNF	Poppet	Left hand – yellow grip	5.37	1.50	1.13	2.06
1/2	9250-16-320*	7/8-14 UNF	Poppet	Left hand – yellow grip	5.37	1.50	1.13	2.06
1/2	9250-334**	9/16-18 UNF	Poppet	Left hand – yellow grip	5.37	1.50	1.13	2.15

* -320 indicates lower sleeve spring force for easier connection when coupler is not mounted in a clamp.

** -334 couplers connect with 1/4" ISO 7241-B series nipples.

8010 Series Nipples



Body Size (in.)	Nipple Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	H2-63-T6*	9/16-18 ORB	Poppet	1.54	1.01	0.88	0.10
1/2	8010-4	1/2-14 NPTF	Ball	1.95	1.23	1.06	0.20
1/2	8010-4P	1/2-14 NPTF	Poppet	1.95	1.23	1.06	0.20
1/2	8010-15	3/4-16 ORB	Ball	1.95	1.23	1.06	0.20
1/2	8010-15P	3/4-16 ORB	Poppet	1.95	1.23	1.06	0.20
1/2	8010-16	7/8-14 ORB	Ball	1.95	1.23	1.06	0.25
1/2	8010-16P	7/8-14 ORB	Poppet	1.95	1.23	1.06	0.25

* Connects with 9250-334 couplers

9200 Series Dust Caps and Plugs



Body Size (in.)	Dust Cover - Coupler	Color/Material	Dust Cap - Nipple	Weight (lbs.)
1/2	9507-4-1	Black Rubber	5209-4M	0.04

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Connect Under Pressure

5000 Series
Threaded Actuation

Accepts ISO 5675 Nipples



The 5000 Series is an economical coupling that can be connected under pressure where tools can be used to make the connection. The coupler and nipple are connected and then the valves are opened from tightening the threaded union on the back of the coupler body. Unscrewing the body threads will permit the valves to close and the coupler sleeve can be retracted to release the nipple.



Features:

- Accepts ISO 5675 universal tips
- Manual, threaded actuation, connect under pressure coupling
- Protective zinc plating with clear trivalent chromate finish

Applications include:


- Lubrication systems
- Hydraulic tools
- Attachments

5000 Series Specification

Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
1/2	12	2500	-40° F to +250° F	Steel	Single Acting	Nitrile

Performance

5000 Series (1/2")
Test Fluid: Oil - 200 SUS



5000 Replacement Parts

	1/2
O-Rings - Nitrile	50001-211-0260

Optional Materials and Features:
(add code to part number)

Contact QCD for availability and additional options.
To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix W	Ethylene Propylene seal material - EPR (Couplers)	5050-4W
suffix Y	Fluorocarbon seal material (Couplers)	5050-4Y
suffix Z	Neoprene seal material (Couplers)	5050-4Z

Hydraulic Quick Couplings

Connect Under Pressure

5000 Series Threaded Actuation

Accepts ISO 5675 Nipples



5000 Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)	Complete Coupling Part Number
1/2	5050-4	1/2-14 NPTF	Ball	2.88	1.52	1.25	2.58	5000-4

8010 Series Nipples



Body Size (in.)	Nipple Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)	Complete Coupling Part Number
1/2	8010-4	1/2-14 NPTF	Ball	1.95	1.23	1.06	0.20	5000-4
1/2	8010-15	3/4-16 ORB	Ball	1.95	1.23	1.06	0.20	-
1/2	8010-16	7/8-14 ORB	Ball	1.95	1.23	1.06	0.20	-

5000 Series Dust Caps and Plugs



Body Size (in.)	Dust Plug - Coupler	Color/Material	Dust Cap - Nipple	Weight (lbs.)
1/2	5205-4M	Black Rubber	5209-4M	0.04
1/2	5205-4M-BU	Blue Rubber	5209-4M-BU	0.04
1/2	5205-4M-GR	Green Rubber	5209-4M-GR	0.04
1/2	5205-4M-RE	Red Rubber	5209-4M-RE	0.04
1/2	5205-4M-YE	Yellow Rubber	5209-4M-YE	0.04
1/2	5005-4	Steel w/Chain	5009-4	0.21

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Connect Under Pressure

75 Series Threaded Connection

Poppet Valves, High Pressure



The rugged 75 Series is an original Snap-tite design, constructed for high pressure hydraulic service. Although these couplings are used in a broad variety of heavy duty applications, a primary usage is in oil fields and offshore drilling. Available in sizes 3/4" through 4", in steel or stainless steel construction.



Features:

- Connect under residual pressure
- Thread-to-connect
- Up to 5,000 psi (345 bar) rated pressures
- Rugged steel construction with Zinc Trivalent Chromate plating
- Stainless steel construction also available
- Wide range of sizes
- Nitrile is standard seal material, other options available
- DBP version is "Fire Safe" rated to API 16D (limited sizes)

Applications include:

- Cranes
- Power tongs
- Horizontal boring and dewatering

75 Series Specification

Body Size	3/4	1	1-1/4	1-1/2	2	2-1/2	3	4
Spillage (cc)	8	16	31	64	141	204	320	400
Air Inclusion (cc)	12	25	48	98	205	368	480	610

75 Series Pressure Ratings

Body Size	Maximum Working Pressure (psi) Steel Only	Minimum Burst Pressure (psi) Steel Only	Maximum Working Pressure (psi) 316 Stainless (Connected Only)
3/4	5000	20000	3000
1	5000	20000	3000
1-1/4	5000	15000	3000
1-1/2	5000	15000	3000
2	5000	15000	3000
2-1/2	3000	6000	-
3	3000	6000	-
4	400	1000	-

Burst pressures listed were taken at the point at which failure rendered the quick-disconnect inoperative.

(Proof pressure equals 1-1/2 times the operating pressure).

NOTE: Pressure Ratings were established under static pressure conditions.

For impulse applications, multiply the above pressure ratings by .6 for approximate pressure ratings.

- Contact QCD

Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix V	Fluorocarbon seal material	75C12-12 FV
suffix E	Ethylene Propylene seal material (EPR)	75C12-12 FE
suffix W	Wrench flats on body (standard on 2-1/2" and larger, no code required)	75C12-12 FW
suffix DBP	"Fire Safe" BOP version (limited sizes, no alternate seal options)	SB-75C12-12F- DBP

Hydraulic Quick Couplings

Connect Under Pressure


75 Series Threaded Connection

Poppet Valves, High Pressure




Performance

Torque Values for Connecting Under Pressure



Flow Chart



75 Series Dust Caps and Plugs



Body Size	Dust Plug - Coupler	Dust Cap - Nipple
3/4	75MDP-12	75MDC-12
1	75MDP-16	75MDC-16
1-1/4	75MDP-20	75MDC-20
1-1/2	75MDP-24	75MDC-24
2	75MDP-32	75MDC-32
2-1/2	75MDP-40	75MDC-40
4	75MDP-64	75MDC-64

75 Series Repair Kits

Body Size	Coupler Kit	Nipple Kit
3/4	75C12-SPK	75N12-SPK
1	75C16-SPK	75N16-SPK
1-1/4	75C20-SPK	75N20-SPK
1-1/2	75C24-SPK	75N24-SPK
2	75C32-SPK	75N32-SPK
2-1/2	75C40-SPK	75N40-SPK
4	75C64-SPK	75N64-SPK

Each kit contains a valve assembly, spring and guide stop. Consult QCD for "DBP" option seals.

Ordering Guide

Material: Blank = Steel plated S = 316 Stainless Steel	Series: 75	Coupling Half: C = Coupler N = Nipple	Coupling Body Size: 12 = 3/4" 16 = 1" 20 = 1-1/4" 24 = 1-1/2"	End Fitting Size: 12 = 3/4" 16 = 1" 20 = 1-1/4" 24 = 1-1/2"	End Fitting Type: F* = Female Pipe NPTF for Steel - NPT for 316 SST EF = Female SAEa RP = Female British Parallel BS2779	Options: DBP*** = "Fire Safe" BOP version 3/4" thru 2" steel, 1" and 1-1/4" stainless steel W** = Wrench Flats on body	Seals: Blank = Nitrile V = Fluorocarbon E = Ethylene Propylene Rubber
---	----------------------	--	--	--	--	---	---

*For sizes up to 3", NPTF threads. For sizes over 3", NPT threads.

**Not available on 2" EF coupler. Standard on 2-1/2" and larger sizes (code not needed).

***DBP available in 3/4" through 2" sizes steel material, 1" and 1-1/4" stainless steel.

†Seal material code not applicable with DBP option-leave blank.

Note: Not all configurations are standard product offering. Contact QCD for price and delivery.

Hydraulic Quick Couplings

Connect Under Pressure

75 Series Threaded Connection

Poppet Valves, High Pressure



75 Series Couplers



Body Size (in.)	Part Number Steel	Port End	Part Number 316 Stainless Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats
3/4	75C12-12F	3/4-14 NPSF	S75C12-12F	3/4-14 NPSF	2.84	2.06	1.31
3/4	75C12-12F-DBP	3/4-14 NPSF	-	-	2.84	2.06	N/A
1	75C16-16F	1-11-1/2 NPSF	S75C16-16F	1-11-1/2 NPSF	3.45	4.25	1.69
1	75C16-16F-DBP	1-11-1/2 NPSF	S75C16-16F-DBP	1-11-1/2 NPSF	3.45	4.25	N/A
1-1/4	75C20-20F	1-1/4-11-1/2 NPTF	S75C20-20F	1-1/4-11-1/2 NPT	4.40	4.75	2.00
1-1/4	75C20-20F-DBP	1-1/4-11-1/2 NPTF	S75C20-20F-DBP	1-1/4-11-1/2 NPT	4.40	4.75	N/A
1-1/2	75C24-24F	1-1/2-11-1/2 NPTF	S75C24-24F	1-1/2-11-1/2 NPT	5.04	5.75	2.25
1-1/2	75C24-24F-DBP	1-1/2-11-1/2 NPTF	-	-	5.04	5.75	N/A
2	75C32-32F	2-11-1/2 NPT	S75C32-32F	2-11-1/2 NPT	6.07	6.75	3.00
2	75C32-32F-DBP	2-11-1/2 NPT	-	-	6.07	6.75	3.00
2-1/2	75C40-40F	2-1/2-8 NPTF	S75C40-40F	2-1/2-8 NPTF	5.29	8.00	3.50
3	75C48-48F	3-8 NPTF	S75C48-48F	3-8 NPTF	5.84	8.50	4.25

75 Series Nipples



Body Size (in.)	Part Number Steel	Port End	Part Number 316 Stainless Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats
3/4	75N12-12F	3/4-14 NPSF	S75N12-12F	3/4-14 NPSF	3.27	1.75	1.56
3/4	75N12-12F-DBP	3/4-14 NPSF	-	-	3.27	1.75	N/A
1	75N16-16F	1-11-1/2 NPSF	S75N16-16F	1-11-1/2 NPSF	4.17	2.25	2.00
1	75N16-16F-DBP	1-11-1/2 NPSF	S75N16-16F-DBP	1-11-1/2 NPSF	4.17	2.25	N/A
1-1/4	75N20-20F	1-1/4-11-1/2 NPTF	S75N20-20F	1-1/4-11-1/2 NPT	5.36	2.62	2.38
1-1/4	75N20-20F-DBP	1-1/4-11-1/2 NPTF	S75N20-20F-DBP	1-1/4-11-1/2 NPT	5.36	2.62	N/A
1-1/2	75N24-24F	1-1/2-11-1/2 NPTF	S75N24-24F	1-1/2-11-1/2 NPT	5.97	3.25	2.88
1-1/2	75N24-24F-DBP	1-1/2-11-1/2 NPTF	-	-	5.97	3.25	N/A
2	75N32-32F	2-11-1/2 NPT	S75N32-32F	2-11-1/2 NPT	7.05	4.00	3.50
2	75N32-32F-DBP	2-11-1/2 NPT	-	-	7.05	4.00	N/A
2-1/2	75N40-40F	2-1/2-8 NPTF	S75N40-40F	2-1/2-8 NPTF	7.46	5.00	3.50
3	75N48-48F	3-8 NPTF	S75N48-48F	3-8 NPTF	8.26	6.00	4.25

Contact QCD for additional sizes and end configurations.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Pressure

71 Series High Pressure, Non-Spill

Push-to-Connect



Parker's 71 Series, formerly Snap-tite couplings are designed for working pressures up to 10,000 psi. Available in a variety of materials and with a wide range of body sizes. Air inclusion and fluid loss are minimal with the flush face valves. Large flow chambers in the body and an exclusive valve design permit superior flow while maintaining low pressure drop.



Features:

- Flush face/Non-spill
- Push-to-connect
- Heavy duty construction
- Designed for up to 10,000 psi (690 bar) working pressures
- Variety of materials
- Wide range of sizes
- Superior flow and low pressure drop
- Sleeve lock option to protect against accidental disconnection.

Applications include:

- Industrial hydraulic lines
- Off-shore drilling

71 Series Specification

Body Size	1/4	3/8 x 1/4 ¹	3/8	3/8 x 1/2 ²	1/2	3/4	1	1 x 1-1/4 ³	2 x 1-1/4 ⁴	2
Spillage (cc)	.02	.02	.02	.02	.03	.06	.10	.10	5.25	5.25
Air Inclusion (cc)	.01	.02	.02	.02	.03	.04	.06	.06	30.50	30.50

71 Series Pressure Ratings

Body Size	Steel		316 Stainless Steel		High Pressure Stainless Steel	
	Maximum Working (psi)	Minimum Burst* (psi)	Maximum Working (psi)	Minimum Burst* (psi)	Maximum Working (psi)	Minimum Burst* (psi)
1/4	10,000	20,000	5,000	12,500	10,000	20,000
3/8 x 1/4 ¹	10,000	20,000	5,000	12,500	10,000	20,000
3/8	10,000	20,000	5,000	12,500	10,000	20,000
3/8 x 1/2 ²	10,000	20,000	5,000	12,500	10,000	20,000
1/2	10,000	20,000	5,000	12,500	10,000	20,000
3/4	7,500	15,000	5,000	12,500	7,500	15,000
1	7,500	15,000	4,000	10,000	7,500	15,000
1 x 1-1/4 ³	7,500	15,000	4,000	10,000	7,500	15,000
2 x 1-1/4 ⁴	5,000	10,000	3,000	6,000	5,000	10,000
2	5,000	10,000	3,000	6,000	5,000	10,000

¹ Unit is 3/8" with 1/4" end fitting. ² Unit is 3/8" with 1/2" end fitting, ³ 1" unit with 1-1/4" end fitting, and ⁴ 2" unit with 1-1/2" end fitting.

*NOTE: Pressure Ratings were established under static pressure conditions. For high impulse applications, consult QCD.

Maximum Recommended Connect/Disconnect Pressures

Body Size	1/4	3/8, 1/2, 3/4	1, 1-1/4	1-1/2, 2
Pressure	300	150	75	0

Hydraulic Quick Couplings

High Pressure


71 Series High Pressure, Non-Spill

Push-to-Connect




Performance

Sizes 1/4 thru 1-1/4



Sizes 1-1/2 and 2



Gallons per minute (gpm) in US gallons. Test Media MIL-H-6083 Hydraulic Fluid at 90°F ± 5°F (+32°C ± 1.5°C) sg .83

Ordering Guide

71-3 C 4 - 4 F

Options:
SL = Sleeve Lock

Seals:
Standard Seal = Nitrile
V = Fluorocarbon
E = Ethylene Propylene
M = MHO

End Fitting Type:
F* = Female NPTF
EF = Female SAE
RP = Female British Parallel BS2779
Autoclave cone & threaded fittings available (consult QCD)

End Fitting Size:
4 = 1/4" 16 = 1"
6 = 3/8" 20 = 1-1/4"
8 = 1/2" 24 = 1-1/2"
12 = 3/4" 32 = 2"

Coupling Body Size:
4 = 1/4" 12 = 3/4"
6 = 3/8" 16 = 1"
8 = 1/2" 32 = 2"

Coupling Half:
C = Coupler
N = Nipple

Series:
71 = 1-1/2" & 2" Nipples Only
71-1 = 1-1/2" & 2" Couplers Only
71-3 = 1/4" thru 1-1/4" Both

Material:
Blank = Steel, zinc trivalent plating
S = 316 Stainless Steel
SH = High Pressure Stainless Steel

* For sizes up to 1" NPTF threads in steel.
For sizes up to 1" NPSF threads in stainless steel.
For sizes over 1" NPT threads.

Hydraulic Quick Couplings

High Pressure

71 Series

High Pressure, Non-Spill

Push-to-Connect



71 Series Couplers



Body Size (in.)	Part Number Steel	Port End	Part Number 316 Stainless Steel	Part Number High Pressure Stainless Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	71-3C4-4F	1/4 - 18 NPTF	S71-3C4-4F	SH71-3C4-4F	1/4 - 18 NPTF	1.96	1.19	0.94
1/4	71-3C4-4EF	7/16 - 20 UNF	S71-3C4-4EF	-	7/16 - 20 UNF	1.96	1.19	0.94
3/8	71-3C6-4F	1/4 - 18 NPTF	-	-	-	2.36	1.56	1.25
3/8	71-3C6-6F	3/8 - 18 NPTF	S71-3C6-6F	SH71-3C6-6F	3/8 - 18 NPSF	2.36	1.56	1.25
3/8	71-3C6-6EF	9/16 - 18 UNF	S71-3C6-6EF	SH71-3C6-6EF	9/16 - 18 UNF	2.36	1.56	1.25
3/8	71-3C6-8F	1/2 - 14 NPTF	S71-3C6-8F	-	1/2 - 14 NPSF	2.57	1.56	1.25
1/2	71-3C8-8F	1/2 - 14 NPTF	S71-3C8-8F	SH71-3C8-8F	1/2 - 14 NPSF	2.77	1.88	1.50
1/2	71-3C8-8EF	3/4 - 16 UNF	S71-3C8-8EF	-	3/4 - 16 UNF	2.77	1.88	1.50
3/4	71-3C12-12F	3/4 - 14 NPTF	S71-3C12-12F	SH71-3C12-12F	3/4 - 14 NPSF	3.05	2.25	1.75
3/4	71-3C12-12EF	1-1/16 - 12 UNF	S71-3C12-12EF	-	1-1/16 - 12 UNF	3.05	2.25	1.75
1	71-3C16-16F	1 - 11-1/2 NPTF	S71-3C16-16F	SH71-3C16-16F	1 - 11-1/2 NPSF	3.32	2.63	2.00
1	71-3C16-16EF	1-5/16 - 12 UNF	S71-3C16-16EF	-	1-5/16 - 12 UNF	3.32	2.63	2.00
1	71-3C16-20F	1-1/4 - 11-1/2 NPT	S71-3C16-20F	-	1-1/4 - 11-1/2 NPT	3.32	2.63	2.00
1	71-3C16-20EF	1-5/8 - 12 UNF	S71-3C16-20EF	-	1-5/8 - 12 UNF	3.32	2.63	2.00
2	71-1C32-24F	1-1/2 - 11-1/2 NPT	-	-	-	6.21	4.50	3.38
2	71-1C32-24EF	1-7/8 - 12 UNF	-	-	-	6.21	4.50	3.38
2	71-1C32-32F	2 - 11-1/2 NPT	-	-	-	6.21	4.50	3.38
2	71-1C32-32EF	2-1/2 - 12 UNF	-	-	-	6.21	4.50	3.38

NOTE:

1. The 71-3 style couplers and nipples are interchangeable with the previous design couplers and nipples in sizes 3/8", 1/2" and 3/4".
2. Old style 1" couplers and nipples (71-2C16 and 71-2N16) are not interchangeable with the 71-3 design. Contact QCD for information.
3. Internal components of S71 and SH71 couplers and nipples are not all 316 stainless steel. Contact QCD for details.
4. Prop 65 Warning does not apply to stainless steel part numbers.

71 Series Dust Caps



Body Size	Dust Cap - Coupler	Dust Cap - Nipple
1/4	71-3PCC-4	71-3PNC-4
3/8	71-3PCC-6	71-3PNC-6
1/2	71-3PCC-8	71-3PNC-8
3/4	71-3PCC-12	71-3PNC-12
1	71-3PCC-16	71-3PNC-16

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Pressure

71 Series High Pressure, Non-Spill

Push-to-Connect



71 Series Nipples



Body Size (in.)	Part Number Steel	Port End	Part Number 316 Stainless Steel	Part Number High Pressure Stainless Steel	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/4	71-3N4-4F	1/4 - 18 NPTF	S71-3N4-4F	SH71-3N4-4F	1/4 - 18 NPTF	1.84	0.89	0.81
1/4	71-3N4-4EF	7/16 - 20 UNF	S71-3N4-4EF	-	7/16 - 20 UNF	1.84	0.89	0.81
3/8	71-3N6-4F	1/4 - 18 NPTF	-	-	-	1.84	1.18	1.00
3/8	71-3N6-6F	3/8 - 18 NPTF	S71-3N6-6F	SH71-3N6-6F	3/8 - 18 NPSF	2.32	1.18	1.00
3/8	71-3N6-6EF	9/16 - 18 UNF	S71-3N6-6EF	SH71-3N6-6EF	9/16 - 18 UNF	2.32	1.18	1.00
3/8	71-3N6-8F	1/2 - 14 NPTF	-	-	-	2.57	1.65	1.25
1/2	71-3N8-8F	1/2 - 14 NPTF	S71-3N8-8F	SH71-3N8-8F	1/2 - 14 NPSF	2.38	1.65	1.50
1/2	71-3N8-8EF	3/4 - 16 UNF	S71-3N8-8EF	SH71-3N8-8EF	3/4 - 16 UNF	2.38	1.65	1.50
3/4	71-3N12-12F	3/4 - 14 NPTF	S71-3N12-12F	SH71-3N12-12F	3/4 - 14 NPSF	2.96	1.92	1.75
3/4	71-3N12-12EF	1-1/16 - 12 UNF	S71-3N12-12EF	-	1-1/16 - 12 UNF	2.96	1.92	1.75
1	71-3N16-16F	1 - 11-1/2 NPTF	S71-3N16-16F	SH71-3N16-16F	1 - 11-1/2 NPSF	3.23	2.09	1.88
1	71-3N16-16EF	1-5/16 - 12 UNF	S71-3N16-16EF	-	1-5/16 - 12 UNF	3.23	2.09	1.88
1	71-3N16-20F	1-1/4 - 11-1/2 NPT	S71-3N16-20F	-	1-1/4 - 11-1/2 NPT	3.23	2.20	1.88
1	71-3N16-20EF	1-5/8 - 12 UNF	S71-3N16-20EF	-	1-5/8 - 12 UNF	3.23	2.20	1.88
2	71N32-24F	1-1/2 - 11-1/2 NPT	-	-	-	4.50	3.50	3.25
2	71N32-24EF	1-7/8 - 12 UNF	-	-	-	4.50	3.50	3.25
2	71N32-32F	2 - 11-1/2 NPT	-	-	-	4.50	3.50	3.25

NOTE:

1. The 71-3 style couplers and nipples are interchangeable with the previous design couplers and nipples in sizes 3/8", 1/2" and 3/4".
2. Old style 1" couplers and nipples (71-2C16 and 71-2N16) are not interchangeable with the 71-3 design. Contact QCD for information.
3. Internal components of S71 and SH71 couplers and nipples are not all 316 stainless steel. Contact QCD for details.
4. Prop 65 Warning does not apply to stainless steel part numbers.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Pressure

3000 Series ISO 14540

Threaded Connection, Screw-to-Connect



The 3000 Series coupling are designed for high pressure applications. The coupler sleeve and nipple body must be manually threaded together to make the connection.



Features:

- Interchanges with ISO 14540
- Manual threaded connection and actuation
- Hard, chrome alloy ball valves
- Polyurethane interface seal resists high pressure extrusion
- Threaded retainer provides a positive valve stop
- Protective zinc plating with clear trivalent chromate finish

Applications include:

- Hydraulic rams
- Portable hydraulic tools
- Crimping equipment

3000 Series Specification


Body Size	Rated Flow (gpm)	Rated Pressure (psi)	Temperature	Body Material	Sleeve Type	Seal Material
1/4	3	10,000	-22° F to +230° F	Steel	Thread to connect	Polyurethane
3/8	6			Steel	Thread to connect	Polyurethane

3000 Series Replacement O-Rings

Body Size	Material	Part Number	Durometer
1/4	Polyurethane	50001-114-0296	90
3/8	Polyurethane	50001-210-0296	90

Performance

3000 Series (1/4", 3/8")
Test Fluid: Oil - 200 SUS



Hydraulic Quick Couplings

High Pressure

3000 Series

ISO 14540

Threaded Connection, Screw-to-Connect



3000 Series Couplers



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	3050-2	1/4-18 NPTF (Male)	Ball	2.38	1.13	0.81	0.25
3/8	3050-3	3/8-18 NPTF (Male)	Ball	2.38	1.38	1.00	0.49
3/8	3050-3-231	3/8-18 NPTF (Female)	Ball	2.38	1.38	1.00	0.49

3000 Series Nipples



Body Size (in.)	Coupler Part Number Steel	Port End	Valve Type	Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	3010-2	1/4-18 NPTF (Female)	Ball	1.29	1.13	0.88	0.14
3/8	3010-3	3/8-18 NPTF (Female)	Ball	1.58	1.25	0.94	0.23
3/8	3010-3-230	3/8-18 NPTF (Male)	Ball	2.31	1.25	1.00	0.30

3000 Series Dust Caps and Plugs



Body Size (in.)	Dust Cap - Nipple	Color/Material	Dust Plug - Coupler	Weight (lbs.)
1/4	3009-2	Steel	3005-2	0.02
3/8	3009-3	Steel	3005-3	0.04

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Pressure

TC Series Manual Sleeve

Sleeve Lock, Fluorocarbon Seal



TC Series couplings are used in high pressure applications with hydraulic and mechanical shock. Steel coupler sleeves and nipple bodies are hardened for resistance to damage. Fluorocarbon seals along with PTFE back up rings provide reliable sealing in high pressures. Available in 3/8 inch size only, with sleeve lock to guard against accidental disconnection.




Features:

- Rated pressure up to 10,000 psi
- Manual sleeve operation
- Fluorocarbon seals
- Standard sleeve lock guards against accidental disconnection
- Positive valve stop prevents flow checking
- Standard end configuration is female pipe thread
- Protective zinc plating with clear trivalent chromate finish

Applications include:

- Hydraulic jacking and house moving equipment
- Construction equipment
- Railway maintenance

Performance



TC Series Specifications

Body Size	3/8
Rated Pressure (psi)	10,000
Rated Flow (gpm)	6
Temperature Range (std seals)	-15° to +400° F

TC Series Dust Plug/Caps

TR-37

TC Series Coupler



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	TC-371	3/8-18 NPSF	2.48	1.25	0.94	0.43

TC Series Nipple



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Largest Diameter	Wrench Flats	Weight (lbs.)
3/8	TC-372	3/8-18 NPSF	1.82	0.66	1.08	0.94	0.14



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Pressure

1141 Series

Threaded Connect Under Pressure

Stainless Body, Polyurethane Seal



1141 Series are general purpose couplings that connect under pressure for high pressure applications. The 1/4 inch stainless steel coupling connects together with a threaded brass sleeve. Polyurethane seals resist extrusion and abrasion.



Features:

- 303 stainless steel body
- Rated pressure up to 10,000 psi and 17,000 psi intermittent pressure
- Small diameter mating seal keeps separation forces to a minimum, allowing easier threaded connection and disconnection at pressures up to 5,000 psi
- Polyurethane seals to resist extrusion and abrasion
- Self locking threads guard against accidental disconnection
- Visual connection indicator – when fully coupled, sleeve edge is flush with the end of the male thread
- Standard end configuration is female pipe thread
- Dust caps and plugs included

Applications include:

- Off shore equipment
- Hydraulic lines in corrosive environments

1141 Series Specification

Body Size	Rated Pressure (psi)	Rated Connect-Under-Pressure Capability (psi)	Rated Flow (gpm)	Temperature Range (Polyurethane seals)	Vacuum Test	Torque to connect at 1000 psi
1/4	10,000	5,000	3	-30° to +180° F	20 in/Hg	47 in/lbs.

1141 Series Coupler



Body Size (in.)	Part Number 303 SS	Thread Size	Length (in.)	Sleeve Hex	Wrench Flats	Weight (lbs.)
1/4	1141-62	1/4-18 NPTF	2.75	1.00	0.88	0.40

1141 Series Nipple



Body Size (in.)	Part Number 303 SS	Thread Size	Length (in.)	Wrench Flats	Weight (lbs.)
1/4	1141-63	1/4-18 NPTF	2.00	0.88	0.26

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Flow

ST Series Straight-thru Interface

Non-valved, Manual Sleeve



ST Series non-valved couplings provide maximum flow and low pressure drop. The smooth, open bore allows easy cleaning in applications where the same lines are used for more than one media.



Features:

- Steel nipples are case hardened for resistance to Brinelling
- Functionally interchanges with similar straight-through design couplings
- Standard Nitrile seals
- Material options available
- Sleeve-Lok option available

Applications include:


- High pressure water
- Steam washers
- Carpet cleaners

ST Series Specifications


Body Size	Rated Pressure (psi) Brass Coupler/Nipple	Rated Pressure (psi) Brass Coupler/Steel Nipple	Rated Pressure (psi) 303 SS Coupler/Nipple	Temperature Range (standard seals)	Rated Flow
1/8	2500	2600	4200	-40° to +250° F	3
1/4	5200	5500	6700		6
3/8	2700	3500	5500		12
1/2	2200	2700	3000		12
3/4	1700	2700	3000		28
1	1200	2000	1700		50
1-1/4	1700	—	—		76
1-1/2	1400	—	—		100

Performance

ST Series (1/8", 1/4", 3/8", 1/2")
Test Fluid: Oil - 150 SUS



ST Series (3/4", 1", 1-1/4")
Test Fluid: Oil - 150 SUS



Hydraulic Quick Couplings

High Flow

ST Series Straight-thru Interface

Non-valved, Manual Sleeve



Optional Materials and Features:

(add code to part number)

Contact QCD for availability and additional options.

To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -SL	Sleeve-Lok (Couplers)	SST-3M-SL
suffix W	Ethylene Propylene seal material- EPR (Couplers)	SST-3MW
suffix Y	Fluorocarbon seal material (Couplers)	SST-3MY
suffix Z	Neoprene seal material (Couplers)	SST-3MZ

ST Series Couplers - Female Pipe Thread



Body Size (in.)	Part Number Brass	Part Number 303 Stainless Steel*	Port End	Length (in.)	Largest Diameter	Wrench Flats	Brass Weight (lbs.)	Stainless Weight (lbs.)
1/8	BST-1	SST-1	1/8-27 NPTF	1.06	0.69	0.56	0.06	0.05
1/4	BST-2	SST-2	1/4-18 NPTF	1.54	0.94	0.81	0.17	0.15
3/8	BST-3	SST-3	3/8-18 NPTF	1.64	1.16	1.00	0.26	0.24
1/2	BST-4	SST-4	1/2-14 NPTF	1.98	1.30	1.13	0.40	0.37
3/4	BST-6	SST-6	3/4-14 NPTF	2.15	1.66	1.44	0.62	0.57
1	BST-8	SST-8	1-11 1/2 NPTF	2.43	2.02	1.75	0.99	0.93
1-1/4	BST-10**	-	1 1/4-11 1/2 NPTF	2.44	2.51	2.00	1.38	-
1-1/2	BST-12**	-	1 1/2-11 1/2 NPTF	2.88	3.00	2.50	2.43	-

** Steel sleeves

ST Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Brass	Part Number 303 Stainless Steel*	Port End	Length (in.)	Largest Diameter	Wrench Flats	Brass Weight (lbs.)	Stainless Weight (lbs.)
1/8	BST-1M	SST-1M	1/8-27 NPTF	1.06	0.69	0.56	0.05	0.05
1/4	BST-2M	SST-2M	1/4-18 NPTF	1.69	0.94	0.81	0.13	0.16
3/8	BST-3M	SST-3M	3/8-18 NPTF	1.75	1.16	1.00	0.25	1.16
1/2	BST-4M	SST-4M	1/2-14 NPTF	1.94	1.30	1.13	0.34	1.30
3/4	BST-6M	SST-6M	3/4-14 NPTF	2.17	1.66	1.44	-	1.66
1	BST-8M	SST-8M	1-11 1/2 NPTF	2.53	2.02	1.75	0.85	2.02

* Prop 65 Warning does not apply to stainless steel part numbers

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Flow

ST Series Straight-thru Interface

Non-valved, Manual Sleeve



ST Series Nipples- Female Pipe Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Part No. 303 Stainless*	Weight (lbs.)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/8	BST-N1	0.03	ST-N1	0.03	SST-N1	0.02	1/8-27 NPTF	0.98	0.65	0.56
1/4	BST-N2	0.07	ST-N2	0.07	SST-N2	0.07	1/4-18 NPTF	1.46	0.87	0.75
3/8	BST-N3	0.12	ST-N3	0.11	SST-N3	0.11	3/8-18 NPTF	1.62	1.59	0.08
1/2	BST-N4	0.23	ST-N4	0.21	SST-N4	0.21	1/2-14 NPTF	1.85	1.30	1.13
3/4	BST-N6	0.33	ST-N6	0.32	SST-N6	0.32	3/4-14 NPTF	2.15	1.59	1.38
1	BST-N8	0.52	ST-N8	0.49	SST-N8	0.48	1-11 1/2 NPTF	2.35	1.88	1.63
1-1/4	BST-N10	0.85	-	-	-	-	1 1/4-11 1/2 NPTF	2.38	2.31	2.00
1-1/2	BST-N12	1.45	-	-	-	-	1 1/2-11 1/2 NPTF	2.81	2.74	2.38

ST Series Nipples- Male Pipe Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Part No. 303 Stainless*	Weight (lbs.)	Port End	Length (in.)	Largest Diameter	Wrench Flats
1/8	BST-N1M	0.02	ST-N1M	0.02	SST-N1M	0.02	1/8-27 NPTF	1.04	0.51	0.44
1/4	BST-N2M	0.06	ST-N2M	0.05	SST-N2M	0.05	1/4-18 NPTF	1.53	0.65	0.56
3/8	BST-N3M	0.08	ST-N3M	0.07	SST-N3M	0.08	3/8-18 NPTF	1.69	0.79	0.69
1/2	BST-N4M	0.15	ST-N4M	0.13	SST-N4M	0.13	1/2-14 NPTF	1.94	1.01	0.88
3/4	BST-N6M	0.23	ST-N6M	0.21	SST-N6M	0.22	3/4-14 NPTF	2.19	1.23	1.06
1	BST-N8M	0.46	ST-N8M	0.43	SST-N8M	0.43	1-11 1/2 NPTF	2.51	1.59	1.38
1-1/4	BST-N10M	0.96	-	-	-	-	1 1/4-11 1/2 NPTF	2.85	2.17	1.88
1-1/2	BST-N12M	1.46	-	-	-	-	1 1/2-11 1/2 NPTF	3.25	2.45	2.13

* Prop 65 Warning does not apply to stainless steel part numbers

ST Series Couplers - Replacement Parts

Body Size	O-rings - Nitrile
1/8	50001-010-0010
1/4	50001-110-0010
3/8	50001-112-0010
1/2	50001-114-0010
3/4	50001-212-0010
1	50001-217-0010

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Flow

1163 Series Water Hose Connectors

Non-valved, Manual Sleeve



Parker Water Service Quick Couplings add convenience and efficiency whenever water hoses are frequently connected and disconnected. The durable 4-ball locking mechanism provides a secure connection.



Features:

- Brass and stainless steel construction
- Nitrile seals

Applications include:

- Garden hoses
- Wash down systems
- Mobile water tank lines

1163 Series Specifications

Body Size	Rated Pressure (psi)	Rated Flow (gpm)	Temperature Range (std seals)
3/4	200	28	-40° to +250° F

1163 Series Coupler



Body Size (in.)	Coupler Part Number	Port End	Length (in.)	Largest Diameter	Weight (lbs.)
3/4	1163-60	3/4-11 1/2 NH	1.16	1.21	0.12

1163 Series Nipple



Body Size (in.)	Nipple Part Number	Port End	Overall Length (in.)	Exposed Length	Weight (lbs.)
3/4	1163-61	3/4-11 1/2 NH	1.25	0.50	0.08

1163 Series Coupler Replacement Seal

Part Number	Material
4730001	Nitrile



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

High Flow

HO Series Non-Valved, High Pressure

Manual Sleeve, Sleeve Lock



HO series couplings are high flow, high pressure, steel couplings for a wide variety of applications. Electroless nickel plating provides corrosion resistance.



Features:

- Steel material with electroless nickel plating
- Nitrile seals with PTFE back up ring
- No valving, unrestricted flow
- Standard sleeve lock guards against accidental disconnection
- Rated pressures up to 15,000 psi

Applications include:

- Paper and pulp processing
- Refinery systems
- Testing systems

HO Series Specifications

Body Size	1/4	3/8	1/2
Rated Pressure (PSI)	15,000	15,000	10,000
Rated Flow (GPM)	3	6	12
Temperature Range (std seals)	-40° to +250°F		

HO Series Couplers



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)	Dust Plug Rubber
1/4	HO-251-4FP	1/4-18 NPTF	1.67	1.06	0.94	0.24	TR-37
3/8	HO-371-6FP	3/8-18 NPTF	1.67	1.06	0.94	0.22	TR-37
1/2	HO-501-8FP	1/2-14 NPTF	2.03	1.62	1.25	0.52	DP-50

HO Series Nipples



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Largest Diameter	Wrench Flats	Weight (lbs.)	Dust Plug Rubber
1/4	HO-252-4FP	1/4-18 NPTF	1.40	0.66	0.94	0.81	0.10	TR-37
3/8	HO-372-6FP	3/8-18 NPTF	1.44	0.70	1.08	0.94	0.12	TR-37
1/2	HO-502-8FP	1/2-14 NPTF	2.03	0.86	1.30	1.12	0.26	DP-50

Optional Materials and Features: (add code to part number)

Contact QCD for availability and additional options.
To select proper seal materials, see Fluid Compatibility Chart or contact QCD.

Code	Description	Part Number Example
suffix -E5	Ethylene Propylene seal material- EPR (Couplers)	HO-371-6FP-E5
suffix -E4	Fluorocarbon seal material (Couplers)	HO-371-6FP-E4
suffix -E12	Neoprene seal material (Couplers)	HO-371-6FP-E12

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Mold Coolant

Moldmate Series Coolant Line Connectors

Brass Body, Silicone Seal



Moldmate series couplings are specifically designed for connecting coolant lines to molds and dies on injection molding machinery and die casting equipment. These couplings significantly reduce downtime, by providing a quick and easy way to connect and disconnect lines during mold changes.

Features:

- Rated pressure is 200 psi
- Valved and unvalved options. Valved couplers have silver colored sleeves
- Brass material with standard silicone interface seals are compatible with water and water glycol fluids. Valved versions have a fluorocarbon seal on the poppet.
- Optional fluorocarbon seal for use with oil based media
- Short nipples can be installed recessed below the mold surface enabling more efficient storage and protecting the nipple from damage
- Standard and Push-Lok hose barb ends are available in straight, 45 or 90 degree configurations
- Manual sleeve operation
- Extension nipples are offered in several lengths

Applications include:

- Mold coolant lines
- Die casting equipment

Guidelines for Selection and Use:

Non-valved couplers provide maximum flow for efficient cooling. Valved couplers shut off automatically when disconnected. Valved couplers can be used with either valved or non-valved nipples. A valved nipple, however, must be used with a valved coupler.

Moldmate couplings are rated for 200 psi max pressure. Most thermoplastic and thermoset heat transfer systems have pumps which provide relatively high flow rates at low pressures. Water and water glycol systems usually have capacities ranging from 10 to 40 gpm with most from 10 to 15 gpm. Normal media opening pressures are 20 to 60 psi for these systems. Heat transfer systems using oil generally operate from 10 to 30 psi. However, their flow rates are usually much higher, requiring the total volume of oil to be circulated at least once per minute.

The number of hose connections in a single mold system results in a cumulative pressure drop. Please note the Pressure Drop vs. Flow Rate chart provided, to select the appropriate size.


Temperature is another important consideration. Parker Moldmate couplings with the standard silicone seal have a temperature capability of -90° to +400°F. Rapid deterioration of the seal and leakage may result if used beyond these limits.

External conditions of temperature, corrosive atmospheres, and other abnormalities may affect coupling performance and must be considered when selection is made. Consult QCD with questions.

Special Order Information:

Standard seal material is Silicone and is compatible with water and water glycol fluids commonly used in heat transfer systems. Fluorocarbon seals are available for use with oil-based media. To specify a Fluorocarbon seal, add the suffix "Y" to the standard moldmate part number, thus: PC206Y.

Performance



Moldmate Series Specifications

Body Size	1/4	3/8	1/2
Rated Pressure (psi)	200		
Rated Flow (gpm)	3	6	12

Material	Temperature Range
Standard Silicone seal	-20° to +400° F
*Optional Fluorocarbon seal	-15° to +400° F

* For use with oil based media only

Hydraulic Quick Couplings

Mold Coolant

Moldmate Series Coolant Line Connectors

Brass Body, Silicone Seal



Moldmate Series Couplers - Straight

											
Non-Valved		Push-Lok Hose Barb		Valved		Non-Valved		Standard Hose Barb		Valved	
Body Size (in.)	Part Number Brass Non-Valved	Weight (lbs.)	Part Number Brass - Valved (silver sleeve)	Weight (lbs.)	Hose I.D.	Overall Length (in.)	Largest Diameter	Overall Length	Largest Diameter	Wrench Flats	
1/4	PC204	0.10	PC204AV	0.10	1/4	1.87	0.63	2.67	0.71	0.63	
1/4	PC204-BP*	0.10	PC204AV-BP	0.10	1/4	1.89	0.63	2.52	0.71	0.63	
1/4	PC205	0.09	PC205AV	0.10	5/16	1.87	0.63	2.67	0.71	0.63	
1/4	PC206	0.09	PC206AV	0.10	3/8	1.87	0.63	2.67	0.71	0.63	
1/4	PC206-BP*	0.11	PC206AV-BP	0.13	3/8	2.04	0.63	2.70	0.71	0.63	
3/8	PC306	0.24	PC306V	0.27	3/8	2.67	0.96	3.17	1.01	0.88	
3/8	PC306-BP*	0.26	PC306V-BP	0.29	3/8	3.15	0.96	3.31	1.01	0.88	
3/8	PC308	0.25	PC308V	0.28	1/2	3.15	0.96	3.17	1.01	0.88	
3/8	PC308-BP*	0.25	PC308V-BP	0.03	1/2	3.27	0.96	3.43	1.01	0.88	
1/2	PC504	0.46	N/A	–	1/2	3.55	1.30	–	–	–	
1/2	PC504-BP*	0.50	N/A	–	1/2	3.68	1.21	–	–	–	
1/2	PC506	0.48	N/A	–	3/4	3.80	1.21	–	–	–	
1/2	PC506-BP*	0.52	N/A	–	3/4	3.80	1.21	–	–	–	

NA = Not Available

Moldmate Series Couplers - 45 Degree

											
Non-Valved		Push-Lok Hose Barb		Valved		Non-Valved		Standard Hose Barb		Valved	
Body Size (in.)	Part Number Brass - Non-Valved	Weight (lbs.)	Part Number Brass - Valved (silver sleeve)	Weight (lbs.)	Hose I.D.	Overall Length (in.)	Largest Diameter	Wrench Flats	Overall Length	Largest Diameter	Wrench Flats
						Non-Valved			Valved		
1/4	PC224	0.13	PC224AV	0.13	1/4	2.67	0.71	0.56	2.87	0.71	0.63
1/4	PC224-BP*	0.13	PC224AV-BP	0.14	1/4	2.57	0.71	0.56	2.77	0.71	0.63
1/4	PC226	0.13	PC226AV	0.14	3/8	2.71	0.71	0.56	2.91	0.71	0.63
1/4	PC226-BP*	0.26	PC226AV-BP	0.17	3/8	2.74	0.71	0.56	2.94	0.71	0.63
3/8	PC326	0.36	PC326V	0.36	3/8	3.65	0.96	0.88	3.65	1.01	0.88
3/8	PC326-BP*	0.34	PC326V-BP	0.36	3/8	3.75	0.96	0.88	3.75	1.01	0.88
3/8	PC328	0.36	PC328V	0.36	1/2	3.69	0.96	0.88	3.69	1.01	0.88
3/8	PC328-BP*	0.34	PC328V-BP	0.40	1/2	3.88	0.96	0.88	3.88	0.96	0.88
1/2	PC524	0.74	N/A	–	1/2	4.18	1.21	1.12	–	–	–
1/2	PC524-BP*	0.78	N/A	–	1/2	4.28	1.21	1.12	–	–	–
1/2	PC526	0.76	N/A	–	3/4	4.56	1.21	1.12	–	–	–
1/2	PC526-BP*	0.80	N/A	–	3/4	4.56	1.21	1.12	–	–	–

* Suffix BP in part number denotes Push-Lok hose barb. Without suffix denotes standard hose barb.

Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

Valved Couplers can be used with either non-valved or valved nipples.

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Mold Coolant

Moldmate Series Coolant Line Connectors

Brass Body, Silicone Seal



Moldmate Series Couplers - 90 Degree

		Non-Valved	Push-Lok Hose Barb	Valved			Non-Valved	Standard Hose Barb	Valved		
Body Size (in.)	Part Number Brass - Non-Valved	Weight (lbs.)	Part Number Brass - Valved (silver sleeve)	Weight (lbs.)	Hose I.D.	Overall Length (in.)	Wrench Flats	Largest Diameter	Overall Length	Wrench Flats	Largest Diameter
						Non-Valved		Valved			
1/4	PC214	0.13	PC214AV	0.14	1/4	1.78	0.56	0.71	1.98	0.63	0.71
1/4	PC214-BP*	0.14	PC214AV-BP	0.14	1/4	1.78	0.56	0.71	1.98	0.63	0.71
1/4	PC215	0.13	PC215AV	0.14	5/16	1.78	0.56	0.71	1.98	0.63	0.71
1/4	PC216	0.14	PC216AV	0.15	3/8	1.78	0.56	0.71	1.98	0.63	0.71
1/4	PC216-BP*	0.16	PC216AV-BP	0.17	3/8	1.80	0.56	0.71	2.00	0.63	0.71
3/8	PC316	0.31	PC316V	0.31	3/8	2.78	0.88	0.96	2.78	0.88	0.96
3/8	PC316-BP*	0.37	PC316V-BP	0.37	3/8	2.78	0.88	0.96	2.78	0.88	0.96
3/8	PC318	0.33	PC318V	0.35	1/2	2.78	0.88	0.96	2.78	0.88	0.96
3/8	PC318-BP*	0.37	PC318V-BP	0.39	1/2	2.80	0.88	0.96	2.80	0.88	0.96
1/2	PC514	0.79	N/A	-	1/2	3.50	1.12	1.21	-	-	-
1/2	PC514-BP*	0.83	N/A	-	1/2	3.50	1.12	1.21	-	-	-
1/2	PC516	0.80	N/A	-	3/4	3.50	1.12	1.21	-	-	-
1/2	PC516-BP*	0.84	N/A	-	3/4	3.50	1.12	1.21	-	-	-

* Suffix BP in part number denotes Push-Lok hose barb. Without suffix denotes standard hose barb.

Push-Lok hose barbs are designed for use with Parker Push-Lok hose and do not require clamps.

Valved Couplers can be used with either non-valved or valved nipples.

Sub Assemblies and Individual Replacement Parts

Non-valved Sub-assembly (Brass Sleeve)



Body Size (in.)	Part Number Brass - Non-Valved	Weight (lbs.)	Thread Size	Length (in.)	Largest Diameter	Wrench Flats
1/4	P208-01A	0.07	1/8-27 NPTF	1.15	0.71	0.56
3/8	P308-01A	0.21	1/4-18 NPTF	1.84	0.96	0.88
3/8	P308-01A-HF	0.20	3/8-18 NPTF	1.84	0.96	0.88
1/2	PC500	0.34	1/2-14 NPTF	2.02	1.21	1.12

Valved Sub-assembly (Silver Colored Sleeve)



Bodies are designed for use with a valve and spring retained by a male pipe fitting (i.e. hose barb). An end fitting is required to retain the internal valving. Valve, valve spring, and end fitting are not included with sub-assembly and must be ordered separately.

Body Size (in.)	Part Number Brass - Non-Valved	Weight (lbs.)	Thread Size	Length (in.)	Largest Diameter	Wrench Flats
1/4	P201-01A	0.07	1/8-27 NPTF	1.35	0.71	0.56
3/8	P301-01A	0.21	1/4-18 NPTF	1.84	0.96	0.88

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Mold Coolant

Moldmate Series Coolant Line Connectors

Brass Body, Silicone Seal



Sub Assemblies and Individual Replacement Parts

Valves (for Valved Sub-assembly)



Body Size (in.)	Part Number	Material
1/4	3613001	Brass
3/8	P300-11S	Brass

Valve Springs (for Valved Sub-assembly)



Body Size (in.)	Part Number	Material
1/4	7820123	Stainless
3/8	P300-6	Stainless

Replacement Seals (for both Valved and Non-valved)



Body Size (in.)	Part Number	Material
1/4	P200-9A	*Silicone
1/4	P200-9AY	*Fluorocarbon
3/8	P300-9A	*Silicone
3/8	P300-9AY	*Fluorocarbon
1/2	P500-9A	*Silicone
1/2	P500-9AY	*Fluorocarbon

* Note: Bulk seals are not returnable.

Assembly Instruction Sheet (for all sizes & configurations)

Part Number
9090065

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Mold Coolant

Moldmate Series Coolant Line Connectors

Brass Body, Silicone Seal



Moldmate Series Nipples - Female Pipe Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Thread Size	Overall Length (in.)	Exposed Length**	Wrench Flats	Largest Diameter
1/4	BPN251F	0.02	PN251F	0.02	1/8-27 NPTF	0.97	0.58	0.50	0.58
1/4	BPN252F	0.05	PN252F	0.04	1/4-18 NPTF	1.28	0.89	0.63	0.72
1/4	BPN253F	0.08	PN253F	0.08	3/8-18 NPTF	1.41	1.02	0.75	0.87
3/8	BPN352F	0.05	PN352F	0.05	1/4-18 NPTF	1.48	0.88	0.63	0.72
3/8	BPN353F	0.07	PN353F	0.06	3/8-18 NPTF	1.58	0.98	0.75	0.87

Moldmate Series Nipples - Male Pipe Thread



Body Size (in.)	Part Number Brass	Weight (lbs.)	Part Number Steel	Weight (lbs.)	Thread Size	Overall Length (in.)	Exposed Length**	Wrench Flats	Largest Diameter	Install Recess Diameter	Depth
1/4	PN250	0.02	-	-	1/16-27 NPTF	0.94	0.54	0.44	0.51	0.69	0.69
1/4	PN251	0.02	PN251S	0.02	1/8-27 NPTF	0.94	0.54	0.44	0.51	0.69	0.69
1/4	PN252	0.03	PN252S	0.03	1/4-18 NPTF	1.13	0.74	0.56	0.67	0.84	0.94
1/4	PN253	0.05	PN253S	0.05	3/8-18 NPTF	1.19	0.79	0.69	0.79	1.00	0.94
3/8	PN352	0.04	PN352S	0.04	1/4-18 NPTF	1.34	0.74	0.56	0.65	1.00	1.09
3/8	PN353	0.06	PN353S	0.06	3/8-18 NPTF	1.38	0.78	0.69	0.79	1.00	1.13
3/8	PN354	0.12	NA	-	1/2-14 NPTF	1.59	0.99	0.88	1.01	1.19	1.25
1/2	PN553	0.12	NA	-	3/8-18 NPTF	1.53	0.77	0.88	1.01	1.25	1.34
1/2	PN554	0.11	NA	-	1/2-14 NPTF	1.70	0.94	0.88	1.01	1.25	1.50
1/2	PN556	0.16	NA	-	3/4-14 NPTF	1.75	0.99	1.06	1.23	1.50	1.56


Moldmate Series - Valved Nipple



Body Size (in.)	Part Number Brass	Thread Size	Overall Length (in.)	Exposed Length**	Largest Diameter	Wrench Flats	Weight (lbs.)
1/4	BPV252*	1/4-18 NPTF	1.21	0.82	0.67	0.56	0.03
3/8	BPV353*	3/8-18 NPTF	1.48	0.88	0.79	0.69	0.07

*Valved Nipple must be used with Valved Coupler.

**This dimension represents the portion of the nipple that is exposed when inserted into a moldmate coupler.



Install Recess Diameter	Depth
0.84	0.94
1.00	1.23

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings


Mold Coolant

Moldmate Series Coolant Line Connectors

Brass Body, Silicone Seal



Moldmate Series Nipples - Moldmate Extension



Body Size (in.)	Part Number Brass	Weight (lbs.)	Thread Size	Overall Length	Exposed Length	Wrench Flats	Largest Diameter
1/4	PN250-25	0.04	1/16-27 NPTF	2.50	0.69	3/8	0.43
1/4	PN250-40	0.06	1/16-27 NPTF	4.00	0.81	3/8	0.43
1/4	PN250-55	0.09	1/16-27 NPTF	5.50	0.81	3/8	0.43
1/4	PN251-25	0.06	1/8-27 NPTF	2.50	0.69	7/16	0.51
1/4	PN251-40	0.10	1/8-27 NPTF	4.00	1.00	7/16	0.51
1/4	PN251-55	0.13	1/8-27 NPTF	5.50	1.00	7/16	0.51
1/4	PN251-70	0.17	1/8-27 NPTF	7.00	1.00	7/16	0.51
1/4	PN251-85	0.21	1/8-27 NPTF	8.50	1.00	7/16	0.51
1/4	PN252-25	0.09	1/4-18 NPTF	2.50	0.88	9/16	0.65
1/4	PN252-40	0.15	1/4-18 NPTF	4.00	1.25	9/16	0.65
1/4	PN252-55	0.22	1/4-18 NPTF	5.50	1.25	9/16	0.65
1/4	PN252-70	0.27	1/4-18 NPTF	7.00	1.25	9/16	0.65
1/4	PN252-85	0.33	1/4-18 NPTF	8.50	1.25	9/16	0.65
3/8	PN351-25	0.07	1/8-27 NPTF	2.50	0.88	9/16	0.65
3/8	PN351-40	0.11	1/8-27 NPTF	4.00	1.00	9/16	0.65
3/8	PN351-55	0.15	1/8-27 NPTF	5.50	1.00	9/16	0.65
3/8	PN351-70	0.18	1/8-27 NPTF	7.00	1.00	9/16	0.65
3/8	PN351-85	0.22	1/8-27 NPTF	8.50	1.00	9/16	0.65
3/8	PN352-25	0.09	1/4-18 NPTF	2.50	0.88	9/16	0.65
3/8	PN352-40	0.15	1/4-18 NPTF	4.00	1.25	9/16	0.65
3/8	PN352-55	0.21	1/4-18 NPTF	5.50	1.25	9/16	0.65
3/8	PN352-70	0.27	1/4-18 NPTF	7.00	1.25	9/16	0.65
3/8	PN352-85	0.33	1/4-18 NPTF	8.50	1.25	9/16	0.65
3/8	PN353-25	0.12	3/8-18 NPTF	2.50	1.00	11/16	0.79
3/8	PN353-40	0.20	3/8-18 NPTF	4.00	1.25	11/16	0.79
3/8	PN353-55	0.28	3/8-18 NPTF	5.50	1.25	11/16	0.79
3/8	PN353-70	0.37	3/8-18 NPTF	7.00	1.25	11/16	0.79
3/8	PN353-85	0.45	3/8-18 NPTF	8.50	1.25	11/16	0.79

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Mold Coolant

Rectus 21 DSO Series Miniature

Formerly DM Series

Double Shut-off, Push-to-Connect

B-103



Rectus 21 DSO Series are special purpose miniature couplings that offer double shut-off and push to connect operation in a small envelope. The 1/8 inch brass couplings are nickel plated with standard fluorocarbon seals.



Features:

- Rated pressure is 250 psi
- Double shut-off valving
- Fluorocarbon seals
- Standard end configurations are female and male pipe thread

Applications include:


- Dental equipment
- Lubrication lines
- Fluid transfer
- Coolant lines

Rectus 21 DSO Series Specifications

Body Size (in.)	Rated Pressure (psi)	Locking Device (balls)	Rated Flow (gpm)	Temperature Range
1/8	250	5	0.8	-15°F to +400°F

Performance

Rectus 21 DSO Series
Test Fluid: Water



Hydraulic Quick Couplings

Mold Coolant

Rectus 21 DSO Series Miniature

Formerly DM Series

Double Shut-off, Push-to-Connect



Rectus 21 DSO Series Couplers - Female Pipe Thread



Body Size (in.)	Old Part Number	New Part Number	Weight (lbs.)	Thread Size	Overall Length (in.)	Largest Diameter	Wrench Flats
1/8	DM-121-2FP	21KBIN10MVN	0.06	1/8-27 NPSF	1.42	0.63	0.55
1/8	DM-121-4FP	21KBIN13MVN	0.10	1/4-18 NPSF	1.81	0.78	0.67

Rectus 21 DSO Series Couplers - Male Pipe Thread



Body Size (in.)	Old Part Number	New Part Number	Weight (lbs.)	Thread Size	Overall Length (in.)	Largest Diameter	Wrench Flats
1/8	DM-121-2MP	21KBAN10MVN	0.06	1/8-27 NPTF	1.50	0.63	0.55
1/8	DM-121-4MP	21KBAN13MVN	0.07	1/4-18 NPTF	1.61	0.63	0.55

Rectus 21 DSO Series Couplers - Standard Hose Barb

IMAGE COMING SOON

Body Size (in.)	Old Part Number	New Part Number	Weight (lbs.)	Hose I.D.	Overall Length (in.)	Largest Diameter	Wrench Flats
1/8	DM-121-4HB	21KBTFO6MVN	0.06	1/4	1.82	0.64	0.55

Rectus 21 DSO Series Nipples - Female Pipe Thread



Body Size (in.)	Old Part Number	New Part Number	Weight (lbs.)	Thread Size	Overall Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats
1/8	DM-122-2FP	21SBIN10MVN	0.05	1/8-27 NPSF	1.56	1.03	0.63	0.55
1/8	DM-122-4FP	21SBIN13MVN	0.09	1/4-18 NPSF	1.97	1.44	0.78	0.67

* This dimension represents the portion that is exposed when a nipple is inserted into a Parker Rectus 21 DSO Series coupler.

Rectus 21 DSO Series Nipples - Male Pipe Thread



Body Size (in.)	Old Part Number	New Part Number	Weight (lbs.)	Thread Size	Overall Length (in.)	Exposed Length*	Largest Diameter	Wrench Flats
1/8	DM-122-2MP	21SBAN10MVN	0.05	1/8-27 NPTF	1.65	1.12	0.63	0.55
1/8	DM-122-4MP	21SBAN13MVN	0.06	1/4-18 NPTF	1.77	1.24	0.63	0.55

* This dimension represents the portion that is exposed when a nipple is inserted into a Parker Rectus 21 DSO Series coupler.



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Hydraulic Quick Couplings

Ordering Information

When ordering Parker coupler bodies and nipples, please state the part number of each type of coupler body and each type of nipple desired. List coupler bodies and nipples as separate items rather than in combinations. Be sure to double check thread or hose sizes of items required.

Many of Parker's coupling products are available with unique non-standard options well suited to very specific applications. Examples of unusual end use applications might include: high temperatures (above 250° F), extremely caustic/corrosive solutions passing through the coupling, external/environmental corrosion situations, or other high wear and tear situations such as dragging the product along the ground. Please see the Fluid Compatibility Chart at the end of the catalog for a guide in selecting material for various media. It is always recommended that the Quick Coupling Division be contacted with any questions concerning specific product application needs.

Typically, a prefix or suffix is added to the base part number to specify a non-standard O-ring seal, or special option such as a sleeve lock. The Optional Seals Suffix chart illustrates the designations.

Optional Features

- Prefix "HD" for Heavy Duty Nipple
- Suffix "SL" for Coupler Sleeve-Lok
- Suffix "P" for Poppet Valve
- Suffix "BP" for Push-Lok Hose Barb
- Suffix "VA" for Valve Actuator

N/A = Not Available

STD = Standard (No Suffix Needed)

* To select proper seal materials, see Fluid Compatibility Chart in Appendices section, or contact your Parker Quick Coupling Distributor.

** Fluorocarbon seal available for use only with oil based media, not water glycol.

*** Contact QCD for Perfluoroelastomer seal options.

Optional Seals Suffix

No suffix is required when ordering products with the standard Nitrile seals.

When specifying an optional seal, refer to the following chart to determine the appropriate suffix.

Coupling Series	Ethylene Propylene	Fluorocarbon	Neoprene	Perfluoroelastomer
60 Series	W	Y	Z	***
6600 Series	W	Y	Z	***
SM Series	E5	E4	E12	***
HP Series	E5	E4	E12	***
4000 Series	W	Y	Z	N/A
4200 Series	W	Y	Z	N/A
NS Series	E5	E4	N/A	***
FF Series Std. is E49	E5	E4	N/A	***
FH Series	E5	E4	N/A	***
FS Series	E5	STD	E12	***
6100 Series	W	Y	Z	N/A
5000 Series	W	Y	Z	N/A
8200 Series	W	Y	Z	N/A
9200 Series	W	Y	Z	N/A
3000 Series	Available with Polyurethane only (no suffix needed)			
TC Series	Available with Fluorocarbon only (no suffix needed)			
1141 Series	Available with Polyurethane only (no suffix needed)			
ST Series	W	Y	Z	
Water Service	Available with Nitrile only			
HO Series	E5	E4	E12	N/A
Moldmate Series Std. is Silicone	N/A	Y**	N/A	N/A

Hydraulic Quick Couplings


Diagnostic Test Port Couplings



Test Port Couplings and SensoControl



[Catalog 4054-3/UK – SensoControl Diagnostic Products](#) ▶



[Catalog 4083-4/UK – SensoControl Industrial Products](#) ▶



For information on Parker's Diagnostic and Industrial solutions, review these SensoControl catalogs or visit Parker.com/SensoControl.

Test Port Coupling Selection Guide

Test Port	Valving Style	Body Size (in.)	Material*			Locking Mechanism	Standard Seal Material	Rated Pressure (psi)	Temp Range**
			Br	SS	S				
PD Series	Flush Face	1/8"	n	n	n	Ball	Nitrile	6000	-40° to +250° F
PDP Series	Ball (Nipple only)	1/8"			n	Ball	Nitrile	6000	-40° to +250° F
EMA3 Series	Poppet	1/8"		n	n	Threads	Nitrile/Fluorocarbon	9000	-15° to +250° F

* See Fluid Compatibility chart and/or consult QCD for questions regarding proper material for specific applications.

CODE: Br = Brass; SS = Stainless Steel; S = Steel

** Temperature Range for standard seal material

Hydraulic Quick Couplings

Couplings

PD Series

Test Port Couplings

PD Series couplings provide easy connection for mechanical gauges or specialized diagnostic equipment like SensoControl®.

Typically, PD or BPD nipples are permanently mounted in the system at threaded test ports, in rigid tubing or in hose assemblies. PD couplers are attached to test instruments.

Couplers align to the mating nipples without threading. This allows gauges, transducers and other test equipment to be snapped into place without difficulty.

Note: Protective dust caps play a crucial role in the life of a quick coupling and no purchase is complete without the selection of an appropriate dust cap.



Features:

- Flush-face poppet valves minimize air inclusion and spillage, provide easy-to-clean surfaces, and help to prevent contamination.
- Grip-tight knurled sleeves help to make connecting and disconnecting easy, even while wearing gloves.
- Nipples are machined from high tensile steel for strength to withstand 6000 PSI continuous operating pressure. BPD nipples offer features similar to the standard steel PD nipples with the added feature of a brass body.
- PD nipples are designed to meet or exceed SAE J1502 and ISO 15171-1 design and performance specifications.
- Nipples are also referred to as compucheck fittings. They are used to attach quick-connect fuel lines at various points in the fuel system such as the fuel system priming pump.
- End connections include pipe, O-ring, metric thread, bulkhead, 37° Flare, ORFS and bite-type.

Optional Seals Suffi

No suffix is required when ordering products with the standard Nitrile seals. When specifying an optional seal, refer to the following chart to determine the appropriate suffix.

Coupling Series	Ethylene Propylene	Fluorocarbon	Neoprene
PD Series	W	Y	Z

**To select proper seal materials, see Fluid Compatibility Chart in Appendix section, or contact your Parker Quick Coupling Distributor.*

Ordering Information

Coupler / Nipple Material

- Prefix "B" for Brass Body with Fluorocarbon seal
- Prefix "SS" for Stainless Steel Body with Fluorocarbon seal
- Standard body material is Steel with Nitrile seal
- Suffix "-6" to include Dust Cap with Nipp

PD Series Specifications - Body Size 1/8

Description	PD Coupler	PD Nipple	BPD Nipple	Assembly
Part Number	PD242	PD361	BDP343Y	—
Body Material (Steel)	Carbon Steel	High Tensile Steel	Brass	—
Rated Pressure (psi)	6000	6000	300	6000
Temperature Range (STD Seals) Nitrile	-40°F to +250°F		-15°F to +400°F Fluorocarbon	-40°F to +250°F
Rated Flow (gpm)	—	—	—	0.8
Max. Recommended Flow (gpm)	—	—	—	4.0
Vacuum Data (Inches Hg)	27.5	27.5	27.5	27.5
Pressure Drop at Rated Flow (PSI) with 200 SUS Fluid	—	—	—	56
Spillage at 15 PSI (ml)-Assembly	0.1 per disconnect			
Air Inclusion (ml)-Assembly	0.02 per connect			
Connect Force-Assembly	41 Lbs. (100 PSI)			
Disconnect Force-Assembly	20 Lbs. (100 PSI)			

Hydraulic Quick Couplings

Couplings

PD Series

Test Port Couplings

PD Series Couplers - Female Thread



Body Size (in.)	Part Number	Thread Size	Overall Length (in.)	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD222	1/8-27 NPTF	1.67	0.81	0.96	0.20
1/8	PD240	7/16-20 UNF	2.12	0.81	0.96	0.26
1/8	PD242	1/4-18 NPTF	2.12	0.81	0.96	0.25
1/8	SSPD242Y**	1/4-18 NPTF	2.12	0.81	0.96	0.25
1/8	PD260	9/16-18 UNF	2.12	0.81	0.96	0.24
1/8	PD248	1/4-19 BSPP	2.12	1.19	-	0.38
1/8	PD288	1/2-14 BSPP	2.52	1.19	-	0.35

PD Series Couplers - Male Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD243	1/4-18 NPTF	2.26	0.81	0.96	0.23

PD Series Nipples - Female Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD322	1/8-27 NPTF	1.48	0.78	0.56	0.65	0.06
1/8	PD342	1/4-18 NPTF	1.63	0.93	0.75	0.87	0.12

PD Series Nipples - Male Pipe Thread



Body Size (in.)	Part Number	Thread Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD323	1/8-27 NPTF	1.55	0.85	0.69	0.79	0.17
1/8	BPD323Y*	1/8-27 NPTF	1.44	0.74	0.63	0.72	0.17
1/8	BPD343Y*	1/4-18 NPTF	1.48	0.78	0.69	0.79	0.06
1/8	PD343	1/4-18 NPTF	1.48	0.78	0.69	0.79	0.06
1/8	SSPD343Y**	1/4-18 NPTF	1.48	0.78	0.69	0.79	0.06
1/8	PD363	3/8-18 NPTF	1.50	1.13	0.81	0.96	0.09

* BPD designates brass body, Fluorocarbon seal standard

** SSPD designates 316SS body, Fluorocarbon seal standard



Note: Add -6 to Nipple part number to include dust cap, for example PD343-6

Hydraulic Quick Couplings

Couplings

PD Series

Test Port Couplings

PD Series Nipples - Male Metric Thread



Body Size (in.)	Part Number	Thread Size Metric	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD357	M10 x 1.0	1.80	1.10	0.69	0.79	0.17
1/8	PD397	M12 x 1.5	1.85	1.05	0.69	0.79	-
1/8	PD367C	M14 x 1.5	1.50	0.80	0.75	0.87	0.07
1/8	PD3107	M16 x 1.5	1.54	0.84	0.88	1.01	0.08
1/8	PD3127	M18 x 1.5	1.60	0.90	0.94	1.08	0.09
1/8	PD3147	M20 x 1.5	1.50	0.80	0.75	0.87	0.07
1/8	BPD3167	M22 x 1.5	1.65	0.95	1.12	1.30	-

PD Series Nipples - Male Straight Thread



Body Size (in.)	Part Number	Thread Size ORB	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD331	3/8-24 UNF	1.80	1.10	0.69	0.79	0.17
1/8	PD341	7/16-20 UNF	1.60	0.90	0.69	0.79	0.08
1/8	PD351	1/2-20 UNF	1.32	0.62	0.63	0.72	0.05
1/8	PD361	9/16-18 UNF	1.32	0.62	0.69	0.79	0.06

PD Series Nipples - Bulkhead Triple-Lok



Body Size (in.)	Part Number	Thread Size	Tube Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD345	7/16-20 UNF	1/4	2.92	2.22	0.81	0.94	0.19
1/8	PD355	1/2-20 UNF	5/16	2.92	2.22	0.81	0.94	0.19
1/8	PD365	9/16-18 UNF	3/8	3.00	2.30	0.81	0.94	0.20

PD Series Nipples - Bulkhead Seal-Lok



Body Size (in.)	Part Number	Thread Size	Tube Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PD346	9/16-18 UNF	1/4	2.98	2.27	0.81	0.94	-
1/8	PD366	11/16-16 UNF	3/8	3.08	2.37	1.00	1.16	-
1/8	PD386	13/16-16 UNF	1/2	3.18	2.47	1.12	1.30	-

* Note: Add -6 to part number to include dust cap, for example PD343-6

* BPD designates brass body, Fluorocarbon seal standard

** SSPD designates 316SS body, Fluorocarbon seal standard

Hydraulic Quick Couplings

Couplings

PD Series

Test Port Couplings

PD Series Tube End Nipples*- Triple Lok



Body Size (in.)	Part Number Steel	Tube Size	Overall Length (in.)	Exposed Length	Weight (lbs.)
1/8	PD34BTX	1/4	1.64	0.94	0.10
1/8	PD36BTX	3/8	1.66	0.96	0.09



Body Size (in.)	Part Number Steel	Tube Size	Overall Length (in.)	Exposed Length	Weight (lbs.)
1/8	PD38BTX	1/2	1.17	0.47	0.12
1/8	PD312BTX	3/4	1.39	0.69	0.27

*Tube end nipples are designed to meet the performance standards of the tube or hose fitting connection, which may or may not meet SAE J1502 Standards

PD Series Tube End Nipples*- Seal Lok



Body Size (in.)	Part Number Steel	Tube Size	Overall Length (in.)	Exposed Length	Weight (lbs.)
1/8	PD34BTL	1/4	2.18	1.48	0.12
1/8	PD36BTL	3/8	2.30	1.60	0.14



Body Size (in.)	Part Number Steel	Tube Size	Overall Length (in.)	Exposed Length	Weight (lbs.)
1/8	PD38BTL	1/2	1.57	0.83	0.13
1/8	PD310BTL	5/8	1.16	0.46	0.19

*Tube end nipples are designed to meet the performance standards of the tube or hose fitting connection, which may or may not meet SAE J1502 Standards

PD Series Dust Cap



Body Size	Dust Cap Part Number
1/8	PD6-285



Note: Add -6 to Nipple part number to include dust cap, for example PD343-6

Hydraulic Quick Couplings

Couplings

PDP Series

Test Port Couplings

PDP Series couplings provide easy connection for mechanical gauges or specialized diagnostic equipment like SensoControl.

Typically, PDP nipples are permanently mounted in the system at threaded test ports, in rigid tubing or in hose assemblies. PDP couplers are attached to test instruments.

Locking balls align the couplers to the mating nipples without threading, so gauges, transducers and other test equipment can be snapped into place without difficulty.

Parker's PDP Series couplings offer the advantages of PD couplings, but are designed to connect easily and quickly under full system pressure up to 6000 PSI (operating).

PDP couplers and nipples push to connect with a constant force of only six pounds. Then the coupler base is turned to open the valve and complete the connection. In the connected position, the coupler base blocks the retracting sleeve to prevent accidental disconnects.



Features:

- Made to connect under pressure up to 6000 psi
- Grip-tight knurled sleeves help to make connecting and disconnecting easy, even while wearing gloves
- Nipples are machined from high tensile steel for strength to withstand 6000 PSI continuous operating pressure
- End connections include pipe, O-ring, 37° Flare and ORFS
- Durable Ball Valve Nipple
- Coupler is unvalved to allow gauges and transducers to return to zero when disconnected

PDP Series Specifications - Body Size 1/8

Description	PDP Coupler	PDP Nipple	Assembly
Body Material (Steel)	Carbon Steel	High Tensile Steel	—
Rated Pressure (psi)	—	6000	6000
Temperature Range (STD Seals) Nitrile	-40°F to +250°F		
Connect Force-Assembly	6 Lbs. (0-6000 PSI)		
Disconnect Force-Assembly	7 Lbs. (0-6000 PSI)		

Optional Seals Suffi

No suffix is required when ordering products with the standard Nitrile seals. When specifying an optional seal, refer to the following chart to determine the appropriate suffix.

Coupling Series	Ethylene Propylene	Fluorocarbon	Neoprene
PDP Series	W	Y	Z

*To select proper seal materials, see Fluid Compatibility Chart in Appendix section, or contact your Parker Quick Coupling Distributor.

Ordering Information

Coupling / Nipple Material:
Standard body material is Steel
Standard seal material is Nitrile



Note: Add -6 to Nipple part number to include dust cap, for example PD343-6

PD Series Dust Cap



Body Size

Dust Cap Part Number

1/8

PD6-285

Hydraulic Quick Couplings

Couplings

PDP Series

Test Port Couplings

PDP Series Coupler - Female Thread



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Largest Diameter	Wrench Flats	Weight (lbs.)
1/8	PDP242	1/4-18 NPTF	2.15	0.96	0.81	-
1/8	PDP288	1/2-14BSPP	2.58	-	1.19	0.35

PDP Series Nipples - Male Pipe Thread



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PDP323	1/8-27 NPTF	2.02	1.46	0.69	0.79	0.26
1/8	PDP343	1/4-18 NPTF	1.48	0.93	0.69	0.79	0.12

PDP Series Nipples - Male Straight Thread



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PDP341	7/16-20 UNF	2.06	1.50	0.69	0.79	0.12
1/8	PDP361	9/16-18 UNF	1.48	0.93	0.69	0.79	0.07

PDP Series Nipples - Triple-Lok



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PDP34BTX	1/4	2.11	1.55	0.69	0.80	-
1/8	PDP36BTX	3/8	2.13	1.57	0.69	0.80	-

PDP Series Nipples - Seal-Lok



Body Size (in.)	Part Number Steel	Thread Size	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PDP34BTL	1/4	2.65	2.09	0.69	0.80	-
1/8	PDP36BTL	3/8	2.77	2.21	0.81	0.94	-

Hydraulic Quick Couplings

Couplings

EMA3 Series

Test Port Couplings

EMA couplings provide easy diagnostic connections for Parker SensoControl® equipment or mechanical gages. EMA test points are typically permanently plumbed into a fluid system at locations where pressure measurements are required for maintenance or testing. Integral pressure cap protects the test point from damage and prevents contamination of the fluid system. Proven twist-to-connect design allows the test points to be connected even when the system is in operation and the test points are pressurized. EMA's compact design and optional high pressure hose assemblies allow extra flexibility for the location of system test points.

Although designed primarily for diagnostic applications, EMA fittings and hose assemblies are a good idea for a wide range of applications that require compact high pressure connections and limited flow rates.

Features:

- Knurled sleeve allows simple twist-to-connect operation without the use of tools
- Rugged design allows connect-under-pressure operation up to 5800 psi
- Maximum rated working pressure of 9000 psi exceeds the requirements of most applications
- Integral threaded dust cap protects the test point from damage and contamination
- EMA fittings are machined from solid barstock and protected with Chromium-6 Free plating.
- Stainless steel springs for corrosion resistance
- Elastomeric interface and valve seals provide leak free operation
- Compact design and optional high pressure hose assemblies provide flexibility for tight space requirements



EMA3 Series Specification

Body Size	Rated Pressure (psi)	Max Connect-Under-Pressure Capability (psi)	Rated Flow (gpm)	Body Material	Seal Material Steel (CF)	Seal Material SS (71)	Nitrile (external)
1/8	9000	5800	0.8	Chromium-6 Free Plated Steel	Fluorocarbon (internal) Nitrile (external)	Fluorocarbon (internal) Fluorocarbon (external)	-15° to +250° F

EMA3 Series - Male Pipe Thread

	New Part Number	Old Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	EMA3/1/8NPTCF	EMA3/1/8NPT	1/8-27NPT	17mm	M16 X 2.0	1.81	0.15
	EMA3/1/4NPTCF	EMA3/1/4NPT	1/4-18NPT	17mm	M16 X 2.0	1.98	0.16
	EMA3/1/4NPT71 Stainless Steel	EMA3/1/4NPT71 Stainless Steel	1/4-18NPT	17mm	M16 X 2.0	1.95	0.16

EMA3 Series - SAE Straight Thread

	New Part Number	Old Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	EMA3/7/16UNFCF*	EMA3/7/16-20UNF-2A	7/16-20UNF-2A	17mm	M16 X 2.0	1.88	0.15
	EMA3/9/16UNFCF*	EMA3/9/16-18UNF-2A	9/16-18UNF-2A	19mm	M16 X 2.0	1.88	0.17
	* O-Ring seal on port						

Hydraulic Quick Couplings

Couplings

EMA3 Series

Test Port Couplings


EMA3 Series - Metric Straight Thread

	New Part Number	Old Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	EMA3/8X10RCF*	EMA3/M8X10R	M8X1	17mm	M16 X 2.0	1.81	0.15
	EMA3/10X1EDCF**	EMA3/10X1ED	M10X1	17mm	M16 X 2.0	1.85	0.15
	EMA3/12X1.5EDCF**	EMA3/12X1.5ED	M12X1.5	17mm	M16 X 2.0	1.94	0.16
	EMA3/14X1.5EDCF**	EMA3/14X1.5ED	M14X1.5	19mm	M16 X 2.0	1.94	0.16
* O-Ring seal on port		**Molded seal on port					

EMA3 Series - British Parallel Pipe

	New Part Number	Old Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	EMA3/1/8EDCF**	EMA3/1/8ED	1/8 BSPP	19mm	M16 X 2.0	1.77	0.15
	EMA3/1/4EDCF**	EMA3/1/4ED	1/4 BSPP	19mm	M16 X 2.0	1.94	0.16
	EMA3/3/8EDCF**	EMA3/3/8ED	3/8 BSPP	21mm	M16 X 2.0	1.94	0.16
**Molded seal on port							

EMA3 Series - EMA Gauge Adapter

	Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	MAV1/4NPTMA3CF	1/4-18NPT	19mm	M16 X 2.0	2.22	0.15
	MAV1/4NPTMA3KMCF Includes Dust Cap	1/4-18NPT	19mm	M16 X 2.0	2.22	0.17
	Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	MAVMD1/4NPTMA3CF	1/4-18NPT	19mm	M16 X 2.0	2.22	0.18
	SCA-7/16-EMA-3	7/16-20UNF	19mm	M16 X 2.0	1.60	-

EMA3 Series - Union

	New Part Number	Old Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (in.)	Weight (lbs.)
	SCA-EMA-3/3	EMA3VSCF	M16 X 2.0	17mm	M16 X 2.0	1.65	0.11

EMA3 Series - Transducer Adapters BSPP Thread*

	Part Number	Port Thread Size	Wrench Flats	Interface Thread Size	Overall Length (mm)	Weight (lbs.)
	SCA-1/4-EMA-3CF	1/4-19 BSPP	27mm	M16 X 2.0	32mm	0.30
	SCA-1/2-EMA-3	1/2-14 BSPP	27mm	M16 X 2.0	36mm	0.30
* Note: For old style M22X1.5 thread contact QCD						

Hydraulic Quick Couplings

Couplings

Transducer Adapters

Test Port Couplings

Flexible Hose				
	Part Number	Length (in.)	Length (mm)	Thread Size
	SMA3-200CF	7.90	200	M16 X 2.0
	SMA3-400CF	15.75	400	M16 X 2.0
	SMA3-800CF	31.50	800	M16 X 2.0
	SMA3-1000CF	39.38	1000	M16 X 2.0
	SMA3-2000CF	78.75	2000	M16 X 2.0
	SMA3-4000CF	157.50	4000	M16 X 2.0

Note: Other lengths available upon request.
Maximum pressure rating for test hose is 9000 psi.

Hose Assembly				
	Part Number	Length (in.)	Length (mm)	Coupling
	PDH-19	19	483	PD
	PDH-32	32	813	PD
	PDH-120	120	3048	PD
	PDH-240	240	6096	PD

Note: Maximum pressure rating for test hose is 6000 psi.

Hydraulic Quick Couplings

Couplings

Fluid Sampling

Test Port Couplings

These diagnostic fluid sampling products are designed to provide an easy access point for obtaining fluid samples. A permanently mounted test point eliminates the need to shut down or break lines when taking samples and reduces the chances of contamination. Fluid analysis is crucial in both engines and hydraulic systems as it can reveal problems with filtration and other internal components. Early detection can prevent costly repairs, unscheduled maintenance and production downtime. These fluid sampling nipples should be installed in either low pressure or return lines. For the most accurate monitoring, fluid samples should be constantly taken from the same location.



Fluid Sampling Specifications

Body Size	1/8
Rated Pressure (psi)	500 PSI
Seal Material	Fluorocarbon
Temperature Range (std. seals) (Fluorocarbon)	-40° to +250° F

Fluid Sampling Couplers - Female Thread



Body Size (in.)	Part Number	Female Thread NPTF	Female Thread ORB	Overall Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	PDFS242	1/4-18	-	2.15	0.81	0.96	0.25

Fluid Sampling Nipples - Male Thread



Body Size (in.)	Part Number	Thread Size ORB or NPTF	Thread Size Metric	Overall Length (in.)	Exposed Length	Wrench Flats	Largest Diameter	Weight (lbs.)
1/8	BPDFS341	7/16-20 ORB	-	1.60	0.90	0.69	0.79	0.08
1/8	BPDFS343	1/4-18 NPTF	-	1.48	0.78	0.69	0.79	0.06
1/8	PDFS-PROBE*	-	N/A	-	-	-	-	-

* Fluorocarbon seal is standard.

Dust Cap PD6-285 is recommended.

Hydraulic Quick Couplings

Couplings

Tee Fittings

Diagnostic Fittings

Parker's in-line diagnostic tees are designed to work with the SensoControl diagnostic couplings.

The tee fittings are offered in a standard and custom line of fixed flow control orifice fittings. These products are available as standard in two Parker product series — ORFS and 37° flare, and as a custom option in virtually any orifice size, fitting series, size, material and configuration.



Features:

- Designed around the two most common hydraulic tube/hose interfaces: O-ring face seal (Parker Seal-Lok) and 37° fl are (JIC / Parker Triple-Lok)
- ORFS and 37° fl are swivel feature offers unlimited positioning without displacing port adapter
- Uses elastomeric sealing: SAE -4 (7/16-20 UNF) port as universal diagnostic port per SAE J1926-1/ISO 11926
- Enlarged and lengthened body hex ensures that diagnostic port offers full thread engagement and pressure capability
- Adaptable to Parker's line of diagnostic and fluid sampling tips including: EMA3, PD and PDFS, as well as various direct connecting electronic/mechanical pressure gauges

Tee Fittings

Part Number (PD)	Type	Picture	Port #1	Port #2	L (in.)	Hex (in.)	Weight (lbs.)
4-4 LOHL6G5TP-S-PD	ORFS		1/4	1/4	1.83	1.063	0.3535
6-4 LOHL6G5TP-S-PD	ORFS		3/8	3/8	1.95	1.063	0.3855
8-4 LOHL6G5TP-S-PD	ORFS		1/2	1/2	2.18	1.063	0.4325
10-4 LOHL6G5TP-S-PD	ORFS		5/8	5/8	2.40	1.125	0.5430
12-4 LOHL6G5TP-S-PD	ORFS		3/4	3/4	2.59	1.25	0.7475
16-4 LOHL6G5TP-S-PD	ORFS		1	1	2.85	1.50	1.0570
4-4 XHX6G5TP-S-PD	37° Flare		1/4	1/4	1.99	1.063	0.3275
6-4 XHX6G5TP-S-PD	37° Flare		3/8	3/8	2.08	1.063	0.3390
8-4 XHX6G5TP-S-PD	37° Flare		1/2	1/2	2.30	1.063	0.3780
10-4 XHX6G5TP-S-PD	37° Flare		5/8	5/8	2.49	1.125	0.4380
12-4 XHX6G5TP-S-PD	37° Flare		3/4	3/4	2.66	1.25	0.5765
16-4 XHX6G5TP-S-PD	37° Flare		1	1	2.99	1.50	0.8280

Part Number (EMA)	Type	Picture	Port #1	Port #2	L (in.)	Hex (in.)	Weight (lbs.)
4-4 LOHL6G5TP-S-EMA	ORFS		1/4	1/4	1.83	1.063	0.4120
6-4 LOHL6G5TP-S-EMA	ORFS		3/8	3/8	1.95	1.063	0.4440
8-4 LOHL6G5TP-S-EMA	ORFS		1/2	1/2	2.18	1.063	0.4925
10-4 LOHL6G5TP-S-EMA	ORFS		5/8	5/8	2.40	1.125	0.6025
12-4 LOHL6G5TP-S-EMA	ORFS		3/4	3/4	2.59	1.25	0.8015
16-4 LOHL6G5TP-S-EMA	ORFS		1	1	2.85	1.50	1.1140
4-4 XHX6G5TP-S-EMA	37° Flare		1/4	1/4	1.99	1.063	0.3865
6-4 XHX6G5TP-S-EMA	37° Flare		3/8	3/8	2.08	1.063	0.3960
8-4 XHX6G5TP-S-EMA	37° Flare		1/2	1/2	2.30	1.063	0.4385
10-4 XHX6G5TP-S-EMA	37° Flare		5/8	5/8	2.49	1.125	0.4965
12-4 XHX6G5TP-S-EMA	37° Flare		3/4	3/4	2.66	1.25	0.6360
16-4 XHX6G5TP-S-EMA	37° Flare		1	1	2.99	1.50	0.8900

Hydraulic Quick Couplings

Promotional Products

These popular Quick Coupling Key Chains are constructed of anodized aluminum and are available in an array of colors. The original design, nickel plated version can be ordered as well.



Quick Coupling Key Chains

Part Number	Sleeve Color
KEY-BK	Black
KEY-BU	Blue
KEY-GR	Green
KEY-RD	Red
KEY-CL	Clear



Swivels

Table of Contents

PS Series

Introduction..... C-1

Seal Options..... C-1

How To Order C-2

Repair Kits C-2

In-Line C-3

90°C-7

S Series

IntroductionC-14

Repair KitsC-14

How To OrderC-15

90°C-16

Swivels

PS Series

Introduction

The PS Series Swivel is designed to meet today's application needs and performance requirements. Pressure capabilities up to 5000 psi, 3/8" through 1" body sizes, a variety of port options, and Chromium-6 Free plating make the PS Series Swivels ideal for an array of dynamic applications.



Features:

- Hardened bearing races for extended service life.
- Full flow design minimizes pressure drop for optimum system performance.
- Sealed bearing design isolates bearing race from media and environment.
- Reduced bearing load design minimizes wear in the bearing race and extends service life.
- PTFE back-up rings support primary seal for high-pressure applications.
- Chromium-6 Free plating for maximum corrosion resistance.
- PS Series Swivels eliminate hose twist and torque that may cause premature hose failure.

PS Series Specification


Body Size (in.)	3/8	1/2	3/4	1
Maximum Rated Pressure (psi)	5000	5000	5000	5000
Except the following port options in the noted size				
03 (Male JIC 37°)				
05 (Male SAE O-Ring Boss)				
06 (Female JIC 37°) In-Line Housing Port				
07 (Female NPSM)		4600	3000	2600
Temperature Range	-40° to 250°			

Seal Options


Nitrile

Performance


Recommended Max. Speed vs. Pressure



Torque vs. Pressure



90 PS Swivel
150 SUS Oil Flow vs. Pressure Drop




Swivels


PS Series

How To Order


In-Line Swivels




PS Part Number



90° Swivels



PS Part Number



PS Series Repair Kits (In-line and 90°)

Repair Kits come complete with O-Rings, PTFE Back-Up Ring, Cap Screws, Locking Balls, Retaining Ring and grease fitting. Repair kits are suitable for both current and previous design in-line and 90° PS Series Swivels.

3/8" Swivel	1/2" Swivel	3/4" Swivel	1" Swivel
PS6-RPR	PS8-RPR	PS12-RPR	PS16-RPR
PS6Y-RPR	PS8Y-RPR	PS12Y-RPR	PS16Y-RPR
PS6A-RPR	PS8A-RPR	PS12A-RPR	PS16A-RPR
PS6W-RPR	PS8W-RPR	PS12W-RPR	PS16W-RPR

Swivels

PS Series

In-Line



Materials Of Construction

Housing:Carbon Steel



Shaft:Carbon Steel

Plating:Chromium-6 Free


Bearing:Chrome

O-Rings:Nitrile

Back-Up Ring PTFE



PS Series Male Pipe - Female Pipe




Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS610102-6-6	2.66" 67.5 mm	1.64" 41.7 mm	3/8-18 NPTF	3/8-18 NPTF	0.88" 22.2 mm	1.31" 33.3 mm
PS810102-8-8	3.03" 76.8 mm	1.79" 45.5 mm	1/2-14 NPTF	1/2-14 NPTF	1.12" 28.6 mm	1.50" 36.5 mm
PS1210102-12-12	3.10" 78.8 mm	1.85" 47.0 mm	3/4-14 NPTF	3/4-14 NPTF	1.38" 35.0 mm	1.69" 42.9 mm
PS1610102-16-16	3.54" 89.8 mm	2.11" 53.5 mm	1-11 1/2 NPTF	1-11 1/2 NPTF	1.62" 41.3 mm	1.88" 47.6 mm

Swivels

PS Series


In-Line

PS Series Male Pipe - Female 37° Flair



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS610106-6-6	2.77" 70.3 mm	1.75" 44.5 mm	3/8-18 NPTF	9/16-18 UNF	0.88" 22.2 mm	1.31" 33.3 mm
PS810106-8-8	3.05" 77.3 mm	1.81" 46.0 mm	1/2-14 NPTF	3/4-16 UNF	1.12" 28.6 mm	1.50" 36.5 mm
PS1210106-12-12	3.27" 83.2 mm	2.02" 51.3 mm	3/4-14 NPTF	1-1/16-12 UN	1.38" 35.0 mm	1.69" 42.9 mm
PS1610106-16-16	3.62" 92.0 mm	2.19" 55.6 mm	1-11 1/2 NPTF	1-5/16-12 UN	1.62" 41.3 mm	1.88" 47.6 mm

PS Series Male 37° Flare - Female Pipe



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS610302-6-6	2.66" 67.5 mm	1.64" 41.7 mm	9/16-18 UNF	3/8-18 NPTF	0.88" 22.2 mm	1.31" 33.3 mm
PS810302-8-8	2.89" 73.5 mm	1.79" 45.5 mm	3/4-16 UNF	1/2-14 NPTF	1.12" 28.6 mm	1.50" 36.5 mm
PS1210302-12-12	3.21" 81.5 mm	1.85" 47.0 mm	1-1/16-12 UNF	3/4-14 NPTF	1.38" 35.0 mm	1.69" 42.9 mm
PS1610302-16-16	3.54" 89.8 mm	2.11" 53.5 mm	1-5/16-12 UNF	1-11 1/2 NPTF	1.62" 41.3 mm	1.88" 47.6 mm

 WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


In-Line

PS Series Male 37° Flare - Female 37° Flare



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS610306-6-6	2.77" 70.3 mm	1.75" 44.5 mm	9/16-18 UNF	9/16-18 UNF	0.88" 22.2 mm	1.31" 33.3 mm
PS810306-8-8	2.91" 74.0 mm	1.81" 46.0 mm	3/4-16 UNF	3/4-16 UNF	1.12" 28.6 mm	1.50" 36.5 mm
PS1210306-12-12	3.38" 85.8 mm	2.02" 51.3 mm	1-1/16-12 UN	1-1/16-12 UN	1.38" 35.0 mm	1.69" 42.9 mm
PS1610306-16-16	3.62" 92.0 mm	2.19" 55.6 mm	1-5/16-12 UN	1-5/16-12 UN	1.62" 41.3 mm	1.88" 47.6 mm

PS Series Male SAE O-Ring Straight Thread - Female Pipe



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS610502-6-6	2.48" 63.0 mm	1.64" 41.7 mm	9/16-18 UNF	3/8-18 NPTF	0.88" 22.2 mm	1.31" 33.3 mm
PS810502-8-8	2.79" 70.8 mm	1.79" 45.5 mm	3/4-16 UNF	1/2-14 NPTF	1.12" 28.6 mm	1.50" 36.5 mm
PS1210502-12-12	3.02" 76.7 mm	1.85" 47.0 mm	1-1/16-12 UN	3/4-14 NPTF	1.38" 35.0 mm	1.69" 42.9 mm
PS1610502-16-16	3.31" 84.1 mm	2.11" 53.5 mm	1-5/16-12 UN	1-11 1/2 NPTF	1.62" 41.3 mm	1.88" 47.6 mm

**WARNING**


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


In-Line

PS Series Male SAE O-Ring Straight Thread - Female 37° Flare



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS610506-6-6	2.59" 65.8 mm	1.75" 44.5 mm	9/16-18 UNF	9/16-18 UNF	0.88" 22.2 mm	1.31" 33.3 mm
PS810506-8-8	2.81" 71.3 mm	1.81" 46.0 mm	3/4-16 UNF	3/4-16 UNF	1.12" 28.6 mm	1.50" 36.5 mm
PS1210506-12-12	3.19" 81.1 mm	2.02" 51.3 mm	1-1/16-12 UN	1-1/16-12 UN	1.38" 35.0 mm	1.69" 42.9 mm
PS1610506-16-16	3.40" 86.3 mm	2.19" 55.6 mm	1-5/16-12 UN	1-5/16-12 UN	1.62" 41.3 mm	1.88" 47.6 mm

PS Series Male Seal-Lok - Male Seal-Lok



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS61JMJM-6-6	2.67" 67.8 mm	1.83" 46.5 mm	11/16 - 16 UN	11/16 - 16 UN	0.88" 22.2 mm	1.31" 33.3 mm
PS81JMJM-8-8	2.89" 73.4 mm	1.90" 48.3 mm	13/16 - 16 UN	13/16 - 16 UN	1.12" 28.6 mm	1.50" 36.5 mm
PS121JMJM-12-12	3.26" 82.8 mm	2.09" 53.1 mm	1-3/16 - 12 UN	1-3/16 - 12 UN	1.38" 35.0 mm	1.75" 44.4 mm
PS161JMJM-16-16	3.41" 86.6 mm	2.20" 55.9 mm	1-7/16 - 12 UN	1-7/16 - 12 UN	1.62" 41.3 mm	1.88" 47.6 mm

 WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Swivels

PS Series
90°




Materials Of Construction

Housing:Carbon Steel
Shaft:Carbon Steel
Plating: Chromium-6 Free
Bearing:Chrome
O-Rings:Nitrile
Back-Up Ring PTFE



PS Series Male Pipe - Female Pipe




Part Number Steel	A	B	Diameter	Port 1	Port 2	Wrench Flats 1
PS690102-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.29" 32.8 mm	3/8-18 NPTF	3/8-18 NPTF	0.88" 22.2 mm
PS890102-8-8	3.43" 87.0 mm	2.84" 72.0 mm	1.49" 37.8 mm	1/2-14 NPTF	1/2-14 NPTF	1.12" 28.6 mm
PS1290102-12-12	3.66" 93.0 mm	3.00" 76.1 mm	1.76" 44.6 mm	3/4-14 NPTF	3/4-14 NPTF	1.38" 35.0 mm
PS1690102-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.16" 54.9 mm	1-11 1/2 NPTF	1-11 1/2 NPTF	1.62" 41.3 mm

Swivels

PS Series


90°

PS Series Male Pipe - Male 37° Flare



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690103-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.44" 36.6 mm	2.09" 53.0 mm	1.29" 32.8 mm	3/8-18 NPTF	9/16-18 UNF	0.88" 22.2 mm	0.69" 17.5 mm
PS890103-8-8	3.43" 87.0 mm	2.84" 72.0 mm	1.78" 45.1 mm	2.64" 67.1 mm	1.73" 44.0 mm	1/2-14 NPTF	3/4-16 UNF	1.12" 28.6 mm	0.88" 22.2 mm
PS1290103-12-12	3.66" 93.0 mm	3.00" 76.1 mm	2.24" 56.9 mm	3.86" 85.3 mm	2.17" 55.2 mm	3/4-14 NPTF	1-1/16-12 UN	1.38" 35.0 mm	1.25" 31.8 mm
PS1690103-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.42" 61.3 mm	3.66" 92.9 mm	2.48" 63.0 mm	1-11 1/2 NPTF	1-5/16-12 UN	1.62" 41.3 mm	1.50" 38.1 mm

PS Series Male Pipe - Female NPSM Pipe Swivel



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690107-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.51" 38.4 mm	2.16" 54.8 mm	1.29" 32.8 mm	3/8-18 NPTF	3/8-18 NPSM	0.88" 22.2 mm	0.88" 22.2 mm
PS890107-8-8	3.43" 87.0 mm	2.84" 72.0 mm	1.86" 47.2 mm	2.72" 69.2 mm	1.73" 44.0 mm	1/2-14 NPTF	1/2-14 NPSM	1.12" 28.6 mm	1.00" 25.4 mm
PS1290107-12-12	3.66" 93.0 mm	3.00" 76.1 mm	2.24" 56.9 mm	3.33" 84.5 mm	2.17" 55.2 mm	3/4-14 NPTF	3/4-14 NPSM	1.38" 35.0 mm	1.25" 31.8 mm
PS1690107-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.48" 63.1 mm	3.73" 94.6 mm	2.48" 63.0 mm	1-11 1/2 NPTF	1-11 1/2 NPSM	1.62" 41.3 mm	1.50" 38.1 mm

 WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


90°

PS Series Male Pipe - Female SAE Straight Thread



Part Number Steel	A	B	Diameter	Port 1	Port 2	Wrench Flats 1
PS690110-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.29" 32.8 mm	3/8-18 NPTF	9/16-18 UNF	0.88" 22.2 mm
PS890110-8-8	3.43" 87.0 mm	2.84" 72.0 mm	1.73" 44.0 mm	1/2-14 NPTF	3/4-16 UNF	1.12" 28.6 mm
PS1290110-12-12	3.66" 93.0 mm	3.00" 76.1 mm	2.17" 55.2 mm	3/4-14 NPTF	1-1/16-12 UN	1.38" 35.0 mm
PS1690110-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.48" 63.0 mm	1-11 1/2 NPTF	1-5/16-12 UN	1.62" 41.3 mm

PS Series Male Pipe - Male Seal-Lok



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS6901JM-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.40" 35.6 mm	2.05" 52.0 mm	1.29" 32.8 mm	3/8-18 NPTF	11/16-16 UN	0.88" 22.2 mm	0.69" 17.5 mm
PS8901JM-8-8	3.43" 87.0 mm	2.84" 72.0 mm	1.74" 44.1 mm	2.60" 66.1 mm	1.73" 44.0 mm	1/2-14 NPTF	13/16-16 UN	1.12" 28.6 mm	0.88" 22.2 mm
PS12901JM-12-12	3.66" 93.0 mm	3.00" 76.1 mm	2.18" 55.4 mm	3.27" 83.0 mm	2.17" 55.2 mm	3/4-14 NPTF	1-3/16-12 UN	1.38" 35.0 mm	1.25" 31.8 mm
PS16901JM-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.34" 59.6 mm	3.59" 91.1 mm	2.48" 63.0 mm	1-11 1/2 NPTF	1-7/16-12 UN	1.62" 41.3 mm	1.50" 38.1 mm

**WARNING**


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


90°

PS Series Male 37° Flare - Female Pipe



Part Number Steel	A	B	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690302-6-6	3.05" 77.4 mm	2.54" 64.4 mm	9/16-18 UNF	3/8-18 NPTF	1.29" 32.8 mm	0.88" 22.2 mm
PS890302-8-8	3.29" 83.7 mm	2.70" 68.7 mm	3/4-16 UNF	1/2-14 NPTF	1.49" 37.8 mm	1.12" 28.6 mm
PS1290302-12-12	3.76" 95.6 mm	3.10" 78.8 mm	1-1/16-12 UN	3/4-14 NPTF	1.76" 44.6 mm	1.38" 35.0 mm
PS1690302-16-16	4.41" 112.0 mm	3.54" 90.0 mm	1-5/16-12 UN	1-11 1/2 NPTF	2.16" 54.9 mm	1.62" 41.3 mm

PS Series Male 37° Flare - Male 37° Flare



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690303-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.44" 36.6 mm	2.09" 53.0 mm	1.29" 32.8 mm	9/16-18 UNF	9/16-18 UNF	0.88" 22.2 mm	0.69" 17.5 mm
PS890303-8-8	3.29" 83.7 mm	2.70" 68.7 mm	1.78" 45.1 mm	2.64" 67.1 mm	1.73" 44.0 mm	3/4-16 UNF	3/4-16 UNF	1.12" 28.6 mm	0.88" 22.2 mm
PS890303-10-10	3.39" 86.2 mm	2.80" 71.2 mm	1.90" 48.4 mm	2.77" 70.4 mm	1.73" 44.0 mm	7/8-14 UNF	7/8-14 UNF	1.12" 28.6 mm	0.88" 22.2 mm
PS1290303-12-12	3.76" 95.6 mm	3.10" 78.8 mm	2.24" 56.9 mm	3.86" 85.3 mm	2.17" 55.2 mm	1-1/16-12 UN	1-1/16-12 UN	1.38" 35.0 mm	1.25" 31.8 mm
PS1690303-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.42" 61.3 mm	3.66" 92.9 mm	2.48" 63.0 mm	1-5/16-12 UN	1-5/16-12 UN	1.62" 41.3 mm	1.50" 38.1 mm

WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


90°

PS Series Male 37° Flare - Female NPSM Pipe Swivel



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690307-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.51" 38.4 mm	2.16" 54.8 mm	1.29" 32.8 mm	9/16-18 UNF	3/8-18 NPSM	0.88" 22.2 mm	0.88" 22.2 mm
PS890307-8-8	3.29" 83.7 mm	2.70" 68.7 mm	1.86" 47.2 mm	2.72" 69.2 mm	1.73" 44.0 mm	3/4-16 UNF	1/2-14 NPSM	1.12" 28.6 mm	1.00" 25.4 mm
PS1290307-12-12	3.76" 95.6 mm	3.10" 78.8 mm	2.24" 56.9 mm	3.33" 84.5 mm	2.17" 55.2 mm	1-1/16-12 UN	3/4-14 NPSM	1.38" 35.0 mm	1.25" 31.8 mm
PS1690307-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.48" 63.1 mm	3.73" 94.6 mm	2.48" 63.0 mm	1-5/16-12 UN	1-11 1/2 NPSM	1.62" 41.3 mm	1.50" 38.1 mm

PS Series Male 37° Flare - Female SAE Straight Thread



Part Number Steel	A	B	Diameter	Port 1	Port 2	Wrench Flats 1
PS690310-6-6	3.05" 77.4 mm	2.54" 64.4 mm	1.29" 32.8 mm	9/16-18 UNF	9/16-18 UNF	0.88" 22.2 mm
PS890310-8-8	3.29" 83.7 mm	2.70" 68.7 mm	1.73" 44.0 mm	3/4-16 UNF	3/4-16 UNF	1.12" 28.6 mm
PS1290310-12-12	3.76" 95.6 mm	3.10" 78.8 mm	2.17" 55.2 mm	1-1/16-12 UN	1-1/16-12 UN	1.38" 35.0 mm
PS1690310-16-16	4.41" 112.0 mm	3.54" 90.0 mm	2.48" 63.0 mm	1-1/16-12 UN	1-1/16-12 UN	1.62" 41.3 mm

**WARNING**


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


90°

PS Series Male SAE O-Ring Straight Thread - Female Pipe



Part Number Steel	A	B	Diameter	Port 1	Port 2	Wrench Flats
PS690502-6-6	2.87" 72.8 mm	2.36" 59.8 mm	1.29" 32.8 mm	9/16-18 UNF	3/8-18 NPTF	0.88" 22.2 mm
PS890502-8-8	3.19" 80.9 mm	2.60" 65.9 mm	1.49" 37.8 mm	3/4-16 UNF	1/2-14 NPTF	1.12" 28.6 mm
PS1290502-12-12	3.58" 90.9 mm	2.92" 74.0 mm	1.76" 44.6 mm	1-1/16-12 UN	3/4-14 NPTF	1.38" 35.0 mm
PS1690502-16-16	4.18" 106.3 mm	3.32" 84.3 mm	2.16" 54.9 mm	1-5/16-12 UN	1-11 1/2 NPTF	1.62" 41.3 mm

PS Series Male SAE O-Ring Straight Thread - Male 37° Flare



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690503-6-6	2.87" 72.8 mm	2.36" 59.8 mm	1.44" 36.6 mm	2.09" 53.0 mm	1.29" 32.8 mm	9/16-18 UNF	9/16-18 UNF	0.88" 22.2 mm	0.69" 17.5 mm
PS890503-8-8	3.19" 80.9 mm	2.60" 65.9 mm	1.78" 45.1 mm	2.64" 67.1 mm	1.73" 44.0 mm	3/4-16 UNF	3/4-16 UNF	1.12" 28.6 mm	0.88" 22.2 mm
PS890503-10-10	3.25" 82.5 mm	2.66" 67.5 mm	1.90" 48.4 mm	2.77" 70.4 mm	1.73" 44.0 mm	7/8-14 UNF	7/8-14 UNF	1.12" 28.6 mm	0.88" 22.2 mm
PS1290503-12-12	3.58" 90.9 mm	2.92" 74.0 mm	2.24" 56.9 mm	3.86" 85.3 mm	2.17" 55.2 mm	1-1/16-12 UN	1-1/16-12 UN	1.38" 35.0 mm	1.25" 31.8 mm
PS1690503-16-16	4.18" 106.3 mm	3.32" 84.3 mm	2.42" 61.3 mm	3.66" 92.9 mm	2.48" 63.0 mm	1-5/16-12 UN	1-5/16-12 UN	1.62" 41.3 mm	1.50" 38.1 mm

 WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

PS Series


90°

PS Series Male SAE O-Ring Straight Thread - Female NPSM Pipe Swivel



Part Number Steel	A	B	C	D	Diameter	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
PS690507-6-6	2.87" 72.8 mm	2.36" 59.8 mm	1.51" 38.4 mm	2.16" 54.8 mm	1.29" 32.8 mm	9/16-18 UNF	3/8-18 NPSM	0.88" 22.2 mm	0.88" 22.2 mm
PS890507-8-8	3.19" 80.9 mm	2.60" 65.9 mm	1.86" 47.2 mm	2.72" 69.2 mm	1.73" 44.0 mm	3/4-16 UNF	1/2-14 NPSM	1.12" 28.6 mm	1.00" 25.4 mm
PS1290507-12-12	3.58" 90.9 mm	2.92" 74.0 mm	2.24" 56.9 mm	3.33" 84.5 mm	2.17" 55.2 mm	1-1/16-12 UN	3/4-14 NPSM	1.38" 35.0 mm	1.25" 31.8 mm
PS1690507-16-16	4.18" 106.3 mm	3.32" 84.3 mm	2.48" 63.1 mm	3.73" 94.6 mm	2.48" 63.0 mm	1-5/16-12 UN	1-11 1/2 NPSM	1.62" 41.3 mm	1.50" 38.1 mm

PS Series Male SAE O-Ring Straight Thread - Female SAE Straight Thread



Part Number Steel	A	B	Diameter	Port 1	Port 2	Wrench Flats
PS690510-6-6	2.87" 72.8 mm	2.36" 59.8 mm	1.29" 32.8 mm	9/16-18 UNF	9/16-18 UNF	0.88" 22.2 mm
PS890510-8-8	3.19" 80.9 mm	2.60" 65.9 mm	1.73" 44.0 mm	3/4-16 UNF	3/4-16 UNF	1.12" 28.6 mm
PS1290510-12-12	3.58" 90.9 mm	2.92" 74.0 mm	2.17" 55.2 mm	1-1/16-12 UN	1-1/16-12 UN	1.38" 35.0 mm
PS1690510-16-16	4.18" 106.3 mm	3.32" 84.3 mm	2.48" 63.0 mm	1-5/16-12 UN	1-5/16-12 UN	1.62" 41.3 mm

**WARNING**

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

S Series

Introduction

The S Series Swivel product line complements the Quick Coupling Division's PS Series swivel line by offering a pressure balanced, compact forged body design. As a result of the pressure balanced design, the S Series Swivel does not experience a significant increase in torque as pressure rises. The housing body is forged to provide superior performance and durability in tough applications. This product is great for eliminating hose twist, torque and stress caused by the movement of the hydraulic components where side load to the swivel can be minimized.




Features:

- 3000 psi working pressure rating for all sizes
- Nitrile Seals
- Torque value does not significantly increase with pressure
- Dust seals protect the swivel from damaging environmental contaminants
- Field service kits are available for quick and reliable repairs
- 360° swivel eliminates long radius bends, hose twist and stress that can cause premature hose failure
- One piece forged housing eliminates a brazed 90° adapter connection
- Case hardened for enhanced service life
- Compact design to fit into tight areas

Performance

S Series Swivel (1/4", 3/8", 1/2", 3/4")
Test Fluid: Oil - 150 SUS vs. Pressure Drop



S Series Swivel Specifications

Body Size	1/4	3/8	1/2	3/4
Maximum Rated Pressure (psi)	3000	3000	3000	3000
Temperature Range	-40° to 250° F			
Maximum RPM	10			

S Series Repair Kits

Repair Kits come complete with primary O-Rings, PTFE back-up rings, external and internal dust seals, retaining ring and instruction sheet.

Nitrile Seals

Size	Kit Number
-4/-6	RK-4/6N
-8/-10	RK-8N
-12	RK-12N


WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

S Series

How To Order



PS Part Number

S 21 02 - 8 - 8

Housing Port Size (1/16 of an inch)

Shaft Port Size (1/16 of an inch)

Housing Port Configuration:

02 = Female NPTF
05 = Male SAE O-Ring Straight Thread
07 = Female NPSM Pipe Swivel

Shaft Port Configuration:

21 = Male NPTF
22 = Female NPTF
25 = Male SAE O-Ring Straight Thread

Parker S Series Swivel designator

WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

S Series


90°

S Series Male Pipe - Female Pipe



Part Number Steel	A	B	C	D	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
S2102-4-4	2.31" 58.7 mm	1.51" 38.4 mm	1.78" 45.1 mm	1.09" 27.6 mm	1/4-18 NPTF	1/4-18 NPTF	0.88" 22.2 mm	0.88" 22.2 mm
S2102-6-6	2.31" 58.7 mm	1.51" 38.4 mm	1.78" 45.1 mm	1.09" 27.6 mm	3/8-18 NPTF	3/8-18 NPTF	0.88" 22.2 mm	0.88" 22.2 mm
S2102-8-8	2.74" 69.6 mm	1.84" 46.8 mm	2.10" 53.3 mm	1.35" 34.3 mm	1/2-14 NPTF	1/2-14 NPTF	1.06" 27.0 mm	1.00" 25.4 mm
S2102-12-12	3.35" 85.1 mm	2.12" 53.9 mm	2.39" 60.7 mm	1.50" 38.0 mm	3/4-14 NPTF	3/4-14 NPTF	1.38" 34.9 mm	1.38" 34.9 mm

S Series Male Pipe - Female NPSM Pipe Swivel



Part Number Steel	A	B	C	D	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
S2107-4-4	2.31" 58.7 mm	1.51" 38.4 mm	2.05" 52.0 mm	1.36" 34.5 mm	1/4-18 NPTF	1/4-18 NPSM	0.88" 22.2 mm	0.69" 17.5 mm
S2107-6-6	2.31" 58.7 mm	1.51" 38.4 mm	2.07" 52.5 mm	1.38" 35.1 mm	3/8-18 NPTF	3/8-18 NPSM	0.88" 22.2 mm	0.88" 22.2 mm
S2107-8-8	2.74" 69.6 mm	1.84" 46.8 mm	2.32" 59.0 mm	1.57" 39.9 mm	1/2-14 NPTF	1/2-14 NPSM	1.06" 27.0 mm	1.00" 25.4 mm
S2107-12-12	3.35" 85.1 mm	2.12" 53.9 mm	2.74" 69.5 mm	1.85" 46.9 mm	3/4-14 NPTF	3/4-14 NPSM	1.38" 34.9 mm	1.25" 31.8 mm

WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

S Series


90°

S Series Female Pipe - Female Pipe



Part Number Steel	A	B	C	D	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
S2202-4-4	2.19" 55.6 mm	1.39" 35.4 mm	1.78" 45.1 mm	1.09" 27.6 mm	1/4-18 NPTF	1/4-18 NPTF	0.88" 22.2 mm	0.88" 22.2 mm
S2202-6-6	2.19" 55.6 mm	1.39" 35.4 mm	1.78" 45.1 mm	1.09" 27.6 mm	3/8-18 NPTF	3/8-18 NPTF	0.88" 22.2 mm	0.88" 22.2 mm
S2202-8-8	2.47" 62.7 mm	1.57" 40.0 mm	2.10" 53.3 mm	1.35" 34.3 mm	1/2-14 NPTF	1/2-14 NPTF	1.06" 27.0 mm	1.00" 25.4 mm
S2202-12-12	3.15" 80.0 mm	1.92" 48.8 mm	2.39" 60.7 mm	1.50" 38.0 mm	3/4-14 NPTF	3/4-14 NPTF	1.38" 34.9 mm	1.38" 34.9 mm

S Series Female Pipe - Female NPSM Pipe Swivel



Part Number Steel	A	B	C	D	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
S2207-4-4	2.19" 55.6 mm	1.39" 35.4 mm	2.05" 52.0 mm	1.36" 34.5 mm	1/4-18 NPTF	1/4-18 NPSM	0.88" 22.2 mm	0.69" 17.5 mm
S2207-6-6	2.19" 55.6 mm	1.39" 35.4 mm	2.07" 52.5 mm	1.38" 35.1 mm	3/8-18 NPTF	3/8-18 NPSM	0.88" 22.2 mm	0.88" 22.2 mm
S2207-8-8	2.47" 62.7 mm	1.57" 40.0 mm	2.32" 59.0 mm	1.57" 39.9 mm	1/2-14 NPTF	1/2-14 NPSM	1.06" 27.0 mm	1.00" 25.4 mm
S2207-12-12	3.15" 80.0 mm	1.92" 48.8 mm	2.74" 69.5 mm	1.85" 46.9 mm	3/4-14 NPTF	3/4-14 NPSM	1.38" 34.9 mm	1.25" 31.8 mm

 WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Swivels

S Series


90°

S Series Male SAE O-Ring Straight Thread - Female Pipe



Part Number Steel	A	B	C	D	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
S2502-6-6	2.13" 54.1 mm	1.33" 33.8 mm	1.78" 45.1 mm	1.09" 27.6 mm	9/16-18 UNF	3/8-18 NPTF	0.88" 22.2 mm	0.88" 22.2 mm
S2502-8-8	2.40" 61.0 mm	1.50" 38.2 mm	2.10" 53.3 mm	1.35" 34.3 mm	3/4-16 UNF	1/2-14 NPTF	1.06" 27.0 mm	1.00" 25.4 mm
S2502-12-12	3.40" 86.4 mm	2.17" 55.2 mm	2.39" 60.7 mm	1.50" 38.0 mm	1-1/16-12 UN	3/4-14 NPTF	1.38" 34.9 mm	1.38" 34.9 mm

S Series Male SAE O-Ring Straight Thread - Female NPSM Pipe Swivel



Part Number Steel	A	B	C	D	Port 1	Port 2	Wrench Flats 1	Wrench Flats 2
S2507-6-6	2.13" 54.1 mm	1.33" 33.8 mm	2.07" 52.5 mm	1.38" 35.1 mm	9/16-18 UNF	3/8-18 NPSM	0.88" 22.2 mm	0.88" 22.2 mm
S2507-8-8	2.40" 61.0 mm	1.50" 38.2 mm	2.32" 59.0 mm	1.57" 39.9 mm	3/4-16 UNF	1/2-14 NPSM	1.06" 27.0 mm	1.00" 25.4 mm
S2507-12-12	3.75" 95.3 mm	2.17" 55.2 mm	2.74" 69.5 mm	1.85" 46.9 mm	1-1/16-12 UN	3/4-14 NPSM	1.38" 34.9 mm	1.25" 31.8 mm

 WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Valves

Table of Contents

Introduction	D-1
---------------------------	------------

Check Valves

Selection Guide & General

Technical Information	D-2
-----------------------------	-----

DT Series	D-3
-----------------	-----

Ordering Information.....	D-7
---------------------------	-----

CV Series	D-8
-----------------	-----

Ordering Information.....	D-10
---------------------------	------

DC Series	D-11
-----------------	------

Ordering Information.....	D-13
---------------------------	------

CPIFF Series (soft seat).....	D-14
-------------------------------	------

S6C Series (soft seat)	D-16, D-17
------------------------------	------------

3C Series (soft seat)	D-16, D-17
-----------------------------	------------

2600 Series (swing type)	D-18
--------------------------------	------

Pressure/Vacuum Relief Valves

H1 & HM1 Series	D-19
-----------------------	------

Ordering Information	D-19
----------------------------	------

PV Series.....	D-20
----------------	------

Ordering Information	D-20
----------------------------	------

Thermal Bypass Valves

TH Series	D-21
-----------------	------

Ordering Information	D-22
----------------------------	------

VALVES

Multiple Hydraulic System Applications

Parker Check Valves are unidirectional flow control devices used primarily in hydraulic systems to eliminate potential damage caused by fluid back pressure. Offered in many configurations, Parker can satisfy most hydraulic system applications. Parker's in-line style check valves are available in a variety of sizes, pressure ratings, flow capacities and crack pressures.

H1, HM1 and PV Series Pressure / Vacuum Relief Valves are used to create and maintain a positive pressure in hydraulic tanks and reservoirs. These pressurized reservoir valves provide the following benefits

- Prevents pump cavitation by assuring a positive supply of oil at the pump inlet
- Minimizes the tank breathing of outside, moist, contaminated air
- Filters all incoming air

General Ordering Information

When ordering Parker coupler bodies and nipples, please state the part number of each type of coupler body and each type of nipple desired. List coupler bodies and nipples as separate items rather than in combinations. Be sure to double check thread or hose sizes of items required.

Many of Parker's coupling products are available with unique non-standard options well suited to very specific applications. Examples of unusual end use applications might include: high temperatures (above 250° F), extremely caustic/corrosive solutions passing through the coupling, external/environmental corrosion situations, or other high wear and tear situations such as dragging the product along the ground. It is always recommended that the Quick Coupling Division be contacted with any questions concerning specific product application needs.

Check Valves

Technical Information

Parker's Check Valves have several unique features that insure years of trouble-free operation.



Crack Pressure

Crack pressure refers to the amount of fluid pressure in the free flow direction required to move the poppet off the seat. The normal crack pressure setting is 5 PSI; however, other crack pressures are available to allow the check valve to perform special circuit functions, or operate under unique conditions.




Check valves are not field repairable or adjustable. Crack pressure settings are made at the factory only.

Applications


Typical hydraulic circuit, the check valve is used to protect the pump by preventing pressure from returning to the outlet port of the pump.

Selection Guide

Series	Body Size	Material	Type	Rated Pressure (psi)	Crack Pressure Range (psi)
CV Series	1/4 - 1"	Steel	Metal to Metal Seal	3000	5-130
DT Series	1/4 - 1 1/4"	Steel	Metal to Metal Seal	2500-5000	5-200
DC Series	1/4 - 2"	Steel	Metal to Metal Seal	3000	5-100
CPIFF Series	1/4 - 1"	Steel	Soft Seat	5000	5-65
3C Series	1 1/4 - 2"	Steel	Soft Seat	3000	5-65
S6C Series	1/4 - 1"	316 Stainless Steel	Soft Seat	6000	5-65



The graphic symbol for a check-valve is:



Oil cooler bypass circuit. If return line pressure becomes excessive due to resistance through oil cooler (such as startup in cold weather). Check valve opens and allows oil to bypass the cooler and flow to the tank.

Check Valves

DT Series Metal Seal

Parker DT Series Check Valves Offer the features of a Compact Body Size, and up to 5000 PSI Maximum Operating Pressure

The DT Series check valves utilize the dependable, internal design features found in Parker check valves, but with the added benefit and convenience of compact design. Sizes are available from 1/4" to 1-1/4" with six different Fitting Styles. The DT Series expands Parker's high quality product line of versatile and efficient check valve




Features:

- Compact Design - Easy to plumb into tight circuits
- All steel construction - No internal gaskets or seals to wear out
- One-piece body eliminates threads and seals that may be potential leakage points
- Smooth flow stream - Poppet spring is isolated from flow stream
- Variety of end fittings
- Optional crack pressures available from 1 to 200 PSI
- Chromium-6 Free plated exterior finish
- Nitrile O-Ring included on MO and MS fittings
- Captive O-Ring Groove is standard on MS end fittings


Specifications

The DT Series check valves have a Maximum Operating Pressure of 2500-5000 PSI. Standard crack pressures are 1, 5, and 65 PSI depending on the port size and configuration. Other crack pressures up to 200 PSI in 5 PSI increments are available upon request.




DT-MFMF

Male Flare 37° JIC Inlet to Male Flare 37° JIC Outlet




DT-MFMO

Male Flare 37° JIC Inlet to Male O-Ring Boss Outlet




DT-MOMF

Male O-Ring Boss Inlet to Male Flare 37° JIC Outlet




DT-MOMS

Male O-Ring Boss Inlet to Male Seal-Lok® Outlet



DT-MSMO

Male Seal-Lok® Inlet to Male O-Ring Boss Outlet




DT-MSMS

Male Seal-Lok® Inlet to Male Seal-Lok® Outlet

Check Valves


DT Series Metal Seal

DT-MFMF Male Flare 37° JIC Inlet to Male Flare 37° JIC Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)				Outlet Port Thread	Wrench Flats	** Std Crack Pressure (psi)
		A	B	C	D	E	F		
3/8	DT-370-MFMF-**	9/16-18 UNF	0.56	0.44	0.56	9/16-18 UNF	0.75	1, 5, 65	
1/2	DT-500-MFMF-**	3/4-16 UNF	0.66	0.50	0.66	3/4-16 UNF	0.88	5, 65	
5/8	DT-620-MFMF-**	7/8-14 UNF	0.76	0.50	0.76	7/8-14 UNF	1.06	5	
3/4	DT-750-MFMF-**	1-1/16 - 12 UN	0.86	0.50	0.86	1-1/16-12 UN	1.25	1, 5, 65	
1	DT-1000-MFMF-**	1-5/16 - 12 UN	0.91	0.62	0.91	1-5/16-12 UN	1.50	5, 65	
1-1/4	DT-1250-MFMF-**	1-5/8 - 12 UN	0.96	1.06	0.96	1-5/8-12 UN	1.88	1, 5	

DT-MFMO Male Flare 37° JIC Inlet to Male O-Ring Boss Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)				Outlet Port Thread	Wrench Flats	** Std Crack Pressure (psi)
		A	B	C	D	E	F		
3/8	DT-370-MFMO- **	9/16-18 UNF	0.56	0.44	0.47	9/16-18 UNF	0.75	1, 5, 65	
1/2	DT-500-MFMO- **	3/4-16 UNF	0.66	0.50	0.55	3/4-16 UNF	0.88	5, 65	
5/8	DT-620-MFMO- **	7/8-14 UNF	0.76	0.50	0.63	7/8-14 UNF	1.06	5	
3/4	DT-750-MFMO- **	1-1/16 - 12 UN	0.86	0.50	0.73	1-1/16-12 UN	1.25	1, 5, 65	
1	DT-1000-MFMO- **	1-5/16 - 12 UN	0.91	0.62	0.73	1-5/16-12 UN	1.50	5, 65	
1-1/4	DT-1250-MFMO- **	1-5/8 - 12 UN	0.96	1.06	0.73	1-5/8-12 UN	1.88	1, 5	


WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves


DT Series Metal Seal

DT-MOMF Male O-Ring Boss Inlet to Male Flare 37° JIC Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)				Outlet Port Thread	Wrench Flats	** Std Crack Pressure (psi)
		A	B	C	D	E	F		
1/4	DT-250-MOMF- **	7/16-20 UNF	0.43	0.44	0.55	7/16-20 UNF	0.62	5	
3/8	DT-370-MOMF- **	9/16-18 UNF	0.47	0.44	0.56	9/16-18 UNF	0.75	1, 5, 65	
1/2	DT-500-MOMF- **	3/4-16 UNF	0.55	0.50	0.66	3/4-16 UNF	0.88	5, 65	
5/8	DT-620-MOMF- **	7/8-14 UNF	0.63	0.50	0.76	7/8-14 UNF	1.06	5	
3/4	DT-750-MOMF- **	1-1/16 - 12 UN	0.73	0.50	0.86	1-1/16 - 12 UN	1.25	1, 5, 65	
1	DT-1000-MOMF- **	1-5/16 - 12 UN	0.73	0.62	0.91	1-5/16 - 12 UN	1.50	5, 65	
1-1/4	DT-1250-MOMF- **	1-5/8 - 12 UN	0.73	1.06	0.96	1-5/8 - 12 UN	1.88	1, 5	

DT-MOMS Male O-Ring Boss Inlet to Male Seal-Lok® Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)			Outlet Port Thread	Wrench Flats	** Std Crack Pressure (psi)
		A	B	C	D	E	F	
1/4	DT-250-MOMS- **	7/16-20 UNF	0.43	0.45	0.39	7/16-20 UNF	0.62	5
3/8	DT-370-MOMS- **	9/16-18 UNF	0.47	0.44	0.44	9/16-18 UNF	0.75	1, 5, 65
1/2	DT-500-MOMS- **	3/4-16 UNF	0.55	0.50	0.51	3/4-16 UNF	0.88	5, 65
5/8	DT-620-MOMS- **	7/8-14 UNF	0.63	0.50	0.62	7/8-14 UNF	1.06	5
3/4	DT-750-MOMS- **	1-1/16 - 12 UN	0.73	0.50	0.68	1-1/16 - 12 UN	1.25	1, 5, 65
1	DT-1000-MOMS- **	1-5/16 - 12 UN	0.73	0.62	0.70	1-5/16 - 12 UN	1.50	5, 65
1-1/4	DT-1250-MOMS- **	1-5/8 - 12 UN	0.73	1.06	0.70	1-5/8 - 12 UN	1.88	1, 5




WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves


DT Series Metal Seal

DT-MSMO Male Seal-Lok® Inlet to Male O-Ring Boss Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)				Outlet Port Thread	Wrench Flats	** Std Crack Pressure (psi)
		A	B	C	D	E	F		
3/8	DT-370-MSMO- ^{**}	11/16-16 UN	0.44	0.44	0.47	9/16-18 UNF	0.75	1, 5, 65	
1/2	DT-500-MSMO- ^{**}	13/16-16 UN	0.51	0.50	0.55	3/4-16 UNF	0.88	5, 65	
5/8	DT-620-MSMO- ^{**}	1-14 UNS	0.62	0.49	0.63	7/8-14 UNF	1.06	5	
3/4	DT-750-MSMO- ^{**}	1-3/16 - 12 UN	0.68	0.50	0.73	1-1/16-12 UN	1.25	1, 5, 65	
1	DT-1000-MSMO- ^{**}	1-7/16 - 12 UN	0.70	0.62	0.73	1-5/16-12 UN	1.50	5, 65	
1-1/4	DT-1250-MSMO- ^{**}	1-11/16 - 12 UN	0.70	1.06	0.73	1-5/8-12 UN	1.88	1, 5	

DT-MSMS Male Seal-Lok® Inlet to Male Seal-Lok® Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)				Outlet Port Thread	Wrench Flats	** Std Crack Pressure (psi)
		A	B	C	D	E	F		
3/8	DT-370-MSMS- **	11/16-16 UN	0.44	0.44	0.44	11/16-16 UN	0.75	1, 5, 65	
1/2	DT-500-MSMS- **	13/16-16 UN	0.51	0.50	0.51	13/16-16 UN	0.88	5, 65	
5/8	DT-620-MSMS- **	1-14 UNS	0.62	0.50	0.62	1-14 UNS	1.06	5	
3/4	DT-750-MSMS- **	1-3/16 - 12 UN	0.68	0.50	0.68	1-3/16 - 12 UN	1.25	1, 5, 65	
1	DT-1000-MSMS- **	1-7/16 - 12 UN	0.70	0.62	0.70	1-7/16 - 12 UN	1.50	5, 65	
1-1/4	DT-1250-MSMS- **	1-11/16 - 12 UN	0.70	1.06	0.70	1-11/16 - 12 UN	1.88	1, 5	




WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves

DT Series Metal Seal

Flow Data



Ordering Information

DT - * - **** - ****

CRACK PRESSURE

1 = 1 PSI

5 = 5 PSI

65 = 65 PSI

Other Crack Pressures up to 200 PSI in 5 PSI increments are available. Contact the Division for price and delivery on non-standard crack pressures

SERIES	SIZE	FITTING STYLE
250	1/4"	MFMF - Male Flare Inlet to Male Flare Outlet
370	3/8"	MFMO - Male Flare Inlet to Male O-Ring Boss Outlet
500	1/2"	MOMF - Male O-Ring Boss Inlet to Male Flare Outlet
620	5/8"	MOMS - Male O-Ring Boss Inlet to Male Face Seal Outlet
750	3/4"	MSMO - Male Face Seal Inlet to Male O-Ring Boss Outlet
1000	1"	MSMS - Male Face Seal Inlet to Male Face Seal Outlet
1250	1-1/4"	

DT Series Specification

Body Size	1/4 - 1 1/4
Rated Pressure (psi)	2500-5000
Material	-40° to +250° F
Crack Pressure Range (psi)	5-200

DT Series Pressure Table (psi)

Body Size	Max Rated Pressure	MF (Male JIC 37)	MO (SAE O-Ring Boss)	MS (Male Seal-Lok)
1/4	5000	5000	5000	5000
3/8	5000	5000	5000	5000
1/2	5000	4500	5000	5000
5/8	5000	3500	5000	5000
3/4	5000	3500	5000	5000
1	5000	3000	5000	5000
1 1/4	4000	2500	4000	4000

DT Series Installation Assembly Torque (ft-lbs)


Body Size	MF (Male JIC 37)	MO (SAE O-Ring Boss)	MS (Male Seal-Lok)
1/4	Refer to Parker TFD Catalog 4300 for torque recommendation	13.3 +10% / -0%	Refer to Parker TFD Catalog 4300 for torque recommendation
3/8		22.1 +10% / -0%	
1/2		62.6 +10% / -0%	
5/8		84.8 +10% / -0%	
3/4		125.3 +10% / -0%	
1		199 +10% / -0%	
1 1/4		210 +10% / -0%	

Check Valves

CV Series Metal Seal


CV Series Check Valves Offer Low Pressure Drop and High Flow

Parker's CV Series check valves are a rugged built and versatile product designed to protect hydraulic systems from fluid back pressure. The CV Series compliments the DT Series by adding the feature of modular design. The larger body results in less pressure drop and increased performance. The CV Series are in-line unidirectional valves, available in sizes 1/4" to 1", with a pressure rating of up to 3000 PSI, and flow capacities to 100 GPM. Standard spring crack pressures are 5 and 65 PSI. Other crack pressures available upon request.




Features:

- Nitrile O-ring is standard in the body assembly - Note port O-rings are included on the MO and MS ports
- All-steel construction
- Valve seats resist damage from shocks, surges and contamination
- Poppet has an oil retention groove that lubricates the bore and eliminates galling
- Poppet spring is isolated from the liquid flow stream, minimizing turbulence
- Poppet is heat treated to help prevent damage from shocks, surges and galling
- Close tolerance fit between poppet and poppet retainer creates a cushion that protects valve from surge shock damage
- Optional crack pressures available upon request



CV-MFMF

Male Flare 37° JIC Inlet to Male Flare 37° JIC Outlet



CV-MOMS


Male O-Ring Boss Inlet to Male Seal-Lok® Outlet

NOTE: Contact QCD for additional port end options.

Check Valves


CV Series Metal Seal

CV-MFMF Male Flare 37° JIC Inlet to Male Flare 37° JIC Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)		Outlet Port Thread	** Std Crack Pressure (psi)	Max Operating Pressure (psi)
			Length	Wrench Flats			
			A	B			
1/4	CV-250-MFMF-**	7/16-20 UNF	1.53	0.68	7/16-20 UNF	5, 65	3000
3/8	CV-370-MFMF-**	9/16-18 UNF	1.75	0.81	9/16-18 UNF	5, 65	3000
1/2	CV-500-MFMF-**	3/4-16 UNF	2.22	1.00	3/4-16 UNF	5, 65	3000
5/8	CV-620-MFMF-**	7/8-14 UNF	2.41	1.12	7/8-14 UNF	5, 65	3000
3/4	CV-750-MFMF-**	1-1/16 - 12 UN	2.75	1.38	1-1/16 - 12 UN	5, 65	3000
1	CV-1000-MFMF-**	1-5/16 - 12 UN	3.31	1.62	1-5/16 - 12 UN	5, 65	3000

CV-MFMF Male Flare 37° JIC Inlet to Male Flare 37° JIC Outlet



Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)		Outlet Port Thread	** Std Crack Pressure (psi)	Max Operating Pressure (psi)
			Length	Wrench Flats			
			A	B			
1/4	CV-250-MOMS-**	7/16-20 UNF	1.53	0.68	9/16-18 UNF	5, 65	3000
3/8	CV-370-MOMS-**	9/16-18 UNF	1.75	0.81	11/16-16 UN	5, 65	3000
1/2	CV-500-MOMS-**	3/4-16 UNF	2.22	1.00	13/16-16 UN	5, 65	3000
5/8	CV-620-MOMS-**	7/8-14 UNF	2.41	1.12	1-14 UNS	5, 65	3000
3/4	CV-750-MOMS-**	1-1/16 - 12 UN	2.75	1.38	1-3/16-12 UN	5, 65	3000
1	CV-1000-MOMS-**	1-5/16 - 12 UN	3.31	1.62	1-7/16-12 UN	5, 65	3000



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves

CV Series Metal Seal

Flow Data



Ordering Information

CV - * - *** - ****

CRACK PRESSURE

5 - 5 PSI

65 - 65 PSI

Other Crack Pressures up to 200 PSI in 5 PSI increments are available. Contact the Division for price and delivery on non-standard crack pressures

SERIES	SIZE	FITTING STYLE
250	1/4"	MFMF - Male Flare Inlet to Male Flare Outlet
370	3/8"	MOMS - Male O-Ring Boss Inlet to Male Seal-Lok® Outlet
500	1/2"	
620	5/8"	
750	3/4"	
1000	1"	


NOTE: Contact QCD for additional port end options.

Check Valves

DC Series Metal Seal

DC Series Check Valves are Rugged, Cost-competitive

The DC Series offers basic, workhorse check valves – ruggedly built, readily available and reasonably priced. They are in-line valves, available in sizes 1/4" to 2", with a pressure rating range up to 3000 psi, and flow capacities to 300 PM.



Features:

- All-steel construction—no internal seals or gaskets to wear out
- One-piece body eliminates threads and seals that may be potential failure or leakage points
- Valve seats resist damage from shocks, surges and contamination
- Poppet has an oil retention groove that lubricates the bore and eliminates galling
- Poppet spring is isolated from the liquid flow stream, minimizing turbulence
- Poppet is heat treated to help prevent damage from shocks, surges and galling
- Close tolerance fit between poppet and poppet retainer creates a cushion that protects valve from surge shock damage
- Check valve body is shaped like an arrow to indicate flow direction
- Available in a variety of standard and non-standard crack pressures

Check Valves

DC Series
Metal Seal

DC Series Part Numbers

Valve Size	Part Number Steel	Inlet Port Thread	Dimensions (in.)		Outlet Port Thread	** Std Crack Pressure (psi)	Max Operating Pressure (psi)
			Length	Wrench Flats			
1/4	DC-250-**	1/4 - 18 NPSF	2.44	0.81	1/4 - 18 NPSF	1, 5, 65	3000
1/4	DC-250-FOFO-**	.438 - 20 UNF	2.44	0.81	.438 - 20 UNF	1, 5	3000
3/8	DC-370-**	3/8 - 18 NPSF	2.75	0.88	3/8 - 18 NPSF	1, 5, 65	3000
3/8	DC-370-FOFO-**	.562 - 18 UNF	2.75	0.88	.562 - 18 UNF	5	3000
1/2	DC-500-**	1/2 - 14 NPSF	3.50	1.06	1/2 - 14 NPSF	1, 5, 65	3000
1/2	DC-500-FOFO-**	.750 - 16 UNF	3.50	1.06	.750 - 16 UNF	5, 65	3000
3/4	DC-750-**	3/4 - 14 NPSF	3.88	1.37	3/4 - 14 NPSF	1, 5, 65	3000
3/4	DC-750-FOFO-**	1.062 - 12 UN	3.88	1.37	1.062 - 12 UN	5, 65	3000
1	DC-1000-**	1 - 11.5 NPSF	4.88	1.62	1 - 11.5 NPSF	5, 65	3000
1	DC-1000-FOFO-**	1.312 - 12 UN	4.88	1.62	1.312 - 12 UN	5, 65	3000
1-1/4	DC-1250-**	1-1/4 - 11.5 NPTF	5.94	2.00	1-1/4 - 11.5 NPTF	5, 65	3000
1-1/4	DC-1250-FOFO-**	1.625 - 12 UN	5.94	2.00	1.625 - 12 UN	5, 65	3000
1-1/2	DC-1500-**	1-1/2 - 11.5 NPTF	6.37	2.38	1-1/2 - 11.5 NPTF	5, 65	3000
1-1/2	DC-1500-FOFO-**	1.875 - 12 UN	6.37	2.38	1.875 - 12 UN	5, 65	3000
2	DC-2000-**	2 - 11.5 NPTF	7.00	3.00	2 - 11.5 NPTF	5, 65	3000
2	DC-2000-FOFO-**	2.500 - 12 UN	7.00	3.00	2.500 - 12 UN	65	3000

 WARNING


This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves


DC Series Metal Seal

Flow Data


DC Series (1/4")
Test Fluid: Oil - 200 SUS



DC Series (3/8", 1/2" & 3/4")
Test Fluid: Oil - 200 SUS



DC Series (1", 1-1/4", 1-1/2" & 2")
Test Fluid: Oil - 200 SUS



Ordering Information

DC - * - *** - ****

Crack Pressure:

1 = 1 PSI

5 = 5 PSI

65 = 65 PSI

Other crack pressures up to 100 PSI (in 5 PSI increments) are available. Contact the Division for price and delivery on non-standard crack pressures.

Fitting Style:

Blank = Female pipe inlet to Female pipe outlet

FOFO = Female O-ring Boss inlet to Female O-ring Boss outlet

Size

250 = 1/4"

370 = 3/8"

500 = 1/2"

750 = 3/4"

1000 = 1"

1250 = 1-1/4"

1500 = 1-1/2"

2000 = 2"

Series

Check Valves

CPIFF Series Soft Seat

CPIFF Series Soft Seat Check Valves Provide a Positive Shut-off to Prevent Reverse Flow


CPIFF Series check valves are designed to protect hydraulic systems from fluid back pressure. The poppet is streamlined with minimum restriction of flow in one direction. Flow is blocked in the reverse direction as the soft seat creates a leak free seal in the closed position.

These in-line unidirectional valves are available in sizes 1/4" to 1" with a pressure rating up to 5000 psi. Standard spring crack pressures are shown in the part number table. Other crack pressures available upon request.



Features:

- Fluorocarbon poppet seal is standard
- Steel construction
- Optional crack pressures available on request



CPIFF Series Specification

Size (in)	Max Pressure (psi)	MF (Male JIC 37)
1/4	5000	3
3/8	5000	8
1/2	5000	12
3/4	5000	20
1	5000	30

Seal Options (add code to part number)

Code	Poppet Seal Material
suffi A	Nitrile
suffi B	Ethylene Propylene

Check Valves

CPIFF Series Soft Seat

CPIFF Series Part Numbers



Valve Size	Part Number Steel	Inlet and Outlet Port Threads (Female)	Dimensions (in.)		Standard Seal Material	** Std Crack Pressure (psi)	Max Operating Pressure (psi)
			Length	Wrench Flats			
			A	B			
1/4	CPIFF-2P-**	1/4 - 18 NPSF	1.97	3/4	Fluorocarbon	5, 15, 25, 65	5000
3/8	CPIFF-3P-**	3/8 - 18 NPSF	2.60	1	Fluorocarbon	5, 15, 25, 65	5000
1/2	CPIFF-4P-**	1/2 - 14 NPSF	3.25	1-1/4	Fluorocarbon	5, 15, 25, 65	5000
1/2	CPIFF-8S-**	3/4 - 16 UNF	3.25	1-1/4	Fluorocarbon	5, 15, 25, 65	5000
3/4	CPIFF-6P-**	3/4 - 14 NPSF	4.33	1-3/8	Fluorocarbon	5, 15, 25, 65	5000
3/4	CPIFF-12S-**	1-1/16 - 12 UN	4.33	1-3/8	Fluorocarbon	5, 15, 25, 65	5000
1	CPIFF-8P-**	1 - 11-1/2 NPSF	4.78	1-3/4	Fluorocarbon	5, 15, 25, 65	5000
1	CPIFF-16S-**	1-5/16 - 12 UN	4.78	1-3/4	Fluorocarbon	5, 15, 25, 65	5000

WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves

C Series Soft Seat

S6C and 3C Soft Seat Check Valves span a wide variety of sizes and end configurations

S6C and 3C check valves have a variety of options enabling them to meet the needs of most systems. The soft seated poppet creates a leak free seal to protect hydraulic systems from reverse flow.



S6C check valves are stainless steel with a rated pressure of 6000 psi (sizes 1/4", 3/8", 1/2", 3/4" & 1"). 3C check valves are steel with a rated pressure of 3000 psi (sizes 1-1/4", 1-1/2" & 2").

These in-line unidirectional valves are available in sizes 1/4" to 2". Standard spring crack pressures are shown in the part number table. Other crack pressures available upon request.



Features:

- Fluorocarbon poppet seal is standard
- Steel or stainless steel construction
- Optional crack pressures available on request
- Contact QCD for other materials or configurations



C Series Specification

Size (in)	Rated Flow (gpm)
1/4	3
3/8	8
1/2	12
3/4	20
1	30
1-1/4	90
1-1/2	125
2	175

Seal Options (add code to part number)

Code	Poppet Seal Material
suffi A	Nitrile
suffi B	Ethylene Propylene

Check Valves

C Series Soft Seat

S6C Series Part Numbers



Body Size	Part Number Steel*	Part Number Stainless Steel*	Inlet Port Threads	Dimensions (in.)		Outlet Port Threads	Std Crack Pressure** (psi)	Max Operating Pressure Steel (psi)	Max Operating Pressure Stainless Steel (psi)
				Length	Wrench Flats				
1/4	6C4F-F**	S6C4F-F**	1/4 - 18 NPTF (female)	2.82	3/4	1/4 - 18 NPTF (female)	5, 25, 65	6000	6000
1/4	6C4F-M**	S6C4F-M**	1/4 - 18 NPTF (female)	2.65	3/4	1/4 - 18 NPT (male)	5, 25, 65	6000	6000
1/4	6C4M-M**	S6C4M-M**	1/4 - 18 NPT (male)	2.70	3/4	1/4 - 18 NPT (male)	5, 25, 65	6000	6000
3/8	6C6F-F**	S6C6F-F**	3/8 - 18 NPTF (female)	3.38	1-1/8	3/8 - 18 NPTF (female)	5, 25, 65	6000	6000
3/8	6C6F-M**	S6C6F-M**	3/8 - 18 NPTF (female)	3.18	1-1/8	3/8 - 18 NPT (male)	5, 25, 65	6000	6000
1/2	6C8F-F**	S6C8F-F**	1/2 - 14 NPTF (female)	3.73	1-1/4	1/2 - 14 NPTF (female)	5, 25, 65	6000	6000
1/2	6C8M-F**	S6C8M-F**	1/2 - 14 NPT (male)	4.20	1-1/4	1/2 - 14 NPTF (female)	5, 25, 65	6000	6000
1/2	6C8M-M**	S6C8M-M**	1/2 - 14 NPT (male)	4.04	1-1/4	1/2 - 14 NPT (male)	5, 25, 65	6000	6000
3/4	6C12F-F**	S6C12F-F**	3/4 - 14 NPTF (female)	4.91	1-5/8	3/4 - 14 NPTF (female)	5, 25, 65	6000	5000
1	6C16F-F**	S6C16F-F**	1 - 11-1/2 NPTF (female)	6.06	1-7/8	1 - 11-1/2 NPTF (female)	5, 25, 65	6000	4000

* Prop 65 Warning does not apply to stainless steel part numbers

3C Series Part Numbers



Body Size	Part Number Steel*	Part Number Stainless Steel*	Inlet Port Threads	Dimensions (in.)		Outlet Port Threads	Std Crack Pressure** (psi)	Max Operating Pressure Steel (psi)	Max Operating Pressure Stainless Steel (psi)
				Length	Wrench Flats				
1-1/4	3C20F-F**	S3C20F-F**	1-1/4 - 11-1/2 NPTF	5.76	2	1/4 - 18 NPTF (female)	5, 15, 25, 65	3000	3000
1-1/4	3C20EF-EF**	S3C20EF-EF**	1-5/8 - 12 UN	5.76	2	1/4 - 18 NPT (male)	5, 15, 25, 65	3000	3000
1-1/4	3C20EM-EM**	S3C20EM-EM**	1-5/8 - 12 UN (male 37° flare)	6.57	2	1/4 - 18 NPT (male)	5, 15, 25, 65	3000	3000
1-1/2	3C24F-F**	S3C24F-F**	1-1/2 - 11-1/2 NPTF	6.50	2-1/2	3/8 - 18 NPTF (female)	5, 15, 25, 65	3000	3000
1-1/2	3C24EF-EF**	S3C24EF-EF**	1-7/8 - 12 UN	6.50	2-1/2	3/8 - 18 NPT (male)	5, 15, 25, 65	3000	3000
2	3C32EF-EF**	S3C32EF-EF**	2-1/2 - 12 UN	7.28	3-1/4	1/2 - 14 NPTF (female)	5, 25, 65	3000	3000

* Prop 65 Warning does not apply to stainless steel part numbers



WARNING

This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Check Valves

2600 Series Swing Type

Low Pressure and Lightweight

Constructed of lightweight aluminum, the 2600 Series Swing Check Valve has a spring-loaded, trapdoor style valve. The valve opens when system pressure approaches 1/2 psi to permit full flow with low pressure drop. As system pressure is relieved, the valve closes, retaining fluids upstream.

Parker's 2600 Series are in-line check valves designed especially for diesel and gasoline engine fuel lines. They are also used for externally mounted oil filters, and coolers, as well as transmission fluid lubrication lines. With a maximum of 1/2 psi cracking pressure, these Swing Check Valves are useful in most low pressure air, liquid, or gas systems.



Features:

- Lightweight, corrosion-resistant aluminum construction
- Available with 1/4" or 3/8" NPTF ports
- Standard Nitrile or Fluorocarbon seals
- 1/2 PSI maximum crack pressure
- Trapdoor style valve permits full flow with low pressure drop

2600 Series Specification

Rated Pressure	250 psi max
Crack Pressure	1/2 psi max
Weight	0.08 lbs
Temperature Range	Nitrile: -40° to 200°F (-40° C to 93° C) Fluorocarbon: -40° to 400°F (-40° C to 204° C)
Max Leakage	5 cc / 24 hours at 28" head
Rated Flow	6 gpm (based on 3/8" hose size)

2600 Series Part Numbers

Part Number	Thread	Seal Material	Dimensions	
			Length (mm)	Wrench Flats (in)
2600	1/4 - 18 NPTF	Nitrile	2.06 (52)	1-1/16
2676	1/4 - 18 NPTF	Fluorocarbon	2.06 (52)	1-1/16
2650	3/8 - 18 NPTF	Nitrile	2.12 (54)	1-1/16
2625	3/8 - 18 NPTF	Fluorocarbon	2.12 (54)	1-1/16

Pressure/Vacuum Relief Valves

H1 and HM1 Series

H1 Series Pressure/Vacuum Relief Valves are used to maintain positive pressure in hydraulic reservoirs. The compact size, reusable bronze filter and high flow characteristics make this valve a popular choice.

The HM1 Series offers the same features and characteristics as the H1 series with the option of manual over ride. This feature allows the operator to relieve the reservoir pressure before opening the tank for refilling, inspection or servicing.



Features:


- Easy to remove, cleanable bronze filter
- High flow characteristics
- Compact size
- Available with male pipe or male ORB threads
- Wide variety of pressure relief settings
- HM1 series has a manual pressure relief button

H1 and HM1 Series Specification

	H1 Series	HM1 Series
Pressure Rating	60 psi max	
Filter Rating	10 micron, nominal	
Pressure Relief Setting	5 psi through 50 psi (in 5 psi increments)	
Vacuum Relief Setting	0.3 psi	
Weight	1.0 lbs	1.1 lbs

Flow Data

H1 and HM1 Pressure-Vacuum Relief Valve



* Pressure drop is pressure relief valve crack pressure until pressure drop curve increases above pressure relief crack pressure.

Ordering Information

H * - * * - * * * *

FITTING STYLE:

MP = Male pipe thread

MO = Male O-ring Boss, SAE threads

FITTING SIZE:

6 = 3/8"

8 = 1/2"

12 = 3/4"

16 = 1"

CRACK PRESSURE (PSI):

5 to 50

(in 5 PSI increments)

SERIES:

H1

HM1 (with manual pressure relief button)

Pressure/Vacuum Relief Valves

PV Series

PV Series is an economical Pressure/Vacuum Relief Valve used to maintain positive pressure in hydraulic reservoirs. The large filter area makes this valve an ideal choice for use in heavily contaminated environments. The optional bayonet type mount allows the valve to be installed in the tank filler port, eliminating the need for an extra port. In this configuration, the valve also serves as a filler cap.




Features:

- Disposable spin-on automotive type, field replaceable filter (240 sq inches)
- Several pressure relief settings
- Economic design
- Optional bayonet style allows mounting in filler port with valve also functioning as filler cap

H1 and HM1 Series Specification

	PV Series	PV Bayonet Style
Filter Rating	10 micron, nominal (240 sq inches)	
Pressure Relief Setting	5 PSI through 30 PSI (in 5 PSI increments)	5 and 10 PSI
Vacuum Relief Setting	0.3 psi	
Weight	1.0 lb.	
Mounting	Male ORB, SAE threads Male pipe threads	Bayonet style with tank receptacle gaskets & screws (optional strainer basket)
Replacement Filter Part Number	7312-009	

Flow Data



Ordering Information

P V - * * - * * * * - * *

BAYONET OPTION ONLY:

- RO = With receptacle, gaskets and screws
- RB = With receptacle, gaskets, screws and strainer basket

FITTING / MOUNTING STYLE:

- BA = Bayonet mount
- MP = Male pipe thread
- MO = Male O-ring Boss, SAE threads

FITTING SIZE:

- Blank = Bayonet style
- 8 = 1/2"
- 12 = 3/4"

CRACK PRESSURE (PSI):

- 05 (PV, PV-Bayonet)
- 10 (PV, PV-Bayonet)
- 15 (PV)
- 20 (PV)
- 25 (PV)
- 30 (PV)

PV SERIES

Thermal Bypass Valves


TH Series

Maintain Optimum Fluid Temperature

Parker's thermal bypass valve will modulate fluid temperature by shifting return line flow through the cooler, or bypassing it directly to the reservoir.

Additionally, an integral pressure relief function automatically releases excess pressure to the reservoir if the cooler becomes restricted, and the inlet pressure becomes excessive. Relief crack pressure settings range from 5 to 85 PSI.

These lightweight, aluminum valves are ideal for hydrostatic drive circuits requiring fast warm-up, controlled fluid temperatures, and low return line back pressure.




Features:


- Lightweight, corrosion-resistant aluminum housing
- Available in five shift temperatures
- Integral relief valve to dump excessive inlet pressures to the reservoir
- 250 PSI maximum operating pressure
- Up to 60 GPM flow rates

Flow Data - Pressure Drop (Mobil DTE 26 oil)


**Inlet Port thru Tank Port
@ 100°F (300 SUS)**



**Inlet Port over Integral Relief Valve
@ 170°F (78 SUS Oil)**



**Inlet Port thru Cooler Port
@ 145°F (110 SUS Oil)**






Thermal Bypass Valves

TH Series

H1 and HM1 Series Specification

Size	1 inch
Weight	2.00 lbs
Std Shift Temperatures	100° F, 120° F, 140° F, 160° F, 180° F
Full Shift Temperature (cooler port open)	Shift Temperature plus 25° F
Proof Pressure	300 PSI (21 bar)
Minimum Burst Pressure	Up to full shift temperature: 325 PSI (22 bar) Above full shift temperature: 600 PSI (41 bar)
Operating Temperature	Min: -30° F Max: Shift temperature plus 75° F
Max Flow Rate	60 GPM (227 l/m)

Dimensions



Ordering Information

TH - 1000 - 16FO - **

VALVE SERIES:
Thermal Bypass

VALVE SIZE:
1000 = 1 inch

CRACK PRESSURE/TEMPERATURE CODE:
(see table)

PORT SIZE & STYLE:
16FO = 1 inch SAE O-Ring Boss (1.312 - 12UN-2B thread)

Crack Pressure/Temperature Code

Shift Temperature	Crack Pressure PSI																
	5 PSI	10 PSI	15 PSI	20 PSI	25 PSI	30 PSI	35 PSI	40 PSI	45 PSI	50 PSI	55 PSI	60 PSI	65 PSI	70 PSI	75 PSI	80 PSI	85 PSI
100° F (38° C)	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17
120° F (49° C)	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37
140° F (60° C)	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57
160° F (71° C)	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77
180° F (82° C)	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96	97

APPENDIX

Codes

The following seal compound and body material compatibility chart is provided as an aid in selecting a specific synthetic rubber compound or body material for a particular application. Operating and environmental conditions must be considered when making the selection of a quick coupling.

Refer to the appropriate section of the catalog for Ordering Information for Seal Codes for specific products.

To indicate a special material just add the appropriate code letter as a suffix to the catalog number of the coupler.

It is not necessary to use the code "STD" as the standard Nitrile seal will be used when another code is not used.

Note

This chart is intended as a guide only and is not be considered as a recommendation to use Parker quick action couplings in a specific application or with a specific fluid, other factors that must be considered include but are not limited to: fluid and ambient temperature, system pressure, both operating and peak, frequency of connect and disconnect, and applicable standards or regulations.

For recommendations for media not listed below, please contact your Parker representative or the factory.

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
3M FC-75	4	4	4	4	1	1	2	1
ACETAMIDE	4	4	1	2	1	1	3	1
ACETIC ACID (5%)	3	3	1	1	2	1	1	1
ACETONE	1	2	1	1	3	1	3	3
ACETOPHENONE	2	2	2	1	3	1	3	3
ACETYL ACETONE	2	2	2	2	3	1	3	3
ACETYL CHLORIDE	4	2	2	2	3	3	1	3
ACETYLENE	3	2	1	1	1	1	1	2
AIR (200 DEGREES F.)	1	2	1	1	1	1	1	1
AIR (300 DEGREES F.)	1	2	1	1	2	2	1	2
AIR (400 DEGREES F.)	2	2	1	1	3	3	1	3
ALUMINUM ACETATE	4	4	4	4	2	1	3	2
ALUMINUM BROMIDE	4	4	4	4	1	1	1	1
ALUMINUM CHLORIDE (10%)	3	3	3	3	1	1	1	1
ALUMINUM CHLORIDE (100%)	3	2	2	2	1	1	1	1
ALUMINUM FLOURIDE	3	3	3	3	1	1	1	1
ALUMINUM NITRATE	3	3	2	2	1	1	1	1
ALUMINUM SALTS	4	4	4	4	1	1	1	1
ALUMINUM SULPHATE	2	3	2	3	1	1	1	1
ALUMS (NH ₃ ,Cr,K)	4	4	4	4	1	1	3	1
AMMONIA (ANHYDROUS)	3	2	1	1	2	1	3	1
AMMONIA (COLD, GAS)	3	2	4	1	1	1	3	1
AMMONIA (HOT, GAS)	3	2	4	1	3	2	3	2
AMMONIUM CARBONATE	3	2	3	3	3	1	1	1

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
AMMONIUM CHLORIDE	3	3	2	3	1	1	1	1
AMMONIUM HYDROXIDE	3	3	1	2	3	1	3	1
AMMONIUM NITRATE	3	3	1	1	1	1	4	1
AMMONIUM PERSULFATE SOLUTION	3	3	1	2	3	1	4	4
AMMONIUM PHOSPHATE (MONO-, DI-, TRI-BASIC)	3	3	3	2	1	1	4	1
AMMONIUM SALTS	4	4	4	4	1	1	3	1
AMMONIUM SULFATE	3	3	2	3	1	1	3	1
AMYL BORATE	4	4	4	4	1	3	1	1
AMYL CHLORIDE	4	2	1	1	4	3	1	3
AMYL CHLORONAPHTHALENE	4	4	4	4	3	3	1	3
AMYL NAPHTHALENE	4	4	4	4	3	3	1	3
ANIMAL OIL (LARD OIL)	2	2	2	2	1	2	1	2
AROCLOR 1248	2	3	3	3	3	2	1	3
AROCLOR 1254	2	3	3	3	3	2	1	3
AROCLOR 1260	2	3	3	3	1	4	1	1
AROMATIC FUEL (50%)	4	4	4	4	2	3	1	3
ARSENIC ACID	3	3	1	1	1	1	1	1
ASPHALT	3	3	1	1	2	3	1	2
ASTM OIL, NO. 1	1	1	1	1	1	3	1	1
ASTM OIL, NO. 2	1	1	1	1	1	3	1	2
ASTM OIL, NO. 3	1	1	1	1	1	3	1	3
ASTM OIL, NO. 4	1	1	1	1	2	3	1	3
ASTM REFERENCE FUEL A	3	2	1	1	1	3	1	2
ASTM REFERENCE FUEL B	3	2	1	1	1	3	1	3
ASTM REFERENCE FUEL C	3	2	1	1	2	3	1	3
AUTOMOTIVE BRAKE FLUID	4	4	4	4	3	1	3	2
BARIUM CHLORIDE	3	3	2	3	1	1	1	1
BARIUM HYDROXIDE	3	2	2	3	1	1	1	1
BARIUM SALTS	4	4	4	4	1	1	1	1
BARIUM SULFIDE	3	2	3	3	1	1	1	1
BEER	3	3	1	1	1	1	1	1
BEET SUGAR LIQUORS	3	3	1	1	1	1	1	2
BENZALDEHYDE	3	3	2	3	3	1	3	3
BENZENE	3	2	3	3	3	3	1	3
BENZENESULFONIC ACID (10%)	3	3	3	3	3	3	1	2
BENZINE	4	4	4	4	1	3	1	2
BENZOIC ACID	3	3	3	3	3	3	1	3
BENZYL ALCOHOL	4	3	1	2	3	2	1	2

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
BENZYL CHLORIDE	3	3	2	3	3	3	1	3
BLEACH LIQUOR	4	4	4	4	3	1	1	2
BORAX	3	2	3	3	2	1	1	3
BORDEAUX MIXTURE	4	4	4	4	2	1	1	2
BORIC ACID	3	3	2	3	1	1	1	1
BRAKE FLUID (NON-PETROLEUM)	4	4	4	4	3	1	3	2
BRINE (SODIUM CHLORIDE)	3	3	1	1	1	1	1	1
BROMINE	4	4	4	4	3	3	1	3
BROMINE WATER	4	4	4	4	3	2	1	3
BUNKER OIL	4	4	4	4	1	3	1	3
BUTADIENE (MONOMER)	3	2	1	2	3	3	1	3
BUTANE	3	1	1	1	1	3	1	1
BUTANE (2,2, & 2,3-DIMETHYL)	4	4	4	4	1	3	1	2
BUTANOL (BUTYL ALCOHOL)	2	1	1	1	1	2	1	1
BUTTER - ANIMAL FAT	2	3	1	2	1	1	1	2
BUTYL BUTYRATE	4	4	4	4	3	1	1	3
BUTYL STEARATE	4	4	4	4	2	3	1	3
CALCINE LIQUORS	4	4	4	4	1	1	1	4
CALCIUM ACETATE	4	4	4	4	2	1	3	2
CALCIUM BISULFITE	3	3	2	3	2	1	2	2
CALCIUM CARBONATE	3	2	3	2	1	1	1	1
CALCIUM CHLORIDE	3	3	2	3	1	1	1	1
CALCIUM HYDROXIDE	3	3	2	3	1	1	1	1
CALCIUM HYPOCHLORITE	3	3	2	3	2	1	1	2
CALCIUM SALTS	4	4	4	4	1	1	1	1
CALCIUM SULFIDE	3	3	2	2	1	1	1	1
CALICHE LIQUORS	4	4	4	4	1	1	1	1
CANE SUGAR LIQUORS	4	2	1	1	1	1	1	1
CARBON MONOXIDE	4	4	4	4	3	3	1	3
CARBON DIOXIDE	1	2	1	1	1	1	1	1
CARBON DISULFIDE	2	2	2	2	3	3	1	3
CALCIUM SULFIDE	1	1	1	1	1	1	1	2
CARBON TETRACHLORIDE	2	3	1	3	2	3	1	3
CARBONIC ACID	3	3	1	2	2	1	1	1
CASTOR OIL	1	1	1	1	1	2	1	1
CELLUGUARD	4	4	4	4	1	1	1	1
CELLULUBE (NOW FYRQUEL)	4	4	4	4	3	1	1	3
CHINA WOOD OIL (TUNG OIL)	2	2	1	1	1	3	1	2
CHLORINATED SALT BRINE	4	4	4	4	3	3	1	3

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
CHLORINATED SOLVENTS	4	4	4	4	3	3	1	3
CHLOROBENZENE	3	3	2	3	3	3	1	3
CHLOROBUTADIENE	4	4	4	4	3	3	1	3
CHLOROFORM	3	2	2	1	3	3	1	3
CHLORPHENOL	4	4	4	4	3	3	1	3
COCONUT OIL	4	4	4	4	1	3	1	3
COPPER CHLORIDE	4	4	4	4	1	1	1	2
COPPER SALTS	4	4	4	4	1	1	1	1
COPPER SULFATE	3	3	2	3	1	1	1	1
CORN OIL	2	1	1	1	1	3	1	3
COTTONSEED OIL	3	2	1	2	1	3	1	3
CREOSOLS	3	2	1	2	3	3	1	3
CREOSOTE	3	3	2	1	1	3	1	2
CRESYLIC ACID	4	2	1	2	3	3	1	3
CRUDE OIL	3	2	1	1	2	3	1	3
CUTTING OIL	4	1	1	1	1	3	1	2
DECANE	4	4	4	4	1	3	1	3
DENATURED ALCOHOL	4	4	4	4	1	1	1	1
DETERGENT, WATER SOLUTION	3	3	1	1	1	1	1	2
DIESEL FUEL	1	1	1	1	1	3	1	3
DIETHYLENE GLYCOL	3	1	1	1	1	1	1	1
DIMETHYL FORMAMIDE	4	4	1	1	2	1	3	3
DOW CHEMICAL HD50-4	4	4	4	4	4	1	3	2
DOW CORNING 200, 510, 550	4	4	4	4	2	1	1	1
DOWTHERM A,E	3	1	2	2	3	3	1	3
ETHANOL	1	1	3	3	3	1	3	1
ETHYL CHLORIDE	3	3	1	3	1	3	1	3
ETHYL HEXANOL	4	4	4	4	1	1	1	1
ETHYLENE DICHLORIDE	3	3	1	2	3	3	1	3
ETHYLENE GLYCOL	2	2	1	2	1	1	1	1
FATTY ACIDS	3	3	1	2	2	3	1	2
FREON 11	1	4	4	4	2	3	2	3
FREON 12	1	1	3	1	2	3	1	1
FREON 22	1	3	1	1	3	3	3	1
FREON 134a	1	1	1	1	2	1	4	1
FUEL OIL	3	1	1	1	1	3	1	2
GALLIC ACID	3	3	2	2	2	2	1	2
GAS, LIQUID, PROPANE (LPG)	1	3	1	1	1	3	1	2
GAS, NATURAL	2	3	1	1	1	3	1	1

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
GASOLINE	1	2	1	1	3	3	1	3
GELATIN	3	3	1	1	1	1	1	1
GLUCOSE	1	1	1	1	1	1	1	1
GLYCERINE (GLYCEROL)	2	1	1	1	1	1	1	1
GLYCOLS	3	2	2	2	1	1	3	1
GREEN SULFATE LIQUOR	3	3	3	3	2	1	1	2
GULF - FR FLUID (EMULSION)	4	4	4	4	1	3	1	2
GULF - FR FLUID G	4	4	4	4	1	1	1	1
GULF - FR FLUID P	4	4	4	4	3	2	2	3
HELIUM	1	1	1	1	1	1	1	1
HEPTANE	1	1	1	1	1	3	1	2
HYDRAULIC OIL (PETROLEUM BASE)	1	1	1	1	1	3	1	1
HYDRAULIC OIL (WATER BASE)	4	1	1	1	2	1	3	2
HYDRAZINE	4	3	1	1	2	1	3	2
HYDROGEN GAS	2	2	1	1	1	1	1	1
HYDROLUBE	4	4	4	4	1	1	1	2
ISO OCTANE	1	1	1	1	1	3	1	2
ISOBUTYL ALCOHOL	4	4	1	1	2	1	1	1
ISOPROPYL ALCOHOL	1	1	2	1	2	1	1	2
ISOPROPYL ETHER	1	1	1	1	2	3	3	3
JP3 AND JP4	1	1	1	1	1	3	1	3
KEROSENE	1	1	1	1	1	3	1	2
LARD, ANIMAL FAT	1	1	1	1	1	2	1	2
LINSEED OIL	3	1	1	1	1	3	1	3
ILUBRICATING OIL SAE (10, 20, 30, 40, 50)	1	1	1	1	1	3	1	2
MAGNESIUM SALTS	4	4	4	4	1	1	1	1
MAGNESIUM SULPHATE	3	3	2	2	1	1	1	1
MERCURY	3	3	1	1	1	1	1	1
METHANE	1	3	1	1	1	3	1	2
METHANOL	1	1	1	1	1	1	3	1
METHYL BROMIDE	4	1	1	1	2	3	1	3
METHYL CHLORIDE (DRY)	2	3	1	1	3	3	1	3
METHYL CHLORIDE (WET)	1	3	1	3	3	3	1	3
METHYL ETHER	4	4	4	4	1	3	1	3
METHYL ETHYL KETONE (MEK)	1	1	1	1	3	1	3	3
MIL-F-81912 (JP-9)	1	1	1	1	3	3	1	3

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
MIL-H-5606	1	1	1	1	1	3	1	2
MIL-H-6083	1	1	1	1	1	3	1	1
MIL-H-7083	1	1	1	1	1	1	2	2
MIL-H-8446 (MLO-8515)	2	1	1	1	2	3	1	1
MIL-L-2104 & 2104B	1	1	1	1	1	3	1	2
MIL-L-7808	3	2	1	1	2	3	1	3
MILK	2	1	1	1	1	1	1	1
MINERAL OILS	1	1	1	1	1	3	1	2
MLO-7277 AND MLO-7557	2	1	1	1	3	3	1	3
MOBILE HF	1	1	1	1	1	3	1	2
MONOMETHYL HYDRAZINE	4	4	4	4	2	1	4	2
NAPHTHA (COAL OR PETROLEUM)	2	1	2	2	2	3	1	3
NAPHTHALENE	2	1	2	2	3	3	1	3
NAPHTHENIC ACID	2	1	2	2	2	3	1	3
NEATSFOOT OIL	4	4	4	4	1	2	1	3
NICKEL, ACETATE	3	2	1	1	2	1	3	2
NICKEL CHLORIDE	3	3	2	2	1	1	1	2
NICKEL SALTS	4	4	4	4	1	1	1	2
NICKEL SULFATE	3	3	1	1	1	1	1	1
NITROGEN	1	1	1	1	1	1	1	1
NITROUS OXIDE	2	2	2	1	1	4	4	4
OCTYL ALCOHOL	1	1	1	1	2	3	1	2
OLIVE OIL	2	1	1	1	1	2	1	2
ORTHO-DICHLOROBENZENE	2	2	2	2	3	3	1	3
OXALIC ACID	3	3	2	1	2	1	1	2
OXYGEN (200-400°F)	1	1	1	1	3	3	2	3
OXYGEN, COLD	1	1	1	1	2	1	1	1
OZONE	3	3	1	1	3	1	1	3
PALMITIC ACID	1	2	1	1	1	2	1	2
PARA-DICHLOROBENZENE	2	1	1	2	3	3	1	3
PARKER O LUBE	3	3	2	1	2	1	1	2
PEANUT OIL	1	1	1	1	3	3	2	3
PENTANE (2-3-METHYL, & 2-4 DIMETHYL)	1	1	1	1	2	1	1	1
PERCHLORIC ACID -2N	3	3	2	2	3	2	1	2
PERCHLOROETHYLENE	3	2	2	2	2	3	1	3
PETROLATUM	1	1	1	1	1	3	1	2

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
GASOLINE	1	2	1	1	3	3	1	3
GELATIN	3	3	1	1	1	1	1	1
GLUCOSE	1	1	1	1	1	1	1	1
GLYCERINE (GLYCEROL)	2	1	1	1	1	1	1	1
GLYCOLS	3	2	2	2	1	1	3	1
GREEN SULFATE LIQUOR	3	3	3	3	2	1	1	2
PETROLEUM OIL, BELOW 250°F	1	1	1	1	1	3	1	2
PHENOL	1	1	1	1	3	3	1	3
PHOSPHORIC ACID (3 MOLAR)	3	3	2	2	1	1	1	2
PHOSPHORIC ACID (CONCENTRATED)	3	3	2	2	3	1	1	3
PHOSPHOROUS TRICHLORIDE	3	3	1	1	3	1	1	3
PICRIC ACID, MOLTEN	3	3	2	2	2	2	1	2
PICRIC ACID, WATER SOLUTION	3	3	2	2	1	1	1	1
PINE OIL	2	2	1	2	1	3	1	3
PLATING SOLUTIONS (CHROME)	1	3	1	1	4	1	1	3
PLATING SOLUTIONS (OTHER)	4	1	1	1	1	1	1	3
PNEUMATIC SERVICE	1	1	1	1	1	1	1	1
POTASSIUM ACETATE	2	1	2	2	2	1	3	2
POTASSIUM CHLORIDE	3	3	1	2	1	1	1	1
POTASSIUM CYANIDE	3	2	2	2	1	1	1	1
POTASSIUM DICHROMATE	3	1	2	2	1	1	1	1
POTASSIUM HYDROXIDE (50%)	3	2	1	2	2	1	3	2
POTASSIUM NITRATE	2	1	1	1	1	1	1	1
POTASSIUM SALTS	4	4	4	4	1	1	1	1
POTASSIUM SULFATE	3	2	1	1	1	1	1	1
PRL-HIGH TEMP. HYDR. OIL	4	4	4	4	2	3	1	2
PRODUCER GAS	2	1	1	1	1	3	1	2
PROPANE	1	3	1	1	1	3	1	2
PROPYL ACETATE	3	1	1	1	3	2	3	3
PROPYL ALCOHOL	1	1	1	1	1	1	1	1
PROPYLENE	1	1	1	1	3	3	1	3
PYDRAUL 10E	3	1	1	1	3	1	3	3
PYDRAULA-200, C SERIES	3	1	1	1	3	3	1	3
PYDRAUL, 3 SERIES	3	1	1	1	3	1	1	3
PYROGARD 42, 43, 53, 55 (PHOSPHATE ESTER)	4	4	4	4	3	1	1	3

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
PYROGARD D	4	4	4	4	1	3	3	2
SEA WATER (SALT WATER)	2	3	1	1	1	1	1	2
SHELL IRUS 905	4	4	4	4	1	3	1	2
SILICONE GREASES	1	1	1	1	1	1	1	1
SILVER NITRATE	3	3	1	2	2	1	1	1
SKYDROL 500, TYPE 2	3	1	1	1	3	1	3	3
SKYDROL 7000, TYPE 2	3	1	1	1	3	1	2	3
SOAP SOLUTIONS	3	3	1	1	1	1	1	2
SODIUM ACETATE	1	1	1	1	2	1	3	2
SODIUM BICARBONATE	1	1	1	1	1	1	1	1
SODIUM BISULPHATE/ BISULPHITE	3	3	1	2	2	1	1	1
SODIUM BORATE	3	1	1	1	3	1	3	3
SODIUM CARBONATE	4	1	1	1	1	1	1	1
SODIUM CHLORIDE	3	2	2	2	1	1	1	1
SODIUM CYANIDE	3	1	1	1	1	1	4	1
SODIUM HYDROXIDE (CAUSTIC SODA, LYE)	3	2	1	2	2	1	2	2
SODIUM HYDROXIDE, 50%	3	3	1	2	2	1	2	2
SODIUM METAPHOSPHATE	2	1	2	2	1	1	1	2
SODIUM NITRATE	3	2	1	1	2	1	4	2
SODIUM PERBORATE	3	3	1	1	2	1	1	2
SODIUM PEROXIDE	3	1	2	2	2	1	1	2
SODIUM PHOSPHATES	1	3	2	1	1	1	1	2
SODIUM SALTS	4	4	4	4	1	1	1	2
SODIUM SULFATE	3	2	1	1	1	1	1	1
SODIUM SULFIDE / SULFITE	3	3	2	3	1	1	1	1
SODIUM THIOSULFATE	3	3	1	2	2	1	1	1
SOYBEAN OIL	2	1	1	1	1	3	1	3
STANNOUS CHLORIDE (15%)	3	3	2	3	1	1	1	1
STEAM, BELOW 400°F	1	3	1	1	3	1*	3	3
STODDARD SOLVENT	2	1	1	1	1	3	1	2
SUCROSE SOLUTIONS	1	1	1	1	1	1	1	2
SULFUR	2	1	1	1	3	1	1	1
SULFUR LIQUORS	1	1	1	1	2	2	1	2
SULFUR (MOLTEN)	3	3	1	1	3	3	1	3
SULFUR DIOXIDE (DRY)	3	1	1	3	3	1	3	3
SULFUR TRIOXIDE (DRY)	2	2	2	3	3	2	1	3

Appendix

Fluid Compatibility Chart

CODES: 1 = Satisfactory 2 = Fair 3 = Not Recommended 4 = Insufficient Data Available

Media	Body Material				Seal Material			
	Brass	Steel	316 S.S.	303 S.S.	Nitrile	E.P.	Fluorocarbon	Neoprene
SUNSAFE	1	2	1	1	3	3	1	3
TANNIC ACID (10%)	3	3	1	1	1	1	1	1
TAR, BITUMINOUS	1	1	1	1	1	1	1	1
TARTARIC ACID	2	3	3	2	1	2	1	2
TERPINEOL	4	4	4	4	2	3	1	3
TERTIARY BUTYL ALCOHOL	1	1	1	1	2	2	1	2
TETRACHLOROETHANE	4	2	1	2	3	3	1	3
TETRACHLOROETHYLENE	3	2	2	4	3	3	1	3
TETRAETHYL LEAD	1	1	1	1	2	3	1	2
TETRAETHYL LEAD (BLEND)	1	1	1	1	2	3	1	3
TITANIUM TETRACHLORIDE	2	1	2	3	2	3	1	3
TOLUENE	1	1	1	1	3	3	1	3
TRANSFORMER OIL	1	1	1	1	1	3	1	2
TRANSMISSION FLUID (TYPE A)	1	1	1	1	1	3	1	2
TRICHLOROETHANE	4	2	1	4	3	3	1	3
TRICHLOROETHYLENE	3	2	2	2	3	3	1	3
TRICRESYL PHOSPHATE	4	1	2	2	3	1	2	3
TURBINE OIL #15 (MIL-L-7808A)	4	2	1	1	2	3	1	3
TURPENTINE	3	2	1	1	1	3	1	3
VARNISH	1	1	1	1	2	3	1	3
WATER	1	3	1	1	1	1	2	2
WHISKEY	1	3	1	1	1	1	1	1
WINE	1	3	1	1	1	1	1	1
WOOD OIL	4	2	1	1	1	3	1	2
XYLENE	3	2	1	1	1	3	1	3
ZINC SULFATE	1	1	1	1	2	3	1	3

Appendix

Fluid Compatibility Chart

PF Series (Plastic/Polypropylene Material)

Ratings Code:

- G** – Good to excellent. Little or no swelling, tensile or surface changes. Preferred choice.
- L** – Marginal or conditional. Noticeable effects but not necessarily indicating lack of serviceability. Further testing suggested for specific application. Very long-term effects such as stiffening or potential for crazing should be evaluated.
- P** – Poor or unsatisfactory. Not recommended without extensive and realistic testing.
- – Indicates that this was not tested.
- #** – For Teflon. Indicates good chemical resistance but potential for excessive permeation.

Body Size	Rating	Body Size	Rating	Body Size	Rating
Acetaldehyde	P	Chloroform	P	Nickel Salts	G
Acetates	L	Chromic Acid	G	Nitric Acid (Conc.)	P
Acetic Acid	G	Copper Salts	G	Nitric Acid (Dil.)	L
Acetic Anhydride	L	Cresol	L	Nitrobenzene	G
Acetone	G	Cyclohexanone	L	Nitrogen Oxides	-
Acetyl Bromide	-	Ethers	P	Nitrous Acid	G
Acetyl Chloride	L	Ethyl Acetate	L	Oils (Animal and Mineral)	L
Air	G	Ethyl Alcohol	G	Oils (Vegetable)	L
Alcohols	L	Ethylamine	L	Oxygen	L
Aluminum Salts	G	Ethyl Bromide	-	Perchloric Acid	L
Ammonia	G	Ethyl Chloride	P	Phenol	G
Amyl Acetate	L	Fatty Acids	G	Potassium Salts	G
Aniline	G	Ferric Salts	G	Pyridine	G
Animal Oils	G	Formaldehyde	G	Silver Nitrate	G
Arsenic Salts	L	Formic Acid	G	Soap Solutions	G
Aromatic Hydrocarbons	-	Freon	L	Sodium Salts	G
Barium Salts	G	Gasoline	L	Stearic Acid	L
Benzaldehyde	L	Glucose	G	Sulfur Chloride	P
Benzene (Benzol)	L	Glycerine	G	Sulfuric Acid (Conc.)	L
Benzyl Alcohol	G	Hydriodic Acid	-	Sulfuric Acid (Dil.)	G
Bleaching Liquors	-	Hydrochloric Acid (Conc.)	G	Sulfurous Acid	L
Boric Acid Solution	G	Hydrochloric Acid (Med. Conc.)	G	Tannic Acid	G
Bromine	P	Hydrofluoric Acid	G	Tanning Extracts	L
Butane	L	Hydrogen Peroxide (Conc.)	L	Titanium Salts	-
Butanol	-	Hydrogen Peroxide (Dil.)	L	Toluene (Toluol)	P
Butyl Acetate	P	Hydrogen Sulfid	G	Trichloroacetic Acid	G
Calcium Salts	G	Iodine	G	Trichlorethylene	P
Carbon Dioxide	G	Kerosene	P	Turpentine	P
Carbon Disulfid	G	Ketones	G	Urea	G
Carbon Tetrachloride	L	Lacquer Solvent	L	Uric Acid	-
Caustic Potash	G	Lactic Acid	G	Water	G
Caustic Soda	G	Lead Acetate	G	Xylene (Xylol)	P
Chloroacetic Acid	L	Linseed Oil	G	Zinc Chloride	G
Chlorine (Dry)	P	Magnesium Salts	G		
Chlorine (Wet)	P	Naphtha	L		
Chlorobenzene	P	Natural Gas	L		

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
0C	A-19	2Z-Q4P-SS	B-64	25SFAN17SXZ (RF-254-6MP) A-32	
0E.....	A-19	2Z-Q4VY-SS	B-63	25SFAN13SXZ (RF-254-4FP) ..A-32	
0F.....	A-19	21KAAN10MPN (HF-121-2MP)A-15		25SFAN17SXZ (RF-254-6FP) ..A-32	
1C	A-19	21KAAN13MPN (HF-121-4MP)A-15		25SFTF06SXZ (RF-254-4HB) .A-32	
1E.....	A-19	21KAIN10MPN (HF-121-2FP) . A-15		25SFTF10SXZ (RF-254-6HB) .A-32	
1F.....	A-19	21KAIN13MPN (HF-121-4FP) . A-15		25SFTP06SXN (RF-254-4PL) .A-32	
10-4 LOHL6G5TP-S-PD.....	B-117	21KBAN10MVN		25SFTP10SXN (RF-254-6PL) .A-32	
10-4 LOHL6G5TP-S-EMA	B-117	(Formerly DM-121-2MP).....	B-104	2600	D-18
10-4 XHX6G5TP-S-PD	B-117	21KBAN13MVN		2625	D-18
10-4 XHX6G5TP-S-EMA	B-117	(Formerly DM-121-4MP).....	B-104	2650	D-18
12-4 LOHL6G5TP-S-PD.....	B-117	21KBIN10MVN		2676	D-18
12-4 LOHL6G5TP-S-EMA	B-117	(Formerly DM-121-2FP).....	B-104	3C	A-19
12-4 XHX6G5TP-S-PD	B-117	21KBIN13MVN		3C-E	A-19
12-4 XHX6G5TP-S-EMA	B-117	(Formerly DM-121-4FP).....	B-104	3C20EF-EF.....	D-17
14	A-21	21KBTF06MVN		3C20EM-EM.....	D-17
14-5B.....	A-22	(Formerly DM-121-4HB)	B-104	3C20F-F.....	D-17
14-5BP.....	A-22	21SBAN10MVN		3C24EF-EF.....	D-17
14-6B.....	A-22	(Formerly DM-122-2MP)	B-104	3C24F-F.....	D-17
14C.....	A-21	21SBAN13MVN		3C32EF-EF.....	D-17
14F	A-21	(Formerly DM-122-4MP)	B-104	3E.....	A-19
15	A-21	21SBIN10MVN		3F.....	A-19
15C.....	A-21	(Formerly DM-122-2FP)	B-104	30KAAN13SPN (HF-371-4MP) A-16	
15F	A-21	21SBIN13MVN		30KAAN17SPN (HF-371-6MP) A-16	
16	A-9, A-21	(Formerly DM-122-4FP)	B-104	30KAAN21SPN (HF-371-8MP) A-16	
16-4 LOHL6G5TP-S-PD.....	B-117	21SFAN10MXN (HF-124-2MP)A-15		30KAIN13SPN (HF-371-4FP) ..A-16	
16-4 LOHL6G5TP-S-EMA	B-117	21SFAN13MXN (HF-124-4MP)A-15		30KAIN17SPN (HF-371-6FP) ..A-16	
16-4 XHX6G5TP-S-PD	B-117	21SFAN10MXN (HF-124-2FP) . A-15		30KAIN21SPN (HF-371-8FP) ..A-16	
16-4 XHX6G5TP-S-EMA	B-117	21SFAN13MXN (HF-124-4FP) . A-15		30KATF10SPN (HF-371-6HB) . A-17	
16-5B.....	A-10, A-22	23KAAN13MPN (HF-251-4MP)A-16		30KATF13SPN (HF-371-8HB) . A-17	
16-5BP.....	A-10, A-22	23KAAN17MPN (HF-251-6MP)A-16		30KATP10SPN (HF-371-6PL) . A-17	
16-6B.....	A-10, A-22	23KAIN13MPN (HF-251-4FP) . A-16		30KATP13SPN (HF-371-8PL) . A-17	
16-6BP.....	A-10, A-22	23KAIN17MPN (HF-251-6FP) . A-16		32-4 LHL6G5TP	B-110
16-7B.....	A-10, A-22	23KATF06MPN (HF-251-4HB) A-17		3005-2	B-89
16E.....	A-9, A-21	23KATF10MPN (HF-251-6HB) A-17		3005-3	B-89
16G.....	A-9, A-21	23KATP06MPN (HF-251-4PL) A-17		3009-2	B-89
17	A-9, A-21	23KATP10MPN (HF-251-6PL) A-17		3009-3	B-89
17E.....	A-9, A-21	24.....	A-9	3010-2	B-89
17G.....	A-9, A-21	24-4 LHL6G5TP	B-110	3010-3	B-89
1141-62	B-91	24-4 XHX6G5TP	B-110	3010-3-230	B-89
1141-63	B-91	24-5B	A-10	3050-2	B-89
1163-60.....	B-95	24-5BP	A-10	3050-3	B-89
1163-61	B-95	24-6B	A-10	3050-3-231	B-89
2A-Q4CY-SSP.....	B-62	24C.....	A-9	3613001	B-100
2A-Q4P-SS	B-64	24F.....	A-9	4-4 LOHL6G5TP-S-PD	B-117
2A-Q4VY-SS	B-63	25	A-9	4-4 LOHL6G5TP-S-EMA	B-117
2C	A-19	25C.....	A-9	4-4 XHX6G5TP-S-PD.....	B-117
2C-E	A-19	25F	A-9	4-4 XHX6G5TP-S-EMA	B-117
2E.....	A-19	25KAAN13MPN (RF-251-4MP)A-31		4A-Q4CY-SSP.....	B-62
2F.....	A-19	25KAAN17MPN (RF-251-6MP)A-31		4A-Q4P-SS	B-64
2F-Q4CY-SSP.....	B-62	25KAIN13MPN (RF-251-4FP) . A-31		4A-Q4VY-SS	B-63
2F-Q4P-SS.....	B-64	25KAIN17MPN (RF-251-6FP) . A-31		4AH-Q4CY-SSP	B-62
2F-Q4VY-SS	B-63	25KATF06MPN (RF-251-4HB) A-31		4F-Q4CY-SSP	B-62
2M-Q4CY-SSP.....	B-62	25KATF10MPN (RF-251-6HB) A-31		4F-Q4P-SS.....	B-64
2M-Q4P-SS.....	B-64	25KATP06MPN (RF-251-4PL) A-31		4F-Q4VY-SS	B-63
2M-Q4VY-SS	B-63	25KATP10MPN (RF-251-6PL) A-31		4F-Q6CY-SSP	B-62
2Z-Q4CY-SSP.....	B-62	25SFAN13SXZ (RF-254-4MP) A-32		4F-Q6P-SS.....	B-64

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
4F-Q6VY-SS	B-63	59-1002-16FO	B-67	5915DC-01	B-67, 74
4M-Q4CY-SSP	B-62	59-1002-16FP	B-67	5915DP-01	B-67, 74
4M-Q4P-SS	B-64	59-1501-20FO	B-67	50001-010-0010	B-94
4M-Q4VY-SS	B-63	59-1501-20FP	B-67	50001-013-0010	B-10
4M-Q6CY-SSP	B-62	59-1501-24FO	B-67	50001-015-0010	B-10
4M-Q6P-SS	B-64	59-1501-24FP	B-67	50001-110-0010	B-94
4M-Q6VY-SS	B-63	59-1502-20FO	B-67	50001-112-0010	B-14, 94
4Z-Q4CY-SSP	B-62	59-1502-20FP	B-67	50001-113-0260	B-35
4Z-Q4P-SS	B-64	59-1502-24FO	B-67	50001-114-0010	B-94
4Z-Q4VY-SS	B-63	59-1502-24FP	B-67	50001-114-0296	B-88
4ZH-Q4CY-SSP	B-62	59-501-8FO	B-67	50001-115-0010	B-14
4010-2P	B-37	59-501-8FP	B-67	50001-116-0010	B-10
4010-3P	B-37, B-39	59-502-8FO	B-67	50001-116-0260	B-35, B-38
4010-6P	B-37	59-502-8FP	B-67	50001-122-0160	B-71
4010-T6	B-37	59-751-12FO	B-67	50001-123-0010	B-14
4050-2P	B-36	59-751-12FP	B-67	50001-124-0010	B-10
4050-2P-T8M	B-36	59-752-12FO	B-67	50001-126-0010	B-14
4050-3P	B-36	59-752-12FP	B-67	50001-133-0010	B-10
4050-4	B-36	595DC-01	B-67	50001-138-0260	B-10
4050-4P	B-36	595DP-01	B-67, 74	50001-210-0296	B-88
4050-5	B-36	597DC-01	B-67, 74	50001-211-0010	B-14
4050-5P	B-36	597DP-01	B-67, 74	50001-211-0260	B-35, B-38, B-77, B-79
4050-6P	B-36	5000-4	B-80	50001-212-0010	B-94
4050-15	B-36	5005-4	B-37, B-38, B-76, B-80	50001-213-0010	B-10
4050-15P	B-36	5009-4	B-37, B-38, B-76, B-80	50001-215-0010	B-35
4050-16	B-36	5050-4	B-80	50001-217-0010	B-94
4050-16P	B-36	5205-2M	B-37	50001-218-0010	B-10
4050-29BSPP	B-36	5205-3M	B-37, B-38	50001-218-0260	B-35
4050-T6	B-36	5205-4M-BU	B-37, B-38, B-76, B-80	50001-219-0160	B-71
4050P-T6	B-36	5205-4M-GR	B-37, B-38, B-76, B-80	50001-222-0010	B-10
4110-5	B-37	5205-4M-RE	B-37, B-38, B-76, B-80	50001-222-0160	B-71
4150-5	B-36	5205-4M-YE	B-37, B-38, B-76, B-80	50001-224-0010	B-11
4250-3P	B-39	5205-4M	B-14, B-37, B-38, B-76, B-80	50001-224-0160	B-71
4250-4	B-39	5205-5M	B-37	50001-226-0160	B-71
4250-4P	B-39	5205-6M	B-37	50001-234-0260	B-10
4250-15	B-39	5209-2M	B-37	50001-333-0010	B-10
4250-15P	B-39	5209-3M	B-37, B-38	50001-335-0160	B-71
4317-2-219	B-66	5209-4M-BU	B-37, B-38, B-76, B-80	50001-351-0160	B-71
4317-2-224	B-66	5209-4M-GR	B-37, B-38, B-76, B-80	50005-211-0200	B-75
4317-2-226	B-66	5209-4M-RE	B-37, B-38, B-76, B-80	6-4 LOHL6G5TP-S-PD	B-117
4317-2-234	B-66	5209-4M-YE	B-37, B-38, B-76, B-80	6-4 LOHL6G5TP-S-EMA	B-117
4118005	B-14	5209-4M	B-14, B-37, B-38, B-76, B-80	6-4 XHX6G5TP-S-PD	B-117
4118006	B-14	5209-5M	B-37	6-4 XHX6G5TP-S-EMA	B-117
4118007	B-10	5209-6M	B-37	6A-Q6CY-SSP	B-62
4128002	B-10	5910DC-01	B-67, 74	6A-Q6P-SS	B-64
4138001	B-14	5910DP-01	B-67, 74	6A-Q6VY-SS	B-63
4148001	B-10			6AH-Q6CY-SSP	B-62
4148002	B-14			6F-Q6CY-SSP	B-62
4158001	B-10			6M-Q6CY-SSP	B-62
4730001	B-95			6M-Q6P-SS	B-64
5E	A-20			6M-Q6VY-SS	B-63
5EP	A-20			6PL-Q8CY-SSP	B-63
5F	A-20			6PL-Q8VY-SS	B-64
50-140-4	B-14			6Z-Q6CY-SSP	B-62
59-1001-16FO	B-67			6Z-Q6P-SS	B-64
59-1001-16FP	B-67				

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
6Z-Q6VY-SS	B-63	6601-16-16	B-13	71-3N16-20F	B-87
6ZH-Q6CY-SSP	B-62	6602-2-4	B-13	71-3PCC-4	B-86
6100-08	B-73	6602-4-4	B-13	71-3PCC-6	B-86
6100-12	B-73	6602-6-6	B-13	71-3PCC-8	B-86
6100-16	B-73	6602-8-10	B-13	71-3PCC-12	B-86
6100-20	B-73	6602-12-10	B-13	71-3PCC-16	B-86
6100-24	B-73	6602-12-12	B-13	71-3PNC-4	B-86
6105-08	B-73	6602-16-16	B-13	71-3PNC-6	B-86
6105-12	B-73	6608-2-4	B-13	71-3PNC-8	B-86
6105-16	B-73	6608-4-4	B-13	71-3PNC-12	B-86
6105-20	B-73	6608-6-6	B-13	71-3PNC-16	B-86
6105-24	B-73	6608-8-10	B-13	71N32-24EF	B-87
6107-08	B-74	6608-12-10	B-13	71N32-24F	B-87
6107-16	B-74	6608-12-12	B-13	71N32-32F	B-87
6107-20	B-74	6608-16-16	B-13	75C12-12F	B-83
6107-24	B-74	6610-6-6	B-13	75C12-12F-DBP	B-83
6108-08	B-74	6610-8-10	B-13	75C12-SPK	B-82
6108-16	B-74	6610-10-10	B-13	75C16-16F	B-83
6108-20	B-74	6610-12-10	B-13	75C16-16F-DBP	B-83
6108-24	B-74	6610-12-12	B-13	75C16-SPK	B-82
6110-08	B-73	6610-16-16	B-13	75C20-20F	B-83
6110-12	B-73	6657-12M	B-14	75C20-20F-DBP	B-83
6110-16	B-73	6657-16M	B-14	75C20-SPK	B-82
6110-20	B-73	6659-12M	B-14	75C24-24F	B-83
6110-24	B-73	6659-16M	B-14	75C24-24F-DBP	B-83
6115-08	B-73	71-3C4-4EF	B-86	75C24-SPK	B-82
6115-12	B-73	71-3C4-4F	B-86	75C32-32F	B-83
6115-16	B-73	71-3C6-4F	B-86	75C32-32F-DBP	B-83
6115-20	B-73	71-3C6-6EF	B-86	75C32-SPK	B-82
6115-24	B-73	71-3C6-6F	B-86	75C40-40F	B-83
6120-08	B-73	71-3C6-8F	B-86	75C40-SPK	B-82
6120-12	B-73	71-3C8-8EF	B-86	75C48-48F	B-83
6120-16	B-73	71-3C8-8F	B-86	75C64-SPK	B-82
6120-20	B-73	71-3C12-12EF	B-86	75MDC-12	B-82
6120-24	B-73	71-3C12-12F	B-86	75MDC-16	B-82
6125-08	B-74	71-3C16-16EF	B-86	75MDC-20	B-82
6125-12	B-74	71-3C16-16F	B-86	75MDC-24	B-82
6125-16	B-74	71-3C16-20EF	B-86	75MDC-32	B-82
6125-20	B-74	71-3C16-20F	B-86	75MDC-40	B-82
6125-24	B-74	71-1C32-24EF	B-86	75MDC-64	B-82
6130-08	B-73	71-1C32-24F	B-86	75MDP-12	B-82
6130-12	B-73	71-1C32-32EF	B-86	75MDP-16	B-82
6130-16	B-73	71-1C32-32F	B-86	75MDP-20	B-82
6130-20	B-73	71-3N4-4EF	B-87	75MDP-24	B-82
6130-24	B-73	71-3N4-4F	B-87	75MDP-32	B-82
6135-08	B-74	71-3N6-4F	B-87	75MDP-40	B-82
6135-12	B-74	71-3N6-6EF	B-87	75MDP-64	B-82
6135-16	B-74	71-3N6-6F	B-87	75N12-12F	B-83
6135-20	B-74	71-3N6-8F	B-87	75N12-12F-DBP	B-83
6135-24	B-74	71-3N8-8EF	B-87	75N12-SPK	B-82
6601-2-4	B-13	71-3N8-8F	B-87	75N16-16F	B-83
6601-4-4	B-13	71-3N12-12EF	B-87	75N16-16F-DBP	B-83
6601-6-6	B-13	71-3N12-12F	B-87	75N16-SPK	B-82
6601-8-10	B-13	71-3N16-16EF	B-87	75N20-20F	B-83
6601-12-10	B-13	71-3N16-16F	B-87	75N20-20F-DBP	B-83
6601-12-12	B-13	71-3N16-20EF	B-87	75N20-SPK	B-82

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
75N24-24F	B-83	9250-16-320	B-78	B12	A-21
75N24-24F-DBP	B-83	9250-334	B-78	B12A	A-21
75N24-SPK	B-82	9507-4-1	B-78	B12E	A-21
75N32-32F	B-83	9090065	B-100	B13	A-21
75N32-32F-DBP	B-83	A2C	A-24	B13A	A-21
75N32-SPK	B-82	A3C	A-24	B13E	A-21
75N40-40F	B-83	A8C	A-24	B14	A-21
75N40-SPK	B-82	A8CP	A-24	B15	A-21
75N48-48F	B-83	ADCE-4	B-29	B16	A-9, A-21
75N64-SPK	B-82	ADCE-6	B-29	B17	A-9, A-21
7820123	B-100	ADCE-8	B-29	B2C	A-19
8-4 LOHL6G5TP-S-PD	B-117	ADCE-12	B-29	B20-3B	A-10
8-4 LOHL6G5TP-S-EMA	B-117	ADCH-4	B-25	B20-3BP	A-10
8-4 XHX6G5TP-S-PD	B-117	ADCH-6	B-25	B20-4B	A-10
8-4 XHX6G5TP-S-EMA	B-117	ADCH-8	B-25	B20-5B	A-10
8A-Q8CY-SSP	B-62	ADCH-12	B-25	B20-5BP	A-10
8A-Q8P-SS	B-64	ADCH-16	B-25	B22	A-9
8A-Q8VY-SS	B-63	ADCH-20	B-25	B22A	A-9
8AH-Q8CY-SSP	B-62	ADCH-24	B-25	B22E	A-9
8C	A-20	ADCH-32	B-25	B23	A-9
8CP	A-20	ADCH-40	B-25	B23A	A-9
8F-Q8CY-SSP	B-62	ADCH-48	B-25	B23E	A-9
8F-Q8P-SS	B-64	AMPE-4	B-29	B24	A-9
8F-Q8VY-SS	B-63	AMPE-6	B-29	B25	A-9
8M-Q8CY-SSP	B-62	AMPE-8	B-29	B3C	A-19
8M-Q8P-SS	B-64	AMPE-12	B-29	B30-3B	A-13
8M-Q8VY-SS	B-63	AMPH-4	B-25	B30-3BP	A-13
8Z-Q8CY-SSP	B-62	AMPH-6	B-25	B30-4B	A-13
8Z-Q8P-SS	B-64	AMPH-8	B-25	B30-5B	A-13
8Z-Q8VY-SS	B-63	AMPH-12	B-25	B30-5BP	A-13
8ZH-Q8CY-SSP	B-62	AMPH-16	B-25	B32	A-12
8010-4	B-37, B-39,	AMPH-20	B-25	B32A	A-12
B-76, B-78, B-80		AMPH-24	B-25	B32E	A-12
8010-4P	B-37, B-39,	AMPH-32	B-25	B33	A-12
B-76, B-78		AMPH-40	B-25	B33A	A-12
8010-4P-DC	B-39	AMPH-48	B-25	B33E	A-12
8010-5	B-37	APHC4-4F	B-18	B34	A-12
8010-5P	B-37	APHC6-6F	B-18	B34-5B	A-13
8010-15	B-37, B-39,	APHN4-4F	B-22	B34-5BP	A-13
B-76, B-78, B-80		APHN4-4M	B-24	B34-6B	A-13
8010-15P	B-37, B-39, B-76, B-78	APHN6-6F	B-22	B34C	A-12
8010-15P-DC	B-39	AVHC4-4F	B-18	B34F	A-12
8010-16	B-37, B-76, B-78, B-80	AVHC4-4M	B-20	B35	A-12
8010-16P	B-37, B-76, B-78	AVHC6-6F	B-18	B35C	A-12
8010-29BSPP	B-37	AVHC6-6M	B-20	B35F	A-12
8200-4	B-76	AVHC8-8F	B-18	B36	A-12
8200-15	B-76	AVHN4-4F	B-22	B36-6B	A-13
8200-16	B-76	AVHN4-4M	B-24	B36-6BP	A-13
8250-4	B-76	AVHN6-6F	B-22	B36-7B	A-13
8250-15	B-76	AVHN6-6M	B-24	B36E	A-12
8250-16	B-76	AVHN8-8F	B-22	B36G	A-12
9C	A-20	B10-3B	A-22	B37	A-12
9CP	A-20	B10-3BP	A-22	B37E	A-12
9250-4-320	B-78	B10-4B	A-22	B37G	A-12
9250-6-320	B-78	B10-5B	A-22	B38	A-12
9250-15-320	B-78	B10-5BP	A-22	B38-7B	A-13

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
B38-8B	A-13	BH2020-60	B-7	BST-3	B-93
B38J	A-12	BH2020-61	B-9	BST-3M	B-93
B39	A-12	BH2024-60	B-7	BST-4	B-93
B39F	A-12	BH2024-61	B-9	BST-4M	B-93
B39J	A-12	BPD3167	B-109	BST-6	B-93
B50-3BP	A-25	BPD323Y	B-108	BST-6M	B-93
B50-5BP	A-25	BPD343Y	B-108	BST-8	B-93
B52	A-25	BPDFS341	B-116	BST-8M	B-93
B52E	A-25	BPDFS343	B-116	BST-10	B-93
B53	A-25	BPEAC12-12F	B-28	BST-12	B-93
B53E	A-25	BPEAC4-4F	B-28	BST-N1	B-94
B72	A-29	BPEAC6-6F	B-28	BST-N1M	B-94
B73	A-29	BPEAC8-8F	B-28	BST-N2	B-94
BH1-60	B-7	BPEAC12-12F	B-28	BST-N2M	B-94
BH1-61	B-9	BPEAN4-4F	B-29	BST-N3	B-94
BH2-60	B-7	BPEAN6-6F	B-29	BST-N3M	B-94
BH2-60-STM	B-11	BPEAN8-8F	B-29	BST-N4	B-94
BH2-61	B-9	BPEAN12-12F	B-29	BST-N4M	B-94
BH2-61-STM	B-11	BPGF-1N12-12F	A-46	BST-N6	B-94
BH2C	A-6	BPGF-1N8-8F	A-46	BST-N6M	B-94
BH2E	A-6	BPGFN16-16F	A-46	BST-N8	B-94
BH2F	A-6	BPGFN20-20F	A-46	BST-N8M	B-94
BH2G	A-6	BPHC4-4F	B-18	BST-N10	B-94
BH3-60	B-7, 10	BPHC6-6F	B-18	BST-N10M	B-94
BH3-61	B-9, 10	BPHC8-8F	B-18	BST-N12	B-94
BH3C	A-5	BPHC12-12F	B-18	BST-N12M	B-94
BH3E	A-5	BPHC16-16F	B-18	BVEAC4-4F	B-28
BH3F	A-5	BPHC24-24F	B-18	BVEAC6-6F	B-28
BH4-60	B-7, 10	BPHC32-32F	B-18	BVEAC6-6M	B-28
BH4-60-STM	B-11	BPHC20-20F	B-18	BVEAC8-8F	B-28
BH4-61	B-9, 10	BPHN4-2F	B-22	BVEAC8-8M	B-28
BH4-61-STM	B-11	BPHN4-2M	B-24	BVEAC12-12F	B-28
BH5G	A-7	BPHN4-4F	B-22	BVEAC12-12M	B-28
BH6-60	B-7, 10	BPHN4-4M	B-24	BVEAN6-6F	B-29
BH6-60-STM	B-11	BPHN6-6F	B-22	BVEAN6-6M	B-29
BH6-61	B-9, 10	BPHN6-6M	B-24	BVEAN8-8F	B-29
BH6-61-STM	B-11	BPHN8-8F	B-22	BVEAN8-8M	B-29
BH8-60	B-7, 10	BPHN8-8M	B-24	BVEAN12-12F	B-29
BH8-60-STM	B-11	BPHN12-12F	B-22	BVEAN12-12M	B-29
BH8-61	B-9, 10	BPHN12-12M	B-24	BVGF-1C12-12F	A-46
BH8-61-STM	B-11	BPHN16-16F	B-22	BVGF-1C8-8F	A-46
BH8CP	A-7	BPHN16-16M	B-24	BVGFC16-16F	A-46
BH12-60L	B-7	BPHN20-20F	B-22	BVGFC20-20F	A-46
BH12-60N	B-7	BPHN24-24F	B-22	BVHC4-4F	B-18
BH12-61L	B-9	BPHN32-32F	B-22	BVHC4-4M	B-20
BH12-61N	B-9	BPN251F	B-101	BVHC6-6F	B-18
BH67E-60K	B-10	BPN252F	B-101	BVHC6-6M	B-20
BH67E-61K	B-10	BPN253F	B-101	BVHC8-8F	B-18
BH67F-60K	B-10	BPN352F	B-101	BVHC8-8M	B-20
BH67F-61K	B-10	BPN353F	B-101	BVHC12-12F	B-18
BH67G-60K	B-10	BPV252	B-101	BVHC12-12M	B-20
BH67G-61K	B-10	BPV353	B-101	BVHC16-16F	B-18
BH67J-60K	B-10	BST-1	B-93	BVHC16-16M	B-20
BH67J-61K	B-10	BST-1M	B-93	BVHC20-20F	B-18
BH2016-60	B-7	BST-2	B-93	BVHC24-24F	B-18
BH2016-61	B-9	BST-2M	B-93	BVHC32-32F	B-18

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
BVHN4-4F.....	B-22	DC-1000-FOFO	D-12	EMA3/1/8NPTCF	B-113
BVHN4-4M.....	B-24	DC-1250	D-12	EMA3/3/8ED	B-114
BVHN6-6F.....	B-22	DC-1250-FOFO	D-12	EMA3/3/8EDCF	B-114
BVHN6-6M.....	B-24	DC-1500	D-12	EMA3/7/16-20UNF-2A	B-113
BVHN8-8F.....	B-22	DC-1500-FOFO	D-12	EMA3/7/16UNFCF	B-113
BVHN8-8M.....	B-24	DC-2000	D-12	EMA3/8X1ORCF	B-114
BVHN12-12F.....	B-22	DC-2000-FOFO	D-12	EMA3/9/16-18UNF-2A	B-113
BVHN12-12M	B-24	DT-250-MOMF	D-5	EMA3/9/16UNFCF	B-113
BVHN16-16F	B-22	DT-250-MOMS.....	D-5	EMA3/10X1ED	B-114
BVHN16-16M	B-24	DT-370-MFMF	D-4	EMA3/10X1EDCF	B-114
BVHN20-20F.....	B-22	DT-370-MFMO	D-4	EMA3/12X1.5ED	B-114
BVHN24-24F.....	B-22	DT-370-MOMF	D-5	EMA3/12X1.5EDCF	B-114
BVHN32-32F.....	B-22	DT-370-MOMS.....	D-5	EMA3/14X1.5ED	B-114
C-25	B-32	DT-370-MSMO	D-6	EMA3/14X1.5EDCF	B-114
C-50	B-32	DT-370-MSMS	D-6	EMA3/M8X1OR	B-114
C-75	B-32	DT-500-MFMF.....	D-4	EMA3VS	B-114
CFE-252-PN.....	B-54	DT-500-MFMO	D-4	EMA3VSCF.....	B-114
CFE-372-PN	B-54	DT-500-MOMF	D-5	EZ-251-4FP	A-43
CFE-502-PN	B-54	DT-500-MOMS	D-5	EZ-251-4HB	A-44
CFE-622-PN.....	B-54	DT-500-MSMO.....	D-6	EZ-251-4MP	A-43
CFE-752-PN.....	B-54	DT-500-MSMS	D-6	EZ-251-4PL	A-44
CFE-1002-PN	B-54	DT-620-MFMF.....	D-4	EZ-251-6FP	A-43
CP-Q4C-SS.....	B-65	DT-620-MFMO	D-4	EZ-251-6HB	A-44
CP-Q6C-SS.....	B-65	DT-620-MOMF	D-5	EZ-251-6MP	A-43
CP-Q8C-SS.....	B-65	DT-620-MOMS.....	D-5	EZ-251-6PL	A-44
CPIFF-12S.....	D-15	DT-620-MSMO.....	D-6	EZ-371-6FP	A-43
CPIFF-16S.....	D-15	DT-620-MSMS	D-6	EZ-371-6HB	A-44
CPIFF-2P	D-15	DT-750-MFMF.....	D-4	EZ-371-6MP	A-43
CPIFF-3P	D-15	DT-750-MFMO	D-4	EZ-371-6PL	A-44
CPIFF-4P	D-15	DT-750-MOMF	D-5	EZ-371-8FP	A-43
CPIFF-6P	D-15	DT-750-MOMS	D-5	EZ-501-12FP	A-43
CPIFF-8P	D-15	DT-750-MSMO	D-6	EZ-501-8FP	A-43
CPIFF-8S	D-15	DT-750-MSMS	D-6	EZ-501-8HB	A-44
CR-25	B-32	DT-1000-MFMF	D-4	EZ-501-8MP.....	A-43
CV-250-MFMF.....	D-9	DT-1000-MFMO	D-4	EZ-501-8PL.....	A-44
CV-250-MOMS	D-9	DT-1000-MOMF	D-5	EZ-751-12FP	A-43
CV-370-MFMF.....	D-9	DT-1000-MOMS	D-5	EZ-751-12MP	A-43
CV-370-MOMS	D-9	DT-1000-MSMO	D-6	EZ-751-16FP	A-43
CV-500-MFMF.....	D-9	DT-1000-MSMS	D-6	FC-372-6FP	B-49
CV-500-MOMS	D-9	DT-1250-MFMF	D-4	FC-372-8FO	B-49
CV-620-MFMF.....	D-9	DT-1250-MFMO	D-4	FC-372-8FP	B-49
CV-620-MOMS	D-9	DT-1250-MOMF	D-5	FC-502-10FO	B-49
CV-750-MFMF.....	D-9	DT-1250-MOMS	D-5	FC-502-8FP	B-49
CV-750-MOMS	D-9	DT-1250-MSMO	D-6	FC-752-12FO	B-49
CV-1000-MFMF	D-9	DT-1250-MSMS	D-6	FC-752-12FP	B-49
CV-1000-MOMS	D-9	EA4-58AS.....	B-27	FEC-502-10FO	B-55
DC-250	D-12	EA8-58V.....	B-27	FEC-502-12FO	B-55
DC-250-FOFO	D-12	EA12-58A	B-27	FEC-502-8FP	B-55
DC-370	D-12	EMA3/1/4ED	B-114	FEC-622-12FO	B-55
DC-370-FOFO	D-12	EMA3/1/4EDCF	B-114	FEC-752-12FO	B-55
DC-50	B-32	EMA3/1/4NPT	B-113	FEM-251-4FP	B-51
DC-500	D-12	EMA3/1/4NPT71	B-113	FEM-251-6FO	B-51
DC-500-FOFO	D-12	EMA3/1/4NPTCF	B-113	FEM-252-4FP	B-53
DC-750	D-12	EMA3/1/8ED	B-114	FEM-252-6FO	B-53
DC-750-FOFO	D-12	EMA3/1/8EDCF	B-114	FEM-371-6FB	B-47, 51
DC-1000	D-12	EMA3/1/8NPT	B-113	FEM-371-6FO	B-51

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
FEM-371-6FP	B-47, 51	FEM-621-12FO	B-51	FET-1002-20SFP	B-71
FEM-371-6MO	B-51	FEM-622-12FO	B-53	FET-1501-24FO	B-69
FEM-371-8BMF	B-52	FEM-751-12FO	B-51	FET-1501-24FP	B-69
FEM-371-8FB	B-47, 51	FEM-751-12FP	B-51	FET-1501-24SF	B-70
FEM-371-8FO	B-47, 51	FEM-752-12FO	B-53	FET-1501-24SFP	B-70
FEM-371-8FP	B-47, 51	FEM-752-12FP	B-53	FET-1502	B-71
FEM-371-8MF	B-51	FEM-1001-16FO	B-51	FET-1502-24FO	B-70
FEM-371-8MO	B-51	FEM-1001-16FP	B-51	FET-1502-24FP	B-70
FEM-371-10FO	B-51	FEM-1002-16FO	B-53	FET-1502-24SF	B-71
FEM-371-10MF	B-51	FEM-1002-16FP	B-53	FET-1502-24SFP	B-71
FEM-371-16BMCL	B-52	FET3DC-01	B-71	FET-2001-32FO	B-69
FEM-371-18BMCL	B-52	FET3DP-01	B-71	FET-2001-32FP	B-69
FEM-372-6FB	B-48, 53	FET5DC-01	B-71	FET-2002	B-71
FEM-372-6FO	B-53	FET5DP-01	B-71	FET-2002-32FO	B-70
FEM-372-6FP	B-48, 53	FET6DC-01	B-71	FET-2002-32FP	B-70
FEM-372-6MF	B-53	FET6DP-01	B-71	FF-251-4FP	B-47
FEM-372-6MO	B-53	FET7DC-01	B-71	FF-251-4MP	B-47
FEM-372-8BMF	B-54	FET7DP-01	B-71	FF-251-6FO	B-47
FEM-372-8FB	B-48, 53	FET10DC-01	B-71	FF-251-KIT	B-48
FEM-372-8FO	B-48, 53	FET10DP-01	B-71	FF-251-KIT-E4	B-48
FEM-372-8FP	B-48, 53	FET15DC-01	B-71	FF-251-KIT-E5	B-48
FEM-372-8MO	B-53	FET15DP-01	B-71	FF-252-4FP	B-48
FEM-372-10FO	B-53	FET20DC-01	B-71	FF-252-4MP	B-48
FEM-372-10MF	B-53	FET20DP-01	B-71	FF-252-6FO	B-48
FEM-372-16BMCL	B-53	FET-371-8FO	B-69	FF-252-KIT	B-48
FEM-501-8BMF	B-52	FET-371-8FP	B-69	FF-252-KIT-E4	B-48
FEM-501-8BMS	B-52	FET-372	B-71	FF-252-KIT-E5	B-48
FEM-501-8FB	B-51	FET-372-8FO	B-70	FF-371-6FB	B-47
FEM-501-8FO	B-51	FET-372-8FP	B-70	FF-371-6FP	B-47
FEM-501-8FP	B-51	FET-501-8FP	B-69	FF-371-8FB	B-47
FEM-501-10FO	B-51	FET-501-10FO	B-69	FF-371-8FO	B-47
FEM-501-12BMF	B-52	FET-502	B-71	FF-371-8FP	B-47
FEM-501-12BMS	B-52	FET-502-8FP	B-70	FF-372-6FB	B-47
FEM-501-12FB	B-51	FET-502-10FO	B-70	FF-372-6FP	B-47
FEM-501-12FO	B-51	FET-621-12FO	B-69	FF-372-6FP	B-47
FEM-501-12FO	B-51	FET-621-12FP	B-69	FF-372-8FB	B-47
FEM-501-C6FO	B-52	FET-622	B-71	FF-372-8FO	B-47
FEM-501-C6FP	B-52	FET-622-12FO	B-70	FF-372-8FP	B-47
FEM-501-C8FO	B-52	FET-622-12FP	B-70	FF-372-KIT	B-48
FEM-501-C8FP	B-52	FET-751-16FO	B-69	FF-372-KIT-E4	B-48
FEM-502-8BMF	B-54	FET-751-16FP	B-69	FF-372-KIT-E5	B-48
FEM-502-8BMS	B-54	FET-751-16SF	B-70	FF-501-10FO	B-47
FEM-502-8FB	B-53	FET-751-16SFP	B-70	FF-501-8FP	B-47
FEM-502-8FO	B-53	FET-752	B-71	FF-502-10FO	B-47
FEM-502-8FP	B-53	FET-752-16FO	B-70	FF-502-8FP	B-47
FEM-502-10BMF	B-54	FET-752-16FP	B-70	FF-502-KIT	B-48
FEM-502-10BMS	B-54	FET-752-16SF	B-71	FF-502-KIT-E4	B-48
FEM-502-10FO	B-54	FET-752-16SFP	B-71	FF-502-KIT-E5	B-48
FEM-502-12BMF	B-54	FET-1001-20FO	B-69	FF-751-12FO	B-47
FEM-502-12BMS	B-54	FET-1001-20FP	B-69	FF-751-12FP	B-47
FEM-502-12FB	B-53	FET-1001-20SF	B-70	FF-752-12FO	B-47
FEM-502-12FO	B-53	FET-1001-20SFP	B-70	FF-752-12FP	B-47
FEM-502-12FP	B-53	FET-1002	B-71	FF-752-KIT	B-48
FEM-502-C6FO	B-54	FET-1002-20FO	B-7	FF-752-KIT-E4	B-48
FEM-502-C6FP	B-54	FET-1002-20FP	B-70	FF-752-KIT-E5	B-48
FEM-502-C8FO	B-54	FET-1002-20SF	B-71	FF-1001-16FO	B-47
				FF-1001-16FP	B-47

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
FF-1002-16FO	B-48	FS-1001-16FP	B-59	H3-65	B-10
FF-1002-16FP	B-48	FS-1001-KIT	B-60	H3-65M	B-10
FF-1002-KIT	B-48	FS-1001-KIT-E5	B-60	H3-66	B-10
FF-1002-KIT-E4	B-48	FS-1002-16FO	B-59	H3-66M	B-10
FF-1002-KIT-E5	B-48	FS-1002-16FP	B-59	H3-68	B-11
FF/FS-251-TOOL	B-60	FS-1002-KIT	B-60	H3-69	B-11
FF/FS-371-TOOL	B-60	FS-1002-KIT-E5	B-60	H4EP	A-8
FF/FS-751-TOOL	B-60	H0C	A-6	H4F	A-7, A-20
FF/FS-1001-TOOL	B-60	H0E	A-6	H4FP	A-8, A-20
FH-371-6FB	B-57	H0F	A-6	H4-56-9	B-17
FH-371-6FP	B-57	H00E	A-6	H4-56-9V	B-17
FH-371-6MP	B-57	H1C	A-5	H4-62	B-7, 10
FH-372-6FB	B-57	H1E	A-5	H4-62-T10	B-7
FH-372-6FP	B-57	H1F	A-5	H4-63	B-9, 10
FR-25	B-48, B-60	H1-05-12MP	D-18	H4-63-T10	B-9
FR-501	B-48, B-60	H1-05-16MP	D-18	H4-65	B-10
FR-502	B-48, B-60	H1-05-6MP	D-18	H4-65M	B-10
FR-751	B-48, B-60	H1-20-12MP	D-18	H4-66	B-10
FR-752	B-48, B-60	H1-62	B-7	H4-66M	B-10
FR-1001	B-48, B-60	H1-62-T4	B-7	H5E	A-7
FR-1002	B-48, B-60	H1-63	B-9	H5EP	A-8
FS-251-4FP	B-59	H1-63-T4	B-9	H5F	A-7
FS-251-4MP	B-59	H1-65	B-10	H5F-G	A-7, A-20
FS-251-6FO	B-59	H1-65M	B-10, B-14	H5FP	A-8, A-20
FS-251-KIT	B-60	H1-66	B-10	H5G	A-7
FS-252-4FP	B-59	H1-66M	B-10, B-14	H5G-F	A-7
FS-252-4MP	B-59	H2C	A-6	H5G-J	A-7
FS-252-6FO	B-59	H2C-E	A-6	H6E	A-7
FS-252-KIT	B-60	H2E	A-6	H6EP	A-8
FS-252-KIT-E5	B-58	H2E-F	A-6	H6FP	A-8
FS-371-6FP	B-59	H2F	A-6	H6-56-9	B-17
FS-371-8FO	B-59	H2F-G	A-6, A-19	H6-56-9V	B-17
FS-371-KIT	B-60	H2G	A-6	H6-62	B-7, 10
FS-371-KIT-E5	B-60	H2G-F	A-6	H6-62-T12	B-7
FS-372-6FP	B-59	H2G-J	A-6	H6-63	B-9, 10
FS-372-8FO	B-59	H2-62	B-7	H6-63-T12	B-9
FS-372-KIT	B-60	H2-62-T6	B-7	H6-65	B-10
FS-372-KIT-E5	B-60	H2-63	B-9	H6-65M	B-10
FS-501-10FO	B-59	H2-63-T6	B-9, B-78	H6-66	B-10
FS-501-8FP	B-59	H2-65	B-10	H6-66M	B-10
FS-501-KIT	B-60	H2-65M	B-10	H8-56-9	B-17
FS-501-KIT-E5	B-60	H2-66	B-10	H8-56-9V	B-17
FS-501-TOOL	B-60	H2-66M	B-10	H8-62	B-7, 10
FS-502-8FP	B-59	H3C	A-5	H8-62-T16	B-7
FS-502-10FO	B-59	H3C-E	A-5	H8-63	B-9, 10
FS-502-KIT	B-60	H3E	A-5	H8-63-T16	B-9
FS-502-KIT-E5	B-60	H3E-F	A-5	H8-65	B-10
FS-751-12FO	B-59	H3F	A-5	H8-65M	B-10
FS-751-12FP	B-59	H3F-G	A-5, A-19	H8-66	B-10
FS-751-KIT	B-60	H3G	A-5	H8-66M	B-10
FS-751-KIT-E5	B-60	H3G-F	A-5	H8C	A-7
FS-752-12FO	B-59	H3G-J	A-5	H8C-D	A-7
FS-752-12FP	B-59	H3-62	B-7, 10	H8CP	A-8
FS-752-KIT	B-60	H3-62-T8	B-7	H9C	A-7
FS-752-KIT-E5	B-60	H3-63	B-9, 10	H9CP	A-8
FS-1001-16FO	B-59	H3-63-T8	B-9	H12-56-9	B-17

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
H12-56-9V.....	B-17	HP-1002-16FO	B-34	NS-1001-16FB.....	B-41
H12-62L.....	B-7	HP-1002-16FP	B-34	NS-1001-16FO	B-41
H12-62N.....	B-7	HP-1501-24FO	B-34	NS-1001-16FP	B-41
H12-62-T20.....	B-7	HP-1501-24FP	B-34	NS-1002-16FB.....	B-41
H12-62-T24.....	B-7	HP-1502-24FO	B-34	NS-1002-16FO	B-41
H12-63L.....	B-9	HP-1502-24FP	B-34	NS-1002-16FP	B-41
H12-63N.....	B-9	HPC-100.....	B-34	NSS-371-6BMA	B-44
H12-63-T20.....	B-9	HPC-150.....	B-34	NSS-371-6FO	B-43
H12-63-T24.....	B-9	HPP-100.....	B-34	NSS-371-6HB	B-43
H12-65.....	B-10	HPP-150.....	B-34	NSS-371-6HMA	B-44
H12-66.....	B-10	KEY-BK	B-118	NSS-371-6MA	B-43
H16-56-9.....	B-17	KEY-BU	B-118	NSS-371-8FO	B-43
H16-56-9V.....	B-17	KEY-CL.....	B-118	NSS-371-8HB	B-43
H20-55A.....	B-17	KEY-GR	B-118	NSS-371-8MA	B-43
H20-55E.....	B-17	KEY-RD	B-118	NSS-372-6BMA	B-45
H20-55V.....	B-17	L2C.....	A-29	NSS-372-6FO	B-44
H20-56-9.....	B-17	L3C.....	A-29	NSS-372-6HB.....	B-44
H20-56-9V.....	B-17	MAV1/4NPTMA3CF.....	B-114	NSS-372-6HMA	B-45
H20P-65.....	B-10	MAV1/4NPTMA3KMCF.....	B-114	NSS-372-6MA	B-45
H20P-66.....	B-10	MAVMD1/4NPTMA3CF.....	B-114	NSS-372-8FO	B-44
H24-55A.....	B-17	MCE-4.....	B-29	NSS-372-8HB.....	B-44
H24-55E.....	B-17	MCE-6.....	B-29	NSS-372-8MA	B-45
H24-55V.....	B-17	MCE-8.....	B-29	NSS-501-8BMA.....	B-44
H32-55A.....	B-17	MCE-12.....	B-29	NSS-501-8HB	B-43
H32-55E.....	B-17	MCH-4.....	B-25	NSS-501-8HMA.....	B-44
H32-55V.....	B-17	MCH-6.....	B-25	NSS-501-8MA	B-43
H67A-28.....	B-10	MCH-8.....	B-25	NSS-501-10FO	B-43
H67C-28.....	B-10	MCH-12.....	B-25	NSS-501-12BMA	B-44
H67E-62K.....	B-10	MCH-16.....	B-25	NSS-501-12FO	B-43
H67E-63K.....	B-10	MCH-20.....	B-25	NSS-501-12HB.....	B-43
H67F-62K.....	B-10	MCH-24.....	B-25	NSS-501-12HMA	B-44
H67F-63K.....	B-10	MCH-32.....	B-25	NSS-501-12MA	B-43
H67G-62K.....	B-10	MCH-40.....	B-25	NSS-502-8BMA.....	B-45
H67G-63K.....	B-10	MCH-48.....	B-25	NSS-502-8HB	B-44
H67J-62K.....	B-10	NR-37.....	B-40, B-48, B-57, B-60	NSS-502-8HMA.....	B-45
H67J-63K.....	B-10	NR-50.....	B-40, B-48, B-57, B-60	NSS-502-8MA	B-45
H68E-67K.....	B-11	NR-75.....	B-40	NSS-502-10FO	B-44
H69E-67K.....	B-11	NR-100.....	B-40	NSS-502-12BMA	B-45
H2016-62.....	B-7	NS-371-6FB	B-41	NSS-502-12FO	B-44
H2016-63.....	B-9	NS-371-6FP	B-41	NSS-502-12HB.....	B-44
H2020-62.....	B-7	NS-371-8FO	B-41	NSS-502-12HMA	B-45
H2020-63.....	B-9	NS-372-6FB	B-41	NSS-502-12MA	B-45
H2024-62.....	B-7	NS-372-6FP	B-41	P-25.....	B-32
H2024-63.....	B-9	NS-372-8FO	B-41	P-50.....	B-32
HM1-05-12MP.....	D-18	NS-501-10FO	B-41	P-75.....	B-32
HM1-10-12MP.....	D-18	NS-501-8FB	B-41	P200-9A.....	B-100
HM1-10-6MP.....	D-18	NS-501-8FP	B-41	P200-9AY.....	B-100
HM1-15-12MP.....	D-18	NS-502-10FO	B-41	P201-01A.....	B-99
HO-251-4FP.....	B-96	NS-502-8FB.....	B-41	P208-01A.....	B-99
HO-252-4FP.....	B-96	NS-502-8FP	B-41	P300-11S.....	B-100
HO-371-6FP.....	B-96	NS-502-8FB.....	B-41	P300-6.....	B-100
HO-372-6FP.....	B-96	NS-751-12FB.....	B-41	P300-9A.....	B-100
HO-501-8FP.....	B-96	NS-751-12FO	B-41	P300-9AY.....	B-100
HO-502-8FP.....	B-96	NS-751-12FP.....	B-41	P301-01A.....	B-99
HP-1001-16FO.....	B-34	NS-752-12FB	B-41	P308-01A.....	B-99
HP-1001-16FP.....	B-34	NS-752-12FO	B-41	P308-01A-HF.....	B-99
		NS-752-12FP	B-41		

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
P500-9A.....	B-100	PC308-BP.....	B-98	PD351.....	B-109
P500-9AY.....	B-100	PC308V.....	B-98	PD355.....	B-109
PBH-251-4FP.....	A-39	PC308V-BP.....	B-98	PD357.....	B-109
PBH-251-4MP.....	A-39	PC316.....	B-99	PD361.....	B-109
PBH-251-6FP.....	A-39	PC316-BP.....	B-99	PD363.....	B-108
PBH-251-6MP.....	A-39	PC316V.....	B-99	PD365.....	B-109
PBH-371-4FP.....	A-39	PC316V-BP.....	B-99	PD366.....	B-109
PBH-371-4MP.....	A-39	PC318.....	B-99	PD367C.....	B-109
PBH-371-6FP.....	A-39	PC318-BP.....	B-99	PD386.....	B-109
PBH-371-6MP.....	A-39	PC318V.....	B-99	PD397.....	B-109
PBH-371-8FP.....	A-39	PC318V-BP.....	B-99	PD3107.....	B-109
PBS-251-4FP.....	A-41	PC326.....	B-98	PD3127.....	B-109
PBS-251-4MP.....	A-41	PC326-BP.....	B-98	PD3147.....	B-109
PBS-251-6FP.....	A-41	PC326V.....	B-98	PDC-4.....	B-25, B-29
PBS-251-6MP.....	A-41	PC326V-BP.....	B-98	PDC-6.....	B-25, B-29
PBS-371-6FP.....	A-41	PC328.....	B-98	PDC-8.....	B-25, B-29
PBS-371-6MP.....	A-41	PC328-BP.....	B-98	PDC-12.....	B-25, B-29
PBS-371-8FP.....	A-41	PC328V.....	B-98	PDC-16.....	B-25
PBS-371-8MP.....	A-41	PC328V-BP.....	B-98	PDFS242.....	B-116
PBS-501-12FP.....	A-41	PC500.....	B-99	PDFS-PROBE.....	B-116
PBS-501-6FP.....	A-41	PC504.....	B-98	PDH-19.....	B-115
PBS-501-8FP.....	A-41	PC504-BP.....	B-98	PDH-32.....	B-115
PBS-501-8MP.....	A-41	PC506.....	B-98	PDH-120.....	B-115
PC204.....	B-98	PC506-BP.....	B-98	PDH-240.....	B-115
PC204-BP.....	B-98	PC514.....	B-99	PDP-4.....	B-25, B-29
PC204AV.....	B-98	PC514-BP.....	B-99	PDP-6.....	B-25, B-29
PC204AV-BP.....	B-98	PC516.....	B-99	PDP-8.....	B-25, B-29
PC205.....	B-98	PC516-BP.....	B-99	PDP-12.....	B-25, B-29
PC205AV.....	B-98	PC524.....	B-98	PDP-16.....	B-25
PC206.....	B-98	PC524-BP.....	B-98	PDP34BTL.....	B-112
PC206-BP.....	B-98	PC526.....	B-98	PDP34BTX.....	B-112
PC206AV.....	B-98	PC526-BP.....	B-98	PDP36BTL.....	B-112
PC206AV-BP.....	B-98	PD6-285.....	B-110, 111	PDP36BTX.....	B-112
PC214.....	B-99	PD34BTL.....	B-110	PDP242.....	B-112
PC214-BP.....	B-99	PD34BTX.....	B-110	PDP288.....	B-112
PC214AV.....	B-99	PD36BTL.....	B-110	PDP323.....	B-112
PC214AV-BP.....	B-99	PD36BTX.....	B-110	PDP341.....	B-112
PC215.....	B-99	PD38BTL.....	B-110	PDP343.....	B-112
PC215AV.....	B-99	PD38BTX.....	B-110	PDP361.....	B-112
PC216.....	B-99	PD222.....	B-108	PEAC4-4F.....	B-28
PC216-BP.....	B-99	PD240.....	B-108	PEAC4-4M.....	B-28
PC216AV.....	B-99	PD242.....	B-108	PEAC6-6F.....	B-28
PC216AV-BP.....	B-99	PD243.....	B-108	PEAC8-8F.....	B-28
PC224.....	B-98	PD248.....	B-108	PEAN4-4F.....	B-29
PC224-BP.....	B-98	PD260.....	B-108	PEAN4-4M.....	B-29
PC224AV.....	B-98	PD288.....	B-108	PEAN6-6F.....	B-29
PC224AV-BP.....	B-98	PD310BTL.....	B-110	PEAN8-8F.....	B-29
PC226.....	B-98	PD312BTX.....	B-110	PER-251-4FP.....	A-39
PC226-BP.....	B-98	PD322.....	B-108	PER-251-4MP.....	A-39
PC226AV.....	B-98	PD323.....	B-108	PER-251-6FP.....	A-39
PC226AV-BP.....	B-98	PD331.....	B-109	PER-251-6MP.....	A-39
PC306.....	B-98	PD341.....	B-109	PES-251-4MP.....	A-41
PC306-BP.....	B-98	PD342.....	B-108	PES-251-6FP.....	A-41
PC306V.....	B-98	PD343.....	B-108	PFE-251-PN.....	B-54
PC306V-BP.....	B-98	PD345.....	B-109	PFE-371-PN.....	B-54
PC308.....	B-98	PD346.....	B-109	PFE-501-PN.....	B-54

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
PFE-621-PN	B-54	PN352.....	B-101	PS690303-6-6.....	C-10
PFE-751-PN	B-54	PN352-25	B-102	PS690307-6-6.....	C-11
PFE-1001-PN	B-54	PN352-40	B-102	PS690310-6-6.....	C-11
PHC4-4F	B-18	PN352-55	B-102	PS690502-6-6.....	C-12
PHC6-6F	B-18	PN352-70	B-102	PS690503-6-6.....	C-12
PHC8-8F	B-18	PN352-85	B-102	PS690507-6-6.....	C-13
PHC12-12F	B-18	PN352F	B-101	PS690510-6-6.....	C-13
PHC16-16F	B-18	PN352S	B-101	PS810102-8-8.....	C-3
PHC20-20F	B-18	PN353	B-101	PS810106-8-8.....	C-4
PHC24-24F	B-18	PN353-25	B-102	PS810302-8-8.....	C-4
PHC32-32F	B-18	PN353-40	B-102	PS810306-8-8.....	C-5
PHN4-2F	B-22	PN353-55	B-102	PS810502-8-8.....	C-5
PHN4-2M	B-24	PN353-70	B-102	PS810506-8-8.....	C-6
PHN4-4F	A-37, B-22	PN353-85	B-102	PS890102-8-8.....	C-7
PHN4-4M	A-37, B-24	PN353F	B-101	PS890103-8-8.....	C-8
PHN6-6F	A-37, B-22	PN353S	B-101	PS890107-8-8.....	C-8
PHN6-6M	A-37, B-24	PN354.....	B-101	PS890110-8-8.....	C-9
PHN8-8F	A-37, B-22	PN553.....	B-101	PS890302-8-8.....	C-10
PHN8-8M	A-37, B-24	PN554.....	B-101	PS890303-8-8.....	C-10
PHN12-12F	A-37, B-22	PN556.....	B-101	PS890307-8-8.....	C-11
PHN12-12M	A-37, B-24	PR-25	B-32	PS890310-8-8.....	C-11
PHN16-16F	B-22	PS6-RPR.....	C-2	PS890502-8-8.....	C-12
PHN16-16M	B-24	PS6A-RPR.....	C-2	PS890503-8-8.....	C-12
PHN20-20F	B-22	PS6W-RPR	C-2	PS890507-8-8.....	C-13
PHN24-24F	B-22	PS6Y-RPR	C-2	PS890510-8-8.....	C-13
PHN32-32F	B-22	PS8-RPR.....	C-2	PS1210102-12-12.....	C-3
PHN32-32M	B-24	PS8A-RPR.....	C-2	PS1210106-12-12.....	C-4
PL-25.....	B-32	PS8W-RPR	C-2	PS1210302-12-12.....	C-4
PN250.....	B-101	PS8Y-RPR	C-2	PS1210306-12-12.....	C-5
PN250-25	B-102	PS12-RPR	C-2	PS1210502-12-12.....	C-5
PN250-40	B-102	PS12A-RPR	C-2	PS1210506-12-12.....	C-6
PN250-55	B-102	PS12W-RPR	C-2	PS1290102-12-12.....	C-7
PN251	B-101	PS12Y-RPR.....	C-2	PS1290103-12-12.....	C-8
PN251-25.....	B-102	PS16-RPR	C-2	PS1290107-12-12.....	C-8
PN251-40.....	B-102	PS16A-RPR	C-2	PS1290110-12-12.....	C-9
PN251-55.....	B-102	PS16W-RPR	C-2	PS1290302-12-12.....	C-10
PN251-70.....	B-102	PS16Y-RPR.....	C-2	PS1290303-12-12.....	C-10
PN251-85.....	B-102	PS61JMJM-6-6	C-6	PS1290307-12-12.....	C-11
PN251F.....	B-101	PS81JMJM-8-8	C-6	PS1290310-12-12.....	C-11
PN251S.....	B-101	PS121JMJM-12-12	C-6	PS1290502-12-12.....	C-12
PN252.....	B-101	PS161JMJM-16-16	C-6	PS1290503-12-12.....	C-12
PN252-25	B-102	PS8901JM-8-8	C-9	PS1290507-12-12.....	C-13
PN252-40	B-102	PS12901JM-12-12	C-9	PS1290510-12-12.....	C-13
PN252-55	B-102	PS16901JM-16-16	C-9	PS1610102-16-16.....	C-3
PN252-70	B-102	PS610102-6-6.....	C-3	PS1610106-16-16.....	C-4
PN252-85	B-102	PS610106-6-6.....	C-4	PS1610302-16-16.....	C-4
PN252F.....	B-101	PS610302-6-6	C-4	PS1610306-16-16.....	C-5
PN252S	B-101	PS610306-6-6	C-5	PS1610502-16-16.....	C-5
PN253.....	B-101	PS610502-6-6	C-5	PS1610506-16-16.....	C-6
PN253F.....	B-101	PS610506-6-6	C-6	PS1690102-16-16.....	C-7
PN253S	B-101	PS690102-6-6	C-7	PS1690103-16-16.....	C-8
PN351-25.....	B-102	PS690103-6-6	C-8	PS1690107-16-16.....	C-8
PN351-40.....	B-102	PS690107-6-6	C-8	PS1690110-16-16.....	C-9
PN351-55.....	B-102	PS690110-6-6.....	C-9	PS1690302-16-16.....	C-10
PN351-70.....	B-102	PS6901JM-6-6	C-9	PS1690303-16-16.....	C-10
PN351-85.....	B-102	PS690302-6-6.....	C-10	PS1690307-16-16.....	C-11

Appendix

Fluid Compatibility Chart

Media	Page	Media	Page	Media	Page
PS1690310-16-16	C-11	S75C32-32F	B-83	SH4-63	B-9, 10
PS1690502-16-16	C-12	S75C40-40F	B-83	SH4-63-T10	B-9
PS1690503-16-16	C-12	S75C48-48F	B-83	SH6-62	B-7, 10
PS1690507-16-16	C-13	S75N12-12F	B-83	SH6-62-T12	B-7
PS1690510-16-16	C-13	S75N16-16F	B-83	SH6-63	B-9, 10
PV-05-12MP	D-19	S75N16-16F-DBP	B-83	SH6-63-T12	B-9
PV-05-8MP	D-19	S75N20-20F	B-83	SH8-62	B-7, 10
PV-10-12MP	D-19	S75N20-20F-DBP	B-83	SH8-62-T16	B-7
PV-20-12MP	D-19	S75N24-24F	B-83	SH8-63	B-9, 10
RK-12N	C-14	S75N32-32F	B-83	SH8-63-T16	B-9
RK-4/6N	C-14	S75N40-40F	B-83	SH8C	A-7
RK-8N	C-14	S75N48-48F	B-83	SH9C	A-7
S2C	A-19	S2102-4-4	C-16	SH12-62L	B-7
S22	A-9	S2102-6-6	C-16	SH12-62N	B-7
S23	A-9	S2102-8-8	C-16	SH12-62-T20	B-7
S6C4F-F	D-17	S2102-12-12	C-16	SH12-62-T24	B-7
S6C4F-M	D-17	S2107-4-4	C-16	SH12-63L	B-9
S6C4M-M	D-17	S2107-6-6	C-16	SH12-63N	B-9
S6C6F-F	D-17	S2107-8-8	C-16	SH12-63-T20	B-9
S6C6F-M	D-17	S2107-12-12	C-16	SH12-63-T24	B-9
S6C8F-F	D-17	S2202-4-4	C-17	SH67E-62K	B-10
S6C8M-F	D-17	S2202-6-6	C-17	SH67E-63K	B-10
S6C8M-M	D-17	S2202-8-8	C-17	SH67F-62K	B-10
S6C12F-F	D-17	S2202-12-12	C-17	SH67F-63K	B-10
S6C16F-F	D-17	S2207-4-4	C-17	SH67G-62K	B-10
S71-3C4-4EF	B-86	S2207-6-6	C-17	SH67G-63K	B-10
S71-3C4-4F	B-86	S2207-8-8	C-17	SH67J-62K	B-10
S71-3C6-6EF	B-86	S2207-12-12	C-17	SH67J-63K	B-10
S71-3C6-6F	B-86	S2502-6-6	C-18	SH71-3C4-4F	B-86
S71-3C6-8F	B-86	S2502-8-8	C-18	SH71-3C6-6EF	B-86
S71-3C8-8EF	B-86	S2502-12-12	C-18	SH71-3C6-6F	B-86
S71-3C8-8F	B-86	S2507-6-6	C-18	SH71-3C8-8F	B-86
S71-3C12-12EF	B-86	S2507-8-8	C-18	SH71-3C12-12F	B-86
S71-3C12-12F	B-86	S2507-12-12	C-18	SH71-3C16-16F	B-86
S71-3C16-16EF	B-86	SCA-1/2-EMA-3	B-114	SH71-3N4-4F	B-87
S71-3C16-16F	B-86	SCA-1/4-EMA-3CF	B-114	SH71-3N6-6EF	B-87
S71-3C16-20EF	B-86	SCA-7/16-EMA-3	B-114	SH71-3N6-6F	B-87
S71-3C16-20F	B-86	SCA-EMA-3/3	B-114	SH71-3N8-8EF	B-87
S71-3N4-4EF	B-87	SH1-62	B-7	SH71-3N8-8F	B-87
S71-3N4-4F	B-87	SH1-62-T4	B-7	SH71-3N12-12F	B-87
S71-3N6-6EF	B-87	SH1-63	B-9	SH71-3N16-16F	B-87
S71-3N6-6F	B-87	SH1-63-T4	B-9	SH2016-62	B-7
S71-3N8-8EF	B-87	SH2-62	B-7	SH2016-63	B-9
S71-3N8-8F	B-87	SH2-62-T6	B-7	SH2020-62	B-7
S71-3N12-12EF	B-87	SH2-63	B-9	SH2020-63	B-9
S71-3N12-12F	B-87	SH2-63-T6	B-9	SH2024-62	B-7
S71-3N16-16EF	B-87	SH2C	A-6	SH2024-63	B-9
S71-3N16-16F	B-87	SH2C-E	A-6	SM-251-4FB	B-31
S71-3N16-20EF	B-87	SH3-62	B-7, 10	SM-251-4FP	B-31
S71-3N16-20F	B-87	SH3-62-T8	B-7	SM-251-6FB	B-31
S75C12-12F	B-83	SH3-63	B-9, 10	SM-251-6FO	B-31
S75C16-16F	B-83	SH3-63-T8	B-9	SM-251-6FP	B-31
S75C16-16F-DBP	B-83	SH3C	A-5	SM-252-4FB	B-32
S75C20-20F	B-83	SH3C-E	A-5	SM-252-4FP	B-32
S75C20-20F-DBP	B-83	SH4-62	B-7, 10	SM-252-6FB	B-32
S75C24-24F	B-83	SH4-62-T10	B-7	SM-252-6FO	B-32

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
SM-252-6FP.....	B-32	SSH1-62Y.....	B-8	SST-6.....	B-93
SM-501-8FB.....	B-31	SSH1-62Y-T4.....	B-8	SST-6M.....	B-93
SM-501-8FO.....	B-31	SSH1-63Y.....	B-8	SST-8.....	B-93
SM-501-8FP.....	B-31	SSH1-63Y-T4.....	B-8	SST-8M.....	B-93
SM-501-12FB.....	B-31	SSH2-62Y.....	B-8	SST-N1.....	B-94
SM-501-12FP.....	B-31	SSH2-62Y-T6.....	B-8	SST-N1M.....	B-94
SM-502-8FB.....	B-32	SSH2-63Y.....	B-8	SST-N2.....	B-94
SM-502-8FO.....	B-32	SSH2-63Y-T6.....	B-8	SST-N2M.....	B-94
SM-502-8FP.....	B-32	SSH3-62Y.....	B-8, 10	SST-N3.....	B-94
SM-502-12FB.....	B-32	SSH3-62Y-T8.....	B-8	SST-N3M.....	B-94
SM-502-12FP.....	B-32	SSH3-63Y.....	B-8, 10	SST-N4.....	B-94
SM-751-12FB.....	B-31	SSH3-63Y-T8.....	B-8	SST-N4M.....	B-94
SM-751-12FO.....	B-31	SSH4-62Y.....	B-8, 10	SST-N6.....	B-94
SM-751-12FP.....	B-31	SSH4-62Y-T10.....	B-8	SST-N6M.....	B-94
SM-751-16FB.....	B-31	SSH4-63Y.....	B-8, 10	SST-N8.....	B-94
SM-751-16FO.....	B-31	SSH4-63Y-T10.....	B-8	SST-N8M.....	B-94
SM-751-16FP.....	B-31	SSH6-62Y.....	B-8, 10	ST-N1.....	B-94
SM-752-12FB.....	B-32	SSH6-62Y-T12.....	B-8	ST-N1M.....	B-94
SM-752-12FO.....	B-32	SSH6-63Y.....	B-8, 10	ST-N2.....	B-94
SM-752-12FP.....	B-32	SSH6-63Y-T12.....	B-8	ST-N2M.....	B-94
SM-752-16FB.....	B-32	SSH8-62Y.....	B-8, 10	ST-N3.....	B-94
SM-752-16FO.....	B-32	SSH8-62Y-T16.....	B-8	ST-N3M.....	B-94
SM-752-16FP.....	B-32	SSH8-63Y.....	B-8, 10	ST-N4.....	B-94
SMA3-200CF.....	B-115	SSH8-63Y-T16.....	B-8	ST-N4M.....	B-94
SMA3-400CF.....	B-115	SSH12-62LY.....	B-8	ST-N6.....	B-94
SMA3-800CF.....	B-115	SSH12-62NY.....	B-8	ST-N6M.....	B-94
SMA3-1000CF.....	B-115	SSH12-62Y-T20.....	B-8	ST-N8.....	B-94
SMA3-2000CF.....	B-115	SSH12-62Y-T24.....	B-8	ST-N8M.....	B-94
SMA3-4000CF.....	B-115	SSH12-63LY.....	B-8	SVEAC4-4F.....	B-28
SPEAC4-4F.....	B-28	SSH12-63NY.....	B-8	SVEAC8-8F.....	B-28
SPEAC4-4M.....	B-28	SSH12-63Y-T20.....	B-8	SVEAC8-8M.....	B-28
SPEAC12-12F.....	B-28	SSH12-63Y-T24.....	B-8	SVEAC12-12F.....	B-28
SPEAN4-4F.....	B-29	SSH67E-62KY.....	B-10	SVEAN4-2F.....	B-29
SPEAN4-4M.....	B-29	SSH67E-63KY.....	B-10	SVEAN4-4F.....	B-29
SPEAN12-12F.....	B-29	SSH67F-62KY.....	B-10	SVEAN4-4M.....	B-29
SPHC4-4F.....	B-19	SSH67F-63KY.....	B-10	SVEAN8-8F.....	B-29
SPHC6-6F.....	B-19	SSH67G-62KY.....	B-10	SVEAN8-8M.....	B-29
SPHC8-8F.....	B-19	SSH67G-63KY.....	B-10	SVEAN12-12F.....	B-29
SPHC12-12F.....	B-19	SSH67J-62KY.....	B-10	SVHC4-2F.....	B-19
SPHC16-16F.....	B-19	SSH67J-63KY.....	B-10	SVHC4-4F.....	B-19
SPHC20-20F.....	B-19	SSH2016-62Y.....	B-8	SVHC4-4M.....	B-20
SPHC24-24F.....	B-19	SSH2016-63Y.....	B-8	SVHC6-6F.....	B-19
SPHC32-32F.....	B-19	SSH2020-62Y.....	B-8	SVHC6-6M.....	B-20
SPHN4-2F.....	B-23	SSH2020-63Y.....	B-8	SVHC8-8F.....	B-19
SPHN4-2M.....	B-24	SSH2024-62Y.....	B-8	SVHC8-8M.....	B-20
SPHN4-4F.....	B-23	SSH2024-63Y.....	B-8	SVHC12-12F.....	B-19
SPHN4-4M.....	B-24	SSPD242Y.....	B-108	SVHC12-12M.....	B-20
SPHN6-6F.....	B-23	SSPD343Y.....	B-108	SVHC16-16F.....	B-19
SPHN6-6M.....	B-24	SST-1.....	B-93	SVHC16-16M.....	B-20
SPHN8-8F.....	B-23	SST-1M.....	B-93	SVHC20-20F.....	B-19
SPHN8-8M.....	B-24	SST-2.....	B-93	SVHC24-24F.....	B-19
SPHN12-12F.....	B-23	SST-2M.....	B-93	SVHC32-32F.....	B-19
SPHN16-16F.....	B-23	SST-3.....	B-93	SVHN4-2F.....	B-23
SPHN20-20F.....	B-23	SST-3M.....	B-93	SVHN4-4F.....	B-23
SPHN24-24F.....	B-23	SST-4.....	B-93	SVHN4-4M.....	B-24
SPHN32-32F.....	B-23	SST-4M.....	B-93	SVHN6-6F.....	B-23

Appendix

Part Number Index

Media	Page	Media	Page	Media	Page
SVHN6-6M	B-24	VEAC6-6F	B-28	VHN12-12F	B-22
SVHN8-8F	B-23	VEAC6-6M	B-28	VHN12-12M	B-24
SVHN8-8M	B-24	VEAC8-8F	B-28	VHN16-16EF	B-22
SVHN12-12F	B-23	VEAC8-8M	B-28	VHN16-16F	B-22
SVHN12-12M	B-24	VEAC8-SPK	B-27	VHN16-16M	B-24
SVHN16-16F	B-23	VEAC12-12F	B-28	VHN20-20F	B-22
SVHN16-16M	B-24	VEAC12-12M	B-28	VHN20-20M	B-24
SVHN20-20F	B-23	VEAN4-4F	B-29	VHN24-24F	B-22
SVHN20-20M	B-24	VEAN4-4M	B-29	VHN32-32F	B-22
SVHN24-24F	B-23	VEAN6-6F	B-29	VIHC4-4F	A-37
SVHN32-32F	B-23	VEAN6-6M	B-29	VIHC4-4FSL	A-37
TC-371	B-90	VEAN8-8F	B-29	VIHC4-4M	A-37
TC-372	B-90	VEAN8-8M	B-29	VIHC4-4MSL	A-37
TH-1000-16FO-05	D-21	VEAN8-SPK	B-27	VIHC6-6F	A-37
TH-1000-16FO-10	D-21	VEAN12-12F	B-29	VIHC6-6FSL	A-37
TH-1000-16FO-13	D-21	VEAN12-12M	B-29	VIHC6-6M	A-37
TH-1000-16FO-25	D-21	VHC4-2F	B-18	VIHC6-6MSL	A-37
TH-1000-16FO-30	D-21	VHC4-2M	B-20	VIHC8-8F	A-37
TH-1000-16FO-33	D-21	VHC4-4EF	B-18	VIHC12-12F	A-37
TH-1000-16FO-45	D-21	VHC4-4EM	B-21	VP-Q4V-SSP	B-65
TH-1000-16FO-50	D-21	VHC4-4F	B-18	VP-Q6V-SSP	B-65
TH-1000-16FO-53	D-21	VHC4-4M	B-20	VP-Q8V-SSP	B-65
TH-1000-16FO-65	D-21	VHC6-6EF	B-18	VPHC6-6F	B-21
TH-1000-16FO-70	D-21	VHC6-6EM	B-21	VPHC8-8F	B-21
TH-1000-16FO-85	D-21	VHC6-6F	B-18	VPHC12-12EF	B-21
TL-251-4FP	A-34	VHC6-6M	B-20	VPHC12-12F	B-21
TL-251-4MP	A-34	VHC8-8EF	B-18	VPHN8-8EM	B-25
TL-251-6MP	A-34	VHC8-8EM	B-21	VPHN8-8F	B-25
TL-254-2FP	A-35	VHC8-8F	B-18		
TL-254-2MP	A-35	VHC8-8M	B-20		
TL-254-4FP	A-35	VHC12-12EFV	B-18		
TL-254-4HB	A-35	VHC12-12EM	B-21		
TL-254-4MP	A-35	VHC12-12F	B-18		
TL-254-6HB	A-35	VHC12-12M	B-20		
TL-501-12FP	A-34	VHC16-16EF	B-18		
TL-501-6FP	A-34	VHC16-16F	B-18		
TL-501-6MP	A-34	VHC16-16M	B-20		
TL-501-8FP	A-34	VHC20-20F	B-18		
TL-501-8MP	A-34	VHC24-24F	B-18		
TL-504-12MP	A-35	VHC32-32F	B-18		
TL-504-4FP	A-35	VHC32-32M	B-20		
TL-504-4HB	A-35	VHN4-2F	B-22		
TL-504-4MP	A-35	VHN4-2M	B-24		
TL-504-6FP	A-35	VHN4-4EM	B-25		
TL-504-6HB	A-35	VHN4-4F	B-22		
TL-504-6MP	A-35	VHN4-4M	B-24		
TL-504-8HB	A-35	VHN6-6EM	B-25		
TL-504-8MP	A-35	VHN6-6F	B-22		
TR-37	B-14, B-90	VHN6-6M	B-24		
UC-251-4FP	A-27	VHN8-8EF	B-22		
UC-251-4MP	A-27	VHN8-8EM	B-25		
UC-251-6FP	A-27	VHN8-8F	B-22		
UC-251-6MP	A-27	VHN8-8M	B-24		
VEAC4-4F	B-28	VHN12-12EF	B-22		
VEAC4-4M	B-28	VHN12-12EM	B-25		

Appendix

Safety Guide



WARNING

SAFETY GUIDE FOR SELECTING AND USING QUICK COUPLING DIVISION PRODUCTS AND RELATED ACCESSORIES



WARNING

DANGER: Failure or improper selection or improper use of Quick Coupling Division (QCD) products and related accessories can cause death, personal injury, and property damage. Possible consequences of failure or improper selection or improper use of QCD products or related accessories include but are not limited to:

- Couplings or parts thrown off at high speed.
- High velocity fluid discharge.
- Explosion or burning of the conveyed fluid.
- Contact with suddenly moving or falling objects that are to be held in position or moved by the conveyed fluid.
- Dangerously whipping hose.
- Contact with conveyed fluids that may be hot, cold, toxic, or otherwise injurious.
- Sparking or explosion while paint or flammable liquid spraying.

Before selecting or using any Parker quick action couplings or related accessories, it is important that you read and follow the following instructions.

No product from the Quick Coupling Division is approved for in-flight aerospace applications. For products used in in-flight aerospace applications, please contact Parker Aerospace Group.

1.1 Scope: This safety guide provides instructions for selecting and using (including installing, connecting, disconnecting, and maintaining) QCD products and related accessories. This safety guide is a supplement to and is to be used with, the specific Parker publications for the specific QCD products and related accessories being considered for use.

1.2 Fail-Safe: QCD products or the hose they are attached to can fail without warning for many reasons. Design all systems and equipment in a fail-safe mode, so failure of the QCD product or hose will not endanger persons or property.

1.3 Distribution: Provide a copy of this safety guide to each person responsible for selecting or using QCD products. Do not select or use QCD products without thoroughly reading and understanding this safety guide as well as the specific Parker publications for the products considered or selected.

1.4 User Responsibility: Due to the wide variety of operating conditions and uses for QCD products, Parker and its distributors do not represent or warrant any particular QCD

product suitable for any specific end use system. This safety guide does not analyze all technical parameters that must be considered in selecting a product. The user, through its own analysis and testing, is solely responsible for:

- Making the final selection of QCD products.
- Assuring the user's requirements are met and the use presents no health or safety hazards.
- Providing all appropriate health and safety warnings on the equipment on which the QCD products are used.

1.5 Additional Questions: Call the appropriate Parker customer service department if you have any questions or require any additional information. For the telephone numbers of the appropriate customer service department, see the Parker publication for the product being considered or used.

2.0 QCD Product Selection Instructions

2.1 Pressure: QCD product selection must be made so the published rated pressure is equal to or greater than the maximum system pressure. Surge pressures in the system higher than the rated pressure will shorten the QCD products' life. Do not confuse burst pressure or other pressure values with rated pressure and do not use burst pressure or other pressure values for this purpose.

2.2 Fluid Compatibility: QCD product selection must assure compatibility of the products' materials of construction with the fluid media being used.

2.3 Temperature: Be certain fluid and ambient temperatures, both steady and transient, do not exceed the limitations of the QCD product. Use caution and proper PPE when handling QCD products heated or cooled by the media they are conducting or by their environment.

2.4 Size: Transmission of power by means of pressurized liquid varies with pressure and flow. The size of the QCD product and other components of the system must be adequate pressure

Appendix

Safety Guide

losses to a minimum and avoid damage due to heat generation or excessive fluid velocity.

2.5 Pressurized Connect or Disconnect:

If connecting or disconnecting under pressure is a requirement, use only quick couplings designed for that purpose. The rated operating pressure of a quick action coupling may not be the pressure at which it may be safely connected or disconnected.

2.6 Environment: Care must be taken to ensure QCD products are either compatible with or protected from the environment (that is, surrounding conditions) to which they are exposed. Environmental conditions including but not limited to ultraviolet radiation, ozone, moisture, water, salt water, chemicals, and air pollutants can cause degradation and premature failure.

2.7 Locking Means: Ball locking quick couplings can unintentionally disconnect if they are dragged over obstructions on the end of a hose or if the sleeve is bumped or moved enough to cause disconnect. Sleeves designed with flanges to provide better ripping for oily or gloved hands are especially susceptible to accidental disconnect and should not be used where these conditions exist. Sleeve lock or union (threaded) sleeve designs should be considered where there is a potential for accidental disconnect.

2.8 Mechanical Loads: External forces can significantly reduce QCD product life or cause failure. Mechanical loads which must be considered include excessive tensile or side loads, and vibration. Unusual applications may require special testing prior to QCD product selection.

2.9 Specifications and Standards: When selecting QCD products, government, industry, and Parker specifications must be reviewed and followed where applicable.

2.10 Vacuum: Not all QCD products are suitable or recommended for vacuum service. QCD products used for vacuum

applications must be selected to ensure the product will withstand the vacuum and pressure of the system.

2.11 Fire Resistant Fluids: Some fire-resistant fluids require seals other than the standard nitrile used in many QCD products.

2.12 Radiant Heat: QCD product can be heated to destruction or loss of sealing integrity without contact by nearby items such as hot manifolds or molten metal. The same heat source may then initiate a fire. This can occur despite the presence of cool air around the QCD product.

2.13 Welding and Brazing: Heating of plated parts, including QCD products and port adapters, above 450°F (232°C) such as during welding, brazing, or soldering may emit deadly gases and may cause permanent product damage.

3.0 Quick Action Coupling Installation Instructions

3.1 Pre-Installation Inspection: Before installing a QCD product, visually inspect it and check for correct style, body material, seal material, and catalog number. Before final installation, coupling halves should be connected and disconnected with a sample of the mating half with which they will be used.

3.2 Quick Coupling Halves from Other Manufacturers: If a quick coupling assembly is made up of one Parker half and one half from another manufacturer, the lowest pressure rating of the two halves should not be exceeded.

3.3 Fitting Installation: Use a thread sealant, lubricant, or a combination of both when assembling pipe thread joints on QCD products. Be sure the sealant is compatible with the system fluid or gas. To avoid system contamination, use a liquid or paste type sealant rather than a tape style. Use the flats provided to hold QCD product when installing fittings. Do not use pipe wrenches or a vice on other parts of the product to hold it when installing or removing fittings as damage or loosening of threaded assembly joints

in the product could result. Do not apply excessive torque to taper pipe threads because cracking or splitting of the female component can result.

3.4 Caps and Plugs: Use dust caps and plugs when quick couplings are not coupled to exclude dirt and contamination and to protect critical surfaces from damage.

3.5 Quick Coupling Location: Locate quick couplings where they can be reached for connect or disconnect without exposing the operator to slipping, falling, getting sprayed, or coming in contact with hot or moving parts.

3.6 Hose Whips: Use a hose whip (a short length of hose between the tool and the coupling half) instead of rigidly mounting a coupling half on hand tools or other devices. This reduces the potential for coupling damage if the tool is dropped and provides some isolation from mechanical vibration which could cause unintended disconnection.

4.0 QCD Product Maintenance Instructions

4.1 Even with proper selection and installation, QCD product life may be significantly reduced without a maintenance program. Frequency should be determined by the severity of the application and risk potential. A maintenance program must be established and followed by the user and must include the following as a minimum:

4.2 Visual Inspection of QCD

Product: Any of the following conditions require immediate shut down and replacement of the QCD product:

- Cracked, damaged, or corroded product.
- Leaks at the fitting, valve or mating seal.
- Broken mounting hardware, especially breakaway clamps.

Appendix

Safety Guide

4.3 Visual Inspection Other: The following items must be tightened, repaired or replaced as required:

- Leaking seals or port connections.
- Excess dirt buildup on the quick coupling locking mechanism or on the interface area of either coupling half
- Clamps, guards, and shields.
- System fluid level, fluid type and any air entrapment.

4.4 Functional Test: Operate the system at maximum operating pressure and check for possible malfunctions and leaks. Personnel must avoid potentially hazardous areas while testing and using the system.

4.5 Replacement Intervals: Specific replacement intervals must be considered based on previous service life, government, or industry recommendations, or when failures could result in unacceptable downtime, damage, or injury risk. See instruction 1.2 above.

Additional copies of the preceding safety information can be ordered by requesting "Safety Guide for Selecting and Using QCD Product and Related Accessories," Parker Publication DS6013.

Contact Parker's Quick Coupling Division, Minneapolis, MN.

Appendix

Offer of Sale

1. Definitions. As used herein, the following terms have the meanings indicated.

Buyer: means any customer receiving a Quote for Products.

Goods: means any tangible part, system or component to be supplied by Seller.

Products: means the Goods, Services and/or Software as described in a Quote.

Quote: means the offer or proposal made by Seller to Buyer for the supply of Products.

Seller: means Parker-Hannifin Corporation, including all divisions and businesses thereof.

Services: means any services to be provided by Seller.

Software: means any software related to the Goods, whether embedded or separately downloaded.

Terms: means the terms and conditions of this Offer of Sale.

2. Terms. All sales of Products by Seller are expressly conditioned upon, and will be governed by the acceptance of, these Terms. These Terms are incorporated into any Quote provided by Seller to Buyer. Buyer's order for any Products whether communicated to Seller verbally, in writing, by electronic data interface or other electronic commerce, shall constitute acceptance of these Terms. Seller objects to any contrary or additional terms or conditions of Buyer. Reference in Seller's order acknowledgement to Buyer's purchase order or purchase order number shall in no way constitute an acceptance of any of Buyer's terms or conditions of purchase. No modification to these Terms will be binding on Seller unless agreed to in writing and signed by an authorized representative of Seller.

3. Price; Payment. The Products set forth in the Quote are offered for sale at the prices indicated in the Quote. Unless otherwise specifically stated in the Quote, prices are valid for thirty (30) days and do not include any sales, use, or other taxes or duties. Seller reserves the right to modify prices at any time to adjust for any raw material price fluctuations. Unless otherwise specified by Seller, all prices are F.C.A. Seller's facility (INCOTERMS 2020). All sales are contingent upon credit approval and full payment for all purchases is due thirty (30) days from the date of invoice (or such date as may be specified in the Quote). Unpaid invoices beyond the specified payment date incur interest at the rate of 1.5% per month or the maximum allowable rate under applicable law.

4. Shipment; Delivery; Title and Risk of Loss. All delivery dates are approximate, and Seller is not responsible for damages resulting from any delay. Regardless of the manner of shipment, delivery occurs and title and risk of loss or damage pass to Buyer, upon placement of the Products with the carrier at Seller's facility. Unless otherwise agreed prior to shipment and for domestic delivery locations only, Seller will select and arrange, at Buyer's sole expense, the carrier and means of delivery. When Seller selects and arranges the carrier and means of delivery, freight and insurance costs for shipment to the designated delivery location will be prepaid by Seller and added as a separate line item to the invoice. Buyer shall be responsible for any additional shipping charges incurred by Seller due to Buyer's acts or omissions. Buyer shall not return or repack any Products without the prior

written authorization from Seller, and any return shall be at the sole cost and expense of Buyer.

5. Warranty. The warranty for the Products is as follows: (i) Goods are warranted against defects in material or workmanship for a period of twelve (12) months from the date of delivery or 2,000 hours of use, whichever occurs first; (ii) Services shall be performed in accordance with generally accepted practices and using the degree of care and skill that is ordinarily exercised and customary in the field to which the Services pertain and are warranted for a period of six (6) months from the date of completion of the Services; and (iii) Software is only warranted to perform in accordance with applicable specifications provided by Seller to Buyer for ninety (90) days from the date of delivery or, when downloaded by a Buyer or end-user, from the date of the initial download. All prices are based upon the exclusive limited warranty stated above, and upon the following disclaimer: EXEMPTION CLAUSE; DISCLAIMER OF WARRANTY, CONDITIONS, REPRESENTATIONS: THIS WARRANTY IS THE SOLE AND ENTIRE WARRANTY, CONDITION, AND REPRESENTATION, PERTAINING TO PRODUCTS. SELLER DISCLAIMS ALL OTHER WARRANTIES, CONDITIONS, AND REPRESENTATIONS, WHETHER STATUTORY, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THOSE RELATING TO DESIGN, NONINFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE. SELLER DOES NOT WARRANT THAT THE SOFTWARE IS ERROR-FREE OR FAULT-TOLERANT, OR THAT BUYER'S USE THEREOF WILL BE SECURE OR UNINTERRUPTED. UNLESS OTHERWISE AUTHORIZED IN WRITING BY SELLER, THE SOFTWARE SHALL NOT BE USED IN CONNECTION WITH HAZARDOUS OR HIGH RISK ACTIVITIES OR ENVIRONMENTS. EXCEPT AS EXPRESSLY STATED HEREIN, ALL PRODUCTS ARE PROVIDED "AS IS".

6. Claims; Commencement of Actions. Buyer shall promptly inspect all Products upon receipt. No claims for shortages will be allowed unless reported to Seller within ten (10) days of delivery. Buyer shall notify Seller of any alleged breach of warranty within thirty (30) days after the date the non-conformance is or should have been discovered by Buyer. Any claim or action against Seller based upon breach of contract or any other theory, including tort, negligence, or otherwise must be commenced within twelve (12) months from the date of the alleged breach or other alleged event, without regard to the date of discovery.

7. LIMITATION OF LIABILITY. IN THE EVENT OF A BREACH OF WARRANTY, SELLER WILL, AT ITS OPTION, REPAIR OR REPLACE THE NON-CONFORMING PRODUCT, RE-PERFORM THE SERVICES, OR REFUND THE PURCHASE PRICE PAID WITHIN A REASONABLE PERIOD OF TIME. IN NO EVENT IS SELLER LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES INCLUDING ANY LOSS OF REVENUE OR PROFITS, WHETHER BASED IN CONTRACT, TORT OR OTHER LEGAL THEORY. IN NO EVENT SHALL SELLER'S LIABILITY UNDER ANY CLAIM MADE BY BUYER EXCEED THE PURCHASE PRICE PAID FOR THE PRODUCTS.

8. Confidential Information. Buyer acknowledges and agrees that any technical, commercial, or other confidential information of Seller, including, without limitation, pricing, technical drawings or

prints and/or part lists, which has been or will be disclosed, delivered or made available, whether directly or indirectly, to Buyer ("Confidential Information"), has been and will be received in confidence and will remain the property of Seller. Buyer further agrees that it will not use Seller's Confidential Information for any purpose other than for the benefit of Seller.

9. Loss to Buyer's Property. Any tools, patterns, materials, equipment or information furnished by Buyer or which are or become Buyer's property ("Buyer's Property"), will be considered obsolete and may be destroyed by Seller after two (2) consecutive years have elapsed without Buyer ordering the Products manufactured using Buyer's Property. Furthermore, Seller shall not be responsible for any loss or damage to Buyer's Property while it is in Seller's possession or control.

10. Special Tooling. "Special Tooling" includes but is not limited to tools, jigs, fixtures and associated manufacturing equipment acquired or necessary to manufacture Goods. Seller may impose a tooling charge for any Special Tooling. Such Special Tooling shall be and remain Seller's property notwithstanding payment of any charges by Buyer. In no event will Buyer acquire any interest in the Special Tooling, even if such Special Tooling has been specially converted or adapted for manufacture of Goods for Buyer and notwithstanding any charges paid by Buyer. Unless otherwise agreed, Seller has the right to alter, discard or otherwise dispose of any Special Tooling or other property owned by Seller in its sole discretion at any time.

11. Security Interest. To secure payment of all sums due from Buyer, Seller retains a security interest in all Products delivered to Buyer and, Buyer's acceptance of these Terms is deemed to be a Security Agreement under the Uniform Commercial Code. Buyer authorizes Seller as its attorney to execute and file on Buyer's behalf all documents Seller deems necessary to perfect Seller's security interest.

12. User Responsibility. Buyer, through its own analysis and testing, is solely responsible for making the final selection of the Products and assuring that all performance, endurance, maintenance, safety and warning requirements of the application of the Products are met. Buyer must analyze all aspects of the application and follow applicable industry standards, specifications, and any technical information provided with the Quote or the Products, such as Seller's instructions, guides and specifications. If Seller provides options of or for Products based upon data or specifications provided by Buyer, Buyer is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the Products. In the event Buyer is not the end-user of the Products, Buyer will ensure such end-user complies with this paragraph.

13. Use of Products, Indemnity by Buyer. Buyer shall comply with all instructions, guides and specifications provided by Seller with the Quote or the Products. Unauthorized Uses. If Buyer uses or resells the Products in any way prohibited by Seller's instructions, guides or specifications, or Buyer otherwise fails to comply with Seller's instructions, guides and specifications, Buyer acknowledges that any such use, resale, or non-compliance

Appendix

Offer of Sale

is at Buyer's sole risk. Further, Buyer shall indemnify, defend, and hold Seller harmless from any losses, claims, liabilities, damages, lawsuits, judgments and costs (including attorney fees and defense costs), whether for personal injury, property damage, intellectual property infringement or any other claim, arising out of or in connection with: (a) improper selection, design, specification, application, or any misuse of Products; (b) any act or omission, negligent or otherwise, of Buyer; (c) Seller's use of patterns, tools, equipment, plans, drawings, designs, specifications or other information or things furnished by Buyer; (d) damage to the Products from an external cause, repair or attempted repair by anyone other than Seller, failure to follow instructions, guides and specifications provided by Seller, use with goods not provided by Seller, or opening, modifying, deconstructing, tampering with or repackaging the Products; or (e) Buyer's failure to comply with these Terms. Seller shall not indemnify Buyer under any circumstance except as otherwise provided in these Terms.

14. Cancellations and Changes. Buyer may not cancel or modify, including but not limited to movement of delivery dates for the Products, any order for any reason except with Seller's written consent and upon terms that will indemnify, defend and hold Seller harmless against all direct, incidental and consequential loss or damage and any additional expense. Seller, at any time, may change features, specifications, designs and availability of Products.

15. Limitation on Assignment. Buyer may not assign its rights or obligations without the prior written consent of Seller.

16. Force Majeure. Seller is not liable for delay or failure to perform any of its obligations by reason of events or circumstances beyond its reasonable control. Such circumstances include without limitation: accidents, labor disputes or stoppages, government acts or orders, acts of nature, pandemics, epidemics, other widespread illness, or public health emergency, delays or failures in delivery from carriers or suppliers, shortages of materials, war (whether declared or not) or the serious threat of same, riots, rebellions, acts of terrorism, fire or any reason whether similar to the foregoing or otherwise. Seller will resume performance as soon as practicable after the event of force majeure has been removed. All delivery dates affected by force majeure shall be tolled for the duration of such force majeure and rescheduled for mutually agreed dates as soon as practicable after the force majeure condition ceases to exist. Force majeure shall not include financial distress, insolvency, bankruptcy, or other similar conditions affecting one of the parties, affiliates and/or sub-contractors.

17. Waiver and Severability. Failure to enforce any provision of these Terms will not invalidate that provision; nor will any such failure prejudice either party's right to enforce that provision in the future. Invalidation of any provision of these Terms shall not invalidate any other provision herein and, the remaining provisions will remain in full force and effect.

18. Termination. Seller may terminate any agreement governed by or arising from these Terms for any reason and at any time by giving Buyer thirty (30) days prior written notice. Seller may immediately terminate, in writing, if Buyer: (a) breaches any provision of these Terms, (b) becomes

or is deemed insolvent, (c) appoints or has appointed a trustee, receiver or custodian for all or any part of Buyer's property, (d) files a petition for relief in bankruptcy on its own behalf, or one is filed against Buyer by a third party, (e) makes an assignment for the benefit of creditors; or (f) dissolves its business or liquidates all or a majority of its assets.

19. Ownership of Software. Seller retains ownership of all Software supplied to Buyer hereunder. In no event shall Buyer obtain any greater right in and to the Software than a right in the nature of a license limited to the use thereof and subject to compliance with any other terms provided with the Software.

20. Indemnity for Infringement of Intellectual Property Rights. Seller is not liable for infringement of any patents, trademarks, copyrights, trade dress, trade secrets or similar rights ("Intellectual Property Rights") except as provided in this Section. Seller will defend at its expense and will pay the cost of any settlement or damages awarded in an action brought against Buyer based on a third party claim that one or more of the Products sold hereunder infringes the Intellectual Property Rights of a third party in the country of delivery of the Products by Seller to Buyer. Seller's obligation to defend and indemnify Buyer is contingent on Buyer notifying Seller within ten (10) days after Buyer becomes aware of any such claim, and Seller having sole control over the defense of the claim including all negotiations for settlement or compromise. If one or more Products sold hereunder is subject to such a claim, Seller may, at its sole expense and option, procure for Buyer the right to continue using the Products, replace or modify the Products so as to render them non-infringing, or offer to accept return of the Products and refund the purchase price less a reasonable allowance for depreciation. Seller has no obligation or liability for any claim of infringement: (i) arising from information provided by Buyer; or (ii) directed to any Products provided hereunder for which the designs are specified in whole or part by Buyer; or (iii) resulting from the modification, combination or use in a system of any Products provided hereunder. The foregoing provisions of this Section constitute Seller's sole and exclusive liability and Buyer's sole and exclusive remedy for claims of infringement of Intellectual Property Rights.

21. Governing Law. These Terms and the sale and delivery of all Products are deemed to have taken place in, and shall be governed and construed in accordance with, the laws of the State of Ohio, as applicable to contracts executed and wholly performed therein and without regard to conflicts of laws principles. Buyer irrevocably agrees and consents to the exclusive jurisdiction and venue of the courts of Cuyahoga County, Ohio with respect to any dispute, controversy or claim arising out of or relating to the sale and delivery of the Products.

22. Entire Agreement. These Terms, along with the terms set forth in the main body of any Quote, forms the entire agreement between the Buyer and Seller and constitutes the final, complete and exclusive expression of the terms of sale and purchase. In the event of a conflict between any term set forth in the main body of a Quote and these Terms, the terms set forth in the main body of the Quote shall prevail. All prior or contemporaneous written or oral agreements or negotiations with respect to the subject matter shall have no effect. These Terms may not be modified unless in writing and signed by an authorized representative of Seller.


23. Compliance with Laws. Buyer agrees to comply with all applicable laws, regulations, and industry and professional standards, including

those of the United States of America, and the country or countries in which Buyer may operate, including without limitation the U.S. Foreign Corrupt Practices Act ("FCPA"), the U.S. Anti-Kickback Act ("Anti-Kickback Act"), U.S. and E.U. export control and sanctions laws ("Export Laws"), the U.S. Food Drug and Cosmetic Act ("FDCA"), and the rules and regulations promulgated by the U.S. Food and Drug Administration ("FDA"), each as currently amended. Buyer agrees to indemnify, defend, and hold harmless Seller from the consequences of any violation of such laws, regulations and standards by Buyer, its employees or agents. Buyer acknowledges that it is familiar with all applicable provisions of the FCPA, the Anti-Kickback Act, Export Laws, the FDCA and the FDA and certifies that Buyer will adhere to the requirements thereof and not take any action that would make Seller violate such requirements. Buyer represents and agrees that Buyer will not make any payment or give anything of value, directly or indirectly, to any governmental official, foreign political party or official thereof, candidate for foreign political office, or commercial entity or person, for any improper purpose, including the purpose of influencing such person to purchase Products or otherwise benefit the business of Seller. Buyer further represents and agrees that it will not receive, use, service, transfer or ship any Products from Seller in a manner or for a purpose that violates Export Laws or would cause Seller to be in violation of Export Laws. Buyer agrees to promptly and reliably provide Seller all requested information or documents, including end-user statements and other written assurances, concerning Buyer's ongoing compliance with Export Laws.

8/2020

Appendix

Glossary of Terms



Air Inclusion: The ambient atmosphere forced into the system during the connection of the quick disconnect halves.

Break-Away: Automatic disconnection of a coupling when an axial separation force is applied.

Brinelling: Dimples or grooves worn into the shoulder of a male half by the locking balls in the female half.

Burst Pressure: The pressure at which a device loses the capability to retain pressure.

Case Hardening: Hardening the surface of low carbon steel.

Cold Flow: Continued deformation under load.

Connect Under Pressure: Ability to connect coupling halves with internal line pressure applied to either both sides or one side.

Coupling, Female Half: Other nomenclature "coupler", "socket", "body".

Coupling, Male Half: Other nomenclature "nipple", "plug", "adapter".

Coupling, Quick Disconnect: A component which can quickly join or separate a fluid line without the use of tools or special devices.

Differential Pressure (ΔP): The difference in pressure between any two points of a system or a component.

Double-Acting Sleeve: Permits push-to-connect and pull-to-disconnect convenience on implement line when female half is clamp mounted and connected with a hose.

Dust Cap: Dust or dirt repelling enclosure for both halves.

Dust Plug: Dust or dirt repelling enclosure both halves.

Flow Checking: Occurs when a nipple valve closes during flow conditions, such as when quickly lowering a heavy implement. (Also called Check Off, Back Checking or Lock-up.)

Flush Position (Valve): When the coupler valve is fully open, allowing maximum oil flow.

Force to Connect: Axial and/or rotational force required to make a complete connection.

Force to Disconnect: The reverse of the above.

Induction Hardening: Localized hardening of medium carbon steel.

Peak Pressure: Maximum momentary pressure encountered in the operation of a component.

Pressure Cap: Cap which incorporates a seal capable of withstanding the rated pressures on the male half.

Pressure Impulse Test: Subjecting a component to a specified pressure at a specified rate of increase or decrease for a specified time limit.

Pressure Operating: The pressure at which a system is operated.

Pressure Plug: Plug which incorporates a seal capable of withstanding the rated pressures on the female half.

Proof Pressure: The non-destructive test pressure in excess of the maximum rated operating pressure.

Push To Connect (Auto Lock): Locking arrangement which permits one handed connection by pushing the nipple into the coupler.

Rated Pressure: The maximum pressure at which a product is designed to operate.

Single-Acting Sleeve: Permits pull-to-disconnect convenience on implement line when female body is clamp mounted. Making connection requires manually pulling female body forward, inserting male tip, then allowing body and tip to return to original position in the clamp.

Sleeve Lock: Arrangement which provides an additional lock which must be actuated before the locking sleeve can be retracted.

Spillage: The fluid removed from the system due to disconnection of a coupling assembly. This is the fluid trapped between the mating seal and the valve seal of the coupling halves.

Surge Pressure: The pressure existing from surge conditions.

Surge Flows: A rapid increase in fluid flow.

Thermal Build-Up: Hydraulic pressure caused by expansion of the fluid due to heat from an external source such as sunlight.

Trapped Pressure: Pressurized hydraulic fluid trapped behind closed coupling valve.

Twist Lock: A locking arrangement which requires a rotational actuation to unlock the mating halves.

Types of Quick Disconnect Coupling Valve:

Straight-Thru (ST): This provides straight through flow.

Double Shut-off Valve (DSO): A valve in the female half and a valve in the male half.

Single Shut-off Valve (SSO): Generally, a valve in the female half with no valve in the male half.

NOTE: Refer to Parker's Publication No. 3800-B1.0: Safety Guide for Selecting and Using Quick Action Couplings and Related Accessories.



About Parker Hannifin Corporation

Parker Hannifin is a Fortune 250 global leader in motion and control technologies. For more than 100 years the company has engineered the success of its customers in a wide range of diversified industrial and aerospace markets. Parker's engineering expertise and broad range of core technologies uniquely positions the company to help solve the world's greatest engineering challenges.

Parker's Charter

To be a leading worldwide manufacturer of components and systems for the builders and users of durable goods. More specifically, we will design, market and manufacture products controlling motion, flow and pressure. We will achieve profitable growth through premier customer service.

Product Information

North American customers seeking product information, the location of a nearby distributor, or repair services will receive prompt attention by calling the Parker Product Information Center at our toll-free number: 1-800-C-PARKER (1-800-272-7537).

In Europe, call: 00800-C-PARKER-H (00800-2727-5374).



Parker Aerospace is a global leader in flight control actuation, hydraulic, fuel, inerting, fluid conveyance, pneumatic and lubrication systems and components used on virtually every commercial and military aerospace platform in production today, from commercial transports, helicopters, and business and general aviation, to military fixed-wing planes and unmanned aerial vehicles.



The Fluid Connectors & Instrumentation Group, the leader in "dry technology" for the fluid power industry, is your single source for high-quality tube fittings, hose and hose fittings, thermoplastic tubing, brass fittings and valves, quick-disconnect couplings and assembly tools. Products are available for shipment 24 hours a day, supported by 49 manufacturing facilities throughout the world, a global distribution network and 25 company-owned stocking service centers.



Parker's Motion Systems Group provides three technologies that create and control motion to customers across major mobile and industrial markets.

Hydraulics: the use of pressurized fluid

Pneumatics: the use of pressurized air

Electromechanical: the use of electricity

Parker's best-in-class components and system solutions are known for their durability, reliability, power density, low noise, efficiency and ease of use. This competitive advantage improves productivity and throughput while reducing energy and fuel consumption for customers worldwide.



The Engineered Materials Group develops and manufactures engineered solutions. Our products play an important role in the safe and reliable operation of critical equipment in hospitals, laboratories, and in everything from semiconductor processing fabs to airplanes and heavy-duty trucks. Additionally, our precision plastic and elastomeric components are used in a variety of medical devices and healthcare equipment. Our shielding and grounding products protect critical electronics from the harmful effects of electromagnetic interference (EMI). In addition, our thermally conductive fillers, gels and interface materials cool hot microprocessors and power supplies. Parker's broad range of adhesives deliver structural integrity and resistance to environmental extremes. Finally, our vibration isolation and advanced sensing technologies provide risk mitigation while delivering superior comfort and performance.



The Instrumentation Group is dedicated to being the global leader in the design, manufacture and distribution of high quality, critical flow and ultra high purity components for the petrochemical, chemical processing, oil and gas, power generation, water analysis, biopharmaceutical, semiconductor, and analytical equipment industries.



Parker Fluid Connectors Group North American Divisions & Distribution Service Centers

Your complete source for quality tube fittings, hose & hose fittings, brass & composite fittings, quick-disconnect couplings, valves and assembly tools, locally available from a worldwide network of authorized distributors.

Fittings:

Available in inch and metric sizes covering SAE, BSP, DIN, GAZ, JIS and ISO thread configurations, manufactured from steel, stainless steel, brass, aluminum, nylon and thermoplastic.

Hose, Tubing and Bundles:

Available in a wide variety of sizes and materials including rubber, wire-reinforced, thermoplastic, hybrid and custom compounds.

Worldwide Availability:

Parker operates Fluid Connectors manufacturing locations and sales offices throughout North America, South America, Europe and Asia-Pacific.

North American Divisions

Fluid System Connectors Division Otsego, MI

phone 269 694 9411
fax 269 694 4614

Hose Products Division Wickliffe, OH

phone 440 943 5700
fax 440 943 3129

Parflex Division Ravenna, OH

phone 330 296 2871
fax 330 296 8433

Quick Coupling Division Minneapolis, MN

phone 763 544 7781
fax 763 544 3418

Tube Fittings Division Columbus, OH

phone 614 279 7070
fax 614 279 7685

Distribution Service Centers

Buena Park, CA

phone 714 522 8840
fax 714 994 1183

Louisville, KY

phone 502 937 1322
fax 502 937 4180

Toledo, OH

phone 419 878 7000
fax 419 878 7001
fax 419 878 7420
(FCG Kit Operations)

Canada

Milton, ONT

phone 905 693 3000
fax 905 876 1958

Mexico

Toluca, MEX

phone (52) 722 2754 200
fax (52) 722 2722 168

For information, call toll free 1-800-C-PARKER | (1-800-272-7537)