



Par-Fit™ Conversion Elements

Bulletin 1300 - 500-1/USA



Finite®

The **Finite**[®] Advantage...

High filtration efficiency, low operating costs, long life, high quality, and the convenience of purchasing your products from a single supplier are the **Finite[®] advantages.**

Each **Finite**[®] coalescing filter element offers our unique UNI-CAST design created from a carefully controlled vacuum process. This design was developed and patented by **Finite**[®] to optimize filter performance and results in a filter element with lower differential pressure and a higher dirt loading capacity. This means lower operating

costs and longer life. Because we have complete control over the manufacture of our products, we also have control over our product's quality and performance.

This means reliable and consistent filtration performance for your applications.

Finite[®]'s filtration efficiency standards are among the highest in the industry. We have been careful to supply you a product that always meets and in most cases exceeds the filtration performance and

flow rate capacity of the original element. We verify these standards in our quality control laboratory. You are assured of getting a filter element with industry leading filtration quality.

Finite[®] is one of the pioneers in coalescing filtration. We are dedicated to the science of this filtration technique.

By purchasing a **Finite**[®] product you will have access to our many years of coalescing experience and research. With the breadth of our product line, including complete

filter housings, most of your needs will be met with a single source, high quality, reliable supplier.

Call your **Finite**[®] distributor now for your filtration needs. Or, your questions can be answered by calling 1-(800)-521-4357. Ask for Applications Engineering. **Finite**[®]'s benefits are available to you, now!

"You can have all of the benefits inherent in a **Finite**[®] filter element without the need to replace your existing filter housing."

Table of Contents

Manufacturer	Page
Arrow	3
Balston	3-4
Binks	4
Busch	4
Cuno (AMF Cuno)	4
Domnick Hunter	5-6
Filterite	6-7
Filtersoft	7-11
Flair	11-13
Hankison	13-14
Headline	14-15
Henderson	15
Johnson Controls	15
Norgen	15
Numatics	15
Pall Corporation/PPC	15-17
Pioneer	17
Pure Air	17
Steris	18
Sullair	18
Ultra Air	18
Ultrafilter	18-19
Van Air	20
Watts	20
Wilkerson	20-21
Zander	21
Zeks	22
Zurn	22
Alpha/Numeric part list	23-40

General Notes:

1. To make a proper conversion, locate the original manufacturer's element number, determine the element type (coalescer, particulate or adsorber), then identify the **Finite**[®] equivalent from the proper manufacturer's list.

2. The grades and types of **Finite**[®] elements recommended are based on the actual performance specifications of the housings to be converted.

3. Number after "X" in "**Finite**[®] Element Part Number" indicates number of elements sold per Box. Elements are sold in Box quantity only.

4. Conversion kits consist of a group of parts, such as center rods and end caps, that adapt other manufacturer's housings to accept a **Finite**[®] conversion element.

5. Conversion kits are required for initial conversion only.

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Arrow			
Oil Removal			
Arrow	EKF401	10RU07-018 X 8	
Arrow	EKF402	10RU10-021 X 8	
Arrow	EKF405	10RA20-040 X 4	
Arrow	EKF407	10RA20-071 X 2	
Arrow	EKF408	10RA20-080 X 2	
Arrow	EKF410	10RU25-101 X 2	
Arrow	EKF418	10RU25-181 X 1	
Arrow	EKF428	10RU25-281 X 1	
Arrow	EKF4N2	10RU25-281 X 1	
Arrow	EKF4 X 2	10RU25-281 X 1	
Arrow	EKF4 X 3	10RU25-281 X 1	
Arrow	EKF4 X 4	10RU25-281 X 1	
Arrow	EKF4 X 5	10RU25-281 X 1	
Arrow	EKF4 X 6	10RU25-281 X 1	
Arrow	EKF4 X 8	10RU25-281 X 1	
Coalescer			
Arrow	EKF501	6CU07-018 X 8	
Arrow	EKF502	6CU10-022 X 8	
Arrow	EKF505	6IA20-040 X 4	
Arrow	EKF507	6IA20-071 X 2	
Arrow	EKF508	6IA20-080 X 2	
Arrow	EKF510	6IU25-101 X 2	
Arrow	EKF518	6IU25-181 X 1	
Arrow	EKF528	6IU25-281 X 1	
Arrow	EKF529	6CA29-280 X 1	
Arrow	EKF5N2	6IU25-281 X 1	
Arrow	EKF5 X 2	6IU25-281 X 1	
Arrow	EKF5 X 3	6IU25-281 X 1	
Arrow	EKF5 X 4	6IU25-281 X 1	
Arrow	EKF5 X 5	6IU25-281 X 1	
Arrow	EKF5 X 6	6IU25-281 X 1	
Arrow	EKF5 X 8	6IU25-281 X 1	
Fine Coalescer Grade A			
Arrow	EKF501A	2CU07-018 X 8	
Arrow	EKF502A	2CU10-022 X 8	
Arrow	EKF505A	2IA20-040 X 4	
Arrow	EKF507A	2IA20-071 X 2	
Arrow	EKF508A	2IA20-080 X 2	
Arrow	EKF510A	2IU25-101 X 2	
Arrow	EKF518A	2IU25-181 X 1	
Arrow	EKF528A	2IU25-281 X 1	
Arrow	EKF529A	2CA29-280 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Arrow	EKF5N2A	2IU25-281 X 1	
Arrow	EKF5 X 2A	2IU25-281 X 1	
Arrow	EKF5 X 3A	2IU25-281 X 1	
Arrow	EKF5 X 4A	2IU25-281 X 1	
Arrow	EKF5 X 5A	2IU25-281 X 1	
Arrow	EKF5 X 6A	2IU25-281 X 1	
Arrow	EKF5 X 8A	2IU25-281 X 1	
Vapor Adsorber			
Arrow	EKF601	AU07-018 X 8	
Arrow	EKF602	AU10-022 X 8	
Arrow	EKF605	AA20-040 X 4	
Arrow	EKF607	AA20-071 X 2	
Arrow	EKF608	AA20-080 X 2	
Arrow	EKF610	AU25-101 X 2	
Arrow	EKF618	AU25-181 X 1	
Arrow	EKF628	AU25-281 X 1	
Arrow	EKF629	AA29-280 X 1	
Arrow	EKF6N2	AU25-281 X 1	
Arrow	EKF6 X 2	AU25-281 X 1	
Arrow	EKF6 X 3	AU25-281 X 1	
Arrow	EKF6 X 4	AU25-281 X 1	
Arrow	EKF6 X 5	AU25-281 X 1	
Arrow	EKF6 X 6	AU25-281 X 1	
Arrow	EKF6 X 8	AU25-281 X 1	
Balston			
Coalescers			
Balston	050-03-BX	6H04-010 X 10	
Balston	050-05-BX	6H04-013 X 10	
Balston	050-11-BX	6H04-023 X 10	
Balston	100-09-BX	6H10-020 X 8	
Balston	100-12-BX	6H10-025 X 8	
Balston	100-18-BX	6H10-050 X 4	
Balston	100-25-BX	6H10-070 X 4	
Balston	150-19-BX	6H15-060 X 4	
Balston	200-16-BX	6H20-035 X 4	
Balston	200-35-BX	6H20-090 X 2	
Balston	200-80-BX	6H20-187 X 1	
Balston	050-03-CX	8H04-010 X 10	
Balston	050-05-CX	8H04-013 X 10	
Balston	050-11-CX	8H04-023 X 10	
Balston	100-09-CX	8H10-020 X 8	
Balston	100-12-CX	8H10-025 X 8	
Balston	100-18-CX	8H10-050 X 4	
Balston	100-25-CX	8H10-070 X 4	
Balston	150-19-CX	8H15-060 X 4	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Balston	200-16-CX	8H20-035 X 4	
Balston	200-35-CX	8H20-090 X 2	
Balston	200-80-CX	8H20-187 X 1	
Balston	050-03-DX	10H04-010 X 10	
Balston	050-05-DX	10H04-013 X 10	
Balston	050-11-DX	10H04-023 X 10	
Balston	100-09-DX	10H10-020 X 8	
Balston	100-12-DX	10H10-025 X 8	
Balston	100-18-DX	10H10-050 X 4	
Balston	100-25-DX	10H10-070 X 4	
Balston	150-19-DX	10H15-060 X 4	
Balston	200-16-DX	10H20-035 X 4	
Balston	200-35-DX	10H20-090 X 2	
Balston	200-80-DX	10H20-187 X 1	

Particulate Diesel Emission Test Filters

Balston	050-11-DH	10T04-023 X 10	
Balston	100-12-DH	10T10-025 X 10	
Balston	100-25-DH	10T10-070 X 10	
Balston	050-11-BH	6T04-023 X 10	
Balston	100-12-BH	6T10-025 X 10	
Balston	100-25-BH	6T10-070 X 10	
Balston	200-35-BH	6T20-090 X 10	

Note: 'T' Tubes are baked at 900°F to eliminate all hydrocarbons.

Particulate

Balston	050-03*	*G04-010 X 10	
Balston	050-05-*	*G04-013 X 10	
Balston	050-11-*	*G04-023 X 10	
Balston	100-12-*	*G10-025 X 10	
Balston	100-25-*	*G10-070 X 10	
Balston	150-19-*	*G15-060 X 10	
Balston	200-35-*	*G20-090 X 10	
Balston	200-80-*	*G20-187 X 10	
Balston	050-03*Q	*T04-010 X 10	
Balston	050-05-*Q	*T04-013 X 10	
Balston	050-11-*Q	*T04-023 X 10	
Balston	100-12-*Q	*T10-025 X 10	
Balston	100-25-*Q	*T10-070 X 10	
Balston	150-19-*Q	*T15-060 X 10	
Balston	200-35-*Q	*T20-090 X 10	
Balston	200-80-*Q	*T20-187 X 10	

Disposable Inline Filter Housings

Balston	9933-05-BQ	IDN-6G X 10	
Balston	9933-05-DQ	IDN-10G X 10	
Balston	9900-05-BK	SDN-O X 10	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
------------	------------------------	---------------------	--------------

*Pore Structure Conversion Chart

Use this chart to determine the Finite® equivalent to the specified Balston grade.

Balston	AA	A	371H or B	C	D	E
Finite®	2	4	6	8	10	12

Notes: 'G' type elements are for general air and gas applications to 350°F.

'T' type elements are suitable for use with air or gases containing most organic fluids and for temperatures to 450°F.

Binks

Binks	86-972	6HU20-070 X 2	
Binks	86-982	6HU10-050 X 4	

Busch

Busch	532-221	8CF20-051 X 2	
Busch	532-302 (532.509.501)	8CF20-099 X 2	
Busch	532-303 (532.082.01)	8CF20-147 X 1	
Busch	532-304 (532.507.01)	8CF20-197 X 1	

Cuno (AMF Cuno)

Reverse Flow Coalescer

Cuno	9-3/4" (78 Series)	6CP15-098 X 2	
Cuno	10" (80 Series)	6CP15-100 X 2	
Cuno	3-3/4" (30 Series)	6CP15-038 X 4	

3um Nominal Particulate

Cuno	G78A3 (9-3/4")	3PP15-098 X 2	
Cuno	G78B2 (9-3/4")	3PP15-098 X 2	
Cuno	G80A3 (10")	3PP15-100 X 2	
Cuno	G80B2 (10")	3PP15-100 X 2	
Cuno	U78A3 (9-3/4")	3PP15-098 X 2	
Cuno	U78B2 (9-3/4")	3PP15-098 X 2	
Cuno	U80A3 (10")	3PP15-100 X 2	
Cuno	U80B2 (10")	3PP15-100 X 2	

Note: Do not use '3P' elements on liquid applications. '3P' grade is 3 micron absolute and has 20 times the surface area of the original element.

Activated Carbon

Cuno	9-3/4" (78 Series)	AP15-098 X 2	
Cuno	10" (80 Series)	AP15-100 X 2	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
------------	------------------------	---------------------	--------------

Domnick Hunter

High Efficiency Coalescing Filters

Domnick Hunter	A002/05	6HJN08-024 X 1	
Domnick Hunter	A003/05	6HJN08-030 X 1	
Domnick Hunter	A003/10	6CJN10-030 X 1	
Domnick Hunter	A004/10	6CJN10-040 X 1	
Domnick Hunter	A004/20	6CJN13-040 X 1	
Domnick Hunter	A005/20	6CJN13-050 X 1	
Domnick Hunter	A005/25	6IJN15-050 X 1	
Domnick Hunter	A007/25	6IJN15-070 X 1	
Domnick Hunter	A007/30	6IJN25-070 X 1	
Domnick Hunter	A010/3	6IJ25-100 X 1	
Domnick Hunter	A010/30	6IJN25-100 X 1	
Domnick Hunter	A015/3	6IG25-150 X 1	
Domnick Hunter	A015/30	6IGN25-150 X 1	
Domnick Hunter	A020/3	6IG25-200 X 1	
Domnick Hunter	A020/30	6IGN25-200 X 1	
Domnick Hunter	A03/1	6CJ10-030 X 1	
Domnick Hunter	A03/1.5	6CJ13-030 X 1	
Domnick Hunter	A030/3	6IG25-300 X 1	
Domnick Hunter	A030/30	6IGN25-300 X 1	
Domnick Hunter	A030/5	6QG43-300 X 1	
Domnick Hunter	A030/50	6QGN43-300 X 1	
Domnick Hunter	A04/1.5	6CJ13-044 X 1	
Domnick Hunter	A04/2.5	6IJ15-040 X 1	
Domnick Hunter	A05/2.5	6IJN15-050 X 1	
Domnick Hunter	A05/3	6IJ25-050 X 1	
Domnick Hunter	AA02/05	4HJN08-024 X 1	
Domnick Hunter	AA03/05	4HJN08-030 X 1	
Domnick Hunter	AA03/10	4CJN10-030 X 1	
Domnick Hunter	AA04/10	4CJN10-040 X 1	
Domnick Hunter	AA04/20	4CJN13-040 X 1	
Domnick Hunter	AA05/20	4CJN13-050 X 1	
Domnick Hunter	AA05/25	4IJN15-050 X 1	
Domnick Hunter	AA07/25	4IJN15-070 X 1	
Domnick Hunter	AA07/30	4IJN25-070 X 1	
Domnick Hunter	AA10/3	6IJ25-100 X 1	
Domnick Hunter	AA10/30	4IJN25-100 X 1	
Domnick Hunter	AA15/3	6IG25-150 X 1	
Domnick Hunter	AA15/30	4IGN25-150 X 1	
Domnick Hunter	AA20/3	6IG25-200 X 1	
Domnick Hunter	AA20/30	4IGN25-200 X 1	
Domnick Hunter	AA3/1	6CJ10-030 X 1	
Domnick Hunter	AA3/1.5	6CJ13-030 X 1	
Domnick Hunter	AA30/3	6IG25-300 X 1	
Domnick Hunter	AA30/30	4IGN25-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
------------	------------------------	---------------------	--------------

Domnick Hunter	AA30/5	6QG43-300 X 1	
Domnick Hunter	AA30/50	4QGN43-300 X 1	
Domnick Hunter	AA4/1.5	6CJ13-044 X 1	
Domnick Hunter	AA4/2.5	6IJ15-040 X 1	
Domnick Hunter	AA5/2.5	6IJN15-050 X 1	
Domnick Hunter	AA5/3	6IJ25-050 X 1	
Domnick Hunter	E006AA	6CF08-026 X 1	
Domnick Hunter	E013AA	6IF10-032 X 1	
Domnick Hunter	E025AA	6IF10-046 X 1	
Domnick Hunter	E040AA	6IF20-063 X 1	
Domnick Hunter	E085AA	6IF20-102 X 1	
Domnick Hunter	E195AA	6IF25-134 X 1	
Domnick Hunter	E295AA	6IF25-254 X 1	
Domnick Hunter	E400AA	6CF35-165 X 1	
Domnick Hunter	E500AA	6CF43-252 X 1	
Domnick Hunter	E620AA	6CF35-251 X 1	
Domnick Hunter	EP1001AO	6QP19-098 X 2	
Domnick Hunter	EZ1030AA	6CZ07-020 X 1	
Domnick Hunter	EZ1050AA	6CZ12-023 X 1	
Domnick Hunter	EZ1070AA	6CZ12-029 X 1	
Domnick Hunter	EZ1140AA	6CZ12-056 X 1	
Domnick Hunter	EZ2010AA	6CZ20-046 X 1	
Domnick Hunter	EZ2020AA	6CZ20-086 X 1	
Domnick Hunter	EZ2030AA	6CZ20-126 X 1	
Domnick Hunter	EZ2050AA	6CZ20-200 X 1	
Domnick Hunter	EZ3050AA	6CZ27-200 X 1	
Domnick Hunter	EZ3075AA	6CZ27-298 X 1	
Domnick Hunter	EZ5060AA	6CZ46-239 X 1	
Domnick Hunter	EZ5075AA	6CZ50-298 X 1	
Domnick Hunter	K145AA	6IF20-102 X 1	
Domnick Hunter	K220AA	6IF25-134 X 1	
Domnick Hunter	K330AA	6IF25-254 X 1	
Domnick Hunter	K430AA	6CF35-165 X 1	

General Purpose Filters

Domnick Hunter	E006AO	10CF08-026 X 1	
Domnick Hunter	E013AO	10IF10-032 X 1	
Domnick Hunter	E025AO	10IF10-046 X 1	
Domnick Hunter	E040AO	10IF20-063 X 1	
Domnick Hunter	E085AO	10IF20-102 X 1	
Domnick Hunter	E195AO	10IF25-134 X 1	
Domnick Hunter	E295AO	10IF25-254 X 1	
Domnick Hunter	E400AO	10CF35-165 X 1	
Domnick Hunter	E500AO	10CF43-252 X 1	
Domnick Hunter	E620AO	10CF35-251 X 1	
Domnick Hunter	EZ1030AO	10CZ07-020 X 1	
Domnick Hunter	EZ1050AO	10CZ12-023 X 1	
Domnick Hunter	EZ1070AO	10CZ12-029 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Domnick Hunter	EZ1140AO	10CZ12-056 X 1	
Domnick Hunter	EZ2010AO	10CZ20-046 X 1	
Domnick Hunter	EZ2020AO	10CZ20-086 X 1	
Domnick Hunter	EZ2030AO	10CZ20-126 X 1	
Domnick Hunter	EZ2050AO	10CZ20-200 X 1	
Domnick Hunter	EZ3050AO	10CZ27-200 X 1	
Domnick Hunter	EZ3075AO	10CZ27-298 X 1	
Domnick Hunter	EZ5060AO	10CZ46-239 X 1	
Domnick Hunter	EZ5075AO	10CZ50-298 X 1	
Domnick Hunter	K145AO	10IF20-102 X 1	
Domnick Hunter	K220AO	10IF25-134 X 1	
Domnick Hunter	K330AO	10IF25-254 X 1	
Domnick Hunter	K430AO	10CF35-165 X 1	
Particulate Filters			
Domnick Hunter	EP1001PL	3PP19-098 X 2	
Domnick Hunter	PF 02/05	12GJN08-024 X 1	
Domnick Hunter	PF 03/05	12GJN08-030 X 1	
Domnick Hunter	PF 03/10	3PJN10-030 X 1	
Domnick Hunter	PF 04/10	3PJN10-040 X 1	
Domnick Hunter	PF 04/20	3PJN13-040 X 1	
Domnick Hunter	PF 05/20	3PJN13-050 X 1	
Domnick Hunter	PF 05/25	3PJN15-050 X 1	
Domnick Hunter	PF 07/25	3PJN15-070 X 1	
Domnick Hunter	PF 07/30	3PJN25-070 X 1	
Domnick Hunter	PF 10/30	3PJN25-100 X 1	
Domnick Hunter	PF 15/30	3PGN25-150 X 1	
Domnick Hunter	PF 20/30	3PGN25-200 X 1	
Domnick Hunter	PF 30/30	3PGN25-300 X 1	
Domnick Hunter	PF 30/50	3PGN43-300 X 1	
Oil Vapor & Odor Removal			
Domnick Hunter	AC 02/05	AJN08-024 X 1	
Domnick Hunter	AC 03/05	AJN08-030 X 1	
Domnick Hunter	AC 03/10	AJN10-030 X 1	
Domnick Hunter	AC 04/10	AJN10-040 X 1	
Domnick Hunter	AC 04/20	AJN13-040 X 1	
Domnick Hunter	AC 05/20	AJN13-050 X 1	
Domnick Hunter	AC 05/25	AJN15-050 X 1	
Domnick Hunter	AC 07/25	AJN15-070 X 1	
Domnick Hunter	AC 07/30	AJN25-070 X 1	
Domnick Hunter	AC 10/30	AJN25-100 X 1	
Domnick Hunter	AC 15/30	AGN25-150 X 1	
Domnick Hunter	AC 20/30	AGN25-200 X 1	
Domnick Hunter	AC 30/30	AGN25-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Domnick Hunter	AC 30/50	AGN43-300 X 1	
Domnick Hunter	AC10/3	AJ25-100 X 1	
Domnick Hunter	AC15/3	AG25-150 X 1	
Domnick Hunter	AC20/3	AG25-200 X 1	
Domnick Hunter	AC3/1	AJ10-030 X 1	
Domnick Hunter	AC3/1.5	AJ13-030 X 1	
Domnick Hunter	AC30/3	AG25-300 X 1	
Domnick Hunter	AC30/5	AG43-300 X 1	
Domnick Hunter	AC4/1.5	AJ13-044 X 1	
Domnick Hunter	AC4/2.5	AJ15-040 X 1	
Domnick Hunter	AC5/2.5	AJN15-050 X 1	
Domnick Hunter	AC5/3	AJ25-050 X 1	
Domnick Hunter	E006AC	AF08-026 X 1	
Domnick Hunter	E013AC	AF10-032 X 1	
Domnick Hunter	E025AC	AF10-046 X 1	
Domnick Hunter	E040AC	AF20-063 X 1	
Domnick Hunter	E085AC	AF20-102 X 1	
Domnick Hunter	E195AC	AF25-134 X 1	
Domnick Hunter	E295AC	AF25-254 X 1	
Domnick Hunter	E400AC	AF35-165 X 1	
Domnick Hunter	E500AC	AF43-252 X 1	
Domnick Hunter	E620AC	AF35-251 X 1	
Domnick Hunter	EZ1030AC	AZ07-020 X 1	
Domnick Hunter	EZ1050AC	AZ12-023 X 1	
Domnick Hunter	EZ1070AC	AZ12-029 X 1	
Domnick Hunter	EZ1140AC	AZ12-056 X 1	
Domnick Hunter	EZ2010AC	AZ20-046 X 1	
Domnick Hunter	EZ2020AC	AZ20-086 X 1	
Domnick Hunter	EZ2030AC	AZ20-126 X 1	
Domnick Hunter	EZ2050AC	AZ20-200 X 1	
Domnick Hunter	EZ3050AC	AZ27-200 X 1	
Domnick Hunter	EZ3075AC	AZ27-298 X 1	
Domnick Hunter	EZ5060AC	AZ46-239 X 1	
Domnick Hunter	EZ5075AC	AZ50-298 X 1	
Domnick Hunter	K145ACS	AF20-102 X 1	
Domnick Hunter	K220ACS	AF25-134 X 1	
Domnick Hunter	K330ACS	AF25-254 X 1	
Domnick Hunter	K430ACS	AF35-165 X 1	
Trouble Shooter (High Temp)			
Domnick Hunter	K330AATS	6DF25-254 X 1	
Domnick Hunter	K330AOTS	10DF25-254 X 1	
Filterite			
Coalescer (Reverse Duo-Fine)			
Filterite	10" Element	6CP15-100 X 2	
Filterite	20" Element	6CP15-198 X 2	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Particulate 3 Micron (Duo-Fine Afterfilter)			
Filterite	10" Element	3PP15-100 X 2	
Filterite	20" Element	3PP15-198 X 2	

Note: Do not use '3P' elements on liquid applications.

Adsorber (Micro-Carbon - A)

Filterite	10" Element	AP15-100 X 2	
Filterite	20" Element	AP15-198 X 2	

Filtersoft

Filtersoft	F05013VE-T	10G04-013 X 10	
Filtersoft	F05013VE-W	10H04-013 X 10	
Filtersoft	F05013WE-T	8T04-013 X 10	
Filtersoft	F05013WE-W	8H04-013 X 10	
Filtersoft	F05013XE-T	6G04-013 X 10	
Filtersoft	F05013XE-W	6H04-013 X 10	
Filtersoft	F05023VE-T	10G04-023 X 10	
Filtersoft	F05023VE-W	10H04-023 X 10	
Filtersoft	F05023VH-TB	10T04-023 X 10	
Filtersoft	F05023WE-T	8T04-023 X 10	
Filtersoft	F05023WE-W	8H04-023 X 10	
Filtersoft	F05023XE-T	6G04-023 X 10	
Filtersoft	F05023XE-W	6H04-023 X 10	
Filtersoft	F05023XH-TB	6T04-023 X 10	
Filtersoft	F07013QE-CU	14JU07-013 X 10	
Filtersoft	F10020QE-CU	14JU10-020 X 10	
Filtersoft	F10020VE-W	10H10-020 X 8	
Filtersoft	F10020XE-W	6H10-020 X 8	
Filtersoft	F10025VE-T	10G10-025 X 10	
Filtersoft	F10025VE-W	10H10-025 X 8	
Filtersoft	F10025VH-TB	10T10-025 X 10	
Filtersoft	F10025WE-T	8T10-025 X 10	
Filtersoft	F10025WE-W	8H10-025 X 8	
Filtersoft	F10025XE-T	6G10-025 X 10	
Filtersoft	F10025XE-W	6H10-025 X 8	
Filtersoft	F10025XH-TB	6T10-025 X 10	
Filtersoft	F10050VE-W	10H10-050 X 4	
Filtersoft	F10050WE-W	8H10-050 X 4	
Filtersoft	F10050XE-W	6H10-050 X 4	
Filtersoft	F10070VE-T	10G10-070 X 10	
Filtersoft	F10070VE-W	10H10-070 X 4	
Filtersoft	F10070VH-TB	10T10-070 X 10	
Filtersoft	F10070WE-T	8T10-070 X 10	
Filtersoft	F10070WE-W	8H10-070 X 4	
Filtersoft	F10070XE-T	6G10-070 X 10	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	F10070XE-W	6H10-070 X 4	
Filtersoft	F10070XH-TB	6T10-070 X 10	
Filtersoft	F15043QE-CU	14JU15-043 X 10	
Filtersoft	F15060AU	AB15-060 X 4	
Filtersoft	F15060AU	AU15-060 X 4	
Filtersoft	F15060VE-T	10G15-060 X 10	
Filtersoft	F15060VE-W	10H15-060 X 4	
Filtersoft	F15060WE-W	8H15-060 X 4	
Filtersoft	F15060XE-T	6G15-060 X 10	
Filtersoft	F15060XE-W	6H15-060 X 4	
Filtersoft	F20035VE-W	10H20-035 X 4	
Filtersoft	F20035WE-W	8H20-035 X 4	
Filtersoft	F20035XE-W	6H20-035 X 4	
Filtersoft	F20090AU	AB15-084 X 2	
Filtersoft	F20090VE-T	10G20-090 X 10	
Filtersoft	F20090VE-W	10H20-090 X 2	
Filtersoft	F20090WE-W	8H20-090 X 2	
Filtersoft	F20090XE-T	6G20-090 X 10	
Filtersoft	F20090XE-W	6H20-090 X 2	
Filtersoft	F20187AU	AP15-180 X 2	
Filtersoft	F20187VE-T	10G20-187 X 10	
Filtersoft	F20187VE-W	10H20-187 X 1	
Filtersoft	F20187WE-W	8H20-187 X 1	
Filtersoft	F20187XE-T	6G20-187 X 10	
Filtersoft	F20187XE-W	6H20-187 X 1	
Filtersoft	F20198AU	AP15-198 X 2	
Filtersoft	F26075QE-CU	14JU26-075 X 4	
Filtersoft	F26120QE-CU	14JU26-120 X 4	
Filtersoft	F26240QE-CU	14JU26-240 X 4	
Filtersoft	FA1030AP-AB	AZ07-020 X 1	
Filtersoft	FA1030K-CB	3PZ07-020 X 1	
Filtersoft	FA1030WE-CB	10CZ07-020 X 1	
Filtersoft	FA1030XE-CB	8CZ07-020 X 1	
Filtersoft	FA1030YE-CB	6CZ07-020 X 1	
Filtersoft	FA1050AP-AB	AZ12-023 X 1	
Filtersoft	FA1050K-CB	3PZ12-023 X 1	
Filtersoft	FA1050WE-CB	10CZ12-023 X 1	
Filtersoft	FA1050XE-CB	8CZ12-023 X 1	
Filtersoft	FA1050YE-CB	6CZ12-023 X 1	
Filtersoft	FA1070AP-AB	AZ12-029 X 1	
Filtersoft	FA1070K-CB	3PZ12-029 X 1	
Filtersoft	FA1070WE-CB	10CZ12-029 X 1	
Filtersoft	FA1070XE-CB	8CZ12-029 X 1	
Filtersoft	FA1070YE-CB	6CZ12-029 X 1	
Filtersoft	FA1140AP-AB	AZ12-056 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FA1140K-CB	3PZ12-056 X 1	
Filtersoft	FA1140WE-CB	10CZ12-056 X 1	
Filtersoft	FA1140XE-CB	8CZ12-056 X 1	
Filtersoft	FA1140YE-CB	6CZ12-056 X 1	
Filtersoft	FA2010AP-AB	AZ20-046 X 1	
Filtersoft	FA2010K-CB	3PZ20-046 X 1	
Filtersoft	FA2010WE-CB	10CZ20-046 X 1	
Filtersoft	FA2010XE-CB	8CZ20-046 X 1	
Filtersoft	FA2010YE-CB	6CZ20-046 X 1	
Filtersoft	FA2020AP-AB	AZ20-086 X 1	
Filtersoft	FA2020K-CB	3PZ20-086 X 1	
Filtersoft	FA2020WE-CB	10CZ20-086 X 1	
Filtersoft	FA2020XE-CB	8CZ20-086 X 1	
Filtersoft	FA2020YE-CB	6CZ20-086 X 1	
Filtersoft	FA2030AP-AB	AZ20-126 X 1	
Filtersoft	FA2030K-CB	3PZ20-126 X 1	
Filtersoft	FA2030WE-CB	10CZ20-126 X 1	
Filtersoft	FA2030XE-CB	8CZ20-126 X 1	
Filtersoft	FA2030YE-CB	6CZ20-126 X 1	
Filtersoft	FA2050AP-AB	AZ20-200 X 1	
Filtersoft	FA2050K-CB	3PZ20-200 X 1	
Filtersoft	FA2050WE-CB	10CZ20-200 X 1	
Filtersoft	FA2050XE-CB	8CZ20-200 X 1	
Filtersoft	FA2050YE-CB	6CZ20-200 X 1	
Filtersoft	FA3050AP-AB	AZ27-200 X 1	
Filtersoft	FA3050K-CB	3PZ27-200 X 1	
Filtersoft	FA3050WE-CB	10CZ27-200 X 1	
Filtersoft	FA3050XE-CB	8CZ27-200 X 1	
Filtersoft	FA3050YE-CB	6CZ27-200 X 1	
Filtersoft	FA3075AP-AB	AZ27-298 X 1	
Filtersoft	FA3075K-CB	3PZ27-298 X 1	
Filtersoft	FA3075WE-CB	10CZ27-298 X 1	
Filtersoft	FA3075XE-CB	8CZ27-298 X 1	
Filtersoft	FA3075YE-CB	6CZ27-298 X 1	
Filtersoft	FA5075AP-AB	AZ50-298 X 1	
Filtersoft	FA5075K-CB	3PZ50-298 X 1	
Filtersoft	FA5075WE-CB	10CZ50-298 X 1	
Filtersoft	FA5075XE-CB	8CZ50-298 X 1	
Filtersoft	FA5075YE-CB	6CZ50-298 X 1	
Filtersoft	FB302VE-CB	8CF20-099 X 2	
Filtersoft	FB303VE-CB	8CF20-147 X 1	
Filtersoft	FB304VE-CB	8CF20-197 X 1	
Filtersoft	FE006AAYE-CB	6CF08-026 X 1	
Filtersoft	FE006AOVE-CBM	10CF08-026 X 1	
Filtersoft	FE013AAYE-CB	6IF10-032 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FE013AOVE-CBM	10IF10-032 X 1	
Filtersoft	FE025AAYE-CB	6IF10-046 X 1	
Filtersoft	FE025AOVE-CBM	10IF10-046 X 1	
Filtersoft	FE040AAYE-CB	6IF20-063 X 1	
Filtersoft	FE040AOVE-CBM	10IF20-063 X 1	
Filtersoft	FE085AAYE-CB	6IF20-102 X 1	
Filtersoft	FE085AOVE-CBM	10IF20-102 X 1	
Filtersoft	FE195AAYE-CB	6IF25-134 X 1	
Filtersoft	FE195AC-AB	AF25-134 X 1	
Filtersoft	FE195AOVE-CBM	10IF25-134 X 1	
Filtersoft	FE295AAYE-CB	6IF25-254 X 1	
Filtersoft	FE295AC-AB	AF25-254 X 1	
Filtersoft	FE295AOVE-CBM	10IF25-254 X 1	
Filtersoft	FE400AAYE-CB	6CF35-165 X 1	
Filtersoft	FE400AC-AB	AF35-165 X 1	
Filtersoft	FE400AOVE-CBM	10CF35-165 X 1	
Filtersoft	FE500AAYE-CB	6CF43-252 X 1	
Filtersoft	FE500AC-AB	AF43-252 X 1	
Filtersoft	FE500AOVE-CBM	10CF43-252 X 1	
Filtersoft	FH71311YE-CB	6CH25-260 X 1	
Filtersoft	FH7139YE-CB	6CH25-260 X 1	
Filtersoft	FH71511-AB	AH25-260 X 1	
Filtersoft	FH7159-AB	AH25-260 X 1	
Filtersoft	FH7319VE-CB	10CH25-260 X 1	
Filtersoft	FI1306XE-C	6C85-250 X 1	
Filtersoft	FI1355XE-C	6C85-250 X 1	
Filtersoft	FI1645XE-C	6C85-360 X 1	
Filtersoft	FI1777XE-C	6C85-360 X 1	
Filtersoft	FN10DXE-CB	6IR04-019 X 4	
Filtersoft	FN20DXE-CB	6IR08-019 X 4	
Filtersoft	FN30DXE-CB	6IR10-034 X 4	
Filtersoft	FP14051J-PB	3PP14-051 X 4	
Filtersoft	FP14051XE-CB	6QP14-051 X 4	
Filtersoft	FP19098J-PU	3PP19-098 X 2	
Filtersoft	FP19098VH-RS	10DP19-098 X 2	
Filtersoft	FP19098VH-RSI	10DPS19-098 X 2	
Filtersoft	FP19098XE-CU	6QP19-098 X 2	
Filtersoft	FP19098XE-DB	6QP19-098 X 2	
Filtersoft	FP19098XK-CB	6QP19-098 X 2	
Filtersoft	FP19198J-PU	3PP19-198 X 2	
Filtersoft	FP19198VH-RS	10DP19-198 X 2	
Filtersoft	FP19198VH-RSI	10DPS19-198 X 2	
Filtersoft	FP19198XE-CU	6QP19-198 X 2	
Filtersoft	FP19198XE-DB	6QP19-198 X 2	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FP19298XE-CU	6QP19-298 X 1	
Filtersoft	FP19298XE-DB	6QP19-298 X 1	
Filtersoft	FP26132J-PU	3PP26-132 X 2	
Filtersoft	FP26132VH-RS	10DP26-132 X 2	
Filtersoft	FP26132XK-CBI	6QP28-132 X 2	
Filtersoft	FP26132XK-CU	6QP28-132 X 2	
Filtersoft	FP26132XK-CUI	6QPS28-132 X 2	
Filtersoft	FP26265J-PU	3PP26-265 X 1	
Filtersoft	FP26265VH-RS	10DP26-265 X 1	
Filtersoft	FP26265XK-CU	6QP28-265 X 1	
Filtersoft	FP30142J-PB	3PP30-143 X 1	
Filtersoft	FP30142J-PBI	3PP30-143 X 1	
Filtersoft	FP30142VH-RV	10DP30-143 X 1	
Filtersoft	FP30142VH-RVI	10DPS30-143 X 1	
Filtersoft	FP30142XE-CB	6QP30-143 X 1	
Filtersoft	FP30142XE-CBI	6QPS30-143 X 1	
Filtersoft	FP30295J-PB	3PP30-295 X 1	
Filtersoft	FP30295J-PBI	3PP30-295 X 1	
Filtersoft	FP30295VH-RV	10DP30-295 X 1	
Filtersoft	FP30295VH-RVI	10DPS30-295 X 1	
Filtersoft	FP30295XE-CB	6QP30-295 X 1	
Filtersoft	FP30295XE-CBI	6QPS30-295 X 1	
Filtersoft	FS1357YE-CB	6CJ25-120 X 2	
Filtersoft	FS1358YE-CB	6CJ25-120 X 2	
Filtersoft	FS1359YE-CB	6CJ25-240 X 1	
Filtersoft	FS1360YE-CB	6CJ25-240 X 1	
Filtersoft	FS1361YE-CB	6CJ25-240 X 1	
Filtersoft	FS1362YE-CB	6CJ25-240 X 1	
Filtersoft	FS1367YE-CB	6CJ25-240 X 1	
Filtersoft	FS1368YE-CB	6CJ25-240 X 1	
Filtersoft	FS1370-AB	AJ25-240 X 1	
Filtersoft	FS1372-AB	AJ25-120 X 2	
Filtersoft	FS1373-AB	AJ25-120 X 2	
Filtersoft	FS1375-AB	AJ25-240 X 1	
Filtersoft	FS1377-AB	AJ25-240 X 1	
Filtersoft	FS1378-AB	AJ25-240 X 1	
Filtersoft	FS1379-AB	AJ25-240 X 1	
Filtersoft	FS1407YE-CB	6CJ25-120 X 2	
Filtersoft	FS1408YE-CB	6CJ25-240 X 1	
Filtersoft	FS1412-AB	AJ25-120 X 2	
Filtersoft	FS1413-AB	AJ25-240 X 1	
Filtersoft	FS1413YE-CB	6CJ25-240 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FS1418-AB	AJ25-240 X 1	
Filtersoft	FS5025-AB	AJ25-240 X 1	
Filtersoft	FS5027-AB	AJ25-240 X 1	
Filtersoft	FUF0205WE-CB	10HJN08-024 X 1	
Filtersoft	FUF0305WE-CB	10HJN08-030 X 1	
Filtersoft	FUF0310WE-CB	10CJN10-030 X 1	
Filtersoft	FUF0410WE-CB	10CJN10-040 X 1	
Filtersoft	FUF0420WE-CB	10CJN13-040 X 1	
Filtersoft	FUF0520WE-CB	10CJN13-050 X 1	
Filtersoft	FUF0525WE-CB	10IJN15-050 X 1	
Filtersoft	FUF0725WE-CB	10IJN15-070 X 1	
Filtersoft	FUF0730WE-CB	10IJN25-070 X 1	
Filtersoft	FUF1030WE-CB	10IJN25-100 X 1	
Filtersoft	FUF103WE-CB	10IJ25-100 X 1	
Filtersoft	FUF1530WE-CB	10IGN25-150 X 1	
Filtersoft	FUF153WE-CB	10IG25-150 X 1	
Filtersoft	FUF2030WE-CB	10IGN25-200 X 1	
Filtersoft	FUF203WE-CB	10IG25-200 X 1	
Filtersoft	FUF3030WE-CB	10IGN25-300 X 1	
Filtersoft	FUF303WE-CB	10IG25-300 X 1	
Filtersoft	FUF3050WE-CB	10QGN43-300 X 1	
Filtersoft	FUF305WE-CB	10QG43-300 X 1	
Filtersoft	FUF315WE-CB	10CJ13-030 X 1	
Filtersoft	FUF31WE-CB	10CJ10-030 X 1	
Filtersoft	FUF415WE-CB	10CJ13-044 X 1	
Filtersoft	FUF425WE-CB	10IJ15-040 X 1	
Filtersoft	FUF525WE-CB	10IJN15-050 X 1	
Filtersoft	FUF53WE-CB	10IJ25-050 X 1	
Filtersoft	FUK0205-AB	AJN08-024 X 1	
Filtersoft	FUK0305-AB	AJN08-030 X 1	
Filtersoft	FUK0310-AB	AJN10-030 X 1	
Filtersoft	FUK0410-AB	AJN10-040 X 1	
Filtersoft	FUK0420-AB	AJN13-040 X 1	
Filtersoft	FUK0520-AB	AJN13-050 X 1	
Filtersoft	FUK0525-AB	AJN15-050 X 1	
Filtersoft	FUK0725-AB	AJN15-070 X 1	
Filtersoft	FUK0730-AB	AJN25-070 X 1	
Filtersoft	FUK103-AB	AJ25-100 X 1	
Filtersoft	FUK1030-AB	AJN25-100 X 1	
Filtersoft	FUK153-AB	AG25-150 X 1	
Filtersoft	FUK1530-AB	AGN25-150 X 1	
Filtersoft	FUK203-AB	AG25-200 X 1	
Filtersoft	FUK2030-AB	AGN25-200 X 1	
Filtersoft	FUK303-AB	AG25-300 X 1	
Filtersoft	FUK3030-AB	AGN25-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required	Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FUK305-AB	AG43-300 X 1		Filtersoft	FUS1530YE-CB	4IGN25-150 X 1	
Filtersoft	FUK3050-AB	AGN43-300 X 1		Filtersoft	FUS153YE-CB	4IG25-150 X 1	
Filtersoft	FUK31-AB	AJ10-030 X 1		Filtersoft	FUS2030YE-CB	4IGN25-200 X 1	
Filtersoft	FUK315-AB	AJ13-030 X 1		Filtersoft	FUS203YE-CB	4IG25-200 X 1	
Filtersoft	FUK415-AB	AJ13-044 X 1		Filtersoft	FUS3030YE-CB	4IGN25-300 X 1	
Filtersoft	FUK425-AB	AJ15-040 X 1		Filtersoft	FUS303YE-CB	4IG25-300 X 1	
Filtersoft	FUK525-AB	AJN15-050 X 1		Filtersoft	FUS3050YE-CB	4QGN43-300 X 1	
Filtersoft	FUK53-AB	AJ25-050 X 1		Filtersoft	FUS305YE-CB	4QG43-300 X 1	
Filtersoft	FUM0205XE-CB	6HJN08-024 X 1		Filtersoft	FUS315YE-CB	4CJ13-030 X 1	
Filtersoft	FUM0305XE-CB	6HJN08-030 1		Filtersoft	FUS31YE-CB	4CJ10-030 X 1	
Filtersoft	FUM0310XE-CB	6CJN10-030 X 1		Filtersoft	FUS415YE-CB	4CJ13-044 X 1	
Filtersoft	FUM0410XE-CB	6CJN10-040 X 1		Filtersoft	FUS425YE-CB	4IJ15-040 X 1	
Filtersoft	FUM0420XE-CB	6CJN13-040 X 1		Filtersoft	FUS525YE-CB	4IJN15-050 X 1	
Filtersoft	FUM0520XE-CB	6CJN13-050 X 1		Filtersoft	FUS53YE-CB	4IJ25-050 X 1	
Filtersoft	FUM0525XE-CB	6IJN15-050 X 1		Filtersoft	FV1500VE-CB	10ICC25-240 X 1	
Filtersoft	FUM0725XE-CB	6IJN15-070 X 1		Filtersoft	FV1500VE-SBM	10DC25-240 X 1	
Filtersoft	FUM0730XE-CB	6IJN25-070 X 1		Filtersoft	FV1500VH-SBM	10DC25-240 X 1	
Filtersoft	FUM1030XE-CB	6IJN25-100 X 1		Filtersoft	FV1500XE-CB	8ICC25-240 X 1	
Filtersoft	FUM103XE-CB	6IJ25-100 X 1		Filtersoft	FV1500XE-SBM	8DC25-240 X 1	
Filtersoft	FUM1530XE-CB	6IGN25-150 X 1		Filtersoft	FV1500ZE-CB	6ICC25-240 X 1	
Filtersoft	FUM153XE-CB	6IG25-150 X 1		Filtersoft	FV1500ZE-SBM	6DC25-240 X 1	
Filtersoft	FUM2030XE-CB	6IGN25-200 X 1		Filtersoft	FV15XE-CB2	6CC15-150 X 2	
Filtersoft	FUM203XE-CB	6IG25-200 X 1		Filtersoft	FV15ZE-CB2	2CC15-150 X 2	
Filtersoft	FUM3030XE-CB	6IGN25-300 X 1		Filtersoft	FV1625VE-CB	10ICC25-300 X 1	
Filtersoft	FUM303XE-CB	6IG25-300 X 1		Filtersoft	FV1625VE-SBM	10DC25-300 X 1	
Filtersoft	FUM3050XE-CB	6QGN43-300 X 1		Filtersoft	FV1625VH-SBM	10DC25-300 X 1	
Filtersoft	FUM3050XE-CB	6QGN43-300 X 1		Filtersoft	FV1625XE-CB	8ICC25-300 X 1	
Filtersoft	FUM305XE-CB	6QG43-300 X 1		Filtersoft	FV1625XE-SBM	8DC25-300 X 1	
Filtersoft	FUM315XE-CB	6CJ13-030 X 1		Filtersoft	FV1625ZE-CB	6ICC25-300 X 1	
Filtersoft	FUM31XE-CB	6CJ10-030 X 1		Filtersoft	FV1625ZE-SBM	6DC25-300 X 1	
Filtersoft	FUM415XE-CB	6CJ13-044 X 1		Filtersoft	FV22XE-CB	6ICC25-220 X 1	
Filtersoft	FUM425XE-CB	6IJ15-040 X 1		Filtersoft	FV22ZE-CB	2ICC25-220 X 1	
Filtersoft	FUM525XE-CB	6IJN15-050 X 1		Filtersoft	FV860XE-CB	6CC15-060 X 2	
Filtersoft	FUM53XE-CB	6IJ25-050 X 1		Filtersoft	FV860ZE-CB	2CC15-060 X 2	
Filtersoft	FUS0205YE-CB	4HJN08-024 X 1		Filtersoft	FV8XE-CB	6CC15-080 X 2	
Filtersoft	FUS0305YE-CB	4HJN08-030 X 1		Filtersoft	FV8ZE-CB	2CC15-080 X 2	
Filtersoft	FUS0310YE-CB	4CJN10-030 X 1		Filtersoft	FVKE15H-RSA	10DC15-150 X 2	
Filtersoft	FUS0410YE-CB	4CJN10-040 X 1		Filtersoft	FVKE15J-PB	3PC15-150 X 2	
Filtersoft	FUS0420YE-CB	4CJN13-040 X 1		Filtersoft	FVKE22H-RSA	10DC25-220 X 1	
Filtersoft	FUS0520YE-CB	4CJN13-050 X 1		Filtersoft	FVKE22J-PB	3PCC25-220 X 1	
Filtersoft	FUS0525YE-CB	4IJN15-050 X 1		Filtersoft	FVKE6J-PB	3PC15-080 X 2	
Filtersoft	FUS0725YE-CB	4IJN15-070 X 1		Filtersoft	FVKEJ-PB	3PC15-060 X 2	
Filtersoft	FUS0730YE-CB	4IJN25-070 X 1		Filtersoft	FW532-AS	AK15-052 X 4	
Filtersoft	FUS1030YE-CB	4IJN25-100 X 1		Filtersoft	FW534-AB	AK25-238 X 1	
Filtersoft	FUS103YE-CB	4IJ25-100 X 1		Filtersoft	FW535-AB	AL25-063 X 2	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FW538-AB	AK35-074 X 2	
Filtersoft	FW540-AB	AL10-024 X 4	
Filtersoft	FW548YE-CB	6HL10-021 X 4	
Filtersoft	FW549YE-CB	6CL10-024 X 4	
Filtersoft	FW550YE-CB	6CU10-052 X 4	
Filtersoft	FW551YE-CS	6CK15-052 X 4	
Filtersoft	FW552YE-CB	6CL25-063 X 2	
Filtersoft	FW553YE-CB	6CK35-074 X 2	
Filtersoft	FW554YE-CB	6CK25-119 X 2	
Filtersoft	FW555YE-CB	6CK25-238 X 1	
Filtersoft	FW556WE-CB	8CK25-119 X 2	
Filtersoft	FW557WE-CB	8CK25-238 X 1	
Filtersoft	FW558-AB	AK25-080 X 2	
Filtersoft	FW559YE-CB	6CK25-080 X 2	
Filtersoft	FW560YE-CBA	6CK35-074 X 2	
Filtersoft	FW561YE-CBA	6CK35-106 X 1	
Filtersoft	FW562YE-CBA	6CK35-172 X 1	
Filtersoft	FW563-ABA	AK35-074 X 2	
Filtersoft	FW564-ABA	AK35-106 X 1	
Filtersoft	FW565-ABA	AK35-172 X 1	
Filtersoft	FW874WE-CBA	8CK35-074 X 2	
Filtersoft	FW875WE-CBA	8CK35-106 X 1	
Filtersoft	FW876WE-CBA	8CK35-172 X 1	
Filtersoft	FW988WE-CB	8HL10-021 X 4	
Filtersoft	FW989WE-CB	8CL10-024 X 4	
Filtersoft	FW992WE-CS	8CK15-052 X 4	

Filtersoft (Elements that require kits)

Filtersoft	FH7132YE-CB	6CM10-025 X 8	KX-21
Filtersoft	FH7133YE-CB	6CM10-050 X 4	KX-22
Filtersoft	FH7134YE-CB	6CM15-060 X 4	KX-23
Filtersoft	FH7135YE-CB	6CM15-095 X 2	KX-24
Filtersoft	FH7136YE-CB	6CM15-185 X 2	KX-25
Filtersoft	FH7137YE-CB	6CU25-187 X 1	KX-2
Filtersoft	FH7138YE-CB	6CU25-187 X 1	KX-2
Filtersoft	FH7152-AB	AM10-025 X 8	KX-21
Filtersoft	FH7153-AB	AM10-050 X 4	KX-22
Filtersoft	FH7154-AB	AM15-060 X 4	KX-23
Filtersoft	FH7155-AB	AM15-095 X 2	KX-24
Filtersoft	FH7156-AB	AM15-185 X 2	KX-25
Filtersoft	FH7157-AB	AU25-187 X 1	KX-2
Filtersoft	FH7158-AB	AU25-187 X 1	KX-2
Filtersoft	FH7313VE-CB	10CM10-025 X 8	KX-21
Filtersoft	FH7314VE-CB	10CM10-050 X 4	KX-22
Filtersoft	FH7315VE-CB	10CM15-060 X 4	KX-23
Filtersoft	FH7316VE-CB	10CM15-095 X 1	KX-24

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Filtersoft	FH7317VE-CB	10CM15-185 X 2	KX-25
Filtersoft	FH7318VE-CB	10CU25-187 X 1	KX-2
Note: Kits are required for initial conversion only.			
Flair			
Flair	DH006AA	6CF08-026 X 1	
Flair	DH006AC	AF08-026 X 1	
Flair	DH006AO	10CF08-026 X 1	
Flair	DH013AA	6IF10-032 X 1	
Flair	DH013AC	AF10-032 X 1	
Flair	DH013AO	10IF10-032 X 1	
Flair	DH025AA	6IF10-046 X 1	
Flair	DH025AC	AF10-046 X 1	
Flair	DH025AO	10IF10-046 X 1	
Flair	DH040AA	6IF20-063 X 1	
Flair	DH040AC	AF20-063 X 1	
Flair	DH040AO	10IF20-063 X 1	
Flair	DH085AA	6IF20-102 X 1	
Flair	DH085AC	AF20-102 X 1	
Flair	DH085AO	10IF20-102 X 1	
Flair	DH195AA	6IF25-134 X 1	
Flair	DH195AC	AF25-134 X 1	
Flair	DH195AO	10IF25-134 X 1	
Flair	DH295AA	6IF25-254 X 1	
Flair	DH295AC	AF25-254 X 1	
Flair	DH295AO	10IF25-254 X 1	
Flair	DH400AA	6CF35-165 X 1	
Flair	DH400AC	AF35-165 X 1	
Flair	DH400AO	10CF35-165 X 1	
Flair	DH500AA	6CF43-252 X 1	
Flair	DH500AC	AF43-252 X 1	
Flair	DH500AO	10CF43-252 X 1	
Flair	HK71311C	6CH25-260 X 1	
Flair	HK7319P	10CH25-260 X 1	
Flair	UFAK0205	AJN08-024 X 1	
Flair	UFAK0305	AJN08-030 X 1	
Flair	UFAK0310	AJN10-030 X 1	
Flair	UFAK0410	AJN10-040 X 1	
Flair	UFAK0420	AJN13-040 X 1	
Flair	UFAK0520	AJN13-050 X 1	
Flair	UFAK0525	AJN15-050 X 1	
Flair	UFAK0725	AJN15-070 X 1	
Flair	UFAK0730	AJN25-070 X 1	
Flair	UFAK1030	AJN25-100 X 1	
Flair	UFAK1530	AGN25-150 X 1	
Flair	UFAK2030	AGN25-200 X1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Flair	UFAK3030	AGN25-300 X 1	
Flair	UFAK3050	AGN43-300 X 1	
Flair	UFFF0205	10HJN08-024 X 1	
Flair	UFFF0305	10HJN08-030 X 1	
Flair	UFFF0310	10CJN10-030 X 1	
Flair	UFFF0410	10CJN10-040 X 1	
Flair	UFFF0420	10CJN13-040 X 1	
Flair	UFFF0520	10CJN13-050 X 1	
Flair	UFFF0525	10IJN15-050 X 1	
Flair	UFFF0725	10IJN15-070 X 1	
Flair	UFFF0730	10IJN25-070 X 1	
Flair	UFFF1030	10IJN25-100 X 1	
Flair	UFFF1530	10IGN25-150 X 1	
Flair	UFFF2030	10IGN25-200 X 1	
Flair	UFFF3030	10IGN25-300 X 1	
Flair	UFFF3050	10QGN43-300 X 1	
Flair	UFMF0205	6HJN08-024 X 1	
Flair	UFMF0305	6HJN08-030 X 1	
Flair	UFMF0310	6CJN10-030 X 1	
Flair	UFMF0410	6CJN10-040 X 1	
Flair	UFMF0420	6CJN13-040 X 1	
Flair	UFMF0520	6CJN13-050 X 1	
Flair	UFMF0525	6IJN15-050 X 1	
Flair	UFMF0725	6IJN15-070 X 1	
Flair	UFMF0730	6IJN25-070 X 1	
Flair	UFMF1030	6IJN25-100 X 1	
Flair	UFMF1530	6IGN25-150 X 1	
Flair	UFMF2030	6IGN25-200 X 1	
Flair	UFMF3030	6IGN25-300 X 1	
Flair	UFMF3050	6QGN43-300 X 1	
Flair	UFPE0205	12GJN08-024 X 1	
Flair	UFPE0305	12GJN08-030 X 1	
Flair	UFPE0310	3PJN10-030 X 1	
Flair	UFPE0410	3PJN10-040 X 1	
Flair	UFPE0420	3PJN13-040 X 1	
Flair	UFPE0520	3PJN13-050 X 1	
Flair	UFPE0525	3PJN15-050 X 1	
Flair	UFPE0725	3PJN15-070 X 1	
Flair	UFPE0730	3PJN25-070 X 1	
Flair	UFPE1030	3PJN25-100 X 1	
Flair	UFPE1530	3PGN25-150 X 1	
Flair	UFPE2030	3PGN25-200 X 1	
Flair	UFPE3030	3PGN25-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Flair	UFPE3050	3PGN43-300 X 1	
Flair	UFSMF0205	4HJN08-024 X 1	
Flair	UFSMF0305	4HJN08-030 X 1	
Flair	UFSMF0310	4CJN10-030 X 1	
Flair	UFSMF0410	4CJN10-040 X 1	
Flair	UFSMF0420	4CJN13-040 X 1	
Flair	UFSMF0520	4CJN13-050 X 1	
Flair	UFSMF0525	4IJN15-050 X 1	
Flair	UFSMF0725	4IJN15-070 X 1	
Flair	UFSMF0730	4IJN25-070 X 1	
Flair	UFSMF1030	4IJN25-100 X 1	
Flair	UFSMF1530	4IGN25-150 X 1	
Flair	UFSMF2030	4IGN25-200 X 1	
Flair	UFSMF3030	4IGN25-300 X 1	
Flair	UFSMF3050	4QGN43-300 X 1	
Flair	VCE15	6CC15-150 X 2	
Flair	VCE22	6ICC25-220 X 1	
Flair	VCE8100	6CC15-080 X 2	
Flair	VCE860	6CC15-060 X 2	
Flair	VCXE15	2CC15-150 X 2	
Flair	VCXE22	2ICC25-220 X 1	
Flair	VCXE8100	2CC15-080 X 2	
Flair	VCXE860	2CC15-060 X 2	
Flair	VE111250B	8ICC25-240 X 1	
Flair	VE11125RB	8DC25-240 X 1	
Flair	VE111265B	8ICC25-300 X 1	
Flair	VE111265RB	8DC25-300 X 1	
Flair	VKE15	3PC15-150 X 2	
Flair	VKE15HT	10DC15-150 X 2	
Flair	VKE22	3PCC25-220 X 1	
Flair	VKE22HT	10DC25-220 X 1	
Flair	VKE6100	3PC15-080 X 2	
Flair	VKE660	3PC15-060 X 2	
Flair	Z1050A	AZ12-023 X 1	
Flair	Z1050V	3PZ12-023 X 1	
Flair	Z1050X	6CZ12-023 X 1	
Flair	Z1050Y	8CZ12-023 X 1	
Flair	Z1050Z	10CZ12-023 X 1	
Flair	Z1070A	AZ12-029 X 1	
Flair	Z1070V	3PZ12-029 X 1	
Flair	Z1070X	6CZ12-029 X 1	
Flair	Z1070Y	8CZ12-029 X 1	
Flair	Z1070Z	10CZ12-029 X 1	
Flair	Z1140A	AZ12-056 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Flair	Z1140V	3PZ12-056 X 1	
Flair	Z1140X	6CZ12-056 X 1	
Flair	Z1140Y	8CZ12-056 X 1	
Flair	Z1140Z	10CZ12-056 X 1	
Flair	Z2010A	AZ20-046 X 1	
Flair	Z2010V	3PZ20-046 X 1	
Flair	Z2010X	6CZ20-046 X 1	
Flair	Z2010Y	8CZ20-046 X 1	
Flair	Z2010Z	10CZ20-046 X 1	
Flair	Z2010Z	10CZ20-046 X 1	
Flair	Z2020A	AZ20-086 X 1	
Flair	Z2020A	AZ20-086 X 1	
Flair	Z2020V	3PZ20-086 X 1	
Flair	Z2020V	3PZ20-086 X 1	
Flair	Z2020X	6CZ20-086 X 1	
Flair	Z2020Y	8CZ20-086 X 1	
Flair	Z2020Z	10CZ20-086 X 1	
Flair	Z2030A	AZ20-126 X 1	
Flair	Z2030V	3PZ20-126 X 1	
Flair	Z2030X	6CZ20-126 X 1	
Flair	Z2030Y	8CZ20-126 X 1	
Flair	Z2030Z	10CZ20-126 X 1	
Flair	Z2050A	AZ20-200 X 1	
Flair	Z2050V	3PZ20-200 X 1	
Flair	Z2050X	6CZ20-200 X 1	
Flair	Z2050Y	8CZ20-200 X 1	
Flair	Z2050Z	10CZ20-200 X 1	
Flair	Z3050A	AZ27-200 X 1	
Flair	Z3050V	3PZ27-200 X 1	
Flair	Z3050X	6CZ27-200 X 1	
Flair	Z3050Y	8CZ27-200 X 1	
Flair	Z3050Z	10CZ27-200 X 1	
Flair	Z3075A	AZ27-298 X 1	
Flair	Z3075V	3PZ27-298 X 1	
Flair	Z3075X	6CZ27-298 X 1	
Flair	Z3075Y	8CZ27-298 X 1	
Flair	Z3075Z	10CZ27-298 X 1	
Flair	Z5075A	AZ50-298 X 1	
Flair	Z5075V	3PZ50-298 X 1	
Flair	Z5075X	6CZ50-298 X 1	
Flair	Z5075Y	8CZ50-298 X 1	
Flair	Z5075Z	10CZ50-298 X 1	
Flair (elements that require kits)			
Flair	HK71312C	6CU25-187 X 1	KX-2

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Flair	HK7132C	6CM10-025 X 8	KX-21
Flair	HK7133C	6CM10-050 X 4	KX-22
Flair	HK7134C	6CM15-060 X 4	KX-23
Flair	HK7135C	6CM15-095 X 2	KX-24
Flair	HK7136C	6CM15-185 X 2	KX-25
Flair	HK7137C	6CU25-187 X 1	KX-2
Flair	HK7313P	10CM10-025 X 8	KX-21
Flair	HK7314P	10CM10-050 X 4	KX-22
Flair	HK7315P	10CM15-060 X 4	KX-23
Flair	HK7316P	10CM15-095 X 2	KX-24
Flair	HK7317P	10CM15-185 X 2	KX-25
Flair	HK7318P	10CU25-187 X 1	KX-2

Note: Kits are required for initial conversion only.

Hankison

Oil Removal

Hankison	0731-3	10CM10-025 X 8	KX-21
Hankison	0731-4	10CM10-050 X 4	KX-22
Hankison	0731-5	10CM15-060 X 4	KX-23
Hankison	0731-6	10CM15-095 X 2	KX-24
Hankison	0731-7	10CM15-185 X 2	KX-25
Hankison	0731-8	10CU25-187 X 1	KX-2
Hankison	0731-9*	10CH25-260 X 1	

Aerolescer

Hankison	0713-11*	6CH25-260 X 1	
Hankison	0713-12*	6CU25-187 X 1	KX-2
Hankison	0713-2	6CM10-025 X 8	KX-21
Hankison	0713-3	6CM10-050 X 4	KX-22
Hankison	0713-4	6CM15-060 X 4	KX-23
Hankison	0713-5	6CM15-095 X 2	KX-24
Hankison	0713-6	6CM15-185 X 2	KX-25
Hankison	0713-7	6CU25-187 X 1	KX-2
Hankison	0713-8	6CU25-187 X 1	KX-2
Hankison	0713-9	6CH25-260 X 1	

Hypersorb

Hankison	0715-11*	AH25-260 X 1	
Hankison	0715-2	AM10-025 X 8	KX-21
Hankison	0715-3	AM10-050 X 4	KX-22
Hankison	0715-4	AM15-060 X 4	KX-23

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Hankison	0715-5	AM15-095 X 2	KX-24
Hankison	0715-6	AM15-185 X 2	KX-25
Hankison	0715-7	AU25-187 X 1	KX-2
Hankison	0715-8	AU25-187 X 1	KX-2
Hankison	0715-9	AH25-260 X 1	
Notes: Kits are required for initial conversion only.			
*The number of elements required varies based on the vessel.			
AccuMax			
Hankison	0740-4	10DH25-260 X 1	
HF Series Filters			
Oil Vapor Removal Filters			
Hankison	E1-12	AH10-020 X 1	
Hankison	E1-16	AH10-036 X 1	
Hankison	E1-20	AH10-060 X 1	
Hankison	E1-24	AHC16-066 X 1	
Hankison	E1-28	AHC16-108 X 1	
Hankison	E1-32	AHC19-131 X 1	
Hankison	E1-36	AHC19-176 X 1	
Hankison	E1-40	AHC25-204 X 1	
Hankison	E1-44	AHC25-265 X 1	
Hankison	E1-48	AHC25-323 X 1	
Hankison	E1-PV	AH25-260 X 1	
Ultra High Efficiency Oil Removal Filters			
Hankison	E3-12	2CH10-020 X 1	
Hankison	E3-16	2CH10-036 X 1	
Hankison	E3-20	2CH10-060 X 1	
Hankison	E3-24	2CH16-066 X 1	
Hankison	E3-28	2CH16-108 X 1	
Hankison	E3-32	2CH19-131 X 1	
Hankison	E3-36	2CH19-176 X 1	
Hankison	E3-40	2CH25-204 X 1	
Hankison	E3-44	2CH25-265 X 1	
Hankison	E3-48	2CH25-323 X 1	
Hankison	E3-PV	2CH25-260 X 1	
High Efficiency Oil Removal Filters			
Hankison	E5-12	6CH10-020 X 1	
Hankison	E5-16	6CH10-036 X 1	
Hankison	E5-20	6CH10-060 X 1	
Hankison	E5-24	6CH16-066 X 1	
Hankison	E5-28	6CH16-108 X 1	
Hankison	E5-32	6CH19-131 X 1	
Hankison	E5-36	6CH19-176 X 1	
Hankison	E5-40	6CH25-204 X 1	
Hankison	E5-44	6CH25-265 X 1	
Hankison	E5-48	6CH25-323 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Hankison	E5-PV	6CH25-260 X 1	
Air Line Filters			
Hankison	E7-12	10CH10-020 X 1	
Hankison	E7-16	10CH10-036 X 1	
Hankison	E7-20	10CH10-060 X 1	
Hankison	E7-24	10CH16-066 X 1	
Hankison	E7-28	10CH16-108 X 1	
Hankison	E7-32	10CH19-131 X 1	
Hankison	E7-36	10CH19-176 X 1	
Hankison	E7-40	10CH25-204 X 1	
Hankison	E7-44	10CH25-265 X 1	
Hankison	E7-48	10CH25-323 X 1	
Hankison	E7-PV	10CH25-260 X 1	
Separator/Filter			
Hankison	E9-12	100WS10-020 X 1	
Hankison	E9-16	100WS10-036 X 1	
Hankison	E9-20	100WS10-060 X 1	
Hankison	E9-24	100WS16-066 X 1	
Hankison	E9-28	100WS16-108 X 1	
Hankison	E9-32	100WS19-131 X 1	
Hankison	E9-36	100WS19-176 X 1	
Hankison	E9-40	100WS25-204 X 1	
Hankison	E9-44	100WS25-265 X 1	
Hankison	E9-48	100WS25-323 X 1	
Hankison	E9-PV	100WS25-260 X 1	

Headline

Headline	12-32-50C	6H04-013 X 10	
Headline	12-32-50K	6T04-013 X 10	
Headline	12-32-70C	10H04-013 X 10	
Headline	12-32-70K	10T04-013 X 10	
Headline	12-57-50C	6H04-023 X 10	
Headline	12-57-50K	6T04-023 X 10	
Headline	12-57-70C	10H04-023 X 10	
Headline	12-57-70K	10T04-023 X 10	
Headline	25-127-50C	6H10-050 X 4	
Headline	25-127-70C	10H10-050 X 4	
Headline	25-178-50C	6H10-070 X 4	
Headline	25-178-50K	6T10-070 X 10	
Headline	25-178-70C	10H10-070 X 4	
Headline	25-178-70K	10T10-070 X 10	
Headline	25-64-50C	6H10-025 X 8	
Headline	25-64-50K	6T10-025 X 10	
Headline	25-64-70C	10H10-025 X 8	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Headline	25-64-70K	10T10-025 X 10	
Headline	38-152-50C	6H15-060 X 4	
Headline	38-152-50K	6T15-060 X 10	
Headline	38-152-70C	10H15-060 X 4	
Headline	38-152-70K	10T15-060 X 10	
Headline	51-230-50C	6H20-090 X 2	
Headline	51-230-50K	6T20-090 X 10	
Headline	51-230-70C	10H20-090 X 2	
Headline	51-230-70K	10T20-090 X 10	
Headline	51-476-50C	6H20-187 X 1	
Headline	51-476-50K	6T20-187 X 10	
Headline	51-476-70C	10H20-187 X 1	
Headline	51-476-70K	10T20-187 X 10	
Headline	51-89-50C	6H20-035 X 4	
Headline	51-89-70C	10H20-035 X 4	

Henderson

Coalescer (Dryer Pre-filter)

Henderson	8D20	6CN10-028 X 8	KX-10
Henderson	8D28	6CN10-038 X 4	KX-11
Henderson	16D33	6CU19-050 X 2	KX-12
Henderson	16D50	6CU19-070 X 2	KX-13
Henderson	16D100	6CU19-130 X 2	KX-14
Henderson	16D150	6CU19-187 X 1	KX-16
Henderson	0812-1	6CE63-118 X 1	

Particulate (Dryer After-Filter 3 Micron)

Henderson	SB4	3PN10-038 X 4	KX-11
Henderson	SB12	3PU19-050 X 2	KX-12
Henderson	245-3	3PE15-050 X 4	
Henderson	0812-1	3PE63-118 X 1	

Particulate - High Temp 450° F

Dryer After - Filter 0.9 Micron

Henderson	F350 (450°)	10DS19-187 X 1	KX-16H
Henderson	F350 (350°)	3PS19-187 X 1	KX-16H

Note: Kits are required for initial conversion only.

Johnson Controls

Johnson Controls	A4000-604	4CL10-024 X 8	
Johnson Controls	A4000-605	4CL10-053 X 4	
Johnson Controls	A4000-606	6CL25-063 X 2	
Johnson Controls	A4000-627	4CL10-024 X 8	
Johnson Controls	A4000-628	4CL10-053 X 4	
Johnson Controls	A4000-629	6CL25-063 X 2	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
------------	------------------------	---------------------	--------------

Norgren

Norgren	665-88	6CN25-080 X 2	
---------	--------	---------------	--

Numatics

Numatics	EKF10D	6IR04-019 X 4	
Numatics	EKF20D	6IR08-019 X 4	
Numatics	EKF30D	6IR10-034 X 4	

Pall/Pneumatic Products Corporation

Reverse Ultipore (Coalescing Pre-Filter for Dryer)

Pall/PPC	GPC-125PF	6QP19-075 X 2	
Pall/PPC	MCC-1001SU	6QP19-098 X 2	
Pall/PPC	MCC-1002SU	6QP19-198 X 2	
Pall/PPC	MCC-1201SU	6QP28-132 X 2	
Pall/PPC	MCC-1202SU	6QP28-265 X 1	
Pall/PPC	MCC-4463SU	6QP14-051 X 4	
Pall/PPC	MCS-1001SU	6QP19-098 X 2	
Pall/PPC	MCS-4463SU	6QP14-051 X 4	
Pall/PPC	MDC-1001SU	6QP19-098 X 2	
Pall/PPC	MDC-1201SU	6QP28-132 X 2	
Pall/PPC	MDC-1202SU	6QP28-265 X 1	
Pall/PPC	MDC-4463SU	6QP14-051 X 4	
Pall/PPC	MDS-1001SU	6QP19-098 X 2	
Pall/PPC	MDS-1201SU	6QPS28-132 X 2	
Pall/PPC	MDS-4463SU	6QP14-051 X 4	
Pall/PPC	OL-5C	6QP14-051 X 4	
Pall/PPC	OL-9C	6QP19-098 X 2	
Pall/PPC	PCC-1001SU	6QP19-098 X 2	
Pall/PPC	PCC-1002SU	6QP19-198 X 2	
Pall/PPC	PCC-1003SU	6QP19-298 X 1	
Pall/PPC	PCC-1200SU	6QP30-295 X 1	
Pall/PPC	PCC-1201SU	6QP28-132 X 2	
Pall/PPC	PCC-1202SU	6QP28-265 X 1	
Pall/PPC	PCC-350SU	6QP30-143 X 1	
Pall/PPC	PCC-4463SU	6QP14-051 X 4	
Pall/PPC	PCC-600SU	6QP30-140 X 1	
Pall/PPC	PCC-700SU	6QP30-295 X 1	
Pall/PPC	PCS-1001SU	6QP19-098 X 2	
Pall/PPC	PCS-060AF	3PP14-051 X 4	
Pall/PPC	PCS-1002AF	3PP19-198 X 2	
Pall/PPC	PCS-1002SU	6QP19-198 X 2	
Pall/PPC	PCS-350SU	6QPS30-143 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Pall/PPC	PCS-4463SU	6QP14-051 X 4	
Pall/PPC	PCS-700SU	6QPS30-295 X 1	
Pall/PPC	PFS1201ZM	6QP28-132 X 1	
Pall/PPC	PFS1001ZM	6QPS19-098 X 2	
Pall/PPC	PFS4463ZM	6QPS28-132 X 1	
Pall/PPC	POC-035SU	6QP14-051 X 4	
Pall/PPC	POC-060SU	6QP14-051 X 4	
Pall/PPC	POC-1001SU	6QP19-098 X 2	
Pall/PPC	POC-1201SU	6QP28-132 X 2	
Pall/PPC	POC-1200SU	6QP30-295 X 1	
Pall/PPC	POC-600SU	6QP30-140 X 1	
Pall/PPC	POS-600SU	6QPS30-140 X 1	
Pall/PPC	POS-700SU	6QPS30-295 X 1	
Pall/PPC	POS-1001SU	6QPS19-098 X 2	
Pall/PPC	POS-1200SU	6QPS30-295 X 1	
Pall/PPC	POS-1201SU	6QPS28-132 X 1	
Pall/PPC	PPC-1200SU	6QP30-295 X 1	
Pall/PPC	PPC-1201SU	6QP28-132 X 2	
Pall/PPC	PPC-1202SU	6QP28-265 X 1	
Pall/PPC	PPC-350SU	6QP30-143 X 1	
Pall/PPC	PPC-700SU	6QP30-295 X 1	
Pall/PPC	PPY-1001SU	6QP19-098 X 2	
Pall/PPC	PPY-1002SU	6QP19-198 X 2	
Pall/PPC	PPY-1003SU	6QP19-298 X 1	
Low Temp (225° F) 3 Micron Particulate After-Filter			
Pall/PPC	GPC-175AF	3PP19-075 X 2	
Pall/PPC	MCS-4463AF	3PP14-051 X 4	
Pall/PPC	MCS-4463EC	3PP14-051 X 4	
Pall/PPC	MDC-1001AF	3PP19-098 X 2	
Pall/PPC	MDC-1002AF	3PP19-198 X 2	
Pall/PPC	MDC-1201AF	3PP26-132 X 2	
Pall/PPC	MDC-1202EC	3PP26-265 X 1	
Pall/PPC	MDC-4463AF	3PP14-051 X 4	
Pall/PPC	PCC-060AF	3PP14-051 X 4	
Pall/PPC	PCC-350AF	3PP30-143 X 1	
Pall/PPC	PCC-600AF	3PP30-140 X 1	
Pall/PPC	PCC-700AF	3PP30-295 X 1	
Pall/PPC	PCC-1001AF	3PP19-098 X 2	
Pall/PPC	PCC-1002AF	3PP19-198 X 2	
Pall/PPC	PCC-1003AF	3PP19-298 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Pall/PPC	PCC-1200AF	3PP30-295 X 1	
Pall/PPC	PCC-1201AF	3PP26-132 X 2	
Pall/PPC	PCC-1202EC	3PP26-265 X 1	
Pall/PPC	PCC-4463AF	3PP14-051 X 4	
Pall/PPC	PCS-1001AF	3PP19-098 X 2	
Pall/PPC	PCS-4463AF	3PP14-051 X 4	
High Temp (425° F) 0.9 Micron Particulate			
Pall/PPC	MCC-1001HT	10DP19-098 X 2	
Pall/PPC	MCC-1002HT	10DP19-198 X 2	
Pall/PPC	MCC-1201HT	10DP26-132 X 2	
Pall/PPC	MCC-1202HT	10DP26-265 X 1	
Pall/PPC	MCS-1001HT	10DPS19-098 X 2	
Pall/PPC	MCS-1002HT	10DPS19-198 X 2	
Pall/PPC	MDC-1001HT	10DP19-098 X 2	
Pall/PPC	MDC-1002HT	10DP19-198 X 2	
Pall/PPC	MDC-1201HT	10DP26-132 X 2	
Pall/PPC	MDC-1202HT	10DP26-265 X 1	
Pall/PPC	MDS-1001HT	10DPS19-098 X 2	
Pall/PPC	MDS-1002HT	10DPS19-198 X 2	
Pall/PPC	PCC-1001HT	10DP19-098 X 2	
Pall/PPC	PCC-1002HT	10DP19-198 X 2	
Pall/PPC	PCC-1003HT	10DP19-298 X 1	
Pall/PPC	PCC-1200HT	10DP30-295 X 1	
Pall/PPC	PCC-1201HT	10DP26-132 X 2	
Pall/PPC	PCC-1202HT	10DP26-265 X 1	
Pall/PPC	PCC-350HT	10DP30-143 X 1	
Pall/PPC	PCC-600HT	10DP30-140 X 1	
Pall/PPC	PCC-700HT	10DP30-295 X 1	
Pall/PPC	PCS-1001HT	10DPS19-098 X 2	
Pall/PPC	PCS-1002HT	10DPS19-198 X 2	
Pall/PPC	PCS-1200HT	10DPS30-295 X 1	
Pall/PPC	PCS-350HT	10DPS30-143 X 1	
Pall/PPC	PCS-700HT	10DPS30-295 X 1	
Petrosorb Ultipore Carbon Adsorber			
Pall/PPC	MCS-1001CE	AP19-098 X 2	
Pall/PPC	MDC-1001CE	AP19-098 X 2	
Pall/PPC	MDC-1001CV	AP19-098 X 2	
Pall/PPC	MDC-1001SAU	AP19-098 X 2	
Pall/PPC	MDC-1002SAU	AP19-198 X 2	
Pall/PPC	MDC-1201SAU	AP26-132 X 2	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Pall/PPC	MDC-1202SAU	AP26-265 X 1	
Pall/PPC	MDC-4463SAU	AP14-051 X 4	
Natural Gas Coalescing Filter			
Pall/PPC	CC05LG13B	6IP15-052 X 4	
Pall/PPC	CC1LG7A	6CPC20-098 X 1	
Pall/PPC	CC3LG7A	7CPP20-290 X 1	
Pall/PPC	CC3LG02H13	7CRP20-290 X 1	
Pioneer			
Particulate Filter Elements			
Pioneer	EPS30	3PU10-035 X 1	
Pioneer	EPS40	3PU10-035 X 1	
Pioneer	EPS100	3PU10-060 X 1	
Pioneer	EPS250D	3PU15-105 X 1	
Pioneer	EPS425D	3PU20-133 X 1	
Pioneer	EPS550D	3PU20-195 X 1	
Pioneer	EPS750D	3PU25-198 X 1	
Pioneer	EPS1000D	3PU25-245 X 1	
Pioneer	EPS1300D	3PU25-285 X 1	
Pioneer	EPS1700D	3PU32-290 X 1	
Pioneer	EPS2000D	3PU32-350 X 1	
Pioneer	EPS2600D	3PU52-290 X 1	
Pioneer	EPS3500D	3PU78-260 X 1	
Pioneer	EPS5200D	3PU78-370 X 1	
Coalescing Filter Elements			
Pioneer	ECS25	6CU10-035 X 1	
Pioneer	ECS35	6CU10-035 X 1	
Pioneer	ECS60	6CU10-060 X 1	
Pioneer	ECS155	6CU15-105 X 1	
Pioneer	ECS250D	6IU20-133 X 1	
Pioneer	ECS350D	6IU20-195 X 1	
Pioneer	ECS450D	6CU25-198 X 1	
Pioneer	ECS600D	6CU25-245 X 1	
Pioneer	ECS800D	6CU25-285 X 1	
Pioneer	ECS1050D	6CU32-290 X 1	
Pioneer	ECS1250D	6CU32-350 X 1	
Pioneer	ECS1650D	6QU52-290 X 1	
Pioneer	ECS2100D	6QU78-260 X 1	
Pioneer	ECS3100D	6QU78-370 X 1	
Micro-lescer Filter Elements			
Pioneer	EMS20	4CU10-035 X 1	
Pioneer	EMS25	4CU10-035 X 1	
Pioneer	EMS50	4CU10-060 X 1	
Pioneer	EMS125D	4CU15-105 X 1	
Pioneer	EMS185D	4IU20-133 X 1	
Pioneer	EMS260D	4IU20-195 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Pioneer	EMS350D	4CU25-198 X 1	
Pioneer	EMS450D	4CU25-245 X 1	
Pioneer	EMS600D	4CU25-285 X 1	
Pioneer	EMS800D	4CU32-290 X 1	
Pioneer	EMS1000D	4CU32-350 X 1	
Pioneer	EMS1250D	4QU52-290 X 1	
Pioneer	EMS1600D	4QU78-260 X 1	
Pioneer	EMS2500D	4QU78-370 X 1	

Pure Air

Puretech				# of Elements required
Pure Air	1350	8DU51-100 X 1	KV-22	1
Pure Air	1351	8DU51-128 X 1	KV-22	1
Pure Air	1352	8DU78-165 X 1	KV-24	1
Pure Air	1353	8CU145-200 X 1		1
Purelescer				
Pure Air	1357	6CJ25-120 X 2		2
Pure Air	1358	6CJ25-120 X 2		3
Pure Air	1359	6CJ25-240 X 1		3
Pure Air	1360	6CJ25-240 X 1		4
Pure Air	1361	6CJ25-240 X 1		5
Pure Air	1362	6CJ25-240 X 1		6
Pure Air	1367	6CJ25-240 X 1		7
Pure Air	1368	6CJ25-240 X 1		8
Pure Air	1406	6CN25-080 X 2		1
Pure Air	1407	6CJ25-120 X 2		1
Pure Air	1408	6CJ25-240 X 1		1
Pure Air	1408	6CJ25-240 X 1		10

Note: Closure end cap O-rings are included for Purelescer elements.

Pureadsorber				
Pure Air	1370	AJ25-240 X 1		3 or 5
Pure Air	1372	AJ25-120 X 2		2
Pure Air	1373	AJ25-120 X 2		3
Pure Air	1375	AJ25-240 X 1		4
Pure Air	1377	AJ25-240 X 1		6
Pure Air	1378	AJ25-240 X 1		7
Pure Air	1379	AJ25-240 X 1		8
Pure Air	1411	AJ25-080 X 2		1
Pure Air	1412	AJ25-120 X 2		1
Pure Air	1413	AJ25-240 X 1		1
Pure Air	1418	AJ25-240 X 1		10

Notes: Closure end cap O-rings are included for Pureadsorber elements.

Kits are required for initial conversion only.

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Steris			
Steris	129360-802	6G10-025 X 10	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Sullair			
Sullair	250024-423	10CF08-026 X 1	
Sullair	250024-424	10IF10-032 X 1	
Sullair	250024-425	10IF10-046 X 1	
Sullair	250024-426	10IF20-063 X 1	
Sullair	250024-427	10IF20-102 X 1	
Sullair	250024-428	10IF25-134 X 1	
Sullair	250024-429	10IF25-254 X 1	
Sullair	250030-644	10CF35-165 X 1	
Sullair	250024-430	10CF35-251 X 1	
Sullair	250024-431	6CF08-026 X 1	
Sullair	250024-432	6IF10-032 X 1	
Sullair	250024-433	6IF10-046 X 1	
Sullair	250024-434	6IF20-063 X 1	
Sullair	250024-435	6IF20-102 X 1	
Sullair	250024-436	6IF25-134 X 1	
Sullair	250024-437	6IF25-254 X 1	
Sullair	250024-438	6CF35-251 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Ultra Air			
Ultra Air	EC100P	6CM15-060 X 4	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Ultrafilter			
80 Series			
Prefilters			
Ultrafilter	V-PE 3/1	3PJ10-030 X 1	
Ultrafilter	V-PE 3/1,5	3PJ13-030 X 1	
Ultrafilter	V-PE 4/1,5	3PJ13-044 X 1	
Ultrafilter	V-PE 4/2,5	3PJ15-040 X 1	
Ultrafilter	V-PE 5/2,5	3PJN15-050 X 1	
Ultrafilter	V-PE 5/3	3PJ25-050 X 1	
Ultrafilter	V-PE 10/3	3PJ25-100 X 1	
Ultrafilter	V-PE 15/3	3PG25-150 X 1	
Ultrafilter	V-PE 20/3	3PG25-200 X 1	
Ultrafilter	V-PE 30/3	3PG25-300 X 1	
Ultrafilter	V-PE 30/5	3PG43-300 X 1	
Fine Filters			
Ultrafilter	FF 3/1	10CJ10-030 X 1	
Ultrafilter	FF 3/1,5	10CJ13-030 X 1	
Ultrafilter	FF 4/1,5	10CJ13-044 X 1	
Ultrafilter	FF 4/2,5	10IJ15-040 X 1	
Ultrafilter	FF 5/2,5	10IJN15-050 X 1	
Ultrafilter	FF 5/3	10IJ25-050 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Ultrafilter	FF 10/3	10IJ25-100 X 1	
Ultrafilter	FF 15/3	10IG25-150 X 1	
Ultrafilter	FF 20/3	10IG25-200 X 1	
Ultrafilter	FF 30/3	10IG25-300 X 1	
Ultrafilter	FF 30/5	10QG43-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Micro Filters			
Ultrafilter	MF 3/1	6CJ10-030 X 1	
Ultrafilter	MF 3/1,5	6CJ13-030 X 1	
Ultrafilter	MF 4/1,5	6CJ13-044 X 1	
Ultrafilter	MF 4/2,5	6IJ15-040 X 1	
Ultrafilter	MF 5/2,5	6IJN15-050 X 1	
Ultrafilter	MF 5/3	6IJ25-050 X 1	
Ultrafilter	MF 10/3	6IJ25-100 X 1	
Ultrafilter	MF 15/3	6IG25-150 X 1	
Ultrafilter	MF 20/3	6IG25-200 X 1	
Ultrafilter	MF 30/3	6IG25-300 X 1	
Ultrafilter	MF 30/5	6QG43-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Sub Micro Filters			
Ultrafilter	SMF 3/1	4CJ10-030 X 1	
Ultrafilter	SMF 3/1,5	4CJ13-030 X 1	
Ultrafilter	SMF 4/1,5	4CJ13-044 X 1	
Ultrafilter	SMF 4/2,5	4IJ15-040 X 1	
Ultrafilter	SMF 5/2,5	4IJN15-050 X 1	
Ultrafilter	SMF 5/3	4IJ25-050 X 1	
Ultrafilter	SMF 10/3	4IJ25-100 X 1	
Ultrafilter	SMF 15/3	4IG25-150 X 1	
Ultrafilter	SMF 20/3	4IG25-200 X 1	
Ultrafilter	SMF 30/3	4IG25-300 X 1	
Ultrafilter	SMF 30/5	4QG43-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Active Carbon Filters			
Ultrafilter	AK 3/1	AJ10-030 X 1	
Ultrafilter	AK 3/1,5	AJ13-030 X 1	
Ultrafilter	AK 4/1,5	AJ13-044 X 1	
Ultrafilter	AK 4/2,5	AJ15-040 X 1	
Ultrafilter	AK 5/2,5	AJN15-050 X 1	
Ultrafilter	AK 5/3	AJ25-050 X 1	
Ultrafilter	AK 10/3	AJ25-100 X 1	
Ultrafilter	AK 15/3	AG25-150 X 1	
Ultrafilter	AK 20/3	AG25-200 X 1	
Ultrafilter	AK 30/3	AG25-300 X 1	
Ultrafilter	AK 30/5	AG43-300 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
90 Series			
Prefilters			
Ultrafilter	PE 02/05	12GJN08-024 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Ultrafilter	PE 03/05	12GJN08-030 X 1	
Ultrafilter	PE 03/10	3PJN10-030 X 1	
Ultrafilter	PE 04/10	3PJN10-040 X 1	
Ultrafilter	PE 04/20	3PJN13-040 X 1	
Ultrafilter	PE 05/20	3PJN13-050 X 1	
Ultrafilter	PE 05/25	3PJN15-050 X 1	
Ultrafilter	PE 07/25	3PJN15-070 X 1	
Ultrafilter	PE 07/30	3PJN25-070 X 1	
Ultrafilter	PE 10/30	3PJN25-100 X 1	
Ultrafilter	PE 15/30	3PGN25-150 X 1	
Ultrafilter	PE 20/30	3PGN25-200 X 1	
Ultrafilter	PE 30/30	3PGN25-300 X 1	
Ultrafilter	PE 30/50	3PGN43-300 X 1	

Fine Filters

Ultrafilter	FF 02/05	10HJN08-024 X 1	
Ultrafilter	FF 03/05	10HJN08-030 X 1	
Ultrafilter	FF 03/10	10CJN10-030 X 1	
Ultrafilter	FF 04/10	10CJN10-040 X 1	
Ultrafilter	FF 04/20	10CJN13-040 X 1	
Ultrafilter	FF 05/20	10CJN13-050 X 1	
Ultrafilter	FF 05/25	10IJN15-050 X 1	
Ultrafilter	FF 07/25	10IJN15-070 X 1	
Ultrafilter	FF 07/30	10IJN25-070 X 1	
Ultrafilter	FF 10/30	10IJN25-100 X 1	
Ultrafilter	FF 15/30	10IGN25-150 X 1	
Ultrafilter	FF 20/30	10IGN25-200 X 1	
Ultrafilter	FF 30/30	10IGN25-300 X 1	
Ultrafilter	FF 30/50	10QGN43-300 X 1	

Micro Filters

Ultrafilter	MF 02/05	6HJN08-024 X 1	
Ultrafilter	MF 03/05	6HJN08-030 X 1	
Ultrafilter	MF 03/10	6CJN10-030 X 1	
Ultrafilter	MF 04/10	6CJN10-040 X 1	
Ultrafilter	MF 04/20	6CJN13-040 X 1	
Ultrafilter	MF 05/20	6CJN13-050 X 1	
Ultrafilter	MF 05/25	6IJN15-050 X 1	
Ultrafilter	MF 07/25	6IJN15-070 X 1	
Ultrafilter	MF 07/30	6IJN25-070 X 1	
Ultrafilter	MF 10/30	6IJN25-100 X 1	
Ultrafilter	MF 15/30	6IGN25-150 X 1	
Ultrafilter	MF 20/30	6IGN25-200 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Ultrafilter	MF 30/30	6IGN25-300 X 1	
Ultrafilter	MF 30/50	6QGN43-300 X 1	

Sub Micro Filters

Ultrafilter	SMF 02/05	4HJN08-024 X 1	
Ultrafilter	SMF 03/05	4HJN08-030 X 1	
Ultrafilter	SMF 03/10	4CJN10-030 X 1	
Ultrafilter	SMF 04/10	4CJN10-040 X 1	
Ultrafilter	SMF 04/20	4CJN13-040 X 1	
Ultrafilter	SMF 05/20	4CJN13-050 X 1	
Ultrafilter	SMF 05/25	4IJN15-050 X 1	
Ultrafilter	SMF 07/25	4IJN15-070 X 1	
Ultrafilter	SMF 07/30	4IJN25-070 X 1	
Ultrafilter	SMF 10/30	4IJN25-100 X 1	
Ultrafilter	SMF 15/30	4IGN25-150 X 1	
Ultrafilter	SMF 20/30	4IGN25-200 X 1	
Ultrafilter	SMF 30/30	4IGN25-300 X 1	
Ultrafilter	SMF 30/50	4QGN43-300 X 1	

Active Carbon Filters

Ultrafilter	AK 02/05	AJN08-024 X 1	
Ultrafilter	AK 03/05	AJN08-030 X 1	
Ultrafilter	AK 03/10	AJN10-030 X 1	
Ultrafilter	AK 04/10	AJN10-040 X 1	
Ultrafilter	AK 04/20	AJN13-040 X 1	
Ultrafilter	AK 05/20	AJN13-050 X 1	
Ultrafilter	AK 05/25	AJN15-050 X 1	
Ultrafilter	AK 07/25	AJN15-070 X 1	
Ultrafilter	AK 07/30	AJN25-070 X 1	
Ultrafilter	AK 10/30	AJN25-100 X 1	
Ultrafilter	AK 15/30	AGN25-150 X 1	
Ultrafilter	AK 20/30	AGN25-200 X 1	
Ultrafilter	AK 30/30	AGN25-300 X 1	
Ultrafilter	AK 30/50	AGN43-300 X 1	

Process Gas Elements

Ultrafilter	P-AK 07/30	AGN25-070 X 1	
Ultrafilter	P-AK 10/30	AGN25-100 X 1	
Ultrafilter	P-FF 07/30	10IJN25-070 X 1	
Ultrafilter	P-FF 10/30	10IJN25-100 X 1	
Ultrafilter	P-MF 07/30	6IGN25-070 X 1	
Ultrafilter	P-MF 10/30	6IGN25-100 X 1	
Ultrafilter	P-PE 07/30	3PGN25-070 X 1	
Ultrafilter	P-PE 10/30	3PGN25-100 X 1	
Ultrafilter	P-SMF 07/30	4IGN25-070 X 1	
Ultrafilter	P-SMF 10/30	4IGN25-100 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Van Air			
Van Air	CE-8/60	6CC15-060 X 2	
Van Air	CE-8/100	6CC15-080 X 2	
Van Air	CE-15	6CC15-150 X 2	
Van Air	CE-22/500	6ICC25-220 X 1	
Van Air	CXE-8/60	2CC15-060 X 2	
Van Air	CXE-8/100	2CC15-080 X 2	
Van Air	CXE-15	2CC15-150 X 2	
Van Air	CXE-22/350	2ICC25-220 X 1	
Van Air	KE-6/60	3PC15-060 X 2	
Van Air	KE-6/100	3PC15-080 X 2	
Van Air	KE-15	3PC15-150 X 2	
Van Air	KE-22	3PCC25-220 X 1	
Van Air	KE-15HT	10DC15-150 X 2	
Van Air	KE-22HT	10DC25-220 X 1	
E100 Series			
Van Air	E100-100-B	8CC25-059 X 1	
Van Air	E100-100-C	6CC25-059 X 1	
Van Air	E100-100-RA	3PC25-059 X 1	
Van Air	E100-100-RD	AC25-059 X 1	
E101/102 Series			
Van Air	E101/102-500-A	10ICC25-240 X 1	
Van Air	E101/102-500-B	8ICC25-240 X 1	
Van Air	E101/102-500-C	6ICC25-240 X 1	
Van Air	E101/102-500-RA	10DC25-240 X 1	
Van Air	E101/102-500-RB	8DC25-240 X 1	
Van Air	E101/102-500-RC	6DC25-240 X 1	
Van Air	E101/102-500-HT	10DC25-240 X 1	
Van Air	E101/102-625-A	10ICC25-300 X 1	
Van Air	E101/102-625-B	8ICC25-300 X 1	
Van Air	E101/102-625-C	6ICC25-300 X 1	
Van Air	E101/102-625-RA	10DC25-300 X 1	
Van Air	E101/102-625-RB	8DC25-300 X 1	
Van Air	E101/102-625-RC	6DC25-300 X 1	
Van Air	E101/102-625-HT	10DC25-300 X 1	
E200 Series			
Van Air	E200-265-C	6CC25-117 X 1	
Van Air	E200-265-B	8CC25-117 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Van Air	E200-265-RD	AC25-117 X 1	
Van Air	E200-265-RA	3PC25-117 X 1	
Van Air	E200-265-RB	8DC25-117 X 1	
Watts			
Watts	EKF507	10HM06-013 X 10	
Watts	EKF604	10HM10-022 X 8	KX-26
Standard Series Coalescing			
Watts	EKF501H	6HM06-013 X 10	
Watts	EKF601J	6CM10-025 X 8	KX-21
Watts	EKF601K	6CM10-050 X 4	KX-22
Watts	EKF601L	6CM15-060 X 4	KX-23
Watts	EK600D	6CM15-185 X 2	KX-25
Watts	EK600ND	*6CM15-185 X 2	KX-25
Watts	EK-600NB	6CM15-060 X 4	KX-23
Qube Series Coalescing			
Watts	EKF31	6H06-018 X 10	
Watts	EKF51	6H08-015 X 10	
Watts	EKF101	6H10-029 X 8	
Note: Kits are required for initial conversion only.			
*Replacement unit is slightly smaller than original unit.			
Wilkerson			
5 Micron Particulate (Type A or Oil Removal)			
Wilkerson	FRP-95-115	14JU10-020 X 10	
Wilkerson	FRP-95-160	14JU07-013 X 10	
Wilkerson	FRP-95-267	14JU07-013 X 10	
Wilkerson	FRP-95-236	14JU10-020 X 10	
Wilkerson	FRP-95-268	14JU10-020 X 10	
Wilkerson	FRP-95-206	14JU10-020 X 10	
Wilkerson	FRP-95-269	14JU10-020 X 10	
Wilkerson	FRP-95-209	14JU15-043 X 10	
Wilkerson	FRP-95-210	14JU15-043 X 10	
Wilkerson	FRP-95-271	14JU15-043 X 10	
Wilkerson	FRP-95-272	14JU15-043 X 10	
Wilkerson	FRP-95-172	14JU26-075 X 4	
Wilkerson	FRP-95-273	14JU26-075 X 4	
Wilkerson	FRP-95-203	14JU26-075 X 4	
Wilkerson	FRP-95-274	14JU26-075 X 4	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Wilkerson	FRP-95-566	14JU26-075 X 4	
Wilkerson	FRP-95-567	14JU26-075 X 4	
Wilkerson	FRP-95-212	14JU26-120 X 4	
Wilkerson	FRP-85-168	14JU26-120 X 4	
Wilkerson	FRP-85-169	14JU26-240 X 4	
Wilkerson	FRP-95-213	14JU26-240 X 4	

Coalescer Type B

Wilkerson	MSP-95-556	8CK25-119 X 2	
Wilkerson	MSP-95-557	8CK25-238 X 1	
Wilkerson	MSP-95-874	8CK35-074 X 2	
Wilkerson	MSP-95-875	8CK35-106 X 1	
Wilkerson	MSP-95-876	8CK35-172 X 1	
Wilkerson	MSP-95-988	8HL10-021 X 4	
Wilkerson	MSP-95-989	8CL10-024 X 4	
Wilkerson	MSP-95-992	8CK15-052 X 4	

Coalescer Type C

Wilkerson	MRP-15-143	6CK35-074 X 2	
Wilkerson	MRP-15-411	6CU10-052 X 4	KY-2
Wilkerson	MRP-15-412	6CL25-063 X 2	
Wilkerson	MRP-15-441	6CU10-052 X 4	KY-2
Wilkerson	MRP-15-508	6CK25-119 X 2	
Wilkerson	MRP-15-513	6CK25-238 X 1	
Wilkerson	MSP-95-873	8CK25-080 X 2	
Wilkerson	MTP-95-547	6HK04-013 X 10	
Wilkerson	MTP-95-548	6HL10-021 X 4	
Wilkerson	MTP-95-549	6CL10-024 X 4	
Wilkerson	MTP-95-550	6CU10-052 X 4	KY-2
Wilkerson	MTP-95-551	6CK15-052 X 4	
Wilkerson	MTP-95-552	6CL25-063 X 2	
Wilkerson	MTP-95-553	6CK35-074 X 2	
Wilkerson	MTP-95-554	6CK25-119 X 2	
Wilkerson	MTP-95-555	6CK25-238 X 1	
Wilkerson	MTP-95-559	6CK25-080 X 2	
Wilkerson	MTP-95-560	6CK35-074 X 2	
Wilkerson	MTP-95-561	6CK35-106 X 1	
Wilkerson	MTP-95-562	6CK35-172 X 1	

Adsorber Type D

Wilkerson	MRP-15-532	AU10-052 X 4	KY-2
Wilkerson	MRP-15-533	AK25-119 X 2	
Wilkerson	MRP-15-534	AK25-238 X 1	
Wilkerson	MRP-15-535	AL25-063 X 2	
Wilkerson	MRP-15-536	AU10-021 X 1	KY-1
Wilkerson	MRP-15-537	AU10-052 X 4	KY-2
Wilkerson	MRP-15-538	AK35-074 X 2	
Wilkerson	MRP-95-534	AK25-238 X 1	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Wilkerson	MXP-95-538	AK35-074 X 2	
Wilkerson	MXP-15-533	AK25-119 X 2	
Wilkerson	MXP-95-532	AK15-052 X 4	
Wilkerson	MXP-95-535	AL25-063 X 2	
Wilkerson	MXP-95-536	AU10-021 X 8	KY-1
Wilkerson	MXP-95-540	AL10-024 X 4	
Wilkerson	MXP-95-558	AK25-080 X 2	
Wilkerson	MXP-95-563	AK35-074 X 2	
Wilkerson	MXP-95-564	AK35-106 X 1	
Wilkerson	MXP-95-565	AK35-172 X 1	
Wilkerson	MXP-95-987	AL10-021 X 4	

Note: Kits are required for initial conversion only.

Zander

Zander	1030 (A, V, X, Y or Z)	*Z07-020 X 1	
Zander	1050 (A, V, X, Y or Z)	*Z12-023 X 1	
Zander	1070 (A, V, X, Y or Z)	*Z12-029 X 1	
Zander	1140 (A, V, X, Y or Z)	*Z12-056 X 1	
Zander	2010 (A, V, X, Y or Z)	*Z20-046 X 1	
Zander	2020 (A, V, X, Y or Z)	*Z20-086 X 1	
Zander	2030 (A, V, X, Y or Z)	*Z20-126 X 1	
Zander	2050 (A, V, X, Y or Z)	*Z20-200 X 1	
Zander	3050 (A, V, X, Y or Z)	*Z27-200 X 1	
Zander	3075 (A, V, X, Y or Z)	*Z27-298 X 1	
Zander	5060 (A, V, X, Y or Z)	*Z46-239 X 1	
Zander	5075 (A, V, X, Y or Z)	*Z50-298 X 1	

*Pore Structure Conversion Chart

Use this chart to determine the **Finite®** equivalent to the specified Zander grade.

Zander Media Designation	Finite® Element Grade
A	A (Adsorber)
V	3P (Particulate)
X	6C (Coalescer)
Y	8C (Coalescer)
Z	10C (Coalescer)

Example: Zander 2030X = **Finite®** 6CZ20-126 X 1

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Zeks			
Accraflow			
Zeks	P30	3PZ10-025	
Zeks	P75	3PZ10-050	
Zeks	P150	3PZ15-060	
Zeks	P275	3PZ15-095	
Zeks	P330	3PZ19-095	
Zeks	P500	3PZ19-193	
Zeks	P670	3PZ19-193	
Accrasieve			
Zeks	R25	10CZ10-025	
Zeks	R60	10CZ10-050	
Zeks	R80	10CZ15-060	
Zeks	R130	10CZ15-060	
Zeks	R230	10CZ15-095	
Zeks	R300	10CZ19-095	
Zeks	R450	10CZ19-193	
Zeks	R600	10CZ19-193	
Accralescor			
Zeks	L18	6CZ10-025	
Zeks	L50	6CZ10-050	
Zeks	L80	6CZ15-060	
Zeks	L100	6CZ15-060	
Zeks	L140	6CZ15-095	
Zeks	L200	6CZ19-095	
Zeks	L300	6CZ19-193	
Zeks	L400	6CZ19-193	
Accrasorb			
Zeks	A18	AZ10-025	
Zeks	A50	AZ10-050	
Zeks	A80	AZ15-060	
Zeks	A100	AZ15-060	
Zeks	A140	AZ15-095	
Zeks	A200	AZ19-095	
Zeks	A300	AZ19-193	
Zeks	A400	AZ19-193	
Accratemp			
Zeks	H130	10DZ15-060	
Zeks	H230	10DZ15-095	
Zeks	H300	10DZ19-095	
Zeks	H450	10DZ19-193	
Zeks	H600	10DZ19-193	

Competitor	Competitor Part Number	Finite® Part Number	Kit Required
Zurn/General Air Dryer			
Particulate Filters			
Zurn	74635-22	12R10-025 X 8	
Zurn	74635-24	12RM10-055 X 4	
Zurn	74635-26	12R15-060 X 4	
Zurn	74635-75	12R20-130 X 2	
Zurn	74635-32	12R20-187 X 1	
Zurn	74635-40	12RD20-187 X 1	
Zurn	74635-90	12RXC20-187 X 1	KV-25
Zurn	74635-139	3PU51-380 X 1	
Coalescing Filters			
Zurn	74635-21	6N10-025 X 8	
Zurn	74635-23	6CM10-055 X 4	
Zurn	74635-25	6N15-060 X 4	
Zurn	74635-74	6N20-130 X 2	
Zurn	74635-31	6N20-187 X 1	
Zurn	74635-39	6ND20-187 X 1	
Zurn	74635-133	6QU51-380 X 1	
Zurn	74635-134	6QU80-380 X 1	
Odorguard			
Zurn	74635-77	AU10-025 X 8	
Zurn	74635-78	AU10-055 X 4	
Zurn	74635-80	AU15-060 X 4	
Zurn	74635-76	AU20-130 X 2	
Zurn	74635-79	AU20-187 X 1	
Zurn	74635-50	AD20-187 X 1	
Zurn	74635-145	AU51-380 X 1	
Zurn	74635-146	AU80-380 X 1	
Note: Kits are required for initial conversion only.			

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
050-03*	*G04-010 X 10	Balston	
050-03*Q	*T04-010 X 10	Balston	
050-03-BX	6H04-010 X 10	Balston	
050-03-CX	8H04-010 X 10	Balston	
050-03-DX	10H04-010 X 10	Balston	
050-05-*	*G04-013 X 10	Balston	
050-05*Q	*T04-013 X 10	Balston	
050-05-BX	6H04-013 X 10	Balston	
050-05-CX	8H04-013 X 10	Balston	
050-05-DX	10H04-013 X 10	Balston	
050-11-*	*G04-023 X 10	Balston	
050-11*Q	*T04-023 X 10	Balston	
050-11-BH	6T04-023 X 10	Balston	
050-11-BX	6H04-023 X 10	Balston	
050-11-CX	8H04-023 X 10	Balston	
050-11-DH	10T04-023 X 10	Balston	
050-11-DX	10H04-023 X 10	Balston	
0713-11*	6CH25-260 X 1	Hankison	
0713-12*	6CU25-187 X 1	Hankison	KX-2
0713-2	6CM10-025 X 8	Hankison	KX-21
0713-3	6CM10-050 X 4	Hankison	KX-22
0713-4	6CM15-060 X 4	Hankison	KX-23
0713-5	6CM15-095 X 2	Hankison	KX-24
0713-6	6CM15-185 X 2	Hankison	KX-25
0713-7	6CU25-187 X 1	Hankison	KX-2
0713-8	6CU25-187 X 1	Hankison	KX-2
0713-9	6CH25-260 X 1	Hankison	
0715-11*	AH25-260 X 1	Hankison	
0715-2	AM10-025 X 8	Hankison	KX-21
0715-3	AM10-050 X 4	Hankison	KX-22
0715-4	AM15-060 X 4	Hankison	KX-23
0715-5	AM15-095 X 2	Hankison	KX-24
0715-6	AM15-185 X 2	Hankison	KX-25
0715-7	AU25-187 X 1	Hankison	KX-2
0715-8	AU25-187 X 1	Hankison	KX-2
0715-9	AH25-260 X 1	Hankison	
0731-3	10CM10-025 X 8	Hankison	KX-21
0731-4	10CM10-050 X 4	Hankison	KX-22
0731-5	10CM15-060 X 4	Hankison	KX-23
0731-6	10CM15-095 X 2	Hankison	KX-24
0731-7	10CM15-185 X 2	Hankison	KX-25
0731-8	10CU25-187 X 1	Hankison	KX-2
0731-9*	10CH25-260 X 1	Hankison	
0740-4	10DH25-260 X 1	Hankison	
0812-1	6CE63-118 X 1	Henderson	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
0812-1	3PE63-118 X 1	Henderson	
10" (80 Series)	6CP15-100 X 2	Cuno	
10" (80 Series)	AP15-100 X 2	Cuno	
10" Element	6CP15-100 X 2	Filterite	
10" Element	3PP15-100 X 2	Filterite	
10" Element	AP15-100 X 2	Filterite	
100-09-BX	6H10-020 X 8	Balston	
100-09-CX	8H10-020 X 8	Balston	
100-09-DX	10H10-020 X 8	Balston	
100-12-*	*G10-025 X 10	Balston	
100-12*Q	*T10-025 X 10	Balston	
100-12-BH	6T10-025 X 10	Balston	
100-12-BX	6H10-025 X 8	Balston	
100-12-CX	8H10-025 X 8	Balston	
100-12-DH	10T10-025 X 10	Balston	
100-12-DX	10H10-025 X 8	Balston	
100-18-BX	6H10-050 X 4	Balston	
100-18-CX	8H10-050 X 4	Balston	
100-18-DX	10H10-050 X 4	Balston	
100-25-*	*G10-070 X 10	Balston	
100-25*Q	*T10-070 X 10	Balston	
100-25-BH	6T10-070 X 10	Balston	
100-25-BX	6H10-070 X 4	Balston	
100-25-CX	8H10-070 X 4	Balston	
100-25-DH	10T10-070 X 10	Balston	
100-25-DX	10H10-070 X 4	Balston	
1030	*Z07-020 X 1	Zander	
1050	*Z12-023 X 1	Zander	
1070	*Z12-029 X 1	Zander	
1140	*Z12-056 X 1	Zander	
12-32-50C	6H04-013 X 10	Headline	
12-32-50K	6T04-013 X 10	Headline	
12-32-70C	10H04-013 X 10	Headline	
12-32-70K	10T04-013 X 10	Headline	
12-57-50C	6H04-023 X 10	Headline	
12-57-50K	6T04-023 X 10	Headline	
12-57-70C	10H04-023 X 10	Headline	
12-57-70K	10T04-023 X 10	Headline	
129360-802	6G10-025 X 10	Steris	
1350	8DU51-100 X 1	Pure Air	KV-22
1351	8DU51-128 X 1	Pure Air	KV-22
1352	8DU78-165 X 1	Pure Air	KV-24
1353	8CU145-200 X 1	Pure Air	
1357	6CJ25-120 X 2	Pure Air	
1358	6CJ25-120 X 2	Pure Air	

*Please refer to appropriate competitor section for complete conversion details.



Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
1359	6CJ25-240 X 1	Pure Air	
1360	6CJ25-240 X 1	Pure Air	
1361	6CJ25-240 X 1	Pure Air	
1362	6CJ25-240 X 1	Pure Air	
1367	6CJ25-240 X 1	Pure Air	
1368	6CJ25-240 X 1	Pure Air	
1370	AJ25-240 X 1	Pure Air	
1372	AJ25-120 X 2	Pure Air	
1373	AJ25-120 X 2	Pure Air	
1375	AJ25-240 X 1	Pure Air	
1377	AJ25-240 X 1	Pure Air	
1378	AJ25-240 X 1	Pure Air	
1379	AJ25-240 X 1	Pure Air	
1406	6CN25-080 X 2	Pure Air	
1407	6CJ25-120 X 2	Pure Air	
1408	6CJ25-240 X 1	Pure Air	
1408	6CJ25-240 X 1	Pure Air	
1411	AJ25-080 X 2	Pure Air	
1412	AJ25-120 X 2	Pure Air	
1413	AJ25-240 X 1	Pure Air	
1418	AJ25-240 X 1	Pure Air	
150-19-*	*G15-060 X 10	Balston	
150-19-*Q	*T15-060 X 10	Balston	
150-19-BX	6H15-060 X 4	Balston	
150-19-CX	8H15-060 X 4	Balston	
150-19-DX	10H15-060 X 4	Balston	
16D100	6CU19-130 X 2	Henderson	KX-14
16D150	6CU19-187 X 1	Henderson	KX-16
16D33	6CU19-050 X 2	Henderson	KX-12
16D50	6CU19-070 X 2	Henderson	KX-13
20" Element	6CP15-198 X 2	Filterite	
20" Element	3PP15-198 X 2	Filterite	
20" Element	AP15-198 X 2	Filterite	
200-16-BX	6H20-035 X 4	Balston	
200-16-CX	8H20-035 X 4	Balston	
200-16-DX	10H20-035 X 4	Balston	
200-35-*	*G20-090 X 10	Balston	
200-35-*Q	*T20-090 X 10	Balston	
200-35-BH	6T20-090 X 10	Balston	
200-35-BX	6H20-090 X 2	Balston	
200-35-CX	8H20-090 X 2	Balston	
200-35-DX	10H20-090 X 2	Balston	
200-80-*	*G20-187 X 10	Balston	
200-80-*Q	*T20-187 X 10	Balston	
200-80-BX	6H20-187 X 1	Balston	
200-80-CX	8H20-187 X 1	Balston	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
200-80-DX	10H20-187 X 1	Balston	
2010	*Z20-046 X 1	Zander	
2020	*Z20-086 X 1	Zander	
2030	*Z20-126 X 1	Zander	
2050	*Z20-200 X 1	Zander	
245-3	3PE15-050 X 4	Henderson	
250024-423	10CF08-026 X 1	Sullair	
250024-424	10IF10-032 X 1	Sullair	
250024-425	10IF10-046 X 1	Sullair	
250024-426	10IF20-063 X 1	Sullair	
250024-427	10IF20-102 X 1	Sullair	
250024-428	10IF25-134 X 1	Sullair	
250024-429	10IF25-254 X 1	Sullair	
250024-430	10CF35-251 X 1	Sullair	
250024-431	6CF08-026 X 1	Sullair	
250024-432	6IF10-032 X 1	Sullair	
250024-433	6IF10-046 X 1	Sullair	
250024-434	6IF20-063 X 1	Sullair	
250024-435	6IF20-102 X 1	Sullair	
250024-436	6IF25-134 X 1	Sullair	
250024-437	6IF25-254 X 1	Sullair	
250024-438	6CF35-251 X 1	Sullair	
250030-644	10CF35-165 X 1	Sullair	
25-127-50C	6H10-050 X 4	Headline	
25-127-70C	10H10-050 X 4	Headline	
25-178-50C	6H10-070 X 4	Headline	
25-178-50K	6T10-070 X 10	Headline	
25-178-70C	10H10-070 X 4	Headline	
25-178-70K	10T10-070 X 10	Headline	
25-64-50C	6H10-025 X 8	Headline	
25-64-50K	6T10-025 X 10	Headline	
25-64-70C	10H10-025 X 8	Headline	
25-64-70K	10T10-025 X 10	Headline	
3-3/4" (30 Series)	6CP15-038 X 4	Cuno	
3050	*Z27-200 X 1	Zander	
3075	*Z27-298 X 1	Zander	
38-152-50C	6H15-060 X 4	Headline	
38-152-50K	6T15-060 X 10	Headline	
38-152-70C	10H15-060 X 4	Headline	
38-152-70K	10T15-060 X 10	Headline	
5060	*Z46-239 X 1	Zander	
5075	*Z50-298 X 1	Zander	
51-230-50C	6H20-090 X 2	Headline	
51-230-50K	6T20-090 X 10	Headline	
51-230-70C	10H20-090 X 2	Headline	

*Please refer to appropriate competitor section for complete conversion details.



Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
51-230-70K	10T20-090 X 10	Headline	
51-476-50C	6H20-187 X 1	Headline	
51-476-50K	6T20-187 X 10	Headline	
51-476-70C	10H20-187 X 1	Headline	
51-476-70K	10T20-187 X 10	Headline	
51-89-50C	6H20-035 X 4	Headline	
51-89-70C	10H20-035 X 4	Headline	
532-221	8CF20-051 X 2	Busch	
532-302	8CF20-099 X 2	Busch	
532-303	8CF20-147 X 1	Busch	
532-304	8CF20-197 X 1	Busch	
74635-133	6QU51-380 X 1	Zurn	
74635-134	6QU80-380 X 1	Zurn	
74635-139	3PU51-380 X 1	Zurn	
74635-145	AU51-380 X 1	Zurn	
74635-146	AU80-380 X 1	Zurn	
74635-21	6N10-025 X 8	Zurn	
74635-22	12R10-025 X 8	Zurn	
74635-23	6CM10-055 X 4	Zurn	
74635-24	12RM10-055 X 4	Zurn	
74635-25	6N15-060 X 4	Zurn	
74635-26	12R15-060 X 4	Zurn	
74635-31	6N20-187 X 1	Zurn	
74635-32	12R20-187 X 1	Zurn	
74635-39	6ND20-187 X 1	Zurn	
74635-40	12RD20-187 X 1	Zurn	
74635-50	AD20-187 X 1	Zurn	
74635-74	6N20-130 X 2	Zurn	
74635-75	12R20-130 X 2	Zurn	
74635-76	AU20-130 X 2	Zurn	
74635-77	AU10-025 X 8	Zurn	
74635-78	AU10-055 X 4	Zurn	
74635-79	AU20-187 X 1	Zurn	
74635-80	AU15-060 X 4	Zurn	
74635-90	12RXC20-187 X 1	Zurn	KV-25
86-972	6HU20-070 X 2	Binks	
86-982	6HU10-050 X 4	Binks	
8D20	6CN10-028 X 8	Henderson	KX-10
8D28	6CN10-038 X 4	Henderson	KX-11
9-3/4" (78 Series)	6CP15-098 X 2	Cuno	
9-3/4" (78 Series)	AP15-098 X 2	Cuno	
9900-05-BK	SDN-O X 10	Balston	
9933-05-BQ	IDN-6G X 10	Balston	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
9933-05-DQ	IDN-10G X 10	Balston	
A002/05	6HJN08-024 X 1	Domnick Hunter	
A003/05	6HJN08-030 X 1	Domnick Hunter	
A003/10	6CJN10-030 X 1	Domnick Hunter	
A004/10	6CJN10-040 X 1	Domnick Hunter	
A004/20	6CJN13-040 X 1	Domnick Hunter	
A005/20	6CJN13-050 X 1	Domnick Hunter	
A005/25	6IJN15-050 X 1	Domnick Hunter	
A007/25	6IJN15-070 X 1	Domnick Hunter	
A007/30	6IJN25-070 X 1	Domnick Hunter	
A010/3	6IJ25-100 X 1	Domnick Hunter	
A010/30	6IJN25-100 X 1	Domnick Hunter	
A015/3	6IG25-150 X 1	Domnick Hunter	
A015/30	6IGN25-150 X 1	Domnick Hunter	
A020/3	6IG25-200 X 1	Domnick Hunter	
A020/30	6IGN25-200 X 1	Domnick Hunter	
A03/1	6CJ10-030 X 1	Domnick Hunter	
A03/1.5	6CJ13-030 X 1	Domnick Hunter	
A030/3	6IG25-300 X 1	Domnick Hunter	
A030/30	6IGN25-300 X 1	Domnick Hunter	
A030/5	6QG43-300 X 1	Domnick Hunter	
A030/50	6QGN43-300 X 1	Domnick Hunter	
A04/1.5	6CJ13-044 X 1	Domnick Hunter	
A04/2.5	6IJ15-040 X 1	Domnick Hunter	
A05/2.5	6IJN15-050 X 1	Domnick Hunter	
A05/3	6IJ25-050 X 1	Domnick Hunter	
A100	AZ15-060	Zeks	
A140	AZ15-095	Zeks	
A18	AZ10-025	Zeks	
A200	AZ19-095	Zeks	
A300	AZ19-193	Zeks	
A400	AZ19-193	Zeks	
A4000-604	4CL10-024 X 8	Johnson Controls	
A4000-605	4CL10-053 X 4	Johnson Controls	
A4000-606	6CL25-063 X 2	Johnson Controls	
A4000-627	4CL10-024 X 8	Johnson Controls	
A4000-628	4CL10-053 X 4	Johnson Controls	
A4000-629	6CL25-063 X 2	Johnson Controls	
A50	AZ10-050	Zeks	
A80	AZ15-060	Zeks	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
AA02/05	4HJN08-024 X 1	Domnick Hunter	
AA03/05	4HJN08-030 X 1	Domnick Hunter	
AA03/10	4CJN10-030 X 1	Domnick Hunter	
AA04/10	4CJN10-040 X 1	Domnick Hunter	
AA04/20	4CJN13-040 X 1	Domnick Hunter	
AA05/20	4CJN13-050 X 1	Domnick Hunter	
AA05/25	4IJN15-050 X 1	Domnick Hunter	
AA07/25	4IJN15-070 X 1	Domnick Hunter	
AA07/30	4IJN25-070 X 1	Domnick Hunter	
AA10/3	6IJ25-100 X 1	Domnick Hunter	
AA10/30	4IJN25-100 X 1	Domnick Hunter	
AA15/3	6IG25-150 X 1	Domnick Hunter	
AA15/30	4IGN25-150 X 1	Domnick Hunter	
AA20/3	6IG25-200 X 1	Domnick Hunter	
AA20/30	4IGN25-200 X 1	Domnick Hunter	
AA3/1	6CJ10-030 X 1	Domnick Hunter	
AA3/1.5	6CJ13-030 X 1	Domnick Hunter	
AA30/3	6IG25-300 X 1	Domnick Hunter	
AA30/30	4IGN25-300 X 1	Domnick Hunter	
AA30/5	6QG43-300 X 1	Domnick Hunter	
AA30/50	4QGN43-300 X 1	Domnick Hunter	
AA4/1.5	6CJ13-044 X 1	Domnick Hunter	
AA4/2.5	6IJ15-040 X 1	Domnick Hunter	
AA5/2.5	6IJN15-050 X 1	Domnick Hunter	
AA5/3	6IJ25-050 X 1	Domnick Hunter	
AC 02/05	AJN08-024 X 1	Domnick Hunter	
AC 03/05	AJN08-030 X 1	Domnick Hunter	
AC 03/10	AJN10-030 X 1	Domnick Hunter	
AC 04/10	AJN10-040 X 1	Domnick Hunter	
AC 04/20	AJN13-040 X 1	Domnick Hunter	
AC 05/20	AJN13-050 X 1	Domnick Hunter	
AC 05/25	AJN15-050 X 1	Domnick Hunter	
AC 07/25	AJN15-070 X 1	Domnick Hunter	
AC 07/30	AJN25-070 X 1	Domnick Hunter	
AC 10/30	AJN25-100 X 1	Domnick Hunter	
AC 15/30	AGN25-150 X 1	Domnick Hunter	
AC 20/30	AGN25-200 X 1	Domnick Hunter	
AC 30/30	AGN25-300 X 1	Domnick Hunter	
AC 30/50	AGN43-300 X 1	Domnick Hunter	
AC10/3	AJ25-100 X 1	Domnick Hunter	
AC15/3	AG25-150 X 1	Domnick Hunter	
AC20/3	AG25-200 X 1	Domnick Hunter	
AC3/1	AJ10-030 X 1	Domnick Hunter	
AC3/1.5	AJ13-030 X 1	Domnick Hunter	
AC30/3	AG25-300 X 1	Domnick Hunter	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
AC30/5	AG43-300 X 1	Domnick Hunter	
AC4/1.5	AJ13-044 X 1	Domnick Hunter	
AC4/2.5	AJ15-040 X 1	Domnick Hunter	
AC5/2.5	AJN15-050 X 1	Domnick Hunter	
AC5/3	AJ25-050 X 1	Domnick Hunter	
AK 02/05	AJN08-024 X 1	Ultrafilter	
AK 03/05	AJN08-030 X 1	Ultrafilter	
AK 03/10	AJN10-030 X 1	Ultrafilter	
AK 04/10	AJN10-040 X 1	Ultrafilter	
AK 04/20	AJN13-040 X 1	Ultrafilter	
AK 05/20	AJN13-050 X 1	Ultrafilter	
AK 05/25	AJN15-050 X 1	Ultrafilter	
AK 07/25	AJN15-070 X 1	Ultrafilter	
AK 07/30	AJN25-070 X 1	Ultrafilter	
AK 10/3	AJ25-100 X 1	Ultrafilter	
AK 10/30	AJN25-100 X 1	Ultrafilter	
AK 15/3	AG25-150 X 1	Ultrafilter	
AK 15/30	AGN25-150 X 1	Ultrafilter	
AK 20/3	AG25-200 X 1	Ultrafilter	
AK 20/30	AGN25-200 X 1	Ultrafilter	
AK 3/1	AJ10-030 X 1	Ultrafilter	
AK 3/1,5	AJ13-030 X 1	Ultrafilter	
AK 30/3	AG25-300 X 1	Ultrafilter	
AK 30/30	AGN25-300 X 1	Ultrafilter	
AK 30/5	AG43-300 X 1	Ultrafilter	
AK 30/50	AGN43-300 X 1	Ultrafilter	
AK 4/1,5	AJ13-044 X 1	Ultrafilter	
AK 4/2,5	AJ15-040 X 1	Ultrafilter	
AK 5/2,5	AJN15-050 X 1	Ultrafilter	
AK 5/3	AJ25-050 X 1	Ultrafilter	
CC05LGH13B	6IP15-052 X 4	Pall/PPC	
CC1LG7A	6CPC20-098 X 1	Pall/PPC	
CC3LG02H13	7CRP20-290 X 1	Pall/PPC	
CC3LG7A	7CPP20-290 X 1	Pall/PPC	
CE-15	6CC15-150 X 2	Van Air	
CE-22/500	6ICC25-220 X 1	Van Air	
CE-8/100	6CC15-080 X 2	Van Air	
CE-8/60	6CC15-060 X 2	Van Air	
CI-100-12	AU10-025 X 8	Balston	
CI-100-25	AU10-070 X 4	Balston	
CI-150-19	AB15-060 X 4	Balston	
CXE-15	2CC15-150 X 2	Van Air	
CXE-22/350	2ICC25-220 X 1	Van Air	
CXE-8/100	2CC15-080 X 2	Van Air	
CXE-8/60	2CC15-060 X 2	Van Air	
DH006AA	6CF08-026 X 1	Flair	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
DH006AC	AF08-026 X 1	Flair	
DH006AO	10CF08-026 X 1	Flair	
DH013AA	6IF10-032 X 1	Flair	
DH013AC	AF10-032 X 1	Flair	
DH013AO	10IF10-032 X 1	Flair	
DH025AA	6IF10-046 X 1	Flair	
DH025AC	AF10-046 X 1	Flair	
DH025AO	10IF10-046 X 1	Flair	
DH040AA	6IF20-063 X 1	Flair	
DH040AC	AF20-063 X 1	Flair	
DH040AO	10IF20-063 X 1	Flair	
DH085AA	6IF20-102 X 1	Flair	
DH085AC	AF20-102 X 1	Flair	
DH085AO	10IF20-102 X 1	Flair	
DH195AA	6IF25-134 X 1	Flair	
DH195AC	AF25-134 X 1	Flair	
DH195AO	10IF25-134 X 1	Flair	
DH295AA	6IF25-254 X 1	Flair	
DH295AC	AF25-254 X 1	Flair	
DH295AO	10IF25-254 X 1	Flair	
DH400AA	6CF35-165 X 1	Flair	
DH400AC	AF35-165 X 1	Flair	
DH400AO	10CF35-165 X 1	Flair	
DH500AA	6CF43-252 X 1	Flair	
DH500AC	AF43-252 X 1	Flair	
DH500AO	10CF43-252 X 1	Flair	
E006AA	6CF08-026 X 1	Domnick Hunter	
E006AC	AF08-026 X 1	Domnick Hunter	
E006AO	10CF08-026 X 1	Domnick Hunter	
E013AA	6IF10-032 X 1	Domnick Hunter	
E013AC	AF10-032 X 1	Domnick Hunter	
E013AO	10IF10-032 X 1	Domnick Hunter	
E025AA	6IF10-046 X 1	Domnick Hunter	
E025AC	AF10-046 X 1	Domnick Hunter	
E025AO	10IF10-046 X 1	Domnick Hunter	
E040AA	6IF20-063 X 1	Domnick Hunter	
E040AC	AF20-063 X 1	Domnick Hunter	
E040AO	10IF20-063 X 1	Domnick Hunter	
E085AA	6IF20-102 X 1	Domnick Hunter	
E085AC	AF20-102 X 1	Domnick Hunter	
E085AO	10IF20-102 X 1	Domnick Hunter	
E100-100-B	8CC25-059 X 1	Van Air	
E100-100-C	6CC25-059 X 1	Van Air	
E100-100-RA	3PC25-059 X 1	Van Air	
E100-100-RD	AC25-059 X 1	Van Air	
E101/102-500-A	10ICC25-240 X 1	Van Air	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
E101/102-500-B	8ICC25-240 X 1	Van Air	
E101/102-500-C	6ICC25-240 X 1	Van Air	
E101/102-500-HT	10DC25-240 X 1	Van Air	
E101/102-500-RA	10DC25-240 X 1	Van Air	
E101/102-500-RB	8DC25-240 X 1	Van Air	
E101/102-500-RC	6DC25-240 X 1	Van Air	
E101/102-625-A	10ICC25-300 X 1	Van Air	
E101/102-625-B	8ICC25-300 X 1	Van Air	
E101/102-625-C	6ICC25-300 X 1	Van Air	
E101/102-625-HT	10DC25-300 X 1	Van Air	
E101/102-625-RA	10DC25-300 X 1	Van Air	
E101/102-625-RB	8DC25-300 X 1	Van Air	
E101/102-625-RC	6DC25-300 X 1	Van Air	
E1-12	AH10-020 X 1	Hankison	
E1-16	AH10-036 X 1	Hankison	
E1-20	AH10-060 X 1	Hankison	
E1-24	AHC16-066 X 1	Hankison	
E1-28	AHC16-108 X 1	Hankison	
E1-32	AHC19-131 X 1	Hankison	
E1-36	AHC19-176 X 1	Hankison	
E1-40	AHC25-204 X 1	Hankison	
E1-44	AHC25-265 X 1	Hankison	
E1-48	AHC25-323 X 1	Hankison	
E195AA	6IF25-134 X 1	Domnick Hunter	
E195AC	AF25-134 X 1	Domnick Hunter	
E195AO	10IF25-134 X 1	Domnick Hunter	
E1-PV	AH25-260 X 1	Hankison	
E200-265-B	8CC25-117 X 2	Van Air	
E200-265-C	6CC25-117 X 1	Van Air	
E200-265-RA	3PC25-117 X 4	Van Air	
E200-265-RB	8DC25-117 X 5	Van Air	
E200-265-RD	AC25-117 X 3	Van Air	
E295AA	6IF25-254 X 1	Domnick Hunter	
E295AC	AF25-254 X 1	Domnick Hunter	
E295AO	10IF25-254 X 1	Domnick Hunter	
E3-12	2CH10-020 X 1	Hankison	
E3-16	2CH10-036 X 1	Hankison	
E3-20	2CH10-060 X 1	Hankison	
E3-24	2CH16-066 X 1	Hankison	
E3-28	2CH16-108 X 1	Hankison	
E3-32	2CH19-131 X 1	Hankison	
E3-36	2CH19-176 X 1	Hankison	
E3-40	2CH25-204 X 1	Hankison	
E3-44	2CH25-265 X 1	Hankison	
E3-48	2CH25-323 X 1	Hankison	
E3-PV	2CH25-260 X 1	Hankison	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
E400AA	6CF35-165 X 1	Domnick Hunter	
E400AC	AF35-165 X 1	Domnick Hunter	
E400AO	10CF35-165 X 1	Domnick Hunter	
E500AA	6CF43-252 X 1	Domnick Hunter	
E500AC	AF43-252 X 1	Domnick Hunter	
E500AO	10CF43-252 X 1	Domnick Hunter	
E5-12	6CH10-020 X 1	Hankison	
E5-16	6CH10-036 X 1	Hankison	
E5-20	6CH10-060 X 1	Hankison	
E5-24	6CH16-066 X 1	Hankison	
E5-28	6CH16-108 X 1	Hankison	
E5-32	6CH19-131 X 1	Hankison	
E5-36	6CH19-176 X 1	Hankison	
E5-40	6CH25-204 X 1	Hankison	
E5-44	6CH25-265 X 1	Hankison	
E5-48	6CH25-323 X 1	Hankison	
E5-PV	6CH25-260 X 1	Hankison	
E620AA	6CF35-251 X 1	Domnick Hunter	
E620AC	AF35-251 X 1	Domnick Hunter	
E620AO	10CF35-251 X 1	Domnick Hunter	
E7-12	10CH10-020 X 1	Hankison	
E7-16	10CH10-036 X 1	Hankison	
E7-20	10CH10-060 X 1	Hankison	
E7-24	10CH16-066 X 1	Hankison	
E7-28	10CH16-108 X 1	Hankison	
E7-32	10CH19-131 X 1	Hankison	
E7-36	10CH19-176 X 1	Hankison	
E7-40	10CH25-204 X 1	Hankison	
E7-44	10CH25-265 X 1	Hankison	
E7-48	10CH25-323 X 1	Hankison	
E7-PV	10CH25-260 X 1	Hankison	
E9-12	100WS10-020 X 1	Hankison	
E9-16	100WS10-036 X 1	Hankison	
E9-20	100WS10-060 X 1	Hankison	
E9-24	100WS16-066 X 1	Hankison	
E9-28	100WS16-108 X 1	Hankison	
E9-32	100WS19-131 X 1	Hankison	
E9-36	100WS19-176 X 1	Hankison	
E9-40	100WS25-204 X 1	Hankison	
E9-44	100WS25-265 X 1	Hankison	
E9-48	100WS25-323 X 1	Hankison	
E9-PV	100WS25-260 X 1	Hankison	
EC100P	6CM15-060 X 4	Ultra Air	
ECS1050D	6CU32-290 X 1	Pioneer	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
ECS1250D	6CU32-350 X 1	Pioneer	
ECS155	6CU15-105 X 1	Pioneer	
ECS1650D	6QU52-290 X 1	Pioneer	
ECS2100D	6QU78-260 X 1	Pioneer	
ECS25	6CU10-035 X 1	Pioneer	
ECS250D	6IU20-133 X 1	Pioneer	
ECS3100D	6QU78-370 X 1	Pioneer	
ECS35	6CU10-035 X 1	Pioneer	
ECS350D	6IU20-195 X 1	Pioneer	
ECS450D	6CU25-198 X 1	Pioneer	
ECS60	6CU10-060 X 1	Pioneer	
ECS600D	6CU25-245 X 1	Pioneer	
ECS800D	6CU25-285 X 1	Pioneer	
EK600D	6CM15-185 X 2	Watts	KX-25
EK-600NB	6CM15-060 X 4	Watts	KX-23
EK600ND	*6CM15-185 X 2	Watts	KX-25
EKF101	6H10-029 X 8	Watts	
EKF10D	6IR04-019 X 4	Numatics	
EKF20D	6IR08-019 X 4	Numatics	
EKF30D	6IR10-034 X 4	Numatics	
EKF31	6H06-018 X 10	Watts	
EKF4 X 2	10RU25-281 X 1	Arrow	
EKF4 X 3	10RU25-281 X 1	Arrow	
EKF4 X 4	10RU25-281 X 1	Arrow	
EKF4 X 5	10RU25-281 X 1	Arrow	
EKF4 X 6	10RU25-281 X 1	Arrow	
EKF4 X 8	10RU25-281 X 1	Arrow	
EKF401	10RU07-018 X 8	Arrow	
EKF402	10RU10-021 X 8	Arrow	
EKF405	10RA20-040 X 4	Arrow	
EKF407	10RA20-071 X 2	Arrow	
EKF408	10RA20-080 X 2	Arrow	
EKF410	10RU25-101 X 2	Arrow	
EKF418	10RU25-181 X 1	Arrow	
EKF428	10RU25-281 X 1	Arrow	
EKF4N2	10RU25-281 X 1	Arrow	
EKF5 X 2	6IU25-281 X 1	Arrow	
EKF5 X 2A	2IU25-281 X 1	Arrow	
EKF5 X 3	6IU25-281 X 1	Arrow	
EKF5 X 3A	2IU25-281 X 1	Arrow	
EKF5 X 4	6IU25-281 X 1	Arrow	
EKF5 X 4A	2IU25-281 X 1	Arrow	
EKF5 X 5	6IU25-281 X 1	Arrow	
EKF5 X 5A	2IU25-281 X 1	Arrow	
EKF5 X 6	6IU25-281 X 1	Arrow	
EKF5 X 6A	2IU25-281 X 1	Arrow	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
EKF5 X 8	6IU25-281 X 1	Arrow	
EKF5 X 8A	2IU25-281 X 1	Arrow	
EKF501	6CU07-018 X 8	Arrow	
EKF501A	2CU07-018 X 8	Arrow	
EKF501H	6HM06-013 X 10	Watts	
EKF502	6CU10-022 X 8	Arrow	
EKF502A	2CU10-022 X 8	Arrow	
EKF505	6IA20-040 X 4	Arrow	
EKF505A	2IA20-040 X 4	Arrow	
EKF507	6IA20-071 X 2	Arrow	
EKF507	10HM06-013 X 10	Watts	
EKF507A	2IA20-071 X 2	Arrow	
EKF508	6IA20-080 X 2	Arrow	
EKF508A	2IA20-080 X 2	Arrow	
EKF51	6H08-015 X 10	Watts	
EKF510	6IU25-101 X 2	Arrow	
EKF510A	2IU25-101 X 2	Arrow	
EKF518	6IU25-181 X 1	Arrow	
EKF518A	2IU25-181 X 1	Arrow	
EKF528	6IU25-281 X 1	Arrow	
EKF528A	2IU25-281 X 1	Arrow	
EKF529	6CA29-280 X 1	Arrow	
EKF529A	2CA29-280 X 1	Arrow	
EKF5N2	6IU25-281 X 1	Arrow	
EKF5N2A	2IU25-281 X 1	Arrow	
EKF6 X 2	AU25-281 X 1	Arrow	
EKF6 X 3	AU25-281 X 1	Arrow	
EKF6 X 4	AU25-281 X 1	Arrow	
EKF6 X 5	AU25-281 X 1	Arrow	
EKF6 X 6	AU25-281 X 1	Arrow	
EKF6 X 8	AU25-281 X 1	Arrow	
EKF601	AU07-018 X 8	Arrow	
EKF601J	6CM10-025 X 8	Watts	KX-21
EKF601K	6CM10-050 X 4	Watts	KX-22
EKF601L	6CM15-060 X 4	Watts	KX-23
EKF602	AU10-022 X 8	Arrow	
EKF604	10HM10-022 X 8	Watts	KX-26
EKF605	AA20-040 X 4	Arrow	
EKF607	AA20-071 X 2	Arrow	
EKF608	AA20-080 X 2	Arrow	
EKF610	AU25-101 X 2	Arrow	
EKF618	AU25-181 X 1	Arrow	
EKF628	AU25-281 X 1	Arrow	
EKF629	AA29-280 X 1	Arrow	
EKF6N2	AU25-281 X 1	Arrow	
EMS1000D	4CU32-350 X 1	Pioneer	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
EMS1250D	4QU52-290 X 1	Pioneer	
EMS125D	4CU15-105 X 1	Pioneer	
EMS1600D	4QU78-260 X 1	Pioneer	
EMS185D	4IU20-133 X 1	Pioneer	
EMS20	4CU10-035 X 1	Pioneer	
EMS25	4CU10-035 X 1	Pioneer	
EMS2500D	4QU78-370 X 1	Pioneer	
EMS260D	4IU20-195 X 1	Pioneer	
EMS350D	4CU25-198 X 1	Pioneer	
EMS450D	4CU25-245 X 1	Pioneer	
EMS50	4CU10-060 X 1	Pioneer	
EMS600D	4CU25-285 X 1	Pioneer	
EMS800D	4CU32-290 X 1	Pioneer	
EP1001AO	6QP19-098 X 2	Domnick Hunter	
EP1001PL	3PP19-098 X 2	Domnick Hunter	
EPS100	3PU10-060 X 1	Pioneer	
EPS1000D	3PU25-245 X 1	Pioneer	
EPS1300D	3PU25-285 X 1	Pioneer	
EPS1700D	3PU32-290 X 1	Pioneer	
EPS2000D	3PU32-350 X 1	Pioneer	
EPS250D	3PU15-105 X 1	Pioneer	
EPS2600D	3PU52-290 X 1	Pioneer	
EPS30	3PU10-035 X 1	Pioneer	
EPS3500D	3PU78-260 X 1	Pioneer	
EPS40	3PU10-035 X 1	Pioneer	
EPS425D	3PU20-133 X 1	Pioneer	
EPS5200D	3PU78-370 X 1	Pioneer	
EPS550D	3PU20-195 X 1	Pioneer	
EPS750D	3PU25-198 X 1	Pioneer	
EZ1030AA	6CZ07-020 X 1	Domnick Hunter	
EZ1030AC	AZ07-020 X 1	Domnick Hunter	
EZ1030AO	10CZ07-020 X 1	Domnick Hunter	
EZ1050AA	6CZ12-023 X 1	Domnick Hunter	
EZ1050AC	AZ12-023 X 1	Domnick Hunter	
EZ1050AO	10CZ12-023 X 1	Domnick Hunter	
EZ1070AA	6CZ12-029 X 1	Domnick Hunter	
EZ1070AC	AZ12-029 X 1	Domnick Hunter	
EZ1070AO	10CZ12-029 X 1	Domnick Hunter	
EZ1140AA	6CZ12-056 X 1	Domnick Hunter	
EZ1140AC	AZ12-056 X 1	Domnick Hunter	
EZ1140AO	10CZ12-056 X 1	Domnick Hunter	
EZ2010AA	6CZ20-046 X 1	Domnick Hunter	
EZ2010AC	AZ20-046 X 1	Domnick Hunter	
EZ2010AO	10CZ20-046 X 1	Domnick Hunter	
EZ2020AA	6CZ20-086 X 1	Domnick Hunter	
EZ2020AC	AZ20-086 X 1	Domnick Hunter	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
EZ2020AO	10CZ20-086 X 1	Domnick Hunter	
EZ2030AA	6CZ20-126 X 1	Domnick Hunter	
EZ2030AC	AZ20-126 X 1	Domnick Hunter	
EZ2030AO	10CZ20-126 X 1	Domnick Hunter	
EZ2050AA	6CZ20-200 X 1	Domnick Hunter	
EZ2050AC	AZ20-200 X 1	Domnick Hunter	
EZ2050AO	10CZ20-200 X 1	Domnick Hunter	
EZ3050AA	6CZ27-200 X 1	Domnick Hunter	
EZ3050AC	AZ27-200 X 1	Domnick Hunter	
EZ3050AO	10CZ27-200 X 1	Domnick Hunter	
EZ3075AA	6CZ27-298 X 1	Domnick Hunter	
EZ3075AC	AZ27-298 X 1	Domnick Hunter	
EZ3075AO	10CZ27-298 X 1	Domnick Hunter	
EZ5060AA	6CZ46-239 X 1	Domnick Hunter	
EZ5060AC	AZ46-239 X 1	Domnick Hunter	
EZ5060AO	10CZ46-239 X 1	Domnick Hunter	
EZ5075AA	6CZ50-298 X 1	Domnick Hunter	
EZ5075AC	AZ50-298 X 1	Domnick Hunter	
EZ5075AO	10CZ50-298 X 1	Domnick Hunter	
F05013VE-T	10G04-013 X 10	Filtersoft	
F05013VE-W	10H04-013 X 10	Filtersoft	
F05013WE-T	8T04-013 X 10	Filtersoft	
F05013WE-W	8H04-013 X 10	Filtersoft	
F05013XE-T	6G04-013 X 10	Filtersoft	
F05013XE-W	6H04-013 X 10	Filtersoft	
F05023VE-T	10G04-023 X 10	Filtersoft	
F05023VE-W	10H04-023 X 10	Filtersoft	
F05023VH-TB	10T04-023 X 10	Filtersoft	
F05023WE-T	8T04-023 X 10	Filtersoft	
F05023WE-W	8H04-023 X 10	Filtersoft	
F05023XE-T	6G04-023 X 10	Filtersoft	
F05023XE-W	6H04-023 X 10	Filtersoft	
F05023XH-TB	6T04-023 X 10	Filtersoft	
F07013QE-CU	14JU07-013 X 10	Filtersoft	
F10020QE-CU	14JU10-020 X 10	Filtersoft	
F10020VE-W	10H10-020 X 8	Filtersoft	
F10020XE-W	6H10-020 X 8	Filtersoft	
F10025VE-T	10G10-025 X 10	Filtersoft	
F10025VE-W	10H10-025 X 8	Filtersoft	
F10025VH-TB	10T10-025 X 10	Filtersoft	
F10025WE-T	8T10-025 X 10	Filtersoft	
F10025WE-W	8H10-025 X 8	Filtersoft	
F10025XE-T	6G10-025 X 10	Filtersoft	
F10025XE-W	6H10-025 X 8	Filtersoft	
F10025XH-TB	6T10-025 X 10	Filtersoft	
F10050VE-W	10H10-050 X 4	Filtersoft	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
F10050WE-W	8H10-050 X 4	Filtersoft	
F10050XE-W	6H10-050 X 4	Filtersoft	
F10070VE-T	10G10-070 X 10	Filtersoft	
F10070VE-W	10H10-070 X 4	Filtersoft	
F10070VH-TB	10T10-070 X 10	Filtersoft	
F10070WE-T	8T10-070 X 10	Filtersoft	
F10070WE-W	8H10-070 X 4	Filtersoft	
F10070XE-T	6G10-070 X 10	Filtersoft	
F10070XE-W	6H10-070 X 4	Filtersoft	
F10070XH-TB	6T10-070 X 10	Filtersoft	
F15043QE-CU	14JU15-043 X 10	Filtersoft	
F15060AU	AB15-060 X 4	Filtersoft	
F15060AU	AU15-060 X 4	Filtersoft	
F15060VE-T	10G15-060 X 10	Filtersoft	
F15060VE-W	10H15-060 X 4	Filtersoft	
F15060WE-W	8H15-060 X 4	Filtersoft	
F15060XE-T	6G15-060 X 10	Filtersoft	
F15060XE-W	6H15-060 X 4	Filtersoft	
F20035VE-W	10H20-035 X 4	Filtersoft	
F20035WE-W	8H20-035 X 4	Filtersoft	
F20035XE-W	6H20-035 X 4	Filtersoft	
F20090AU	AB15-084 X 2	Filtersoft	
F20090VE-T	10G20-090 X 10	Filtersoft	
F20090VE-W	10H20-090 X 2	Filtersoft	
F20090WE-W	8H20-090 X 2	Filtersoft	
F20090XE-T	6G20-090 X 10	Filtersoft	
F20090XE-W	6H20-090 X 2	Filtersoft	
F20187AU	AP15-180 X 2	Filtersoft	
F20187VE-T	10G20-187 X 10	Filtersoft	
F20187VE-W	10H20-187 X 1	Filtersoft	
F20187WE-W	8H20-187 X 1	Filtersoft	
F20187XE-T	6G20-187 X 10	Filtersoft	
F20187XE-W	6H20-187 X 1	Filtersoft	
F20198AU	AP15-198 X 2	Filtersoft	
F26075QE-CU	14JU26-075 X 4	Filtersoft	
F26120QE-CU	14JU26-120 X 4	Filtersoft	
F26240QE-CU	14JU26-240 X 4	Filtersoft	
F350 (350°)	3PS19-187 X 1	Henderson	KX-16H
F350 (450°)	10DS19-187 X 1	Henderson	KX-16H
FA1030AP-AB	AZ07-020 X 1	Filtersoft	
FA1030K-CB	3PZ07-020 X 1	Filtersoft	
FA1030WE-CB	10CZ07-020 X 1	Filtersoft	
FA1030XE-CB	8CZ07-020 X 1	Filtersoft	
FA1030YE-CB	6CZ07-020 X 1	Filtersoft	
FA1050AP-AB	AZ12-023 X 1	Filtersoft	
FA1050K-CB	3PZ12-023 X 1	Filtersoft	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FA1050WE-CB	10CZ12-023 X 1	Filtersoft	
FA1050XE-CB	8CZ12-023 X 1	Filtersoft	
FA1050YE-CB	6CZ12-023 X 1	Filtersoft	
FA1070AP-AB	AZ12-029 X 1	Filtersoft	
FA1070K-CB	3PZ12-029 X 1	Filtersoft	
FA1070WE-CB	10CZ12-029 X 1	Filtersoft	
FA1070XE-CB	8CZ12-029 X 1	Filtersoft	
FA1070YE-CB	6CZ12-029 X 1	Filtersoft	
FA1140AP-AB	AZ12-056 X 1	Filtersoft	
FA1140K-CB	3PZ12-056 X 1	Filtersoft	
FA1140WE-CB	10CZ12-056 X 1	Filtersoft	
FA1140XE-CB	8CZ12-056 X 1	Filtersoft	
FA1140YE-CB	6CZ12-056 X 1	Filtersoft	
FA2010AP-AB	AZ20-046 X 1	Filtersoft	
FA2010K-CB	3PZ20-046 X 1	Filtersoft	
FA2010WE-CB	10CZ20-046 X 1	Filtersoft	
FA2010XE-CB	8CZ20-046 X 1	Filtersoft	
FA2010YE-CB	6CZ20-046 X 1	Filtersoft	
FA2020AP-AB	AZ20-086 X 1	Filtersoft	
FA2020K-CB	3PZ20-086 X 1	Filtersoft	
FA2020WE-CB	10CZ20-086 X 1	Filtersoft	
FA2020XE-CB	8CZ20-086 X 1	Filtersoft	
FA2020YE-CB	6CZ20-086 X 1	Filtersoft	
FA2030AP-AB	AZ20-126 X 1	Filtersoft	
FA2030K-CB	3PZ20-126 X 1	Filtersoft	
FA2030WE-CB	10CZ20-126 X 1	Filtersoft	
FA2030XE-CB	8CZ20-126 X 1	Filtersoft	
FA2030YE-CB	6CZ20-126 X 1	Filtersoft	
FA2050AP-AB	AZ20-200 X 1	Filtersoft	
FA2050K-CB	3PZ20-200 X 1	Filtersoft	
FA2050WE-CB	10CZ20-200 X 1	Filtersoft	
FA2050XE-CB	8CZ20-200 X 1	Filtersoft	
FA2050YE-CB	6CZ20-200 X 1	Filtersoft	
FA3050AP-AB	AZ27-200 X 1	Filtersoft	
FA3050K-CB	3PZ27-200 X 1	Filtersoft	
FA3050WE-CB	10CZ27-200 X 1	Filtersoft	
FA3050XE-CB	8CZ27-200 X 1	Filtersoft	
FA3050YE-CB	6CZ27-200 X 1	Filtersoft	
FA3075AP-AB	AZ27-298 X 1	Filtersoft	
FA3075K-CB	3PZ27-298 X 1	Filtersoft	
FA3075WE-CB	10CZ27-298 X 1	Filtersoft	
FA3075XE-CB	8CZ27-298 X 1	Filtersoft	
FA3075YE-CB	6CZ27-298 X 1	Filtersoft	
FA5075AP-AB	AZ50-298 X 1	Filtersoft	
FA5075K-CB	3PZ50-298 X 1	Filtersoft	
FA5075WE-CB	10CZ50-298 X 1	Filtersoft	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FA5075XE-CB	8CZ50-298 X 1	Filtersoft	
FA5075YE-CB	6CZ50-298 X 1	Filtersoft	
FB302VE-CB	8CF20-099 X 2	Filtersoft	
FB303VE-CB	8CF20-147 X 1	Filtersoft	
FB304VE-CB	8CF20-197 X 1	Filtersoft	
FE006AAYE-CB	6CF08-026 X 1	Filtersoft	
FE006AOVE-CBM	10CF08-026 X 1	Filtersoft	
FE013AAYE-CB	6IF10-032 X 1	Filtersoft	
FE013AOVE-CBM	10IF10-032 X 1	Filtersoft	
FE025AAYE-CB	6IF10-046 X 1	Filtersoft	
FE025AOVE-CBM	10IF10-046 X 1	Filtersoft	
FE040AAYE-CB	6IF20-063 X 1	Filtersoft	
FE040AOVE-CBM	10IF20-063 X 1	Filtersoft	
FE085AAYE-CB	6IF20-102 X 1	Filtersoft	
FE085AOVE-CBM	10IF20-102 X 1	Filtersoft	
FE195AAYE-CB	6IF25-134 X 1	Filtersoft	
FE195AC-AB	AF25-134 X 1	Filtersoft	
FE195AOVE-CBM	10IF25-134 X 1	Filtersoft	
FE295AAYE-CB	6IF25-254 X 1	Filtersoft	
FE295AC-AB	AF25-254 X 1	Filtersoft	
FE295AOVE-CBM	10IF25-254 X 1	Filtersoft	
FE400AAYE-CB	6CF35-165 X 1	Filtersoft	
FE400AC-AB	AF35-165 X 1	Filtersoft	
FE400AOVE-CBM	10CF35-165 X 1	Filtersoft	
FE500AAYE-CB	6CF43-252 X 1	Filtersoft	
FE500AC-AB	AF43-252 X 1	Filtersoft	
FE500AOVE-CBM	10CF43-252 X 1	Filtersoft	
FF 02/05	10HJN08-024 X 1	Ultrafilter	
FF 03/05	10HJN08-030 X 1	Ultrafilter	
FF 03/10	10CJN10-030 X 1	Ultrafilter	
FF 04/10	10CJN10-040 X 1	Ultrafilter	
FF 04/20	10CJN13-040 X 1	Ultrafilter	
FF 05/20	10CJN13-050 X 1	Ultrafilter	
FF 05/25	10IJN15-050 X 1	Ultrafilter	
FF 07/25	10IJN15-070 X 1	Ultrafilter	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FF 07/30	10IJN25-070 X 1	Ultrafilter	
FF 10/3	10IJ25-100 X 1	Ultrafilter	
FF 10/30	10IJN25-100 X 1	Ultrafilter	
FF 15/3	10IG25-150 X 1	Ultrafilter	
FF 15/30	10IGN25-150 X 1	Ultrafilter	
FF 20/3	10IG25-200 X 1	Ultrafilter	
FF 20/30	10IGN25-200 X 1	Ultrafilter	
FF 3/1	10CJ10-030 X 1	Ultrafilter	
FF 3/1,5	10CJ13-030 X 1	Ultrafilter	
FF 30/3	10IG25-300 X 1	Ultrafilter	
FF 30/30	10IGN25-300 X 1	Ultrafilter	
FF 30/5	10QG43-300 X 1	Ultrafilter	
FF 30/50	10QGN43-300 X 1	Ultrafilter	
FF 4/1,5	10CJ13-044 X 1	Ultrafilter	
FF 4/2,5	10IJ15-040 X 1	Ultrafilter	
FF 5/2,5	10IJN15-050 X 1	Ultrafilter	
FF 5/3	10IJ25-050 X 1	Ultrafilter	
FH71311YE-CB	6CH25-260 X 1	Filtersoft	
FH7132YE-CB	6CM10-025 X 8	Filtersoft	KX-21
FH7133YE-CB	6CM10-050 X 4	Filtersoft	KX-22
FH7134YE-CB	6CM15-060 X 4	Filtersoft	KX-23
FH7135YE-CB	6CM15-095 X 2	Filtersoft	KX-24
FH7136YE-CB	6CM15-185 X 2	Filtersoft	KX-25
FH7137YE-CB	6CU25-187 X 1	Filtersoft	KX-2
FH7138YE-CB	6CU25-187 X 1	Filtersoft	KX-2
FH7139YE-CB	6CH25-260 X 1	Filtersoft	
FH71511-AB	AH25-260 X 1	Filtersoft	
FH7152-AB	AM10-025 X 8	Filtersoft	KX-21
FH7153-AB	AM10-050 X 4	Filtersoft	KX-22
FH7154-AB	AM15-060 X 4	Filtersoft	KX-23
FH7155-AB	AM15-095 X 2	Filtersoft	KX-24
FH7156-AB	AM15-185 X 2	Filtersoft	KX-25
FH7157-AB	AU25-187 X 1	Filtersoft	KX-2
FH7158-AB	AU25-187 X 1	Filtersoft	KX-2
FH7159-AB	AH25-260 X 1	Filtersoft	
FH7313VE-CB	10CM10-025 X 8	Filtersoft	KX-21
FH7314VE-CB	10CM10-050 X 4	Filtersoft	KX-22
FH7315VE-CB	10CM15-060 X 4	Filtersoft	KX-23
FH7316VE-CB	10CM15-095 X 1	Filtersoft	KX-24
FH7317VE-CB	10CM15-185 X 2	Filtersoft	KX-25
FH7318VE-CB	10CU25-187 X 1	Filtersoft	KX-2

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FH7319VE-CB	10CH25-260 X 1	Filtersoft	
FI1306XE-C	6C85-250 X 1	Filtersoft	
FI1355XE-C	6C85-250 X 1	Filtersoft	
FI1645XE-C	6C85-360 X 1	Filtersoft	
FI1777XE-C	6C85-360 X 1	Filtersoft	
FN10DXE-CB	6IR04-019 X 4	Filtersoft	
FN20DXE-CB	6IR08-019 X 4	Filtersoft	
FN30DXE-CB	6IR10-034 X 4	Filtersoft	
FP14051J-PB	3PP14-051 X 4	Filtersoft	
FP14051XE-CB	6QP14-051 X 4	Filtersoft	
FP19098J-PU	3PP19-098 X 2	Filtersoft	
FP19098VH-RS	10DP19-098 X 2	Filtersoft	
FP19098VH-RSI	10DPS19-098 X 2	Filtersoft	
FP19098XE-CU	6QP19-098 X 2	Filtersoft	
FP19098XE-DB	6QP19-098 X 2	Filtersoft	
FP19098XK-CB	6QP19-098 X 2	Filtersoft	
FP19198J-PU	3PP19-198 X 2	Filtersoft	
FP19198VH-RS	10DP19-198 X 2	Filtersoft	
FP19198VH-RSI	10DPS19-198 X 2	Filtersoft	
FP19198XE-CU	6QP19-198 X 2	Filtersoft	
FP19198XE-DB	6QP19-198 X 2	Filtersoft	
FP19298XE-CU	6QP19-298 X 1	Filtersoft	
FP19298XE-DB	6QP19-298 X 1	Filtersoft	
FP26132J-PU	3PP26-132 X 2	Filtersoft	
FP26132VH-RS	10DP26-132 X 2	Filtersoft	
FP26132XK-CBI	6QP28-132 X 2	Filtersoft	
FP26132XK-CU	6QP28-132 X 2	Filtersoft	
FP26132XK-CUI	6QPS28-132 X 2	Filtersoft	
FP26265J-PU	3PP26-265 X 1	Filtersoft	
FP26265VH-RS	10DP26-265 X 1	Filtersoft	
FP26265XK-CU	6QP28-265 X 1	Filtersoft	
FP30142J-PB	3PP30-143 X 1	Filtersoft	
FP30142J-PBI	3PP30-143 X 1	Filtersoft	
FP30142VH-RV	10DP30-143 X 1	Filtersoft	
FP30142VH-RVI	10DPS30-143 X 1	Filtersoft	
FP30142XE-CB	6QP30-143 X 1	Filtersoft	
FP30142XE-CBI	6QPS30-143 X 1	Filtersoft	
FP30295J-PB	3PP30-295 X 1	Filtersoft	
FP30295J-PBI	3PP30-295 X 1	Filtersoft	
FP30295VH-RV	10DP30-295 X 1	Filtersoft	
FP30295VH-RVI	10DPS30-295 X 1	Filtersoft	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FP30295XE-CB	6QP30-295 X 1	Filtersoft	
FP30295XE-CBI	6QPS30-295 X 1	Filtersoft	
FRP-85-168	14JU26-120 X 4	Wilkerson	
FRP-85-169	14JU26-240 X 4	Wilkerson	
FRP-95-115	14JU10-020 X 10	Wilkerson	
FRP-95-160	14JU07-013 X 10	Wilkerson	
FRP-95-172	14JU26-075 X 4	Wilkerson	
FRP-95-203	14JU26-075 X 4	Wilkerson	
FRP-95-206	14JU10-020 X 10	Wilkerson	
FRP-95-209	14JU15-043 X 10	Wilkerson	
FRP-95-210	14JU15-043 X 10	Wilkerson	
FRP-95-212	14JU26-120 X 4	Wilkerson	
FRP-95-213	14JU26-240 X 4	Wilkerson	
FRP-95-236	14JU10-020 X 10	Wilkerson	
FRP-95-267	14JU07-013 X 10	Wilkerson	
FRP-95-268	14JU10-020 X 10	Wilkerson	
FRP-95-269	14JU10-020 X 10	Wilkerson	
FRP-95-271	14JU15-043 X 10	Wilkerson	
FRP-95-272	14JU15-043 X 10	Wilkerson	
FRP-95-273	14JU26-075 X 4	Wilkerson	
FRP-95-274	14JU26-075 X 4	Wilkerson	
FRP-95-566	14JU26-075 X 4	Wilkerson	
FRP-95-567	14JU26-075 X 4	Wilkerson	
FS1357YE-CB	6CJ25-120 X 2	Filtersoft	
FS1358YE-CB	6CJ25-120 X 2	Filtersoft	
FS1359YE-CB	6CJ25-240 X 1	Filtersoft	
FS1360YE-CB	6CJ25-240 X 1	Filtersoft	
FS1361YE-CB	6CJ25-240 X 1	Filtersoft	
FS1362YE-CB	6CJ25-240 X 1	Filtersoft	
FS1367YE-CB	6CJ25-240 X 1	Filtersoft	
FS1368YE-CB	6CJ25-240 X 1	Filtersoft	
FS1370-AB	AJ25-240 X 1	Filtersoft	
FS1372-AB	AJ25-120 X 2	Filtersoft	
FS1373-AB	AJ25-120 X 2	Filtersoft	
FS1375-AB	AJ25-240 X 1	Filtersoft	
FS1377-AB	AJ25-240 X 1	Filtersoft	
FS1378-AB	AJ25-240 X 1	Filtersoft	
FS1379-AB	AJ25-240 X 1	Filtersoft	
FS1407YE-CB	6CJ25-120 X 2	Filtersoft	
FS1408YE-CB	6CJ25-240 X 1	Filtersoft	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FS1412-AB	AJ25-120 X 2	Filtersoft	
FS1413-AB	AJ25-240 X 1	Filtersoft	
FS1413YE-CB	6CJ25-240 X 1	Filtersoft	
FS1418-AB	AJ25-240 X 1	Filtersoft	
FS5025-AB	AJ25-240 X 1	Filtersoft	
FS5027-AB	AJ25-240 X 1	Filtersoft	
FUF0205WE-CB	10HJN08-024 X 1	Filtersoft	
FUF0305WE-CB	10HJN08-030 X 1	Filtersoft	
FUF0310WE-CB	10CJN10-030 X 1	Filtersoft	
FUF0410WE-CB	10CJN10-040 X 1	Filtersoft	
FUF0420WE-CB	10CJN13-040 X 1	Filtersoft	
FUF0520WE-CB	10CJN13-050 X 1	Filtersoft	
FUF0525WE-CB	10IJN15-050 X 1	Filtersoft	
FUF0725WE-CB	10IJN15-070 X 1	Filtersoft	
FUF0730WE-CB	10IJN25-070 X 1	Filtersoft	
FUF1030WE-CB	10IJN25-100 X 1	Filtersoft	
FUF103WE-CB	10IJ25-100 X 1	Filtersoft	
FUF1530WE-CB	10IGN25-150 X 1	Filtersoft	
FUF153WE-CB	10IG25-150 X 1	Filtersoft	
FUF2030WE-CB	10IGN25-200 X 1	Filtersoft	
FUF203WE-CB	10IG25-200 X 1	Filtersoft	
FUF3030WE-CB	10IGN25-300 X 1	Filtersoft	
FUF303WE-CB	10IG25-300 X 1	Filtersoft	
FUF3050WE-CB	10QGN43-300 X 1	Filtersoft	
FUF305WE-CB	10QG43-300 X 1	Filtersoft	
FUF315WE-CB	10CJ13-030 X 1	Filtersoft	
FUF31WE-CB	10CJ10-030 X 1	Filtersoft	
FUF415WE-CB	10CJ13-044 X 1	Filtersoft	
FUF425WE-CB	10IJ15-040 X 1	Filtersoft	
FUF525WE-CB	10IJN15-050 X 1	Filtersoft	
FUF53WE-CB	10IJ25-050 X 1	Filtersoft	
FUK0205-AB	AJN08-024 X 1	Filtersoft	
FUK0305-AB	AJN08-030 X 1	Filtersoft	
FUK0310-AB	AJN10-030 X 1	Filtersoft	
FUK0410-AB	AJN10-040 X 1	Filtersoft	
FUK0420-AB	AJN13-040 X 1	Filtersoft	
FUK0520-AB	AJN13-050 X 1	Filtersoft	
FUK0525-AB	AJN15-050 X 1	Filtersoft	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FUK0725-AB	AJN15-070 X 1	Filtersoft	
FUK0730-AB	AJN25-070 X 1	Filtersoft	
FUK1030-AB	AJN25-100 X 1	Filtersoft	
FUK103-AB	AJ25-100 X 1	Filtersoft	
FUK1530-AB	AGN25-150 X 1	Filtersoft	
FUK153-AB	AG25-150 X 1	Filtersoft	
FUK2030-AB	AGN25-200 X 1	Filtersoft	
FUK203-AB	AG25-200 X 1	Filtersoft	
FUK3030-AB	AGN25-300 X 1	Filtersoft	
FUK303-AB	AG25-300 X 1	Filtersoft	
FUK3050-AB	AGN43-300 X 1	Filtersoft	
FUK305-AB	AG43-300 X 1	Filtersoft	
FUK315-AB	AJ13-030 X 1	Filtersoft	
FUK31-AB	AJ10-030 X 1	Filtersoft	
FUK415-AB	AJ13-044 X 1	Filtersoft	
FUK425-AB	AJ15-040 X 1	Filtersoft	
FUK525-AB	AJN15-050 X 1	Filtersoft	
FUK53-AB	AJ25-050 X 1	Filtersoft	
FUM0205XE-CB	6HJN08-024 X 1	Filtersoft	
FUM0305XE-CB	6HJN08-030 1	Filtersoft	
FUM0310XE-CB	6CJN10-030 X 1	Filtersoft	
FUM0410XE-CB	6CJN10-040 X 1	Filtersoft	
FUM0420XE-CB	6CJN13-040 X 1	Filtersoft	
FUM0520XE-CB	6CJN13-050 X 1	Filtersoft	
FUM0525XE-CB	6IJN15-050 X 1	Filtersoft	
FUM0725XE-CB	6IJN15-070 X 1	Filtersoft	
FUM0730XE-CB	6IJN25-070 X 1	Filtersoft	
FUM1030XE-CB	6IJN25-100 X 1	Filtersoft	
FUM103XE-CB	6IJ25-100 X 1	Filtersoft	
FUM1530XE-CB	6IGN25-150 X 1	Filtersoft	
FUM153XE-CB	6IG25-150 X 1	Filtersoft	
FUM2030XE-CB	6IGN25-200 X 1	Filtersoft	
FUM203XE-CB	6IG25-200 X 1	Filtersoft	
FUM3030XE-CB	6IGN25-300 X 1	Filtersoft	
FUM303XE-CB	6IG25-300 X 1	Filtersoft	
FUM3050XE-CB	6QGN43-300 X 1	Filtersoft	
FUM3050XE-CB	6QGN43-300 X 1	Filtersoft	
FUM305XE-CB	6QG43-300 X 1	Filtersoft	
FUM315XE-CB	6CJ13-030 X 1	Filtersoft	
FUM31XE-CB	6CJ10-030 X 1	Filtersoft	
FUM415XE-CB	6CJ13-044 X 1	Filtersoft	
FUM425XE-CB	6IJ15-040 X 1	Filtersoft	
FUM525XE-CB	6IJN15-050 X 1	Filtersoft	
FUM53XE-CB	6IJ25-050 X 1	Filtersoft	
FUS0205YE-CB	4HJN08-024 X 1	Filtersoft	
FUS0305YE-CB	4HJN08-030 X 1	Filtersoft	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
FUS0310YE-CB	4CJN10-030 X 1	Filtersoft	
FUS0410YE-CB	4CJN10-040 X 1	Filtersoft	
FUS0420YE-CB	4CJN13-040 X 1	Filtersoft	
FUS0520YE-CB	4CJN13-050 X 1	Filtersoft	
FUS0525YE-CB	4IJN15-050 X 1	Filtersoft	
FUS0725YE-CB	4IJN15-070 X 1	Filtersoft	
FUS0730YE-CB	4IJN25-070 X 1	Filtersoft	
FUS1030YE-CB	4IJN25-100 X 1	Filtersoft	
FUS103YE-CB	4IJ25-100 X 1	Filtersoft	
FUS1530YE-CB	4IGN25-150 X 1	Filtersoft	
FUS153YE-CB	4IG25-150 X 1	Filtersoft	
FUS2030YE-CB	4IGN25-200 X 1	Filtersoft	
FUS203YE-CB	4IG25-200 X 1	Filtersoft	
FUS3030YE-CB	4IGN25-300 X 1	Filtersoft	
FUS303YE-CB	4IG25-300 X 1	Filtersoft	
FUS3050YE-CB	4QGN43-300 X 1	Filtersoft	
FUS305YE-CB	4QG43-300 X 1	Filtersoft	
FUS315YE-CB	4CJ13-030 X 1	Filtersoft	
FUS31YE-CB	4CJ10-030 X 1	Filtersoft	
FUS415YE-CB	4CJ13-044 X 1	Filtersoft	
FUS425YE-CB	4IJ15-040 X 1	Filtersoft	
FUS525YE-CB	4IJN15-050 X 1	Filtersoft	
FUS53YE-CB	4IJ25-050 X 1	Filtersoft	
FV1500VE-CB	10ICC25-240 X 1	Filtersoft	
FV1500VE-SBM	10DC25-240 X 1	Filtersoft	
FV1500VH-SBM	10DC25-240 X 1	Filtersoft	
FV1500XE-CB	8ICC25-240 X 1	Filtersoft	
FV1500XE-SBM	8DC25-240 X 1	Filtersoft	
FV1500ZE-CB	6ICC25-240 X 1	Filtersoft	
FV1500ZE-SBM	6DC25-240 X 1	Filtersoft	
FV15XE-CB2	6CC15-150 X 2	Filtersoft	
FV15ZE-CB2	2CC15-150 X 2	Filtersoft	
FV1625VE-CB	10ICC25-300 X 1	Filtersoft	
FV1625VE-SBM	10DC25-300 X 1	Filtersoft	
FV1625VH-SBM	10DC25-300 X 1	Filtersoft	
FV1625XE-CB	8ICC25-300 X 1	Filtersoft	
FV1625XE-SBM	8DC25-300 X 1	Filtersoft	
FV1625ZE-CB	6ICC25-300 X 1	Filtersoft	
FV1625ZE-SBM	6DC25-300 X 1	Filtersoft	
FV22XE-CB	6ICC25-220 X 1	Filtersoft	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
L200	6CZ19-095	Zeks	
L300	6CZ19-193	Zeks	
L400	6CZ19-193	Zeks	
L50	6CZ10-050	Zeks	
L80	6CZ15-060	Zeks	
MCC-1001HT	10DP19-098 X 2	Pall/PPC	
MCC-1001SU	6QP19-098 X 2	Pall/PPC	
MCC-1002HT	10DP19-198 X 2	Pall/PPC	
MCC-1002SU	6QP19-198 X 2	Pall/PPC	
MCC-1201HT	10DP26-132 X 2	Pall/PPC	
MCC-1201SU	6QP28-132 X 2	Pall/PPC	
MCC-1202HT	10DP26-265 X 1	Pall/PPC	
MCC-1202SU	6QP28-265 X 1	Pall/PPC	
MCC-4463SU	6QP14-051 X 4	Pall/PPC	
MCS-1001CE	AP19-098 X 2	Pall/PPC	
MCS-1001HT	10DPS19-098 X 2	Pall/PPC	
MCS-1001SU	6QP19-098 X 2	Pall/PPC	
MCS-1002HT	10DPS19-198 X 2	Pall/PPC	
MCS-4463AF	3PP14-051 X 4	Pall/PPC	
MCS-4463EC	3PP14-051 X 4	Pall/PPC	
MCS-4463SU	6QP14-051 X 4	Pall/PPC	
MDC-1001AF	3PP19-098 X 2	Pall/PPC	
MDC-1001CE	AP19-098 X 2	Pall/PPC	
MDC-1001CV	AP19-098 X 2	Pall/PPC	
MDC-1001HT	10DP19-098 X 2	Pall/PPC	
MDC-1001SAU	AP19-098 X 2	Pall/PPC	
MDC-1001SU	6QP19-098 X 2	Pall/PPC	
MDC-1002AF	3PP19-198 X 2	Pall/PPC	
MDC-1002HT	10DP19-198 X 2	Pall/PPC	
MDC-1002SAU	AP19-198 X 2	Pall/PPC	
MDC-1201AF	3PP26-132 X 2	Pall/PPC	
MDC-1201HT	10DP26-132 X 2	Pall/PPC	
MDC-1201SAU	AP26-132 X 2	Pall/PPC	
MDC-1201SU	6QP28-132 X 2	Pall/PPC	
MDC-1202EC	3PP26-265 X 1	Pall/PPC	
MDC-1202HT	10DP26-265 X 1	Pall/PPC	
MDC-1202SAU	AP26-265 X 1	Pall/PPC	
MDC-1202SU	6QP28-265 X 1	Pall/PPC	
MDC-4463AF	3PP14-051 X 4	Pall/PPC	
MDC-4463SAU	AP14-051 X 4	Pall/PPC	
MDC-4463SU	6QP14-051 X 4	Pall/PPC	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
MDS-1001HT	10DPS19-098 X 2	Pall/PPC	
MDS-1001SU	6QP19-098 X 2	Pall/PPC	
MDS-1002HT	10DPS19-198 X 2	Pall/PPC	
MDS-1201SU	6QPS28-132 X 2	Pall/PPC	
MDS-4463SU	6QP14-051 X 4	Pall/PPC	
MF 02/05	6HJN08-024 X 1	Ultrafilter	
MF 03/05	6HJN08-030 X 1	Ultrafilter	
MF 03/10	6CJN10-030 X 1	Ultrafilter	
MF 04/10	6CJN10-040 X 1	Ultrafilter	
MF 04/20	6CJN13-040 X 1	Ultrafilter	
MF 05/20	6CJN13-050 X 1	Ultrafilter	
MF 05/25	6IJN15-050 X 1	Ultrafilter	
MF 07/25	6IJN15-070 X 1	Ultrafilter	
MF 07/30	6IJN25-070 X 1	Ultrafilter	
MF 10/3	6IJ25-100 X 1	Ultrafilter	
MF 10/30	6IJN25-100 X 1	Ultrafilter	
MF 15/3	6IG25-150 X 1	Ultrafilter	
MF 15/30	6IGN25-150 X 1	Ultrafilter	
MF 20/3	6IG25-200 X 1	Ultrafilter	
MF 20/30	6IGN25-200 X 1	Ultrafilter	
MF 3/1	6CJ10-030 X 1	Ultrafilter	
MF 3/1,5	6CJ13-030 X 1	Ultrafilter	
MF 30/3	6IG25-300 X 1	Ultrafilter	
MF 30/30	6IGN25-300 X 1	Ultrafilter	
MF 30/5	6QG43-300 X 1	Ultrafilter	
MF 30/50	6QGN43-300 X 1	Ultrafilter	
MF 4/1,5	6CJ13-044 X 1	Ultrafilter	
MF 4/2,5	6IJ15-040 X 1	Ultrafilter	
MF 5/2,5	6IJN15-050 X 1	Ultrafilter	
MF 5/3	6IJ25-050 X 1	Ultrafilter	
MRP-15-140	6CU10-021 X 8	Wilkerson	KY- 1
MRP-15-143	6CK35-074 X 2	Wilkerson	
MRP-15-411	6CU10-052 X 4	Wilkerson	KY-2
MRP-15-412	6CL25-063 X 2	Wilkerson	
MRP-15-441	6CU10-052 X 4	Wilkerson	KY-2
MRP-15-508	6CK25-119 X 2	Wilkerson	
MRP-15-513	6CK25-238 X 1	Wilkerson	
MRP-15-532	AU10-052 X 4	Wilkerson	KY-2
MRP-15-533	AK25-119 X 2	Wilkerson	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
MRP-15-534	AK25-238 X 1	Wilkerson	
MRP-15-535	AL25-063 X 2	Wilkerson	
MRP-15-536	AU10-021 X 1	Wilkerson	KY-1
MRP-15-537	AU10-052 X 4	Wilkerson	KY-2
MRP-15-538	AK35-074 X 2	Wilkerson	
MRP-95-534	AK25-238 X 1	Wilkerson	
MSP-95-556	8CK25-119 X 2	Wilkerson	
MSP-95-557	8CK25-238 X 1	Wilkerson	
MSP-95-873	8CK25-080 X 2	Wilkerson	
MSP-95-874	8CK35-074 X 2	Wilkerson	
MSP-95-875	8CK35-106 X 1	Wilkerson	
MSP-95-876	8CK35-172 X 1	Wilkerson	
MSP-95-988	8HL10-021 X 4	Wilkerson	
MSP-95-989	8CL10-024 X 4	Wilkerson	
MSP-95-992	8CK15-052 X 4	Wilkerson	
MTP-95-548	6HL10-021 X 4	Wilkerson	
MTP-95-549	6CL10-024 X 4	Wilkerson	
MTP-95-550	6CU10-052 X 4	Wilkerson	KY-2
MTP-95-551	6CK15-052 X 4	Wilkerson	
MTP-95-552	6CL25-063 X 2	Wilkerson	
MTP-95-553	6CK35-074 X 2	Wilkerson	
MTP-95-554	6CK25-119 X 2	Wilkerson	
MTP-95-555	6CK25-238 X 1	Wilkerson	
MTP-95-559	6CK25-080 X 2	Wilkerson	
MTP-95-560	6CK35-074 X 2	Wilkerson	
MTP-95-561	6CK35-106 X 1	Wilkerson	
MTP-95-562	6CK35-172 X 1	Wilkerson	
MXP-15-533	AK25-119 X 2	Wilkerson	
MXP-95-532	AK15-052 X 4	Wilkerson	
MXP-95-535	AL25-063 X 2	Wilkerson	
MXP-95-536	AU10-021 X 8	Wilkerson	KY-1
MXP-95-538	AK35-074 X 2	Wilkerson	
MXP-95-540	AL10-024 X 4	Wilkerson	
MXP-95-558	AK25-080 X 2	Wilkerson	
MXP-95-563	AK35-074 X 2	Wilkerson	
MXP-95-564	AK35-106 X 1	Wilkerson	
MXP-95-565	AK35-172 X 1	Wilkerson	
MXP-95-987	AL10-021 X 4	Wilkerson	
OL-5C	6QP14-051 X 4	Pall/PPC	
OL-9C	6QP19-098 X 2	Pall/PPC	
P150	3PZ15-060	Zeks	
P275	3PZ15-095	Zeks	
P30	3PZ10-025	Zeks	
P330	3PZ19-095	Zeks	
P500	3PZ19-193	Zeks	
P670	3PZ19-193	Zeks	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
P75	3PZ10-050	Zeks	
P-AK 07/30	AGN25-070 X 1	Ultrafilter	
P-AK 10/30	AGN25-100 X 1	Ultrafilter	
PCC-060AF	3PP14-051 X 4	Pall/PPC	
PCC-1001AF	3PP19-098 X 2	Pall/PPC	
PCC-1001HT	10DP19-098 X 2	Pall/PPC	
PCC-1001SU	6QP19-098 X 2	Pall/PPC	
PCC-1002AF	3PP19-198 X 2	Pall/PPC	
PCC-1002HT	10DP19-198 X 2	Pall/PPC	
PCC-1002SU	6QP19-198 X 2	Pall/PPC	
PCC-1003AF	3PP19-298 X 1	Pall/PPC	
PCC-1003HT	10DP19-298 X 1	Pall/PPC	
PCC-1003SU	6QP19-298 X 1	Pall/PPC	
PCC-1200AF	3PP30-295 X 1	Pall/PPC	
PCC-1200HT	10DP30-295 X 1	Pall/PPC	
PCC-1200SU	6QP30-295 X 1	Pall/PPC	
PCC-1201AF	3PP26-132 X 2	Pall/PPC	
PCC-1201HT	10DP26-132 X 2	Pall/PPC	
PCC-1201SU	6QP28-132 X 2	Pall/PPC	
PCC-1202EC	3PP26-265 X 1	Pall/PPC	
PCC-1202HT	10DP26-265 X 1	Pall/PPC	
PCC-1202SU	6QP28-265 X 1	Pall/PPC	
PCC-350AF	3PP30-143 X 1	Pall/PPC	
PCC-350HT	10DP30-143 X 1	Pall/PPC	
PCC-350SU	6QP30-143 X 1	Pall/PPC	
PCC-4463AF	3PP14-051 X 4	Pall/PPC	
PCC-4463SU	6QP14-051 X 4	Pall/PPC	
PCC-600AF	3PP30-140 X 1	Pall/PPC	
PCC-600HT	10DP30-140 X 1	Pall/PPC	
PCC-600SU	6QP30-140 X 1	Pall/PPC	
PCC-700AF	3PP30-295 X 1	Pall/PPC	
PCC-700HT	10DP30-295 X 1	Pall/PPC	
PCC-700SU	6QP30-295 X 1	Pall/PPC	
PCS-060AF	3PP14-051 X 4	Pall/PPC	
PCS-1001AF	3PP19-098 X 2	Pall/PPC	
PCS-1001HT	10DPS19-098 X 2	Pall/PPC	
PCS-1001SU	6QP19-098 X 2	Pall/PPC	
PCS-1002AF	3PP19-198 X 2	Pall/PPC	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
PCS-1002HT	10DPS19-198 X 2	Pall/PPC	
PCS-1002SU	6QP19-198 X 2	Pall/PPC	
PCS-1200HT	10DPS30-295 X 1	Pall/PPC	
PCS-350HT	10DPS30-143 X 1	Pall/PPC	
PCS-350SU	6QPS30-143 X 1	Pall/PPC	
PCS-4463AF	3PP14-051 X 4	Pall/PPC	
PCS-4463SU	6QP14-051 X 4	Pall/PPC	
PCS-700HT	10DPS30-295 X 1	Pall/PPC	
PCS-700SU	6QPS30-295 X 1	Pall/PPC	
PE 02/05	12GJN08-024 X 1	Ultrafilter	
PE 03/05	12GJN08-030 X 1	Ultrafilter	
PE 03/10	3PJN10-030 X 1	Ultrafilter	
PE 04/10	3PJN10-040 X 1	Ultrafilter	
PE 04/20	3PJN13-040 X 1	Ultrafilter	
PE 05/20	3PJN13-050 X 1	Ultrafilter	
PE 05/25	3PJN15-050 X 1	Ultrafilter	
PE 07/25	3PJN15-070 X 1	Ultrafilter	
PE 07/30	3PJN25-070 X 1	Ultrafilter	
PE 10/30	3PJN25-100 X 1	Ultrafilter	
PE 15/30	3PGN25-150 X 1	Ultrafilter	
PE 20/30	3PGN25-200 X 1	Ultrafilter	
PE 30/30	3PGN25-300 X 1	Ultrafilter	
PE 30/50	3PGN43-300 X 1	Ultrafilter	
PF 02/05	12GJN08-024 X 1	Domnick Hunter	
PF 03/05	12GJN08-030 X 1	Domnick Hunter	
PF 03/10	3PJN10-030 X 1	Domnick Hunter	
PF 04/10	3PJN10-040 X 1	Domnick Hunter	
PF 04/20	3PJN13-040 X 1	Domnick Hunter	
PF 05/20	3PJN13-050 X 1	Domnick Hunter	
PF 05/25	3PJN15-050 X 1	Domnick Hunter	
PF 07/25	3PJN15-070 X 1	Domnick Hunter	
PF 07/30	3PJN25-070 X 1	Domnick Hunter	
PF 10/30	3PJN25-100 X 1	Domnick Hunter	
PF 15/30	3PGN25-150 X 1	Domnick Hunter	
PF 20/30	3PGN25-200 X 1	Domnick Hunter	
PF 30/30	3PGN25-300 X 1	Domnick Hunter	
PF 30/50	3PGN43-300 X 1	Domnick Hunter	
P-FF 07/30	10IJN25-070 X 1	Ultrafilter	
P-FF 10/30	10IJN25-100 X 1	Ultrafilter	
P-MF 07/30	6IGN25-070 X 1	Ultrafilter	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
P-MF 10/30	6IGN25-100 X 1	Ultrafilter	
POC-035SU	6QP14-051 X 4	Pall/PPC	
POC-060SU	6QP14-051 X 4	Pall/PPC	
POC-1001SU	6QP19-098 X 2	Pall/PPC	
POC-1200SU	6QP30-295 X 1	Pall/PPC	
POC-1201SU	6QP28-132 X 2	Pall/PPC	
POC-600SU	6QP30-140 X 1	Pall/PPC	
POS-1001SU	6QPS19-098 X 2	Pall/PPC	
POS-1201SU	6QPS28-132 X 1	Pall/PPC	
POS-600SU	6QPS30-140 X 1	Pall/PPC	
POS-700SU	6QPS30-295 X 1	Pall/PPC	
PPC-1200SU	6QP30-295 X 1	Pall/PPC	
PPC-1201SU	6QP28-132 X 2	Pall/PPC	
PPC-1202SU	6QP28-265 X 1	Pall/PPC	
PPC-350SU	6QP30-143 X 1	Pall/PPC	
PPC-700SU	6QP30-295 X 1	Pall/PPC	
P-PE 07/30	3PGN25-070 X 1	Ultrafilter	
P-PE 10/30	3PGN25-100 X 1	Ultrafilter	
PPY-1001SU	6QP19-098 X 2	Pall/PPC	
PPY-1002SU	6QP19-198 X 2	Pall/PPC	
PPY-1003SU	6QP19-298 X 1	Pall/PPC	
P-SMF 07/30	4IGN25-070 X 1	Ultrafilter	
P-SMF 10/30	4IGN25-100 X 1	Ultrafilter	
R130	10CZ15-060	Zeks	
R230	10CZ15-095	Zeks	
R25	10CZ10-025	Zeks	
R300	10CZ19-095	Zeks	
R450	10CZ19-193	Zeks	
R60	10CZ19-193	Zeks	
R600	10CZ10-050	Zeks	
R80	10CZ15-060	Zeks	
SB12	3PU19-050 X 2	Henderson	KX-12
SB4	3PN10-038 X 4	Henderson	KX-11
SMF 02/05	4HJN08-024 X 1	Ultrafilter	
SMF 03/05	4HJN08-030 X 1	Ultrafilter	
SMF 03/10	4CJN10-030 X 1	Ultrafilter	
SMF 04/10	4CJN10-040 X 1	Ultrafilter	
SMF 04/20	4CJN13-040 X 1	Ultrafilter	
SMF 05/20	4CJN13-050 X 1	Ultrafilter	
SMF 05/25	4IJN15-050 X 1	Ultrafilter	
SMF 07/25	4IJN15-070 X 1	Ultrafilter	
SMF 07/30	4IJN25-070 X 1	Ultrafilter	
SMF 10/3	4IJ25-100 X 1	Ultrafilter	
SMF 10/30	4IJN25-100 X 1	Ultrafilter	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
SMF 15/3	4IG25-150 X 1	Ultrafilter	
SMF 15/30	4IGN25-150 X 1	Ultrafilter	
SMF 20/3	4IG25-200 X 1	Ultrafilter	
SMF 20/30	4IGN25-200 X 1	Ultrafilter	
SMF 3/1	4CJ10-030 X 1	Ultrafilter	
SMF 3/1,5	4CJ13-030 X 1	Ultrafilter	
SMF 30/3	4IG25-300 X 1	Ultrafilter	
SMF 30/30	4IGN25-300 X 1	Ultrafilter	
SMF 30/5	4QG43-300 X 1	Ultrafilter	
SMF 30/50	4QGN43-300 X 1	Ultrafilter	
SMF 4/1,5	4CJ13-044 X 1	Ultrafilter	
SMF 4/2,5	4IJ15-040 X 1	Ultrafilter	
SMF 5/2,5	4IJN15-050 X 1	Ultrafilter	
SMF 5/3	4IJ25-050 X 1	Ultrafilter	
U78A3 (9-3/4")	3PP15-098 X 2	Cuno	
U78B2 (9-3/4")	3PP15-098 X 2	Cuno	
U80A3 (10")	3PP15-100 X 2	Cuno	
U80B2 (10")	3PP15-100 X 2	Cuno	
UFAK0205	AJN08-024 X 1	Flair	
UFAK0305	AJN08-030 X 1	Flair	
UFAK0310	AJN10-030 X 1	Flair	
UFAK0410	AJN10-040 X 1	Flair	
UFAK0420	AJN13-040 X 1	Flair	
UFAK0520	AJN13-050 X 1	Flair	
UFAK0525	AJN15-050 X 1	Flair	
UFAK0725	AJN15-070 X 1	Flair	
UFAK0730	AJN25-070 X 1	Flair	
UFAK1030	AJN25-100 X 1	Flair	
UFAK1530	AGN25-150 X 1	Flair	
UFAK2030	AGN25-200 X 1	Flair	
UFAK3030	AGN25-300 X 1	Flair	
UFAK3050	AGN43-300 X 1	Flair	
UFFF0205	10HJN08-024 X 1	Flair	
UFFF0305	10HJN08-030 X 1	Flair	
UFFF0310	10CJN10-030 X 1	Flair	
UFFF0410	10CJN10-040 X 1	Flair	
UFFF0420	10CJN13-040 X 1	Flair	
UFFF0520	10CJN13-050 X 1	Flair	
UFFF0525	10IJN15-050 X 1	Flair	
UFFF0725	10IJN15-070 X 1	Flair	
UFFF0730	10IJN25-070 X 1	Flair	
UFFF1030	10IJN25-100 X 1	Flair	
UFFF1530	10IGN25-150 X 1	Flair	
UFFF2030	10IGN25-200 X 1	Flair	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
UFFF3030	10IGN25-300 X 1	Flair	
UFFF3050	10QGN43-300 X 1	Flair	
UFMF0205	6HJN08-024 X 1	Flair	
UFMF0305	6HJN08-030 X 1	Flair	
UFMF0310	6CJN10-030 X 1	Flair	
UFMF0410	6CJN10-040 X 1	Flair	
UFMF0420	6CJN13-040 X 1	Flair	
UFMF0520	6CJN13-050 X 1	Flair	
UFMF0525	6IJN15-050 X 1	Flair	
UFMF0725	6IJN15-070 X 1	Flair	
UFMF0730	6IJN25-070 X 1	Flair	
UFMF1030	6IJN25-100 X 1	Flair	
UFMF1530	6IGN25-150 X 1	Flair	
UFMF2030	6IGN25-200 X 1	Flair	
UFMF3030	6IGN25-300 X 1	Flair	
UFMF3050	6QGN43-300 X 1	Flair	
UFPE0205	12GJN08-024 X 1	Flair	
UFPE0305	12GJN08-030 X 1	Flair	
UFPE0310	3PJN10-030 X 1	Flair	
UFPE0410	3PJN10-040 X 1	Flair	
UFPE0420	3PJN13-040 X 1	Flair	
UFPE0520	3PJN13-050 X 1	Flair	
UFPE0525	3PJN15-050 X 1	Flair	
UFPE0725	3PJN15-070 X 1	Flair	
UFPE0730	3PJN25-070 X 1	Flair	
UFPE1030	3PJN25-100 X 1	Flair	
UFPE1530	3PGN25-150 X 1	Flair	
UFPE2030	3PGN25-200 X 1	Flair	
UFPE3030	3PGN25-300 X 1	Flair	
UFPE3050	3PGN43-300 X 1	Flair	
UFSMF0205	4HJN08-024 X 1	Flair	
UFSMF0305	4HJN08-030 X 1	Flair	
UFSMF0310	4CJN10-030 X 1	Flair	
UFSMF0410	4CJN10-040 X 1	Flair	
UFSMF0420	4CJN13-040 X 1	Flair	

*Please refer to appropriate competitor section for complete conversion details.

Alpha/Numeric Part List

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
UFSMF0520	4CJN13-050 X 1	Flair	
UFSMF0525	4IJN15-050 X 1	Flair	
UFSMF0725	4IJN15-070 X 1	Flair	
UFSMF0730	4IJN25-070 X 1	Flair	
UFSMF1030	4IJN25-100 X 1	Flair	
UFSMF1530	4IGN25-150 X 1	Flair	
UFSMF2030	4IGN25-200 X 1	Flair	
UFSMF3030	4IGN25-300 X 1	Flair	
UFSMF3050	4QGN43-300 X 1	Flair	
VCE15	6CC15-150 X 2	Flair	
VCE22	6ICC25-220 X 1	Flair	
VCE8100	6CC15-080 X 2	Flair	
VCE860	6CC15-060 X 2	Flair	
VCXE15	2CC15-150 X 2	Flair	
VCXE22	2ICC25-220 X 1	Flair	
VCXE8100	2CC15-080 X 2	Flair	
VCXE860	2CC15-060 X 2	Flair	
VE111250B	8ICC25-240 X 1	Flair	
VE11125RB	8DC25-240 X 1	Flair	
VE111265B	8ICC25-300 X 1	Flair	
VE111265RB	8DC25-300 X 1	Flair	
VKE15	3PC15-150 X 2	Flair	
VKE15HT	10DC15-150 X 2	Flair	
VKE22	3PCC25-220 X 1	Flair	
VKE22HT	10DC25-220 X 1	Flair	
VKE6100	3PC15-080 X 2	Flair	
VKE660	3PC15-060 X 2	Flair	
V-PE 10/3	3PJ25-100 X 1	Ultrafilter	
V-PE 15/3	3PG25-150 X 1	Ultrafilter	
V-PE 20/3	3PG25-200 X 1	Ultrafilter	
V-PE 3/1	3PJ10-030 X 1	Ultrafilter	
V-PE 3/1,5	3PJ13-030 X 1	Ultrafilter	
V-PE 30/3	3PG25-300 X 1	Ultrafilter	
V-PE 30/5	3PG43-300 X 1	Ultrafilter	
V-PE 4/1,5	3PJ13-044 X 1	Ultrafilter	
V-PE 4/2,5	3PJ15-040 X 1	Ultrafilter	
V-PE 5/2,5	3PJN15-050 X 1	Ultrafilter	
V-PE 5/3	3PJ25-050 X 1	Ultrafilter	
Z1050A	AZ12-023 X 1	Flair	
Z1050V	3PZ12-023 X 1	Flair	
Z1050X	6CZ12-023 X 1	Flair	
Z1050Y	8CZ12-023 X 1	Flair	
Z1050Z	10CZ12-023 X 1	Flair	
Z1070A	AZ12-029 X 1	Flair	
Z1070V	3PZ12-029 X 1	Flair	
Z1070X	6CZ12-029 X 1	Flair	

Competitor Part Number	Finite® Part Number	Competitor	Kit Required
Z1070Y	8CZ12-029 X 1	Flair	
Z1070Z	10CZ12-029 X 1	Flair	
Z1140A	AZ12-056 X 1	Flair	
Z1140V	3PZ12-056 X 1	Flair	
Z1140X	6CZ12-056 X 1	Flair	
Z1140Y	8CZ12-056 X 1	Flair	
Z1140Z	10CZ12-056 X 1	Flair	
Z2010A	AZ20-046 X 1	Flair	
Z2010V	3PZ20-046 X 1	Flair	
Z2010X	6CZ20-046 X 1	Flair	
Z2010Y	8CZ20-046 X 1	Flair	
Z2010Y	8CZ20-046 X 1	Flair	
Z2010Z	10CZ20-046 X 1	Flair	
Z2010Z	10CZ20-046 X 1	Flair	
Z2020A	AZ20-086 X 1	Flair	
Z2020A	AZ20-086 X 1	Flair	
Z2020V	3PZ20-086 X 1	Flair	
Z2020V	3PZ20-086 X 1	Flair	
Z2020X	6CZ20-086 X 1	Flair	
Z2020Y	8CZ20-086 X 1	Flair	
Z2020Z	10CZ20-086 X 1	Flair	
Z2030A	AZ20-126 X 1	Flair	
Z2030V	3PZ20-126 X 1	Flair	
Z2030X	6CZ20-126 X 1	Flair	
Z2030Y	8CZ20-126 X 1	Flair	
Z2030Z	10CZ20-126 X 1	Flair	
Z2050A	AZ20-200 X 1	Flair	
Z2050V	3PZ20-200 X 1	Flair	
Z2050X	6CZ20-200 X 1	Flair	
Z2050Y	8CZ20-200 X 1	Flair	
Z2050Z	10CZ20-200 X 1	Flair	
Z3050A	AZ27-200 X 1	Flair	
Z3050V	3PZ27-200 X 1	Flair	
Z3050X	6CZ27-200 X 1	Flair	
Z3050Y	8CZ27-200 X 1	Flair	
Z3050Z	10CZ27-200 X 1	Flair	
Z3075A	AZ27-298 X 1	Flair	
Z3075V	3PZ27-298 X 1	Flair	
Z3075X	6CZ27-298 X 1	Flair	
Z3075Y	8CZ27-298 X 1	Flair	
Z3075Z	10CZ27-298 X 1	Flair	
Z5075A	AZ50-298 X 1	Flair	
Z5075V	3PZ50-298 X 1	Flair	
Z5075X	6CZ50-298 X 1	Flair	
Z5075Y	8CZ50-298 X 1	Flair	
Z5075Z	10CZ50-298 X 1	Flair	

*Please refer to appropriate competitor section for complete conversion details.