

P Series Ordering Information

Select an option from each numbered field to create a complete model order code.

Drive

Order Example : ① ② ③

P D	-	04	C
-----	---	----	---

① Series	② Frame Size	③ Interface
PD	04 - 400W	C - EtherCAT P - Pulse/Indexer
	10 - 1000W	
	35 - 3500W	

Motor

Order Example : ① ② ③ ④ ⑤ ⑥ ⑦

P M	-	FBL	04	A	M	K	2
-----	---	-----	----	---	---	---	---

① Series	② Frame Size	③ Rated Power	④ Winding	⑤ Feedback	⑥ Key	⑦ Options
PM	FAL - 40mm	R5 -50W	A - 3000rpm	M8 -18bit BiSS-C	N - none	[] - None
		01 -100W				[] - None 2 - Brake
		15 -150W				[] - None
	FBL - 62mm	01 -100W		M - 19bit BiSS-C	K - keyway	[] - None 2 - Brake
		02 -200W				
		04 -400W				
	FCL - 80mm	04 -400W				
		06 -600W				
		08 -800W				
		10 -1000W				