




# IQAN-SP Sensors

Electronic Control Systems



ENGINEERING YOUR SUCCESS.

### Application

The IQAN-SP pressure transducers belong to the family of IQAN accessories developed to complement IQAN control systems. IQAN-SP is a range of 0-5V pressure transducers for mobile hydraulic applications. These transducers are available in two pressure ranges; 35 bar (507 psi) and 500 bar (7250 psi). To make the sensors suitable for mobile equipment, we have focused upon properties such as reliability, electromagnetic immunity and ease of installation.

### Properties

#### Reliability

The IQAN-SP has stainless steel construction for strength. The sensor cells use thin film technology with no internal o-rings or fluid. The high pressure capability makes the sensor very robust and able to withstand vibration.

#### Electromagnetic immunity

The design of the IQAN-SP has an EMI cap that separates the sensor electronics from the connector. This ensures a high level of EMI protection.

#### Installation

The two interface types of the IQAN-SP are well designed for the mobile hydraulics industry.

The first type, -B, has a G1/4 thread. The hex of the transducer has an integrated face seal to eliminate sealing washers. The integral 3 pin connector is a sealed AMP/Tyco Junior Timer type designed for automotive use.

The second type, -D, has a SAE 6 (9/16"-18UNF) thread and an o-ring seal. The connector is a 4 pin Deutsch DT04 type and is attached via a short cable.

Both connector types give the sensor IP65 protection for exposed outdoor applications. These features provide for easy installation and removal, even in field conditions.

#### EN 13849-1

MTTFd and failure mode distribution available on request.

### General

Weight	0.06 kg
Operating temperature	-40 °C to 125 °C
Storage temperature	-40 °C to 140 °C
Pressure range	
SP035	0 - 35 bar
SP500	0 - 500 bar
Over pressure	
SP035	Max 100 bar
SP500	Max 1050 bar
Burst pressure	
SP035	Min 150 bar
SP500	Min 1500 bar
Total error (-40°C to 105°C) <sup>1)</sup>	Max 4.0 % FS
Total error ( 40°C to 80°C) <sup>1)</sup>	Max 1.0 % FS
Response time <sup>2)</sup>	5.0 msec

#### EN 13849-1

MTTFd, SP035	384 [y]
MTTFd, SP500	402 [y]

1) Total accuracy includes non-linearity, hysteresis, repeatability and temperature effects.  
 2) Measured from initial value to output at 90%.

### Electrical specifications

Output at FS <sup>3)</sup>	4.5 V
Zero output <sup>3)</sup>	0.5 V
Supply Voltage(Vs)	5.0+/-10% Vdc <sup>4)</sup>
Current supply	Max 12.5 mA
Load resistor	Min 5 kΩ
Load capacitor	Max 0.1 μF

3) The output is ratiometric to supply voltage (Vs)  
 4) The max supply voltage with sensor operating is 6 Volt. (switch off app. 6.2Volt)

### Threaded interface

-B	G1/4 BSP with integral face seal
-D	9/16"-18 UNF, SAE 6 with nitrile o-ring

### Connector

-B	AMP/Tyco Integral to sensor
-D	Deutsch DT04-4P

### Ordering part numbers

IQAN-SP035-B	5020026
IQAN-SP500-B	5020027
IQAN-SP035-D	2820008
IQAN-SP500-D	2820009

**Environmental Protection**

**EMI**

- ISO 11452-2 (immunity vs EM field)
- ISO 14982 (radiated emission)
- EN 55022 (conducted emission)
- ISO 11452-4 (immunity vs injected RF)

**ESD**

- EN 61000-4-8 (external)

**Mechanical environment**


- IEC 60068-2-64 Fh,  
 24-2000 Hz, 31 Grms, 3\*8 h (vibration)
- IEC 60068-2-27 Es (shock)
- IEC 60068-2-29 Eb (bump)

**Climate environment**

- IEC 60068-2-18 Rb3 (water)
- IEC 60068-2-30 Db (var1, damp, cyclic)
- IEC 60068-2-3 Ca (damp, heat steady state)
- IEC 60068-2-2 Bb (heat)
- IEC 60068-2-1 Ab (cold)
- IEC 60068-2-14 Nb (change of temperature)


**Chemical environment**

- IEC 60068-2-52 Kb (salt mist, cyclic)



IQAN-SPxxx-B

unit = mm



IQAN-SPxxx-D

unit = mm

**! WARNING**

**FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.**

This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application, including consequences of any failure, and review the information concerning the product or system in the current product catalogue. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection of the products and systems and assuring that all performance, safety and warning requirements of the application are met.

The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.

**Offer of Sale**

Please contact your Parker representation for a detailed "Offer of Sale".

# Parker Worldwide

## Europe, Middle East, Africa

**AE – United Arab Emirates,** Dubai

Tel: +971 4 8127100  
parker.me@parker.com

**AT – Austria,** Wiener Neustadt

Tel: +43 (0)2622 23501-0  
parker.austria@parker.com

**AT – Eastern Europe,** Wiener Neustadt

Tel: +43 (0)2622 23501 900  
parker.easteurope@parker.com

**AZ – Azerbaijan,** Baku

Tel: +994 50 22 33 458  
parker.azerbaijan@parker.com

**BE/LU – Belgium,** Nivelles

Tel: +32 (0)67 280 900  
parker.belgium@parker.com

**BG – Bulgaria,** Sofia

Tel: +359 2 980 1344  
parker.bulgaria@parker.com

**BY – Belarus,** Minsk

Tel: +48 (0)22 573 24 00  
parker.poland@parker.com

**CH – Switzerland,** Etoy

Tel: +41 (0)21 821 87 00  
parker.switzerland@parker.com

**CZ – Czech Republic,** Klecany

Tel: +420 284 083 111  
parker.czechrepublic@parker.com

**DE – Germany,** Kaarst

Tel: +49 (0)2131 4016 0  
parker.germany@parker.com

**DK – Denmark,** Ballerup

Tel: +45 43 56 04 00  
parker.denmark@parker.com

**ES – Spain,** Madrid

Tel: +34 902 330 001  
parker.spain@parker.com

**FI – Finland,** Vantaa

Tel: +358 (0)20 753 2500  
parker.finland@parker.com

**FR – France,** Contamine s/Arve

Tel: +33 (0)4 50 25 80 25  
parker.france@parker.com

**GR – Greece,** Athens

Tel: +30 210 933 6450  
parker.greece@parker.com

**HU – Hungary,** Budaoers

Tel: +36 23 885 470  
parker.hungary@parker.com

**IE – Ireland,** Dublin

Tel: +353 (0)1 466 6370  
parker.ireland@parker.com

**IT – Italy,** Corsico (MI)

Tel: +39 02 45 19 21  
parker.italy@parker.com

**KZ – Kazakhstan,** Almaty

Tel: +7 7273 561 000  
parker.easteurope@parker.com

**NL – The Netherlands,** Oldenzaal

Tel: +31 (0)541 585 000  
parker.nl@parker.com

**NO – Norway,** Asker

Tel: +47 66 75 34 00  
parker.norway@parker.com

**PL – Poland,** Warsaw

Tel: +48 (0)22 573 24 00  
parker.poland@parker.com

**PT – Portugal**

Tel: +351 22 999 7360  
parker.portugal@parker.com

**RO – Romania,** Bucharest

Tel: +40 21 252 1382  
parker.romania@parker.com

**RU – Russia,** Moscow

Tel: +7 495 645-2156  
parker.russia@parker.com

**SE – Sweden,** Spånga

Tel: +46 (0)8 59 79 50 00  
parker.sweden@parker.com

**SK – Slovakia,** Banská Bystrica

Tel: +421 484 162 252  
parker.slovakia@parker.com

**SL – Slovenia,** Novo Mesto

Tel: +386 7 337 6650  
parker.slovenia@parker.com

**TR – Turkey,** Istanbul

Tel: +90 216 4997081  
parker.turkey@parker.com

**UA – Ukraine,** Kiev

Tel: +48 (0)22 573 24 00  
parker.poland@parker.com

**UK – United Kingdom,** Warwick

Tel: +44 (0)1926 317 878  
parker.uk@parker.com

**ZA – South Africa,** Kempton Park

Tel: +27 (0)11 961 0700  
parker.southafrica@parker.com

## North America

**CA – Canada,** Milton, Ontario

Tel: +1 905 693 3000

**US – USA,** Cleveland

(industrial)  
Tel: +1 216 896 3000

**US – USA,** Elk Grove Village

(mobile)  
Tel: +1 847 258 6200

## Asia Pacific

**AU – Australia,** Castle Hill

Tel: +61 (0)2-9634 7777

**CN – China,** Shanghai

Tel: +86 21 2899 5000

**HK – Hong Kong**

Tel: +852 2428 8008

**ID – Indonesia,** Tangerang

Tel: +62 21 7588 1906

**IN – India,** Mumbai

Tel: +91 22 6513 7081-85

**JP – Japan,** Fujisawa

Tel: +81 (0)4 6635 3050

**KR – South Korea,** Seoul

Tel: +82 2 559 0400

**MY – Malaysia,** Shah Alam

Tel: +60 3 7849 0800

**NZ – New Zealand,** Mt Wellington

Tel: +64 9 574 1744

**SG – Singapore**

Tel: +65 6887 6300

**TH – Thailand,** Bangkok

Tel: +662 186 7000

**TW – Taiwan,** New Taipei City

Tel: +886 2 2298 8987

**VN – Vietnam,** Ho Chi Minh City

Tel: +84 8 3999 1600

## South America

**AR – Argentina,** Buenos Aires

Tel: +54 3327 44 4129

**BR – Brazil,** Cachoeirinha RS

Tel: +55 51 3470 9144

**CL – Chile,** Santiago

Tel: +56 2 623 1216

**MX – Mexico,** Toluca

Tel: +52 72 2275 4200



### EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

### US Product Information Centre

Toll-free number: 1-800-272-7537

www.parker.com

Your local authorized Parker distributor