

# Potable Water Pump

This inline potable water pump is designed to supply a flow of up to six gallons per minute at 18 psi. It is equipped with electromagnetic interface (EMI) filtering, sensor-less locked rotor protection software, and discrete output signals for high-current, high-temperature, and rotor rotation.



## Product Overview & Features

This pump uses single-phase 115V AC at frequencies from 360-800Hz to drive a high-efficiency, brushless DC motor. The pump is mounted in line and uses standard Wiggins flexible coupling-style hydraulic connections.

The pump is mounted via four mounting holes in the feet. A standard military-style connector is used for the electrical connection.

- All wetted surfaces are made up of 316L stainless steel, making this pump compliant to NSF61
- The mechanical design allows recovery from freezing while not in use without permanent damage
- The electronics are housed in a dry cavity by way of a canned rotor design
- The canned rotor design allows for no elimination of rotating shaft seals
- The wetted carbon bearings allow for long-life fluid film design

## Specifications

Application	Commercial aircraft
Rated flow	6 GPM at 18 psig
Maximum pressure	42.6 psig at 0 GPM
Fluid type	Potable water
Fluid temperature	40°F to 130°F
Ambient temperature	40°F to 130°F
Voltage	115 VAC single-phase
Frequency	360-800 Hz
Maximum current	Maximum 4 amps
Total weight	6.5 pounds

## Applications

- Boeing 787
- Bombardier C Series

## Contact Information

Parker Hannifin Corporation  
 Parker Aerospace  
**Fluid Systems Division**  
 3580 Shaw Boulevard  
 Naples, Florida 34117-8408  
 Phone: (239) 304-1000  
 Fax: (239) 304-1065  
[www.parker.com](http://www.parker.com)