


▶ HRU-1000 Interface Drawing ^(a)



1. NO RESTRICTIONS ON ORIENTATION FOR MOUNTING OR OPERATION.
2. STANDARD 1/2 ATR SHORT CASE SPECIFICATIONS. (ARINC 404A)
3. SEGREGATION OF INLET AND OUTLET AIRFLOW RECOMMENDED TO AVOID RECIRCULATION OF HEATED OUTLET AIRFLOW.

01	PAO/JET FUEL
02	EGW/PGW
03	HFE/FLOURINERT
04	RESERVED
05	COOLANOL

For more information, contact:
Parker Advanced Cooling Systems
 9200 Tyler Boulevard
 Mentor, Ohio 44060
 USA

Phone and fax numbers:
 USA: (877) 912-COOL (2665)
 Int'l: +1 (440) 954-8100
 Fax: +1 (440) 954-8111

^(a) Parker Hannifin Corporation reserves the right to modify this drawing at any time without notice.