

**DRYER DATA SHEET**  
**Refrigerant Dryers**

<b>MODEL DATA</b>				
1	Manufacturer	Parker		
2	Date	3/28/2016		
3	Model Number	PNC500		
4	Cycling/Non-Cycling	Non- Cycling		
5	Refrigerant Type	R404A		
	<b>DESCRIPTION</b>	<b>FULL FLOW</b>	<b>10% FLOW</b>	<b>UNITS</b>
6	Tested Flow <sup>a</sup>	500	50	scfm <sup>b</sup>
7	Outlet Pressure Dewpoint	39	39	°F
8	Pressure Drop	2.6	0.2	psi(d)
9	Total Dryer Input Power	3.64	3.17	kW
10	Specific Package Power <sup>c</sup>	.73	6.34	kW/100 scfm

Notes:

- a. Dryer ratings at the following inlet conditions to the dryer (as per adopted CAGI Standard ADF 100):

Inlet Compressed Air Temperature:	100°F (37.78°C)
Inlet Compressed Air Pressure:	100 psig (6.9 Bar)
Max. Ambient Air Temperature:	100°F (37.78°C)
Inlet Compressed Air Relative Humidity	100% (Saturated)

- b. SCFM defined as the volume of free air in cubic feet per minute measured at 14.5 psia (1.0 Bar), 68°F (20°C) temperature and 0% R.H. (0 WVP).

- c. (Total Dryer Input Power/tested flow) x 100



This form was developed by the Compressed Air and Gas Institute for the use of its members. CAGI has not independently verified the reported data.

Consult the CAGI website, [www.cagi.org](http://www.cagi.org), for a list of participants in the third party verification program.

Form Number REF 010