



MATERIAL REPORT

Date: 7/12/2006

TITLE: General evaluation of Parker low-swell fluorocarbon compound V1274-80.

PURPOSE: Test compound V1274-80 for resistance to various acids and bases.

CONCLUSION: Parker's low-swell fluorocarbon compound V1274-80 offers excellent resistance to acids and hot water.

Temperature Range: -15 to 400°F

Recommended For: Oils and greases made from petroleum or synthetic hydrocarbon base stock, silicone fluids, aromatic fuels and solvents, chlorinated hydrocarbon solvents, water, steam, alcohols, concentrated strong acids, ozone and weathering.

Not Recommended For: Automotive brake fluid, commercial aircraft hydraulic fluid, polar solvents (MEK, acetone, etc.)

Parker O-Ring Division
2360 Palumbo Drive
Lexington, Kentucky 40509
(859) 269-2351

REPORT DATA

Date: 7/12/2006
Compound: V1274-80

<u>Original Physical Properties</u>	<u>ASTM Test Method</u>	<u>Results (Platen)</u>
Hardness, Shore A	D2240	82
Tensile Strength, psi	D412	1845
Elongation at Break, %	D412	257
Modulus @ 100% Elongation, psi	D412	626
Fluid Resistance, Concentrated Sulfuric Acid		
<u>70 Hrs. @ 73° F</u>		
Hardness Change, pts.	D471	+1
Tensile Strength Change, %	D471	-16
Elongation Change, %	D471	-12
Modulus @ 100% change, %	D471	-7
Volume Change, %	D471	+2
Compression set, %	D395 Method B	32
Fluid Resistance, Concentrated Nitric Acid		
<u>70 Hrs. @ 73° F</u>		
Hardness Change, pts.	D471	+1
Tensile Strength Change, %	D471	-3
Elongation Change, %	D471	+17
Modulus @ 100% change, %	D471	-18
Volume Change, %	D471	+10
Compression set, %	D395 Method B	36
Fluid Resistance, Concentrated Ammonium Hydroxide		
<u>168 Hrs. @ 73° F</u>		
Hardness Change, pts.	D471	+2
Tensile Strength Change, %	D471	-9
Elongation Change, %	D471	+12
Modulus @ 100% change, %	D471	-12
Volume Change, %	D471	+4
Compression set, %	D395 Method B	35
Fluid Resistance, Dilute Phosphoric Acid		
<u>168 Hrs. @ 73° F</u>		
Hardness Change, pts.	D471	+3
Tensile Strength Change, %	D471	+13
Elongation Change, %	D471	+27
Modulus @ 100% change, %	D471	-3
Volume Change, %	D471	0
Compression set, %	D395 Method B	35
Fluid Resistance, Concentrated Hydrochloric Acid		
<u>168 Hrs. @ 73° F</u>		
Hardness Change, pts.	D471	+1
Tensile Strength Change, %	D471	+18
Elongation Change, %	D471	+26
Modulus @ 100% change, %	D471	-1
Volume Change, %	D471	+3
Compression set, %	D395 Method B	19

Fluid Resistance, Distilled Water

168 Hrs. @ 212° F

Hardness Change, pts.	D471	+3
Tensile Strength Change, %	D471	-27
Elongation Change, %	D471	-6
Modulus @ 100% change, %	D471	-16
Volume Change, %	D471	+5
Compression set, %	D395 Method B	54

**Purchaser use only. Reproduce only in full. Data pertains to items referenced only.
The recording of false, fictitious or fraudulent statements or entries on this
report may be punishable as a felony under federal law.**