

Lean Solutions

From Design to Completion
with Parker's T-Slot Aluminum Framing (IPS)



ENGINEERING YOUR SUCCESS.

Components for any project

IPS T-slot framing provides affordable materials for every step of the lean journey.

The challenge. Are you faced with the task of improving lean manufacturing at your location? One of our customers had a strong strategic vision for lean at their facility and needed the right partner to help them make it happen.

We helped them create tools that support their commitment to process improvement. They were able to make the changes they needed with Parker T-Slot Aluminum, quickly and affordably.

The right solution. Parker’s IPS line is constructed from high strength, airplane grade aluminum. Built-in structural reinforcements at key locations deliver a product that’s strong, lightweight, and durable.

Choosing IPS instead of steel or plastic alternatives means easy to configure components with reliable connectivity. If you can think it, we can design it.

The right partner. The best in lean manufacturing design takes planning beyond improved workflow. We’ll show you how Parker IPS is the right choice to help you manage data, maximize space, improve ergonomics, and increase safety awareness.

Make your designs a reality with Parker.



Team Tracking and Communication Board.




Floor Mounted Safety Communication Sign.



Day by the Hour Boards.

A closer look at IPS

Everything you need to build anything.



Ships installation ready.

The complete line. Structural profile options and all the accessories needed for durable, high performance solutions. Learn more at <http://bit.ly/IPSProducts>.

Best in class. Over 100 smooth, grooveless structural profiles in high-strength aluminum for best-in-class performance. Unique T-slot design for easy connection and modification. Custom fabricated and shipped installation-ready.

Design expertise. The right level of product and engineering expertise for perfect field integration, from the ground up. Save money with the right assembly, and save time with our quick quote turnaround.


Benefits of Aluminum

- Extremely short turnaround times
- No welding, grinding, cleaning, painting, or distortions
- Greatly reduced costs over traditional manufacturing processes
- Flexibility to re-configure as requirements change
- Lightweight
- Easy storage
- Easy fabrication
- Great esthetics


More lean solutions

Examples from our customers.

Track your data.



Organize your parts.



Execute on your new processes.

EM Sales Offices

Australia

Parker Hannifin (Australia) Pty Ltd.
9 Carrington Road
Castle Hill NSW 2154
Australia
Tel: +61 (0) 2 9634-7777
Fax: +61 (0) 2 9634 3749

Brazil

Parker Hannifin Ind. Com Ltda.
Av. Lucas Nogueira Garcez 2181
Esperança
12325-900 Jacareí, SP
Tel: 12 3954 5100
Fax: 12 3954 5262
Email: automation.brazil@parker.com

Canada

Parker Hannifin (Canada) Inc.
160 Chisholm Dr
Milton, Ontario L9T 3G9
Tel: 905-693-3000
Fax: 905-876-1958
Email: miltoncustservice@parker.com

China

Parker Hannifin Motion & Control
(Shanghai) Co., Ltd
280 Yunqiao Rd. Jin Qiao Export
Processing Zone
Shanghai 201206, China
Tel: (86-21) 50312525
Fax: (86-21) 64459717

France

Parker SSD Parvex
8 avenue du Lac
B.P. 249
F-21107 Dijon Cedex
Tel: +33 (0) 3 80 42 41 40
Fax: +33 (0) 3 80 42 41 23

Germany

Electromechanical Europe
Parker Hannifin GmbH & Co KG
Robert-Bosch-Strasse 22
D-77656 Offenburg
Germany
Tel: +49 (0) 781 509 0
Fax: +49 (0) 781 509 98176
Email: em-motion@parker.com

India

Parker Hannifin India Pvt. Ltd
Automation Group-SSD Drives Div.
133 & 151 Developed Plots Estate
Perungudi, Chennai 600 096
Tel: 044-4391-0799
Fax: 044-4391-0700

Italy

Parker Hannifin SpA
Via Gounod 1
20092 Cinsello Balsamo
Milano, Italy
Tel: +39 02 361081
Fax: +39 02 36108400
Email: em-motion@parker.com

Korea

Parker Hannifin Korea
9th Floor KAMCO Yangjae Tower
949-3 Dogok 1-dong Gangnam-gu
Seoul 135-860, Korea
Tel: 82-2-559-0454
Fax: 82-2-556-8187

Mexico

Parker Hannifin de Mexico
Eje uno Norte No.100
Parque Industrial Toluca 2000
Toluca, CP 50100 México
Tel: 52-722-275-4200
Fax: 52-722-279-0316

Singapore

Parker Hannifin Singapore Pte Ltd
11, Fourth Chin Bee Road
Singapore 619702
Tel: (65) 6887 6300
Fax: (65) 6265 5125/6261 4929

Taiwan

Parker Hannifin Taiwan Co., Ltd
No. 40, Wuchiuan 3rd Road
Wuku Industrial Park
Taipei County, Taiwan 248
ROC
Tel: 886 2 2298 8987
Fax: 886 2 2298 8982

Thailand

Parker Hannifin (Thailand) Co., Ltd.
1265 Rama 9 Road
Suanluang, Bangkok 10250
Thailand
Tel: (66) 2 186 7000
Fax: (66) 2 374 1645

UK

Parker Hannifin Ltd.
Tachbrook Park Drive
Tachbrook Park
Warwick CV34 6TU
Tel: +44 (0) 1926 317970
Fax: +44 (0) 1926 317980

USA

Parker Hannifin Electromechanical
& Drives Division Main Office
9225 Forsyth Park Drive
Charlotte NC 28273 USA
Tel: (704) 588-3246
800-358-9070
Fax: (704) 588-3249
Email: emn_support@parker.com

Parker Hannifin Corporation Electromechanical Automation Div.

135 Quadral Drive
Wadsworth, OH 44281 USA
Tel: 800.333.4932 or 330-335-6740
Fax: 330.334.2350

5500 Business Park Drive
Rohnert Park, CA 94928
Tel: 800.358.9070
Fax: 707.584.8029

Email: ipsquotes@parker.com or emn_support@parker.com

