




Packaged Drives *Express* Program

Complete packaged drives *when you need them...*



Choose your drive.....then choose your options

AC890PX
 DC590+ AC30V
AC890 AC690+
AC650V **AC650**



D/B Circuit breaker
Reactor
Keypad **Enclosure**
 Input contactor
Dushbuttons **Speed pot**
 Output contactor
 HVAC features **communications**



**Custom Packaged Drive
 shipped in 2 weeks!**

Your Parker SSD territory manager can provide pricing. 2 week delivery is based on AC drive ratings through 150 HP or DC drive ratings through 100 HP, with options defined by program. Units through 500 HP are available with 2-4 week lead time.

Parker Hannifin - SSD Drives Division
 9225 Forsyth Park Dr.
 Charlotte, NC 28273 USA
 Phone 704-588-3246 Fax 704-588-3249
 E-mail info.us.ssd@parker.com www.parker.com/ssdusa



Packaged Drives *Express* Quote Request Form

Company Info:

Company Name: _____ Contact: _____
Address: _____
City: _____ Zip/Postal Code: _____ Country: _____
Phone: _____ Fax: _____ E-mail: _____

Plant Power:

230VAC 460VAC 575VAC (AC890PX only) 690VAC (AC890PX only)

Drive Series:

AC650 AC650V AC650G AC30V AC690+ AC890 AC890PX DC590+

Duty (AC drives only):

Constant Torque/Heavy Duty Variable Torque/Standard Duty

Rating:

_____ HP _____ Full Load Amps (if known) For DC Drive: Field Volts _____ Amps _____

Feedback capability:

Encoder _____ PPR Resolver (AC890 only) Endat (AC890 only)
 Tachometer (DC Drives only) _____ V/1000 RPM

Communications (subject to availability):

RS232/RS485/Modbus RTU EtherNet/IP Modbus/TCP
 Profibus – DP ControlNet Modbus Plus
 Lonworks CanOpen DeviceNet
 FireWire IEEE1394A FireWire IEEE1394B Link

Options:

Circuit breaker Input contactor Output contactor
 Output reactor (for motor leads >50m) Dynamic braking resistor HVAC Package (HVAC10)
 AC line reactor (Includes 3-contactor bypass, disconnect, overload, 115V transformer)

Operator devices:

6901 keypad, door mounted E-Stop pushbutton Start p/b (illuminated)
 Stop pushbutton Reset p/b (illuminated) Jog Fwd pushbutton
 Jog Rev pushbutton Auto/Man selector switch Fwd/Rev selector switch
 Indicator light, Power On Indicator light, Healthy Indicator light, Run
 Speed pot, 10-turn Speed pot, 1-turn

(Maximum of 6 operator devices OR keypad may be chosen)

Requested Lead Time: _____ **Days**

Additional Comments:

Return this form to your Parker SSD territory manager by fax or e-mail. You will receive verification that your configuration is valid, and a price and confirmation of lead time within 48 hours. OR, send to info.us.ssd@parker.com or fax (704) 588-4806