



SmogHog® Model MSH Compact Machine Mount Mist Collector

SmogHog is the most recognized name for effective removal of mist and smoke within the metalworking industry. Our electrostatic precipitators (ESPs) have been cleaning the air and recycling machining fluids for companies around the world for nearly five decades. The SmogHog model MSH is a self-contained mist collector that can be mounted directly onto machining centers or locally ducted. Mists, fumes and smoke generated from oil and water based coolants are drawn into the system and then subjected to a highly efficient multi-stage filtration process including a coalescing pre-filter and ESP collection cell(s). Clean air is then recirculated back into the plant for a cleaner, healthier work environment.

SmogHog Benefits

- High Filtration Efficiency. Keeps air clean in your factory and process running at peak performance with more than 99% removal efficiency by mass and greater than 90%* particle removal of 0.3 μm liquid particles (* independently verified in accordance with EN 1822-5).
- Life Cycle Cost Advantages. Low airflow resistance leads to energy savings and reduced operational costs. Washable filters eliminate the need for costly replacement filters and associated disposal costs.
- Reduce Operational Expenses. The Mist-Stop Coalescing pre-filter, high capacity collection cell(s) and variable speed airflow controls work to extend service intervals reducing production downtime and operational expenses.
- Flexible Configurations. Horizontal and vertical airflow orientations, single or multiple ESP passes and full line of accessories allows systems to be configured to match your unique application.
- Ease of Installation. The compact design allows the system to be conveniently installed directly onto machining centers or into tight spaces.



SmogHog MSH-05-V



SmogHog MSH-11-H



© 2018 Parker Hannifin Corporation



Parker Hannifin Corporation

Industrial Gas Filtration and Generation Division
4087 Walden Avenue
Lancaster NY 14086 USA
Ph: 800-252-4647
Ph: 513-891-0400
smoghog@parker.com






SmogHog® Model MSH Compact Machine Mount Mist Collector

How the Model MSH Works

Different than centrifugal, bag or box filters that remove only the largest particles, ESP electrically charges both large and microscopic contaminants, and then strips them from the air stream collecting on grounded collection plates. The resulting discharged air leaves virtually no oil mist, smoke or hazardous particle untouched, releasing only clean air from the system to help you comply with even the strictest federal, state and local environmental standards and keep your workers safe.

SmogHog technology ensures constant airflow, unlike barrier filters that can plug and become ineffective. Additionally, you will save operational costs with this technology, the ESP cells are washable, eliminating otherwise costly filter replacements and disposal concerns, making your factory cleaner and greener.



SmogHog MSH Unit Specifications

Model	ESP Passes	Airflow Direction	Nominal Airflow CFM (m³/hr)		Dimensions nches (cm) Width		Weight lb (kg)	Sound Level** dBA	Blower Size HP (kW)	Supply Power	FLA
MSH-05-H	1	Horizontal*	500 (850)	16.4 (42)	27.5 (70)	15.4 (39)	115 (52)	64.9	0.25 (0.2)	115V / 1PH / 60 Hz.	2.3
MSH-05-M-H	2			16.4 (42)	41.9 (106)	15.4 (39)	175 (79)				2.9
MSH-05-V	1	Vertical		29.9 (76)	16.4 (42)	15.4 (39)	115 (52)				2.3
MSH-05-M-V	2			44.5 (113)	16.4 (42)	15.4 (39)	175 (79)				2.9
MSH-11-H	1	· Horizontal*	- 1,100 (1,870)	22.5 (57)	30 (76)	22.4 (57)	192 (87)	73.5	1.45 (1.1)	230 V / 1 PH / 60 Hz.	5.0
MSH-11-M-H	2			22.5 (57)	44.6 (113)	22.4 (57)	275 (125)				5.3
MSH-11-V	1	Vertical		32.3 (82)	22.5 (57)	22.4 (57)	192 (87)				5.0
MSH-11-M-V	2			46.9 (119)	22.5 (57)	22.4 (57)	275 (125)				5.3

- * Horizontal units available in left to right or right to left airflow arrangements
- ** Sound level at 5'

Options and Accessories

- 3-phase power adaptors
- Machine mount kits
- 6, 8, 10 and 12" inlet collars (horizontal only)
- Flexible duct and clamps
- Vibration isolation kit
- High energy power supply

- Drain loop assembly
- Drain bottle
- Power cord
- · Remote power switch
- Custom paint

© 2018 Parker Hannifin Corporation



Parker Hannifin Corporation Industrial Gas Filtration and Generation Division 4087 Walden Avenue

Lancaster NY 14086 USA Ph: 800-252-4647 Ph: 513-891-0400 smoghog@parker.com

ENGINEERING YOUR SUCCESS.

PH1810-002