



Products for Aviation Fuel Handling




ENGINEERING YOUR SUCCESS.

The Aerospace Filtration Division (AFD) of Parker Hannifin manufactures a wide range of best in class Parker Velcon filtration and separation solutions and fuel condition monitoring products for use in assuring clean dry aviation fuel.

As the global leader in bulk aviation fuel filtration, Parker AFD proprietary products range from micronic filters, fiberglass coalescers, separators, water absorbent cartridges, and clay canisters designed to meet required industry standards. This includes

a complete line of cartridges qualified to the latest editions of EI specifications: EI 1581, EI 1583, EI 1590 as well as housings that meet best in class EI 1596 requirements.

TYPICAL DISTRIBUTION SYSTEM FOR CLEAN DRY AVIATION FUEL



- DPM™ – Differential Pressure Module monitors differential pressure of filter monitor or filter water separator vessels
- FDPM® MKII – Flow Differential Pressure Module, Mark II provides automatic reporting of flow corrected differential

- VCA® – Velcon Contaminant Analyzer for real-time fuel quality analysis in the field.

- VCA-CV – The VCA combined with a Cla-Val valve.




1 Filter Water Separator

Parker Velcon Filter Water Separators are two-stage vessels designed to remove dirt and separate water from aviation fuel at refineries, product terminals, fuel farms, and on refueling vehicles.

They continuously coalesce and separate water, which collects in the vessel sump where it can be drained. Parker Velcon Filter/Separators have passed numerous tests qualifying them to the latest EI 1581 edition. Construction is to ASME Code and EI1596 Specifications. Units qualified to military specifications are also available.

VESSELS

- Fixed Installations
 - VV Vertical Vessels
 - HV Horizontal Vessels
- Mobile Fueling Equipment
 - HV Horizontal Vessels
 - HVS Horizontal Vessels




COALESCER CARTRIDGES

Used as a first-stage cartridge in Filter/Separators. Remove particulates and coalesce water into large water droplets. Available in open-ended or threaded base designs.

SEPARATOR CARTRIDGES

Second stage cartridges in Filter/Separators repel coalesced water drops which then collect in the sump for easy removal. Available in Teflon® Coated Screen, Synthetic Media or Pleated Paper Media.



2 Water Absorption

Parker Velcon Water Absorbent Filters are single-stage filter vessel systems which remove water and dirt from Avgas and Jet Fuel and provide protection from water at the point of final fuel filtration. When a monitor system's water holding capacity is reached, the flow of fuel is restricted. Units meet EI 1596 Specifications. Construction is to ASME Code Section VIII.



VESSELS

- Fixed or Mobile Units
 - AHM or HM Horizontal Monitor Vessels
 - AVM or VM Vertical Monitor Vessels
- High Capacity Aquacon® Units
 - HA Horizontal Vessels
 - VA Vertical Vessels

CDF FUEL MONITOR

Absorb water and filter particulate from Avgas and Jet Fuel. Provide protection against water slug transmission.

AQUACON® FUEL MONITOR

Filter particulate matter and absorb water with great efficiency. Water capacity is approximately 40 times greater than 2" diameter monitor cartridges. Also provide protection against water slugs.



3 Micronic Filtration

Micronic vessels offer economical particulate prefiltration upstream of clay units or Filter/Separators. Units available to meet EI1596 Specifications. Construction is to ASME Code Section VIII.

VESSELS

- Fixed Installations
 - VF, VFAP (EI1596) Vertical Filter Vessels
 - HF, HFAP (EI1596) Horizontal Filter Vessels



PLEATED FILTER

Corrugated pleated media with large surface area for filtration of particulate contaminants. Available in open-ended or threaded base designs.

FIBERGLASS FILTER

Progressively finer layers of fiberglass filter colloidal or slimy contaminants.

COMMISSIONING CARTRIDGES

Commissioning Cartridges (FI Series) can be used in place of coalescers to remove heavy solid contaminants during start up.



4 Surfactant Removal

Clay Vessels & Elements are placed upstream of F/S vessels prior to pre-filtration to remove surfactants and protect coalescer and separator elements. Construction is to ASME Code Section VIII.

Vessels

- Fixed Installations
 - VC Clay Element Vessels

Clay Cartridges

Clay canisters use a low volatile matter (LVM), 60-90 mesh, with a superior water tolerant Attapulgite clay that has a lower tolerance for aggregating. The clay cartridges remove surfactants from jet fuel and other petroleum products.



5 Fuel Condition Monitoring & Control

The Parker Velcon line of fuel condition monitoring solutions range from fixed on-line systems such as the Flow Differential Pressure Module (FDPM®) MK-II to portable in-field systems such as the icountACM20. All are designed to provide reliable accurate results in very short time.

The icount particle analyzers are designed for monitoring and testing of solid contaminants. Parker AFD offers four types of systems depending on your application needs. All products can be used as an on-line monitoring system or be completely portable while providing real-time or immediate results with the capability of storing of test results.

Water in Fuel (WIF™) Detector

SIMPLE, ACCURATE, AFFORDABLE AND RELIABLE SOLUTION FOR WATER CONTAMINANT DETECTION

Parker Velcon's Water-in-Fuel (WIF™) Sensor is designed to meet Energy Institute (EI) 1598 Specifications for electronic sensors used to monitor fuel contamination including free water and/or particulate matter.

The WIF sensor was created using technologies developed by Parker Velcon for the U.S. military. Utilizing laser light scattering principles, the WIF is designed and calibrated to detect the presence of free water in fuel from 0 to 50 ppm.

The WIF is designed to interface with common meter systems using a 0-20 mA output or can be implemented with a simple secondary control box that can be connected to a "dead man" circuit assuring safe fueling.

When used in conjunction with Parker Velcon aviation fuel filtration solutions, the WIF Sensor can provide for your overall ground fuel handling needs and helps you assure CLEAN DRY FUEL™.

Cost Effective

Simple: Installation • Integration • Operation



Sensing the Future

Hydrokit® Water in Fuel Detection Kit HK Series

DETECT EXCESSIVE FREE WATER IN AVIATION FUEL

The HYDROKIT® is an effective “Go, No-Go” field test designed to periodically check for free water, which is removed to ppm levels by properly operating filter/ separators, Aquacon®, and monitor vessels.



Flow Differential Pressure Module FDPM®-MKII Series

AUTOMATIC CALCULATION OF CORRECTED DIFFERENTIAL PRESSURE FOR VARYING FLOW RATES

The FDPM® MK II builds on its field tested predecessor. Designed to comply with the requirements of industry standards such as A4A 103 and JIG Guidelines, the FDPM® MK II eliminates this normally complicated calculation by automatically calculating the condition of the filters inside a vessel based on the inputs from differential pressure and flow-rate sensors. FDPM® MK II can be used with either mobile or stationary equipment.



Differential Pressure Module DPM™ Series

DIFFERENTIAL PRESSURE MONITORING AND SHUTDOWN SYSTEM

The DPM continuously monitors the differential pressure between the inlet and outlet of a filter monitor or filter water separator vessel in order to evaluate the condition of internal filter elements.

In the event that the filter differential pressure reaches maximum allowable pressure, the industrial strength relay on board the DPM control unit breaks the deadman circuit, immediately terminating the refueling operation. The system can only be overridden/reset by inserting a supervisor key. The DPM can also be placed in an override status in order to conduct the required DP Gauge free movement test.



icountACM20

STATE-OF-THE-ART FUEL CONTAMINATION MONITORING. THE FIRST FULLY FUNCTIONAL PARTICLE COUNTER APPROVED FOR USE ON AVIATION FUELS.

The icountACM20 Portable Particle Counter has been developed from existing technology for monitoring contamination in AVTur and other hydrocarbon fuels, in accordance with Energy Institute (EI) Method IP 564.

In addition, the ACM can also be used to monitor fuels from existing sampling points in locations from refineries, pipelines, distribution terminals, fuel supply storage.



Mission

Parker AFD is committed to being the world's preferred source for the expert aviation filtration solutions we deliver to our customers.

Values

Superior customer service

Profitable growth

Meet or exceed customer expectations

Accountability

Integrity

