

CoolTherm® ME-543 Underfill Encapsulant

Technical Data Sheet

CoolTherm® ME-543 encapsulant is an anhydride-free, thermally conductive, semiconductor grade epoxy underfill product developed for the encapsulation of densely populated area array flip chip devices. It is formulated with the necessary structural strength to handle over-molding processes.

CoolTherm ME-543 encapsulant can be fast cured and is engineered to withstand 260°C peak reflow temperatures of lead-free solders.

Features and Benefits:

High Thermal Conductivity – provides thermal conductivity for applications where superior heat dissipation is required.

Jetable – provides low viscosity for high speed jetting dispense.

Self-Filleting – provides surface tension and viscosity flow properties to achieve full coverage without producing bulky fillet on top of device.

Rapid Flow – formulated to flow consistently without voids while maintaining a fast flow rate; can be used under small or large dies with high-density interconnects and under devices with stand-off heights below 25 micron.

Low Coefficient of Thermal Expansion – minimizes the possibility of cracking during temperature cycling (-40°C to +150°C); provides excellent thermal shock performance.

Good Adhesion – provides good adhesion to laminate, ceramic, solder mask and metal surfaces.

Device Reliability – provides high Tg and high fracture toughness, reducing the amount of thermally induced stress placed on the solder interconnects.

Typical Properties*

Uncured

Appearance	Black Liquid
Viscosity, cP @ 25°C TA Rheometer	21,000
Specific Gravity	2.2
Gel Time, minutes @ 150°C	3
Working Life, hours @ 25°C	36

Cured

Thermal Conductivity, W/m·K	1.2
Coefficient of Linear Thermal Expansion, ppm/°C	
alpha 1	27
alpha 2	95
Glass Transition Temperature (Tg), °C by TMA	135
Die Shear Strength, MPa (psi)	62 (9000)
Storage Modulus, MPa	5500
Moisture Absorption, %	0.7
Volume Resistivity, ohm-cm @ 25°C	>1 x 10 ¹⁵
Extractable Ionic Contaminants, ppm	
Chloride	100
Sodium	10
Potassium	5

*Data is typical and not to be used for specification purposes.



ENGINEERING YOUR SUCCESS.

Application:

Applying – Before use with dispensing equipment, allow encapsulant to be warmed to room temperature (ideally 20-25°C). Thaw encapsulant by placing the syringe in a vertical (upright) position with dispense tip facing downward in an ambient environment. Consult handling instructions** for specific guidelines.

To decrease underfill time, preheat substrate to 100°C prior to encapsulant application.

Mount the syringe onto the dispensing equipment that has been thoroughly cleaned and purge encapsulant through the system until an unbroken flow of encapsulant is extruded. Dispense underfill encapsulant as a corner dot, line or L-shaped extrusion.

Curing – Allow material to cure for 7-20 minutes at 160-165°C. This time-at-temperature profile refers to the time the material should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay material reaching the target temperature.

Material can be cured at temperatures lower than 160°C with a longer duration.

Cleanup – Remove uncured encapsulant using common organic solvents such as acetone or isopropanol.

Shelf Life/Storage:

Shelf life is six months when stored at -40°C in original, unopened container. Syringe must be maintained at -40°C in a vertical (upright) position with the dispense tip facing down. Do not store syringe on its side (horizontally).

This material is shipped and stored frozen. Consult handling instructions** for thawing.

Cautionary Information:

Before using this or any Parker LORD product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

****Handling instructions are available on LORD.com.**

Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker LORD has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker LORD does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

©2022 Parker Hannifin - All Rights Reserved

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

OD DS4024 07/22 Rev.4



Parker LORD
Engineered Materials Group

111 LORD Drive
Cary, NC 27511-7923
USA

phone +1 877 ASK LORD (275 5673)

www.lord.com