

COOLTHERM® SC-6703 THERMALLY CONDUCTIVE SILICONE ENCAPSULANT

Technical Data Sheet

CoolTherm® SC-6703 thermally conductive silicone encapsulant is a two-component system designed to provide thermal conductivity for encapsulating densely packed power units.

Features and Benefits

Low Stress: exhibits low shrinkage and stress on components as it cures.

Environmentally Resistant: provides excellent thermal shock resistance.

UL Rated: meets requirements of UL 94 V-0 standard; provides excellent flame retardancy.

Application

Mixing: Thoroughly mix each component prior to combining resin and hardener. Mix CoolTherm SC-6703 resin with CoolTherm SC-6703 hardener at a 1:1 ratio, by weight. Automatic meter/mix/dispense equipment may be used for high volume production.

Unless a closed-chamber mechanical mixer is used, air may be introduced into the encapsulant system either during mixing or when catalyzing the mixture. Electrical properties of the silicone encapsulant are best when air bubbles and voids are minimized. Therefore, in extremely high voltage or other critical applications, vacuuming may be appropriate.

Applying: Apply silicone encapsulant using automatic meter/mix/dispense equipment.

Avoid applying CoolTherm SC-6703 encapsulant to surfaces that contain cure inhibiting ingredients, such as amines, sulfur, or tin salts. If bonding surface is in question, apply a test patch of CoolTherm SC-6703 encapsulant to the surface and allow it to set for the normal cure time.

Curing: Allow encapsulant to cure for 4 hours at 65°C. This time-at-temperature profile refers to the time the bondline should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay bondline reaching the target temperature.

Shelf Life/Storage

Shelf life of each component is six months when stored at 25°C in original, unopened container. The material must be periodically rotated within its container to maintain maximum shelf life. Settling will occur if not mixed.

Typical Properties*

	SC-6703 Resin	SC-6703 Hardener	Mixed
Appearance	SC-6703 BLK R: Black Liquid SC-6703 WHT R: White Liquid	White Liquid	SC-6703 BLK R/SC-6703 H: Light Gray Liquid SC-6703 WHT R/SC-6703 H: White Liquid
Viscosity, cP @ 25°C	15,000	6000	8000
Specific Gravity ASTM D 1475	2.09	1.91	2.0
Gel Time, minutes @ 66°C	–	–	6
Working Life, hours @ 25°C	–	–	1-2

*Data is typical and not to be used for specification purposes.

Typical Cured Properties**

Thermal Conductivity, W/m·K Hot Disc Transient Method, ISO 22007-2	0.8
Coefficient of Linear Thermal Expansion, ppm/°C ASTM C 864	220
Hardness Shore A	60
Tensile Strength, MPa (psi) ASTM D 412	1.38 (200)
Elongation at Break, % ASTM D 412	80
Volume Resistivity, ohm-cm @ 25°C ASTM D 257	1 x 10 ¹⁴
Dielectric Strength, kV/mm (V/mil) ASTM D 149	19.7 (500)
Dielectric Constant @ 25°C 1 MHz, ASTM D 150	4.25
Dissipation Factor, % @ 25°C 1 MHz, ASTM D 150	0.02

**Data is typical and not to be used for specification purposes.
Cure schedule of 1-2 hours at 65°C.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275-5673
www.parker.com/APS

DS3568 OD 09/26 Rev.7

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2026 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.