

THERMOSET® EP-939 BOARD LEVEL ENCAPSULANT

Technical Data Sheet

Thermoset® EP-939 encapsulant is a black, one-component epoxy specifically designed to meet the needs of coating semiconductor devices on printed circuit boards.

Features and Benefits

Convenient: requires no mixing; provides excellent shelf life stability; prepared under vacuum and contains no entrapped air or solvents.

Environmentally Resistant: provides excellent resistance to thermal shock and moisture.

Fast Cure: quickly cures at 150°C with a void-free, smooth surface.

Outstanding Adhesion: offers a fast elevated temperature cure for outstanding adhesion to a variety of materials.

Application

Applying: Before use with dispensing equipment, allow encapsulant to be warmed to room temperature (ideally 20-25°C). Thaw encapsulant by placing the syringe in a vertical (upright) position with dispense tip facing downward in an ambient environment. Consult handling instructions** for specific guidelines.

**Handling instructions are available on Parker.com.

Typical Properties*

Uncured

Appearance	Black Paste
Viscosity, cP @ 25°C Spindle 6, 10 rpm	37,200
Specific Gravity	1.49
Gel Time, minutes @ 150°C	4
Working Life, month @ 25°C	1

Cured


Coefficient of Linear Thermal Expansion, ppm/°C below Tg, by TMA	45
Glass Transition Temperature (Tg), °C by TMA	125
Hardness Shore D	87-95
Modulus of Elasticity, GPa by DMA	1
Volume Resistivity, ohm-cm @ 25°C	1 x 10 ¹⁵
Dielectric Constant 1 MHz, ASTM D 150	4.0
Dissipation Factor 1 MHz, ASTM D 150	0.01

*Data is typical and not to be used for specification purposes. Data obtained by using a cure schedule of one hour at 150°C. Choice of cure schedule will vary with the application; user must establish optimum cure schedule.

Curing: Allow encapsulant to cure for 20 minutes at 150°C in an elevated temperature circulating air oven or on a hot plate.

Cleanup: Disposable containers and utensils are recommended when working with epoxies. However, when disposable materials are impractical, uncured encapsulant can be removed by cleaning equipment with solvent. Solvent-cleaned utensils should be thoroughly dried before reuse; any remaining solvent can contaminate the next mixture.

Cure Time for Thermoset EP-939 Encapsulant



Shelf Life/Storage

Shelf life is six months when stored between 0° and 5°C in original, unopened container. Do not store containers outdoors or in non-ventilated exterior structures. Store product away from heat sources such as ovens or hot plates. Elevated storage temperatures will shorten product's shelf life.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275-5673
www.parker.com/APS

DS3620 OD 10/24 Rev.4

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2024 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.